

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065055

Luminaire Tested: **GLAN-SA8C-940-U-RBC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1065055  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA8C-940-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 8xLight Square PACKAGE  
90CRI 4000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (112) 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 29420.2 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G4


Input Watts (W): 372.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 4.3 fc  
 Type III - Short - N/A

REPORT NUMBER: P1065055  
CATALOG NUMBER: GLAN-SA8C-940-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 147.3    | 0.0    | 147.3   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 29272.9  | 0.0    | 29272.9 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 29420.2  | 0.0    | 29420.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 11.5    | 0.0       |
| 10°-20°   | 64.6    | 0.2       |
| 20°-30°   | 697.2   | 2.4       |
| 30°-40°   | 2061.8  | 7.0       |
| 40°-50°   | 6144.7  | 20.9      |
| 50°-60°   | 9743.3  | 33.1      |
| 60°-70°   | 8133.3  | 27.6      |
| 70°-80°   | 2508.0  | 8.5       |
| 80°-90°   | 55.8    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 29420.2 | 100.0     |
| 0°-180°   | 29420.2 | 100.0     |



REPORT NUMBER: P1065055


CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 746.3   | 2.5       |                         |      |          |
| FM   | (30°-60°)   | 17897.1 | 60.8      |                         |      |          |
| FH   | (60°-80°)   | 10586.3 | 36.0      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 43.1    | 0.1       |                         |      | G1/100   |
| BL   | (0°-30°)    | 27.1    | 0.1       | B0/110                  |      |          |
| BM   | (30°-60°)   | 52.7    | 0.2       | B0/220                  |      |          |
| BH   | (60°-80°)   | 55.0    | 0.2       | B0/110                  |      | G0/110   |
| BVH  | (80°-90°)   | 12.7    | 0.0       |                         |      | G1/100   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B0-U0-G4**

Type III Short



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° |
|--------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|
| 0°     | 128.9  | 128.9  | 128.9  | 128.9  | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 |
| 2.5°   | 117.8  | 117.8  | 117.8  | 117.8  | 115.6 | 115.6 | 113.4 | 113.4 | 111.2 | 111.2 |
| 5°     | 124.5  | 124.5  | 122.3  | 120.1  | 120.1 | 117.8 | 115.6 | 113.4 | 113.4 | 111.2 |
| 7.5°   | 135.6  | 133.4  | 131.2  | 128.9  | 124.5 | 122.3 | 117.8 | 115.6 | 113.4 | 108.9 |
| 10°    | 149.0  | 144.5  | 140.1  | 135.6  | 131.2 | 126.7 | 122.3 | 120.1 | 115.6 | 113.4 |
| 12.5°  | 166.7  | 160.1  | 151.2  | 144.5  | 140.1 | 133.4 | 128.9 | 124.5 | 117.8 | 113.4 |
| 15°    | 182.3  | 173.4  | 162.3  | 153.4  | 146.7 | 137.8 | 131.2 | 124.5 | 120.1 | 113.4 |
| 17.5°  | 204.5  | 189.0  | 171.2  | 160.1  | 151.2 | 140.1 | 128.9 | 122.3 | 115.6 | 106.7 |
| 20°    | 242.3  | 211.2  | 177.9  | 164.5  | 151.2 | 137.8 | 124.5 | 115.6 | 108.9 | 100.0 |
| 22.5°  | 302.4  | 249.0  | 195.6  | 175.6  | 157.9 | 137.8 | 120.1 | 111.2 | 102.3 | 93.4  |
| 25°    | 418.0  | 322.4  | 226.8  | 200.1  | 173.4 | 146.7 | 120.1 | 108.9 | 100.0 | 88.9  |
| 27.5°  | 555.8  | 413.5  | 269.0  | 231.2  | 195.6 | 157.9 | 120.1 | 106.7 | 95.6  | 82.3  |
| 30°    | 695.9  | 506.9  | 315.7  | 266.8  | 217.9 | 169.0 | 120.1 | 104.5 | 91.2  | 75.6  |
| 32.5°  | 829.3  | 593.6  | 355.7  | 297.9  | 240.1 | 180.1 | 122.3 | 104.5 | 86.7  | 68.9  |
| 35°    | 964.9  | 664.8  | 362.4  | 302.4  | 242.3 | 180.1 | 120.1 | 100.0 | 82.3  | 62.3  |
| 37.5°  | 1138.3 | 744.8  | 349.1  | 289.0  | 231.2 | 171.2 | 113.4 | 95.6  | 77.8  | 57.8  |
| 40°    | 1400.7 | 878.2  | 355.7  | 293.5  | 231.2 | 169.0 | 106.7 | 88.9  | 73.4  | 55.6  |
| 42.5°  | 1885.3 | 1136.1 | 384.6  | 313.5  | 242.3 | 169.0 | 97.8  | 82.3  | 68.9  | 53.4  |
| 45°    | 3259.3 | 1887.5 | 515.8  | 409.1  | 302.4 | 195.6 | 88.9  | 75.6  | 64.5  | 51.1  |
| 47.5°  | 5391.4 | 3159.2 | 927.1  | 715.9  | 506.9 | 295.7 | 86.7  | 75.6  | 64.5  | 51.1  |
| 50°    | 6881.0 | 4024.1 | 1167.2 | 898.2  | 629.2 | 360.2 | 91.2  | 77.8  | 66.7  | 53.4  |
| 52.5°  | 6869.9 | 4086.3 | 1300.6 | 998.2  | 698.1 | 395.7 | 95.6  | 82.3  | 71.1  | 57.8  |
| 55°    | 6107.3 | 3717.3 | 1325.1 | 1018.3 | 713.7 | 406.9 | 102.3 | 88.9  | 75.6  | 62.3  |
| 57.5°  | 5104.6 | 3157.0 | 1209.5 | 936.0  | 664.8 | 391.3 | 117.8 | 102.3 | 88.9  | 73.4  |
| 60°    | 4037.4 | 2490.0 | 942.7  | 744.8  | 549.1 | 351.3 | 155.6 | 135.6 | 117.8 | 97.8  |
| 62.5°  | 2788.0 | 1805.3 | 822.6  | 660.3  | 500.2 | 337.9 | 177.9 | 157.9 | 140.1 | 120.1 |
| 65°    | 1972.0 | 1358.4 | 742.6  | 604.7  | 469.1 | 331.3 | 193.4 | 171.2 | 151.2 | 128.9 |
| 67.5°  | 1474.0 | 1080.5 | 684.8  | 566.9  | 449.1 | 331.3 | 213.4 | 186.8 | 162.3 | 135.6 |
| 70°    | 1129.4 | 887.1  | 642.5  | 546.9  | 453.5 | 357.9 | 262.3 | 224.5 | 189.0 | 151.2 |
| 72.5°  | 920.4  | 758.1  | 593.6  | 524.7  | 455.8 | 386.8 | 317.9 | 269.0 | 220.1 | 169.0 |
| 75°    | 762.6  | 649.2  | 535.8  | 478.0  | 422.4 | 364.6 | 306.8 | 262.3 | 220.1 | 175.6 |
| 77.5°  | 506.9  | 462.4  | 415.7  | 382.4  | 349.1 | 313.5 | 280.1 | 242.3 | 206.8 | 169.0 |
| 80°    | 177.9  | 171.2  | 164.5  | 177.9  | 191.2 | 204.5 | 217.9 | 191.2 | 166.7 | 140.1 |
| 82.5°  | 26.7   | 24.5   | 22.2   | 24.5   | 26.7  | 28.9  | 31.1  | 33.3  | 35.6  | 37.8  |
| 85°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°   | 32.5° | 35°   | 37.5° | 40°   | 42.5° | 45°   | 47.5° | 50°   |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0 | 0°     | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 |
| 0.0 | 2.5°   | 108.9 | 108.9 | 106.7 | 106.7 | 106.7 | 104.5 | 104.5 | 102.3 | 102.3 | 102.3 |
| 0.0 | 5°     | 106.7 | 106.7 | 104.5 | 102.3 | 100.0 | 100.0 | 97.8  | 95.6  | 95.6  | 93.4  |
| 0.0 | 7.5°   | 104.5 | 102.3 | 100.0 | 97.8  | 95.6  | 93.4  | 91.2  | 88.9  | 88.9  | 86.7  |
| 0.0 | 10°    | 106.7 | 102.3 | 100.0 | 95.6  | 93.4  | 91.2  | 86.7  | 84.5  | 82.3  | 82.3  |
| 0.0 | 12.5°  | 102.3 | 100.0 | 95.6  | 91.2  | 88.9  | 84.5  | 82.3  | 77.8  | 75.6  | 75.6  |
| 0.0 | 15°    | 102.3 | 97.8  | 91.2  | 86.7  | 82.3  | 80.0  | 75.6  | 71.1  | 68.9  | 66.7  |
| 0.0 | 17.5°  | 95.6  | 91.2  | 84.5  | 80.0  | 75.6  | 71.1  | 66.7  | 62.3  | 60.0  | 57.8  |
| 0.0 | 20°    | 86.7  | 82.3  | 75.6  | 68.9  | 64.5  | 60.0  | 55.6  | 51.1  | 48.9  | 46.7  |
| 0.0 | 22.5°  | 77.8  | 73.4  | 66.7  | 60.0  | 55.6  | 51.1  | 44.5  | 40.0  | 37.8  | 33.3  |
| 0.0 | 25°    | 73.4  | 66.7  | 60.0  | 53.4  | 46.7  | 42.2  | 35.6  | 28.9  | 24.5  | 20.0  |
| 0.0 | 27.5°  | 62.3  | 55.6  | 48.9  | 42.2  | 35.6  | 28.9  | 22.2  | 15.6  | 11.1  | 8.9   |
| 0.0 | 30°    | 53.4  | 46.7  | 40.0  | 33.3  | 24.5  | 17.8  | 11.1  | 2.2   | 2.2   | 2.2   |
| 0.0 | 32.5°  | 44.5  | 37.8  | 28.9  | 22.2  | 17.8  | 11.1  | 6.7   | 0.0   | 0.0   | 0.0   |
| 0.0 | 35°    | 35.6  | 28.9  | 20.0  | 13.3  | 11.1  | 6.7   | 4.4   | 0.0   | 0.0   | 0.0   |
| 0.0 | 37.5°  | 31.1  | 24.5  | 15.6  | 6.7   | 4.4   | 4.4   | 2.2   | 0.0   | 0.0   | 0.0   |
| 0.0 | 40°    | 28.9  | 20.0  | 11.1  | 2.2   | 2.2   | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 42.5°  | 28.9  | 20.0  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 45°    | 28.9  | 20.0  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 47.5°  | 28.9  | 20.0  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 50°    | 31.1  | 22.2  | 11.1  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 52.5°  | 35.6  | 26.7  | 17.8  | 8.9   | 6.7   | 4.4   | 2.2   | 0.0   | 0.0   | 0.0   |
| 0.0 | 55°    | 44.5  | 40.0  | 33.3  | 28.9  | 22.2  | 15.6  | 6.7   | 0.0   | 0.0   | 0.0   |
| 0.0 | 57.5°  | 57.8  | 57.8  | 55.6  | 53.4  | 40.0  | 26.7  | 13.3  | 0.0   | 0.0   | 0.0   |
| 0.0 | 60°    | 77.8  | 77.8  | 77.8  | 77.8  | 57.8  | 40.0  | 20.0  | 0.0   | 0.0   | 0.0   |
| 0.0 | 62.5°  | 95.6  | 91.2  | 84.5  | 80.0  | 60.0  | 40.0  | 20.0  | 0.0   | 0.0   | 0.0   |
| 0.0 | 65°    | 95.6  | 86.7  | 75.6  | 64.5  | 48.9  | 33.3  | 15.6  | 0.0   | 0.0   | 0.0   |
| 0.0 | 67.5°  | 88.9  | 71.1  | 51.1  | 33.3  | 24.5  | 17.8  | 8.9   | 0.0   | 0.0   | 0.0   |
|     | 70°    | 88.9  | 62.3  | 35.6  | 8.9   | 6.7   | 4.4   | 2.2   | 0.0   | 0.0   | 0.0   |
|     | 72.5°  | 88.9  | 60.0  | 28.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 75°    | 97.8  | 66.7  | 33.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 77.5°  | 97.8  | 66.7  | 33.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 80°    | 86.7  | 57.8  | 28.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 82.5°  | 28.9  | 20.0  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°   | 77.5° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0   | 0°     | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 |
| 0.0   | 2.5°   | 100.0 | 100.0 | 100.0 | 97.8  | 97.8  | 97.8  | 97.8  | 95.6  | 95.6  | 95.6  |
| 0.0   | 5°     | 91.2  | 91.2  | 88.9  | 88.9  | 86.7  | 86.7  | 84.5  | 84.5  | 82.3  | 82.3  |
| 0.0   | 7.5°   | 84.5  | 82.3  | 82.3  | 80.0  | 77.8  | 77.8  | 75.6  | 75.6  | 73.4  | 71.1  |
| 0.0   | 10°    | 77.8  | 75.6  | 75.6  | 73.4  | 71.1  | 68.9  | 68.9  | 66.7  | 64.5  | 62.3  |
| 0.0   | 12.5°  | 71.1  | 68.9  | 66.7  | 64.5  | 62.3  | 60.0  | 60.0  | 57.8  | 55.6  | 53.4  |
| 0.0   | 15°    | 62.3  | 60.0  | 57.8  | 55.6  | 53.4  | 51.1  | 51.1  | 48.9  | 46.7  | 44.5  |
| 0.0   | 17.5°  | 53.4  | 51.1  | 51.1  | 48.9  | 46.7  | 44.5  | 42.2  | 37.8  | 35.6  | 33.3  |
| 0.0   | 20°    | 40.0  | 37.8  | 35.6  | 33.3  | 31.1  | 26.7  | 24.5  | 20.0  | 15.6  | 13.3  |
| 0.0   | 22.5°  | 26.7  | 22.2  | 20.0  | 15.6  | 11.1  | 8.9   | 6.7   | 2.2   | 0.0   | 0.0   |
| 0.0   | 25°    | 8.9   | 6.7   | 4.4   | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°   | 87.5° | 90°   | 92.5° | 95°   | 97.5° | 100°  | 102.5° | 105°  |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 0.0 | 0°     | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9 | 128.9  | 128.9 |
| 0.0 | 2.5°   | 93.4  | 93.4  | 93.4  | 91.2  | 91.2  | 91.2  | 91.2  | 91.2  | 91.2   | 91.2  |
| 0.0 | 5°     | 80.0  | 80.0  | 80.0  | 77.8  | 77.8  | 75.6  | 75.6  | 75.6  | 73.4   | 73.4  |
| 0.0 | 7.5°   | 68.9  | 66.7  | 66.7  | 64.5  | 64.5  | 62.3  | 62.3  | 62.3  | 60.0   | 60.0  |
| 0.0 | 10°    | 57.8  | 55.6  | 55.6  | 53.4  | 53.4  | 51.1  | 51.1  | 48.9  | 48.9   | 46.7  |
| 0.0 | 12.5°  | 51.1  | 48.9  | 46.7  | 44.5  | 44.5  | 42.2  | 40.0  | 40.0  | 37.8   | 35.6  |
| 0.0 | 15°    | 40.0  | 37.8  | 35.6  | 33.3  | 31.1  | 28.9  | 26.7  | 26.7  | 24.5   | 22.2  |
| 0.0 | 17.5°  | 26.7  | 22.2  | 20.0  | 17.8  | 17.8  | 15.6  | 13.3  | 11.1  | 8.9    | 6.7   |
| 0.0 | 20°    | 6.7   | 4.4   | 2.2   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 22.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 25°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  |
| 0.0    | 2.5°   | 91.2  | 88.9   | 88.9  | 88.9   | 91.2  | 91.2   | 91.2  | 91.2   | 91.2  | 91.2   |
| 0.0    | 5°     | 73.4  | 71.1   | 71.1  | 71.1   | 71.1  | 71.1   | 71.1  | 71.1   | 71.1  | 71.1   |
| 0.0    | 7.5°   | 60.0  | 57.8   | 57.8  | 57.8   | 57.8  | 55.6   | 55.6  | 55.6   | 55.6  | 55.6   |
| 0.0    | 10°    | 46.7  | 44.5   | 44.5  | 44.5   | 44.5  | 42.2   | 42.2  | 42.2   | 42.2  | 42.2   |
| 0.0    | 12.5°  | 33.3  | 33.3   | 31.1  | 31.1   | 31.1  | 28.9   | 28.9  | 28.9   | 28.9  | 26.7   |
| 0.0    | 15°    | 20.0  | 17.8   | 15.6  | 15.6   | 15.6  | 13.3   | 13.3  | 13.3   | 13.3  | 11.1   |
| 0.0    | 17.5°  | 4.4   | 4.4    | 2.2   | 2.2    | 2.2   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 20°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 22.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 25°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 |
| 0.0  | 2.5°   | 93.4   | 93.4  | 95.6   | 95.6  | 97.8   | 102.3 | 104.5  | 106.7 | 111.2  | 115.6 |
| 0.0  | 5°     | 73.4   | 75.6  | 75.6   | 77.8  | 80.0   | 82.3  | 84.5   | 86.7  | 91.2   | 95.6  |
| 0.0  | 7.5°   | 57.8   | 57.8  | 60.0   | 60.0  | 62.3   | 66.7  | 68.9   | 71.1  | 75.6   | 82.3  |
| 0.0  | 10°    | 44.5   | 44.5  | 46.7   | 46.7  | 48.9   | 53.4  | 55.6   | 57.8  | 62.3   | 68.9  |
| 0.0  | 12.5°  | 28.9   | 31.1  | 31.1   | 33.3  | 35.6   | 40.0  | 42.2   | 44.5  | 48.9   | 53.4  |
| 0.0  | 15°    | 13.3   | 15.6  | 15.6   | 17.8  | 20.0   | 24.5  | 26.7   | 28.9  | 33.3   | 40.0  |
| 0.0  | 17.5°  | 2.2    | 2.2   | 4.4    | 4.4   | 6.7    | 8.9   | 11.1   | 13.3  | 20.0   | 24.5  |
| 0.0  | 20°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 4.4    | 8.9   |
| 0.0  | 22.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 2.2   |
| 0.0  | 25°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 27.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 30°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 32.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 82.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 85°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  |
| 0.0    | 2.5°   | 122.3 | 126.7  | 131.2 | 135.6  | 140.1 | 144.5  | 146.7 | 151.2  | 153.4 | 155.6  |
| 0.0    | 5°     | 104.5 | 108.9  | 115.6 | 120.1  | 124.5 | 128.9  | 133.4 | 135.6  | 137.8 | 140.1  |
| 0.0    | 7.5°   | 91.2  | 95.6   | 102.3 | 106.7  | 111.2 | 115.6  | 120.1 | 124.5  | 126.7 | 128.9  |
| 0.0    | 10°    | 77.8  | 84.5   | 88.9  | 95.6   | 100.0 | 104.5  | 108.9 | 113.4  | 117.8 | 120.1  |
| 0.0    | 12.5°  | 62.3  | 68.9   | 75.6  | 80.0   | 86.7  | 93.4   | 97.8  | 102.3  | 106.7 | 111.2  |
| 0.0    | 15°    | 48.9  | 55.6   | 62.3  | 66.7   | 73.4  | 80.0   | 86.7  | 91.2   | 95.6  | 100.0  |
| 0.0    | 17.5°  | 35.6  | 42.2   | 48.9  | 53.4   | 60.0  | 66.7   | 71.1  | 77.8   | 82.3  | 86.7   |
| 0.0    | 20°    | 17.8  | 24.5   | 31.1  | 37.8   | 44.5  | 51.1   | 55.6  | 62.3   | 66.7  | 71.1   |
| 0.0    | 22.5°  | 2.2   | 8.9    | 15.6  | 20.0   | 26.7  | 33.3   | 37.8  | 44.5   | 48.9  | 53.4   |
| 0.0    | 25°    | 0.0   | 2.2    | 6.7   | 8.9    | 11.1  | 15.6   | 20.0  | 24.5   | 28.9  | 33.3   |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    | 4.4   | 8.9    | 13.3  | 17.8   |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 4.4    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    |
|        | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    | 2.2   | 4.4    |
|        | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 4.4    | 6.7   | 11.1   | 13.3  | 15.6   |
|        | 87.5°  | 0.0   | 2.2    | 4.4   | 6.7    | 8.9   | 13.3   | 17.8  | 22.2   | 24.5  | 26.7   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190°  |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 128.9 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155.6 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.3 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 131.2 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 124.5 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 113.4 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 104.5 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 93.4  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 75.6  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.8  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40.0  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 22.2  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6.7   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 2.2   |        |      |        |      |        |      |        |      |        |      |        |
| 8.9   |        |      |        |      |        |      |        |      |        |      |        |
| 20.0  |        |      |        |      |        |      |        |      |        |      |        |
| 28.9  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 |
| 0.0  | 2.5°   | 157.9  | 157.9 | 157.9  | 157.9 | 155.6  | 155.6 | 155.6  | 153.4 | 153.4  | 151.2 |
| 0.0  | 5°     | 144.5  | 146.7 | 146.7  | 146.7 | 146.7  | 146.7 | 146.7  | 146.7 | 144.5  | 144.5 |
| 0.0  | 7.5°   | 133.4  | 135.6 | 137.8  | 137.8 | 140.1  | 140.1 | 140.1  | 137.8 | 137.8  | 135.6 |
| 0.0  | 10°    | 126.7  | 128.9 | 128.9  | 131.2 | 131.2  | 131.2 | 131.2  | 131.2 | 131.2  | 131.2 |
| 0.0  | 12.5°  | 117.8  | 120.1 | 122.3  | 122.3 | 124.5  | 124.5 | 124.5  | 124.5 | 122.3  | 122.3 |
| 0.0  | 15°    | 106.7  | 111.2 | 113.4  | 115.6 | 115.6  | 117.8 | 117.8  | 117.8 | 117.8  | 117.8 |
| 0.0  | 17.5°  | 97.8   | 102.3 | 104.5  | 106.7 | 106.7  | 108.9 | 108.9  | 111.2 | 111.2  | 111.2 |
| 0.0  | 20°    | 80.0   | 84.5  | 86.7   | 91.2  | 93.4   | 95.6  | 97.8   | 100.0 | 100.0  | 102.3 |
| 0.0  | 22.5°  | 62.3   | 66.7  | 68.9   | 73.4  | 75.6   | 77.8  | 80.0   | 82.3  | 84.5   | 86.7  |
| 0.0  | 25°    | 44.5   | 48.9  | 51.1   | 55.6  | 57.8   | 60.0  | 62.3   | 64.5  | 64.5   | 66.7  |
| 0.0  | 27.5°  | 24.5   | 28.9  | 33.3   | 35.6  | 40.0   | 42.2  | 44.5   | 46.7  | 48.9   | 51.1  |
| 0.0  | 30°    | 11.1   | 13.3  | 15.6   | 20.0  | 22.2   | 24.5  | 26.7   | 31.1  | 33.3   | 35.6  |
| 0.0  | 32.5°  | 0.0    | 0.0   | 2.2    | 6.7   | 8.9    | 11.1  | 13.3   | 15.6  | 15.6   | 17.8  |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.2    | 4.4   | 6.7    | 8.9   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 4.4    | 4.4   | 4.4    | 6.7   | 6.7    | 6.7   | 6.7    | 6.7   | 6.7    | 6.7   |
|      | 82.5°  | 11.1   | 13.3  | 15.6   | 15.6  | 17.8   | 17.8  | 17.8   | 17.8  | 15.6   | 15.6  |
|      | 85°    | 22.2   | 24.5  | 26.7   | 26.7  | 28.9   | 28.9  | 28.9   | 28.9  | 28.9   | 28.9  |
|      | 87.5°  | 31.1   | 33.3  | 35.6   | 35.6  | 37.8   | 37.8  | 37.8   | 37.8  | 37.8   | 37.8  |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 128.9  | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 151.2  | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 144.5  | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135.6  | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 131.2  | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.3  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.8  | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 111.2  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 100.0  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 86.7   | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 68.9   | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 53.4   | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 37.8   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 22.2   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 13.3   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4.4    | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4.4    | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.2    | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.2    | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.2    | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.2    | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.2    | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 6.7    |        |      |        |      |        |      |        |      |        |      |
| 15.6   |        |      |        |      |        |      |        |      |        |      |
| 28.9   |        |      |        |      |        |      |        |      |        |      |
| 37.8   |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  |
| 0.0    | 2.5°   | 149.0 | 149.0  | 146.7 | 146.7  | 146.7 | 146.7  | 146.7 | 149.0  | 151.2 | 151.2  |
| 0.0    | 5°     | 142.3 | 142.3  | 140.1 | 140.1  | 140.1 | 142.3  | 142.3 | 144.5  | 146.7 | 149.0  |
| 0.0    | 7.5°   | 135.6 | 133.4  | 133.4 | 135.6  | 135.6 | 137.8  | 137.8 | 140.1  | 142.3 | 144.5  |
| 0.0    | 10°    | 131.2 | 128.9  | 128.9 | 128.9  | 131.2 | 131.2  | 133.4 | 135.6  | 137.8 | 140.1  |
| 0.0    | 12.5°  | 122.3 | 122.3  | 122.3 | 122.3  | 124.5 | 124.5  | 126.7 | 128.9  | 133.4 | 135.6  |
| 0.0    | 15°    | 117.8 | 115.6  | 115.6 | 115.6  | 115.6 | 117.8  | 117.8 | 122.3  | 126.7 | 128.9  |
| 0.0    | 17.5°  | 108.9 | 108.9  | 106.7 | 106.7  | 108.9 | 108.9  | 111.2 | 115.6  | 120.1 | 122.3  |
| 0.0    | 20°    | 100.0 | 97.8   | 95.6  | 95.6   | 97.8  | 97.8   | 100.0 | 104.5  | 108.9 | 111.2  |
| 0.0    | 22.5°  | 86.7  | 84.5   | 84.5  | 84.5   | 84.5  | 86.7   | 86.7  | 91.2   | 97.8  | 102.3  |
| 0.0    | 25°    | 68.9  | 71.1   | 71.1  | 73.4   | 73.4  | 75.6   | 77.8  | 82.3   | 88.9  | 93.4   |
| 0.0    | 27.5°  | 53.4  | 55.6   | 55.6  | 60.0   | 62.3  | 64.5   | 66.7  | 73.4   | 80.0  | 84.5   |
| 0.0    | 30°    | 40.0  | 42.2   | 44.5  | 46.7   | 51.1  | 55.6   | 60.0  | 66.7   | 73.4  | 77.8   |
| 0.0    | 32.5°  | 24.5  | 28.9   | 31.1  | 35.6   | 40.0  | 44.5   | 48.9  | 55.6   | 64.5  | 71.1   |
| 0.0    | 35°    | 17.8  | 20.0   | 24.5  | 26.7   | 31.1  | 35.6   | 40.0  | 48.9   | 55.6  | 64.5   |
| 0.0    | 37.5°  | 8.9   | 13.3   | 17.8  | 22.2   | 26.7  | 31.1   | 35.6  | 44.5   | 53.4  | 60.0   |
| 0.0    | 40°    | 6.7   | 11.1   | 13.3  | 17.8   | 24.5  | 28.9   | 33.3  | 42.2   | 51.1  | 60.0   |
| 0.0    | 42.5°  | 4.4   | 6.7    | 8.9   | 15.6   | 20.0  | 26.7   | 33.3  | 42.2   | 51.1  | 60.0   |
| 0.0    | 45°    | 4.4   | 4.4    | 6.7   | 13.3   | 20.0  | 28.9   | 35.6  | 44.5   | 51.1  | 60.0   |
| 0.0    | 47.5°  | 4.4   | 6.7    | 8.9   | 17.8   | 22.2  | 28.9   | 35.6  | 42.2   | 51.1  | 57.8   |
| 0.0    | 50°    | 6.7   | 8.9    | 11.1  | 20.0   | 24.5  | 31.1   | 35.6  | 44.5   | 51.1  | 60.0   |
| 0.0    | 52.5°  | 4.4   | 6.7    | 8.9   | 17.8   | 24.5  | 33.3   | 40.0  | 48.9   | 57.8  | 64.5   |
| 0.0    | 55°    | 2.2   | 2.2    | 2.2   | 13.3   | 26.7  | 37.8   | 51.1  | 57.8   | 66.7  | 73.4   |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 8.9    | 26.7  | 42.2   | 57.8  | 66.7   | 75.6  | 82.3   |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 8.9    | 26.7  | 42.2   | 57.8  | 68.9   | 80.0  | 91.2   |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 8.9    | 22.2  | 35.6   | 48.9  | 66.7   | 86.7  | 104.5  |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 6.7    | 17.8  | 28.9   | 40.0  | 66.7   | 93.4  | 117.8  |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 6.7    | 17.8  | 26.7   | 37.8  | 66.7   | 93.4  | 122.3  |
|        | 70°    | 0.0   | 0.0    | 0.0   | 6.7    | 17.8  | 28.9   | 40.0  | 66.7   | 93.4  | 120.1  |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 6.7    | 20.0  | 31.1   | 44.5  | 66.7   | 88.9  | 111.2  |
|        | 75°    | 0.0   | 0.0    | 0.0   | 8.9    | 20.0  | 33.3   | 46.7  | 66.7   | 86.7  | 104.5  |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 6.7    | 20.0  | 31.1   | 44.5  | 64.5   | 84.5  | 102.3  |
|        | 80°    | 6.7   | 4.4    | 4.4   | 11.1   | 20.0  | 28.9   | 37.8  | 57.8   | 80.0  | 100.0  |
|        | 82.5°  | 13.3  | 13.3   | 11.1  | 15.6   | 20.0  | 26.7   | 33.3  | 51.1   | 71.1  | 88.9   |
|        | 85°    | 26.7  | 26.7   | 24.5  | 26.7   | 26.7  | 28.9   | 31.1  | 40.0   | 48.9  | 57.8   |
|        | 87.5°  | 35.6  | 35.6   | 33.3  | 33.3   | 33.3  | 31.1   | 31.1  | 31.1   | 31.1  | 28.9   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245°  |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 128.9 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 153.4 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 151.2 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 146.7 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.3 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.8 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 133.4 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 126.7 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115.6 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 106.7 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.8  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 91.2  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 84.5  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 77.8  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 71.1  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 68.9  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 68.9  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 68.9  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 66.7  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 64.5  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 66.7  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 73.4  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80.0  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 91.2  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.3 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.3 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 144.5 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 149.0 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 146.7 |        |      |        |      |        |      |        |      |        |      |        |
| 133.4 |        |      |        |      |        |      |        |      |        |      |        |
| 124.5 |        |      |        |      |        |      |        |      |        |      |        |
| 122.3 |        |      |        |      |        |      |        |      |        |      |        |
| 120.1 |        |      |        |      |        |      |        |      |        |      |        |
| 106.7 |        |      |        |      |        |      |        |      |        |      |        |
| 66.7  |        |      |        |      |        |      |        |      |        |      |        |
| 28.9  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|
| 0.0  | 0°     | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9 | 128.9  | 128.9  |
| 0.0  | 2.5°   | 155.6  | 157.9 | 157.9  | 160.1 | 162.3  | 164.5 | 164.5  | 166.7 | 166.7  | 166.7  |
| 0.0  | 5°     | 153.4  | 157.9 | 160.1  | 162.3 | 164.5  | 166.7 | 169.0  | 171.2 | 173.4  | 173.4  |
| 0.0  | 7.5°   | 151.2  | 153.4 | 157.9  | 160.1 | 164.5  | 166.7 | 171.2  | 173.4 | 175.6  | 177.9  |
| 0.0  | 10°    | 146.7  | 151.2 | 155.6  | 160.1 | 164.5  | 169.0 | 173.4  | 177.9 | 182.3  | 184.5  |
| 0.0  | 12.5°  | 142.3  | 149.0 | 153.4  | 157.9 | 164.5  | 171.2 | 175.6  | 182.3 | 186.8  | 191.2  |
| 0.0  | 15°    | 140.1  | 144.5 | 151.2  | 155.6 | 164.5  | 173.4 | 180.1  | 189.0 | 197.9  | 204.5  |
| 0.0  | 17.5°  | 133.4  | 142.3 | 149.0  | 155.6 | 164.5  | 175.6 | 184.5  | 193.4 | 206.8  | 220.1  |
| 0.0  | 20°    | 124.5  | 131.2 | 140.1  | 146.7 | 160.1  | 171.2 | 184.5  | 195.6 | 215.7  | 235.7  |
| 0.0  | 22.5°  | 115.6  | 124.5 | 131.2  | 140.1 | 155.6  | 169.0 | 184.5  | 197.9 | 231.2  | 262.3  |
| 0.0  | 25°    | 106.7  | 117.8 | 126.7  | 135.6 | 153.4  | 171.2 | 189.0  | 206.8 | 262.3  | 317.9  |
| 0.0  | 27.5°  | 102.3  | 111.2 | 122.3  | 131.2 | 153.4  | 177.9 | 200.1  | 222.3 | 311.3  | 398.0  |
| 0.0  | 30°    | 95.6   | 106.7 | 115.6  | 126.7 | 155.6  | 184.5 | 213.4  | 242.3 | 378.0  | 513.6  |
| 0.0  | 32.5°  | 88.9   | 100.0 | 111.2  | 122.3 | 160.1  | 197.9 | 233.4  | 271.2 | 449.1  | 624.7  |
| 0.0  | 35°    | 82.3   | 95.6  | 106.7  | 117.8 | 166.7  | 217.9 | 266.8  | 315.7 | 513.6  | 709.2  |
| 0.0  | 37.5°  | 80.0   | 93.4  | 104.5  | 115.6 | 169.0  | 220.1 | 273.5  | 324.6 | 520.2  | 715.9  |
| 0.0  | 40°    | 82.3   | 93.4  | 106.7  | 117.8 | 162.3  | 206.8 | 249.0  | 293.5 | 498.0  | 700.3  |
| 0.0  | 42.5°  | 82.3   | 95.6  | 108.9  | 122.3 | 157.9  | 193.4 | 229.0  | 264.6 | 491.3  | 718.1  |
| 0.0  | 45°    | 80.0   | 93.4  | 106.7  | 120.1 | 153.4  | 184.5 | 217.9  | 249.0 | 531.4  | 811.5  |
| 0.0  | 47.5°  | 77.8   | 91.2  | 104.5  | 117.8 | 151.2  | 184.5 | 217.9  | 251.2 | 687.0  | 1120.5 |
| 0.0  | 50°    | 77.8   | 91.2  | 102.3  | 113.4 | 153.4  | 195.6 | 235.7  | 275.7 | 1000.5 | 1723.0 |
| 0.0  | 52.5°  | 82.3   | 93.4  | 102.3  | 111.2 | 157.9  | 206.8 | 253.5  | 300.1 | 1271.7 | 2241.0 |
| 0.0  | 55°    | 88.9   | 95.6  | 104.5  | 111.2 | 169.0  | 224.5 | 282.4  | 337.9 | 1354.0 | 2370.0 |
| 0.0  | 57.5°  | 97.8   | 104.5 | 111.2  | 117.8 | 189.0  | 260.1 | 329.0  | 400.2 | 1360.6 | 2318.9 |
| 0.0  | 60°    | 108.9  | 117.8 | 124.5  | 131.2 | 206.8  | 284.6 | 360.2  | 435.8 | 1231.7 | 2025.4 |
| 0.0  | 62.5°  | 133.4  | 144.5 | 153.4  | 164.5 | 237.9  | 309.0 | 382.4  | 453.5 | 1022.7 | 1591.9 |
| 0.0  | 65°    | 153.4  | 162.3 | 171.2  | 180.1 | 251.2  | 324.6 | 395.7  | 466.9 | 867.1  | 1267.3 |
| 0.0  | 67.5°  | 157.9  | 166.7 | 173.4  | 182.3 | 255.7  | 329.0 | 400.2  | 473.6 | 742.6  | 1009.4 |
|      | 70°    | 160.1  | 171.2 | 184.5  | 195.6 | 271.2  | 346.8 | 420.2  | 495.8 | 658.1  | 820.4  |
|      | 72.5°  | 153.4  | 175.6 | 195.6  | 215.7 | 286.8  | 355.7 | 426.9  | 495.8 | 611.4  | 727.0  |
|      | 75°    | 153.4  | 184.5 | 213.4  | 242.3 | 295.7  | 346.8 | 400.2  | 451.3 | 540.3  | 629.2  |
|      | 77.5°  | 162.3  | 202.3 | 242.3  | 282.4 | 313.5  | 342.4 | 373.5  | 402.4 | 460.2  | 518.0  |
|      | 80°    | 162.3  | 204.5 | 244.6  | 286.8 | 300.1  | 315.7 | 329.0  | 342.4 | 349.1  | 355.7  |
|      | 82.5°  | 140.1  | 173.4 | 206.8  | 240.1 | 224.5  | 209.0 | 193.4  | 177.9 | 166.7  | 153.4  |
|      | 85°    | 71.1   | 77.8  | 82.3   | 86.7  | 80.0   | 73.4  | 66.7   | 60.0  | 55.6   | 48.9   |
|      | 87.5°  | 28.9   | 28.9  | 26.7   | 26.7  | 26.7   | 26.7  | 24.5   | 24.5  | 24.5   | 24.5   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 128.9  | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 166.7  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 173.4  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180.1  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 189.0  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 197.9  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 215.7  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 237.9  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 273.5  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 349.1  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 473.6  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 658.1  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 891.5  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1113.9 | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1265.0 | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1378.4 | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1491.8 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1714.1 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2158.8 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3290.4 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5040.1 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 6345.2 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 6489.7 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5856.1 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5006.8 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3912.9 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2956.9 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2183.2 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1545.2 |        |        |      |        |      |        |      |        |      |        |      |
| 1149.4 |        |        |      |        |      |        |      |        |      |        |      |
| 835.9  |        |        |      |        |      |        |      |        |      |        |      |
| 629.2  |        |        |      |        |      |        |      |        |      |        |      |
| 353.5  |        |        |      |        |      |        |      |        |      |        |      |
| 160.1  |        |        |      |        |      |        |      |        |      |        |      |
| 46.7   |        |        |      |        |      |        |      |        |      |        |      |
| 22.2   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°    | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   |
| 0.0    | 2.5°   | 166.7   | 164.5   | 164.5   | 162.3   | 160.1   | 157.9   | 155.6   | 153.4   | 151.2   | 149.0   |
| 0.0    | 5°     | 173.4   | 173.4   | 173.4   | 171.2   | 171.2   | 169.0   | 169.0   | 166.7   | 164.5   | 162.3   |
| 0.0    | 7.5°   | 180.1   | 182.3   | 182.3   | 184.5   | 184.5   | 184.5   | 184.5   | 182.3   | 182.3   | 182.3   |
| 0.0    | 10°    | 191.2   | 193.4   | 195.6   | 197.9   | 200.1   | 202.3   | 202.3   | 204.5   | 204.5   | 204.5   |
| 0.0    | 12.5°  | 204.5   | 211.2   | 215.7   | 222.3   | 226.8   | 233.4   | 237.9   | 244.6   | 249.0   | 253.5   |
| 0.0    | 15°    | 224.5   | 235.7   | 249.0   | 260.1   | 271.2   | 286.8   | 304.6   | 320.1   | 335.7   | 360.2   |
| 0.0    | 17.5°  | 253.5   | 289.0   | 324.6   | 357.9   | 393.5   | 471.3   | 549.1   | 624.7   | 702.5   | 815.9   |
| 0.0    | 20°    | 309.0   | 415.7   | 520.2   | 627.0   | 731.5   | 1004.9  | 1276.1  | 1549.6  | 1820.8  | 2112.1  |
| 0.0    | 22.5°  | 433.5   | 695.9   | 958.2   | 1220.6  | 1482.9  | 2054.3  | 2623.4  | 3194.8  | 3764.0  | 4433.2  |
| 0.0    | 25°    | 629.2   | 1111.6  | 1594.1  | 2074.3  | 2556.7  | 3450.5  | 4346.5  | 5240.2  | 6134.0  | 7003.3  |
| 0.0    | 27.5°  | 916.0   | 1654.1  | 2392.2  | 3128.1  | 3866.2  | 5077.9  | 6291.8  | 7503.5  | 8715.2  | 9697.8  |
| 0.0    | 30°    | 1269.5  | 2269.9  | 3270.4  | 4270.9  | 5271.3  | 6649.8  | 8028.2  | 9404.4  | 10782.8 | 11856.6 |
| 0.0    | 32.5°  | 1603.0  | 2828.0  | 4053.0  | 5275.8  | 6500.8  | 8070.4  | 9642.3  | 11211.9 | 12781.5 | 13955.4 |
| 0.0    | 35°    | 1820.8  | 3301.5  | 4784.5  | 6265.1  | 7745.8  | 9444.4  | 11143.0 | 12839.3 | 14537.9 | 15878.5 |
| 0.0    | 37.5°  | 2038.7  | 3748.4  | 5455.9  | 7165.6  | 8873.0  | 10738.3 | 12603.6 | 14469.0 | 16334.3 | 17990.6 |
| 0.0    | 40°    | 2283.3  | 4288.7  | 6291.8  | 8297.2  | 10300.4 | 12510.3 | 14718.0 | 16927.9 | 19135.6 | 21472.2 |
| 0.0    | 42.5°  | 2707.9  | 5184.6  | 7663.6  | 10140.3 | 12617.0 | 15540.6 | 18464.2 | 21385.5 | 24309.1 | 27644.0 |
| 0.0    | 45°    | 3506.1  | 6996.6  | 10489.3 | 13979.8 | 17470.4 | 21343.3 | 25218.4 | 29091.3 | 32964.2 | 37401.9 |
| 0.0    | 47.5°  | 5460.3  | 10262.6 | 15062.6 | 19864.8 | 24664.8 | 28846.8 | 33026.5 | 37208.4 | 41388.2 | 45808.0 |
| 0.0    | 50°    | 8355.0  | 13944.3 | 19533.5 | 25120.6 | 30709.9 | 34493.8 | 38275.6 | 42059.6 | 45841.3 | 50045.5 |
| 0.0    | 52.5°  | 10449.3 | 16272.0 | 22097.0 | 27919.7 | 33742.4 | 37157.3 | 40574.4 | 43989.4 | 47404.3 | 51332.8 |
| 0.0    | 55°    | 10607.2 | 16396.5 | 22188.1 | 27977.5 | 33766.8 | 37197.3 | 40627.8 | 44058.3 | 47488.8 | 51652.9 |
| 0.0    | 57.5°  | 9391.0  | 15133.7 | 20874.2 | 26616.8 | 32357.3 | 36263.6 | 40167.6 | 44073.9 | 47977.9 | 52480.0 |
| 0.0    | 60°    | 7988.2  | 13733.1 | 19475.7 | 25220.6 | 30963.3 | 35463.2 | 39965.3 | 44465.2 | 48965.0 | 53182.5 |
| 0.0    | 62.5°  | 6231.8  | 12141.2 | 18052.9 | 23962.3 | 29871.7 | 34440.5 | 39009.3 | 43575.8 | 48144.6 | 51308.3 |
| 0.0    | 65°    | 4644.4  | 10382.6 | 16120.8 | 21856.8 | 27595.1 | 31254.6 | 34914.0 | 38571.3 | 42230.8 | 44189.5 |
| 0.0    | 67.5°  | 3357.1  | 8306.1  | 13252.8 | 18201.8 | 23148.6 | 25767.6 | 28386.6 | 31003.3 | 33622.3 | 35120.8 |
|        | 70°    | 2269.9  | 5698.2  | 9124.2  | 12552.5 | 15978.6 | 18130.7 | 20285.0 | 22437.1 | 24589.2 | 26612.4 |
|        | 72.5°  | 1571.8  | 3497.2  | 5424.7  | 7350.1  | 9275.4  | 11440.9 | 13604.1 | 15769.6 | 17932.8 | 20073.8 |
|        | 75°    | 1042.7  | 1918.7  | 2796.9  | 3672.8  | 4548.8  | 6151.8  | 7756.9  | 9359.9  | 10962.9 | 12239.0 |
|        | 77.5°  | 740.3   | 1002.7  | 1267.3  | 1529.6  | 1791.9  | 2092.1  | 2394.4  | 2694.6  | 2994.7  | 3450.5  |
|        | 80°    | 351.3   | 384.6   | 418.0   | 449.1   | 482.4   | 591.4   | 700.3   | 809.3   | 918.2   | 1033.8  |
|        | 82.5°  | 166.7   | 180.1   | 193.4   | 204.5   | 217.9   | 229.0   | 240.1   | 251.2   | 262.3   | 251.2   |
|        | 85°    | 44.5    | 44.5    | 46.7    | 46.7    | 46.7    | 46.7    | 46.7    | 46.7    | 46.7    | 44.5    |
|        | 87.5°  | 20.0    | 20.0    | 20.0    | 20.0    | 20.0    | 20.0    | 20.0    | 17.8    | 17.8    | 15.6    |
|        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 128.9   | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 146.7   | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160.1   | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180.1   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 206.8   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 255.7   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 386.8   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 927.1   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 2405.6  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5102.4  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 7872.6  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 10680.5 | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12932.7 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15131.5 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 17219.1 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 19649.1 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 23808.9 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30978.9 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 41839.5 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50227.8 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 54249.7 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55261.3 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55819.3 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 56982.1 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57397.8 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 54474.3 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 46150.4 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 36621.5 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28633.3 |        |      |        |      |        |      |        |      |        |      |        |
| 22214.8 |        |      |        |      |        |      |        |      |        |      |        |
| 13515.2 |        |      |        |      |        |      |        |      |        |      |        |
| 3906.3  |        |      |        |      |        |      |        |      |        |      |        |
| 1149.4  |        |      |        |      |        |      |        |      |        |      |        |
| 237.9   |        |      |        |      |        |      |        |      |        |      |        |
| 42.2    |        |      |        |      |        |      |        |      |        |      |        |
| 15.6    |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   |
| 0.0  | 2.5°   | 144.5   | 142.3   | 140.1   | 137.8   | 135.6   | 131.2   | 131.2   | 128.9   | 128.9   |
| 0.0  | 5°     | 157.9   | 155.6   | 153.4   | 151.2   | 151.2   | 149.0   | 146.7   | 146.7   | 144.5   |
| 0.0  | 7.5°   | 180.1   | 177.9   | 175.6   | 173.4   | 173.4   | 171.2   | 171.2   | 169.0   | 169.0   |
| 0.0  | 10°    | 206.8   | 206.8   | 206.8   | 206.8   | 206.8   | 204.5   | 204.5   | 204.5   | 202.3   |
| 0.0  | 12.5°  | 260.1   | 262.3   | 266.8   | 271.2   | 277.9   | 277.9   | 277.9   | 275.7   | 275.7   |
| 0.0  | 15°    | 411.3   | 435.8   | 453.5   | 471.3   | 486.9   | 522.5   | 518.0   | 511.3   | 506.9   |
| 0.0  | 17.5°  | 1040.5  | 1151.6  | 1211.7  | 1269.5  | 1329.5  | 1494.0  | 1467.3  | 1440.7  | 1416.2  |
| 0.0  | 20°    | 2696.8  | 2988.1  | 3181.5  | 3374.9  | 3570.6  | 3879.6  | 3804.0  | 3728.4  | 3652.8  |
| 0.0  | 22.5°  | 5769.4  | 6438.6  | 6729.8  | 7021.0  | 7310.1  | 7683.6  | 7441.2  | 7198.9  | 6958.8  |
| 0.0  | 25°    | 8739.6  | 9608.9  | 10100.3 | 10591.6 | 11080.7 | 11294.1 | 10978.4 | 10660.5 | 10344.8 |
| 0.0  | 27.5°  | 11663.2 | 12645.9 | 13079.4 | 13510.7 | 13944.3 | 14391.1 | 13999.9 | 13606.3 | 13215.0 |
| 0.0  | 30°    | 14006.5 | 15080.4 | 15549.5 | 16016.3 | 16485.5 | 16796.7 | 16392.1 | 15985.2 | 15580.6 |
| 0.0  | 32.5°  | 16305.4 | 17479.3 | 17992.8 | 18506.4 | 19017.7 | 19464.6 | 18966.6 | 18466.4 | 17968.4 |
| 0.0  | 35°    | 18557.5 | 19898.2 | 20605.2 | 21312.1 | 22019.1 | 22434.9 | 21843.5 | 21249.9 | 20658.5 |
| 0.0  | 37.5°  | 21305.5 | 22961.8 | 23753.3 | 24544.8 | 25336.2 | 26094.4 | 25443.0 | 24789.3 | 24137.9 |
| 0.0  | 40°    | 26145.5 | 28482.2 | 29696.1 | 30912.2 | 32126.1 | 33104.3 | 32281.7 | 31459.1 | 30636.5 |
| 0.0  | 42.5°  | 34313.8 | 37648.6 | 39393.9 | 41136.9 | 42882.2 | 44409.6 | 43544.7 | 42679.9 | 41815.0 |
| 0.0  | 45°    | 46277.1 | 50714.7 | 52842.4 | 54967.8 | 57095.5 | 58211.6 | 56966.5 | 55719.3 | 54474.3 |
| 0.0  | 47.5°  | 54645.4 | 59065.3 | 60959.5 | 62853.7 | 64747.9 | 66021.9 | 64498.9 | 62976.0 | 61455.3 |
| 0.0  | 50°    | 58451.7 | 62655.8 | 64556.7 | 66455.4 | 68356.3 | 69367.9 | 67609.3 | 65848.4 | 64089.8 |
| 0.0  | 52.5°  | 59187.6 | 63116.1 | 65383.8 | 67653.7 | 69921.4 | 71273.2 | 69196.7 | 67117.9 | 65041.4 |
| 0.0  | 55°    | 59983.5 | 64147.6 | 66777.8 | 69410.1 | 72040.2 | 73912.2 | 71564.4 | 69214.5 | 66866.7 |
| 0.0  | 57.5°  | 61482.0 | 65984.1 | 68607.5 | 71228.7 | 73852.2 | 75441.8 | 73087.4 | 70730.7 | 68376.3 |
| 0.0  | 60°    | 61615.4 | 65830.7 | 68085.0 | 70341.6 | 72596.0 | 73596.5 | 71344.3 | 69090.0 | 66837.8 |
| 0.0  | 62.5°  | 57638.0 | 60801.6 | 62366.8 | 63932.0 | 65497.2 | 66584.3 | 64234.4 | 61882.1 | 59532.2 |
| 0.0  | 65°    | 48109.1 | 50067.8 | 51315.0 | 52562.3 | 53809.5 | 55105.7 | 52953.5 | 50801.4 | 48649.3 |
| 0.0  | 67.5°  | 38120.0 | 39618.4 | 41261.4 | 42904.4 | 44547.4 | 45932.5 | 44209.5 | 42484.2 | 40761.2 |
|      | 70°    | 30656.5 | 32677.4 | 34525.0 | 36372.5 | 38220.0 | 39353.9 | 37624.2 | 35892.3 | 34162.6 |
|      | 72.5°  | 24355.8 | 26496.8 | 28039.7 | 29580.4 | 31123.4 | 31401.3 | 30129.6 | 28857.9 | 27588.4 |
|      | 75°    | 14789.1 | 16065.3 | 16096.4 | 16125.3 | 16156.4 | 16421.0 | 15367.2 | 14313.3 | 13261.7 |
|      | 77.5°  | 4362.0  | 4817.8  | 5193.5  | 5567.0  | 5942.8  | 6396.3  | 6009.5  | 5620.4  | 5233.5  |
|      | 80°    | 1262.8  | 1378.4  | 1476.2  | 1571.8  | 1669.7  | 1611.9  | 1520.7  | 1429.6  | 1338.4  |
|      | 82.5°  | 226.8   | 213.4   | 211.2   | 209.0   | 209.0   | 197.9   | 180.1   | 162.3   | 144.5   |
|      | 85°    | 40.0    | 37.8    | 35.6    | 33.3    | 31.1    | 28.9    | 24.5    | 22.2    | 17.8    |
|      | 87.5°  | 13.3    | 11.1    | 8.9     | 6.7     | 6.7     | 2.2     | 2.2     | 2.2     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   | 128.9   |
| 0.0  | 0.0    | 2.5°   | 126.7   | 124.5   | 124.5   | 124.5   | 124.5   | 122.3   | 122.3   | 122.3   | 122.3   |
| 0.0  | 0.0    | 5°     | 140.1   | 140.1   | 137.8   | 137.8   | 135.6   | 135.6   | 133.4   | 133.4   | 131.2   |
| 0.0  | 0.0    | 7.5°   | 164.5   | 162.3   | 160.1   | 157.9   | 155.6   | 151.2   | 149.0   | 146.7   | 146.7   |
| 0.0  | 0.0    | 10°    | 197.9   | 193.4   | 191.2   | 186.8   | 184.5   | 180.1   | 175.6   | 171.2   | 166.7   |
| 0.0  | 0.0    | 12.5°  | 260.1   | 251.2   | 244.6   | 235.7   | 226.8   | 220.1   | 211.2   | 204.5   | 195.6   |
| 0.0  | 0.0    | 15°    | 451.3   | 429.1   | 404.6   | 375.7   | 344.6   | 315.7   | 284.6   | 266.8   | 246.8   |
| 0.0  | 0.0    | 17.5°  | 1153.9  | 1038.3  | 920.4   | 824.8   | 729.2   | 635.9   | 540.3   | 471.3   | 402.4   |
| 0.0  | 0.0    | 20°    | 2936.9  | 2616.8  | 2296.6  | 1980.9  | 1663.0  | 1347.3  | 1029.4  | 869.3   | 709.2   |
| 0.0  | 0.0    | 22.5°  | 5527.0  | 4933.4  | 4337.6  | 3761.8  | 3183.7  | 2607.9  | 2032.1  | 1669.7  | 1309.5  |
| 0.0  | 0.0    | 25°    | 8530.6  | 7783.6  | 7036.6  | 6089.5  | 5140.2  | 4193.1  | 3246.0  | 2656.8  | 2067.6  |
| 0.0  | 0.0    | 27.5°  | 11100.7 | 10240.3 | 9379.9  | 8228.3  | 7076.6  | 5925.0  | 4773.3  | 3895.1  | 3019.2  |
| 0.0  | 0.0    | 30°    | 13326.2 | 12401.3 | 11476.5 | 10135.8 | 8795.2  | 7454.6  | 6114.0  | 5015.7  | 3917.4  |
| 0.0  | 0.0    | 32.5°  | 15256.0 | 14148.8 | 13041.6 | 11658.8 | 10275.9 | 8893.0  | 7510.2  | 6162.9  | 4815.6  |
| 0.0  | 0.0    | 35°    | 17481.5 | 16189.8 | 14895.8 | 13361.8 | 11825.5 | 10291.5 | 8757.4  | 7236.7  | 5713.8  |
| 0.0  | 0.0    | 37.5°  | 20309.5 | 18724.3 | 17136.9 | 15427.2 | 13717.5 | 12010.0 | 10300.4 | 8561.8  | 6823.2  |
| 0.0  | 0.0    | 40°    | 25723.1 | 23677.7 | 21632.3 | 19460.2 | 17285.8 | 15113.7 | 12941.6 | 10807.3 | 8672.9  |
| 0.0  | 0.0    | 42.5°  | 35423.2 | 32659.7 | 29896.1 | 27005.9 | 24113.5 | 21223.2 | 18330.8 | 15320.5 | 12308.0 |
| 0.0  | 0.0    | 45°    | 46370.5 | 42942.2 | 39511.7 | 36268.0 | 33022.0 | 29778.3 | 26534.6 | 22403.8 | 18273.0 |
| 0.0  | 0.0    | 47.5°  | 52526.7 | 48825.0 | 45123.2 | 42052.9 | 38982.6 | 35912.3 | 32842.0 | 28388.8 | 23935.6 |
| 0.0  | 0.0    | 50°    | 54792.2 | 51023.8 | 47255.3 | 44429.6 | 41601.6 | 38775.8 | 35947.9 | 31488.0 | 27025.9 |
| 0.0  | 0.0    | 52.5°  | 55274.6 | 51430.6 | 47586.6 | 44743.1 | 41899.5 | 39058.2 | 36214.6 | 31783.7 | 27352.7 |
| 0.0  | 0.0    | 55°    | 56266.2 | 52142.1 | 48015.7 | 44774.2 | 41532.7 | 38291.2 | 35049.7 | 30547.6 | 26045.5 |
| 0.0  | 0.0    | 57.5°  | 57562.4 | 53333.7 | 49105.1 | 45412.3 | 41719.4 | 38028.8 | 34336.0 | 29413.7 | 24491.4 |
| 0.0  | 0.0    | 60°    | 57222.2 | 53542.7 | 49861.0 | 45905.8 | 41948.4 | 37993.2 | 34035.8 | 28622.2 | 23206.4 |
| 0.0  | 0.0    | 62.5°  | 51317.2 | 48387.0 | 45454.5 | 42201.9 | 38947.0 | 35694.4 | 32441.8 | 26868.1 | 21294.4 |
| 0.0  | 0.0    | 65°    | 42217.4 | 40078.7 | 37939.9 | 35323.1 | 32704.1 | 30087.3 | 27470.6 | 22472.7 | 17477.0 |
| 0.0  | 0.0    | 67.5°  | 34215.9 | 31805.9 | 29393.7 | 27308.3 | 25220.6 | 23135.2 | 21047.6 | 17114.6 | 13181.7 |
|      |        | 70°    | 27183.8 | 24562.5 | 21939.1 | 19902.6 | 17863.9 | 15827.4 | 13790.9 | 11176.3 | 8564.0  |
|      |        | 72.5°  | 21587.8 | 19224.5 | 16861.2 | 14689.1 | 12514.7 | 10342.6 | 8168.2  | 6623.1  | 5077.9  |
|      |        | 75°    | 10318.1 | 9373.3  | 8428.4  | 7292.3  | 6156.2  | 5020.1  | 3884.0  | 3210.4  | 2539.0  |
|      |        | 77.5°  | 3824.0  | 3314.9  | 2803.5  | 2341.1  | 1878.7  | 1418.4  | 956.0   | 876.0   | 795.9   |
|      |        | 80°    | 989.3   | 862.6   | 733.7   | 642.5   | 549.1   | 458.0   | 366.8   | 331.3   | 297.9   |
|      |        | 82.5°  | 113.4   | 104.5   | 97.8    | 93.4    | 86.7    | 82.3    | 75.6    | 68.9    | 62.3    |
|      |        | 85°    | 6.7     | 4.4     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5°  | 360°   |
|--------|------|--------|---------|--------|
| 0.0    | 0.0  | 0°     | 128.9   | 128.9  |
| 0.0    | 0.0  | 2.5°   | 120.1   | 117.8  |
| 0.0    | 0.0  | 5°     | 126.7   | 124.5  |
| 0.0    | 0.0  | 7.5°   | 140.1   | 135.6  |
| 0.0    | 0.0  | 10°    | 153.4   | 149.0  |
| 0.0    | 0.0  | 12.5°  | 173.4   | 166.7  |
| 0.0    | 0.0  | 15°    | 195.6   | 182.3  |
| 0.0    | 0.0  | 17.5°  | 233.4   | 204.5  |
| 0.0    | 0.0  | 20°    | 315.7   | 242.3  |
| 0.0    | 0.0  | 22.5°  | 444.7   | 302.4  |
| 0.0    | 0.0  | 25°    | 653.6   | 418.0  |
| 0.0    | 0.0  | 27.5°  | 909.3   | 555.8  |
| 0.0    | 0.0  | 30°    | 1209.5  | 695.9  |
| 0.0    | 0.0  | 32.5°  | 1474.0  | 829.3  |
| 0.0    | 0.0  | 35°    | 1818.6  | 964.9  |
| 0.0    | 0.0  | 37.5°  | 2243.3  | 1138.3 |
| 0.0    | 0.0  | 40°    | 2901.4  | 1400.7 |
| 0.0    | 0.0  | 42.5°  | 4086.3  | 1885.3 |
| 0.0    | 0.0  | 45°    | 6636.4  | 3259.3 |
| 0.0    | 0.0  | 47.5°  | 10211.4 | 5391.4 |
| 0.0    | 0.0  | 50°    | 12492.5 | 6881.0 |
| 0.0    | 0.0  | 52.5°  | 12679.2 | 6869.9 |
| 0.0    | 0.0  | 55°    | 11574.3 | 6107.3 |
| 0.0    | 0.0  | 57.5°  | 9875.7  | 5104.6 |
| 0.0    | 0.0  | 60°    | 8208.3  | 4037.4 |
| 0.0    | 0.0  | 62.5°  | 6467.5  | 2788.0 |
| 0.0    | 0.0  | 65°    | 4726.6  | 1972.0 |
| 0.0    | 0.0  | 67.5°  | 3394.9  | 1474.0 |
|        |      | 70°    | 2232.2  | 1129.4 |
|        |      | 72.5°  | 1454.0  | 920.4  |
|        |      | 75°    | 978.2   | 762.6  |
|        |      | 77.5°  | 571.4   | 506.9  |
|        |      | 80°    | 202.3   | 177.9  |
|        |      | 82.5°  | 37.8    | 26.7   |
|        |      | 85°    | 0.0     | 0.0    |
|        |      | 87.5°  | 0.0     | 0.0    |
|        |      | 90°    | 0.0     | 0.0    |
|        |      | 92.5°  | 0.0     | 0.0    |
|        |      | 95°    | 0.0     | 0.0    |
|        |      | 97.5°  | 0.0     | 0.0    |
|        |      | 100°   | 0.0     | 0.0    |
|        |      | 102.5° | 0.0     | 0.0    |
|        |      | 105°   | 0.0     | 0.0    |
|        |      | 107.5° | 0.0     | 0.0    |
|        |      | 110°   | 0.0     | 0.0    |



REPORT NUMBER: P1065055

CATALOG NUMBER: GLAN-SA8C-940-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-16

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-940-U-5WQ

Data in this report applies to families of products including GSS-SB1A-940-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-16  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-940-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI  
 4000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 3856  
 CIE  $u'$ : 0.2261  
 CIE  $v'$ : 0.5084  
 Duv: 0.0032  
 CIE x: 0.3896  
 CIE y: 0.3894  
 CIE z: 0.2211  
 Peak Wavelength (nm): 614  
 Dominant Wavelength (nm): 578  
 Purity: 33.77304  
 R<sub>f</sub>: 91.8  
 R<sub>g</sub>: 98.4

CRI (Ra): 92.1  
 R1: 91.8  
 R2: 94.1  
 R3: 95.3  
 R4: 92.8  
 R5: 91.0  
 R6: 91.6  
 R7: 95.0  
 R8: 85.2  
 R9: 60.7  
 R10: 85.2  
 R11: 92.4  
 R12: 74.5  
 R13: 92.3  
 R14: 97.0  
 R15: 88.5



### Test Conditions


Stabilization Time: 23M  
 Operation Time: 1H 23M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-16


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-16

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-16

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 492                                  | NR                             | 620               | 993                                  | NR                             | 750               | 73                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 539                                  | NR                             | 625               | 978                                  | NR                             | 755               | 62                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 583                                  | NR                             | 630               | 962                                  | NR                             | 760               | 54                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 623                                  | NR                             | 635               | 933                                  | NR                             | 765               | 46                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 661                                  | NR                             | 640               | 898                                  | NR                             | 770               | 39                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 698                                  | NR                             | 645               | 855                                  | NR                             | 775               | 34                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 733                                  | NR                             | 650               | 810                                  | NR                             | 780               | 29                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 1                                    | NR                             | 525               | 764                                  | NR                             | 655               | 759                                  | NR                             | 785               | 25                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 794                                  | NR                             | 660               | 704                                  | NR                             | 790               | 21                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 6                                    | NR                             | 535               | 820                                  | NR                             | 665               | 651                                  | NR                             | 795               | 18                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 12                                   | NR                             | 540               | 837                                  | NR                             | 670               | 592                                  | NR                             | 800               | 16                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 22                                   | NR                             | 545               | 853                                  | NR                             | 675               | 538                                  | NR                             | 805               | 13                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 42                                   | NR                             | 550               | 864                                  | NR                             | 680               | 486                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 79                                   | NR                             | 555               | 872                                  | NR                             | 685               | 435                                  | NR                             | 815               | 10                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 147                                  | NR                             | 560               | 876                                  | NR                             | 690               | 389                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 278                                  | NR                             | 565               | 883                                  | NR                             | 695               | 344                                  | NR                             | 825               | 7                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 515                                  | NR                             | 570               | 891                                  | NR                             | 700               | 303                                  | NR                             | 830               | 6                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 832                                  | NR                             | 575               | 900                                  | NR                             | 705               | 266                                  | NR                             | 835               | 5                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 874                                  | NR                             | 580               | 914                                  | NR                             | 710               | 233                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 659                                  | NR                             | 585               | 927                                  | NR                             | 715               | 203                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 567                                  | NR                             | 590               | 944                                  | NR                             | 720               | 178                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 485                                  | NR                             | 595               | 961                                  | NR                             | 725               | 154                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 401                                  | NR                             | 600               | 975                                  | NR                             | 730               | 133                                  | NR                             | 860               | 3                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 393                                  | NR                             | 605               | 988                                  | NR                             | 735               | 115                                  | NR                             | 865               | 2                                    | NR                             | 995               | 1                                    | NR                             |
| 480               | 417                                  | NR                             | 610               | 996                                  | NR                             | 740               | 98                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 448                                  | NR                             | 615               | 998                                  | NR                             | 745               | 85                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-16

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR


S/P: 1.72

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 492                         | NR               | 620       | 993                         | NR               | 750       | 73                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 539                         | NR               | 625       | 978                         | NR               | 755       | 62                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 583                         | NR               | 630       | 962                         | NR               | 760       | 54                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 623                         | NR               | 635       | 933                         | NR               | 765       | 46                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 661                         | NR               | 640       | 898                         | NR               | 770       | 39                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 698                         | NR               | 645       | 855                         | NR               | 775       | 34                          | NR               | 905       | 1                           | NR               |
| 390       | 0                           | NR               | 520       | 733                         | NR               | 650       | 810                         | NR               | 780       | 29                          | NR               | 910       | 1                           | NR               |
| 395       | 1                           | NR               | 525       | 764                         | NR               | 655       | 759                         | NR               | 785       | 25                          | NR               | 915       | 1                           | NR               |
| 400       | 3                           | NR               | 530       | 794                         | NR               | 660       | 704                         | NR               | 790       | 21                          | NR               | 920       | 1                           | NR               |
| 405       | 6                           | NR               | 535       | 820                         | NR               | 665       | 651                         | NR               | 795       | 18                          | NR               | 925       | 1                           | NR               |
| 410       | 12                          | NR               | 540       | 837                         | NR               | 670       | 592                         | NR               | 800       | 16                          | NR               | 930       | 1                           | NR               |
| 415       | 22                          | NR               | 545       | 853                         | NR               | 675       | 538                         | NR               | 805       | 13                          | NR               | 935       | 0                           | NR               |
| 420       | 42                          | NR               | 550       | 864                         | NR               | 680       | 486                         | NR               | 810       | 12                          | NR               | 940       | 0                           | NR               |
| 425       | 79                          | NR               | 555       | 872                         | NR               | 685       | 435                         | NR               | 815       | 10                          | NR               | 945       | 0                           | NR               |
| 430       | 147                         | NR               | 560       | 876                         | NR               | 690       | 389                         | NR               | 820       | 9                           | NR               | 950       | 0                           | NR               |
| 435       | 278                         | NR               | 565       | 883                         | NR               | 695       | 344                         | NR               | 825       | 7                           | NR               | 955       | 0                           | NR               |
| 440       | 515                         | NR               | 570       | 891                         | NR               | 700       | 303                         | NR               | 830       | 6                           | NR               | 960       | 0                           | NR               |
| 445       | 832                         | NR               | 575       | 900                         | NR               | 705       | 266                         | NR               | 835       | 5                           | NR               | 965       | 0                           | NR               |
| 450       | 874                         | NR               | 580       | 914                         | NR               | 710       | 233                         | NR               | 840       | 5                           | NR               | 970       | 0                           | NR               |
| 455       | 659                         | NR               | 585       | 927                         | NR               | 715       | 203                         | NR               | 845       | 4                           | NR               | 975       | 0                           | NR               |
| 460       | 567                         | NR               | 590       | 944                         | NR               | 720       | 178                         | NR               | 850       | 4                           | NR               | 980       | 0                           | NR               |
| 465       | 485                         | NR               | 595       | 961                         | NR               | 725       | 154                         | NR               | 855       | 3                           | NR               | 985       | 0                           | NR               |
| 470       | 401                         | NR               | 600       | 975                         | NR               | 730       | 133                         | NR               | 860       | 3                           | NR               | 990       | 0                           | NR               |
| 475       | 393                         | NR               | 605       | 988                         | NR               | 735       | 115                         | NR               | 865       | 2                           | NR               | 995       | 1                           | NR               |
| 480       | 417                         | NR               | 610       | 996                         | NR               | 740       | 98                          | NR               | 870       | 2                           | NR               | 1000      | 0                           | NR               |
| 485       | 448                         | NR               | 615       | 998                         | NR               | 745       | 85                          | NR               | 875       | 2                           | NR               |           |                             |                  |



REPORT NUMBER: SP1-2407-184-16

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.52


| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 492                      | NR            | 620    | 993                      | NR            | 750    | 73                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 539                      | NR            | 625    | 978                      | NR            | 755    | 62                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 583                      | NR            | 630    | 962                      | NR            | 760    | 54                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 623                      | NR            | 635    | 933                      | NR            | 765    | 46                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 661                      | NR            | 640    | 898                      | NR            | 770    | 39                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 698                      | NR            | 645    | 855                      | NR            | 775    | 34                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 733                      | NR            | 650    | 810                      | NR            | 780    | 29                       | NR            | 910    | 1                        | NR            |
| 395    | 1                        | NR            | 525    | 764                      | NR            | 655    | 759                      | NR            | 785    | 25                       | NR            | 915    | 1                        | NR            |
| 400    | 3                        | NR            | 530    | 794                      | NR            | 660    | 704                      | NR            | 790    | 21                       | NR            | 920    | 1                        | NR            |
| 405    | 6                        | NR            | 535    | 820                      | NR            | 665    | 651                      | NR            | 795    | 18                       | NR            | 925    | 1                        | NR            |
| 410    | 12                       | NR            | 540    | 837                      | NR            | 670    | 592                      | NR            | 800    | 16                       | NR            | 930    | 1                        | NR            |
| 415    | 22                       | NR            | 545    | 853                      | NR            | 675    | 538                      | NR            | 805    | 13                       | NR            | 935    | 0                        | NR            |
| 420    | 42                       | NR            | 550    | 864                      | NR            | 680    | 486                      | NR            | 810    | 12                       | NR            | 940    | 0                        | NR            |
| 425    | 79                       | NR            | 555    | 872                      | NR            | 685    | 435                      | NR            | 815    | 10                       | NR            | 945    | 0                        | NR            |
| 430    | 147                      | NR            | 560    | 876                      | NR            | 690    | 389                      | NR            | 820    | 9                        | NR            | 950    | 0                        | NR            |
| 435    | 278                      | NR            | 565    | 883                      | NR            | 695    | 344                      | NR            | 825    | 7                        | NR            | 955    | 0                        | NR            |
| 440    | 515                      | NR            | 570    | 891                      | NR            | 700    | 303                      | NR            | 830    | 6                        | NR            | 960    | 0                        | NR            |
| 445    | 832                      | NR            | 575    | 900                      | NR            | 705    | 266                      | NR            | 835    | 5                        | NR            | 965    | 0                        | NR            |
| 450    | 874                      | NR            | 580    | 914                      | NR            | 710    | 233                      | NR            | 840    | 5                        | NR            | 970    | 0                        | NR            |
| 455    | 659                      | NR            | 585    | 927                      | NR            | 715    | 203                      | NR            | 845    | 4                        | NR            | 975    | 0                        | NR            |
| 460    | 567                      | NR            | 590    | 944                      | NR            | 720    | 178                      | NR            | 850    | 4                        | NR            | 980    | 0                        | NR            |
| 465    | 485                      | NR            | 595    | 961                      | NR            | 725    | 154                      | NR            | 855    | 3                        | NR            | 985    | 0                        | NR            |
| 470    | 401                      | NR            | 600    | 975                      | NR            | 730    | 133                      | NR            | 860    | 3                        | NR            | 990    | 0                        | NR            |
| 475    | 393                      | NR            | 605    | 988                      | NR            | 735    | 115                      | NR            | 865    | 2                        | NR            | 995    | 1                        | NR            |
| 480    | 417                      | NR            | 610    | 996                      | NR            | 740    | 98                       | NR            | 870    | 2                        | NR            | 1000   | 0                        | NR            |
| 485    | 448                      | NR            | 615    | 998                      | NR            | 745    | 85                       | NR            | 875    | 2                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-16





TM-30-18

### Summary

$R_f = 91.8$   
 $R_g = 98.4$   
 $CIE R_a = 92.1$   
 $R_9 = 60.7$







### Color Vector Graphics





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 96 | CES76 = 87 |
| CES02 = 62 | CES27 = 91 | CES52 = 98 | CES77 = 90 |
| CES03 = 31 | CES28 = 96 | CES53 = 95 | CES78 = 84 |
| CES04 = 69 | CES29 = 96 | CES54 = 94 | CES79 = 96 |
| CES05 = 49 | CES30 = 93 | CES55 = 92 | CES80 = 94 |
| CES06 = 50 | CES31 = 97 | CES56 = 93 | CES81 = 89 |
| CES07 = 42 | CES32 = 92 | CES57 = 92 | CES82 = 97 |
| CES08 = 41 | CES33 = 99 | CES58 = 92 | CES83 = 98 |
| CES09 = 29 | CES34 = 94 | CES59 = 96 | CES84 = 94 |
| CES10 = 74 | CES35 = 96 | CES60 = 93 | CES85 = 85 |
| CES11 = 57 | CES36 = 82 | CES61 = 92 | CES86 = 88 |
| CES12 = 63 | CES37 = 95 | CES62 = 87 | CES87 = 92 |
| CES13 = 43 | CES38 = 88 | CES63 = 92 | CES88 = 96 |
| CES14 = 74 | CES39 = 99 | CES64 = 89 | CES89 = 87 |
| CES15 = 71 | CES40 = 98 | CES65 = 88 | CES90 = 96 |
| CES16 = 47 | CES41 = 97 | CES66 = 87 | CES91 = 74 |
| CES17 = 49 | CES42 = 96 | CES67 = 86 | CES92 = 80 |
| CES18 = 56 | CES43 = 96 | CES68 = 88 | CES93 = 88 |
| CES19 = 71 | CES44 = 99 | CES69 = 89 | CES94 = 82 |
| CES20 = 66 | CES45 = 98 | CES70 = 86 | CES95 = 83 |
| CES21 = 85 | CES46 = 97 | CES71 = 81 | CES96 = 92 |
| CES22 = 78 | CES47 = 97 | CES72 = 94 | CES97 = 95 |
| CES23 = 91 | CES48 = 91 | CES73 = 81 | CES98 = 94 |
| CES24 = 90 | CES49 = 96 | CES74 = 93 | CES99 = 91 |
| CES25 = 71 | CES50 = 97 | CES75 = 83 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)