

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1064447

Luminaire Tested: **GLAN-SA9C-940-U-T4BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1064447
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA9C-940-U-T4BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 9xLight Square PACKAGE
90CRI 4000K FIXTURE w/ TYPE IV ANGLED BACKLIGHT CONTROL
Light Source: (126) 4000K CCT, 90 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 36569 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G5

Input Watts (W): 417.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1064447

CATALOG NUMBER: GLAN-SA9C-940-U-T4BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 37.6 fc
Type IV - Short - N/A

REPORT NUMBER: P1064447

CATALOG NUMBER: GLAN-SA9C-940-U-T4BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1064447

CATALOG NUMBER: GLAN-SA9C-940-U-T4BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	130.0	0.0	130.0
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	36439.0	0.0	36439.0
	% Fixture	99.6	0.0	99.6
Total	Lumens	36569.0	0.0	36569.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.6	0.1
10°-20°	390.8	1.1
20°-30°	1391.9	3.8
30°-40°	3354.6	9.2
40°-50°	5614.2	15.4
50°-60°	7210.8	19.7
60°-70°	9125.3	25.0
70°-80°	8135.6	22.2
80°-90°	1315.1	3.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	36569.0	100.0
0°-180°	36569.0	100.0



REPORT NUMBER: P1064447


CATALOG NUMBER: GLAN-SA9C-940-U-T4BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1781.9	4.9			
FM	(30°-60°)	16149.6	44.2			
FH	(60°-80°)	17198.4	47.0			G5
FVH	(80°-90°)	1309.1	3.6			G5
BL	(0°-30°)	31.4	0.1	B0/110		
BM	(30°-60°)	30.1	0.1	B0/220		
BH	(60°-80°)	62.5	0.2	B0/110		G0/110
BVH	(80°-90°)	6.0	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G5

Type IV Short



REPORT NUMBER: P1064447

CATALOG NUMBER: GLAN-SA9C-940-U-T4BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	39°	45°	55°	65°	75°	85°
0°	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.5
2.5°	230.2	230.2	230.2	222.8	222.8	220.3	217.8	217.8	212.9	210.4	205.5
5°	349.0	341.6	324.3	314.4	294.6	282.2	269.8	252.5	235.2	222.8	207.9
7.5°	789.7	807.0	750.1	643.6	534.7	487.7	408.5	329.2	272.3	235.2	210.4
10°	2012.6	2002.7	1809.6	1596.7	1232.8	1086.8	851.6	537.2	351.5	257.5	212.9
12.5°	3423.6	3413.7	3186.0	2896.4	2416.1	2111.6	1666.0	1002.6	505.0	292.1	212.9
15°	4609.4	4569.8	4498.0	4210.9	3648.9	3393.9	2804.8	1772.5	816.9	351.5	217.8
17.5°	5394.2	5359.5	5292.7	5188.7	4832.2	4530.2	4057.4	2785.0	1321.9	455.5	227.7
20°	6114.5	6089.8	6035.3	6015.5	5785.3	5624.4	5233.3	3948.5	2059.6	618.9	242.6
22.5°	7104.7	7052.8	7075.0	6956.2	6730.9	6537.9	6297.7	5166.4	2960.7	891.2	269.8
25°	8317.8	8293.0	8231.1	8146.9	7835.0	7666.7	7297.8	6315.1	3968.3	1247.7	299.5
27.5°	9783.3	9756.0	9741.2	9548.1	9189.1	9006.0	8491.0	7399.3	5102.1	1747.7	339.1
30°	11471.6	11483.9	11387.4	11139.9	10721.5	10464.0	9934.3	8535.6	6263.1	2334.4	381.2
32.5°	13219.3	13194.5	13046.0	12753.9	12380.1	12140.0	11466.6	9780.8	7481.0	3109.3	430.7
35°	15103.2	15056.1	14665.0	14330.8	14011.5	13709.4	13095.5	11226.5	8699.0	3978.2	497.6
37.5°	17004.4	16784.0	15999.3	15576.0	15355.7	15108.1	14536.3	12768.7	9909.5	4948.6	579.3
40°	18440.2	18269.4	17338.6	16558.8	16383.0	16172.6	15746.8	14100.6	11196.8	5990.8	678.3
42.5°	19234.8	19140.7	18304.0	17534.1	17120.7	16935.0	16571.1	15264.1	12469.2	7141.9	821.9
45°	19574.0	19427.9	18868.4	18509.5	17851.0	17544.0	17110.8	16142.9	13798.6	8449.0	1022.4
47.5°	19470.0	19385.8	18984.8	19116.0	18638.2	18160.4	17524.2	16816.2	14934.8	9949.1	1297.2
50°	18816.4	18744.7	18620.9	19331.4	19271.9	18707.5	18058.9	17348.5	15863.1	11496.3	1723.0
52.5°	17573.7	17544.0	17860.9	19163.0	19630.9	19190.2	18573.8	17818.8	16729.6	13112.8	2331.9
55°	15972.1	16093.4	16999.4	18900.6	19814.1	19546.7	19029.3	18259.5	17425.2	14558.5	3230.6
57.5°	15313.6	15345.8	16477.1	18714.9	19895.8	19861.1	19472.5	18680.3	18063.9	15714.6	4602.0
60°	16083.5	16034.0	16630.6	18856.1	20059.2	20143.3	19866.1	19071.4	18618.4	16707.3	6428.9
62.5°	17474.7	17447.5	17638.1	19457.6	20536.9	20707.7	20413.2	19353.6	19108.6	17360.8	8513.3
65°	18717.4	18660.5	19014.5	20524.6	21376.1	21497.4	21240.0	19836.4	19323.9	17836.1	10471.5
67.5°	19254.6	19242.2	19811.6	21539.5	22257.4	22388.6	22163.4	20502.3	19274.4	17987.1	11335.4
70°	19009.5	18962.5	19873.5	21970.3	22755.0	22903.5	22685.7	20749.8	18737.2	17509.4	10055.6
71°	18739.7	18613.5	19687.8	21940.6	22824.3	22950.6	22569.3	20524.6	18197.6	16831.1	8894.6
72.5°	17903.0	17925.3	19177.9	21631.1	22658.5	22621.3	21910.8	19717.5	17546.5	15291.3	7144.4
75°	15843.3	15974.5	17526.7	20331.5	21178.1	20705.3	19618.5	18175.3	16239.4	10964.1	4960.9
77.5°	12947.0	13142.5	14848.2	17831.2	17591.1	17544.0	17499.5	16014.2	13867.9	5889.3	3450.9
80°	6181.4	6604.7	8956.4	12729.1	13828.3	14360.5	14026.3	12904.9	10724.0	2804.8	2062.1
82.5°	403.5	398.6	564.4	1069.4	4507.9	5827.4	9258.5	9223.8	7476.1	1366.5	841.7
85°	190.6	195.6	215.4	245.1	284.7	311.9	430.7	2525.0	3577.1	651.1	183.2
87.5°	111.4	113.9	133.7	170.8	222.8	247.6	294.6	378.8	465.4	359.0	39.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1064447

CATALOG NUMBER: GLAN-SA9C-940-U-T4BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.5
2.5°	203.0	200.5	193.1	185.7	178.2	173.3	170.8	173.3	173.3	175.8	175.8
5°	203.0	195.6	183.2	168.3	158.4	148.5	143.6	141.1	143.6	143.6	143.6
7.5°	200.5	188.1	170.8	153.5	141.1	128.7	123.8	121.3	121.3	123.8	123.8
10°	195.6	183.2	160.9	141.1	126.3	111.4	104.0	96.5	96.5	96.5	99.0
12.5°	193.1	175.8	148.5	128.7	108.9	91.6	76.7	69.3	71.8	71.8	71.8
15°	188.1	168.3	141.1	116.3	91.6	69.3	56.9	49.5	52.0	54.5	52.0
17.5°	188.1	165.9	131.2	101.5	71.8	52.0	42.1	37.1	37.1	39.6	39.6
20°	188.1	160.9	123.8	86.6	54.5	39.6	29.7	27.2	27.2	32.2	34.7
22.5°	193.1	160.9	113.9	71.8	44.6	29.7	22.3	19.8	22.3	27.2	29.7
25°	200.5	158.4	104.0	64.4	37.1	22.3	17.3	12.4	14.9	19.8	22.3
27.5°	207.9	156.0	94.1	56.9	29.7	17.3	12.4	9.9	7.4	9.9	9.9
30°	215.4	156.0	84.2	47.0	24.8	12.4	7.4	5.0	2.5	0.0	0.0
32.5°	220.3	151.0	76.7	37.1	19.8	9.9	5.0	2.5	0.0	0.0	0.0
35°	225.3	146.1	66.8	29.7	14.9	7.4	2.5	0.0	0.0	0.0	0.0
37.5°	230.2	138.6	56.9	24.8	12.4	5.0	0.0	0.0	0.0	0.0	0.0
40°	235.2	128.7	47.0	22.3	7.4	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	240.1	121.3	39.6	17.3	5.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	252.5	116.3	32.2	14.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	274.8	111.4	29.7	9.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	307.0	106.4	27.2	7.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	351.5	104.0	24.8	5.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	430.7	101.5	22.3	5.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	566.9	99.0	22.3	5.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	868.9	94.1	22.3	5.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	1552.2	91.6	19.8	5.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	2705.7	94.1	19.8	5.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	3879.1	99.0	17.3	7.4	2.5	0.0	0.0	0.0	0.0	0.0	0.0
70°	3319.7	86.6	17.3	9.9	5.0	2.5	0.0	0.0	0.0	0.0	0.0
71°	2705.7	76.7	17.3	9.9	5.0	2.5	2.5	0.0	0.0	0.0	0.0
72.5°	1740.3	59.4	14.9	9.9	5.0	5.0	2.5	0.0	0.0	0.0	0.0
75°	735.2	49.5	14.9	9.9	7.4	5.0	5.0	2.5	0.0	0.0	0.0
77.5°	314.4	37.1	14.9	12.4	9.9	7.4	7.4	5.0	2.5	0.0	0.0
80°	118.8	29.7	17.3	14.9	12.4	12.4	9.9	5.0	2.5	0.0	0.0
82.5°	54.5	24.8	17.3	14.9	14.9	12.4	9.9	7.4	5.0	0.0	0.0
85°	34.7	22.3	17.3	14.9	14.9	12.4	12.4	7.4	5.0	0.0	0.0
87.5°	27.2	22.3	17.3	17.3	14.9	14.9	9.9	7.4	2.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-16

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-940-U-5WQ

Data in this report applies to families of products including GSS-SB1A-940-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-16
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-940-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K): 3856
 CIE u' : 0.2261
 CIE v' : 0.5084
 Duv: 0.0032
 CIE x: 0.3896
 CIE y: 0.3894
 CIE z: 0.2211
 Peak Wavelength (nm): 614
 Dominant Wavelength (nm): 578
 Purity: 33.77304
 R_f: 91.8
 R_g: 98.4

CRI (Ra): 92.1
 R1: 91.8
 R2: 94.1
 R3: 95.3
 R4: 92.8
 R5: 91.0
 R6: 91.6
 R7: 95.0
 R8: 85.2
 R9: 60.7
 R10: 85.2
 R11: 92.4
 R12: 74.5
 R13: 92.3
 R14: 97.0
 R15: 88.5



Test Conditions

Stabilization Time: 23M
 Operation Time: 1H 23M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-16

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-16

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-16

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	492	NR	620	993	NR	750	73	NR	880	1	NR
365	0	NR	495	539	NR	625	978	NR	755	62	NR	885	1	NR
370	0	NR	500	583	NR	630	962	NR	760	54	NR	890	1	NR
375	0	NR	505	623	NR	635	933	NR	765	46	NR	895	1	NR
380	0	NR	510	661	NR	640	898	NR	770	39	NR	900	1	NR
385	0	NR	515	698	NR	645	855	NR	775	34	NR	905	1	NR
390	0	NR	520	733	NR	650	810	NR	780	29	NR	910	1	NR
395	1	NR	525	764	NR	655	759	NR	785	25	NR	915	1	NR
400	3	NR	530	794	NR	660	704	NR	790	21	NR	920	1	NR
405	6	NR	535	820	NR	665	651	NR	795	18	NR	925	1	NR
410	12	NR	540	837	NR	670	592	NR	800	16	NR	930	1	NR
415	22	NR	545	853	NR	675	538	NR	805	13	NR	935	0	NR
420	42	NR	550	864	NR	680	486	NR	810	12	NR	940	0	NR
425	79	NR	555	872	NR	685	435	NR	815	10	NR	945	0	NR
430	147	NR	560	876	NR	690	389	NR	820	9	NR	950	0	NR
435	278	NR	565	883	NR	695	344	NR	825	7	NR	955	0	NR
440	515	NR	570	891	NR	700	303	NR	830	6	NR	960	0	NR
445	832	NR	575	900	NR	705	266	NR	835	5	NR	965	0	NR
450	874	NR	580	914	NR	710	233	NR	840	5	NR	970	0	NR
455	659	NR	585	927	NR	715	203	NR	845	4	NR	975	0	NR
460	567	NR	590	944	NR	720	178	NR	850	4	NR	980	0	NR
465	485	NR	595	961	NR	725	154	NR	855	3	NR	985	0	NR
470	401	NR	600	975	NR	730	133	NR	860	3	NR	990	0	NR
475	393	NR	605	988	NR	735	115	NR	865	2	NR	995	1	NR
480	417	NR	610	996	NR	740	98	NR	870	2	NR	1000	0	NR
485	448	NR	615	998	NR	745	85	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-16

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.72

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	492	NR	620	993	NR	750	73	NR	880	1	NR
365	0	NR	495	539	NR	625	978	NR	755	62	NR	885	1	NR
370	0	NR	500	583	NR	630	962	NR	760	54	NR	890	1	NR
375	0	NR	505	623	NR	635	933	NR	765	46	NR	895	1	NR
380	0	NR	510	661	NR	640	898	NR	770	39	NR	900	1	NR
385	0	NR	515	698	NR	645	855	NR	775	34	NR	905	1	NR
390	0	NR	520	733	NR	650	810	NR	780	29	NR	910	1	NR
395	1	NR	525	764	NR	655	759	NR	785	25	NR	915	1	NR
400	3	NR	530	794	NR	660	704	NR	790	21	NR	920	1	NR
405	6	NR	535	820	NR	665	651	NR	795	18	NR	925	1	NR
410	12	NR	540	837	NR	670	592	NR	800	16	NR	930	1	NR
415	22	NR	545	853	NR	675	538	NR	805	13	NR	935	0	NR
420	42	NR	550	864	NR	680	486	NR	810	12	NR	940	0	NR
425	79	NR	555	872	NR	685	435	NR	815	10	NR	945	0	NR
430	147	NR	560	876	NR	690	389	NR	820	9	NR	950	0	NR
435	278	NR	565	883	NR	695	344	NR	825	7	NR	955	0	NR
440	515	NR	570	891	NR	700	303	NR	830	6	NR	960	0	NR
445	832	NR	575	900	NR	705	266	NR	835	5	NR	965	0	NR
450	874	NR	580	914	NR	710	233	NR	840	5	NR	970	0	NR
455	659	NR	585	927	NR	715	203	NR	845	4	NR	975	0	NR
460	567	NR	590	944	NR	720	178	NR	850	4	NR	980	0	NR
465	485	NR	595	961	NR	725	154	NR	855	3	NR	985	0	NR
470	401	NR	600	975	NR	730	133	NR	860	3	NR	990	0	NR
475	393	NR	605	988	NR	735	115	NR	865	2	NR	995	1	NR
480	417	NR	610	996	NR	740	98	NR	870	2	NR	1000	0	NR
485	448	NR	615	998	NR	745	85	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-16

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.52

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	492	NR	620	993	NR	750	73	NR	880	1	NR
365	0	NR	495	539	NR	625	978	NR	755	62	NR	885	1	NR
370	0	NR	500	583	NR	630	962	NR	760	54	NR	890	1	NR
375	0	NR	505	623	NR	635	933	NR	765	46	NR	895	1	NR
380	0	NR	510	661	NR	640	898	NR	770	39	NR	900	1	NR
385	0	NR	515	698	NR	645	855	NR	775	34	NR	905	1	NR
390	0	NR	520	733	NR	650	810	NR	780	29	NR	910	1	NR
395	1	NR	525	764	NR	655	759	NR	785	25	NR	915	1	NR
400	3	NR	530	794	NR	660	704	NR	790	21	NR	920	1	NR
405	6	NR	535	820	NR	665	651	NR	795	18	NR	925	1	NR
410	12	NR	540	837	NR	670	592	NR	800	16	NR	930	1	NR
415	22	NR	545	853	NR	675	538	NR	805	13	NR	935	0	NR
420	42	NR	550	864	NR	680	486	NR	810	12	NR	940	0	NR
425	79	NR	555	872	NR	685	435	NR	815	10	NR	945	0	NR
430	147	NR	560	876	NR	690	389	NR	820	9	NR	950	0	NR
435	278	NR	565	883	NR	695	344	NR	825	7	NR	955	0	NR
440	515	NR	570	891	NR	700	303	NR	830	6	NR	960	0	NR
445	832	NR	575	900	NR	705	266	NR	835	5	NR	965	0	NR
450	874	NR	580	914	NR	710	233	NR	840	5	NR	970	0	NR
455	659	NR	585	927	NR	715	203	NR	845	4	NR	975	0	NR
460	567	NR	590	944	NR	720	178	NR	850	4	NR	980	0	NR
465	485	NR	595	961	NR	725	154	NR	855	3	NR	985	0	NR
470	401	NR	600	975	NR	730	133	NR	860	3	NR	990	0	NR
475	393	NR	605	988	NR	735	115	NR	865	2	NR	995	1	NR
480	417	NR	610	996	NR	740	98	NR	870	2	NR	1000	0	NR
485	448	NR	615	998	NR	745	85	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-16




TM-30-18

Summary

$R_f = 91.8$
 $R_g = 98.4$
 $CIE\ R_a = 92.1$
 $R_9 = 60.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 96	CES76 = 87
CES02 = 62	CES27 = 91	CES52 = 98	CES77 = 90
CES03 = 31	CES28 = 96	CES53 = 95	CES78 = 84
CES04 = 69	CES29 = 96	CES54 = 94	CES79 = 96
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 94
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 92	CES57 = 92	CES82 = 97
CES08 = 41	CES33 = 99	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 94	CES59 = 96	CES84 = 94
CES10 = 74	CES35 = 96	CES60 = 93	CES85 = 85
CES11 = 57	CES36 = 82	CES61 = 92	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 87	CES87 = 92
CES13 = 43	CES38 = 88	CES63 = 92	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 89	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 88	CES90 = 96
CES16 = 47	CES41 = 97	CES66 = 87	CES91 = 74
CES17 = 49	CES42 = 96	CES67 = 86	CES92 = 80
CES18 = 56	CES43 = 96	CES68 = 88	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 82
CES20 = 66	CES45 = 98	CES70 = 86	CES95 = 83
CES21 = 85	CES46 = 97	CES71 = 81	CES96 = 92
CES22 = 78	CES47 = 97	CES72 = 94	CES97 = 95
CES23 = 91	CES48 = 91	CES73 = 81	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 93	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 83	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)