

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1063842

Luminaire Tested: **GLAN-SA2B-950-U-T2BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1063842
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA2B-950-U-T2BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 2xLight Square PACKAGE
90CRI 5000K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (28) 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7224.5 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 72.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1063842

CATALOG NUMBER: GLAN-SA2B-950-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 9.6 fc
 Type II - Short - N/A

REPORT NUMBER: P1063842

CATALOG NUMBER: GLAN-SA2B-950-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1063842

CATALOG NUMBER: GLAN-SA2B-950-U-T2BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	30.9	0.0	30.9
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	7193.6	0.0	7193.6
	% Fixture	99.6	0.0	99.6
Total	Lumens	7224.5	0.0	7224.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	5.6	0.1
10°-20°	59.4	0.8
20°-30°	213.2	3.0
30°-40°	567.6	7.9
40°-50°	1491.2	20.6
50°-60°	2310.1	32.0
60°-70°	1937.0	26.8
70°-80°	570.0	7.9
80°-90°	70.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7224.5	100.0
0°-180°	7224.5	100.0



REPORT NUMBER: P1063842


CATALOG NUMBER: GLAN-SA2B-950-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	271.3	3.8			
FM	(30°-60°)	4357.2	60.3			
FH	(60°-80°)	2496.1	34.6			G2/5000
FVH	(80°-90°)	69.0	1.0			G1/100
BL	(0°-30°)	6.9	0.1	B0/110		
BM	(30°-60°)	11.7	0.2	B0/220		
BH	(60°-80°)	10.9	0.2	B0/110		G0/110
BVH	(80°-90°)	1.3	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type II Short





REPORT NUMBER: P1063842

CATALOG NUMBER: GLAN-SA2B-950-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	64°	65°	75°	85°
0°	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2
2.5°	53.7	54.2	53.2	51.2	49.7	49.7	49.2	47.7	47.7	46.2	45.2
5°	75.0	74.0	72.1	68.1	64.6	61.1	57.6	54.2	53.7	49.2	46.2
7.5°	122.8	123.7	117.3	104.9	94.4	81.0	68.6	61.1	60.1	52.7	46.7
10°	269.4	261.9	247.0	198.8	163.5	123.2	91.4	71.1	70.1	56.7	47.7
12.5°	491.0	485.0	457.7	408.0	317.1	220.7	133.7	88.0	85.0	60.1	48.2
15°	707.7	698.2	683.3	633.1	526.8	395.6	218.7	120.3	112.3	65.1	47.7
17.5°	845.8	847.3	833.9	812.5	744.0	585.4	377.7	179.4	164.0	74.0	46.7
20°	966.6	963.1	970.6	959.1	910.9	795.6	549.6	284.3	257.9	88.5	47.2
22.5°	1105.8	1114.2	1119.7	1117.2	1064.0	965.6	745.0	425.4	392.1	114.8	48.7
25°	1292.1	1291.1	1291.6	1285.2	1233.5	1124.1	940.8	600.8	567.0	157.5	52.2
27.5°	1487.4	1493.4	1495.9	1472.5	1404.9	1297.6	1122.2	792.7	752.9	226.1	56.7
30°	1754.3	1749.3	1737.9	1690.2	1608.2	1475.0	1301.1	993.9	952.2	322.0	63.6
32.5°	2114.1	2108.6	2051.0	1945.6	1822.9	1659.9	1481.0	1195.7	1145.0	441.8	73.1
35°	2707.0	2715.4	2573.8	2301.0	2080.8	1882.0	1680.2	1396.5	1351.7	589.4	86.0
37.5°	3614.9	3568.7	3376.4	2894.3	2420.2	2159.3	1870.6	1599.2	1560.5	771.3	102.9
40°	4497.1	4451.3	4395.7	3939.0	3010.1	2465.0	2137.0	1837.3	1787.1	976.5	127.7
42.5°	5424.4	5399.0	5396.6	5052.2	4086.6	2945.5	2457.5	2116.1	2073.3	1201.7	168.5
45°	6081.4	6056.0	6109.2	6169.3	5552.6	3975.2	3015.6	2478.4	2416.3	1475.0	233.6
47.5°	6169.8	6170.8	6313.0	6501.3	6642.0	5568.0	3759.1	2958.4	2882.9	1866.1	342.9
50°	5875.6	5887.1	6113.2	6450.1	6828.8	6904.4	5070.1	3655.2	3543.4	2329.8	498.0
52.5°	5315.6	5328.5	5643.6	6197.7	6656.9	7225.4	6613.6	4566.6	4437.9	2908.2	716.6
55°	4811.1	4819.1	5180.4	5880.6	6449.6	7051.0	7530.0	5783.7	5614.7	3619.9	932.3
57.5°	4311.7	4293.3	4528.4	5330.0	6414.3	6836.8	7665.2	7170.7	6984.4	4397.7	1100.3
60°	3643.8	3612.9	3801.8	4311.7	5950.2	6977.4	7412.3	7938.0	7895.8	5480.5	1230.0
61°	3259.6	3246.7	3436.5	3873.9	5559.6	6941.6	7351.6	7970.4	7974.8	5992.9	1288.1
62.5°	2327.8	2364.6	2654.8	3223.3	4656.6	6709.5	7359.6	7870.5	7914.7	6673.8	1438.7
65°	1034.7	1093.8	1319.4	1782.1	2708.0	5581.4	7289.0	7651.3	7629.4	6860.6	1957.6
67.5°	613.8	622.7	735.0	1009.8	1434.2	3002.2	6432.2	7361.6	7332.2	5972.5	2435.6
70°	483.5	488.0	523.8	633.6	832.4	1150.0	3671.1	6369.1	6496.8	4842.9	2384.4
72.5°	458.7	457.7	462.7	482.1	524.3	570.5	1421.3	4233.7	4493.6	3487.7	1999.3
75°	452.7	450.7	445.8	438.3	379.7	335.9	440.3	1872.6	2023.2	2383.0	1505.3
77.5°	439.3	439.8	440.8	420.4	325.5	237.6	213.2	600.8	739.0	1512.3	1070.0
80°	297.2	301.7	309.1	301.2	292.7	172.0	150.6	213.7	216.7	848.8	706.7
82.5°	150.6	150.6	147.1	131.2	113.3	111.8	119.8	155.1	157.0	429.4	332.5
85°	90.9	95.9	97.9	89.0	81.5	75.0	91.4	123.2	127.7	166.5	77.5
87.5°	20.4	20.9	22.9	30.3	44.2	60.1	85.0	112.8	114.8	106.8	9.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1063842

CATALOG NUMBER: GLAN-SA2B-950-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2
2.5°	44.7	43.7	43.2	41.7	40.3	38.8	37.8	37.3	37.8	38.3	38.3
5°	44.2	42.7	40.3	37.8	35.8	33.8	31.8	31.3	31.3	31.8	31.8
7.5°	44.2	41.7	38.3	35.3	32.3	29.3	27.8	26.8	27.3	27.3	27.3
10°	44.2	41.2	36.8	32.3	28.8	25.3	22.9	21.9	21.9	21.9	21.9
12.5°	43.7	40.8	35.3	29.8	24.8	20.9	17.9	16.4	16.9	16.9	16.9
15°	42.7	39.3	33.3	25.3	19.9	15.9	12.9	11.4	11.9	12.9	13.4
17.5°	41.2	37.8	29.8	21.4	15.9	11.9	8.9	8.0	8.4	9.9	9.9
20°	40.8	36.3	26.3	17.4	11.9	8.4	6.0	5.0	5.5	7.5	8.0
22.5°	40.8	35.3	23.9	14.4	8.9	5.5	3.5	2.0	2.0	3.5	3.5
25°	41.2	34.8	21.9	11.9	6.5	4.0	2.0	1.0	2.0	5.5	6.5
27.5°	42.2	34.3	20.9	9.9	5.0	3.5	1.5	3.5	6.0	6.0	6.0
30°	43.2	33.3	19.4	8.4	4.5	2.5	2.5	5.0	5.0	6.0	6.5
32.5°	44.7	32.8	18.4	7.5	3.5	2.0	3.5	3.0	3.0	3.5	4.0
35°	47.7	33.3	17.4	7.5	3.5	2.5	3.0	1.5	1.0	1.0	1.0
37.5°	51.7	33.8	15.9	6.5	3.0	3.0	1.5	0.0	0.0	0.0	0.0
40°	58.1	35.3	14.9	6.0	2.5	2.5	0.5	0.0	0.0	0.0	0.0
42.5°	69.1	38.3	14.4	5.5	2.5	2.0	0.0	0.0	0.0	0.0	0.0
45°	90.9	45.2	13.4	5.0	2.5	1.0	0.0	0.0	0.0	0.0	0.0
47.5°	130.7	61.6	12.9	4.0	1.5	0.0	0.0	0.0	0.0	0.0	0.0
50°	190.8	83.5	12.4	3.5	0.5	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	243.5	88.0	8.4	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	249.5	60.6	6.5	2.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	198.8	39.3	5.5	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	150.6	29.8	5.0	0.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
61°	144.6	26.8	5.0	0.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	159.5	23.4	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	259.4	19.4	4.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	450.7	16.9	3.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	569.5	15.9	3.0	0.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	496.5	14.4	3.0	1.0	0.5	0.0	0.0	0.0	0.0	0.0	0.0
75°	298.7	12.4	3.0	2.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	156.5	9.4	3.0	2.5	1.5	0.5	0.0	0.0	0.0	0.0	0.0
80°	76.0	8.4	3.5	2.5	2.0	1.0	0.0	0.0	0.0	0.0	0.0
82.5°	29.8	7.0	4.0	3.5	2.5	1.5	0.5	0.0	0.0	0.0	0.0
85°	13.4	6.0	4.5	4.0	3.5	2.0	0.5	0.0	0.0	0.0	0.0
87.5°	7.0	5.5	5.0	4.5	3.5	2.5	1.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-17

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-950-U-5WQ

Data in this report applies to families of products including GSS-SB1A-950-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-17
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-950-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI
 5000K CCT 26 LEDS

Spectral Parameters

CCT (K): 4765
 CIE u' : 0.2105
 CIE v' : 0.4941
 Duv: 0.0052
 CIE x: 0.3536
 CIE y: 0.3689
 CIE z: 0.2775
 Peak Wavelength (nm): 449
 Dominant Wavelength (nm): 571
 Purity: 16.80041
 R_f: 90.7
 R_g: 98

CRI (Ra): 90.8
 R1: 89.8
 R2: 93.1
 R3: 95.3
 R4: 90.3
 R5: 89.0
 R6: 89.7
 R7: 94.9
 R8: 84.0
 R9: 54.9
 R10: 83.0
 R11: 89.6
 R12: 68.0
 R13: 90.6
 R14: 97.3
 R15: 86.2



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-17

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-17

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-17

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	462	NR	620	668	NR	750	45	NR	880	1	NR
365	0	NR	495	498	NR	625	652	NR	755	39	NR	885	1	NR
370	0	NR	500	533	NR	630	634	NR	760	33	NR	890	1	NR
375	0	NR	505	562	NR	635	610	NR	765	28	NR	895	1	NR
380	0	NR	510	590	NR	640	583	NR	770	24	NR	900	1	NR
385	0	NR	515	617	NR	645	552	NR	775	21	NR	905	1	NR
390	0	NR	520	642	NR	650	519	NR	780	18	NR	910	0	NR
395	2	NR	525	661	NR	655	484	NR	785	15	NR	915	0	NR
400	4	NR	530	681	NR	660	448	NR	790	13	NR	920	0	NR
405	7	NR	535	695	NR	665	411	NR	795	11	NR	925	0	NR
410	12	NR	540	702	NR	670	373	NR	800	10	NR	930	0	NR
415	21	NR	545	708	NR	675	338	NR	805	8	NR	935	0	NR
420	39	NR	550	707	NR	680	305	NR	810	7	NR	940	0	NR
425	74	NR	555	706	NR	685	272	NR	815	6	NR	945	0	NR
430	139	NR	560	700	NR	690	243	NR	820	5	NR	950	0	NR
435	270	NR	565	696	NR	695	214	NR	825	5	NR	955	0	NR
440	517	NR	570	692	NR	700	188	NR	830	4	NR	960	0	NR
445	877	NR	575	689	NR	705	165	NR	835	3	NR	965	0	NR
450	978	NR	580	688	NR	710	144	NR	840	3	NR	970	0	NR
455	738	NR	585	688	NR	715	125	NR	845	3	NR	975	0	NR
460	618	NR	590	689	NR	720	110	NR	850	2	NR	980	0	NR
465	529	NR	595	690	NR	725	95	NR	855	2	NR	985	0	NR
470	420	NR	600	690	NR	730	82	NR	860	2	NR	990	0	NR
475	395	NR	605	688	NR	735	71	NR	865	1	NR	995	0	NR
480	408	NR	610	685	NR	740	61	NR	870	1	NR	1000	0	NR
485	429	NR	615	678	NR	745	52	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-17

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.99

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	462	NR	620	668	NR	750	45	NR	880	1	NR
365	0	NR	495	498	NR	625	652	NR	755	39	NR	885	1	NR
370	0	NR	500	533	NR	630	634	NR	760	33	NR	890	1	NR
375	0	NR	505	562	NR	635	610	NR	765	28	NR	895	1	NR
380	0	NR	510	590	NR	640	583	NR	770	24	NR	900	1	NR
385	0	NR	515	617	NR	645	552	NR	775	21	NR	905	1	NR
390	0	NR	520	642	NR	650	519	NR	780	18	NR	910	0	NR
395	2	NR	525	661	NR	655	484	NR	785	15	NR	915	0	NR
400	4	NR	530	681	NR	660	448	NR	790	13	NR	920	0	NR
405	7	NR	535	695	NR	665	411	NR	795	11	NR	925	0	NR
410	12	NR	540	702	NR	670	373	NR	800	10	NR	930	0	NR
415	21	NR	545	708	NR	675	338	NR	805	8	NR	935	0	NR
420	39	NR	550	707	NR	680	305	NR	810	7	NR	940	0	NR
425	74	NR	555	706	NR	685	272	NR	815	6	NR	945	0	NR
430	139	NR	560	700	NR	690	243	NR	820	5	NR	950	0	NR
435	270	NR	565	696	NR	695	214	NR	825	5	NR	955	0	NR
440	517	NR	570	692	NR	700	188	NR	830	4	NR	960	0	NR
445	877	NR	575	689	NR	705	165	NR	835	3	NR	965	0	NR
450	978	NR	580	688	NR	710	144	NR	840	3	NR	970	0	NR
455	738	NR	585	688	NR	715	125	NR	845	3	NR	975	0	NR
460	618	NR	590	689	NR	720	110	NR	850	2	NR	980	0	NR
465	529	NR	595	690	NR	725	95	NR	855	2	NR	985	0	NR
470	420	NR	600	690	NR	730	82	NR	860	2	NR	990	0	NR
475	395	NR	605	688	NR	735	71	NR	865	1	NR	995	0	NR
480	408	NR	610	685	NR	740	61	NR	870	1	NR	1000	0	NR
485	429	NR	615	678	NR	745	52	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-17

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 4.22

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	462	NR	620	668	NR	750	45	NR	880	1	NR
365	0	NR	495	498	NR	625	652	NR	755	39	NR	885	1	NR
370	0	NR	500	533	NR	630	634	NR	760	33	NR	890	1	NR
375	0	NR	505	562	NR	635	610	NR	765	28	NR	895	1	NR
380	0	NR	510	590	NR	640	583	NR	770	24	NR	900	1	NR
385	0	NR	515	617	NR	645	552	NR	775	21	NR	905	1	NR
390	0	NR	520	642	NR	650	519	NR	780	18	NR	910	0	NR
395	2	NR	525	661	NR	655	484	NR	785	15	NR	915	0	NR
400	4	NR	530	681	NR	660	448	NR	790	13	NR	920	0	NR
405	7	NR	535	695	NR	665	411	NR	795	11	NR	925	0	NR
410	12	NR	540	702	NR	670	373	NR	800	10	NR	930	0	NR
415	21	NR	545	708	NR	675	338	NR	805	8	NR	935	0	NR
420	39	NR	550	707	NR	680	305	NR	810	7	NR	940	0	NR
425	74	NR	555	706	NR	685	272	NR	815	6	NR	945	0	NR
430	139	NR	560	700	NR	690	243	NR	820	5	NR	950	0	NR
435	270	NR	565	696	NR	695	214	NR	825	5	NR	955	0	NR
440	517	NR	570	692	NR	700	188	NR	830	4	NR	960	0	NR
445	877	NR	575	689	NR	705	165	NR	835	3	NR	965	0	NR
450	978	NR	580	688	NR	710	144	NR	840	3	NR	970	0	NR
455	738	NR	585	688	NR	715	125	NR	845	3	NR	975	0	NR
460	618	NR	590	689	NR	720	110	NR	850	2	NR	980	0	NR
465	529	NR	595	690	NR	725	95	NR	855	2	NR	985	0	NR
470	420	NR	600	690	NR	730	82	NR	860	2	NR	990	0	NR
475	395	NR	605	688	NR	735	71	NR	865	1	NR	995	0	NR
480	408	NR	610	685	NR	740	61	NR	870	1	NR	1000	0	NR
485	429	NR	615	678	NR	745	52	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-17

TM-30-18

Summary

$R_f = 90.7$
 $R_g = 98$
 CIE $R_a = 90.8$
 $R_9 = 54.9$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 92	CES51 = 96	CES76 = 85
CES02 = 60	CES27 = 92	CES52 = 97	CES77 = 88
CES03 = 31	CES28 = 95	CES53 = 94	CES78 = 82
CES04 = 69	CES29 = 95	CES54 = 93	CES79 = 96
CES05 = 48	CES30 = 94	CES55 = 92	CES80 = 93
CES06 = 50	CES31 = 96	CES56 = 92	CES81 = 89
CES07 = 41	CES32 = 91	CES57 = 91	CES82 = 97
CES08 = 40	CES33 = 99	CES58 = 91	CES83 = 98
CES09 = 29	CES34 = 93	CES59 = 95	CES84 = 93
CES10 = 73	CES35 = 96	CES60 = 92	CES85 = 85
CES11 = 56	CES36 = 82	CES61 = 92	CES86 = 88
CES12 = 62	CES37 = 95	CES62 = 87	CES87 = 90
CES13 = 42	CES38 = 89	CES63 = 91	CES88 = 94
CES14 = 74	CES39 = 99	CES64 = 88	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 86	CES90 = 94
CES16 = 46	CES41 = 97	CES66 = 85	CES91 = 74
CES17 = 48	CES42 = 95	CES67 = 84	CES92 = 78
CES18 = 56	CES43 = 95	CES68 = 86	CES93 = 87
CES19 = 70	CES44 = 100	CES69 = 88	CES94 = 80
CES20 = 65	CES45 = 97	CES70 = 84	CES95 = 81
CES21 = 85	CES46 = 96	CES71 = 79	CES96 = 90
CES22 = 77	CES47 = 98	CES72 = 93	CES97 = 95
CES23 = 91	CES48 = 90	CES73 = 78	CES98 = 92
CES24 = 90	CES49 = 95	CES74 = 93	CES99 = 88
CES25 = 70	CES50 = 97	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)