

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065095

Luminaire Tested: **GLAN-SA9C-950-U-RBC**

Issue Date: 08/07/2025



**Test Information**

Test Method: LM-79-08  
Report Number: P1065095  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA9C-950-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 9xLight Square PACKAGE  
90CRI 5000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (126) 5000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 35571.6 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G5


Input Watts (W): 417.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5.2 fc  
 Type III - Short - N/A

REPORT NUMBER: P1065095  
CATALOG NUMBER: GLAN-SA9C-950-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 178.1    | 0.0    | 178.1   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 35393.5  | 0.0    | 35393.5 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 35571.6  | 0.0    | 35571.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 13.9    | 0.0       |
| 10°-20°   | 78.2    | 0.2       |
| 20°-30°   | 843.0   | 2.4       |
| 30°-40°   | 2492.9  | 7.0       |
| 40°-50°   | 7429.5  | 20.9      |
| 50°-60°   | 11780.5 | 33.1      |
| 60°-70°   | 9833.8  | 27.6      |
| 70°-80°   | 3032.4  | 8.5       |
| 80°-90°   | 67.4    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 35571.6 | 100.0     |
| 0°-180°   | 35571.6 | 100.0     |



REPORT NUMBER: P1065095


CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |        |
|------|-------------|---------|-----------|-------------------------|------|--------|
|      |             |         |           | B                       | U    | G      |
| FL   | (0°-30°)    | 902.4   | 2.5       |                         |      |        |
| FM   | (30°-60°)   | 21639.2 | 60.8      |                         |      |        |
| FH   | (60°-80°)   | 12799.8 | 36.0      |                         |      | G5     |
| FVH  | (80°-90°)   | 52.1    | 0.1       |                         |      | G1/100 |
| BL   | (0°-30°)    | 32.7    | 0.1       | B0/110                  |      |        |
| BM   | (30°-60°)   | 63.7    | 0.2       | B0/220                  |      |        |
| BH   | (60°-80°)   | 66.4    | 0.2       | B0/110                  |      | G0/110 |
| BVH  | (80°-90°)   | 15.3    | 0.0       |                         |      | G1/100 |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |        |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |        |

**BUG Rating: B0-U0-G5**

Type III Short



REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° |
|--------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|
| 0°     | 155.9  | 155.9  | 155.9  | 155.9  | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 |
| 2.5°   | 142.5  | 142.5  | 142.5  | 142.5  | 139.8 | 139.8 | 137.1 | 137.1 | 134.4 | 134.4 |
| 5°     | 150.5  | 150.5  | 147.8  | 145.2  | 145.2 | 142.5 | 139.8 | 137.1 | 137.1 | 134.4 |
| 7.5°   | 164.0  | 161.3  | 158.6  | 155.9  | 150.5 | 147.8 | 142.5 | 139.8 | 137.1 | 131.7 |
| 10°    | 180.1  | 174.7  | 169.4  | 164.0  | 158.6 | 153.2 | 147.8 | 145.2 | 139.8 | 137.1 |
| 12.5°  | 201.6  | 193.5  | 182.8  | 174.7  | 169.4 | 161.3 | 155.9 | 150.5 | 142.5 | 137.1 |
| 15°    | 220.4  | 209.7  | 196.2  | 185.5  | 177.4 | 166.7 | 158.6 | 150.5 | 145.2 | 137.1 |
| 17.5°  | 247.3  | 228.5  | 207.0  | 193.5  | 182.8 | 169.4 | 155.9 | 147.8 | 139.8 | 129.0 |
| 20°    | 293.0  | 255.4  | 215.0  | 198.9  | 182.8 | 166.7 | 150.5 | 139.8 | 131.7 | 121.0 |
| 22.5°  | 365.6  | 301.1  | 236.6  | 212.4  | 190.9 | 166.7 | 145.2 | 134.4 | 123.7 | 112.9 |
| 25°    | 505.4  | 389.8  | 274.2  | 241.9  | 209.7 | 177.4 | 145.2 | 131.7 | 121.0 | 107.5 |
| 27.5°  | 672.0  | 500.0  | 325.3  | 279.6  | 236.6 | 190.9 | 145.2 | 129.0 | 115.6 | 99.5  |
| 30°    | 841.4  | 612.9  | 381.7  | 322.6  | 263.4 | 204.3 | 145.2 | 126.3 | 110.2 | 91.4  |
| 32.5°  | 1002.7 | 717.7  | 430.1  | 360.2  | 290.3 | 217.7 | 147.8 | 126.3 | 104.8 | 83.3  |
| 35°    | 1166.6 | 803.7  | 438.2  | 365.6  | 293.0 | 217.7 | 145.2 | 121.0 | 99.5  | 75.3  |
| 37.5°  | 1376.3 | 900.5  | 422.0  | 349.5  | 279.6 | 207.0 | 137.1 | 115.6 | 94.1  | 69.9  |
| 40°    | 1693.5 | 1061.8 | 430.1  | 354.8  | 279.6 | 204.3 | 129.0 | 107.5 | 88.7  | 67.2  |
| 42.5°  | 2279.5 | 1373.6 | 465.0  | 379.0  | 293.0 | 204.3 | 118.3 | 99.5  | 83.3  | 64.5  |
| 45°    | 3940.8 | 2282.2 | 623.6  | 494.6  | 365.6 | 236.6 | 107.5 | 91.4  | 78.0  | 61.8  |
| 47.5°  | 6518.7 | 3819.8 | 1120.9 | 865.6  | 612.9 | 357.5 | 104.8 | 91.4  | 78.0  | 61.8  |
| 50°    | 8319.7 | 4865.5 | 1411.3 | 1086.0 | 760.7 | 435.5 | 110.2 | 94.1  | 80.6  | 64.5  |
| 52.5°  | 8306.3 | 4940.8 | 1572.5 | 1207.0 | 844.1 | 478.5 | 115.6 | 99.5  | 86.0  | 69.9  |
| 55°    | 7384.3 | 4494.5 | 1602.1 | 1231.2 | 862.9 | 491.9 | 123.7 | 107.5 | 91.4  | 75.3  |
| 57.5°  | 6171.9 | 3817.1 | 1462.3 | 1131.7 | 803.7 | 473.1 | 142.5 | 123.7 | 107.5 | 88.7  |
| 60°    | 4881.6 | 3010.7 | 1139.8 | 900.5  | 664.0 | 424.7 | 188.2 | 164.0 | 142.5 | 118.3 |
| 62.5°  | 3370.9 | 2182.7 | 994.6  | 798.4  | 604.8 | 408.6 | 215.0 | 190.9 | 169.4 | 145.2 |
| 65°    | 2384.4 | 1642.4 | 897.8  | 731.2  | 567.2 | 400.5 | 233.9 | 207.0 | 182.8 | 155.9 |
| 67.5°  | 1782.2 | 1306.4 | 827.9  | 685.5  | 543.0 | 400.5 | 258.1 | 225.8 | 196.2 | 164.0 |
| 70°    | 1365.6 | 1072.6 | 776.9  | 661.3  | 548.4 | 432.8 | 317.2 | 271.5 | 228.5 | 182.8 |
| 72.5°  | 1112.9 | 916.6  | 717.7  | 634.4  | 551.1 | 467.7 | 384.4 | 325.3 | 266.1 | 204.3 |
| 75°    | 922.0  | 784.9  | 647.8  | 577.9  | 510.7 | 440.9 | 371.0 | 317.2 | 266.1 | 212.4 |
| 77.5°  | 612.9  | 559.1  | 502.7  | 462.4  | 422.0 | 379.0 | 338.7 | 293.0 | 250.0 | 204.3 |
| 80°    | 215.0  | 207.0  | 198.9  | 215.0  | 231.2 | 247.3 | 263.4 | 231.2 | 201.6 | 169.4 |
| 82.5°  | 32.3   | 29.6   | 26.9   | 29.6   | 32.3  | 34.9  | 37.6  | 40.3  | 43.0  | 45.7  |
| 85°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°   | 32.5° | 35°   | 37.5° | 40°   | 42.5° | 45°   | 47.5° | 50°   |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0 | 0°     | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 |
| 0.0 | 2.5°   | 131.7 | 131.7 | 129.0 | 129.0 | 129.0 | 126.3 | 126.3 | 123.7 | 123.7 | 123.7 |
| 0.0 | 5°     | 129.0 | 129.0 | 126.3 | 123.7 | 121.0 | 121.0 | 118.3 | 115.6 | 115.6 | 112.9 |
| 0.0 | 7.5°   | 126.3 | 123.7 | 121.0 | 118.3 | 115.6 | 112.9 | 110.2 | 107.5 | 107.5 | 104.8 |
| 0.0 | 10°    | 129.0 | 123.7 | 121.0 | 115.6 | 112.9 | 110.2 | 104.8 | 102.1 | 99.5  | 99.5  |
| 0.0 | 12.5°  | 123.7 | 121.0 | 115.6 | 110.2 | 107.5 | 102.1 | 99.5  | 94.1  | 91.4  | 91.4  |
| 0.0 | 15°    | 123.7 | 118.3 | 110.2 | 104.8 | 99.5  | 96.8  | 91.4  | 86.0  | 83.3  | 80.6  |
| 0.0 | 17.5°  | 115.6 | 110.2 | 102.1 | 96.8  | 91.4  | 86.0  | 80.6  | 75.3  | 72.6  | 69.9  |
| 0.0 | 20°    | 104.8 | 99.5  | 91.4  | 83.3  | 78.0  | 72.6  | 67.2  | 61.8  | 59.1  | 56.5  |
| 0.0 | 22.5°  | 94.1  | 88.7  | 80.6  | 72.6  | 67.2  | 61.8  | 53.8  | 48.4  | 45.7  | 40.3  |
| 0.0 | 25°    | 88.7  | 80.6  | 72.6  | 64.5  | 56.5  | 51.1  | 43.0  | 34.9  | 29.6  | 24.2  |
| 0.0 | 27.5°  | 75.3  | 67.2  | 59.1  | 51.1  | 43.0  | 34.9  | 26.9  | 18.8  | 13.4  | 10.8  |
| 0.0 | 30°    | 64.5  | 56.5  | 48.4  | 40.3  | 29.6  | 21.5  | 13.4  | 2.7   | 2.7   | 2.7   |
| 0.0 | 32.5°  | 53.8  | 45.7  | 34.9  | 26.9  | 21.5  | 13.4  | 8.1   | 0.0   | 0.0   | 0.0   |
| 0.0 | 35°    | 43.0  | 34.9  | 24.2  | 16.1  | 13.4  | 8.1   | 5.4   | 0.0   | 0.0   | 0.0   |
| 0.0 | 37.5°  | 37.6  | 29.6  | 18.8  | 8.1   | 5.4   | 5.4   | 2.7   | 0.0   | 0.0   | 0.0   |
| 0.0 | 40°    | 34.9  | 24.2  | 13.4  | 2.7   | 2.7   | 2.7   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 42.5°  | 34.9  | 24.2  | 10.8  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 45°    | 34.9  | 24.2  | 10.8  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 47.5°  | 34.9  | 24.2  | 10.8  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 50°    | 37.6  | 26.9  | 13.4  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 52.5°  | 43.0  | 32.3  | 21.5  | 10.8  | 8.1   | 5.4   | 2.7   | 0.0   | 0.0   | 0.0   |
| 0.0 | 55°    | 53.8  | 48.4  | 40.3  | 34.9  | 26.9  | 18.8  | 8.1   | 0.0   | 0.0   | 0.0   |
| 0.0 | 57.5°  | 69.9  | 69.9  | 67.2  | 64.5  | 48.4  | 32.3  | 16.1  | 0.0   | 0.0   | 0.0   |
| 0.0 | 60°    | 94.1  | 94.1  | 94.1  | 94.1  | 69.9  | 48.4  | 24.2  | 0.0   | 0.0   | 0.0   |
| 0.0 | 62.5°  | 115.6 | 110.2 | 102.1 | 96.8  | 72.6  | 48.4  | 24.2  | 0.0   | 0.0   | 0.0   |
| 0.0 | 65°    | 115.6 | 104.8 | 91.4  | 78.0  | 59.1  | 40.3  | 18.8  | 0.0   | 0.0   | 0.0   |
| 0.0 | 67.5°  | 107.5 | 86.0  | 61.8  | 40.3  | 29.6  | 21.5  | 10.8  | 0.0   | 0.0   | 0.0   |
|     | 70°    | 107.5 | 75.3  | 43.0  | 10.8  | 8.1   | 5.4   | 2.7   | 0.0   | 0.0   | 0.0   |
|     | 72.5°  | 107.5 | 72.6  | 34.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 75°    | 118.3 | 80.6  | 40.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 77.5°  | 118.3 | 80.6  | 40.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 80°    | 104.8 | 69.9  | 34.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 82.5°  | 34.9  | 24.2  | 10.8  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°   | 77.5° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0   | 0°     | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 |
| 0.0   | 2.5°   | 121.0 | 121.0 | 121.0 | 118.3 | 118.3 | 118.3 | 118.3 | 115.6 | 115.6 | 115.6 |
| 0.0   | 5°     | 110.2 | 110.2 | 107.5 | 107.5 | 104.8 | 104.8 | 102.1 | 102.1 | 99.5  | 99.5  |
| 0.0   | 7.5°   | 102.1 | 99.5  | 99.5  | 96.8  | 94.1  | 94.1  | 91.4  | 91.4  | 88.7  | 86.0  |
| 0.0   | 10°    | 94.1  | 91.4  | 91.4  | 88.7  | 86.0  | 83.3  | 83.3  | 80.6  | 78.0  | 75.3  |
| 0.0   | 12.5°  | 86.0  | 83.3  | 80.6  | 78.0  | 75.3  | 72.6  | 72.6  | 69.9  | 67.2  | 64.5  |
| 0.0   | 15°    | 75.3  | 72.6  | 69.9  | 67.2  | 64.5  | 61.8  | 61.8  | 59.1  | 56.5  | 53.8  |
| 0.0   | 17.5°  | 64.5  | 61.8  | 61.8  | 59.1  | 56.5  | 53.8  | 51.1  | 45.7  | 43.0  | 40.3  |
| 0.0   | 20°    | 48.4  | 45.7  | 43.0  | 40.3  | 37.6  | 32.3  | 29.6  | 24.2  | 18.8  | 16.1  |
| 0.0   | 22.5°  | 32.3  | 26.9  | 24.2  | 18.8  | 13.4  | 10.8  | 8.1   | 2.7   | 0.0   | 0.0   |
| 0.0   | 25°    | 10.8  | 8.1   | 5.4   | 2.7   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°   | 87.5° | 90°   | 92.5° | 95°   | 97.5° | 100°  | 102.5° | 105°  |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 0.0 | 0°     | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9 | 155.9  | 155.9 |
| 0.0 | 2.5°   | 112.9 | 112.9 | 112.9 | 110.2 | 110.2 | 110.2 | 110.2 | 110.2 | 110.2  | 110.2 |
| 0.0 | 5°     | 96.8  | 96.8  | 96.8  | 94.1  | 94.1  | 91.4  | 91.4  | 91.4  | 88.7   | 88.7  |
| 0.0 | 7.5°   | 83.3  | 80.6  | 80.6  | 78.0  | 78.0  | 75.3  | 75.3  | 75.3  | 72.6   | 72.6  |
| 0.0 | 10°    | 69.9  | 67.2  | 67.2  | 64.5  | 64.5  | 61.8  | 61.8  | 59.1  | 59.1   | 56.5  |
| 0.0 | 12.5°  | 61.8  | 59.1  | 56.5  | 53.8  | 53.8  | 51.1  | 48.4  | 48.4  | 45.7   | 43.0  |
| 0.0 | 15°    | 48.4  | 45.7  | 43.0  | 40.3  | 37.6  | 34.9  | 32.3  | 32.3  | 29.6   | 26.9  |
| 0.0 | 17.5°  | 32.3  | 26.9  | 24.2  | 21.5  | 21.5  | 18.8  | 16.1  | 13.4  | 10.8   | 8.1   |
| 0.0 | 20°    | 8.1   | 5.4   | 2.7   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 22.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 25°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  |
| 0.0    | 2.5°   | 110.2 | 107.5  | 107.5 | 107.5  | 110.2 | 110.2  | 110.2 | 110.2  | 110.2 | 110.2  |
| 0.0    | 5°     | 88.7  | 86.0   | 86.0  | 86.0   | 86.0  | 86.0   | 86.0  | 86.0   | 86.0  | 86.0   |
| 0.0    | 7.5°   | 72.6  | 69.9   | 69.9  | 69.9   | 69.9  | 67.2   | 67.2  | 67.2   | 67.2  | 67.2   |
| 0.0    | 10°    | 56.5  | 53.8   | 53.8  | 53.8   | 53.8  | 51.1   | 51.1  | 51.1   | 51.1  | 51.1   |
| 0.0    | 12.5°  | 40.3  | 40.3   | 37.6  | 37.6   | 37.6  | 34.9   | 34.9  | 34.9   | 34.9  | 32.3   |
| 0.0    | 15°    | 24.2  | 21.5   | 18.8  | 18.8   | 18.8  | 16.1   | 16.1  | 16.1   | 16.1  | 13.4   |
| 0.0    | 17.5°  | 5.4   | 5.4    | 2.7   | 2.7    | 2.7   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 20°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 22.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 25°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 |
| 0.0  | 2.5°   | 112.9  | 112.9 | 115.6  | 115.6 | 118.3  | 123.7 | 126.3  | 129.0 | 134.4  | 139.8 |
| 0.0  | 5°     | 88.7   | 91.4  | 91.4   | 94.1  | 96.8   | 99.5  | 102.1  | 104.8 | 110.2  | 115.6 |
| 0.0  | 7.5°   | 69.9   | 69.9  | 72.6   | 72.6  | 75.3   | 80.6  | 83.3   | 86.0  | 91.4   | 99.5  |
| 0.0  | 10°    | 53.8   | 53.8  | 56.5   | 56.5  | 59.1   | 64.5  | 67.2   | 69.9  | 75.3   | 83.3  |
| 0.0  | 12.5°  | 34.9   | 37.6  | 37.6   | 40.3  | 43.0   | 48.4  | 51.1   | 53.8  | 59.1   | 64.5  |
| 0.0  | 15°    | 16.1   | 18.8  | 18.8   | 21.5  | 24.2   | 29.6  | 32.3   | 34.9  | 40.3   | 48.4  |
| 0.0  | 17.5°  | 2.7    | 2.7   | 5.4    | 5.4   | 8.1    | 10.8  | 13.4   | 16.1  | 24.2   | 29.6  |
| 0.0  | 20°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 5.4    | 10.8  |
| 0.0  | 22.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 2.7   |
| 0.0  | 25°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 27.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 30°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 32.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 82.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 85°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  |
| 0.0    | 2.5°   | 147.8 | 153.2  | 158.6 | 164.0  | 169.4 | 174.7  | 177.4 | 182.8  | 185.5 | 188.2  |
| 0.0    | 5°     | 126.3 | 131.7  | 139.8 | 145.2  | 150.5 | 155.9  | 161.3 | 164.0  | 166.7 | 169.4  |
| 0.0    | 7.5°   | 110.2 | 115.6  | 123.7 | 129.0  | 134.4 | 139.8  | 145.2 | 150.5  | 153.2 | 155.9  |
| 0.0    | 10°    | 94.1  | 102.1  | 107.5 | 115.6  | 121.0 | 126.3  | 131.7 | 137.1  | 142.5 | 145.2  |
| 0.0    | 12.5°  | 75.3  | 83.3   | 91.4  | 96.8   | 104.8 | 112.9  | 118.3 | 123.7  | 129.0 | 134.4  |
| 0.0    | 15°    | 59.1  | 67.2   | 75.3  | 80.6   | 88.7  | 96.8   | 104.8 | 110.2  | 115.6 | 121.0  |
| 0.0    | 17.5°  | 43.0  | 51.1   | 59.1  | 64.5   | 72.6  | 80.6   | 86.0  | 94.1   | 99.5  | 104.8  |
| 0.0    | 20°    | 21.5  | 29.6   | 37.6  | 45.7   | 53.8  | 61.8   | 67.2  | 75.3   | 80.6  | 86.0   |
| 0.0    | 22.5°  | 2.7   | 10.8   | 18.8  | 24.2   | 32.3  | 40.3   | 45.7  | 53.8   | 59.1  | 64.5   |
| 0.0    | 25°    | 0.0   | 2.7    | 8.1   | 10.8   | 13.4  | 18.8   | 24.2  | 29.6   | 34.9  | 40.3   |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.7    | 5.4   | 10.8   | 16.1  | 21.5   |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 5.4    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.7    |
|        | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.7    | 2.7   | 5.4    |
|        | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 5.4    | 8.1   | 13.4   | 16.1  | 18.8   |
|        | 87.5°  | 0.0   | 2.7    | 5.4   | 8.1    | 10.8  | 16.1   | 21.5  | 26.9   | 29.6  | 32.3   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190°  |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 155.9 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 188.2 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.0 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 158.6 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150.5 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.1 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 126.3 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 112.9 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 91.4  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 69.9  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 48.4  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 26.9  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8.1   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 2.7   |        |      |        |      |        |      |        |      |        |      |        |
| 10.8  |        |      |        |      |        |      |        |      |        |      |        |
| 24.2  |        |      |        |      |        |      |        |      |        |      |        |
| 34.9  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 |
| 0.0  | 2.5°   | 190.9  | 190.9 | 190.9  | 190.9 | 188.2  | 188.2 | 188.2  | 185.5 | 185.5  | 182.8 |
| 0.0  | 5°     | 174.7  | 177.4 | 177.4  | 177.4 | 177.4  | 177.4 | 177.4  | 177.4 | 174.7  | 174.7 |
| 0.0  | 7.5°   | 161.3  | 164.0 | 166.7  | 166.7 | 169.4  | 169.4 | 169.4  | 166.7 | 166.7  | 164.0 |
| 0.0  | 10°    | 153.2  | 155.9 | 155.9  | 158.6 | 158.6  | 158.6 | 158.6  | 158.6 | 158.6  | 158.6 |
| 0.0  | 12.5°  | 142.5  | 145.2 | 147.8  | 147.8 | 150.5  | 150.5 | 150.5  | 150.5 | 147.8  | 147.8 |
| 0.0  | 15°    | 129.0  | 134.4 | 137.1  | 139.8 | 139.8  | 142.5 | 142.5  | 142.5 | 142.5  | 142.5 |
| 0.0  | 17.5°  | 118.3  | 123.7 | 126.3  | 129.0 | 129.0  | 131.7 | 131.7  | 134.4 | 134.4  | 134.4 |
| 0.0  | 20°    | 96.8   | 102.1 | 104.8  | 110.2 | 112.9  | 115.6 | 118.3  | 121.0 | 121.0  | 123.7 |
| 0.0  | 22.5°  | 75.3   | 80.6  | 83.3   | 88.7  | 91.4   | 94.1  | 96.8   | 99.5  | 102.1  | 104.8 |
| 0.0  | 25°    | 53.8   | 59.1  | 61.8   | 67.2  | 69.9   | 72.6  | 75.3   | 78.0  | 78.0   | 80.6  |
| 0.0  | 27.5°  | 29.6   | 34.9  | 40.3   | 43.0  | 48.4   | 51.1  | 53.8   | 56.5  | 59.1   | 61.8  |
| 0.0  | 30°    | 13.4   | 16.1  | 18.8   | 24.2  | 26.9   | 29.6  | 32.3   | 37.6  | 40.3   | 43.0  |
| 0.0  | 32.5°  | 0.0    | 0.0   | 2.7    | 8.1   | 10.8   | 13.4  | 16.1   | 18.8  | 18.8   | 21.5  |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.7    | 5.4   | 8.1    | 10.8  |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 5.4    | 5.4   | 5.4    | 8.1   | 8.1    | 8.1   | 8.1    | 8.1   | 8.1    | 8.1   |
|      | 82.5°  | 13.4   | 16.1  | 18.8   | 18.8  | 21.5   | 21.5  | 21.5   | 21.5  | 18.8   | 18.8  |
|      | 85°    | 26.9   | 29.6  | 32.3   | 32.3  | 34.9   | 34.9  | 34.9   | 34.9  | 34.9   | 34.9  |
|      | 87.5°  | 37.6   | 40.3  | 43.0   | 43.0  | 45.7   | 45.7  | 45.7   | 45.7  | 45.7   | 45.7  |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 155.9  | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 182.8  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 174.7  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 164.0  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 158.6  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.8  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 134.4  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 121.0  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 104.8  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 83.3   | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 64.5   | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 45.7   | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 26.9   | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 16.1   | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5.4    | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5.4    | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.7    | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.7    | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.7    | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.7    | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.7    | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 8.1    |        |        |      |        |      |        |      |        |      |        |      |
| 18.8   |        |        |      |        |      |        |      |        |      |        |      |
| 34.9   |        |        |      |        |      |        |      |        |      |        |      |
| 45.7   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |



REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  |
| 0.0    | 2.5°   | 180.1 | 180.1  | 177.4 | 177.4  | 177.4 | 177.4  | 177.4 | 180.1  | 182.8 | 182.8  |
| 0.0    | 5°     | 172.0 | 172.0  | 169.4 | 169.4  | 169.4 | 172.0  | 172.0 | 174.7  | 177.4 | 180.1  |
| 0.0    | 7.5°   | 164.0 | 161.3  | 161.3 | 164.0  | 164.0 | 166.7  | 166.7 | 169.4  | 172.0 | 174.7  |
| 0.0    | 10°    | 158.6 | 155.9  | 155.9 | 155.9  | 158.6 | 158.6  | 161.3 | 164.0  | 166.7 | 169.4  |
| 0.0    | 12.5°  | 147.8 | 147.8  | 147.8 | 147.8  | 150.5 | 150.5  | 153.2 | 155.9  | 161.3 | 164.0  |
| 0.0    | 15°    | 142.5 | 139.8  | 139.8 | 139.8  | 139.8 | 142.5  | 142.5 | 147.8  | 153.2 | 155.9  |
| 0.0    | 17.5°  | 131.7 | 131.7  | 129.0 | 129.0  | 131.7 | 131.7  | 134.4 | 139.8  | 145.2 | 147.8  |
| 0.0    | 20°    | 121.0 | 118.3  | 115.6 | 115.6  | 118.3 | 118.3  | 121.0 | 126.3  | 131.7 | 134.4  |
| 0.0    | 22.5°  | 104.8 | 102.1  | 102.1 | 102.1  | 102.1 | 104.8  | 104.8 | 110.2  | 118.3 | 123.7  |
| 0.0    | 25°    | 83.3  | 86.0   | 86.0  | 88.7   | 88.7  | 91.4   | 94.1  | 99.5   | 107.5 | 112.9  |
| 0.0    | 27.5°  | 64.5  | 67.2   | 67.2  | 72.6   | 75.3  | 78.0   | 80.6  | 88.7   | 96.8  | 102.1  |
| 0.0    | 30°    | 48.4  | 51.1   | 53.8  | 56.5   | 61.8  | 67.2   | 72.6  | 80.6   | 88.7  | 94.1   |
| 0.0    | 32.5°  | 29.6  | 34.9   | 37.6  | 43.0   | 48.4  | 53.8   | 59.1  | 67.2   | 78.0  | 86.0   |
| 0.0    | 35°    | 21.5  | 24.2   | 29.6  | 32.3   | 37.6  | 43.0   | 48.4  | 59.1   | 67.2  | 78.0   |
| 0.0    | 37.5°  | 10.8  | 16.1   | 21.5  | 26.9   | 32.3  | 37.6   | 43.0  | 53.8   | 64.5  | 72.6   |
| 0.0    | 40°    | 8.1   | 13.4   | 16.1  | 21.5   | 29.6  | 34.9   | 40.3  | 51.1   | 61.8  | 72.6   |
| 0.0    | 42.5°  | 5.4   | 8.1    | 10.8  | 18.8   | 24.2  | 32.3   | 40.3  | 51.1   | 61.8  | 72.6   |
| 0.0    | 45°    | 5.4   | 5.4    | 8.1   | 16.1   | 24.2  | 34.9   | 43.0  | 53.8   | 61.8  | 72.6   |
| 0.0    | 47.5°  | 5.4   | 8.1    | 10.8  | 21.5   | 26.9  | 34.9   | 43.0  | 51.1   | 61.8  | 69.9   |
| 0.0    | 50°    | 8.1   | 10.8   | 13.4  | 24.2   | 29.6  | 37.6   | 43.0  | 53.8   | 61.8  | 72.6   |
| 0.0    | 52.5°  | 5.4   | 8.1    | 10.8  | 21.5   | 29.6  | 40.3   | 48.4  | 59.1   | 69.9  | 78.0   |
| 0.0    | 55°    | 2.7   | 2.7    | 2.7   | 16.1   | 32.3  | 45.7   | 61.8  | 69.9   | 80.6  | 88.7   |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 10.8   | 32.3  | 51.1   | 69.9  | 80.6   | 91.4  | 99.5   |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 10.8   | 32.3  | 51.1   | 69.9  | 83.3   | 96.8  | 110.2  |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 10.8   | 26.9  | 43.0   | 59.1  | 80.6   | 104.8 | 126.3  |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 8.1    | 21.5  | 34.9   | 48.4  | 80.6   | 112.9 | 142.5  |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 8.1    | 21.5  | 32.3   | 45.7  | 80.6   | 112.9 | 147.8  |
|        | 70°    | 0.0   | 0.0    | 0.0   | 8.1    | 21.5  | 34.9   | 48.4  | 80.6   | 112.9 | 145.2  |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 8.1    | 24.2  | 37.6   | 53.8  | 80.6   | 107.5 | 134.4  |
|        | 75°    | 0.0   | 0.0    | 0.0   | 10.8   | 24.2  | 40.3   | 56.5  | 80.6   | 104.8 | 126.3  |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 8.1    | 24.2  | 37.6   | 53.8  | 78.0   | 102.1 | 123.7  |
|        | 80°    | 8.1   | 5.4    | 5.4   | 13.4   | 24.2  | 34.9   | 45.7  | 69.9   | 96.8  | 121.0  |
|        | 82.5°  | 16.1  | 16.1   | 13.4  | 18.8   | 24.2  | 32.3   | 40.3  | 61.8   | 86.0  | 107.5  |
|        | 85°    | 32.3  | 32.3   | 29.6  | 32.3   | 32.3  | 34.9   | 37.6  | 48.4   | 59.1  | 69.9   |
|        | 87.5°  | 43.0  | 43.0   | 40.3  | 40.3   | 40.3  | 37.6   | 37.6  | 37.6   | 37.6  | 34.9   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245°  |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 155.9 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 185.5 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 182.8 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.4 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.0 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 166.7 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 161.3 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 153.2 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 139.8 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 129.0 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 118.3 | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 110.2 | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.1 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 94.1  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 86.0  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 83.3  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 83.3  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 83.3  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80.6  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 78.0  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80.6  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 88.7  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 96.8  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 110.2 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 123.7 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.8 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 174.7 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180.1 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.4 |        |      |        |      |        |      |        |      |        |      |        |
| 161.3 |        |      |        |      |        |      |        |      |        |      |        |
| 150.5 |        |      |        |      |        |      |        |      |        |      |        |
| 147.8 |        |      |        |      |        |      |        |      |        |      |        |
| 145.2 |        |      |        |      |        |      |        |      |        |      |        |
| 129.0 |        |      |        |      |        |      |        |      |        |      |        |
| 80.6  |        |      |        |      |        |      |        |      |        |      |        |
| 34.9  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|
| 0.0  | 0°     | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9 | 155.9  | 155.9  |
| 0.0  | 2.5°   | 188.2  | 190.9 | 190.9  | 193.5 | 196.2  | 198.9 | 198.9  | 201.6 | 201.6  | 201.6  |
| 0.0  | 5°     | 185.5  | 190.9 | 193.5  | 196.2 | 198.9  | 201.6 | 204.3  | 207.0 | 209.7  | 209.7  |
| 0.0  | 7.5°   | 182.8  | 185.5 | 190.9  | 193.5 | 198.9  | 201.6 | 207.0  | 209.7 | 212.4  | 215.0  |
| 0.0  | 10°    | 177.4  | 182.8 | 188.2  | 193.5 | 198.9  | 204.3 | 209.7  | 215.0 | 220.4  | 223.1  |
| 0.0  | 12.5°  | 172.0  | 180.1 | 185.5  | 190.9 | 198.9  | 207.0 | 212.4  | 220.4 | 225.8  | 231.2  |
| 0.0  | 15°    | 169.4  | 174.7 | 182.8  | 188.2 | 198.9  | 209.7 | 217.7  | 228.5 | 239.2  | 247.3  |
| 0.0  | 17.5°  | 161.3  | 172.0 | 180.1  | 188.2 | 198.9  | 212.4 | 223.1  | 233.9 | 250.0  | 266.1  |
| 0.0  | 20°    | 150.5  | 158.6 | 169.4  | 177.4 | 193.5  | 207.0 | 223.1  | 236.6 | 260.7  | 284.9  |
| 0.0  | 22.5°  | 139.8  | 150.5 | 158.6  | 169.4 | 188.2  | 204.3 | 223.1  | 239.2 | 279.6  | 317.2  |
| 0.0  | 25°    | 129.0  | 142.5 | 153.2  | 164.0 | 185.5  | 207.0 | 228.5  | 250.0 | 317.2  | 384.4  |
| 0.0  | 27.5°  | 123.7  | 134.4 | 147.8  | 158.6 | 185.5  | 215.0 | 241.9  | 268.8 | 376.3  | 481.2  |
| 0.0  | 30°    | 115.6  | 129.0 | 139.8  | 153.2 | 188.2  | 223.1 | 258.1  | 293.0 | 457.0  | 621.0  |
| 0.0  | 32.5°  | 107.5  | 121.0 | 134.4  | 147.8 | 193.5  | 239.2 | 282.3  | 328.0 | 543.0  | 755.4  |
| 0.0  | 35°    | 99.5   | 115.6 | 129.0  | 142.5 | 201.6  | 263.4 | 322.6  | 381.7 | 621.0  | 857.5  |
| 0.0  | 37.5°  | 96.8   | 112.9 | 126.3  | 139.8 | 204.3  | 266.1 | 330.6  | 392.5 | 629.0  | 865.6  |
| 0.0  | 40°    | 99.5   | 112.9 | 129.0  | 142.5 | 196.2  | 250.0 | 301.1  | 354.8 | 602.1  | 846.8  |
| 0.0  | 42.5°  | 99.5   | 115.6 | 131.7  | 147.8 | 190.9  | 233.9 | 276.9  | 319.9 | 594.1  | 868.3  |
| 0.0  | 45°    | 96.8   | 112.9 | 129.0  | 145.2 | 185.5  | 223.1 | 263.4  | 301.1 | 642.5  | 981.2  |
| 0.0  | 47.5°  | 94.1   | 110.2 | 126.3  | 142.5 | 182.8  | 223.1 | 263.4  | 303.8 | 830.6  | 1354.8 |
| 0.0  | 50°    | 94.1   | 110.2 | 123.7  | 137.1 | 185.5  | 236.6 | 284.9  | 333.3 | 1209.7 | 2083.3 |
| 0.0  | 52.5°  | 99.5   | 112.9 | 123.7  | 134.4 | 190.9  | 250.0 | 306.4  | 362.9 | 1537.6 | 2709.6 |
| 0.0  | 55°    | 107.5  | 115.6 | 126.3  | 134.4 | 204.3  | 271.5 | 341.4  | 408.6 | 1637.1 | 2865.5 |
| 0.0  | 57.5°  | 118.3  | 126.3 | 134.4  | 142.5 | 228.5  | 314.5 | 397.8  | 483.9 | 1645.1 | 2803.7 |
| 0.0  | 60°    | 131.7  | 142.5 | 150.5  | 158.6 | 250.0  | 344.1 | 435.5  | 526.9 | 1489.2 | 2448.9 |
| 0.0  | 62.5°  | 161.3  | 174.7 | 185.5  | 198.9 | 287.6  | 373.6 | 462.4  | 548.4 | 1236.5 | 1924.7 |
| 0.0  | 65°    | 185.5  | 196.2 | 207.0  | 217.7 | 303.8  | 392.5 | 478.5  | 564.5 | 1048.4 | 1532.2 |
| 0.0  | 67.5°  | 190.9  | 201.6 | 209.7  | 220.4 | 309.1  | 397.8 | 483.9  | 572.6 | 897.8  | 1220.4 |
|      | 70°    | 193.5  | 207.0 | 223.1  | 236.6 | 328.0  | 419.3 | 508.1  | 599.4 | 795.7  | 991.9  |
|      | 72.5°  | 185.5  | 212.4 | 236.6  | 260.7 | 346.8  | 430.1 | 516.1  | 599.4 | 739.2  | 879.0  |
|      | 75°    | 185.5  | 223.1 | 258.1  | 293.0 | 357.5  | 419.3 | 483.9  | 545.7 | 653.2  | 760.7  |
|      | 77.5°  | 196.2  | 244.6 | 293.0  | 341.4 | 379.0  | 414.0 | 451.6  | 486.5 | 556.4  | 626.3  |
|      | 80°    | 196.2  | 247.3 | 295.7  | 346.8 | 362.9  | 381.7 | 397.8  | 414.0 | 422.0  | 430.1  |
|      | 82.5°  | 169.4  | 209.7 | 250.0  | 290.3 | 271.5  | 252.7 | 233.9  | 215.0 | 201.6  | 185.5  |
|      | 85°    | 86.0   | 94.1  | 99.5   | 104.8 | 96.8   | 88.7  | 80.6   | 72.6  | 67.2   | 59.1   |
|      | 87.5°  | 34.9   | 34.9  | 32.3   | 32.3  | 32.3   | 32.3  | 29.6   | 29.6  | 29.6   | 29.6   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 155.9  | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 201.6  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 209.7  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 217.7  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 228.5  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 239.2  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 260.7  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 287.6  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 330.6  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 422.0  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 572.6  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 795.7  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1077.9 | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1346.7 | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1529.5 | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1666.6 | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1803.7 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2072.5 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2610.2 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3978.4 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 6094.0 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 7671.9 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 7846.6 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 7080.5 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 6053.6 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4731.1 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3575.2 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2639.7 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1868.2 |        |        |      |        |      |        |      |        |      |        |      |
| 1389.8 |        |        |      |        |      |        |      |        |      |        |      |
| 1010.7 |        |        |      |        |      |        |      |        |      |        |      |
| 760.7  |        |        |      |        |      |        |      |        |      |        |      |
| 427.4  |        |        |      |        |      |        |      |        |      |        |      |
| 193.5  |        |        |      |        |      |        |      |        |      |        |      |
| 56.5   |        |        |      |        |      |        |      |        |      |        |      |
| 26.9   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°    | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   |
| 0.0    | 2.5°   | 201.6   | 198.9   | 198.9   | 196.2   | 193.5   | 190.9   | 188.2   | 185.5   | 182.8   | 180.1   |
| 0.0    | 5°     | 209.7   | 209.7   | 209.7   | 207.0   | 207.0   | 204.3   | 204.3   | 201.6   | 198.9   | 196.2   |
| 0.0    | 7.5°   | 217.7   | 220.4   | 220.4   | 223.1   | 223.1   | 223.1   | 223.1   | 220.4   | 220.4   | 220.4   |
| 0.0    | 10°    | 231.2   | 233.9   | 236.6   | 239.2   | 241.9   | 244.6   | 244.6   | 247.3   | 247.3   | 247.3   |
| 0.0    | 12.5°  | 247.3   | 255.4   | 260.7   | 268.8   | 274.2   | 282.3   | 287.6   | 295.7   | 301.1   | 306.4   |
| 0.0    | 15°    | 271.5   | 284.9   | 301.1   | 314.5   | 328.0   | 346.8   | 368.3   | 387.1   | 405.9   | 435.5   |
| 0.0    | 17.5°  | 306.4   | 349.5   | 392.5   | 432.8   | 475.8   | 569.9   | 664.0   | 755.4   | 849.4   | 986.5   |
| 0.0    | 20°    | 373.6   | 502.7   | 629.0   | 758.0   | 884.4   | 1215.0  | 1543.0  | 1873.6  | 2201.6  | 2553.7  |
| 0.0    | 22.5°  | 524.2   | 841.4   | 1158.6  | 1475.8  | 1793.0  | 2483.8  | 3172.0  | 3862.8  | 4551.0  | 5360.1  |
| 0.0    | 25°    | 760.7   | 1344.1  | 1927.4  | 2508.0  | 3091.3  | 4172.0  | 5255.3  | 6335.9  | 7416.5  | 8467.6  |
| 0.0    | 27.5°  | 1107.5  | 2000.0  | 2892.4  | 3782.2  | 4674.6  | 6139.7  | 7607.4  | 9072.4  | 10537.4 | 11725.6 |
| 0.0    | 30°    | 1534.9  | 2744.6  | 3954.2  | 5163.9  | 6373.5  | 8040.2  | 9706.8  | 11370.7 | 13037.4 | 14335.7 |
| 0.0    | 32.5°  | 1938.1  | 3419.3  | 4900.4  | 6378.9  | 7860.0  | 9757.9  | 11658.4 | 13556.2 | 15454.0 | 16873.3 |
| 0.0    | 35°    | 2201.6  | 3991.9  | 5784.8  | 7575.1  | 9365.4  | 11419.1 | 13472.8 | 15523.9 | 17577.6 | 19198.5 |
| 0.0    | 37.5°  | 2465.0  | 4532.2  | 6596.6  | 8663.8  | 10728.3 | 12983.6 | 15238.9 | 17494.3 | 19749.6 | 21752.2 |
| 0.0    | 40°    | 2760.7  | 5185.4  | 7607.4  | 10032.0 | 12454.0 | 15126.0 | 17795.3 | 20467.3 | 23136.6 | 25961.8 |
| 0.0    | 42.5°  | 3274.1  | 6268.7  | 9265.9  | 12260.5 | 15255.1 | 18789.9 | 22324.8 | 25857.0 | 29391.9 | 33424.0 |
| 0.0    | 45°    | 4239.2  | 8459.5  | 12682.5 | 16902.9 | 21123.2 | 25805.9 | 30491.3 | 35174.0 | 39856.7 | 45222.2 |
| 0.0    | 47.5°  | 6602.0  | 12408.3 | 18212.0 | 24018.3 | 29821.9 | 34878.3 | 39931.9 | 44988.3 | 50042.0 | 55385.9 |
| 0.0    | 50°    | 10101.9 | 16859.9 | 23617.8 | 30373.0 | 37130.9 | 41706.1 | 46278.6 | 50853.8 | 55426.2 | 60509.5 |
| 0.0    | 52.5°  | 12634.1 | 19674.3 | 26717.2 | 33757.3 | 40797.5 | 44926.5 | 49058.1 | 53187.0 | 57316.0 | 62065.9 |
| 0.0    | 55°    | 12825.0 | 19824.8 | 26827.4 | 33827.2 | 40827.1 | 44974.9 | 49122.6 | 53270.4 | 57418.1 | 62453.0 |
| 0.0    | 57.5°  | 11354.6 | 18298.0 | 25238.7 | 32182.1 | 39122.8 | 43845.8 | 48566.2 | 53289.2 | 58009.5 | 63453.0 |
| 0.0    | 60°    | 9658.4  | 16604.5 | 23547.9 | 30494.0 | 37437.4 | 42878.1 | 48321.6 | 53762.3 | 59203.0 | 64302.4 |
| 0.0    | 62.5°  | 7534.8  | 14679.8 | 21827.5 | 28972.5 | 36117.5 | 41641.6 | 47165.7 | 52687.1 | 58211.1 | 62036.3 |
| 0.0    | 65°    | 5615.5  | 12553.5 | 19491.5 | 26426.9 | 33364.9 | 37789.5 | 42214.2 | 46636.1 | 51060.7 | 53429.0 |
| 0.0    | 67.5°  | 4059.1  | 10042.8 | 16023.9 | 22007.6 | 27988.7 | 31155.3 | 34321.9 | 37485.8 | 40652.4 | 42464.2 |
|        | 70°    | 2744.6  | 6889.6  | 11032.0 | 15177.1 | 19319.5 | 21921.6 | 24526.4 | 27128.5 | 29730.6 | 32176.7 |
|        | 72.5°  | 1900.5  | 4228.4  | 6559.0  | 8886.9  | 11214.8 | 13833.0 | 16448.6 | 19066.8 | 21682.3 | 24271.0 |
|        | 75°    | 1260.7  | 2319.8  | 3381.6  | 4440.8  | 5499.9  | 7438.0  | 9378.8  | 11317.0 | 13255.1 | 14798.1 |
|        | 77.5°  | 895.1   | 1212.3  | 1532.2  | 1849.4  | 2166.6  | 2529.5  | 2895.1  | 3258.0  | 3620.9  | 4172.0  |
|        | 80°    | 424.7   | 465.0   | 505.4   | 543.0   | 583.3   | 715.0   | 846.8   | 978.5   | 1110.2  | 1250.0  |
|        | 82.5°  | 201.6   | 217.7   | 233.9   | 247.3   | 263.4   | 276.9   | 290.3   | 303.8   | 317.2   | 303.8   |
|        | 85°    | 53.8    | 53.8    | 56.5    | 56.5    | 56.5    | 56.5    | 56.5    | 56.5    | 56.5    | 53.8    |
|        | 87.5°  | 24.2    | 24.2    | 24.2    | 24.2    | 24.2    | 24.2    | 24.2    | 21.5    | 21.5    | 18.8    |
|        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 155.9   | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.4   | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 193.5   | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 217.7   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 250.0   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 309.1   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 467.7   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1120.9  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 2908.5  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6169.2  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 9518.6  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12913.7 | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15636.8 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 18295.3 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 20819.5 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 23757.6 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28787.0 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37456.2 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50587.6 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 60729.9 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 65592.7 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 66815.8 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 67490.5 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 68896.4 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 69399.1 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 65864.2 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55799.9 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 44278.6 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 34620.2 |        |      |        |      |        |      |        |      |        |      |        |
| 26859.6 |        |      |        |      |        |      |        |      |        |      |        |
| 16341.1 |        |      |        |      |        |      |        |      |        |      |        |
| 4723.0  |        |      |        |      |        |      |        |      |        |      |        |
| 1389.8  |        |      |        |      |        |      |        |      |        |      |        |
| 287.6   |        |      |        |      |        |      |        |      |        |      |        |
| 51.1    |        |      |        |      |        |      |        |      |        |      |        |
| 18.8    |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   |
| 0.0  | 2.5°   | 174.7   | 172.0   | 169.4   | 166.7   | 164.0   | 158.6   | 158.6   | 155.9   | 155.9   |
| 0.0  | 5°     | 190.9   | 188.2   | 185.5   | 182.8   | 182.8   | 180.1   | 177.4   | 177.4   | 174.7   |
| 0.0  | 7.5°   | 217.7   | 215.0   | 212.4   | 209.7   | 209.7   | 207.0   | 207.0   | 204.3   | 204.3   |
| 0.0  | 10°    | 250.0   | 250.0   | 250.0   | 250.0   | 250.0   | 247.3   | 247.3   | 247.3   | 244.6   |
| 0.0  | 12.5°  | 314.5   | 317.2   | 322.6   | 328.0   | 336.0   | 336.0   | 336.0   | 333.3   | 333.3   |
| 0.0  | 15°    | 497.3   | 526.9   | 548.4   | 569.9   | 588.7   | 631.7   | 626.3   | 618.3   | 612.9   |
| 0.0  | 17.5°  | 1258.0  | 1392.4  | 1465.0  | 1534.9  | 1607.5  | 1806.4  | 1774.2  | 1741.9  | 1712.3  |
| 0.0  | 20°    | 3260.7  | 3612.8  | 3846.7  | 4080.6  | 4317.1  | 4690.8  | 4599.4  | 4508.0  | 4416.6  |
| 0.0  | 22.5°  | 6975.7  | 7784.8  | 8136.9  | 8489.1  | 8838.5  | 9290.1  | 8997.1  | 8704.1  | 8413.8  |
| 0.0  | 25°    | 10567.0 | 11618.0 | 12212.1 | 12806.2 | 13397.6 | 13655.6 | 13273.9 | 12889.5 | 12507.8 |
| 0.0  | 27.5°  | 14101.9 | 15290.0 | 15814.2 | 16335.7 | 16859.9 | 17400.2 | 16927.1 | 16451.3 | 15978.2 |
| 0.0  | 30°    | 16935.1 | 18233.5 | 18800.7 | 19365.2 | 19932.4 | 20308.7 | 19819.5 | 19327.5 | 18838.3 |
| 0.0  | 32.5°  | 19714.6 | 21134.0 | 21754.9 | 22375.9 | 22994.1 | 23534.4 | 22932.3 | 22327.5 | 21725.3 |
| 0.0  | 35°    | 22437.7 | 24058.6 | 24913.5 | 25768.3 | 26623.1 | 27125.8 | 26410.7 | 25693.0 | 24978.0 |
| 0.0  | 37.5°  | 25760.2 | 27762.9 | 28719.8 | 29676.8 | 30633.8 | 31550.4 | 30762.8 | 29972.5 | 29184.9 |
| 0.0  | 40°    | 31612.2 | 34437.4 | 35905.2 | 37375.6 | 38843.3 | 40026.0 | 39031.4 | 38036.8 | 37042.2 |
| 0.0  | 42.5°  | 41488.4 | 45520.5 | 47630.7 | 49738.2 | 51848.4 | 53695.1 | 52649.4 | 51603.7 | 50558.1 |
| 0.0  | 45°    | 55953.1 | 61318.6 | 63891.1 | 66461.0 | 69033.5 | 70382.9 | 68877.6 | 67369.5 | 65864.2 |
| 0.0  | 47.5°  | 66071.2 | 71415.2 | 73705.4 | 75995.7 | 78286.0 | 79826.3 | 77984.9 | 76143.5 | 74304.9 |
| 0.0  | 50°    | 70673.2 | 75756.5 | 78054.8 | 80350.4 | 82648.8 | 83871.9 | 81745.6 | 79616.6 | 77490.3 |
| 0.0  | 52.5°  | 71563.0 | 76312.9 | 79054.8 | 81799.3 | 84541.2 | 86175.6 | 83664.9 | 81151.5 | 78640.8 |
| 0.0  | 55°    | 72525.3 | 77560.2 | 80740.2 | 83923.0 | 87103.0 | 89366.4 | 86527.7 | 83686.4 | 80847.7 |
| 0.0  | 57.5°  | 74337.1 | 79780.6 | 82952.5 | 86121.8 | 89293.8 | 91215.8 | 88369.1 | 85519.7 | 82673.0 |
| 0.0  | 60°    | 74498.4 | 79595.1 | 82320.8 | 85049.3 | 87775.0 | 88984.7 | 86261.6 | 83535.9 | 80812.8 |
| 0.0  | 62.5°  | 69689.4 | 73514.6 | 75407.0 | 77299.4 | 79191.9 | 80506.4 | 77665.0 | 74821.0 | 71979.7 |
| 0.0  | 65°    | 58168.1 | 60536.4 | 62044.4 | 63552.4 | 65060.4 | 66627.6 | 64025.5 | 61423.4 | 58821.3 |
| 0.0  | 67.5°  | 46090.4 | 47902.2 | 49888.7 | 51875.2 | 53861.8 | 55536.5 | 53453.2 | 51367.2 | 49283.9 |
|      | 70°    | 37066.4 | 39509.9 | 41743.7 | 43977.6 | 46211.4 | 47582.3 | 45491.0 | 43396.9 | 41305.6 |
|      | 72.5°  | 29448.3 | 32037.0 | 33902.5 | 35765.4 | 37630.9 | 37966.9 | 36429.3 | 34891.7 | 33356.8 |
|      | 75°    | 17881.3 | 19424.3 | 19462.0 | 19496.9 | 19534.5 | 19854.4 | 18580.3 | 17306.1 | 16034.6 |
|      | 77.5°  | 5274.1  | 5825.1  | 6279.4  | 6731.0  | 7185.3  | 7733.7  | 7266.0  | 6795.6  | 6327.8  |
|      | 80°    | 1526.8  | 1666.6  | 1784.9  | 1900.5  | 2018.8  | 1948.9  | 1838.7  | 1728.5  | 1618.2  |
|      | 82.5°  | 274.2   | 258.1   | 255.4   | 252.7   | 252.7   | 239.2   | 217.7   | 196.2   | 174.7   |
|      | 85°    | 48.4    | 45.7    | 43.0    | 40.3    | 37.6    | 34.9    | 29.6    | 26.9    | 21.5    |
|      | 87.5°  | 16.1    | 13.4    | 10.8    | 8.1     | 8.1     | 2.7     | 2.7     | 2.7     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325°    | 327.5°  |        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° |
|---------|---------|--------|--------|------|--------|------|--------|------|--------|------|--------|
| 155.9   | 155.9   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 153.2   | 153.2   | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.0   | 172.0   | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 201.6   | 198.9   | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 244.6   | 241.9   | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 330.6   | 322.6   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 604.8   | 575.3   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1680.1  | 1537.6  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4325.2  | 3938.1  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8120.8  | 7403.1  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12123.4 | 11220.2 | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15505.0 | 14464.7 | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 18349.1 | 17230.8 | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21123.2 | 19784.5 | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 24262.9 | 22701.1 | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28394.6 | 26475.2 | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 36047.6 | 33574.6 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 49512.4 | 46171.1 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 64358.9 | 60213.8 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 72463.5 | 67987.8 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 75364.0 | 70807.6 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 76127.4 | 71479.7 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 78006.4 | 73020.0 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 79826.3 | 74713.5 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 78089.7 | 73638.2 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 69135.6 | 65592.7 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 56219.2 | 53633.3 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47200.6 | 44286.7 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 39211.5 | 36039.6 |        |        |      |        |      |        |      |        |      |        |
| 31819.2 | 28961.8 |        |        |      |        |      |        |      |        |      |        |
| 14760.4 | 13618.0 |        |        |      |        |      |        |      |        |      |        |
| 5860.1  | 5241.8  |        |        |      |        |      |        |      |        |      |        |
| 1508.0  | 1352.1  |        |        |      |        |      |        |      |        |      |        |
| 153.2   | 145.2   |        |        |      |        |      |        |      |        |      |        |
| 16.1    | 13.4    |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     | 0.0     |        |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   | 155.9   |
| 0.0  | 0.0    | 2.5°   | 153.2   | 150.5   | 150.5   | 150.5   | 150.5   | 147.8   | 147.8   | 147.8   | 147.8   |
| 0.0  | 0.0    | 5°     | 169.4   | 169.4   | 166.7   | 166.7   | 164.0   | 164.0   | 161.3   | 161.3   | 158.6   |
| 0.0  | 0.0    | 7.5°   | 198.9   | 196.2   | 193.5   | 190.9   | 188.2   | 182.8   | 180.1   | 177.4   | 177.4   |
| 0.0  | 0.0    | 10°    | 239.2   | 233.9   | 231.2   | 225.8   | 223.1   | 217.7   | 212.4   | 207.0   | 201.6   |
| 0.0  | 0.0    | 12.5°  | 314.5   | 303.8   | 295.7   | 284.9   | 274.2   | 266.1   | 255.4   | 247.3   | 236.6   |
| 0.0  | 0.0    | 15°    | 545.7   | 518.8   | 489.2   | 454.3   | 416.7   | 381.7   | 344.1   | 322.6   | 298.4   |
| 0.0  | 0.0    | 17.5°  | 1395.1  | 1255.3  | 1112.9  | 997.3   | 881.7   | 768.8   | 653.2   | 569.9   | 486.5   |
| 0.0  | 0.0    | 20°    | 3551.0  | 3163.9  | 2776.8  | 2395.1  | 2010.7  | 1629.0  | 1244.6  | 1051.1  | 857.5   |
| 0.0  | 0.0    | 22.5°  | 6682.7  | 5964.9  | 5244.5  | 4548.3  | 3849.4  | 3153.2  | 2456.9  | 2018.8  | 1583.3  |
| 0.0  | 0.0    | 25°    | 10314.3 | 9411.1  | 8507.9  | 7362.7  | 6214.9  | 5069.8  | 3924.6  | 3212.3  | 2499.9  |
| 0.0  | 0.0    | 27.5°  | 13421.8 | 12381.5 | 11341.2 | 9948.7  | 8556.3  | 7163.8  | 5771.4  | 4709.6  | 3650.5  |
| 0.0  | 0.0    | 30°    | 16112.6 | 14994.3 | 13876.1 | 12255.1 | 10634.2 | 9013.2  | 7392.3  | 6064.4  | 4736.5  |
| 0.0  | 0.0    | 32.5°  | 18445.8 | 17107.2 | 15768.5 | 14096.5 | 12424.5 | 10752.5 | 9080.5  | 7451.5  | 5822.5  |
| 0.0  | 0.0    | 35°    | 21136.6 | 19574.9 | 18010.4 | 16155.6 | 14298.1 | 12443.3 | 10588.5 | 8749.8  | 6908.5  |
| 0.0  | 0.0    | 37.5°  | 24555.9 | 22639.3 | 20720.0 | 18652.8 | 16585.7 | 14521.2 | 12454.0 | 10351.9 | 8249.8  |
| 0.0  | 0.0    | 40°    | 31101.5 | 28628.4 | 26155.4 | 23529.1 | 20900.1 | 18273.8 | 15647.5 | 13066.9 | 10486.3 |
| 0.0  | 0.0    | 42.5°  | 42829.7 | 39488.4 | 36147.1 | 32652.5 | 29155.3 | 25660.7 | 22163.5 | 18523.8 | 14881.4 |
| 0.0  | 0.0    | 45°    | 56066.0 | 51920.9 | 47773.2 | 43851.2 | 39926.6 | 36004.6 | 32082.7 | 27088.1 | 22093.6 |
| 0.0  | 0.0    | 47.5°  | 63509.4 | 59033.7 | 54558.0 | 50845.7 | 47133.4 | 43421.1 | 39708.8 | 34324.5 | 28940.2 |
| 0.0  | 0.0    | 50°    | 66248.6 | 61692.2 | 57135.9 | 53719.3 | 50300.0 | 46883.4 | 43464.1 | 38071.8 | 32676.7 |
| 0.0  | 0.0    | 52.5°  | 66831.9 | 62184.2 | 57536.4 | 54098.3 | 50660.2 | 47224.8 | 43786.7 | 38429.3 | 33071.9 |
| 0.0  | 0.0    | 55°    | 68030.8 | 63044.4 | 58055.2 | 54135.9 | 50216.7 | 46297.4 | 42378.1 | 36934.7 | 31491.3 |
| 0.0  | 0.0    | 57.5°  | 69598.0 | 64485.2 | 59372.4 | 54907.4 | 50442.5 | 45980.2 | 41515.2 | 35563.8 | 29612.3 |
| 0.0  | 0.0    | 60°    | 69186.7 | 64737.9 | 60286.4 | 55504.2 | 50719.4 | 45937.2 | 41152.4 | 34606.8 | 28058.5 |
| 0.0  | 0.0    | 62.5°  | 62047.1 | 58504.1 | 54958.5 | 51025.8 | 47090.4 | 43157.7 | 39225.0 | 32485.9 | 25746.8 |
| 0.0  | 0.0    | 65°    | 51044.6 | 48458.7 | 45872.7 | 42708.8 | 39542.2 | 36378.3 | 33214.3 | 27171.5 | 21131.3 |
| 0.0  | 0.0    | 67.5°  | 41370.1 | 38456.2 | 35539.6 | 33018.1 | 30494.0 | 27972.5 | 25448.4 | 20693.1 | 15937.8 |
|      |        | 70°    | 32867.6 | 29698.3 | 26526.3 | 24064.0 | 21599.0 | 19136.7 | 16674.4 | 13513.2 | 10354.6 |
|      |        | 72.5°  | 26101.6 | 23244.1 | 20386.7 | 17760.4 | 15131.4 | 12505.1 | 9876.1  | 8007.9  | 6139.7  |
|      |        | 75°    | 12475.5 | 11333.1 | 10190.6 | 8817.0  | 7443.4  | 6069.8  | 4696.1  | 3881.6  | 3069.8  |
|      |        | 77.5°  | 4623.6  | 4008.0  | 3389.7  | 2830.6  | 2271.5  | 1715.0  | 1155.9  | 1059.1  | 962.3   |
|      |        | 80°    | 1196.2  | 1043.0  | 887.1   | 776.9   | 664.0   | 553.8   | 443.5   | 400.5   | 360.2   |
|      |        | 82.5°  | 137.1   | 126.3   | 118.3   | 112.9   | 104.8   | 99.5    | 91.4    | 83.3    | 75.3    |
|      |        | 85°    | 8.1     | 5.4     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5°  | 360°   |
|--------|------|--------|---------|--------|
| 0.0    | 0.0  | 0°     | 155.9   | 155.9  |
| 0.0    | 0.0  | 2.5°   | 145.2   | 142.5  |
| 0.0    | 0.0  | 5°     | 153.2   | 150.5  |
| 0.0    | 0.0  | 7.5°   | 169.4   | 164.0  |
| 0.0    | 0.0  | 10°    | 185.5   | 180.1  |
| 0.0    | 0.0  | 12.5°  | 209.7   | 201.6  |
| 0.0    | 0.0  | 15°    | 236.6   | 220.4  |
| 0.0    | 0.0  | 17.5°  | 282.3   | 247.3  |
| 0.0    | 0.0  | 20°    | 381.7   | 293.0  |
| 0.0    | 0.0  | 22.5°  | 537.6   | 365.6  |
| 0.0    | 0.0  | 25°    | 790.3   | 505.4  |
| 0.0    | 0.0  | 27.5°  | 1099.4  | 672.0  |
| 0.0    | 0.0  | 30°    | 1462.3  | 841.4  |
| 0.0    | 0.0  | 32.5°  | 1782.2  | 1002.7 |
| 0.0    | 0.0  | 35°    | 2198.9  | 1166.6 |
| 0.0    | 0.0  | 37.5°  | 2712.3  | 1376.3 |
| 0.0    | 0.0  | 40°    | 3508.0  | 1693.5 |
| 0.0    | 0.0  | 42.5°  | 4940.8  | 2279.5 |
| 0.0    | 0.0  | 45°    | 8024.0  | 3940.8 |
| 0.0    | 0.0  | 47.5°  | 12346.5 | 6518.7 |
| 0.0    | 0.0  | 50°    | 15104.5 | 8319.7 |
| 0.0    | 0.0  | 52.5°  | 15330.3 | 8306.3 |
| 0.0    | 0.0  | 55°    | 13994.3 | 7384.3 |
| 0.0    | 0.0  | 57.5°  | 11940.6 | 6171.9 |
| 0.0    | 0.0  | 60°    | 9924.5  | 4881.6 |
| 0.0    | 0.0  | 62.5°  | 7819.7  | 3370.9 |
| 0.0    | 0.0  | 65°    | 5714.9  | 2384.4 |
| 0.0    | 0.0  | 67.5°  | 4104.8  | 1782.2 |
|        |      | 70°    | 2698.9  | 1365.6 |
|        |      | 72.5°  | 1758.0  | 1112.9 |
|        |      | 75°    | 1182.8  | 922.0  |
|        |      | 77.5°  | 690.8   | 612.9  |
|        |      | 80°    | 244.6   | 215.0  |
|        |      | 82.5°  | 45.7    | 32.3   |
|        |      | 85°    | 0.0     | 0.0    |
|        |      | 87.5°  | 0.0     | 0.0    |
|        |      | 90°    | 0.0     | 0.0    |
|        |      | 92.5°  | 0.0     | 0.0    |
|        |      | 95°    | 0.0     | 0.0    |
|        |      | 97.5°  | 0.0     | 0.0    |
|        |      | 100°   | 0.0     | 0.0    |
|        |      | 102.5° | 0.0     | 0.0    |
|        |      | 105°   | 0.0     | 0.0    |
|        |      | 107.5° | 0.0     | 0.0    |
|        |      | 110°   | 0.0     | 0.0    |



REPORT NUMBER: P1065095

CATALOG NUMBER: GLAN-SA9C-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-17

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-950-U-5WQ

Data in this report applies to families of products including GSS-SB1A-950-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-17  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-950-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI  
 5000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 4765  
 CIE  $u'$ : 0.2105  
 CIE  $v'$ : 0.4941  
 Duv: 0.0052  
 CIE x: 0.3536  
 CIE y: 0.3689  
 CIE z: 0.2775  
 Peak Wavelength (nm): 449  
 Dominant Wavelength (nm): 571  
 Purity: 16.80041  
 R<sub>f</sub>: 90.7  
 R<sub>g</sub>: 98

CRI (Ra): 90.8  
 R1: 89.8  
 R2: 93.1  
 R3: 95.3  
 R4: 90.3  
 R5: 89.0  
 R6: 89.7  
 R7: 94.9  
 R8: 84.0  
 R9: 54.9  
 R10: 83.0  
 R11: 89.6  
 R12: 68.0  
 R13: 90.6  
 R14: 97.3  
 R15: 86.2



### Test Conditions


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-17


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-17

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-17

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 462                         | NR               | 620       | 668                         | NR               | 750       | 45                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 498                         | NR               | 625       | 652                         | NR               | 755       | 39                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 533                         | NR               | 630       | 634                         | NR               | 760       | 33                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 562                         | NR               | 635       | 610                         | NR               | 765       | 28                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 590                         | NR               | 640       | 583                         | NR               | 770       | 24                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 617                         | NR               | 645       | 552                         | NR               | 775       | 21                          | NR               | 905       | 1                           | NR               |
| 390       | 0                           | NR               | 520       | 642                         | NR               | 650       | 519                         | NR               | 780       | 18                          | NR               | 910       | 0                           | NR               |
| 395       | 2                           | NR               | 525       | 661                         | NR               | 655       | 484                         | NR               | 785       | 15                          | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 681                         | NR               | 660       | 448                         | NR               | 790       | 13                          | NR               | 920       | 0                           | NR               |
| 405       | 7                           | NR               | 535       | 695                         | NR               | 665       | 411                         | NR               | 795       | 11                          | NR               | 925       | 0                           | NR               |
| 410       | 12                          | NR               | 540       | 702                         | NR               | 670       | 373                         | NR               | 800       | 10                          | NR               | 930       | 0                           | NR               |
| 415       | 21                          | NR               | 545       | 708                         | NR               | 675       | 338                         | NR               | 805       | 8                           | NR               | 935       | 0                           | NR               |
| 420       | 39                          | NR               | 550       | 707                         | NR               | 680       | 305                         | NR               | 810       | 7                           | NR               | 940       | 0                           | NR               |
| 425       | 74                          | NR               | 555       | 706                         | NR               | 685       | 272                         | NR               | 815       | 6                           | NR               | 945       | 0                           | NR               |
| 430       | 139                         | NR               | 560       | 700                         | NR               | 690       | 243                         | NR               | 820       | 5                           | NR               | 950       | 0                           | NR               |
| 435       | 270                         | NR               | 565       | 696                         | NR               | 695       | 214                         | NR               | 825       | 5                           | NR               | 955       | 0                           | NR               |
| 440       | 517                         | NR               | 570       | 692                         | NR               | 700       | 188                         | NR               | 830       | 4                           | NR               | 960       | 0                           | NR               |
| 445       | 877                         | NR               | 575       | 689                         | NR               | 705       | 165                         | NR               | 835       | 3                           | NR               | 965       | 0                           | NR               |
| 450       | 978                         | NR               | 580       | 688                         | NR               | 710       | 144                         | NR               | 840       | 3                           | NR               | 970       | 0                           | NR               |
| 455       | 738                         | NR               | 585       | 688                         | NR               | 715       | 125                         | NR               | 845       | 3                           | NR               | 975       | 0                           | NR               |
| 460       | 618                         | NR               | 590       | 689                         | NR               | 720       | 110                         | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 529                         | NR               | 595       | 690                         | NR               | 725       | 95                          | NR               | 855       | 2                           | NR               | 985       | 0                           | NR               |
| 470       | 420                         | NR               | 600       | 690                         | NR               | 730       | 82                          | NR               | 860       | 2                           | NR               | 990       | 0                           | NR               |
| 475       | 395                         | NR               | 605       | 688                         | NR               | 735       | 71                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 408                         | NR               | 610       | 685                         | NR               | 740       | 61                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 429                         | NR               | 615       | 678                         | NR               | 745       | 52                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-17

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.99

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 462                         | NR               | 620       | 668                         | NR               | 750       | 45                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 498                         | NR               | 625       | 652                         | NR               | 755       | 39                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 533                         | NR               | 630       | 634                         | NR               | 760       | 33                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 562                         | NR               | 635       | 610                         | NR               | 765       | 28                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 590                         | NR               | 640       | 583                         | NR               | 770       | 24                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 617                         | NR               | 645       | 552                         | NR               | 775       | 21                          | NR               | 905       | 1                           | NR               |
| 390       | 0                           | NR               | 520       | 642                         | NR               | 650       | 519                         | NR               | 780       | 18                          | NR               | 910       | 0                           | NR               |
| 395       | 2                           | NR               | 525       | 661                         | NR               | 655       | 484                         | NR               | 785       | 15                          | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 681                         | NR               | 660       | 448                         | NR               | 790       | 13                          | NR               | 920       | 0                           | NR               |
| 405       | 7                           | NR               | 535       | 695                         | NR               | 665       | 411                         | NR               | 795       | 11                          | NR               | 925       | 0                           | NR               |
| 410       | 12                          | NR               | 540       | 702                         | NR               | 670       | 373                         | NR               | 800       | 10                          | NR               | 930       | 0                           | NR               |
| 415       | 21                          | NR               | 545       | 708                         | NR               | 675       | 338                         | NR               | 805       | 8                           | NR               | 935       | 0                           | NR               |
| 420       | 39                          | NR               | 550       | 707                         | NR               | 680       | 305                         | NR               | 810       | 7                           | NR               | 940       | 0                           | NR               |
| 425       | 74                          | NR               | 555       | 706                         | NR               | 685       | 272                         | NR               | 815       | 6                           | NR               | 945       | 0                           | NR               |
| 430       | 139                         | NR               | 560       | 700                         | NR               | 690       | 243                         | NR               | 820       | 5                           | NR               | 950       | 0                           | NR               |
| 435       | 270                         | NR               | 565       | 696                         | NR               | 695       | 214                         | NR               | 825       | 5                           | NR               | 955       | 0                           | NR               |
| 440       | 517                         | NR               | 570       | 692                         | NR               | 700       | 188                         | NR               | 830       | 4                           | NR               | 960       | 0                           | NR               |
| 445       | 877                         | NR               | 575       | 689                         | NR               | 705       | 165                         | NR               | 835       | 3                           | NR               | 965       | 0                           | NR               |
| 450       | 978                         | NR               | 580       | 688                         | NR               | 710       | 144                         | NR               | 840       | 3                           | NR               | 970       | 0                           | NR               |
| 455       | 738                         | NR               | 585       | 688                         | NR               | 715       | 125                         | NR               | 845       | 3                           | NR               | 975       | 0                           | NR               |
| 460       | 618                         | NR               | 590       | 689                         | NR               | 720       | 110                         | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 529                         | NR               | 595       | 690                         | NR               | 725       | 95                          | NR               | 855       | 2                           | NR               | 985       | 0                           | NR               |
| 470       | 420                         | NR               | 600       | 690                         | NR               | 730       | 82                          | NR               | 860       | 2                           | NR               | 990       | 0                           | NR               |
| 475       | 395                         | NR               | 605       | 688                         | NR               | 735       | 71                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 408                         | NR               | 610       | 685                         | NR               | 740       | 61                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 429                         | NR               | 615       | 678                         | NR               | 745       | 52                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-17

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 4.22**


| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 462                                    | NR                             | 620               | 668                                    | NR                             | 750               | 45                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 498                                    | NR                             | 625               | 652                                    | NR                             | 755               | 39                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 533                                    | NR                             | 630               | 634                                    | NR                             | 760               | 33                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 562                                    | NR                             | 635               | 610                                    | NR                             | 765               | 28                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 590                                    | NR                             | 640               | 583                                    | NR                             | 770               | 24                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 617                                    | NR                             | 645               | 552                                    | NR                             | 775               | 21                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 642                                    | NR                             | 650               | 519                                    | NR                             | 780               | 18                                     | NR                             | 910               | 0                                      | NR                             |
| 395               | 2                                      | NR                             | 525               | 661                                    | NR                             | 655               | 484                                    | NR                             | 785               | 15                                     | NR                             | 915               | 0                                      | NR                             |
| 400               | 4                                      | NR                             | 530               | 681                                    | NR                             | 660               | 448                                    | NR                             | 790               | 13                                     | NR                             | 920               | 0                                      | NR                             |
| 405               | 7                                      | NR                             | 535               | 695                                    | NR                             | 665               | 411                                    | NR                             | 795               | 11                                     | NR                             | 925               | 0                                      | NR                             |
| 410               | 12                                     | NR                             | 540               | 702                                    | NR                             | 670               | 373                                    | NR                             | 800               | 10                                     | NR                             | 930               | 0                                      | NR                             |
| 415               | 21                                     | NR                             | 545               | 708                                    | NR                             | 675               | 338                                    | NR                             | 805               | 8                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 39                                     | NR                             | 550               | 707                                    | NR                             | 680               | 305                                    | NR                             | 810               | 7                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 74                                     | NR                             | 555               | 706                                    | NR                             | 685               | 272                                    | NR                             | 815               | 6                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 139                                    | NR                             | 560               | 700                                    | NR                             | 690               | 243                                    | NR                             | 820               | 5                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 270                                    | NR                             | 565               | 696                                    | NR                             | 695               | 214                                    | NR                             | 825               | 5                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 517                                    | NR                             | 570               | 692                                    | NR                             | 700               | 188                                    | NR                             | 830               | 4                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 877                                    | NR                             | 575               | 689                                    | NR                             | 705               | 165                                    | NR                             | 835               | 3                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 978                                    | NR                             | 580               | 688                                    | NR                             | 710               | 144                                    | NR                             | 840               | 3                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 738                                    | NR                             | 585               | 688                                    | NR                             | 715               | 125                                    | NR                             | 845               | 3                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 618                                    | NR                             | 590               | 689                                    | NR                             | 720               | 110                                    | NR                             | 850               | 2                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 529                                    | NR                             | 595               | 690                                    | NR                             | 725               | 95                                     | NR                             | 855               | 2                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 420                                    | NR                             | 600               | 690                                    | NR                             | 730               | 82                                     | NR                             | 860               | 2                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 395                                    | NR                             | 605               | 688                                    | NR                             | 735               | 71                                     | NR                             | 865               | 1                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 408                                    | NR                             | 610               | 685                                    | NR                             | 740               | 61                                     | NR                             | 870               | 1                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 429                                    | NR                             | 615               | 678                                    | NR                             | 745               | 52                                     | NR                             | 875               | 1                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2407-184-17





TM-30-18

### Summary

$R_f = 90.7$   
 $R_g = 98$   
 $CIE R_a = 90.8$   
 $R_9 = 54.9$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 85 | CES26 = 92  | CES51 = 96 | CES76 = 85 |
| CES02 = 60 | CES27 = 92  | CES52 = 97 | CES77 = 88 |
| CES03 = 31 | CES28 = 95  | CES53 = 94 | CES78 = 82 |
| CES04 = 69 | CES29 = 95  | CES54 = 93 | CES79 = 96 |
| CES05 = 48 | CES30 = 94  | CES55 = 92 | CES80 = 93 |
| CES06 = 50 | CES31 = 96  | CES56 = 92 | CES81 = 89 |
| CES07 = 41 | CES32 = 91  | CES57 = 91 | CES82 = 97 |
| CES08 = 40 | CES33 = 99  | CES58 = 91 | CES83 = 98 |
| CES09 = 29 | CES34 = 93  | CES59 = 95 | CES84 = 93 |
| CES10 = 73 | CES35 = 96  | CES60 = 92 | CES85 = 85 |
| CES11 = 56 | CES36 = 82  | CES61 = 92 | CES86 = 88 |
| CES12 = 62 | CES37 = 95  | CES62 = 87 | CES87 = 90 |
| CES13 = 42 | CES38 = 89  | CES63 = 91 | CES88 = 94 |
| CES14 = 74 | CES39 = 99  | CES64 = 88 | CES89 = 87 |
| CES15 = 71 | CES40 = 98  | CES65 = 86 | CES90 = 94 |
| CES16 = 46 | CES41 = 97  | CES66 = 85 | CES91 = 74 |
| CES17 = 48 | CES42 = 95  | CES67 = 84 | CES92 = 78 |
| CES18 = 56 | CES43 = 95  | CES68 = 86 | CES93 = 87 |
| CES19 = 70 | CES44 = 100 | CES69 = 88 | CES94 = 80 |
| CES20 = 65 | CES45 = 97  | CES70 = 84 | CES95 = 81 |
| CES21 = 85 | CES46 = 96  | CES71 = 79 | CES96 = 90 |
| CES22 = 77 | CES47 = 98  | CES72 = 93 | CES97 = 95 |
| CES23 = 91 | CES48 = 90  | CES73 = 78 | CES98 = 92 |
| CES24 = 90 | CES49 = 95  | CES74 = 93 | CES99 = 88 |
| CES25 = 70 | CES50 = 97  | CES75 = 80 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)