

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P1456457

Luminaire Tested: GLAN-SB5C-730-U-T3LG

Issue Date: 05/20/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1456457  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 5/21/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB5C-730-U-T3LG  
Description: GALLEON II AREA AND ROADWAY HIGH DENSITY LUMINAIRE 615mA 5xLight Square  
PACKAGE 70CRI 3000K FIXTURE w/ TYPE III LOW GLARE  
Light Source: (130) 3000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 36891.8 lumens  
Efficiency: N/A  
Efficacy: 147.9 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B3 - U0 - G4  
  
Input Watts (W): 249.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1456457

CATALOG NUMBER: GLAN-SB5C-730-U-T3LG

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 30 foot mounting height. Maximum calculated value = 9.4 fc  
 Type III - Short - N/A

REPORT NUMBER: P1456457

CATALOG NUMBER: GLAN-SB5C-730-U-T3LG

### Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral      - - - Horizontal Cone Through 53-Deg Vertical

REPORT NUMBER: P1456457

CATALOG NUMBER: GLAN-SB5C-730-U-T3LG

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	9300.1	0.0	9300.1
	% Fixture	25.2	0.0	25.2
<b>Street Side</b>	Lumens	27591.6	0.0	27591.6
	% Fixture	74.8	0.0	74.8
<b>Total</b>	Lumens	36891.8	0.0	36891.8
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	516.0	1.4
10°-20°	1598.0	4.3
20°-30°	3055.3	8.3
30°-40°	5245.6	14.2
40°-50°	7347.5	19.9
50°-60°	8338.4	22.6
60°-70°	7312.3	19.8
70°-80°	2859.2	7.8
80°-90°	619.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	36891.8	100.0
0°-180°	36891.8	100.0



REPORT NUMBER: P1456457


CATALOG NUMBER: GLAN-SB5C-730-U-T3LG

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2932.6	7.9			
FM (30°-60°)	16079.8	43.6			
FH (60°-80°)	8278.8	22.4			G4/12000
FVH (80°-90°)	300.5	0.8			G3/500
BL (0°-30°)	2236.7	6.1	B3/2500		
BM (30°-60°)	4851.7	13.2	B3/5000		
BH (60°-80°)	1892.7	5.1	B3/2500		G3/2500
BVH (80°-90°)	319.0	0.9			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G4**

Type III Short





REPORT NUMBER: P1456457

CATALOG NUMBER: GLAN-SB5C-730-U-T3LG

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8
2.5°	5424.0	5424.0	5391.2	5424.0	5407.6	5432.2	5448.7	5448.7	5481.6	5473.3	5473.3
5°	5333.6	5317.2	5309.0	5366.5	5399.4	5465.1	5539.1	5572.0	5629.5	5629.5	5637.7
7.5°	5095.3	5087.1	5128.2	5243.2	5350.1	5514.4	5670.6	5761.0	5851.4	5867.8	5867.8
10°	4947.4	4939.2	4988.5	5128.2	5300.8	5539.1	5785.6	5974.6	6122.6	6163.7	6163.7
12.5°	4947.4	4947.4	4988.5	5128.2	5309.0	5596.6	5933.6	6254.1	6484.2	6533.5	6517.0
15°	5087.1	5078.9	5128.2	5276.1	5448.7	5719.9	6130.8	6558.1	6870.4	6960.8	6969.1
17.5°	5235.0	5226.8	5300.8	5489.8	5695.2	5966.4	6385.6	6911.5	7355.3	7470.4	7495.0
20°	5465.1	5456.9	5547.3	5728.1	5982.9	6295.2	6730.7	7330.7	7947.0	8070.3	8103.2
22.5°	5728.1	5736.3	5834.9	6056.8	6311.6	6722.5	7256.7	7922.4	8662.0	8851.0	8883.9
25°	6278.7	6254.1	6336.2	6492.4	6763.6	7256.7	7914.1	8637.3	9516.7	9746.8	9787.9
27.5°	7010.1	6969.1	7059.5	7215.6	7412.8	7873.1	8629.1	9434.5	10494.7	10782.3	10790.5
30°	7667.6	7642.9	7766.2	8086.7	8292.2	8645.6	9451.0	10371.4	11702.7	12121.9	12138.3
32.5°	8234.7	8226.4	8456.5	8867.5	9335.9	9713.9	10494.7	11554.8	13231.3	13716.2	13609.4
35°	8777.1	8801.7	9089.4	9516.7	10141.3	10897.4	11686.3	12894.4	14842.1	15425.6	15253.0
37.5°	9327.7	9344.1	9722.2	10272.8	10930.2	11916.4	12976.6	14349.0	16239.2	16962.4	16584.4
40°	9837.2	9886.5	10396.0	10987.8	11842.5	12845.1	14028.5	15359.9	17315.8	18030.8	17619.9
42.5°	10346.7	10420.7	10971.3	11784.9	12697.2	13740.9	14759.9	15976.2	18006.1	18803.3	18170.5
45°	10872.7	10922.0	11604.1	12450.6	13486.1	14447.6	15179.1	16370.7	18482.8	19345.7	18482.8
47.5°	11226.1	11324.7	12072.6	13050.5	14086.0	14990.0	15516.0	16535.1	18786.9	19699.1	18597.8
50°	11365.8	11505.5	12310.9	13395.7	14579.1	15499.6	15779.0	16625.5	19123.8	20011.4	18573.2
52.5°	11341.1	11472.6	12352.0	13551.8	14973.6	15968.0	16033.7	16724.1	19362.1	20118.2	18359.5
53°	11209.7	11390.5	12376.6	13560.1	15031.1	16091.3	16148.8	16732.3	19395.0	20266.1	18326.6
55°	10757.7	10856.3	12121.9	13551.8	15302.3	16551.5	16469.3	16978.8	19485.4	20167.5	17965.0
57.5°	10346.7	10445.4	11546.6	13395.7	15524.2	17200.7	16987.1	16937.8	18992.3	19608.7	17052.8
60°	10083.8	10116.6	11045.3	12902.6	15433.8	17652.7	17324.0	16452.9	17776.0	18285.5	15450.3
62.5°	9861.9	9853.6	10675.5	12195.8	15088.7	17718.5	17389.8	15253.0	15992.7	16074.8	13313.5
65°	9360.6	9303.0	10100.2	11398.7	14373.7	17422.6	16584.4	13436.8	13625.8	13354.6	10691.9
67.5°	8366.1	8242.9	8949.6	10182.4	12919.0	16584.4	15047.6	11324.7	10741.2	10198.8	8053.9
70°	5991.1	5991.1	6558.1	7790.9	10371.4	14332.6	12919.0	8571.6	7396.4	6911.5	5382.9
72.5°	2933.9	3007.9	3599.6	4602.2	6952.6	10404.3	9894.7	5555.5	4487.1	4248.8	3451.7
75°	1249.2	1257.4	1536.8	2038.1	3525.6	6155.4	6196.5	3205.1	2876.4	2761.3	2284.7
77.5°	871.1	887.6	1010.8	1199.9	1676.5	2827.1	3221.5	1939.5	1931.3	1849.1	1627.2
80°	665.7	682.1	764.3	895.8	1125.9	1446.4	1668.3	1314.9	1380.7	1298.5	1175.2
82.5°	501.3	517.7	575.3	673.9	805.4	969.8	936.9	969.8	1019.1	969.8	846.5
85°	336.9	345.2	386.3	468.4	517.7	583.5	583.5	706.8	739.6	723.2	665.7
87.5°	172.6	172.6	205.5	246.5	263.0	271.2	238.3	312.3	353.4	386.3	312.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1456457

CATALOG NUMBER: GLAN-SB5C-730-U-T3LG

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8	5415.8
2.5°	5473.3	5481.6	5456.9	5448.7	5440.5	5399.4	5399.4	5358.3	5350.1	5358.3	5333.6
5°	5654.1	5637.7	5572.0	5522.6	5465.1	5350.1	5284.3	5193.9	5169.3	5144.6	5120.0
7.5°	5876.0	5851.4	5736.3	5604.8	5448.7	5226.8	5103.5	4955.6	4906.3	4865.2	4848.8
10°	6155.4	6106.1	5925.3	5645.9	5358.3	5087.1	4914.5	4733.7	4651.5	4635.1	4594.0
12.5°	6517.0	6426.6	6089.7	5654.1	5276.1	4922.7	4733.7	4594.0	4561.1	4552.9	4511.8
15°	6919.7	6788.3	6245.8	5662.4	5169.3	4783.0	4667.9	4594.0	4594.0	4585.8	4561.1
17.5°	7412.8	7199.2	6393.8	5629.5	5037.8	4741.9	4684.4	4618.6	4602.2	4610.4	4577.5
20°	8004.5	7651.2	6549.9	5588.4	4980.2	4750.1	4684.4	4594.0	4552.9	4544.7	4520.0
22.5°	8686.7	8168.9	6722.5	5522.6	4980.2	4741.9	4635.1	4511.8	4429.6	4396.7	4363.9
25°	9467.4	8768.8	6903.3	5498.0	4996.7	4709.0	4536.5	4339.2	4207.7	4158.4	4133.8
27.5°	10412.5	9401.6	7034.8	5522.6	4988.5	4635.1	4363.9	4109.1	3961.2	3879.0	3862.6
30°	11456.2	10083.8	7125.2	5563.7	4939.2	4495.4	4158.4	3870.8	3665.3	3566.7	3542.1
32.5°	12688.9	10848.1	7215.6	5563.7	4815.9	4298.1	3920.1	3607.8	3394.1	3279.1	3262.6
35°	14053.2	11784.9	7297.8	5555.5	4667.9	4084.5	3681.8	3361.3	3139.4	3024.3	3016.1
37.5°	15211.9	12491.7	7338.9	5473.3	4462.5	3837.9	3459.9	3139.4	2909.3	2786.0	2777.8
40°	15926.9	12787.6	7256.7	5309.0	4215.9	3583.1	3213.3	2917.5	2687.4	2539.4	2506.6
42.5°	16198.1	12647.8	6993.7	5037.8	3920.1	3328.4	3007.9	2695.6	2391.5	2268.2	2243.6
45°	16107.7	12105.4	6434.9	4651.5	3591.4	3098.3	2827.1	2473.7	2276.4	2169.6	2161.4
47.5°	15803.6	11267.2	5736.3	4166.6	3246.2	2892.8	2588.7	2416.2	2235.4	2120.3	2112.1
50°	15269.5	10371.4	4898.1	3616.0	2933.9	2679.1	2531.2	2391.5	2243.6	2153.2	2136.7
52.5°	14587.3	9360.6	4125.5	3081.8	2662.7	2490.1	2473.7	2375.1	2260.0	2161.4	2120.3
53°	14431.2	9097.6	3977.6	2991.4	2621.6	2465.5	2457.2	2375.1	2243.6	2153.2	2120.3
55°	13683.3	8284.0	3509.2	2670.9	2416.2	2383.3	2457.2	2366.8	2202.5	2128.5	2103.9
57.5°	12483.5	7215.6	3057.2	2375.1	2202.5	2284.7	2432.6	2334.0	2153.2	2021.7	1980.6
60°	11037.1	5991.1	2712.0	2177.8	2046.3	2161.4	2334.0	2218.9	1972.4	1906.6	1898.4
62.5°	9311.2	4848.8	2449.0	2013.5	1914.8	2029.9	2186.0	1988.8	1808.0	1758.7	1742.3
65°	7273.1	3854.3	2243.6	1890.2	1783.4	1873.8	1980.6	1857.3	1742.3	1701.2	1693.0
67.5°	5407.6	3024.3	2079.2	1783.4	1651.9	1709.4	1832.7	1799.8	1701.2	1676.5	1668.3
70°	3731.1	2457.2	1931.3	1684.7	1487.5	1553.2	1742.3	1766.9	1668.3	1651.9	1643.6
72.5°	2613.4	2079.2	1775.1	1577.9	1356.0	1421.8	1701.2	1701.2	1594.3	1619.0	1602.6
75°	1964.2	1750.5	1594.3	1446.4	1191.6	1290.3	1643.6	1627.2	1520.4	1627.2	1586.1
77.5°	1479.3	1413.5	1380.7	1282.0	1043.7	1142.3	1528.6	1495.7	1356.0	1364.2	1290.3
80°	1076.6	1093.0	1183.4	1093.0	871.1	945.1	1290.3	1273.8	1101.2	1134.1	1043.7
82.5°	772.5	813.6	1010.8	879.3	632.8	673.9	887.6	961.5	862.9	813.6	830.0
85°	583.5	608.1	813.6	649.2	394.5	443.8	608.1	690.3	673.9	624.6	632.8
87.5°	246.5	279.4	378.0	304.1	230.1	230.1	378.0	484.9	435.6	369.8	386.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-730-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

**Spectral Parameters**

CCT (K): 2985  
 CIE u': 0.2504  
 CIE v': 0.5243  
 Duv: 0.0019  
 CIE x: 0.4408  
 CIE y: 0.4101  
 CIE z: 0.1491  
 Peak Wavelength (nm): 595  
 Dominant Wavelength (nm): 582  
 Purity: 55.41818  
 Rf: 73.8  
 Rg: 94.4

CRI (Ra):	70.8		
R1:	66.3	R9:	-43.2
R2:	80.6	R10:	57.6
R3:	94.5	R11:	64.8
R4:	68.2	R12:	53.5
R5:	66.5	R13:	68.7
R6:	74.7	R14:	97.0
R7:	76.2	R15:	56.4
R8:	39.6		



**Test Conditions**

Stabilization Time: 36M  
 Operation Time: 1H 36M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-4

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2985K  
 CIE x = 0.4408  
 CIE y = 0.4101  
 Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.19**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.13


λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

**Summary**

$R_f = 73.8$   
 $R_g = 94.4$   
 CIE  $R_a = 70.8$   
 $R_g = -43.2$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)