

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P954584

Luminaire Tested: **GLAN-SB7D-750-U-SLL**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P954584
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB7D-750-U-SLL
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(7) 70 CRI, 5000K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 76290 lumens
Efficiency: N/A
Efficacy: 148.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B5 - U0 - G5


Input Watts (W): 512.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P954584
 CATALOG NUMBER: GLAN-SB7D-750-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 23.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P954584
CATALOG NUMBER: GLAN-SB7D-750-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P954584
 CATALOG NUMBER: GLAN-SB7D-750-U-SLL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 19389.1 | 0.0 | 19389.1 |
| | % Fixture | 25.4 | 0.0 | 25.4 |
| Street Side | Lumens | 56900.9 | 0.0 | 56900.9 |
| | % Fixture | 74.6 | 0.0 | 74.6 |
| Total | Lumens | 76290.0 | 0.0 | 76290.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 1040.6 | 1.4 |
| 10°-20° | 3266.8 | 4.3 |
| 20°-30° | 5046.1 | 6.6 |
| 30°-40° | 6394.7 | 8.4 |
| 40°-50° | 9644.8 | 12.6 |
| 50°-60° | 15582.6 | 20.4 |
| 60°-70° | 19426.2 | 25.5 |
| 70°-80° | 12738.8 | 16.7 |
| 80°-90° | 3149.3 | 4.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 76290.0 | 100.0 |
| 0°-180° | 76290.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P954584


CATALOG NUMBER: GLAN-SB7D-750-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 5131.4 | 6.7 | | | |
| FM (30°-60°) | 22252.1 | 29.2 | | | |
| FH (60°-80°) | 26923.1 | 35.3 | | | G5 |
| FVH (80°-90°) | 2594.4 | 3.4 | | | G5 |
| BL (0°-30°) | 4222.2 | 5.5 | B4/5000 | | |
| BM (30°-60°) | 9370.0 | 12.3 | B5 | | |
| BH (60°-80°) | 5241.9 | 6.9 | B5 | | G5 |
| BVH (80°-90°) | 555.0 | 0.7 | | | G4/750 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B5-U0-G5

Type IV Short



REPORT NUMBER: P954584
 CATALOG NUMBER: GLAN-SB7D-750-U-SLL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 |
| 2.5° | 11281.5 | 11324.2 | 11367.3 | 11428.1 | 11488.9 | 11525.1 | 11561.3 | 11579.4 | 11597.6 | 11589.5 |
| 5° | 12130.9 | 12280.3 | 12430.0 | 12578.2 | 12726.7 | 12807.2 | 12887.7 | 12936.4 | 12985.6 | 13022.6 |
| 7.5° | 12984.3 | 13227.5 | 13470.2 | 13688.8 | 13907.4 | 14039.0 | 14170.7 | 14241.9 | 14312.8 | 14347.0 |
| 10° | 13638.5 | 13925.9 | 14213.3 | 14469.8 | 14726.2 | 14881.6 | 15036.2 | 15105.4 | 15174.2 | 15200.4 |
| 12.5° | 14039.0 | 14350.6 | 14661.8 | 14893.7 | 15124.7 | 15237.4 | 15350.2 | 15388.0 | 15425.8 | 15429.9 |
| 15° | 14282.6 | 14551.5 | 14820.0 | 14965.3 | 15111.0 | 15115.1 | 15119.1 | 15078.8 | 15038.6 | 14991.1 |
| 17.5° | 14419.4 | 14601.0 | 14782.6 | 14785.4 | 14787.8 | 14624.8 | 14461.7 | 14312.4 | 14162.6 | 14057.2 |
| 20° | 14570.4 | 14633.6 | 14697.2 | 14506.0 | 14314.8 | 13954.9 | 13595.0 | 13333.0 | 13070.9 | 12909.9 |
| 22.5° | 14745.5 | 14662.6 | 14579.7 | 14183.6 | 13787.4 | 13258.1 | 12728.7 | 12401.0 | 12073.4 | 11895.4 |
| 25° | 14970.9 | 14709.3 | 14447.6 | 13846.2 | 13244.8 | 12601.9 | 11959.0 | 11614.5 | 11270.7 | 11102.4 |
| 27.5° | 15276.9 | 14809.1 | 14341.0 | 13544.3 | 12748.0 | 12035.5 | 11323.0 | 10984.1 | 10645.5 | 10486.5 |
| 30° | 15689.5 | 14991.9 | 14294.7 | 13314.0 | 12333.4 | 11591.1 | 10848.8 | 10534.4 | 10220.0 | 10071.9 |
| 32.5° | 16176.6 | 15221.3 | 14266.5 | 13157.0 | 12047.6 | 11350.0 | 10652.4 | 10405.6 | 10158.4 | 10051.7 |
| 35° | 16768.3 | 15599.3 | 14430.7 | 13274.6 | 12118.9 | 11634.2 | 11149.9 | 11092.3 | 11034.8 | 11025.9 |
| 37.5° | 17764.7 | 16389.5 | 15014.4 | 13963.8 | 12913.1 | 12881.7 | 12850.3 | 13113.6 | 13376.8 | 13513.7 |
| 40° | 19270.2 | 17774.7 | 16279.2 | 15497.9 | 14716.5 | 15268.0 | 15819.5 | 16459.6 | 17099.6 | 17418.5 |
| 42.5° | 21266.9 | 19783.1 | 18299.3 | 17849.2 | 17399.1 | 18602.0 | 19804.8 | 20969.0 | 22133.2 | 22816.7 |
| 45° | 23732.5 | 22399.7 | 21066.4 | 20867.9 | 20669.1 | 22596.1 | 24523.5 | 26436.5 | 28349.8 | 29511.2 |
| 47.5° | 26816.1 | 25519.4 | 24222.4 | 24182.2 | 24141.9 | 26921.9 | 29701.2 | 32501.7 | 35301.9 | 36946.3 |
| 50° | 30857.7 | 29255.9 | 27654.6 | 27661.4 | 27668.3 | 31251.0 | 34833.7 | 38530.4 | 42227.0 | 44462.0 |
| 52.5° | 35497.1 | 33557.6 | 31618.5 | 31422.5 | 31226.0 | 35505.6 | 39785.1 | 44358.9 | 48932.3 | 51611.3 |
| 55° | 40436.5 | 38520.3 | 36604.1 | 35839.7 | 35075.3 | 39838.3 | 44600.9 | 50053.4 | 55506.0 | 58692.2 |
| 57.5° | 44928.9 | 43885.5 | 42841.7 | 41308.4 | 39775.5 | 44584.8 | 49394.1 | 55570.0 | 61745.6 | 65696.7 |
| 60° | 47644.2 | 49264.8 | 50885.9 | 48981.8 | 47077.8 | 51629.0 | 56180.3 | 62792.6 | 69405.0 | 73675.3 |
| 62.5° | 46265.4 | 50693.9 | 55122.4 | 54907.8 | 54692.9 | 58862.1 | 63031.8 | 69322.9 | 75613.5 | 79560.6 |
| 65° | 43505.9 | 47662.3 | 51818.6 | 52641.1 | 53463.1 | 58761.5 | 64060.3 | 70160.6 | 76260.5 | 79621.0 |
| 67.5° | 39808.5 | 43761.5 | 47714.6 | 48100.3 | 48485.5 | 54006.1 | 59526.3 | 65652.8 | 71779.2 | 74411.9 |
| 70° | 35366.3 | 39666.0 | 43966.0 | 44138.3 | 44311.0 | 49247.9 | 54184.4 | 59456.7 | 64728.5 | 66191.8 |
| 72.5° | 30072.7 | 35006.8 | 39941.3 | 40065.3 | 40188.9 | 44051.4 | 47913.9 | 51862.5 | 55810.8 | 55958.9 |
| 75° | 23376.3 | 28483.0 | 33589.8 | 34048.3 | 34506.8 | 37511.9 | 40517.0 | 43296.6 | 46076.2 | 45331.5 |
| 77.5° | 16701.9 | 21469.0 | 26236.4 | 26892.6 | 27548.7 | 29833.2 | 32117.7 | 34089.0 | 36060.7 | 34780.6 |
| 80° | 10931.3 | 14942.0 | 18952.2 | 19767.8 | 20583.3 | 22308.7 | 24033.2 | 25068.6 | 26103.6 | 24044.5 |
| 82.5° | 6354.3 | 9096.1 | 11838.3 | 12749.3 | 13660.6 | 14848.2 | 16035.7 | 16467.6 | 16899.2 | 15280.9 |
| 85° | 2795.7 | 4251.0 | 5706.2 | 6481.1 | 7256.0 | 8231.8 | 9207.2 | 9452.3 | 9697.5 | 8401.3 |
| 87.5° | 865.5 | 1354.6 | 1843.7 | 2276.0 | 2708.4 | 3196.3 | 3684.2 | 3705.1 | 3725.6 | 3127.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P954584
 CATALOG NUMBER: GLAN-SB7D-750-U-SLL

CANDELA DISTRIBUTION (continued):

| 50° | | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 10490.5 | 0° | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 |
| 11597.6 | 2.5° | 11579.4 | 11561.3 | 11525.1 | 11488.9 | 11428.1 | 11367.3 | 11324.2 | 11281.5 | 11195.0 | 11108.5 |
| 12985.6 | 5° | 12936.4 | 12887.7 | 12807.2 | 12726.7 | 12578.2 | 12430.0 | 12280.3 | 12130.9 | 11939.7 | 11748.5 |
| 14312.8 | 7.5° | 14241.9 | 14170.7 | 14039.0 | 13907.4 | 13688.8 | 13470.2 | 13227.5 | 12984.3 | 12668.7 | 12353.5 |
| 15174.2 | 10° | 15105.4 | 15036.2 | 14881.6 | 14726.2 | 14469.8 | 14213.3 | 13925.9 | 13638.5 | 13239.6 | 12840.6 |
| 15425.8 | 12.5° | 15388.0 | 15350.2 | 15237.4 | 15124.7 | 14893.7 | 14661.8 | 14350.6 | 14039.0 | 13600.7 | 13162.7 |
| 15038.6 | 15° | 15078.8 | 15119.1 | 15115.1 | 15111.0 | 14965.3 | 14820.0 | 14551.5 | 14282.6 | 13825.7 | 13368.8 |
| 14162.6 | 17.5° | 14312.4 | 14461.7 | 14624.8 | 14787.8 | 14785.4 | 14782.6 | 14601.0 | 14419.4 | 13956.1 | 13492.8 |
| 13070.9 | 20° | 13333.0 | 13595.0 | 13954.9 | 14314.8 | 14506.0 | 14697.2 | 14633.6 | 14570.4 | 14089.0 | 13607.1 |
| 12073.4 | 22.5° | 12401.0 | 12728.7 | 13258.1 | 13787.4 | 14183.6 | 14579.7 | 14662.6 | 14745.5 | 14253.6 | 13761.3 |
| 11270.7 | 25° | 11614.5 | 11959.0 | 12601.9 | 13244.8 | 13846.2 | 14447.6 | 14709.3 | 14970.9 | 14488.7 | 14006.8 |
| 10645.5 | 27.5° | 10984.1 | 11323.0 | 12035.5 | 12748.0 | 13544.3 | 14341.0 | 14809.1 | 15276.9 | 14817.2 | 14357.1 |
| 10220.0 | 30° | 10534.4 | 10848.8 | 11591.1 | 12333.4 | 13314.0 | 14294.7 | 14991.9 | 15689.5 | 15245.1 | 14801.1 |
| 10158.4 | 32.5° | 10405.6 | 10652.4 | 11350.0 | 12047.6 | 13157.0 | 14266.5 | 15221.3 | 16176.6 | 15736.6 | 15297.0 |
| 11034.8 | 35° | 11092.3 | 11149.9 | 11634.2 | 12118.9 | 13274.6 | 14430.7 | 15599.3 | 16768.3 | 16347.3 | 15925.8 |
| 13376.8 | 37.5° | 13113.6 | 12850.3 | 12881.7 | 12913.1 | 13963.8 | 15014.4 | 16389.5 | 17764.7 | 17227.7 | 16690.7 |
| 17099.6 | 40° | 16459.6 | 15819.5 | 15268.0 | 14716.5 | 15497.9 | 16279.2 | 17774.7 | 19270.2 | 18487.7 | 17705.1 |
| 22133.2 | 42.5° | 20969.0 | 19804.8 | 18602.0 | 17399.1 | 17849.2 | 18299.3 | 19783.1 | 21266.9 | 20137.3 | 19007.7 |
| 28349.8 | 45° | 26436.5 | 24523.5 | 22596.1 | 20669.1 | 20867.9 | 21066.4 | 22399.7 | 23732.5 | 22208.9 | 20685.2 |
| 35301.9 | 47.5° | 32501.7 | 29701.2 | 26921.9 | 24141.9 | 24182.2 | 24222.4 | 25519.4 | 26816.1 | 24671.7 | 22526.9 |
| 42227.0 | 50° | 38530.4 | 34833.7 | 31251.0 | 27668.3 | 27661.4 | 27654.6 | 29255.9 | 30857.7 | 27624.8 | 24391.5 |
| 48932.3 | 52.5° | 44358.9 | 39785.1 | 35505.6 | 31226.0 | 31422.5 | 31618.5 | 33557.6 | 35497.1 | 30726.9 | 25956.6 |
| 55506.0 | 55° | 50053.4 | 44600.9 | 39838.3 | 35075.3 | 35839.7 | 36604.1 | 38520.3 | 40436.5 | 33477.1 | 26518.2 |
| 61745.6 | 57.5° | 55570.0 | 49394.1 | 44584.8 | 39775.5 | 41308.4 | 42841.7 | 43885.5 | 44928.9 | 35426.3 | 25923.6 |
| 69405.0 | 60° | 62792.6 | 56180.3 | 51629.0 | 47077.8 | 48981.8 | 50885.9 | 49264.8 | 47644.2 | 35913.4 | 24182.2 |
| 75613.5 | 62.5° | 69322.9 | 63031.8 | 58862.1 | 54692.9 | 54907.8 | 55122.4 | 50693.9 | 46265.4 | 33862.4 | 21459.3 |
| 76260.5 | 65° | 70160.6 | 64060.3 | 58761.5 | 53463.1 | 52641.1 | 51818.6 | 47662.3 | 43505.9 | 30960.4 | 18414.8 |
| 71779.2 | 67.5° | 65652.8 | 59526.3 | 54006.1 | 48485.5 | 48100.3 | 47714.6 | 43761.5 | 39808.5 | 27506.9 | 15205.2 |
| 64728.5 | 70° | 59456.7 | 54184.4 | 49247.9 | 44311.0 | 44138.3 | 43966.0 | 39666.0 | 35366.3 | 23738.6 | 12110.8 |
| 55810.8 | 72.5° | 51862.5 | 47913.9 | 44051.4 | 40188.9 | 40065.3 | 39941.3 | 35006.8 | 30072.7 | 19653.4 | 9234.6 |
| 46076.2 | 75° | 43296.6 | 40517.0 | 37511.9 | 34506.8 | 34048.3 | 33589.8 | 28483.0 | 23376.3 | 14970.5 | 6564.8 |
| 36060.7 | 77.5° | 34089.0 | 32117.7 | 29833.2 | 27548.7 | 26892.6 | 26236.4 | 21469.0 | 16701.9 | 10478.1 | 4254.2 |
| 26103.6 | 80° | 25068.6 | 24033.2 | 22308.7 | 20583.3 | 19767.8 | 18952.2 | 14942.0 | 10931.3 | 6750.8 | 2570.3 |
| 16899.2 | 82.5° | 16467.6 | 16035.7 | 14848.2 | 13660.6 | 12749.3 | 11838.3 | 9096.1 | 6354.3 | 3907.2 | 1460.5 |
| 9697.5 | 85° | 9452.3 | 9207.2 | 8231.8 | 7256.0 | 6481.1 | 5706.2 | 4251.0 | 2795.7 | 1757.5 | 719.8 |
| 3725.6 | 87.5° | 3705.1 | 3684.2 | 3196.3 | 2708.4 | 2276.0 | 1843.7 | 1354.6 | 865.5 | 575.7 | 285.8 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P954584
 CATALOG NUMBER: GLAN-SB7D-750-U-SLL

CANDELA DISTRIBUTION (continued):

| 105° | | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 10490.5 | 0° | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 |
| 11016.3 | 2.5° | 10924.5 | 10831.9 | 10739.3 | 10650.7 | 10562.2 | 10476.4 | 10381.0 | 10303.7 | 10226.9 | 10157.2 |
| 11557.7 | 5° | 11367.3 | 11175.3 | 10983.7 | 10804.5 | 10625.4 | 10456.3 | 10289.3 | 10143.5 | 9997.4 | 9875.0 |
| 12062.1 | 7.5° | 11770.7 | 11486.9 | 11203.1 | 10953.1 | 10703.1 | 10472.4 | 10256.2 | 10062.2 | 9868.6 | 9707.6 |
| 12455.4 | 10° | 12070.6 | 11726.0 | 11381.0 | 11085.5 | 10789.2 | 10504.6 | 10272.3 | 10067.9 | 9863.4 | 9702.3 |
| 12726.3 | 12.5° | 12289.9 | 11883.4 | 11476.8 | 11142.3 | 10807.7 | 10508.6 | 10292.5 | 10125.0 | 9958.4 | 9851.3 |
| 12895.4 | 15° | 12422.0 | 11953.8 | 11485.6 | 11098.4 | 10711.1 | 10379.8 | 10206.7 | 10126.6 | 10046.9 | 10061.4 |
| 12976.3 | 17.5° | 12459.8 | 11916.4 | 11372.9 | 10907.2 | 10441.4 | 10051.7 | 9945.1 | 9974.5 | 10003.4 | 10179.0 |
| 13039.5 | 20° | 12471.9 | 11813.3 | 11154.7 | 10577.5 | 10000.2 | 9546.5 | 9518.4 | 9655.2 | 9792.1 | 10096.8 |
| 13124.8 | 22.5° | 12488.0 | 11686.9 | 10885.8 | 10190.6 | 9495.4 | 8978.9 | 9034.1 | 9236.6 | 9439.1 | 9786.9 |
| 13279.4 | 25° | 12551.6 | 11562.1 | 10573.1 | 9758.7 | 8944.7 | 8415.4 | 8564.3 | 8797.8 | 9031.3 | 9344.1 |
| 13521.0 | 27.5° | 12684.4 | 11478.8 | 10273.2 | 9363.8 | 8454.4 | 7972.6 | 8153.7 | 8379.1 | 8604.6 | 8861.8 |
| 13833.7 | 30° | 12866.4 | 11439.8 | 10012.3 | 9033.7 | 8055.1 | 7650.5 | 7792.6 | 7971.4 | 8150.9 | 8364.2 |
| 14160.2 | 32.5° | 13023.4 | 11391.4 | 9758.7 | 8749.1 | 7739.1 | 7413.0 | 7476.2 | 7582.1 | 7688.0 | 7858.2 |
| 14532.2 | 35° | 13138.5 | 11300.5 | 9463.2 | 8469.3 | 7475.4 | 7203.7 | 7177.5 | 7206.5 | 7235.9 | 7365.9 |
| 14948.8 | 37.5° | 13207.0 | 11144.7 | 9082.4 | 8140.0 | 7197.6 | 6960.1 | 6864.3 | 6832.1 | 6799.9 | 6893.3 |
| 15477.8 | 40° | 13250.0 | 10930.1 | 8610.6 | 7747.1 | 6883.7 | 6668.3 | 6521.4 | 6448.5 | 6375.6 | 6442.9 |
| 16169.8 | 42.5° | 13331.8 | 10708.7 | 8086.5 | 7313.6 | 6540.7 | 6342.2 | 6157.0 | 6060.4 | 5963.8 | 6018.6 |
| 17080.3 | 45° | 13475.5 | 10503.0 | 7531.0 | 6853.1 | 6175.2 | 5973.9 | 5794.8 | 5700.6 | 5606.8 | 5652.6 |
| 18050.5 | 47.5° | 13574.1 | 10333.1 | 7092.2 | 6488.8 | 5885.3 | 5625.7 | 5471.5 | 5392.6 | 5313.7 | 5357.2 |
| 18950.6 | 50° | 13509.7 | 10148.0 | 6786.2 | 6246.8 | 5707.4 | 5366.0 | 5186.9 | 5116.9 | 5047.2 | 5114.8 |
| 19535.1 | 52.5° | 13113.2 | 9835.2 | 6557.6 | 6087.4 | 5617.6 | 5225.1 | 4974.8 | 4905.5 | 4836.7 | 4938.5 |
| 19406.3 | 55° | 12294.0 | 9316.7 | 6339.4 | 5971.9 | 5604.3 | 5239.2 | 4862.0 | 4752.5 | 4643.4 | 4788.0 |
| 18499.7 | 57.5° | 11076.2 | 8585.7 | 6094.7 | 5835.0 | 5575.4 | 5253.3 | 4794.4 | 4635.0 | 4475.6 | 4631.0 |
| 16812.6 | 60° | 9443.1 | 7636.4 | 5829.8 | 5625.7 | 5421.6 | 5209.0 | 4730.8 | 4524.3 | 4317.4 | 4453.8 |
| 14531.4 | 62.5° | 7603.4 | 6500.4 | 5397.4 | 5261.8 | 5126.5 | 5100.3 | 4656.7 | 4398.3 | 4140.3 | 4226.8 |
| 12203.8 | 65° | 5993.2 | 5478.3 | 4963.5 | 4899.5 | 4835.5 | 4838.7 | 4500.5 | 4226.0 | 3951.1 | 3984.5 |
| 9923.7 | 67.5° | 4642.2 | 4496.1 | 4349.6 | 4385.4 | 4420.8 | 4412.0 | 4222.0 | 3993.3 | 3764.7 | 3754.2 |
| 7813.6 | 70° | 3516.3 | 3558.2 | 3599.6 | 3765.5 | 3930.9 | 3930.9 | 3868.5 | 3705.9 | 3543.3 | 3507.0 |
| 5973.5 | 72.5° | 2712.4 | 2838.4 | 2964.8 | 3199.9 | 3434.6 | 3474.0 | 3474.8 | 3363.3 | 3251.8 | 3198.7 |
| 4335.5 | 75° | 2106.2 | 2220.5 | 2334.8 | 2598.1 | 2861.3 | 3043.3 | 3028.0 | 2942.3 | 2856.1 | 2805.4 |
| 2937.8 | 77.5° | 1621.5 | 1699.2 | 1777.3 | 2032.9 | 2288.5 | 2588.4 | 2580.4 | 2511.5 | 2442.7 | 2391.2 |
| 1892.8 | 80° | 1215.7 | 1247.9 | 1280.1 | 1496.7 | 1712.9 | 2071.1 | 2069.9 | 2012.4 | 1954.4 | 1911.3 |
| 1164.2 | 82.5° | 868.7 | 874.3 | 880.8 | 1040.2 | 1199.6 | 1505.5 | 1522.5 | 1494.3 | 1466.1 | 1435.5 |
| 622.3 | 85° | 525.3 | 522.5 | 519.3 | 636.0 | 752.8 | 980.2 | 1002.4 | 972.2 | 942.0 | 907.8 |
| 258.0 | 87.5° | 230.3 | 227.4 | 224.6 | 272.1 | 320.0 | 414.6 | 442.8 | 430.7 | 418.7 | 412.2 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P954584
 CATALOG NUMBER: GLAN-SB7D-750-U-SLL

CANDELA DISTRIBUTION (continued):

| 160° | | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 10490.5 | 0° | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 |
| 10088.0 | 2.5° | 10027.2 | 9966.4 | 9905.2 | 9844.4 | 9797.3 | 9749.8 | 9711.6 | 9673.3 | 9643.6 | 9613.8 |
| 9753.1 | 5° | 9645.2 | 9537.3 | 9439.5 | 9341.2 | 9266.0 | 9190.3 | 9137.6 | 9084.8 | 9047.4 | 9009.9 |
| 9546.5 | 7.5° | 9410.9 | 9274.8 | 9154.9 | 9035.3 | 8945.5 | 8856.2 | 8793.4 | 8730.6 | 8687.5 | 8644.8 |
| 9541.3 | 10° | 9395.2 | 9248.7 | 9113.8 | 8978.9 | 8871.9 | 8764.4 | 8694.3 | 8623.5 | 8582.8 | 8542.2 |
| 9745.0 | 12.5° | 9629.9 | 9515.5 | 9375.9 | 9236.6 | 9099.7 | 8962.8 | 8872.3 | 8781.7 | 8736.2 | 8691.1 |
| 10075.9 | 15° | 10046.1 | 10016.3 | 9895.2 | 9774.0 | 9579.2 | 9384.3 | 9246.6 | 9109.0 | 9045.8 | 8983.0 |
| 10354.5 | 17.5° | 10447.9 | 10540.9 | 10443.0 | 10345.6 | 10087.6 | 9829.5 | 9626.7 | 9423.8 | 9330.4 | 9236.6 |
| 10402.0 | 20° | 10597.2 | 10792.4 | 10747.4 | 10701.9 | 10406.8 | 10112.1 | 9863.4 | 9615.0 | 9495.4 | 9375.5 |
| 10135.5 | 22.5° | 10389.5 | 10643.5 | 10670.9 | 10697.8 | 10416.1 | 10134.3 | 9878.2 | 9621.8 | 9495.8 | 9369.4 |
| 9657.2 | 25° | 9907.2 | 10157.2 | 10250.6 | 10343.6 | 10112.5 | 9881.9 | 9654.0 | 9427.0 | 9317.5 | 9208.4 |
| 9118.6 | 27.5° | 9319.1 | 9519.6 | 9623.4 | 9727.7 | 9563.0 | 9398.8 | 9222.1 | 9045.4 | 8972.1 | 8898.4 |
| 8577.6 | 30° | 8743.9 | 8910.5 | 8995.0 | 9079.6 | 8954.4 | 8828.8 | 8702.4 | 8575.2 | 8537.7 | 8499.9 |
| 8028.9 | 32.5° | 8188.3 | 8348.1 | 8441.9 | 8536.1 | 8421.0 | 8305.5 | 8204.4 | 8103.4 | 8078.8 | 8054.3 |
| 7495.5 | 35° | 7653.3 | 7811.5 | 7924.3 | 8037.0 | 7954.9 | 7873.1 | 7779.7 | 7686.8 | 7649.3 | 7612.3 |
| 6986.3 | 37.5° | 7143.7 | 7301.5 | 7440.8 | 7580.1 | 7542.2 | 7504.4 | 7418.6 | 7332.5 | 7264.5 | 7196.8 |
| 6510.1 | 40° | 6662.3 | 6814.4 | 6974.6 | 7135.3 | 7144.5 | 7153.4 | 7080.5 | 7007.6 | 6908.6 | 6810.4 |
| 6073.7 | 42.5° | 6217.8 | 6362.4 | 6535.4 | 6708.5 | 6754.8 | 6801.1 | 6739.5 | 6678.4 | 6555.6 | 6432.8 |
| 5699.3 | 45° | 5836.2 | 5973.1 | 6152.6 | 6332.2 | 6398.6 | 6465.0 | 6409.4 | 6354.3 | 6213.8 | 6073.7 |
| 5400.2 | 47.5° | 5534.3 | 5667.9 | 5845.1 | 6022.2 | 6098.7 | 6175.2 | 6136.5 | 6097.9 | 5973.1 | 5848.3 |
| 5182.9 | 50° | 5309.3 | 5435.3 | 5593.9 | 5752.5 | 5850.7 | 5948.9 | 5946.5 | 5944.9 | 5845.1 | 5745.2 |
| 5040.0 | 52.5° | 5155.9 | 5271.4 | 5419.2 | 5567.3 | 5683.6 | 5800.0 | 5820.9 | 5841.8 | 5760.5 | 5679.2 |
| 4932.1 | 55° | 5056.9 | 5181.7 | 5311.3 | 5440.5 | 5563.7 | 5687.3 | 5716.3 | 5745.2 | 5674.4 | 5603.5 |
| 4786.4 | 57.5° | 4932.9 | 5079.4 | 5207.4 | 5335.8 | 5460.2 | 5584.2 | 5613.6 | 5643.0 | 5571.3 | 5499.7 |
| 4589.9 | 60° | 4758.2 | 4926.4 | 5056.5 | 5186.9 | 5311.7 | 5436.5 | 5468.7 | 5500.9 | 5430.8 | 5361.2 |
| 4313.4 | 62.5° | 4509.4 | 4705.8 | 4844.7 | 4983.6 | 5097.9 | 5212.3 | 5243.3 | 5274.2 | 5211.0 | 5147.8 |
| 4017.5 | 65° | 4227.6 | 4438.1 | 4571.0 | 4703.8 | 4804.5 | 4905.1 | 4936.9 | 4968.3 | 4907.5 | 4846.7 |
| 3743.7 | 67.5° | 3937.8 | 4132.2 | 4258.2 | 4383.8 | 4470.8 | 4557.7 | 4588.7 | 4619.3 | 4563.3 | 4507.8 |
| 3470.8 | 70° | 3641.5 | 3812.2 | 3920.9 | 4029.6 | 4108.1 | 4186.6 | 4216.3 | 4246.1 | 4200.6 | 4155.2 |
| 3146.0 | 72.5° | 3280.4 | 3414.5 | 3512.7 | 3610.9 | 3687.8 | 3764.7 | 3800.1 | 3835.5 | 3797.7 | 3759.8 |
| 2754.3 | 75° | 2854.1 | 2953.9 | 3042.9 | 3131.9 | 3201.9 | 3272.0 | 3309.0 | 3346.0 | 3327.5 | 3309.0 |
| 2339.6 | 77.5° | 2421.0 | 2501.9 | 2578.4 | 2654.8 | 2728.5 | 2801.8 | 2836.4 | 2871.0 | 2845.2 | 2818.7 |
| 1867.8 | 80° | 1935.5 | 2002.7 | 2067.1 | 2131.5 | 2187.5 | 2243.0 | 2288.9 | 2334.8 | 2323.5 | 2312.7 |
| 1404.9 | 82.5° | 1399.3 | 1393.6 | 1371.1 | 1348.6 | 1467.7 | 1586.9 | 1665.0 | 1743.1 | 1738.2 | 1733.0 |
| 873.5 | 85° | 844.6 | 815.2 | 752.8 | 690.4 | 801.9 | 913.8 | 1010.4 | 1107.0 | 1099.0 | 1090.9 |
| 405.8 | 87.5° | 404.6 | 403.4 | 355.9 | 308.0 | 354.6 | 401.7 | 440.8 | 479.8 | 470.2 | 459.7 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P954584
 CATALOG NUMBER: GLAN-SB7D-750-U-SLL

CANDELA DISTRIBUTION (continued):

| 215° | | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 10490.5 | 0° | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 |
| 9586.4 | 2.5° | 9558.6 | 9524.4 | 9558.6 | 9586.4 | 9613.8 | 9643.6 | 9673.3 | 9711.6 | 9749.8 | 9797.3 |
| 8981.4 | 5° | 8952.8 | 8924.6 | 8952.8 | 8981.4 | 9009.9 | 9047.4 | 9084.8 | 9137.6 | 9190.3 | 9266.0 |
| 8619.1 | 7.5° | 8593.7 | 8574.4 | 8593.7 | 8619.1 | 8644.8 | 8687.5 | 8730.6 | 8793.4 | 8856.2 | 8945.5 |
| 8520.4 | 10° | 8498.7 | 8489.8 | 8498.7 | 8520.4 | 8542.2 | 8582.8 | 8623.5 | 8694.3 | 8764.4 | 8871.9 |
| 8672.6 | 12.5° | 8654.1 | 8650.9 | 8654.1 | 8672.6 | 8691.1 | 8736.2 | 8781.7 | 8872.3 | 8962.8 | 9099.7 |
| 8958.8 | 15° | 8934.7 | 8932.7 | 8934.7 | 8958.8 | 8983.0 | 9045.8 | 9109.0 | 9246.6 | 9384.3 | 9579.2 |
| 9206.0 | 17.5° | 9175.0 | 9170.2 | 9175.0 | 9206.0 | 9236.6 | 9330.4 | 9423.8 | 9626.7 | 9829.5 | 10087.6 |
| 9337.2 | 20° | 9299.0 | 9286.9 | 9299.0 | 9337.2 | 9375.5 | 9495.4 | 9615.0 | 9863.4 | 10112.1 | 10406.8 |
| 9327.2 | 22.5° | 9284.9 | 9266.8 | 9284.9 | 9327.2 | 9369.4 | 9495.8 | 9621.8 | 9878.2 | 10134.3 | 10416.1 |
| 9168.5 | 25° | 9129.1 | 9105.7 | 9129.1 | 9168.5 | 9208.4 | 9317.5 | 9427.0 | 9654.0 | 9881.9 | 10112.5 |
| 8880.3 | 27.5° | 8862.2 | 8856.2 | 8862.2 | 8880.3 | 8898.4 | 8972.1 | 9045.4 | 9222.1 | 9398.8 | 9563.0 |
| 8499.9 | 30° | 8499.9 | 8505.9 | 8499.9 | 8499.9 | 8499.9 | 8537.7 | 8575.2 | 8702.4 | 8828.8 | 8954.4 |
| 8057.5 | 32.5° | 8061.1 | 8067.2 | 8061.1 | 8057.5 | 8054.3 | 8078.8 | 8103.4 | 8204.4 | 8305.5 | 8421.0 |
| 7604.2 | 35° | 7596.2 | 7592.2 | 7596.2 | 7604.2 | 7612.3 | 7649.3 | 7686.8 | 7779.7 | 7873.1 | 7954.9 |
| 7161.0 | 37.5° | 7125.2 | 7105.1 | 7125.2 | 7161.0 | 7196.8 | 7264.5 | 7332.5 | 7418.6 | 7504.4 | 7542.2 |
| 6743.6 | 40° | 6677.5 | 6638.1 | 6677.5 | 6743.6 | 6810.4 | 6908.6 | 7007.6 | 7080.5 | 7153.4 | 7144.5 |
| 6335.8 | 42.5° | 6238.8 | 6175.2 | 6238.8 | 6335.8 | 6432.8 | 6555.6 | 6678.4 | 6739.5 | 6801.1 | 6754.8 |
| 5959.8 | 45° | 5845.9 | 5772.6 | 5845.9 | 5959.8 | 6073.7 | 6213.8 | 6354.3 | 6409.4 | 6465.0 | 6398.6 |
| 5742.8 | 47.5° | 5637.8 | 5567.3 | 5637.8 | 5742.8 | 5848.3 | 5973.1 | 6097.9 | 6136.5 | 6175.2 | 6098.7 |
| 5647.8 | 50° | 5550.4 | 5482.8 | 5550.4 | 5647.8 | 5745.2 | 5845.1 | 5944.9 | 5946.5 | 5948.9 | 5850.7 |
| 5591.9 | 52.5° | 5504.9 | 5442.5 | 5504.9 | 5591.9 | 5679.2 | 5760.5 | 5841.8 | 5820.9 | 5800.0 | 5683.6 |
| 5527.1 | 55° | 5450.6 | 5394.2 | 5450.6 | 5527.1 | 5603.5 | 5674.4 | 5745.2 | 5716.3 | 5687.3 | 5563.7 |
| 5424.0 | 57.5° | 5347.9 | 5289.5 | 5347.9 | 5424.0 | 5499.7 | 5571.3 | 5643.0 | 5613.6 | 5584.2 | 5460.2 |
| 5283.1 | 60° | 5205.0 | 5144.6 | 5205.0 | 5283.1 | 5361.2 | 5430.8 | 5500.9 | 5468.7 | 5436.5 | 5311.7 |
| 5065.7 | 62.5° | 4983.6 | 4911.1 | 4983.6 | 5065.7 | 5147.8 | 5211.0 | 5274.2 | 5243.3 | 5212.3 | 5097.9 |
| 4767.0 | 65° | 4687.7 | 4625.3 | 4687.7 | 4767.0 | 4846.7 | 4907.5 | 4968.3 | 4936.9 | 4905.1 | 4804.5 |
| 4433.7 | 67.5° | 4359.6 | 4303.3 | 4359.6 | 4433.7 | 4507.8 | 4563.3 | 4619.3 | 4588.7 | 4557.7 | 4470.8 |
| 4084.3 | 70° | 4013.5 | 3949.0 | 4013.5 | 4084.3 | 4155.2 | 4200.6 | 4246.1 | 4216.3 | 4186.6 | 4108.1 |
| 3692.2 | 72.5° | 3625.0 | 3562.6 | 3625.0 | 3692.2 | 3759.8 | 3797.7 | 3835.5 | 3800.1 | 3764.7 | 3687.8 |
| 3252.2 | 75° | 3195.5 | 3135.9 | 3195.5 | 3252.2 | 3309.0 | 3327.5 | 3346.0 | 3309.0 | 3272.0 | 3201.9 |
| 2761.5 | 77.5° | 2704.4 | 2656.9 | 2704.4 | 2761.5 | 2818.7 | 2845.2 | 2871.0 | 2836.4 | 2801.8 | 2728.5 |
| 2235.8 | 80° | 2158.5 | 2069.1 | 2158.5 | 2235.8 | 2312.7 | 2323.5 | 2334.8 | 2288.9 | 2243.0 | 2187.5 |
| 1668.2 | 82.5° | 1603.0 | 1545.8 | 1603.0 | 1668.2 | 1733.0 | 1738.2 | 1743.1 | 1665.0 | 1586.9 | 1467.7 |
| 1040.2 | 85° | 989.5 | 937.9 | 989.5 | 1040.2 | 1090.9 | 1099.0 | 1107.0 | 1010.4 | 913.8 | 801.9 |
| 434.0 | 87.5° | 407.4 | 382.4 | 407.4 | 434.0 | 459.7 | 470.2 | 479.8 | 440.8 | 401.7 | 354.6 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P954584
 CATALOG NUMBER: GLAN-SB7D-750-U-SLL

CANDELA DISTRIBUTION (continued):

| 270° | | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 10490.5 | 0° | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 |
| 9844.4 | 2.5° | 9905.2 | 9966.4 | 10027.2 | 10088.0 | 10157.2 | 10226.9 | 10303.7 | 10381.0 | 10476.4 | 10562.2 |
| 9341.2 | 5° | 9439.5 | 9537.3 | 9645.2 | 9753.1 | 9875.0 | 9997.4 | 10143.5 | 10289.3 | 10456.3 | 10625.4 |
| 9035.3 | 7.5° | 9154.9 | 9274.8 | 9410.9 | 9546.5 | 9707.6 | 9868.6 | 10062.2 | 10256.2 | 10472.4 | 10703.1 |
| 8978.9 | 10° | 9113.8 | 9248.7 | 9395.2 | 9541.3 | 9702.3 | 9863.4 | 10067.9 | 10272.3 | 10504.6 | 10789.2 |
| 9236.6 | 12.5° | 9375.9 | 9515.5 | 9629.9 | 9745.0 | 9851.3 | 9958.4 | 10125.0 | 10292.5 | 10508.6 | 10807.7 |
| 9774.0 | 15° | 9895.2 | 10016.3 | 10046.1 | 10075.9 | 10061.4 | 10046.9 | 10126.6 | 10206.7 | 10379.8 | 10711.1 |
| 10345.6 | 17.5° | 10443.0 | 10540.9 | 10447.9 | 10354.5 | 10179.0 | 10003.4 | 9974.5 | 9945.1 | 10051.7 | 10441.4 |
| 10701.9 | 20° | 10747.4 | 10792.4 | 10597.2 | 10402.0 | 10096.8 | 9792.1 | 9655.2 | 9518.4 | 9546.5 | 10000.2 |
| 10697.8 | 22.5° | 10670.9 | 10643.5 | 10389.5 | 10135.5 | 9786.9 | 9439.1 | 9236.6 | 9034.1 | 8978.9 | 9495.4 |
| 10343.6 | 25° | 10250.6 | 10157.2 | 9907.2 | 9657.2 | 9344.1 | 9031.3 | 8797.8 | 8564.3 | 8415.4 | 8944.7 |
| 9727.7 | 27.5° | 9623.4 | 9519.6 | 9319.1 | 9118.6 | 8861.8 | 8604.6 | 8379.1 | 8153.7 | 7972.6 | 8454.4 |
| 9079.6 | 30° | 8995.0 | 8910.5 | 8743.9 | 8577.6 | 8364.2 | 8150.9 | 7971.4 | 7792.6 | 7650.5 | 8055.1 |
| 8536.1 | 32.5° | 8441.9 | 8348.1 | 8188.3 | 8028.9 | 7858.2 | 7688.0 | 7582.1 | 7476.2 | 7413.0 | 7739.1 |
| 8037.0 | 35° | 7924.3 | 7811.5 | 7653.3 | 7495.5 | 7365.9 | 7235.9 | 7206.5 | 7177.5 | 7203.7 | 7475.4 |
| 7580.1 | 37.5° | 7440.8 | 7301.5 | 7143.7 | 6986.3 | 6893.3 | 6799.9 | 6832.1 | 6864.3 | 6960.1 | 7197.6 |
| 7135.3 | 40° | 6974.6 | 6814.4 | 6662.3 | 6510.1 | 6442.9 | 6375.6 | 6448.5 | 6521.4 | 6668.3 | 6883.7 |
| 6708.5 | 42.5° | 6535.4 | 6362.4 | 6217.8 | 6073.7 | 6018.6 | 5963.8 | 6060.4 | 6157.0 | 6342.2 | 6540.7 |
| 6332.2 | 45° | 6152.6 | 5973.1 | 5836.2 | 5699.3 | 5652.6 | 5606.8 | 5700.6 | 5794.8 | 5973.9 | 6175.2 |
| 6022.2 | 47.5° | 5845.1 | 5667.9 | 5534.3 | 5400.2 | 5357.2 | 5313.7 | 5392.6 | 5471.5 | 5625.7 | 5885.3 |
| 5752.5 | 50° | 5593.9 | 5435.3 | 5309.3 | 5182.9 | 5114.8 | 5047.2 | 5116.9 | 5186.9 | 5366.0 | 5707.4 |
| 5567.3 | 52.5° | 5419.2 | 5271.4 | 5155.9 | 5040.0 | 4938.5 | 4836.7 | 4905.5 | 4974.8 | 5225.1 | 5617.6 |
| 5440.5 | 55° | 5311.3 | 5181.7 | 5056.9 | 4932.1 | 4788.0 | 4643.4 | 4752.5 | 4862.0 | 5239.2 | 5604.3 |
| 5335.8 | 57.5° | 5207.4 | 5079.4 | 4932.9 | 4786.4 | 4631.0 | 4475.6 | 4635.0 | 4794.4 | 5253.3 | 5575.4 |
| 5186.9 | 60° | 5056.5 | 4926.4 | 4758.2 | 4589.9 | 4453.8 | 4317.4 | 4524.3 | 4730.8 | 5209.0 | 5421.6 |
| 4983.6 | 62.5° | 4844.7 | 4705.8 | 4509.4 | 4313.4 | 4226.8 | 4140.3 | 4398.3 | 4656.7 | 5100.3 | 5126.5 |
| 4703.8 | 65° | 4571.0 | 4438.1 | 4227.6 | 4017.5 | 3984.5 | 3951.1 | 4226.0 | 4500.5 | 4838.7 | 4835.5 |
| 4383.8 | 67.5° | 4258.2 | 4132.2 | 3937.8 | 3743.7 | 3754.2 | 3764.7 | 3993.3 | 4222.0 | 4412.0 | 4420.8 |
| 4029.6 | 70° | 3920.9 | 3812.2 | 3641.5 | 3470.8 | 3507.0 | 3543.3 | 3705.9 | 3868.5 | 3930.9 | 3930.9 |
| 3610.9 | 72.5° | 3512.7 | 3414.5 | 3280.4 | 3146.0 | 3198.7 | 3251.8 | 3363.3 | 3474.8 | 3474.0 | 3434.6 |
| 3131.9 | 75° | 3042.9 | 2953.9 | 2854.1 | 2754.3 | 2805.4 | 2856.1 | 2942.3 | 3028.0 | 3043.3 | 2861.3 |
| 2654.8 | 77.5° | 2578.4 | 2501.9 | 2421.0 | 2339.6 | 2391.2 | 2442.7 | 2511.5 | 2580.4 | 2588.4 | 2288.5 |
| 2131.5 | 80° | 2067.1 | 2002.7 | 1935.5 | 1867.8 | 1911.3 | 1954.4 | 2012.4 | 2069.9 | 2071.1 | 1712.9 |
| 1348.6 | 82.5° | 1371.1 | 1393.6 | 1399.3 | 1404.9 | 1435.5 | 1466.1 | 1494.3 | 1522.5 | 1505.5 | 1199.6 |
| 690.4 | 85° | 752.8 | 815.2 | 844.6 | 873.5 | 907.8 | 942.0 | 972.2 | 1002.4 | 980.2 | 752.8 |
| 308.0 | 87.5° | 355.9 | 403.4 | 404.6 | 405.8 | 412.2 | 418.7 | 430.7 | 442.8 | 414.6 | 320.0 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P954584
 CATALOG NUMBER: GLAN-SB7D-750-U-SLL

CANDELA DISTRIBUTION (continued):

| 325° | | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|
| 10490.5 | 0° | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 | 10490.5 |
| 10650.7 | 2.5° | 10739.3 | 10831.9 | 10924.5 | 11016.3 | 11108.5 | 11195.0 | 11281.5 |
| 10804.5 | 5° | 10983.7 | 11175.3 | 11367.3 | 11557.7 | 11748.5 | 11939.7 | 12130.9 |
| 10953.1 | 7.5° | 11203.1 | 11486.9 | 11770.7 | 12062.1 | 12353.5 | 12668.7 | 12984.3 |
| 11085.5 | 10° | 11381.0 | 11726.0 | 12070.6 | 12455.4 | 12840.6 | 13239.6 | 13638.5 |
| 11142.3 | 12.5° | 11476.8 | 11883.4 | 12289.9 | 12726.3 | 13162.7 | 13600.7 | 14039.0 |
| 11098.4 | 15° | 11485.6 | 11953.8 | 12422.0 | 12895.4 | 13368.8 | 13825.7 | 14282.6 |
| 10907.2 | 17.5° | 11372.9 | 11916.4 | 12459.8 | 12976.3 | 13492.8 | 13956.1 | 14419.4 |
| 10577.5 | 20° | 11154.7 | 11813.3 | 12471.9 | 13039.5 | 13607.1 | 14089.0 | 14570.4 |
| 10190.6 | 22.5° | 10885.8 | 11686.9 | 12488.0 | 13124.8 | 13761.3 | 14253.6 | 14745.5 |
| 9758.7 | 25° | 10573.1 | 11562.1 | 12551.6 | 13279.4 | 14006.8 | 14488.7 | 14970.9 |
| 9363.8 | 27.5° | 10273.2 | 11478.8 | 12684.4 | 13521.0 | 14357.1 | 14817.2 | 15276.9 |
| 9033.7 | 30° | 10012.3 | 11439.8 | 12866.4 | 13833.7 | 14801.1 | 15245.1 | 15689.5 |
| 8749.1 | 32.5° | 9758.7 | 11391.4 | 13023.4 | 14160.2 | 15297.0 | 15736.6 | 16176.6 |
| 8469.3 | 35° | 9463.2 | 11300.5 | 13138.5 | 14532.2 | 15925.8 | 16347.3 | 16768.3 |
| 8140.0 | 37.5° | 9082.4 | 11144.7 | 13207.0 | 14948.8 | 16690.7 | 17227.7 | 17764.7 |
| 7747.1 | 40° | 8610.6 | 10930.1 | 13250.0 | 15477.8 | 17705.1 | 18487.7 | 19270.2 |
| 7313.6 | 42.5° | 8086.5 | 10708.7 | 13331.8 | 16169.8 | 19007.7 | 20137.3 | 21266.9 |
| 6853.1 | 45° | 7531.0 | 10503.0 | 13475.5 | 17080.3 | 20685.2 | 22208.9 | 23732.5 |
| 6488.8 | 47.5° | 7092.2 | 10333.1 | 13574.1 | 18050.5 | 22526.9 | 24671.7 | 26816.1 |
| 6246.8 | 50° | 6786.2 | 10148.0 | 13509.7 | 18950.6 | 24391.5 | 27624.8 | 30857.7 |
| 6087.4 | 52.5° | 6557.6 | 9835.2 | 13113.2 | 19535.1 | 25956.6 | 30726.9 | 35497.1 |
| 5971.9 | 55° | 6339.4 | 9316.7 | 12294.0 | 19406.3 | 26518.2 | 33477.1 | 40436.5 |
| 5835.0 | 57.5° | 6094.7 | 8585.7 | 11076.2 | 18499.7 | 25923.6 | 35426.3 | 44928.9 |
| 5625.7 | 60° | 5829.8 | 7636.4 | 9443.1 | 16812.6 | 24182.2 | 35913.4 | 47644.2 |
| 5261.8 | 62.5° | 5397.4 | 6500.4 | 7603.4 | 14531.4 | 21459.3 | 33862.4 | 46265.4 |
| 4899.5 | 65° | 4963.5 | 5478.3 | 5993.2 | 12203.8 | 18414.8 | 30960.4 | 43505.9 |
| 4385.4 | 67.5° | 4349.6 | 4496.1 | 4642.2 | 9923.7 | 15205.2 | 27506.9 | 39808.5 |
| 3765.5 | 70° | 3599.6 | 3558.2 | 3516.3 | 7813.6 | 12110.8 | 23738.6 | 35366.3 |
| 3199.9 | 72.5° | 2964.8 | 2838.4 | 2712.4 | 5973.5 | 9234.6 | 19653.4 | 30072.7 |
| 2598.1 | 75° | 2334.8 | 2220.5 | 2106.2 | 4335.5 | 6564.8 | 14970.5 | 23376.3 |
| 2032.9 | 77.5° | 1777.3 | 1699.2 | 1621.5 | 2937.8 | 4254.2 | 10478.1 | 16701.9 |
| 1496.7 | 80° | 1280.1 | 1247.9 | 1215.7 | 1892.8 | 2570.3 | 6750.8 | 10931.3 |
| 1040.2 | 82.5° | 880.8 | 874.3 | 868.7 | 1164.2 | 1460.5 | 3907.2 | 6354.3 |
| 636.0 | 85° | 519.3 | 522.5 | 525.3 | 622.3 | 719.8 | 1757.5 | 2795.7 |
| 272.1 | 87.5° | 224.6 | 227.4 | 230.3 | 258.0 | 285.8 | 575.7 | 865.5 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)