

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P949672

Luminaire Tested: **GLAN-SB4B-835-U-SLR**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P949672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB4B-835-U-SLR
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(4) 80 CRI, 3500K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20858 lumens
Efficiency: N/A
Efficacy: 141.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G4

Input Watts (W): 147
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P949672

CATALOG NUMBER: GLAN-SB4B-835-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
- - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.7 fc
Type IV - Short - N/A

REPORT NUMBER: P949672
CATALOG NUMBER: GLAN-SB4B-835-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P949672

CATALOG NUMBER: GLAN-SB4B-835-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5301.1	0.0	5301.1
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	15556.9	0.0	15556.9
	% Fixture	74.6	0.0	74.6
Total	Lumens	20858.0	0.0	20858.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.5	1.4
10°-20°	893.2	4.3
20°-30°	1379.6	6.6
30°-40°	1748.3	8.4
40°-50°	2636.9	12.6
50°-60°	4260.3	20.4
60°-70°	5311.2	25.5
70°-80°	3482.8	16.7
80°-90°	861.0	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	20858.0	100.0
0°-180°	20858.0	100.0

Coefficient of Utilization



REPORT NUMBER: P949672


CATALOG NUMBER: GLAN-SB4B-835-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1402.9	6.7			
FM	(30°-60°)	6083.8	29.2			
FH	(60°-80°)	7360.9	35.3			G3/7500
FVH	(80°-90°)	709.3	3.4			G4/750
BL	(0°-30°)	1154.4	5.5	B3/2500		
BM	(30°-60°)	2561.8	12.3	B3/5000		
BH	(60°-80°)	1433.2	6.9	B3/2500		G3/2500
BVH	(80°-90°)	151.7	0.7			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4

Type IV Short



REPORT NUMBER: P949672

CATALOG NUMBER: GLAN-SB4B-835-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2
2.5°	3084.4	3060.8	3037.1	3011.9	2986.8	2961.5	2936.2	2912.0	2887.7	2864.3
5°	3316.6	3264.4	3212.1	3159.9	3107.9	3055.4	3003.0	2954.0	2905.0	2858.8
7.5°	3550.0	3463.7	3377.5	3297.8	3218.1	3140.6	3063.0	2994.6	2926.3	2863.2
10°	3728.8	3619.8	3510.7	3405.4	3300.1	3205.9	3111.6	3030.8	2949.8	2872.0
12.5°	3838.3	3718.5	3598.7	3479.4	3360.1	3249.0	3137.8	3046.3	2954.9	2873.1
15°	3904.9	3780.0	3655.1	3525.7	3396.2	3268.2	3140.2	3034.3	2928.5	2837.9
17.5°	3942.3	3815.7	3689.0	3547.8	3406.6	3258.0	3109.4	2982.1	2854.7	2748.2
20°	3983.6	3852.0	3720.2	3565.1	3409.9	3229.8	3049.8	2891.9	2734.1	2610.1
22.5°	4031.5	3897.0	3762.4	3588.4	3414.3	3195.3	2976.2	2786.2	2596.1	2454.9
25°	4093.1	3961.3	3829.5	3630.6	3431.7	3161.1	2890.7	2668.1	2445.5	2300.8
27.5°	4176.8	4051.1	3925.3	3696.7	3468.0	3138.4	2808.7	2560.1	2311.5	2179.7
30°	4289.6	4168.1	4046.7	3782.2	3517.7	3127.7	2737.4	2469.8	2202.3	2091.7
32.5°	4422.7	4302.5	4182.3	3871.5	3560.6	3114.5	2668.1	2392.0	2115.9	2026.7
35°	4584.5	4469.4	4354.2	3973.2	3592.1	3089.6	2587.3	2315.5	2043.8	1969.5
37.5°	4856.9	4710.1	4563.3	4087.1	3610.8	3047.0	2483.2	2225.5	1967.9	1902.9
40°	5268.6	5054.6	4840.6	4231.7	3622.6	2988.3	2354.2	2118.1	1882.0	1823.1
42.5°	5814.5	5505.6	5196.8	4420.9	3645.0	2927.8	2210.9	1999.6	1788.2	1734.0
45°	6488.6	6072.0	5655.4	4669.8	3684.2	2871.6	2059.0	1873.7	1688.3	1633.3
47.5°	7331.6	6745.3	6158.9	4935.1	3711.2	2825.1	1939.0	1774.1	1609.1	1538.1
50°	8436.6	7552.7	6668.7	5181.2	3693.6	2774.5	1855.4	1707.9	1560.4	1467.1
52.5°	9705.1	8400.9	7096.6	5341.0	3585.2	2689.0	1792.9	1664.3	1535.9	1428.6
55°	11055.5	9152.8	7250.2	5305.8	3361.2	2547.2	1733.2	1632.7	1532.3	1432.4
57.5°	12283.8	9685.7	7087.6	5057.9	3028.3	2347.4	1666.3	1595.3	1524.3	1436.3
60°	13026.1	9818.9	6611.5	4596.6	2581.8	2087.8	1593.9	1538.1	1482.3	1424.2
62.5°	12649.2	9258.1	5867.1	3972.9	2078.8	1777.2	1475.7	1438.6	1401.6	1394.5
65°	11894.7	8464.7	5034.7	3336.6	1638.6	1497.8	1357.0	1339.5	1322.0	1322.9
67.5°	10883.8	7520.5	4157.2	2713.2	1269.2	1229.3	1189.2	1199.0	1208.7	1206.3
70°	9669.3	6490.2	3311.1	2136.3	961.4	972.8	984.2	1029.5	1074.7	1074.7
72.5°	8222.0	5373.3	2524.8	1633.2	741.6	776.0	810.6	874.9	939.0	949.8
75°	6391.2	4093.0	1794.9	1185.3	575.8	607.1	638.3	710.3	782.3	832.1
77.5°	4566.4	2864.7	1163.1	803.2	443.3	464.6	485.9	555.8	625.7	707.7
80°	2988.7	1845.7	702.7	517.5	332.4	341.2	350.0	409.2	468.3	566.3
82.5°	1737.3	1068.2	399.3	318.3	237.5	239.0	240.8	284.4	328.0	411.6
85°	764.4	480.5	196.8	170.2	143.6	142.9	142.0	173.9	205.8	268.0
87.5°	236.6	157.4	78.1	70.5	63.0	62.2	61.4	74.4	87.5	113.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949672

CATALOG NUMBER: GLAN-SB4B-835-U-SLR

CANDELA DISTRIBUTION (continued):

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
2868.2	0°	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2
2838.2	2.5°	2817.1	2796.1	2777.0	2758.1	2741.5	2724.9	2708.1	2691.5	2678.6	2665.6
2813.1	5°	2773.3	2733.3	2699.9	2666.5	2637.0	2607.5	2580.8	2553.9	2533.4	2512.7
2804.1	7.5°	2751.1	2698.1	2654.1	2610.1	2573.0	2535.8	2503.0	2470.3	2445.7	2421.3
2808.5	10°	2752.6	2696.7	2652.7	2608.6	2568.7	2528.6	2491.8	2454.9	2425.6	2396.2
2814.0	12.5°	2768.2	2722.7	2693.4	2664.3	2632.8	2601.6	2563.4	2525.3	2487.9	2450.5
2790.6	15°	2768.7	2746.9	2750.8	2754.8	2746.6	2738.5	2705.4	2672.2	2619.0	2565.7
2719.0	17.5°	2727.1	2735.0	2783.0	2831.0	2856.5	2881.9	2855.2	2828.5	2758.0	2687.4
2602.4	20°	2639.8	2677.2	2760.5	2843.9	2897.3	2950.7	2938.4	2925.9	2845.3	2764.7
2470.0	22.5°	2525.3	2580.7	2675.8	2771.1	2840.5	2910.0	2917.5	2924.8	2847.8	2770.8
2341.5	25°	2405.4	2469.2	2554.7	2640.3	2708.7	2777.0	2802.6	2828.0	2764.8	2701.7
2229.3	27.5°	2290.9	2352.5	2422.9	2493.1	2547.9	2602.7	2631.1	2659.6	2614.6	2569.7
2130.5	30°	2179.4	2228.5	2286.8	2345.2	2390.6	2436.2	2459.3	2482.4	2448.2	2413.8
2044.0	32.5°	2073.0	2101.9	2148.5	2195.1	2238.7	2282.4	2308.1	2333.8	2302.3	2270.8
1962.4	35°	1970.3	1978.3	2013.9	2049.3	2092.5	2135.7	2166.5	2197.3	2174.9	2152.5
1876.7	37.5°	1867.9	1859.1	1884.7	1910.1	1953.1	1996.3	2034.3	2072.4	2062.1	2051.7
1783.0	40°	1763.0	1743.1	1761.5	1779.9	1821.5	1863.1	1906.9	1950.8	1953.3	1955.8
1683.4	42.5°	1656.9	1630.5	1645.5	1660.6	1700.0	1739.5	1786.8	1834.1	1846.8	1859.5
1584.3	45°	1558.6	1532.9	1545.5	1558.2	1595.6	1633.1	1682.2	1731.2	1749.4	1767.6
1495.9	47.5°	1474.4	1452.8	1464.7	1476.5	1513.1	1549.6	1598.1	1646.5	1667.4	1688.3
1418.1	50°	1399.0	1379.9	1398.4	1417.0	1451.6	1486.0	1529.4	1572.8	1599.6	1626.5
1360.1	52.5°	1341.2	1322.4	1350.2	1377.9	1409.6	1441.2	1481.6	1522.1	1553.9	1585.7
1329.3	55°	1299.4	1269.5	1309.0	1348.5	1382.6	1416.7	1452.1	1487.5	1521.1	1554.9
1310.8	57.5°	1267.2	1223.6	1266.1	1308.6	1348.7	1388.7	1423.7	1458.8	1492.8	1526.7
1293.4	60°	1237.0	1180.4	1217.7	1254.9	1300.9	1346.9	1382.5	1418.1	1452.2	1486.4
1273.2	62.5°	1202.5	1132.0	1155.6	1179.3	1232.9	1286.6	1324.6	1362.5	1393.8	1425.1
1230.5	65°	1155.4	1080.2	1089.4	1098.4	1155.8	1213.4	1249.7	1286.0	1313.6	1341.1
1154.3	67.5°	1091.8	1029.3	1026.4	1023.6	1076.6	1129.8	1164.2	1198.5	1222.3	1246.1
1057.7	70°	1013.2	968.7	958.8	948.9	995.6	1042.3	1072.0	1101.7	1123.2	1144.6
950.0	72.5°	919.5	889.1	874.5	860.1	896.9	933.5	960.4	987.2	1008.3	1029.3
827.9	75°	804.4	780.9	767.0	753.0	780.3	807.6	831.9	856.3	875.4	894.6
705.5	77.5°	686.7	667.8	653.8	639.7	661.9	684.0	704.9	725.8	746.0	766.0
565.9	80°	550.2	534.3	522.6	510.7	529.2	547.5	565.2	582.8	598.1	613.3
416.2	82.5°	408.5	400.8	392.5	384.1	382.6	381.0	374.9	368.7	401.3	433.9
274.0	85°	265.8	257.5	248.2	238.8	230.9	222.9	205.8	188.8	219.2	249.8
121.1	87.5°	117.8	114.5	112.7	110.9	110.6	110.3	97.3	84.2	97.0	109.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949672

CATALOG NUMBER: GLAN-SB4B-835-U-SLR

CANDELA DISTRIBUTION (continued):

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
2868.2	0°	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2
2655.2	2.5°	2644.7	2636.6	2628.4	2621.0	2613.4	2604.0	2613.4	2621.0	2628.4	2636.6
2498.2	5°	2483.8	2473.6	2463.4	2455.5	2447.7	2440.0	2447.7	2455.5	2463.4	2473.6
2404.1	7.5°	2387.0	2375.2	2363.5	2356.5	2349.6	2344.3	2349.6	2356.5	2363.5	2375.2
2377.1	10°	2357.7	2346.6	2335.5	2329.5	2323.6	2321.2	2323.6	2329.5	2335.5	2346.6
2425.7	12.5°	2401.0	2388.5	2376.2	2371.1	2366.1	2365.2	2366.1	2371.1	2376.2	2388.5
2528.1	15°	2490.4	2473.2	2456.0	2449.4	2442.8	2442.2	2442.8	2449.4	2456.0	2473.2
2632.0	17.5°	2576.5	2551.0	2525.3	2517.0	2508.5	2507.2	2508.5	2517.0	2525.3	2551.0
2696.7	20°	2628.8	2596.1	2563.3	2552.8	2542.4	2539.1	2542.4	2552.8	2563.3	2596.1
2700.8	22.5°	2630.6	2596.2	2561.6	2550.1	2538.5	2533.6	2538.5	2550.1	2561.6	2596.2
2639.5	25°	2577.4	2547.4	2517.6	2506.7	2495.9	2489.5	2495.9	2506.7	2517.6	2547.4
2521.4	27.5°	2473.0	2453.0	2432.9	2427.9	2423.0	2421.3	2423.0	2427.9	2432.9	2453.0
2379.3	30°	2344.5	2334.3	2323.9	2323.9	2323.9	2325.6	2323.9	2323.9	2323.9	2334.3
2243.1	32.5°	2215.5	2208.8	2202.1	2203.0	2203.9	2205.6	2203.9	2203.0	2202.1	2208.8
2127.0	35°	2101.6	2091.4	2081.2	2079.0	2076.8	2075.7	2076.8	2079.0	2081.2	2091.4
2028.3	37.5°	2004.7	1986.1	1967.6	1957.9	1948.1	1942.6	1948.1	1957.9	1967.6	1986.1
1935.8	40°	1915.9	1888.8	1862.0	1843.7	1825.7	1814.9	1825.7	1843.7	1862.0	1888.8
1842.6	42.5°	1825.9	1792.3	1758.8	1732.2	1705.7	1688.3	1705.7	1732.2	1758.8	1792.3
1752.4	45°	1737.3	1698.9	1660.6	1629.4	1598.3	1578.3	1598.3	1629.4	1660.6	1698.9
1677.7	47.5°	1667.2	1633.1	1598.9	1570.1	1541.4	1522.1	1541.4	1570.1	1598.9	1633.1
1625.8	50°	1625.4	1598.1	1570.8	1544.1	1517.5	1499.0	1517.5	1544.1	1570.8	1598.1
1591.5	52.5°	1597.2	1575.0	1552.7	1528.8	1505.1	1488.0	1505.1	1528.8	1552.7	1575.0
1562.8	55°	1570.8	1551.4	1532.0	1511.1	1490.2	1474.8	1490.2	1511.1	1532.0	1551.4
1534.8	57.5°	1542.8	1523.2	1503.6	1482.9	1462.1	1446.2	1462.1	1482.9	1503.6	1523.2
1495.2	60°	1504.0	1484.8	1465.8	1444.4	1423.1	1406.6	1423.1	1444.4	1465.8	1484.8
1433.5	62.5°	1442.0	1424.7	1407.4	1385.0	1362.5	1342.7	1362.5	1385.0	1407.4	1424.7
1349.8	65°	1358.4	1341.7	1325.1	1303.3	1281.6	1264.6	1281.6	1303.3	1325.1	1341.7
1254.6	67.5°	1262.9	1247.6	1232.4	1212.2	1191.9	1176.5	1191.9	1212.2	1232.4	1247.6
1152.8	70°	1160.9	1148.5	1136.0	1116.7	1097.3	1079.7	1097.3	1116.7	1136.0	1148.5
1039.0	72.5°	1048.6	1038.3	1028.0	1009.5	991.1	974.0	991.1	1009.5	1028.0	1038.3
904.7	75°	914.8	909.8	904.7	889.2	873.7	857.4	873.7	889.2	904.7	909.8
775.5	77.5°	784.9	777.9	770.6	755.0	739.4	726.4	739.4	755.0	770.6	777.9
625.8	80°	638.3	635.3	632.3	611.3	590.1	565.7	590.1	611.3	632.3	635.3
455.2	82.5°	476.6	475.2	473.8	456.1	438.3	422.6	438.3	456.1	473.8	475.2
276.2	85°	302.7	300.5	298.3	284.4	270.5	256.4	270.5	284.4	298.3	300.5
120.5	87.5°	131.2	128.5	125.7	118.6	111.4	104.6	111.4	118.6	125.7	128.5
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949672

CATALOG NUMBER: GLAN-SB4B-835-U-SLR

CANDELA DISTRIBUTION (continued):

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
2868.2	0°	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2
2644.7	2.5°	2655.2	2665.6	2678.6	2691.5	2708.1	2724.9	2741.5	2758.1	2777.0	2796.1
2483.8	5°	2498.2	2512.7	2533.4	2553.9	2580.8	2607.5	2637.0	2666.5	2699.9	2733.3
2387.0	7.5°	2404.1	2421.3	2445.7	2470.3	2503.0	2535.8	2573.0	2610.1	2654.1	2698.1
2357.7	10°	2377.1	2396.2	2425.6	2454.9	2491.8	2528.6	2568.7	2608.6	2652.7	2696.7
2401.0	12.5°	2425.7	2450.5	2487.9	2525.3	2563.4	2601.6	2632.8	2664.3	2693.4	2722.7
2490.4	15°	2528.1	2565.7	2619.0	2672.2	2705.4	2738.5	2746.6	2754.8	2750.8	2746.9
2576.5	17.5°	2632.0	2687.4	2758.0	2828.5	2855.2	2881.9	2856.5	2831.0	2783.0	2735.0
2628.8	20°	2696.7	2764.7	2845.3	2925.9	2938.4	2950.7	2897.3	2843.9	2760.5	2677.2
2630.6	22.5°	2700.8	2770.8	2847.8	2924.8	2917.5	2910.0	2840.5	2771.1	2675.8	2580.7
2577.4	25°	2639.5	2701.7	2764.8	2828.0	2802.6	2777.0	2708.7	2640.3	2554.7	2469.2
2473.0	27.5°	2521.4	2569.7	2614.6	2659.6	2631.1	2602.7	2547.9	2493.1	2422.9	2352.5
2344.5	30°	2379.3	2413.8	2448.2	2482.4	2459.3	2436.2	2390.6	2345.2	2286.8	2228.5
2215.5	32.5°	2243.1	2270.8	2302.3	2333.8	2308.1	2282.4	2238.7	2195.1	2148.5	2101.9
2101.6	35°	2127.0	2152.5	2174.9	2197.3	2166.5	2135.7	2092.5	2049.3	2013.9	1978.3
2004.7	37.5°	2028.3	2051.7	2062.1	2072.4	2034.3	1996.3	1953.1	1910.1	1884.7	1859.1
1915.9	40°	1935.8	1955.8	1953.3	1950.8	1906.9	1863.1	1821.5	1779.9	1761.5	1743.1
1825.9	42.5°	1842.6	1859.5	1846.8	1834.1	1786.8	1739.5	1700.0	1660.6	1645.5	1630.5
1737.3	45°	1752.4	1767.6	1749.4	1731.2	1682.2	1633.1	1595.6	1558.2	1545.5	1532.9
1667.2	47.5°	1677.7	1688.3	1667.4	1646.5	1598.1	1549.6	1513.1	1476.5	1464.7	1452.8
1625.4	50°	1625.8	1626.5	1599.6	1572.8	1529.4	1486.0	1451.6	1417.0	1398.4	1379.9
1597.2	52.5°	1591.5	1585.7	1553.9	1522.1	1481.6	1441.2	1409.6	1377.9	1350.2	1322.4
1570.8	55°	1562.8	1554.9	1521.1	1487.5	1452.1	1416.7	1382.6	1348.5	1309.0	1269.5
1542.8	57.5°	1534.8	1526.7	1492.8	1458.8	1423.7	1388.7	1348.7	1308.6	1266.1	1223.6
1504.0	60°	1495.2	1486.4	1452.2	1418.1	1382.5	1346.9	1300.9	1254.9	1217.7	1180.4
1442.0	62.5°	1433.5	1425.1	1393.8	1362.5	1324.6	1286.6	1232.9	1179.3	1155.6	1132.0
1358.4	65°	1349.8	1341.1	1313.6	1286.0	1249.7	1213.4	1155.8	1098.4	1089.4	1080.2
1262.9	67.5°	1254.6	1246.1	1222.3	1198.5	1164.2	1129.8	1076.6	1023.6	1026.4	1029.3
1160.9	70°	1152.8	1144.6	1123.2	1101.7	1072.0	1042.3	995.6	948.9	958.8	968.7
1048.6	72.5°	1039.0	1029.3	1008.3	987.2	960.4	933.5	896.9	860.1	874.5	889.1
914.8	75°	904.7	894.6	875.4	856.3	831.9	807.6	780.3	753.0	767.0	780.9
784.9	77.5°	775.5	766.0	746.0	725.8	704.9	684.0	661.9	639.7	653.8	667.8
638.3	80°	625.8	613.3	598.1	582.8	565.2	547.5	529.2	510.7	522.6	534.3
476.6	82.5°	455.2	433.9	401.3	368.7	374.9	381.0	382.6	384.1	392.5	400.8
302.7	85°	276.2	249.8	219.2	188.8	205.8	222.9	230.9	238.8	248.2	257.5
131.2	87.5°	120.5	109.8	97.0	84.2	97.3	110.3	110.6	110.9	112.7	114.5
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949672

CATALOG NUMBER: GLAN-SB4B-835-U-SLR

CANDELA DISTRIBUTION (continued):

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
2868.2	0°	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2
2817.1	2.5°	2838.2	2864.3	2887.7	2912.0	2936.2	2961.5	2986.8	3011.9	3037.1	3060.8
2773.3	5°	2813.1	2858.8	2905.0	2954.0	3003.0	3055.4	3107.9	3159.9	3212.1	3264.4
2751.1	7.5°	2804.1	2863.2	2926.3	2994.6	3063.0	3140.6	3218.1	3297.8	3377.5	3463.7
2752.6	10°	2808.5	2872.0	2949.8	3030.8	3111.6	3205.9	3300.1	3405.4	3510.7	3619.8
2768.2	12.5°	2814.0	2873.1	2954.9	3046.3	3137.8	3249.0	3360.1	3479.4	3598.7	3718.5
2768.7	15°	2790.6	2837.9	2928.5	3034.3	3140.2	3268.2	3396.2	3525.7	3655.1	3780.0
2727.1	17.5°	2719.0	2748.2	2854.7	2982.1	3109.4	3258.0	3406.6	3547.8	3689.0	3815.7
2639.8	20°	2602.4	2610.1	2734.1	2891.9	3049.8	3229.8	3409.9	3565.1	3720.2	3852.0
2525.3	22.5°	2470.0	2454.9	2596.1	2786.2	2976.2	3195.3	3414.3	3588.4	3762.4	3897.0
2405.4	25°	2341.5	2300.8	2445.5	2668.1	2890.7	3161.1	3431.7	3630.6	3829.5	3961.3
2290.9	27.5°	2229.3	2179.7	2311.5	2560.1	2808.7	3138.4	3468.0	3696.7	3925.3	4051.1
2179.4	30°	2130.5	2091.7	2202.3	2469.8	2737.4	3127.7	3517.7	3782.2	4046.7	4168.1
2073.0	32.5°	2044.0	2026.7	2115.9	2392.0	2668.1	3114.5	3560.6	3871.5	4182.3	4302.5
1970.3	35°	1962.4	1969.5	2043.8	2315.5	2587.3	3089.6	3592.1	3973.2	4354.2	4469.4
1867.9	37.5°	1876.7	1902.9	1967.9	2225.5	2483.2	3047.0	3610.8	4087.1	4563.3	4710.1
1763.0	40°	1783.0	1823.1	1882.0	2118.1	2354.2	2988.3	3622.6	4231.7	4840.6	5054.6
1656.9	42.5°	1683.4	1734.0	1788.2	1999.6	2210.9	2927.8	3645.0	4420.9	5196.8	5505.6
1558.6	45°	1584.3	1633.3	1688.3	1873.7	2059.0	2871.6	3684.2	4669.8	5655.4	6072.0
1474.4	47.5°	1495.9	1538.1	1609.1	1774.1	1939.0	2825.1	3711.2	4935.1	6158.9	6745.3
1399.0	50°	1418.1	1467.1	1560.4	1707.9	1855.4	2774.5	3693.6	5181.2	6668.7	7552.7
1341.2	52.5°	1360.1	1428.6	1535.9	1664.3	1792.9	2689.0	3585.2	5341.0	7096.6	8400.9
1299.4	55°	1329.3	1432.4	1532.3	1632.7	1733.2	2547.2	3361.2	5305.8	7250.2	9152.8
1267.2	57.5°	1310.8	1436.3	1524.3	1595.3	1666.3	2347.4	3028.3	5057.9	7087.6	9685.7
1237.0	60°	1293.4	1424.2	1482.3	1538.1	1593.9	2087.8	2581.8	4596.6	6611.5	9818.9
1202.5	62.5°	1273.2	1394.5	1401.6	1438.6	1475.7	1777.2	2078.8	3972.9	5867.1	9258.1
1155.4	65°	1230.5	1322.9	1322.0	1339.5	1357.0	1497.8	1638.6	3336.6	5034.7	8464.7
1091.8	67.5°	1154.3	1206.3	1208.7	1199.0	1189.2	1229.3	1269.2	2713.2	4157.2	7520.5
1013.2	70°	1057.7	1074.7	1074.7	1029.5	984.2	972.8	961.4	2136.3	3311.1	6490.2
919.5	72.5°	950.0	949.8	939.0	874.9	810.6	776.0	741.6	1633.2	2524.8	5373.3
804.4	75°	827.9	832.1	782.3	710.3	638.3	607.1	575.8	1185.3	1794.9	4093.0
686.7	77.5°	705.5	707.7	625.7	555.8	485.9	464.6	443.3	803.2	1163.1	2864.7
550.2	80°	565.9	566.3	468.3	409.2	350.0	341.2	332.4	517.5	702.7	1845.7
408.5	82.5°	416.2	411.6	328.0	284.4	240.8	239.0	237.5	318.3	399.3	1068.2
265.8	85°	274.0	268.0	205.8	173.9	142.0	142.9	143.6	170.2	196.8	480.5
117.8	87.5°	121.1	113.4	87.5	74.4	61.4	62.2	63.0	70.5	78.1	157.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949672

CATALOG NUMBER: GLAN-SB4B-835-U-SLR

CANDELA DISTRIBUTION (continued):

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
2868.2	0°	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2
3084.4	2.5°	3096.1	3107.9	3124.5	3141.1	3151.0	3160.9	3165.9	3170.8	3168.6	3170.8
3316.6	5°	3357.5	3398.4	3438.9	3479.5	3501.5	3523.6	3536.9	3550.3	3560.4	3550.3
3550.0	7.5°	3616.5	3682.8	3742.6	3802.3	3838.3	3874.3	3893.8	3913.2	3922.5	3913.2
3728.8	10°	3807.4	3886.0	3956.1	4026.2	4068.7	4110.9	4129.9	4148.7	4155.9	4148.7
3838.3	12.5°	3923.5	4008.6	4072.0	4135.2	4166.0	4196.8	4207.1	4217.5	4218.6	4217.5
3904.9	15°	3978.4	4051.8	4091.6	4131.4	4132.5	4133.6	4122.6	4111.6	4098.6	4111.6
3942.3	17.5°	3992.0	4041.6	4042.4	4043.0	3998.5	3953.9	3913.1	3872.1	3843.3	3872.1
3983.6	20°	4000.9	4018.3	3966.0	3913.7	3815.3	3716.9	3645.3	3573.6	3529.6	3573.6
4031.5	22.5°	4008.8	3986.1	3877.8	3769.5	3624.8	3480.1	3390.5	3300.9	3252.3	3300.9
4093.1	25°	4021.6	3950.0	3785.6	3621.2	3445.4	3269.7	3175.4	3081.5	3035.4	3081.5
4176.8	27.5°	4048.9	3920.9	3703.1	3485.4	3290.6	3095.8	3003.1	2910.5	2867.1	2910.5
4289.6	30°	4098.8	3908.2	3640.1	3372.0	3169.1	2966.1	2880.2	2794.2	2753.7	2794.2
4422.7	32.5°	4161.6	3900.5	3597.2	3293.9	3103.1	2912.4	2844.9	2777.4	2748.2	2777.4
4584.5	35°	4264.9	3945.4	3629.3	3313.3	3180.8	3048.4	3032.7	3017.0	3014.5	3017.0
4856.9	37.5°	4481.0	4105.0	3817.7	3530.5	3521.9	3513.3	3585.3	3657.3	3694.7	3657.3
5268.6	40°	4859.7	4450.8	4237.2	4023.6	4174.3	4325.1	4500.1	4675.1	4762.3	4675.1
5814.5	42.5°	5408.8	5003.1	4880.0	4757.0	5085.9	5414.7	5733.0	6051.3	6238.2	6051.3
6488.6	45°	6124.2	5759.6	5705.4	5651.0	6177.9	6704.8	7227.8	7751.0	8068.5	7751.0
7331.6	47.5°	6977.1	6622.5	6611.5	6600.5	7360.6	8120.4	8886.1	9651.7	10101.3	9651.7
8436.6	50°	7998.7	7560.9	7562.7	7564.6	8544.2	9523.7	10534.4	11545.0	12156.1	11545.0
9705.1	52.5°	9174.8	8644.6	8591.0	8537.3	9707.4	10877.4	12127.9	13378.3	14110.7	13378.3
11055.5	55°	10531.6	10007.7	9798.7	9589.7	10891.9	12194.1	13684.8	15175.6	16046.7	15175.6
12283.8	57.5°	11998.5	11713.1	11293.9	10874.8	12189.7	13504.5	15193.1	16881.5	17961.7	16881.5
13026.1	60°	13469.2	13912.4	13391.8	12871.3	14115.6	15359.9	17167.8	18975.6	20143.1	18975.6
12649.2	62.5°	13859.9	15070.7	15012.0	14953.3	16093.1	17233.1	18953.2	20673.1	21752.2	20673.1
11894.7	65°	13031.1	14167.4	14392.3	14617.0	16065.6	17514.3	19182.2	20849.9	21768.7	20849.9
10883.8	67.5°	11964.6	13045.4	13150.8	13256.1	14765.5	16274.7	17949.7	19624.7	20344.5	19624.7
9669.3	70°	10844.8	12020.5	12067.6	12114.8	13464.6	14814.2	16255.7	17697.0	18097.1	17697.0
8222.0	72.5°	9571.0	10920.1	10954.0	10987.8	12043.8	13099.9	14179.4	15258.9	15299.4	15258.9
6391.2	75°	7787.4	9183.6	9309.0	9434.3	10255.9	11077.5	11837.5	12597.4	12393.8	12597.4
4566.4	77.5°	5869.7	7173.1	7352.5	7531.9	8156.5	8781.1	9320.1	9859.1	9509.2	9859.1
2988.7	80°	4085.2	5181.6	5404.6	5627.6	6099.3	6570.8	6853.9	7136.8	6573.9	7136.8
1737.3	82.5°	2486.9	3236.6	3485.7	3734.9	4059.6	4384.2	4502.3	4620.3	4177.9	4620.3
764.4	85°	1162.2	1560.1	1772.0	1983.8	2250.6	2517.3	2584.3	2651.3	2296.9	2651.3
236.6	87.5°	370.4	504.1	622.3	740.5	873.9	1007.3	1013.0	1018.6	855.2	1018.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949672

CATALOG NUMBER: GLAN-SB4B-835-U-SLR

CANDELA DISTRIBUTION (continued):

325°		330°	335°	340°	345°	350°	355°	360°
2868.2	0°	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2	2868.2
3165.9	2.5°	3160.9	3151.0	3141.1	3124.5	3107.9	3096.1	3084.4
3536.9	5°	3523.6	3501.5	3479.5	3438.9	3398.4	3357.5	3316.6
3893.8	7.5°	3874.3	3838.3	3802.3	3742.6	3682.8	3616.5	3550.0
4129.9	10°	4110.9	4068.7	4026.2	3956.1	3886.0	3807.4	3728.8
4207.1	12.5°	4196.8	4166.0	4135.2	4072.0	4008.6	3923.5	3838.3
4122.6	15°	4133.6	4132.5	4131.4	4091.6	4051.8	3978.4	3904.9
3913.1	17.5°	3953.9	3998.5	4043.0	4042.4	4041.6	3992.0	3942.3
3645.3	20°	3716.9	3815.3	3913.7	3966.0	4018.3	4000.9	3983.6
3390.5	22.5°	3480.1	3624.8	3769.5	3877.8	3986.1	4008.8	4031.5
3175.4	25°	3269.7	3445.4	3621.2	3785.6	3950.0	4021.6	4093.1
3003.1	27.5°	3095.8	3290.6	3485.4	3703.1	3920.9	4048.9	4176.8
2880.2	30°	2966.1	3169.1	3372.0	3640.1	3908.2	4098.8	4289.6
2844.9	32.5°	2912.4	3103.1	3293.9	3597.2	3900.5	4161.6	4422.7
3032.7	35°	3048.4	3180.8	3313.3	3629.3	3945.4	4264.9	4584.5
3585.3	37.5°	3513.3	3521.9	3530.5	3817.7	4105.0	4481.0	4856.9
4500.1	40°	4325.1	4174.3	4023.6	4237.2	4450.8	4859.7	5268.6
5733.0	42.5°	5414.7	5085.9	4757.0	4880.0	5003.1	5408.8	5814.5
7227.8	45°	6704.8	6177.9	5651.0	5705.4	5759.6	6124.2	6488.6
8886.1	47.5°	8120.4	7360.6	6600.5	6611.5	6622.5	6977.1	7331.6
10534.4	50°	9523.7	8544.2	7564.6	7562.7	7560.9	7998.7	8436.6
12127.9	52.5°	10877.4	9707.4	8537.3	8591.0	8644.6	9174.8	9705.1
13684.8	55°	12194.1	10891.9	9589.7	9798.7	10007.7	10531.6	11055.5
15193.1	57.5°	13504.5	12189.7	10874.8	11293.9	11713.1	11998.5	12283.8
17167.8	60°	15359.9	14115.6	12871.3	13391.8	13912.4	13469.2	13026.1
18953.2	62.5°	17233.1	16093.1	14953.3	15012.0	15070.7	13859.9	12649.2
19182.2	65°	17514.3	16065.6	14617.0	14392.3	14167.4	13031.1	11894.7
17949.7	67.5°	16274.7	14765.5	13256.1	13150.8	13045.4	11964.6	10883.8
16255.7	70°	14814.2	13464.6	12114.8	12067.6	12020.5	10844.8	9669.3
14179.4	72.5°	13099.9	12043.8	10987.8	10954.0	10920.1	9571.0	8222.0
11837.5	75°	11077.5	10255.9	9434.3	9309.0	9183.6	7787.4	6391.2
9320.1	77.5°	8781.1	8156.5	7531.9	7352.5	7173.1	5869.7	4566.4
6853.9	80°	6570.8	6099.3	5627.6	5404.6	5181.6	4085.2	2988.7
4502.3	82.5°	4384.2	4059.6	3734.9	3485.7	3236.6	2486.9	1737.3
2584.3	85°	2517.3	2250.6	1983.8	1772.0	1560.1	1162.2	764.4
1013.0	87.5°	1007.3	873.9	740.5	622.3	504.1	370.4	236.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)