

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P1456673

Luminaire Tested: GLAN-SB5C-835-U-T3LG

Issue Date: 05/20/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1456673  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 5/22/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB5C-835-U-T3LG  
Description: GALLEON II AREA AND ROADWAY HIGH DENSITY LUMINAIRE 615mA 5xLight Square  
PACKAGE 80CRI 3500K FIXTURE w/ TYPE III LOW GLARE  
Light Source: (130) 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 34237.1 lumens  
Efficiency: N/A  
Efficacy: 137.2 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B3 - U0 - G4  
  
Input Watts (W): 249.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1456673

CATALOG NUMBER: GLAN-SB5C-835-U-T3LG

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 30 foot mounting height. Maximum calculated value = 8.7 fc  
 Type III - Short - N/A

REPORT NUMBER: P1456673

CATALOG NUMBER: GLAN-SB5C-835-U-T3LG

### Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral      - - - Horizontal Cone Through 53-Deg Vertical

REPORT NUMBER: P1456673

CATALOG NUMBER: GLAN-SB5C-835-U-T3LG

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	8630.9	0.0	8630.9
	% Fixture	25.2	0.0	25.2
<b>Street Side</b>	Lumens	25606.2	0.0	25606.2
	% Fixture	74.8	0.0	74.8
<b>Total</b>	Lumens	34237.1	0.0	34237.1
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	478.9	1.4
10°-20°	1483.0	4.3
20°-30°	2835.4	8.3
30°-40°	4868.1	14.2
40°-50°	6818.8	19.9
50°-60°	7738.4	22.6
60°-70°	6786.1	19.8
70°-80°	2653.5	7.8
80°-90°	574.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	34237.1	100.0
0°-180°	34237.1	100.0



REPORT NUMBER: P1456673


CATALOG NUMBER: GLAN-SB5C-835-U-T3LG

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2721.5	7.9			
FM	(30°-60°)	14922.7	43.6			
FH	(60°-80°)	7683.1	22.4			G4/12000
FVH	(80°-90°)	278.9	0.8			G3/500
BL	(0°-30°)	2075.8	6.1	B3/2500		
BM	(30°-60°)	4502.6	13.2	B3/5000		
BH	(60°-80°)	1756.5	5.1	B3/2500		G3/2500
BVH	(80°-90°)	296.1	0.9			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G4**

Type III Short





REPORT NUMBER: P1456673

CATALOG NUMBER: GLAN-SB5C-835-U-T3LG

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1
2.5°	5033.7	5033.7	5003.2	5033.7	5018.5	5041.4	5056.6	5056.6	5087.1	5079.5	5079.5
5°	4949.8	4934.6	4926.9	4980.3	5010.8	5071.9	5140.5	5171.0	5224.4	5224.4	5232.0
7.5°	4728.7	4721.0	4759.2	4865.9	4965.1	5117.6	5262.5	5346.4	5430.3	5445.6	5445.6
10°	4591.4	4583.7	4629.5	4759.2	4919.3	5140.5	5369.3	5544.7	5682.0	5720.1	5720.1
12.5°	4591.4	4591.4	4629.5	4759.2	4926.9	5193.9	5506.6	5804.0	6017.6	6063.4	6048.1
15°	4721.0	4713.4	4759.2	4896.4	5056.6	5308.3	5689.6	6086.2	6376.1	6459.9	6467.6
17.5°	4858.3	4850.7	4919.3	5094.7	5285.4	5537.1	5926.1	6414.2	6826.0	6932.8	6955.7
20°	5071.9	5064.2	5148.1	5315.9	5552.4	5842.2	6246.4	6803.2	7375.2	7489.6	7520.1
22.5°	5315.9	5323.5	5415.1	5621.0	5857.4	6238.8	6734.5	7352.3	8038.7	8214.1	8244.6
25°	5826.9	5804.0	5880.3	6025.2	6276.9	6734.5	7344.7	8015.8	8831.9	9045.5	9083.6
27.5°	6505.7	6467.6	6551.5	6696.4	6879.4	7306.5	8008.2	8755.6	9739.5	10006.4	10014.1
30°	7115.9	7093.0	7207.4	7504.8	7695.5	8023.5	8770.9	9625.1	10860.6	11249.6	11264.9
32.5°	7642.1	7634.5	7848.0	8229.4	8664.1	9014.9	9739.5	10723.4	12279.2	12729.2	12630.1
35°	8145.5	8168.4	8435.3	8831.9	9411.5	10113.2	10845.4	11966.5	13774.1	14315.6	14155.4
37.5°	8656.5	8671.7	9022.6	9533.6	10143.7	11058.9	12042.8	13316.5	15070.7	15741.8	15391.0
40°	9129.3	9175.1	9648.0	10197.1	10990.3	11920.8	13019.0	14254.6	16069.8	16733.3	16352.0
42.5°	9602.2	9670.9	10181.9	10936.9	11783.5	12752.1	13697.8	14826.6	16710.4	17450.2	16863.0
45°	10090.3	10136.1	10769.1	11554.7	12515.7	13408.0	14086.8	15192.7	17152.8	17953.6	17152.8
47.5°	10418.3	10509.8	11203.9	12111.4	13072.4	13911.4	14399.5	15345.2	17435.0	18281.6	17259.6
50°	10547.9	10677.6	11425.0	12431.8	13530.0	14384.3	14643.6	15429.1	17747.7	18571.4	17236.7
52.5°	10525.1	10647.1	11463.2	12576.7	13896.1	14819.0	14880.0	15520.7	17968.9	18670.5	17038.4
53°	10403.0	10570.8	11486.0	12584.3	13949.5	14933.4	14986.8	15528.3	17999.4	18807.8	17007.9
55°	9983.6	10075.1	11249.6	12576.7	14201.2	15360.5	15284.2	15757.1	18083.3	18716.3	16672.3
57.5°	9602.2	9693.7	10715.7	12431.8	14407.1	15963.0	15764.7	15719.0	17625.7	18197.7	15825.7
60°	9358.2	9388.7	10250.5	11974.2	14323.2	16382.5	16077.4	15269.0	16496.9	16969.8	14338.5
62.5°	9152.2	9144.6	9907.3	11318.3	14002.9	16443.5	16138.4	14155.4	14841.9	14918.1	12355.5
65°	8687.0	8633.6	9373.4	10578.4	13339.4	16168.9	15391.0	12469.9	12645.3	12393.6	9922.5
67.5°	7764.1	7649.7	8305.6	9449.7	11989.4	15391.0	13964.8	10509.8	9968.3	9464.9	7474.3
70°	5560.0	5560.0	6086.2	7230.3	9625.1	13301.2	11989.4	7954.8	6864.2	6414.2	4995.6
72.5°	2722.8	2791.4	3340.6	4271.0	6452.3	9655.6	9182.7	5155.8	4164.3	3943.1	3203.3
75°	1159.3	1166.9	1426.2	1891.5	3271.9	5712.5	5750.6	2974.5	2669.4	2562.6	2120.3
77.5°	808.4	823.7	938.1	1113.5	1555.9	2623.6	2989.7	1799.9	1792.3	1716.0	1510.1
80°	617.8	633.0	709.3	831.3	1044.9	1342.3	1548.3	1220.3	1281.3	1205.0	1090.6
82.5°	465.2	480.5	533.9	625.4	747.4	900.0	869.5	900.0	945.7	900.0	785.6
85°	312.7	320.3	358.5	434.7	480.5	541.5	541.5	655.9	686.4	671.2	617.8
87.5°	160.2	160.2	190.7	228.8	244.1	251.7	221.2	289.8	328.0	358.5	289.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1456673

CATALOG NUMBER: GLAN-SB5C-835-U-T3LG

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1	5026.1
2.5°	5079.5	5087.1	5064.2	5056.6	5049.0	5010.8	5010.8	4972.7	4965.1	4972.7	4949.8
5°	5247.3	5232.0	5171.0	5125.2	5071.9	4965.1	4904.1	4820.2	4797.3	4774.4	4751.5
7.5°	5453.2	5430.3	5323.5	5201.5	5056.6	4850.7	4736.3	4599.0	4553.2	4515.1	4499.8
10°	5712.5	5666.8	5499.0	5239.7	4972.7	4721.0	4560.9	4393.1	4316.8	4301.5	4263.4
12.5°	6048.1	5964.2	5651.5	5247.3	4896.4	4568.5	4393.1	4263.4	4232.9	4225.3	4187.1
15°	6421.8	6299.8	5796.4	5254.9	4797.3	4438.8	4332.1	4263.4	4263.4	4255.8	4232.9
17.5°	6879.4	6681.1	5933.7	5224.4	4675.3	4400.7	4347.3	4286.3	4271.0	4278.7	4248.2
20°	7428.6	7100.6	6078.6	5186.3	4621.9	4408.3	4347.3	4263.4	4225.3	4217.7	4194.8
22.5°	8061.6	7581.1	6238.8	5125.2	4621.9	4400.7	4301.5	4187.1	4110.9	4080.4	4049.9
25°	8786.1	8137.9	6406.6	5102.4	4637.1	4370.2	4210.0	4027.0	3905.0	3859.2	3836.3
27.5°	9663.2	8725.1	6528.6	5125.2	4629.5	4301.5	4049.9	3813.4	3676.1	3599.9	3584.6
30°	10631.8	9358.2	6612.5	5163.4	4583.7	4171.9	3859.2	3592.2	3401.6	3310.1	3287.2
32.5°	11775.9	10067.5	6696.4	5163.4	4469.3	3988.8	3638.0	3348.2	3149.9	3043.1	3027.9
35°	13041.9	10936.9	6772.6	5155.8	4332.1	3790.5	3416.8	3119.4	2913.5	2806.7	2799.1
37.5°	14117.3	11592.8	6810.8	5079.5	4141.4	3561.7	3210.9	2913.5	2699.9	2585.5	2577.9
40°	14780.8	11867.4	6734.5	4926.9	3912.6	3325.3	2982.1	2707.5	2494.0	2356.7	2326.2
42.5°	15032.5	11737.7	6490.5	4675.3	3638.0	3088.9	2791.4	2501.6	2219.4	2105.0	2082.1
45°	14948.6	11234.4	5971.8	4316.8	3332.9	2875.3	2623.6	2295.7	2112.6	2013.5	2005.9
47.5°	14666.4	10456.4	5323.5	3866.8	3012.6	2684.7	2402.5	2242.3	2074.5	1967.7	1960.1
50°	14170.7	9625.1	4545.6	3355.8	2722.8	2486.4	2349.1	2219.4	2082.1	1998.2	1983.0
52.5°	13537.7	8687.0	3828.7	2860.1	2471.1	2310.9	2295.7	2204.2	2097.4	2005.9	1967.7
53°	13392.8	8442.9	3691.4	2776.2	2433.0	2288.1	2280.4	2204.2	2082.1	1998.2	1967.7
55°	12698.7	7687.9	3256.7	2478.7	2242.3	2211.8	2280.4	2196.5	2044.0	1975.4	1952.5
57.5°	11585.2	6696.4	2837.2	2204.2	2044.0	2120.3	2257.5	2166.0	1998.2	1876.2	1838.1
60°	10242.9	5560.0	2516.9	2021.1	1899.1	2005.9	2166.0	2059.3	1830.4	1769.4	1761.8
62.5°	8641.2	4499.8	2272.8	1868.6	1777.1	1883.8	2028.7	1845.7	1677.9	1632.1	1616.9
65°	6749.8	3577.0	2082.1	1754.2	1655.0	1738.9	1838.1	1723.7	1616.9	1578.8	1571.1
67.5°	5018.5	2806.7	1929.6	1655.0	1533.0	1586.4	1700.8	1670.3	1578.8	1555.9	1548.3
70°	3462.6	2280.4	1792.3	1563.5	1380.5	1441.5	1616.9	1639.8	1548.3	1533.0	1525.4
72.5°	2425.3	1929.6	1647.4	1464.4	1258.4	1319.4	1578.8	1578.8	1479.6	1502.5	1487.2
75°	1822.8	1624.5	1479.6	1342.3	1105.9	1197.4	1525.4	1510.1	1411.0	1510.1	1472.0
77.5°	1372.8	1311.8	1281.3	1189.8	968.6	1060.1	1418.6	1388.1	1258.4	1266.1	1197.4
80°	999.1	1014.4	1098.3	1014.4	808.4	877.1	1197.4	1182.2	1022.0	1052.5	968.6
82.5°	716.9	755.1	938.1	816.1	587.3	625.4	823.7	892.3	800.8	755.1	770.3
85°	541.5	564.4	755.1	602.5	366.1	411.9	564.4	640.7	625.4	579.6	587.3
87.5°	228.8	259.3	350.8	282.2	213.6	213.6	350.8	450.0	404.2	343.2	358.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-10

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-835-U-5WQ

Data in this report applies to families of products including GSS-SB1A-835-U-5WQ

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-10  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-835-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI 3500K CCT 26 LEDS

**Spectral Parameters**

CCT (K): 3411  
 CIE u': 0.2360  
 CIE v': 0.5189  
 Duv: 0.0044  
 CIE x: 0.4154  
 CIE y: 0.4059  
 CIE z: 0.1787  
 Peak Wavelength (nm): 601  
 Dominant Wavelength (nm): 579  
 Purity: 46.51914  
 Rf: 86.6  
 Rg: 95.9

CRI (Ra):	83.5		
R1:	81.1	R9:	6.3
R2:	88.9	R10:	75.4
R3:	97.2	R11:	84.1
R4:	83.8	R12:	69.7
R5:	81.7	R13:	82.8
R6:	86.9	R14:	98.5
R7:	86.1	R15:	72.6
R8:	62.2		



**Test Conditions**

Stabilization Time: 35M  
 Operation Time: 1H 35M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-10

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-10

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-10

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	311	NR	620	903	NR	750	26	NR	880	1	NR
365	0	NR	495	376	NR	625	851	NR	755	22	NR	885	1	NR
370	0	NR	500	438	NR	630	797	NR	760	19	NR	890	0	NR
375	0	NR	505	491	NR	635	735	NR	765	16	NR	895	0	NR
380	0	NR	510	533	NR	640	672	NR	770	14	NR	900	0	NR
385	0	NR	515	566	NR	645	607	NR	775	12	NR	905	0	NR
390	0	NR	520	592	NR	650	546	NR	780	10	NR	910	0	NR
395	1	NR	525	608	NR	655	487	NR	785	9	NR	915	0	NR
400	3	NR	530	625	NR	660	429	NR	790	7	NR	920	0	NR
405	6	NR	535	642	NR	665	378	NR	795	6	NR	925	0	NR
410	12	NR	540	657	NR	670	329	NR	800	5	NR	930	0	NR
415	22	NR	545	677	NR	675	286	NR	805	5	NR	935	0	NR
420	43	NR	550	701	NR	680	248	NR	810	4	NR	940	0	NR
425	80	NR	555	728	NR	685	213	NR	815	3	NR	945	0	NR
430	140	NR	560	757	NR	690	184	NR	820	3	NR	950	0	NR
435	243	NR	565	793	NR	695	156	NR	825	3	NR	955	0	NR
440	412	NR	570	831	NR	700	134	NR	830	2	NR	960	0	NR
445	610	NR	575	872	NR	705	114	NR	835	2	NR	965	0	NR
450	597	NR	580	911	NR	710	97	NR	840	2	NR	970	0	NR
455	412	NR	585	944	NR	715	83	NR	845	1	NR	975	0	NR
460	330	NR	590	974	NR	720	70	NR	850	1	NR	980	0	NR
465	274	NR	595	992	NR	725	60	NR	855	1	NR	985	0	NR
470	211	NR	600	999	NR	730	51	NR	860	1	NR	990	0	NR
475	200	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	220	NR	610	975	NR	740	36	NR	870	1	NR	1000	0	NR
485	255	NR	615	944	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-10

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.48**

$\lambda$ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens $(\phi/\text{nm})$	$\lambda$ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens $(\phi/\text{nm})$	$\lambda$ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens $(\phi/\text{nm})$	$\lambda$ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens $(\phi/\text{nm})$	$\lambda$ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens $(\phi/\text{nm})$
360	0	NR	490	311	NR	620	903	NR	750	26	NR	880	1	NR
365	0	NR	495	376	NR	625	851	NR	755	22	NR	885	1	NR
370	0	NR	500	438	NR	630	797	NR	760	19	NR	890	0	NR
375	0	NR	505	491	NR	635	735	NR	765	16	NR	895	0	NR
380	0	NR	510	533	NR	640	672	NR	770	14	NR	900	0	NR
385	0	NR	515	566	NR	645	607	NR	775	12	NR	905	0	NR
390	0	NR	520	592	NR	650	546	NR	780	10	NR	910	0	NR
395	1	NR	525	608	NR	655	487	NR	785	9	NR	915	0	NR
400	3	NR	530	625	NR	660	429	NR	790	7	NR	920	0	NR
405	6	NR	535	642	NR	665	378	NR	795	6	NR	925	0	NR
410	12	NR	540	657	NR	670	329	NR	800	5	NR	930	0	NR
415	22	NR	545	677	NR	675	286	NR	805	5	NR	935	0	NR
420	43	NR	550	701	NR	680	248	NR	810	4	NR	940	0	NR
425	80	NR	555	728	NR	685	213	NR	815	3	NR	945	0	NR
430	140	NR	560	757	NR	690	184	NR	820	3	NR	950	0	NR
435	243	NR	565	793	NR	695	156	NR	825	3	NR	955	0	NR
440	412	NR	570	831	NR	700	134	NR	830	2	NR	960	0	NR
445	610	NR	575	872	NR	705	114	NR	835	2	NR	965	0	NR
450	597	NR	580	911	NR	710	97	NR	840	2	NR	970	0	NR
455	412	NR	585	944	NR	715	83	NR	845	1	NR	975	0	NR
460	330	NR	590	974	NR	720	70	NR	850	1	NR	980	0	NR
465	274	NR	595	992	NR	725	60	NR	855	1	NR	985	0	NR
470	211	NR	600	999	NR	730	51	NR	860	1	NR	990	0	NR
475	200	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	220	NR	610	975	NR	740	36	NR	870	1	NR	1000	0	NR
485	255	NR	615	944	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-10

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.88

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	311	NR	620	903	NR	750	26	NR	880	1	NR
365	0	NR	495	376	NR	625	851	NR	755	22	NR	885	1	NR
370	0	NR	500	438	NR	630	797	NR	760	19	NR	890	0	NR
375	0	NR	505	491	NR	635	735	NR	765	16	NR	895	0	NR
380	0	NR	510	533	NR	640	672	NR	770	14	NR	900	0	NR
385	0	NR	515	566	NR	645	607	NR	775	12	NR	905	0	NR
390	0	NR	520	592	NR	650	546	NR	780	10	NR	910	0	NR
395	1	NR	525	608	NR	655	487	NR	785	9	NR	915	0	NR
400	3	NR	530	625	NR	660	429	NR	790	7	NR	920	0	NR
405	6	NR	535	642	NR	665	378	NR	795	6	NR	925	0	NR
410	12	NR	540	657	NR	670	329	NR	800	5	NR	930	0	NR
415	22	NR	545	677	NR	675	286	NR	805	5	NR	935	0	NR
420	43	NR	550	701	NR	680	248	NR	810	4	NR	940	0	NR
425	80	NR	555	728	NR	685	213	NR	815	3	NR	945	0	NR
430	140	NR	560	757	NR	690	184	NR	820	3	NR	950	0	NR
435	243	NR	565	793	NR	695	156	NR	825	3	NR	955	0	NR
440	412	NR	570	831	NR	700	134	NR	830	2	NR	960	0	NR
445	610	NR	575	872	NR	705	114	NR	835	2	NR	965	0	NR
450	597	NR	580	911	NR	710	97	NR	840	2	NR	970	0	NR
455	412	NR	585	944	NR	715	83	NR	845	1	NR	975	0	NR
460	330	NR	590	974	NR	720	70	NR	850	1	NR	980	0	NR
465	274	NR	595	992	NR	725	60	NR	855	1	NR	985	0	NR
470	211	NR	600	999	NR	730	51	NR	860	1	NR	990	0	NR
475	200	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	220	NR	610	975	NR	740	36	NR	870	1	NR	1000	0	NR
485	255	NR	615	944	NR	745	31	NR	875	1	NR			

**Summary**

$R_f = 86.6$   
 $R_g = 95.9$   
 $CIE R_a = 83.5$   
 $R_9 = 6.3$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

CES01 = 86	CES26 = 85	CES51 = 97	CES76 = 81
CES02 = 62	CES27 = 95	CES52 = 96	CES77 = 87
CES03 = 31	CES28 = 94	CES53 = 91	CES78 = 80
CES04 = 70	CES29 = 87	CES54 = 92	CES79 = 93
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 89	CES56 = 88	CES81 = 77
CES07 = 41	CES32 = 84	CES57 = 87	CES82 = 96
CES08 = 40	CES33 = 91	CES58 = 88	CES83 = 95
CES09 = 29	CES34 = 91	CES59 = 93	CES84 = 92
CES10 = 75	CES35 = 95	CES60 = 94	CES85 = 80
CES11 = 58	CES36 = 90	CES61 = 91	CES86 = 72
CES12 = 64	CES37 = 95	CES62 = 95	CES87 = 86
CES13 = 43	CES38 = 100	CES63 = 88	CES88 = 88
CES14 = 74	CES39 = 97	CES64 = 85	CES89 = 77
CES15 = 71	CES40 = 94	CES65 = 80	CES90 = 88
CES16 = 47	CES41 = 97	CES66 = 84	CES91 = 81
CES17 = 49	CES42 = 96	CES67 = 82	CES92 = 67
CES18 = 56	CES43 = 93	CES68 = 85	CES93 = 81
CES19 = 72	CES44 = 99	CES69 = 89	CES94 = 63
CES20 = 66	CES45 = 95	CES70 = 81	CES95 = 76
CES21 = 86	CES46 = 91	CES71 = 79	CES96 = 84
CES22 = 78	CES47 = 93	CES72 = 93	CES97 = 92
CES23 = 91	CES48 = 85	CES73 = 76	CES98 = 86
CES24 = 90	CES49 = 92	CES74 = 95	CES99 = 77
CES25 = 72	CES50 = 96	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)