

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P953471

Luminaire Tested: **GLAN-SB7A-735-U-SLL**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P953471
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB7A-735-U-SLL
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(7) 70 CRI, 3500K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 31787 lumens
Efficiency: N/A
Efficacy: 159.7 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5


Input Watts (W): 199.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P953471
 CATALOG NUMBER: GLAN-SB7A-735-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P953471
CATALOG NUMBER: GLAN-SB7A-735-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P953471
 CATALOG NUMBER: GLAN-SB7A-735-U-SLL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 8078.7 | 0.0 | 8078.7 |
| | % Fixture | 25.4 | 0.0 | 25.4 |
| Street Side | Lumens | 23708.3 | 0.0 | 23708.3 |
| | % Fixture | 74.6 | 0.0 | 74.6 |
| Total | Lumens | 31787.0 | 0.0 | 31787.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 433.6 | 1.4 |
| 10°-20° | 1361.2 | 4.3 |
| 20°-30° | 2102.5 | 6.6 |
| 30°-40° | 2664.4 | 8.4 |
| 40°-50° | 4018.6 | 12.6 |
| 50°-60° | 6492.7 | 20.4 |
| 60°-70° | 8094.1 | 25.5 |
| 70°-80° | 5307.7 | 16.7 |
| 80°-90° | 1312.2 | 4.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 31787.0 | 100.0 |
| 0°-180° | 31787.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P953471
 CATALOG NUMBER: GLAN-SB7A-735-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 2138.0 | 6.7 | | | |
| FM (30°-60°) | 9271.6 | 29.2 | | | |
| FH (60°-80°) | 11217.8 | 35.3 | | | G4/12000 |
| FVH (80°-90°) | 1081.0 | 3.4 | | | G5 |
| BL (0°-30°) | 1759.2 | 5.5 | B3/2500 | | |
| BM (30°-60°) | 3904.1 | 12.3 | B3/5000 | | |
| BH (60°-80°) | 2184.1 | 6.9 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 231.2 | 0.7 | | | G3/500 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G5

Type IV Short



REPORT NUMBER: P953471
 CATALOG NUMBER: GLAN-SB7A-735-U-SLL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 |
| 2.5° | 4700.6 | 4718.4 | 4736.3 | 4761.6 | 4787.0 | 4802.0 | 4817.1 | 4824.7 | 4832.2 | 4828.9 |
| 5° | 5054.5 | 5116.7 | 5179.1 | 5240.8 | 5302.7 | 5336.3 | 5369.8 | 5390.1 | 5410.6 | 5426.0 |
| 7.5° | 5410.1 | 5511.4 | 5612.5 | 5703.6 | 5794.7 | 5849.5 | 5904.4 | 5934.0 | 5963.6 | 5977.8 |
| 10° | 5682.6 | 5802.4 | 5922.1 | 6029.0 | 6135.8 | 6200.6 | 6265.0 | 6293.8 | 6322.5 | 6333.4 |
| 12.5° | 5849.5 | 5979.3 | 6109.0 | 6205.6 | 6301.9 | 6348.8 | 6395.8 | 6411.6 | 6427.3 | 6429.0 |
| 15° | 5951.0 | 6063.0 | 6174.9 | 6235.4 | 6296.2 | 6297.8 | 6299.5 | 6282.7 | 6266.0 | 6246.2 |
| 17.5° | 6008.0 | 6083.7 | 6159.3 | 6160.5 | 6161.5 | 6093.6 | 6025.6 | 5963.4 | 5901.0 | 5857.1 |
| 20° | 6070.9 | 6097.2 | 6123.7 | 6044.1 | 5964.4 | 5814.5 | 5664.5 | 5555.3 | 5446.1 | 5379.0 |
| 22.5° | 6143.9 | 6109.3 | 6074.8 | 5909.7 | 5744.7 | 5524.1 | 5303.6 | 5167.0 | 5030.5 | 4956.4 |
| 25° | 6237.8 | 6128.8 | 6019.8 | 5769.2 | 5518.6 | 5250.7 | 4982.9 | 4839.3 | 4696.0 | 4625.9 |
| 27.5° | 6365.3 | 6170.4 | 5975.3 | 5643.4 | 5311.6 | 5014.7 | 4717.8 | 4576.6 | 4435.6 | 4369.3 |
| 30° | 6537.2 | 6246.5 | 5956.0 | 5547.4 | 5138.8 | 4829.6 | 4520.3 | 4389.3 | 4258.3 | 4196.5 |
| 32.5° | 6740.1 | 6342.1 | 5944.3 | 5482.0 | 5019.8 | 4729.1 | 4438.4 | 4335.6 | 4232.6 | 4188.2 |
| 35° | 6986.7 | 6499.6 | 6012.7 | 5531.0 | 5049.4 | 4847.5 | 4645.7 | 4621.7 | 4597.8 | 4594.1 |
| 37.5° | 7401.8 | 6828.9 | 6255.9 | 5818.1 | 5380.4 | 5367.3 | 5354.2 | 5463.9 | 5573.6 | 5630.6 |
| 40° | 8029.1 | 7406.0 | 6782.9 | 6457.4 | 6131.8 | 6361.6 | 6591.4 | 6858.1 | 7124.7 | 7257.6 |
| 42.5° | 8861.1 | 8242.8 | 7624.6 | 7437.1 | 7249.5 | 7750.7 | 8251.9 | 8736.9 | 9222.0 | 9506.8 |
| 45° | 9888.4 | 9333.0 | 8777.5 | 8694.8 | 8612.0 | 9414.9 | 10218.0 | 11015.0 | 11812.2 | 12296.1 |
| 47.5° | 11173.2 | 10632.9 | 10092.5 | 10075.7 | 10059.0 | 11217.3 | 12375.3 | 13542.2 | 14708.9 | 15394.1 |
| 50° | 12857.2 | 12189.8 | 11522.6 | 11525.4 | 11528.3 | 13021.0 | 14513.8 | 16054.1 | 17594.3 | 18525.5 |
| 52.5° | 14790.2 | 13982.1 | 13174.2 | 13092.5 | 13010.6 | 14793.8 | 16576.9 | 18482.6 | 20388.2 | 21504.4 |
| 55° | 16848.3 | 16049.9 | 15251.5 | 14933.0 | 14614.5 | 16599.0 | 18583.4 | 20855.3 | 23127.1 | 24454.7 |
| 57.5° | 18720.1 | 18285.3 | 17850.4 | 17211.6 | 16572.8 | 18576.7 | 20580.5 | 23153.8 | 25726.9 | 27373.2 |
| 60° | 19851.4 | 20526.7 | 21202.1 | 20408.8 | 19615.4 | 21511.8 | 23408.1 | 26163.2 | 28918.3 | 30697.5 |
| 62.5° | 19277.0 | 21122.1 | 22967.3 | 22877.9 | 22788.3 | 24525.5 | 26262.8 | 28884.1 | 31505.1 | 33149.7 |
| 65° | 18127.2 | 19859.0 | 21590.8 | 21933.4 | 22275.9 | 24483.6 | 26691.4 | 29233.1 | 31774.7 | 33174.9 |
| 67.5° | 16586.6 | 18233.7 | 19880.8 | 20041.5 | 20202.0 | 22502.2 | 24802.2 | 27354.9 | 29907.5 | 31004.5 |
| 70° | 14735.7 | 16527.2 | 18318.9 | 18390.7 | 18462.6 | 20519.7 | 22576.5 | 24773.2 | 26969.8 | 27579.5 |
| 72.5° | 12530.1 | 14585.9 | 16642.0 | 16693.6 | 16745.1 | 18354.5 | 19963.8 | 21609.0 | 23254.1 | 23315.8 |
| 75° | 9740.0 | 11867.7 | 13995.5 | 14186.6 | 14377.6 | 15629.7 | 16881.8 | 18040.0 | 19198.1 | 18887.8 |
| 77.5° | 6959.0 | 8945.3 | 10931.7 | 11205.1 | 11478.5 | 12430.3 | 13382.2 | 14203.5 | 15025.1 | 14491.7 |
| 80° | 4554.6 | 6225.7 | 7896.6 | 8236.4 | 8576.3 | 9295.1 | 10013.7 | 10445.1 | 10876.3 | 10018.4 |
| 82.5° | 2647.6 | 3790.0 | 4932.5 | 5312.1 | 5691.8 | 6186.6 | 6681.4 | 6861.4 | 7041.2 | 6366.9 |
| 85° | 1164.9 | 1771.2 | 2377.5 | 2700.4 | 3023.3 | 3429.9 | 3836.3 | 3938.4 | 4040.6 | 3500.5 |
| 87.5° | 360.6 | 564.4 | 768.2 | 948.3 | 1128.5 | 1331.8 | 1535.0 | 1543.8 | 1552.3 | 1303.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P953471
 CATALOG NUMBER: GLAN-SB7A-735-U-SLL

CANDELA DISTRIBUTION (continued):

| 50° | | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 4371.0 | 0° | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 |
| 4832.2 | 2.5° | 4824.7 | 4817.1 | 4802.0 | 4787.0 | 4761.6 | 4736.3 | 4718.4 | 4700.6 | 4664.5 | 4628.4 |
| 5410.6 | 5° | 5390.1 | 5369.8 | 5336.3 | 5302.7 | 5240.8 | 5179.1 | 5116.7 | 5054.5 | 4974.8 | 4895.1 |
| 5963.6 | 7.5° | 5934.0 | 5904.4 | 5849.5 | 5794.7 | 5703.6 | 5612.5 | 5511.4 | 5410.1 | 5278.6 | 5147.2 |
| 6322.5 | 10° | 6293.8 | 6265.0 | 6200.6 | 6135.8 | 6029.0 | 5922.1 | 5802.4 | 5682.6 | 5516.4 | 5350.2 |
| 6427.3 | 12.5° | 6411.6 | 6395.8 | 6348.8 | 6301.9 | 6205.6 | 6109.0 | 5979.3 | 5849.5 | 5666.9 | 5484.4 |
| 6266.0 | 15° | 6282.7 | 6299.5 | 6297.8 | 6296.2 | 6235.4 | 6174.9 | 6063.0 | 5951.0 | 5760.6 | 5570.2 |
| 5901.0 | 17.5° | 5963.4 | 6025.6 | 6093.6 | 6161.5 | 6160.5 | 6159.3 | 6083.7 | 6008.0 | 5815.0 | 5621.9 |
| 5446.1 | 20° | 5555.3 | 5664.5 | 5814.5 | 5964.4 | 6044.1 | 6123.7 | 6097.2 | 6070.9 | 5870.3 | 5669.5 |
| 5030.5 | 22.5° | 5167.0 | 5303.6 | 5524.1 | 5744.7 | 5909.7 | 6074.8 | 6109.3 | 6143.9 | 5938.9 | 5733.8 |
| 4696.0 | 25° | 4839.3 | 4982.9 | 5250.7 | 5518.6 | 5769.2 | 6019.8 | 6128.8 | 6237.8 | 6036.9 | 5836.1 |
| 4435.6 | 27.5° | 4576.6 | 4717.8 | 5014.7 | 5311.6 | 5643.4 | 5975.3 | 6170.4 | 6365.3 | 6173.7 | 5982.0 |
| 4258.3 | 30° | 4389.3 | 4520.3 | 4829.6 | 5138.8 | 5547.4 | 5956.0 | 6246.5 | 6537.2 | 6352.0 | 6167.0 |
| 4232.6 | 32.5° | 4335.6 | 4438.4 | 4729.1 | 5019.8 | 5482.0 | 5944.3 | 6342.1 | 6740.1 | 6556.8 | 6373.7 |
| 4597.8 | 35° | 4621.7 | 4645.7 | 4847.5 | 5049.4 | 5531.0 | 6012.7 | 6499.6 | 6986.7 | 6811.3 | 6635.6 |
| 5573.6 | 37.5° | 5463.9 | 5354.2 | 5367.3 | 5380.4 | 5818.1 | 6255.9 | 6828.9 | 7401.8 | 7178.1 | 6954.3 |
| 7124.7 | 40° | 6858.1 | 6591.4 | 6361.6 | 6131.8 | 6457.4 | 6782.9 | 7406.0 | 8029.1 | 7703.1 | 7377.0 |
| 9222.0 | 42.5° | 8736.9 | 8251.9 | 7750.7 | 7249.5 | 7437.1 | 7624.6 | 8242.8 | 8861.1 | 8390.4 | 7919.8 |
| 11812.2 | 45° | 11015.0 | 10218.0 | 9414.9 | 8612.0 | 8694.8 | 8777.5 | 9333.0 | 9888.4 | 9253.5 | 8618.7 |
| 14708.9 | 47.5° | 13542.2 | 12375.3 | 11217.3 | 10059.0 | 10075.7 | 10092.5 | 10632.9 | 11173.2 | 10279.7 | 9386.0 |
| 17594.3 | 50° | 16054.1 | 14513.8 | 13021.0 | 11528.3 | 11525.4 | 11522.6 | 12189.8 | 12857.2 | 11510.2 | 10163.0 |
| 20388.2 | 52.5° | 18482.6 | 16576.9 | 14793.8 | 13010.6 | 13092.5 | 13174.2 | 13982.1 | 14790.2 | 12802.7 | 10815.1 |
| 23127.1 | 55° | 20855.3 | 18583.4 | 16599.0 | 14614.5 | 14933.0 | 15251.5 | 16049.9 | 16848.3 | 13948.6 | 11049.1 |
| 25726.9 | 57.5° | 23153.8 | 20580.5 | 18576.7 | 16572.8 | 17211.6 | 17850.4 | 18285.3 | 18720.1 | 14760.7 | 10801.3 |
| 28918.3 | 60° | 26163.2 | 23408.1 | 21511.8 | 19615.4 | 20408.8 | 21202.1 | 20526.7 | 19851.4 | 14963.7 | 10075.7 |
| 31505.1 | 62.5° | 28884.1 | 26262.8 | 24525.5 | 22788.3 | 22877.9 | 22967.3 | 21122.1 | 19277.0 | 14109.1 | 8941.2 |
| 31774.7 | 65° | 29233.1 | 26691.4 | 24483.6 | 22275.9 | 21933.4 | 21590.8 | 19859.0 | 18127.2 | 12899.9 | 7672.7 |
| 29907.5 | 67.5° | 27354.9 | 24802.2 | 22502.2 | 20202.0 | 20041.5 | 19880.8 | 18233.7 | 16586.6 | 11461.0 | 6335.4 |
| 26969.8 | 70° | 24773.2 | 22576.5 | 20519.7 | 18462.6 | 18390.7 | 18318.9 | 16527.2 | 14735.7 | 9890.9 | 5046.1 |
| 23254.1 | 72.5° | 21609.0 | 19963.8 | 18354.5 | 16745.1 | 16693.6 | 16642.0 | 14585.9 | 12530.1 | 8188.8 | 3847.7 |
| 19198.1 | 75° | 18040.0 | 16881.8 | 15629.7 | 14377.6 | 14186.6 | 13995.5 | 11867.7 | 9740.0 | 6237.6 | 2735.3 |
| 15025.1 | 77.5° | 14203.5 | 13382.2 | 12430.3 | 11478.5 | 11205.1 | 10931.7 | 8945.3 | 6959.0 | 4365.8 | 1772.5 |
| 10876.3 | 80° | 10445.1 | 10013.7 | 9295.1 | 8576.3 | 8236.4 | 7896.6 | 6225.7 | 4554.6 | 2812.8 | 1070.9 |
| 7041.2 | 82.5° | 6861.4 | 6681.4 | 6186.6 | 5691.8 | 5312.1 | 4932.5 | 3790.0 | 2647.6 | 1628.0 | 608.5 |
| 4040.6 | 85° | 3938.4 | 3836.3 | 3429.9 | 3023.3 | 2700.4 | 2377.5 | 1771.2 | 1164.9 | 732.3 | 299.9 |
| 1552.3 | 87.5° | 1543.8 | 1535.0 | 1331.8 | 1128.5 | 948.3 | 768.2 | 564.4 | 360.6 | 239.9 | 119.1 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P953471
 CATALOG NUMBER: GLAN-SB7A-735-U-SLL

CANDELA DISTRIBUTION (continued):

| 105° | | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4371.0 | 0° | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 |
| 4590.0 | 2.5° | 4551.8 | 4513.2 | 4474.6 | 4437.7 | 4400.8 | 4365.1 | 4325.4 | 4293.2 | 4261.1 | 4232.1 |
| 4815.6 | 5° | 4736.3 | 4656.3 | 4576.5 | 4501.8 | 4427.2 | 4356.7 | 4287.1 | 4226.4 | 4165.5 | 4114.5 |
| 5025.8 | 7.5° | 4904.4 | 4786.1 | 4667.9 | 4563.7 | 4459.5 | 4363.4 | 4273.4 | 4192.5 | 4111.8 | 4044.8 |
| 5189.7 | 10° | 5029.3 | 4885.7 | 4742.0 | 4618.9 | 4495.4 | 4376.9 | 4280.1 | 4194.9 | 4109.7 | 4042.6 |
| 5302.5 | 12.5° | 5120.7 | 4951.3 | 4781.9 | 4642.5 | 4503.2 | 4378.5 | 4288.5 | 4218.7 | 4149.3 | 4104.6 |
| 5373.0 | 15° | 5175.7 | 4980.7 | 4785.6 | 4624.3 | 4462.9 | 4324.9 | 4252.7 | 4219.4 | 4186.2 | 4192.2 |
| 5406.7 | 17.5° | 5191.5 | 4965.1 | 4738.6 | 4544.6 | 4350.5 | 4188.2 | 4143.7 | 4156.0 | 4168.0 | 4241.2 |
| 5433.0 | 20° | 5196.5 | 4922.1 | 4647.7 | 4407.2 | 4166.7 | 3977.7 | 3965.9 | 4023.0 | 4080.0 | 4206.9 |
| 5468.6 | 22.5° | 5203.3 | 4869.5 | 4535.7 | 4246.0 | 3956.4 | 3741.2 | 3764.1 | 3848.5 | 3932.9 | 4077.8 |
| 5533.0 | 25° | 5229.8 | 4817.5 | 4405.4 | 4066.1 | 3726.9 | 3506.3 | 3568.4 | 3665.7 | 3763.0 | 3893.3 |
| 5633.6 | 27.5° | 5285.1 | 4782.8 | 4280.4 | 3901.5 | 3522.6 | 3321.8 | 3397.3 | 3491.3 | 3585.2 | 3692.4 |
| 5764.0 | 30° | 5360.9 | 4766.5 | 4171.7 | 3764.0 | 3356.2 | 3187.7 | 3246.9 | 3321.3 | 3396.2 | 3485.0 |
| 5900.0 | 32.5° | 5426.3 | 4746.4 | 4066.1 | 3645.4 | 3224.6 | 3088.7 | 3115.0 | 3159.2 | 3203.3 | 3274.2 |
| 6055.0 | 35° | 5474.3 | 4708.5 | 3942.9 | 3528.8 | 3114.7 | 3001.5 | 2990.6 | 3002.7 | 3014.9 | 3069.1 |
| 6228.6 | 37.5° | 5502.8 | 4643.5 | 3784.3 | 3391.6 | 2999.0 | 2900.0 | 2860.1 | 2846.7 | 2833.3 | 2872.2 |
| 6449.0 | 40° | 5520.8 | 4554.1 | 3587.7 | 3227.9 | 2868.1 | 2778.4 | 2717.2 | 2686.8 | 2656.5 | 2684.5 |
| 6737.3 | 42.5° | 5554.8 | 4461.9 | 3369.3 | 3047.3 | 2725.2 | 2642.6 | 2565.4 | 2525.1 | 2484.9 | 2507.7 |
| 7116.7 | 45° | 5614.7 | 4376.2 | 3137.9 | 2855.4 | 2572.9 | 2489.1 | 2414.4 | 2375.2 | 2336.1 | 2355.2 |
| 7520.9 | 47.5° | 5655.8 | 4305.4 | 2955.0 | 2703.6 | 2452.2 | 2344.0 | 2279.8 | 2246.9 | 2214.0 | 2232.1 |
| 7896.0 | 50° | 5628.9 | 4228.2 | 2827.6 | 2602.8 | 2378.0 | 2235.8 | 2161.2 | 2132.0 | 2103.0 | 2131.1 |
| 8139.5 | 52.5° | 5463.7 | 4097.9 | 2732.3 | 2536.4 | 2340.6 | 2177.1 | 2072.8 | 2043.9 | 2015.2 | 2057.7 |
| 8085.8 | 55° | 5122.4 | 3881.9 | 2641.4 | 2488.2 | 2335.1 | 2183.0 | 2025.8 | 1980.2 | 1934.7 | 1995.0 |
| 7708.1 | 57.5° | 4615.0 | 3577.3 | 2539.4 | 2431.2 | 2323.0 | 2188.8 | 1997.6 | 1931.2 | 1864.8 | 1929.5 |
| 7005.2 | 60° | 3934.6 | 3181.8 | 2429.0 | 2344.0 | 2259.0 | 2170.4 | 1971.1 | 1885.1 | 1798.9 | 1855.7 |
| 6054.6 | 62.5° | 3168.0 | 2708.5 | 2248.9 | 2192.4 | 2136.0 | 2125.1 | 1940.3 | 1832.6 | 1725.1 | 1761.1 |
| 5084.8 | 65° | 2497.1 | 2282.6 | 2068.1 | 2041.4 | 2014.7 | 2016.1 | 1875.2 | 1760.8 | 1646.2 | 1660.2 |
| 4134.8 | 67.5° | 1934.2 | 1873.4 | 1812.3 | 1827.2 | 1842.0 | 1838.3 | 1759.1 | 1663.9 | 1568.6 | 1564.2 |
| 3255.6 | 70° | 1465.1 | 1482.5 | 1499.8 | 1568.9 | 1637.9 | 1637.9 | 1611.9 | 1544.1 | 1476.3 | 1461.2 |
| 2488.9 | 72.5° | 1130.1 | 1182.6 | 1235.3 | 1333.3 | 1431.1 | 1447.5 | 1447.8 | 1401.4 | 1354.9 | 1332.8 |
| 1806.4 | 75° | 877.6 | 925.2 | 972.8 | 1082.5 | 1192.2 | 1268.0 | 1261.6 | 1225.9 | 1190.0 | 1168.9 |
| 1224.1 | 77.5° | 675.6 | 708.0 | 740.5 | 847.0 | 953.5 | 1078.5 | 1075.1 | 1046.5 | 1017.8 | 996.3 |
| 788.7 | 80° | 506.5 | 520.0 | 533.4 | 623.6 | 713.7 | 863.0 | 862.5 | 838.5 | 814.3 | 796.4 |
| 485.1 | 82.5° | 362.0 | 364.3 | 367.0 | 433.4 | 499.8 | 627.3 | 634.3 | 622.6 | 610.9 | 598.1 |
| 259.3 | 85° | 218.9 | 217.7 | 216.4 | 265.0 | 313.7 | 408.4 | 417.6 | 405.1 | 392.5 | 378.2 |
| 107.5 | 87.5° | 95.9 | 94.8 | 93.6 | 113.4 | 133.3 | 172.8 | 184.5 | 179.5 | 174.4 | 171.8 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P953471
 CATALOG NUMBER: GLAN-SB7A-735-U-SLL

CANDELA DISTRIBUTION (continued):

| 160° | | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4371.0 | 0° | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 |
| 4203.3 | 2.5° | 4177.9 | 4152.6 | 4127.1 | 4101.8 | 4082.2 | 4062.4 | 4046.4 | 4030.5 | 4018.1 | 4005.7 |
| 4063.7 | 5° | 4018.8 | 3973.8 | 3933.0 | 3892.1 | 3860.8 | 3829.2 | 3807.3 | 3785.3 | 3769.7 | 3754.1 |
| 3977.7 | 7.5° | 3921.1 | 3864.4 | 3814.5 | 3764.7 | 3727.2 | 3690.0 | 3663.8 | 3637.7 | 3619.7 | 3602.0 |
| 3975.5 | 10° | 3914.6 | 3853.5 | 3797.4 | 3741.2 | 3696.6 | 3651.8 | 3622.6 | 3593.1 | 3576.1 | 3559.2 |
| 4060.4 | 12.5° | 4012.4 | 3964.7 | 3906.5 | 3848.5 | 3791.5 | 3734.5 | 3696.7 | 3659.0 | 3640.0 | 3621.2 |
| 4198.2 | 15° | 4185.8 | 4173.4 | 4122.9 | 4072.4 | 3991.3 | 3910.1 | 3852.7 | 3795.3 | 3769.0 | 3742.8 |
| 4314.3 | 17.5° | 4353.2 | 4392.0 | 4351.2 | 4310.6 | 4203.1 | 4095.6 | 4011.0 | 3926.5 | 3887.6 | 3848.5 |
| 4334.1 | 20° | 4415.4 | 4496.8 | 4478.0 | 4459.0 | 4336.1 | 4213.3 | 4109.7 | 4006.2 | 3956.4 | 3906.4 |
| 4223.1 | 22.5° | 4328.9 | 4434.7 | 4446.1 | 4457.4 | 4340.0 | 4222.5 | 4115.9 | 4009.0 | 3956.5 | 3903.9 |
| 4023.8 | 25° | 4127.9 | 4232.1 | 4271.0 | 4309.8 | 4213.5 | 4117.4 | 4022.4 | 3927.8 | 3882.2 | 3836.8 |
| 3799.4 | 27.5° | 3882.9 | 3966.4 | 4009.7 | 4053.1 | 3984.5 | 3916.1 | 3842.5 | 3768.8 | 3738.3 | 3707.6 |
| 3573.9 | 30° | 3643.2 | 3712.7 | 3747.9 | 3783.1 | 3730.9 | 3678.6 | 3625.9 | 3572.9 | 3557.3 | 3541.6 |
| 3345.3 | 32.5° | 3411.8 | 3478.3 | 3517.4 | 3556.7 | 3508.7 | 3460.6 | 3418.5 | 3376.4 | 3366.1 | 3355.9 |
| 3123.1 | 35° | 3188.8 | 3254.8 | 3301.7 | 3348.7 | 3314.5 | 3280.4 | 3241.5 | 3202.8 | 3187.2 | 3171.7 |
| 2910.9 | 37.5° | 2976.5 | 3042.2 | 3100.3 | 3158.3 | 3142.5 | 3126.8 | 3091.1 | 3055.2 | 3026.8 | 2998.6 |
| 2712.5 | 40° | 2775.9 | 2839.3 | 2906.1 | 2973.0 | 2976.8 | 2980.5 | 2950.2 | 2919.8 | 2878.5 | 2837.6 |
| 2530.7 | 42.5° | 2590.7 | 2650.9 | 2723.1 | 2795.2 | 2814.5 | 2833.8 | 2808.1 | 2782.6 | 2731.4 | 2680.3 |
| 2374.7 | 45° | 2431.7 | 2488.7 | 2563.6 | 2638.4 | 2666.0 | 2693.7 | 2670.6 | 2647.6 | 2589.0 | 2530.7 |
| 2250.1 | 47.5° | 2305.9 | 2361.6 | 2435.4 | 2509.2 | 2541.1 | 2572.9 | 2556.8 | 2540.7 | 2488.7 | 2436.7 |
| 2159.5 | 50° | 2212.2 | 2264.7 | 2330.7 | 2396.8 | 2437.8 | 2478.7 | 2477.7 | 2477.0 | 2435.4 | 2393.8 |
| 2100.0 | 52.5° | 2148.3 | 2196.4 | 2258.0 | 2319.7 | 2368.1 | 2416.6 | 2425.3 | 2434.1 | 2400.2 | 2366.3 |
| 2055.0 | 55° | 2107.0 | 2159.0 | 2213.0 | 2266.8 | 2318.2 | 2369.7 | 2381.7 | 2393.8 | 2364.3 | 2334.8 |
| 1994.3 | 57.5° | 2055.3 | 2116.4 | 2169.7 | 2223.2 | 2275.1 | 2326.7 | 2339.0 | 2351.2 | 2321.4 | 2291.5 |
| 1912.4 | 60° | 1982.5 | 2052.7 | 2106.8 | 2161.2 | 2213.2 | 2265.2 | 2278.6 | 2292.0 | 2262.8 | 2233.8 |
| 1797.2 | 62.5° | 1878.9 | 1960.7 | 2018.6 | 2076.5 | 2124.1 | 2171.7 | 2184.7 | 2197.6 | 2171.2 | 2144.9 |
| 1673.9 | 65° | 1761.5 | 1849.2 | 1904.5 | 1959.9 | 2001.8 | 2043.8 | 2057.0 | 2070.1 | 2044.8 | 2019.4 |
| 1559.9 | 67.5° | 1640.7 | 1721.7 | 1774.2 | 1826.6 | 1862.8 | 1899.0 | 1911.9 | 1924.7 | 1901.4 | 1878.2 |
| 1446.1 | 70° | 1517.3 | 1588.4 | 1633.7 | 1679.0 | 1711.7 | 1744.4 | 1756.8 | 1769.2 | 1750.2 | 1731.3 |
| 1310.8 | 72.5° | 1366.8 | 1422.7 | 1463.6 | 1504.5 | 1536.6 | 1568.6 | 1583.4 | 1598.1 | 1582.3 | 1566.6 |
| 1147.6 | 75° | 1189.2 | 1230.8 | 1267.9 | 1304.9 | 1334.1 | 1363.3 | 1378.7 | 1394.2 | 1386.4 | 1378.7 |
| 974.8 | 77.5° | 1008.7 | 1042.4 | 1074.3 | 1106.2 | 1136.9 | 1167.4 | 1181.8 | 1196.2 | 1185.5 | 1174.4 |
| 778.3 | 80° | 806.4 | 834.4 | 861.3 | 888.1 | 911.4 | 934.6 | 953.7 | 972.8 | 968.1 | 963.6 |
| 585.4 | 82.5° | 583.0 | 580.7 | 571.3 | 561.9 | 611.5 | 661.2 | 693.7 | 726.3 | 724.2 | 722.1 |
| 364.0 | 85° | 351.9 | 339.6 | 313.7 | 287.7 | 334.1 | 380.7 | 421.0 | 461.3 | 457.9 | 454.5 |
| 169.1 | 87.5° | 168.6 | 168.1 | 148.3 | 128.3 | 147.8 | 167.4 | 183.7 | 199.9 | 195.9 | 191.5 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P953471
 CATALOG NUMBER: GLAN-SB7A-735-U-SLL

CANDELA DISTRIBUTION (continued):

| 215° | | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4371.0 | 0° | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 |
| 3994.3 | 2.5° | 3982.7 | 3968.4 | 3982.7 | 3994.3 | 4005.7 | 4018.1 | 4030.5 | 4046.4 | 4062.4 | 4082.2 |
| 3742.2 | 5° | 3730.3 | 3718.5 | 3730.3 | 3742.2 | 3754.1 | 3769.7 | 3785.3 | 3807.3 | 3829.2 | 3860.8 |
| 3591.2 | 7.5° | 3580.7 | 3572.6 | 3580.7 | 3591.2 | 3602.0 | 3619.7 | 3637.7 | 3663.8 | 3690.0 | 3727.2 |
| 3550.1 | 10° | 3541.1 | 3537.4 | 3541.1 | 3550.1 | 3559.2 | 3576.1 | 3593.1 | 3622.6 | 3651.8 | 3696.6 |
| 3613.5 | 12.5° | 3605.8 | 3604.5 | 3605.8 | 3613.5 | 3621.2 | 3640.0 | 3659.0 | 3696.7 | 3734.5 | 3791.5 |
| 3732.8 | 15° | 3722.7 | 3721.9 | 3722.7 | 3732.8 | 3742.8 | 3769.0 | 3795.3 | 3852.7 | 3910.1 | 3991.3 |
| 3835.8 | 17.5° | 3822.9 | 3820.8 | 3822.9 | 3835.8 | 3848.5 | 3887.6 | 3926.5 | 4011.0 | 4095.6 | 4203.1 |
| 3890.4 | 20° | 3874.5 | 3869.5 | 3874.5 | 3890.4 | 3906.4 | 3956.4 | 4006.2 | 4109.7 | 4213.3 | 4336.1 |
| 3886.3 | 22.5° | 3868.6 | 3861.1 | 3868.6 | 3886.3 | 3903.9 | 3956.5 | 4009.0 | 4115.9 | 4222.5 | 4340.0 |
| 3820.2 | 25° | 3803.7 | 3794.0 | 3803.7 | 3820.2 | 3836.8 | 3882.2 | 3927.8 | 4022.4 | 4117.4 | 4213.5 |
| 3700.1 | 27.5° | 3692.5 | 3690.0 | 3692.5 | 3700.1 | 3707.6 | 3738.3 | 3768.8 | 3842.5 | 3916.1 | 3984.5 |
| 3541.6 | 30° | 3541.6 | 3544.1 | 3541.6 | 3541.6 | 3541.6 | 3557.3 | 3572.9 | 3625.9 | 3678.6 | 3730.9 |
| 3357.2 | 32.5° | 3358.7 | 3361.3 | 3358.7 | 3357.2 | 3355.9 | 3366.1 | 3376.4 | 3418.5 | 3460.6 | 3508.7 |
| 3168.4 | 35° | 3165.0 | 3163.3 | 3165.0 | 3168.4 | 3171.7 | 3187.2 | 3202.8 | 3241.5 | 3280.4 | 3314.5 |
| 2983.7 | 37.5° | 2968.8 | 2960.4 | 2968.8 | 2983.7 | 2998.6 | 3026.8 | 3055.2 | 3091.1 | 3126.8 | 3142.5 |
| 2809.8 | 40° | 2782.3 | 2765.8 | 2782.3 | 2809.8 | 2837.6 | 2878.5 | 2919.8 | 2950.2 | 2980.5 | 2976.8 |
| 2639.9 | 42.5° | 2599.4 | 2572.9 | 2599.4 | 2639.9 | 2680.3 | 2731.4 | 2782.6 | 2808.1 | 2833.8 | 2814.5 |
| 2483.2 | 45° | 2435.7 | 2405.2 | 2435.7 | 2483.2 | 2530.7 | 2589.0 | 2647.6 | 2670.6 | 2693.7 | 2666.0 |
| 2392.8 | 47.5° | 2349.0 | 2319.7 | 2349.0 | 2392.8 | 2436.7 | 2488.7 | 2540.7 | 2556.8 | 2572.9 | 2541.1 |
| 2353.2 | 50° | 2312.6 | 2284.5 | 2312.6 | 2353.2 | 2393.8 | 2435.4 | 2477.0 | 2477.7 | 2478.7 | 2437.8 |
| 2329.9 | 52.5° | 2293.7 | 2267.7 | 2293.7 | 2329.9 | 2366.3 | 2400.2 | 2434.1 | 2425.3 | 2416.6 | 2368.1 |
| 2302.9 | 55° | 2271.0 | 2247.6 | 2271.0 | 2302.9 | 2334.8 | 2364.3 | 2393.8 | 2381.7 | 2369.7 | 2318.2 |
| 2260.0 | 57.5° | 2228.3 | 2203.9 | 2228.3 | 2260.0 | 2291.5 | 2321.4 | 2351.2 | 2339.0 | 2326.7 | 2275.1 |
| 2201.3 | 60° | 2168.7 | 2143.6 | 2168.7 | 2201.3 | 2233.8 | 2262.8 | 2292.0 | 2278.6 | 2265.2 | 2213.2 |
| 2110.7 | 62.5° | 2076.5 | 2046.3 | 2076.5 | 2110.7 | 2144.9 | 2171.2 | 2197.6 | 2184.7 | 2171.7 | 2124.1 |
| 1986.2 | 65° | 1953.2 | 1927.2 | 1953.2 | 1986.2 | 2019.4 | 2044.8 | 2070.1 | 2057.0 | 2043.8 | 2001.8 |
| 1847.4 | 67.5° | 1816.5 | 1793.0 | 1816.5 | 1847.4 | 1878.2 | 1901.4 | 1924.7 | 1911.9 | 1899.0 | 1862.8 |
| 1701.8 | 70° | 1672.2 | 1645.4 | 1672.2 | 1701.8 | 1731.3 | 1750.2 | 1769.2 | 1756.8 | 1744.4 | 1711.7 |
| 1538.4 | 72.5° | 1510.4 | 1484.4 | 1510.4 | 1538.4 | 1566.6 | 1582.3 | 1598.1 | 1583.4 | 1568.6 | 1536.6 |
| 1355.1 | 75° | 1331.4 | 1306.6 | 1331.4 | 1355.1 | 1378.7 | 1386.4 | 1394.2 | 1378.7 | 1363.3 | 1334.1 |
| 1150.6 | 77.5° | 1126.8 | 1107.0 | 1126.8 | 1150.6 | 1174.4 | 1185.5 | 1196.2 | 1181.8 | 1167.4 | 1136.9 |
| 931.6 | 80° | 899.4 | 862.1 | 899.4 | 931.6 | 963.6 | 968.1 | 972.8 | 953.7 | 934.6 | 911.4 |
| 695.1 | 82.5° | 667.9 | 644.1 | 667.9 | 695.1 | 722.1 | 724.2 | 726.3 | 693.7 | 661.2 | 611.5 |
| 433.4 | 85° | 412.3 | 390.8 | 412.3 | 433.4 | 454.5 | 457.9 | 461.3 | 421.0 | 380.7 | 334.1 |
| 180.8 | 87.5° | 169.7 | 159.3 | 169.7 | 180.8 | 191.5 | 195.9 | 199.9 | 183.7 | 167.4 | 147.8 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P953471
 CATALOG NUMBER: GLAN-SB7A-735-U-SLL

CANDELA DISTRIBUTION (continued):

| 270° | | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4371.0 | 0° | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 |
| 4101.8 | 2.5° | 4127.1 | 4152.6 | 4177.9 | 4203.3 | 4232.1 | 4261.1 | 4293.2 | 4325.4 | 4365.1 | 4400.8 |
| 3892.1 | 5° | 3933.0 | 3973.8 | 4018.8 | 4063.7 | 4114.5 | 4165.5 | 4226.4 | 4287.1 | 4356.7 | 4427.2 |
| 3764.7 | 7.5° | 3814.5 | 3864.4 | 3921.1 | 3977.7 | 4044.8 | 4111.8 | 4192.5 | 4273.4 | 4363.4 | 4459.5 |
| 3741.2 | 10° | 3797.4 | 3853.5 | 3914.6 | 3975.5 | 4042.6 | 4109.7 | 4194.9 | 4280.1 | 4376.9 | 4495.4 |
| 3848.5 | 12.5° | 3906.5 | 3964.7 | 4012.4 | 4060.4 | 4104.6 | 4149.3 | 4218.7 | 4288.5 | 4378.5 | 4503.2 |
| 4072.4 | 15° | 4122.9 | 4173.4 | 4185.8 | 4198.2 | 4192.2 | 4186.2 | 4219.4 | 4252.7 | 4324.9 | 4462.9 |
| 4310.6 | 17.5° | 4351.2 | 4392.0 | 4353.2 | 4314.3 | 4241.2 | 4168.0 | 4156.0 | 4143.7 | 4188.2 | 4350.5 |
| 4459.0 | 20° | 4478.0 | 4496.8 | 4415.4 | 4334.1 | 4206.9 | 4080.0 | 4023.0 | 3965.9 | 3977.7 | 4166.7 |
| 4457.4 | 22.5° | 4446.1 | 4434.7 | 4328.9 | 4223.1 | 4077.8 | 3932.9 | 3848.5 | 3764.1 | 3741.2 | 3956.4 |
| 4309.8 | 25° | 4271.0 | 4232.1 | 4127.9 | 4023.8 | 3893.3 | 3763.0 | 3665.7 | 3568.4 | 3506.3 | 3726.9 |
| 4053.1 | 27.5° | 4009.7 | 3966.4 | 3882.9 | 3799.4 | 3692.4 | 3585.2 | 3491.3 | 3397.3 | 3321.8 | 3522.6 |
| 3783.1 | 30° | 3747.9 | 3712.7 | 3643.2 | 3573.9 | 3485.0 | 3396.2 | 3321.3 | 3246.9 | 3187.7 | 3356.2 |
| 3556.7 | 32.5° | 3517.4 | 3478.3 | 3411.8 | 3345.3 | 3274.2 | 3203.3 | 3159.2 | 3115.0 | 3088.7 | 3224.6 |
| 3348.7 | 35° | 3301.7 | 3254.8 | 3188.8 | 3123.1 | 3069.1 | 3014.9 | 3002.7 | 2990.6 | 3001.5 | 3114.7 |
| 3158.3 | 37.5° | 3100.3 | 3042.2 | 2976.5 | 2910.9 | 2872.2 | 2833.3 | 2846.7 | 2860.1 | 2900.0 | 2999.0 |
| 2973.0 | 40° | 2906.1 | 2839.3 | 2775.9 | 2712.5 | 2684.5 | 2656.5 | 2686.8 | 2717.2 | 2778.4 | 2868.1 |
| 2795.2 | 42.5° | 2723.1 | 2650.9 | 2590.7 | 2530.7 | 2507.7 | 2484.9 | 2525.1 | 2565.4 | 2642.6 | 2725.2 |
| 2638.4 | 45° | 2563.6 | 2488.7 | 2431.7 | 2374.7 | 2355.2 | 2336.1 | 2375.2 | 2414.4 | 2489.1 | 2572.9 |
| 2509.2 | 47.5° | 2435.4 | 2361.6 | 2305.9 | 2250.1 | 2232.1 | 2214.0 | 2246.9 | 2279.8 | 2344.0 | 2452.2 |
| 2396.8 | 50° | 2330.7 | 2264.7 | 2212.2 | 2159.5 | 2131.1 | 2103.0 | 2132.0 | 2161.2 | 2235.8 | 2378.0 |
| 2319.7 | 52.5° | 2258.0 | 2196.4 | 2148.3 | 2100.0 | 2057.7 | 2015.2 | 2043.9 | 2072.8 | 2177.1 | 2340.6 |
| 2266.8 | 55° | 2213.0 | 2159.0 | 2107.0 | 2055.0 | 1995.0 | 1934.7 | 1980.2 | 2025.8 | 2183.0 | 2335.1 |
| 2223.2 | 57.5° | 2169.7 | 2116.4 | 2055.3 | 1994.3 | 1929.5 | 1864.8 | 1931.2 | 1997.6 | 2188.8 | 2323.0 |
| 2161.2 | 60° | 2106.8 | 2052.7 | 1982.5 | 1912.4 | 1855.7 | 1798.9 | 1885.1 | 1971.1 | 2170.4 | 2259.0 |
| 2076.5 | 62.5° | 2018.6 | 1960.7 | 1878.9 | 1797.2 | 1761.1 | 1725.1 | 1832.6 | 1940.3 | 2125.1 | 2136.0 |
| 1959.9 | 65° | 1904.5 | 1849.2 | 1761.5 | 1673.9 | 1660.2 | 1646.2 | 1760.8 | 1875.2 | 2016.1 | 2014.7 |
| 1826.6 | 67.5° | 1774.2 | 1721.7 | 1640.7 | 1559.9 | 1564.2 | 1568.6 | 1663.9 | 1759.1 | 1838.3 | 1842.0 |
| 1679.0 | 70° | 1633.7 | 1588.4 | 1517.3 | 1446.1 | 1461.2 | 1476.3 | 1544.1 | 1611.9 | 1637.9 | 1637.9 |
| 1504.5 | 72.5° | 1463.6 | 1422.7 | 1366.8 | 1310.8 | 1332.8 | 1354.9 | 1401.4 | 1447.8 | 1447.5 | 1431.1 |
| 1304.9 | 75° | 1267.9 | 1230.8 | 1189.2 | 1147.6 | 1168.9 | 1190.0 | 1225.9 | 1261.6 | 1268.0 | 1192.2 |
| 1106.2 | 77.5° | 1074.3 | 1042.4 | 1008.7 | 974.8 | 996.3 | 1017.8 | 1046.5 | 1075.1 | 1078.5 | 953.5 |
| 888.1 | 80° | 861.3 | 834.4 | 806.4 | 778.3 | 796.4 | 814.3 | 838.5 | 862.5 | 863.0 | 713.7 |
| 561.9 | 82.5° | 571.3 | 580.7 | 583.0 | 585.4 | 598.1 | 610.9 | 622.6 | 634.3 | 627.3 | 499.8 |
| 287.7 | 85° | 313.7 | 339.6 | 351.9 | 364.0 | 378.2 | 392.5 | 405.1 | 417.6 | 408.4 | 313.7 |
| 128.3 | 87.5° | 148.3 | 168.1 | 168.6 | 169.1 | 171.8 | 174.4 | 179.5 | 184.5 | 172.8 | 133.3 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P953471
 CATALOG NUMBER: GLAN-SB7A-735-U-SLL

CANDELA DISTRIBUTION (continued):

| 325° | | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|-------|--------|--------|--------|--------|---------|---------|---------|
| 4371.0 | 0° | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 | 4371.0 |
| 4437.7 | 2.5° | 4474.6 | 4513.2 | 4551.8 | 4590.0 | 4628.4 | 4664.5 | 4700.6 |
| 4501.8 | 5° | 4576.5 | 4656.3 | 4736.3 | 4815.6 | 4895.1 | 4974.8 | 5054.5 |
| 4563.7 | 7.5° | 4667.9 | 4786.1 | 4904.4 | 5025.8 | 5147.2 | 5278.6 | 5410.1 |
| 4618.9 | 10° | 4742.0 | 4885.7 | 5029.3 | 5189.7 | 5350.2 | 5516.4 | 5682.6 |
| 4642.5 | 12.5° | 4781.9 | 4951.3 | 5120.7 | 5302.5 | 5484.4 | 5666.9 | 5849.5 |
| 4624.3 | 15° | 4785.6 | 4980.7 | 5175.7 | 5373.0 | 5570.2 | 5760.6 | 5951.0 |
| 4544.6 | 17.5° | 4738.6 | 4965.1 | 5191.5 | 5406.7 | 5621.9 | 5815.0 | 6008.0 |
| 4407.2 | 20° | 4647.7 | 4922.1 | 5196.5 | 5433.0 | 5669.5 | 5870.3 | 6070.9 |
| 4246.0 | 22.5° | 4535.7 | 4869.5 | 5203.3 | 5468.6 | 5733.8 | 5938.9 | 6143.9 |
| 4066.1 | 25° | 4405.4 | 4817.5 | 5229.8 | 5533.0 | 5836.1 | 6036.9 | 6237.8 |
| 3901.5 | 27.5° | 4280.4 | 4782.8 | 5285.1 | 5633.6 | 5982.0 | 6173.7 | 6365.3 |
| 3764.0 | 30° | 4171.7 | 4766.5 | 5360.9 | 5764.0 | 6167.0 | 6352.0 | 6537.2 |
| 3645.4 | 32.5° | 4066.1 | 4746.4 | 5426.3 | 5900.0 | 6373.7 | 6556.8 | 6740.1 |
| 3528.8 | 35° | 3942.9 | 4708.5 | 5474.3 | 6055.0 | 6635.6 | 6811.3 | 6986.7 |
| 3391.6 | 37.5° | 3784.3 | 4643.5 | 5502.8 | 6228.6 | 6954.3 | 7178.1 | 7401.8 |
| 3227.9 | 40° | 3587.7 | 4554.1 | 5520.8 | 6449.0 | 7377.0 | 7703.1 | 8029.1 |
| 3047.3 | 42.5° | 3369.3 | 4461.9 | 5554.8 | 6737.3 | 7919.8 | 8390.4 | 8861.1 |
| 2855.4 | 45° | 3137.9 | 4376.2 | 5614.7 | 7116.7 | 8618.7 | 9253.5 | 9888.4 |
| 2703.6 | 47.5° | 2955.0 | 4305.4 | 5655.8 | 7520.9 | 9386.0 | 10279.7 | 11173.2 |
| 2602.8 | 50° | 2827.6 | 4228.2 | 5628.9 | 7896.0 | 10163.0 | 11510.2 | 12857.2 |
| 2536.4 | 52.5° | 2732.3 | 4097.9 | 5463.7 | 8139.5 | 10815.1 | 12802.7 | 14790.2 |
| 2488.2 | 55° | 2641.4 | 3881.9 | 5122.4 | 8085.8 | 11049.1 | 13948.6 | 16848.3 |
| 2431.2 | 57.5° | 2539.4 | 3577.3 | 4615.0 | 7708.1 | 10801.3 | 14760.7 | 18720.1 |
| 2344.0 | 60° | 2429.0 | 3181.8 | 3934.6 | 7005.2 | 10075.7 | 14963.7 | 19851.4 |
| 2192.4 | 62.5° | 2248.9 | 2708.5 | 3168.0 | 6054.6 | 8941.2 | 14109.1 | 19277.0 |
| 2041.4 | 65° | 2068.1 | 2282.6 | 2497.1 | 5084.8 | 7672.7 | 12899.9 | 18127.2 |
| 1827.2 | 67.5° | 1812.3 | 1873.4 | 1934.2 | 4134.8 | 6335.4 | 11461.0 | 16586.6 |
| 1568.9 | 70° | 1499.8 | 1482.5 | 1465.1 | 3255.6 | 5046.1 | 9890.9 | 14735.7 |
| 1333.3 | 72.5° | 1235.3 | 1182.6 | 1130.1 | 2488.9 | 3847.7 | 8188.8 | 12530.1 |
| 1082.5 | 75° | 972.8 | 925.2 | 877.6 | 1806.4 | 2735.3 | 6237.6 | 9740.0 |
| 847.0 | 77.5° | 740.5 | 708.0 | 675.6 | 1224.1 | 1772.5 | 4365.8 | 6959.0 |
| 623.6 | 80° | 533.4 | 520.0 | 506.5 | 788.7 | 1070.9 | 2812.8 | 4554.6 |
| 433.4 | 82.5° | 367.0 | 364.3 | 362.0 | 485.1 | 608.5 | 1628.0 | 2647.6 |
| 265.0 | 85° | 216.4 | 217.7 | 218.9 | 259.3 | 299.9 | 732.3 | 1164.9 |
| 113.4 | 87.5° | 93.6 | 94.8 | 95.9 | 107.5 | 119.1 | 239.9 | 360.6 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)