

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P951581

Luminaire Tested: **GLAN-SB5C-940-U-SLL**

Issue Date: 1/21/2025

### Test Information

Test Method: LM-79-08  
Report Number: P951581  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB5C-940-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(5) 90 CRI, 4000K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

### Summary

Lumens per Lamp: N/A  
Luminaire Lumens: 27315 lumens  
Efficiency: N/A  
Efficacy: 109.5 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5


Input Watts (W): 249.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P951581  
 CATALOG NUMBER: GLAN-SB5C-940-U-SLL

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.3 fc  
 Type IV - Short - N/A

REPORT NUMBER: P951581  
CATALOG NUMBER: GLAN-SB5C-940-U-SLL

## Luminous Intensity Polar Plot



REPORT NUMBER: P951581

CATALOG NUMBER: GLAN-SB5C-940-U-SLL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 6942.1   | 0.0    | 6942.1  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 20372.9  | 0.0    | 20372.9 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 27315.0  | 0.0    | 27315.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 372.6   | 1.4       |
| 10°-20°   | 1169.7  | 4.3       |
| 20°-30°   | 1806.7  | 6.6       |
| 30°-40°   | 2289.6  | 8.4       |
| 40°-50°   | 3453.2  | 12.6      |
| 50°-60°   | 5579.2  | 20.4      |
| 60°-70°   | 6955.4  | 25.5      |
| 70°-80°   | 4561.0  | 16.7      |
| 80°-90°   | 1127.6  | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 27315.0 | 100.0     |
| 0°-180°   | 27315.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P951581


CATALOG NUMBER: GLAN-SB5C-940-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|--------|-----------|-------------------------|------|----------|
|      |             |        |           | B                       | U    | G        |
| FL   | (0°-30°)    | 1837.2 | 6.7       |                         |      |          |
| FM   | (30°-60°)   | 7967.2 | 29.2      |                         |      |          |
| FH   | (60°-80°)   | 9639.6 | 35.3      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 928.9  | 3.4       |                         |      | G5       |
| BL   | (0°-30°)    | 1511.7 | 5.5       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 3354.8 | 12.3      | B3/5000                 |      |          |
| BH   | (60°-80°)   | 1876.8 | 6.9       | B3/2500                 |      | G3/2500  |
| BVH  | (80°-90°)   | 198.7  | 0.7       |                         |      | G2/225   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G5**

Type IV Short



REPORT NUMBER: P951581

CATALOG NUMBER: GLAN-SB5C-940-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  |
| 2.5°  | 4039.3  | 4054.5  | 4070.0  | 4091.7  | 4113.5  | 4126.5  | 4139.4  | 4145.9  | 4152.4  | 4149.5  |
| 5°    | 4343.4  | 4396.9  | 4450.5  | 4503.5  | 4556.7  | 4585.5  | 4614.3  | 4631.8  | 4649.4  | 4662.6  |
| 7.5°  | 4648.9  | 4736.0  | 4822.9  | 4901.2  | 4979.4  | 5026.6  | 5073.7  | 5099.2  | 5124.6  | 5136.8  |
| 10°   | 4883.2  | 4986.1  | 5089.0  | 5180.8  | 5272.6  | 5328.2  | 5383.6  | 5408.4  | 5433.0  | 5442.4  |
| 12.5° | 5026.6  | 5138.1  | 5249.5  | 5332.6  | 5415.3  | 5455.6  | 5496.0  | 5509.5  | 5523.1  | 5524.5  |
| 15°   | 5113.8  | 5210.0  | 5306.2  | 5358.2  | 5410.4  | 5411.8  | 5413.3  | 5398.9  | 5384.4  | 5367.4  |
| 17.5° | 5162.8  | 5227.8  | 5292.8  | 5293.8  | 5294.6  | 5236.3  | 5177.9  | 5124.4  | 5070.8  | 5033.0  |
| 20°   | 5216.8  | 5239.4  | 5262.2  | 5193.8  | 5125.3  | 4996.4  | 4867.6  | 4773.8  | 4679.9  | 4622.3  |
| 22.5° | 5279.5  | 5249.8  | 5220.1  | 5078.3  | 4936.5  | 4746.9  | 4557.4  | 4440.1  | 4322.8  | 4259.1  |
| 25°   | 5360.2  | 5266.5  | 5172.9  | 4957.5  | 4742.2  | 4512.0  | 4281.8  | 4158.5  | 4035.4  | 3975.1  |
| 27.5° | 5469.8  | 5302.3  | 5134.7  | 4849.4  | 4564.3  | 4309.2  | 4054.1  | 3932.8  | 3811.5  | 3754.6  |
| 30°   | 5617.5  | 5367.7  | 5118.1  | 4767.0  | 4415.9  | 4150.1  | 3884.3  | 3771.8  | 3659.2  | 3606.2  |
| 32.5° | 5791.9  | 5449.9  | 5108.0  | 4710.8  | 4313.5  | 4063.8  | 3814.0  | 3725.6  | 3637.1  | 3598.9  |
| 35°   | 6003.8  | 5585.2  | 5166.8  | 4752.9  | 4339.1  | 4165.5  | 3992.1  | 3971.5  | 3950.9  | 3947.7  |
| 37.5° | 6360.5  | 5868.1  | 5375.8  | 4999.6  | 4623.4  | 4612.2  | 4600.9  | 4695.2  | 4789.5  | 4838.5  |
| 40°   | 6899.5  | 6364.1  | 5828.6  | 5548.9  | 5269.1  | 5466.6  | 5664.1  | 5893.2  | 6122.4  | 6236.5  |
| 42.5° | 7614.4  | 7083.2  | 6551.9  | 6390.8  | 6229.6  | 6660.3  | 7090.9  | 7507.8  | 7924.6  | 8169.3  |
| 45°   | 8497.2  | 8020.0  | 7542.7  | 7471.6  | 7400.4  | 8090.3  | 8780.4  | 9465.4  | 10150.4 | 10566.2 |
| 47.5° | 9601.3  | 9137.0  | 8672.6  | 8658.2  | 8643.8  | 9639.2  | 10634.3 | 11637.0 | 12639.5 | 13228.3 |
| 50°   | 11048.3 | 10474.8 | 9901.5  | 9903.9  | 9906.4  | 11189.2 | 12471.9 | 13795.5 | 15119.0 | 15919.2 |
| 52.5° | 12709.5 | 12015.0 | 11320.8 | 11250.6 | 11180.2 | 12712.5 | 14244.7 | 15882.3 | 17519.8 | 18479.0 |
| 55°   | 14477.9 | 13791.9 | 13105.8 | 12832.1 | 12558.4 | 14263.8 | 15969.0 | 17921.2 | 19873.5 | 21014.3 |
| 57.5° | 16086.4 | 15712.8 | 15339.1 | 14790.1 | 14241.3 | 15963.2 | 17685.1 | 19896.4 | 22107.5 | 23522.1 |
| 60°   | 17058.6 | 17638.9 | 18219.3 | 17537.5 | 16855.8 | 18485.3 | 20114.9 | 22482.4 | 24849.9 | 26378.8 |
| 62.5° | 16564.9 | 18150.5 | 19736.1 | 19659.3 | 19582.3 | 21075.1 | 22568.0 | 24820.5 | 27072.8 | 28486.0 |
| 65°   | 15576.9 | 17065.1 | 18553.2 | 18847.7 | 19142.0 | 21039.1 | 22936.2 | 25120.4 | 27304.4 | 28507.6 |
| 67.5° | 14253.1 | 15668.5 | 17083.8 | 17221.9 | 17359.8 | 19336.4 | 21312.9 | 23506.4 | 25700.0 | 26642.6 |
| 70°   | 12662.6 | 14202.1 | 15741.7 | 15803.4 | 15865.2 | 17632.8 | 19400.3 | 21288.0 | 23175.5 | 23699.4 |
| 72.5° | 10767.3 | 12533.9 | 14300.7 | 14345.0 | 14389.3 | 15772.2 | 17155.2 | 18568.9 | 19982.6 | 20035.6 |
| 75°   | 8369.7  | 10198.1 | 12026.6 | 12190.7 | 12354.9 | 13430.8 | 14506.8 | 15502.0 | 16497.2 | 16230.6 |
| 77.5° | 5980.0  | 7686.8  | 9393.7  | 9628.7  | 9863.6  | 10681.5 | 11499.5 | 12205.3 | 12911.2 | 12452.9 |
| 80°   | 3913.9  | 5349.8  | 6785.7  | 7077.7  | 7369.7  | 7987.4  | 8604.9  | 8975.6  | 9346.2  | 8608.9  |
| 82.5° | 2275.1  | 3256.8  | 4238.6  | 4564.8  | 4891.1  | 5316.3  | 5741.4  | 5896.1  | 6050.6  | 5471.2  |
| 85°   | 1001.0  | 1522.0  | 2043.1  | 2320.5  | 2598.0  | 2947.3  | 3296.6  | 3384.3  | 3472.1  | 3008.0  |
| 87.5° | 309.9   | 485.0   | 660.1   | 814.9   | 969.7   | 1144.4  | 1319.1  | 1326.6  | 1333.9  | 1119.9  |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P951581

CATALOG NUMBER: GLAN-SB5C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 50°     |       | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°     | 100°   |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|--------|
| 3756.0  | 0°    | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0  | 3756.0 |
| 4152.4  | 2.5°  | 4145.9  | 4139.4  | 4126.5  | 4113.5  | 4091.7  | 4070.0  | 4054.5  | 4039.3  | 4008.3  | 3977.3 |
| 4649.4  | 5°    | 4631.8  | 4614.3  | 4585.5  | 4556.7  | 4503.5  | 4450.5  | 4396.9  | 4343.4  | 4274.9  | 4206.5 |
| 5124.6  | 7.5°  | 5099.2  | 5073.7  | 5026.6  | 4979.4  | 4901.2  | 4822.9  | 4736.0  | 4648.9  | 4535.9  | 4423.1 |
| 5433.0  | 10°   | 5408.4  | 5383.6  | 5328.2  | 5272.6  | 5180.8  | 5089.0  | 4986.1  | 4883.2  | 4740.3  | 4597.5 |
| 5523.1  | 12.5° | 5509.5  | 5496.0  | 5455.6  | 5415.3  | 5332.6  | 5249.5  | 5138.1  | 5026.6  | 4869.6  | 4712.8 |
| 5384.4  | 15°   | 5398.9  | 5413.3  | 5411.8  | 5410.4  | 5358.2  | 5306.2  | 5210.0  | 5113.8  | 4950.2  | 4786.6 |
| 5070.8  | 17.5° | 5124.4  | 5177.9  | 5236.3  | 5294.6  | 5293.8  | 5292.8  | 5227.8  | 5162.8  | 4996.9  | 4831.0 |
| 4679.9  | 20°   | 4773.8  | 4867.6  | 4996.4  | 5125.3  | 5193.8  | 5262.2  | 5239.4  | 5216.8  | 5044.4  | 4871.9 |
| 4322.8  | 22.5° | 4440.1  | 4557.4  | 4746.9  | 4936.5  | 5078.3  | 5220.1  | 5249.8  | 5279.5  | 5103.4  | 4927.1 |
| 4035.4  | 25°   | 4158.5  | 4281.8  | 4512.0  | 4742.2  | 4957.5  | 5172.9  | 5266.5  | 5360.2  | 5187.6  | 5015.0 |
| 3811.5  | 27.5° | 3932.8  | 4054.1  | 4309.2  | 4564.3  | 4849.4  | 5134.7  | 5302.3  | 5469.8  | 5305.2  | 5140.4 |
| 3659.2  | 30°   | 3771.8  | 3884.3  | 4150.1  | 4415.9  | 4767.0  | 5118.1  | 5367.7  | 5617.5  | 5458.4  | 5299.4 |
| 3637.1  | 32.5° | 3725.6  | 3814.0  | 4063.8  | 4313.5  | 4710.8  | 5108.0  | 5449.9  | 5791.9  | 5634.4  | 5477.0 |
| 3950.9  | 35°   | 3971.5  | 3992.1  | 4165.5  | 4339.1  | 4752.9  | 5166.8  | 5585.2  | 6003.8  | 5853.0  | 5702.1 |
| 4789.5  | 37.5° | 4695.2  | 4600.9  | 4612.2  | 4623.4  | 4999.6  | 5375.8  | 5868.1  | 6360.5  | 6168.2  | 5975.9 |
| 6122.4  | 40°   | 5893.2  | 5664.1  | 5466.6  | 5269.1  | 5548.9  | 5828.6  | 6364.1  | 6899.5  | 6619.3  | 6339.2 |
| 7924.6  | 42.5° | 7507.8  | 7090.9  | 6660.3  | 6229.6  | 6390.8  | 6551.9  | 7083.2  | 7614.4  | 7210.0  | 6805.6 |
| 10150.4 | 45°   | 9465.4  | 8780.4  | 8090.3  | 7400.4  | 7471.6  | 7542.7  | 8020.0  | 8497.2  | 7951.7  | 7406.2 |
| 12639.5 | 47.5° | 11637.0 | 10634.3 | 9639.2  | 8643.8  | 8658.2  | 8672.6  | 9137.0  | 9601.3  | 8833.5  | 8065.6 |
| 15119.0 | 50°   | 13795.5 | 12471.9 | 11189.2 | 9906.4  | 9903.9  | 9901.5  | 10474.8 | 11048.3 | 9890.8  | 8733.2 |
| 17519.8 | 52.5° | 15882.3 | 14244.7 | 12712.5 | 11180.2 | 11250.6 | 11320.8 | 12015.0 | 12709.5 | 11001.5 | 9293.6 |
| 19873.5 | 55°   | 17921.2 | 15969.0 | 14263.8 | 12558.4 | 12832.1 | 13105.8 | 13791.9 | 14477.9 | 11986.2 | 9494.6 |
| 22107.5 | 57.5° | 19896.4 | 17685.1 | 15963.2 | 14241.3 | 14790.1 | 15339.1 | 15712.8 | 16086.4 | 12684.1 | 9281.7 |
| 24849.9 | 60°   | 22482.4 | 20114.9 | 18485.3 | 16855.8 | 17537.5 | 18219.3 | 17638.9 | 17058.6 | 12858.5 | 8658.2 |
| 27072.8 | 62.5° | 24820.5 | 22568.0 | 21075.1 | 19582.3 | 19659.3 | 19736.1 | 18150.5 | 16564.9 | 12124.1 | 7683.3 |
| 27304.4 | 65°   | 25120.4 | 22936.2 | 21039.1 | 19142.0 | 18847.7 | 18553.2 | 17065.1 | 15576.9 | 11085.1 | 6593.3 |
| 25700.0 | 67.5° | 23506.4 | 21312.9 | 19336.4 | 17359.8 | 17221.9 | 17083.8 | 15668.5 | 14253.1 | 9848.6  | 5444.1 |
| 23175.5 | 70°   | 21288.0 | 19400.3 | 17632.8 | 15865.2 | 15803.4 | 15741.7 | 14202.1 | 12662.6 | 8499.4  | 4336.2 |
| 19982.6 | 72.5° | 18568.9 | 17155.2 | 15772.2 | 14389.3 | 14345.0 | 14300.7 | 12533.9 | 10767.3 | 7036.8  | 3306.4 |
| 16497.2 | 75°   | 15502.0 | 14506.8 | 13430.8 | 12354.9 | 12190.7 | 12026.6 | 10198.1 | 8369.7  | 5360.1  | 2350.5 |
| 12911.2 | 77.5° | 12205.3 | 11499.5 | 10681.5 | 9863.6  | 9628.7  | 9393.7  | 7686.8  | 5980.0  | 3751.6  | 1523.2 |
| 9346.2  | 80°   | 8975.6  | 8604.9  | 7987.4  | 7369.7  | 7077.7  | 6785.7  | 5349.8  | 3913.9  | 2417.1  | 920.3  |
| 6050.6  | 82.5° | 5896.1  | 5741.4  | 5316.3  | 4891.1  | 4564.8  | 4238.6  | 3256.8  | 2275.1  | 1398.9  | 522.9  |
| 3472.1  | 85°   | 3384.3  | 3296.6  | 2947.3  | 2598.0  | 2320.5  | 2043.1  | 1522.0  | 1001.0  | 629.3   | 257.7  |
| 1333.9  | 87.5° | 1326.6  | 1319.1  | 1144.4  | 969.7   | 814.9   | 660.1   | 485.0   | 309.9   | 206.1   | 102.3  |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |

REPORT NUMBER: P951581

CATALOG NUMBER: GLAN-SB5C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3756.0 | 0°    | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 |
| 3944.3 | 2.5°  | 3911.4 | 3878.3 | 3845.1 | 3813.4 | 3781.7 | 3751.0 | 3716.8 | 3689.2 | 3661.6 | 3636.7 |
| 4138.1 | 5°    | 4070.0 | 4001.2 | 3932.6 | 3868.5 | 3804.3 | 3743.8 | 3684.0 | 3631.8 | 3579.5 | 3535.7 |
| 4318.7 | 7.5°  | 4214.4 | 4112.8 | 4011.2 | 3921.7 | 3832.1 | 3749.6 | 3672.2 | 3602.7 | 3533.4 | 3475.7 |
| 4459.6 | 10°   | 4321.8 | 4198.4 | 4074.9 | 3969.1 | 3863.0 | 3761.1 | 3677.9 | 3604.7 | 3531.5 | 3473.8 |
| 4556.6 | 12.5° | 4400.3 | 4254.7 | 4109.2 | 3989.4 | 3869.6 | 3762.5 | 3685.1 | 3625.2 | 3565.5 | 3527.2 |
| 4617.1 | 15°   | 4447.6 | 4280.0 | 4112.3 | 3973.7 | 3835.0 | 3716.4 | 3654.4 | 3625.8 | 3597.2 | 3602.4 |
| 4646.1 | 17.5° | 4461.1 | 4266.6 | 4072.0 | 3905.2 | 3738.5 | 3598.9 | 3560.8 | 3571.3 | 3581.6 | 3644.5 |
| 4668.7 | 20°   | 4465.5 | 4229.7 | 3993.9 | 3787.2 | 3580.5 | 3418.1 | 3408.0 | 3457.0 | 3506.0 | 3615.1 |
| 4699.2 | 22.5° | 4471.2 | 4184.4 | 3897.6 | 3648.7 | 3399.8 | 3214.8 | 3234.6 | 3307.1 | 3379.6 | 3504.1 |
| 4754.6 | 25°   | 4494.0 | 4139.7 | 3785.6 | 3494.0 | 3202.6 | 3013.1 | 3066.4 | 3150.0 | 3233.6 | 3345.6 |
| 4841.1 | 27.5° | 4541.6 | 4109.9 | 3678.2 | 3352.6 | 3027.0 | 2854.5 | 2919.4 | 3000.1 | 3080.8 | 3172.9 |
| 4953.1 | 30°   | 4606.7 | 4095.9 | 3584.8 | 3234.4 | 2884.1 | 2739.2 | 2790.1 | 2854.1 | 2918.4 | 2994.7 |
| 5069.9 | 32.5° | 4662.9 | 4078.6 | 3494.0 | 3132.5 | 2770.9 | 2654.2 | 2676.8 | 2714.7 | 2752.6 | 2813.6 |
| 5203.1 | 35°   | 4704.1 | 4046.0 | 3388.2 | 3032.4 | 2676.5 | 2579.2 | 2569.9 | 2580.2 | 2590.8 | 2637.3 |
| 5352.3 | 37.5° | 4728.6 | 3990.3 | 3251.9 | 2914.5 | 2577.1 | 2492.0 | 2457.7 | 2446.2 | 2434.7 | 2468.1 |
| 5541.7 | 40°   | 4744.1 | 3913.4 | 3083.0 | 2773.8 | 2464.6 | 2387.5 | 2334.9 | 2308.8 | 2282.7 | 2306.8 |
| 5789.4 | 42.5° | 4773.3 | 3834.2 | 2895.3 | 2618.6 | 2341.8 | 2270.8 | 2204.5 | 2169.9 | 2135.3 | 2154.9 |
| 6115.5 | 45°   | 4824.8 | 3760.5 | 2696.4 | 2453.7 | 2211.0 | 2138.9 | 2074.8 | 2041.0 | 2007.5 | 2023.9 |
| 6462.8 | 47.5° | 4860.1 | 3699.7 | 2539.3 | 2323.2 | 2107.2 | 2014.2 | 1959.0 | 1930.8 | 1902.5 | 1918.1 |
| 6785.1 | 50°   | 4837.0 | 3633.4 | 2429.8 | 2236.6 | 2043.5 | 1921.3 | 1857.1 | 1832.0 | 1807.1 | 1831.3 |
| 6994.4 | 52.5° | 4695.1 | 3521.4 | 2347.9 | 2179.5 | 2011.3 | 1870.8 | 1781.2 | 1756.4 | 1731.7 | 1768.2 |
| 6948.3 | 55°   | 4401.8 | 3335.8 | 2269.8 | 2138.2 | 2006.6 | 1875.9 | 1740.8 | 1701.6 | 1662.5 | 1714.3 |
| 6623.7 | 57.5° | 3965.8 | 3074.0 | 2182.1 | 2089.2 | 1996.2 | 1880.9 | 1716.6 | 1659.5 | 1602.4 | 1658.1 |
| 6019.6 | 60°   | 3381.0 | 2734.2 | 2087.3 | 2014.2 | 1941.2 | 1865.1 | 1693.8 | 1619.9 | 1545.8 | 1594.7 |
| 5202.8 | 62.5° | 2722.3 | 2327.4 | 1932.5 | 1883.9 | 1835.5 | 1826.1 | 1667.3 | 1574.8 | 1482.4 | 1513.4 |
| 4369.5 | 65°   | 2145.8 | 1961.5 | 1777.1 | 1754.2 | 1731.3 | 1732.5 | 1611.4 | 1513.1 | 1414.6 | 1426.6 |
| 3553.1 | 67.5° | 1662.1 | 1609.8 | 1557.3 | 1570.2 | 1582.8 | 1579.7 | 1511.6 | 1429.8 | 1347.9 | 1344.2 |
| 2797.6 | 70°   | 1259.0 | 1274.0 | 1288.8 | 1348.2 | 1407.4 | 1407.4 | 1385.1 | 1326.9 | 1268.6 | 1255.7 |
| 2138.8 | 72.5° | 971.2  | 1016.3 | 1061.5 | 1145.7 | 1229.7 | 1243.8 | 1244.1 | 1204.2 | 1164.3 | 1145.3 |
| 1552.3 | 75°   | 754.1  | 795.0  | 836.0  | 930.2  | 1024.5 | 1089.6 | 1084.2 | 1053.5 | 1022.6 | 1004.4 |
| 1051.9 | 77.5° | 580.6  | 608.4  | 636.3  | 727.9  | 819.4  | 926.8  | 923.9  | 899.2  | 874.6  | 856.1  |
| 677.7  | 80°   | 435.3  | 446.8  | 458.3  | 535.9  | 613.3  | 741.6  | 741.1  | 720.5  | 699.8  | 684.3  |
| 416.8  | 82.5° | 311.0  | 313.1  | 315.4  | 372.4  | 429.5  | 539.0  | 545.1  | 535.0  | 524.9  | 514.0  |
| 222.8  | 85°   | 188.1  | 187.1  | 185.9  | 227.7  | 269.5  | 351.0  | 358.9  | 348.1  | 337.3  | 325.0  |
| 92.4   | 87.5° | 82.4   | 81.4   | 80.4   | 97.4   | 114.6  | 148.5  | 158.5  | 154.2  | 149.9  | 147.6  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P951581

CATALOG NUMBER: GLAN-SB5C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3756.0 | 0°    | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 |
| 3611.9 | 2.5°  | 3590.2 | 3568.4 | 3546.5 | 3524.7 | 3507.9 | 3490.8 | 3477.2 | 3463.5 | 3452.8 | 3442.1 |
| 3492.0 | 5°    | 3453.4 | 3414.7 | 3379.7 | 3344.6 | 3317.6 | 3290.5 | 3271.6 | 3252.7 | 3239.3 | 3225.9 |
| 3418.1 | 7.5°  | 3369.5 | 3320.8 | 3277.8 | 3235.0 | 3202.9 | 3170.9 | 3148.4 | 3125.9 | 3110.5 | 3095.2 |
| 3416.2 | 10°   | 3363.9 | 3311.4 | 3263.1 | 3214.8 | 3176.5 | 3138.0 | 3112.9 | 3087.6 | 3073.0 | 3058.5 |
| 3489.1 | 12.5° | 3447.9 | 3407.0 | 3356.9 | 3307.1 | 3258.1 | 3209.1 | 3176.6 | 3144.2 | 3127.9 | 3111.8 |
| 3607.6 | 15°   | 3596.9 | 3586.3 | 3542.9 | 3499.5 | 3429.7 | 3360.0 | 3310.7 | 3261.4 | 3238.8 | 3216.3 |
| 3707.3 | 17.5° | 3740.8 | 3774.1 | 3739.0 | 3704.2 | 3611.8 | 3519.4 | 3446.7 | 3374.1 | 3340.7 | 3307.1 |
| 3724.3 | 20°   | 3794.2 | 3864.1 | 3848.0 | 3831.7 | 3726.1 | 3620.6 | 3531.5 | 3442.6 | 3399.8 | 3356.8 |
| 3628.9 | 22.5° | 3719.9 | 3810.8 | 3820.6 | 3830.3 | 3729.4 | 3628.5 | 3536.8 | 3445.0 | 3399.9 | 3354.6 |
| 3457.7 | 25°   | 3547.2 | 3636.7 | 3670.1 | 3703.4 | 3620.7 | 3538.1 | 3456.5 | 3375.3 | 3336.1 | 3297.0 |
| 3264.9 | 27.5° | 3336.6 | 3408.4 | 3445.6 | 3482.9 | 3424.0 | 3365.2 | 3301.9 | 3238.6 | 3212.4 | 3186.0 |
| 3071.1 | 30°   | 3130.7 | 3190.3 | 3220.6 | 3250.9 | 3206.0 | 3161.1 | 3115.8 | 3070.3 | 3056.9 | 3043.3 |
| 2874.7 | 32.5° | 2931.8 | 2989.0 | 3022.6 | 3056.3 | 3015.1 | 2973.7 | 2937.5 | 2901.4 | 2892.6 | 2883.8 |
| 2683.7 | 35°   | 2740.2 | 2796.9 | 2837.2 | 2877.6 | 2848.2 | 2818.9 | 2785.5 | 2752.2 | 2738.8 | 2725.5 |
| 2501.4 | 37.5° | 2557.7 | 2614.2 | 2664.1 | 2714.0 | 2700.4 | 2686.9 | 2656.2 | 2625.3 | 2601.0 | 2576.8 |
| 2330.9 | 40°   | 2385.4 | 2439.8 | 2497.2 | 2554.7 | 2558.0 | 2561.2 | 2535.1 | 2509.0 | 2473.6 | 2438.4 |
| 2174.6 | 42.5° | 2226.2 | 2278.0 | 2340.0 | 2401.9 | 2418.5 | 2435.1 | 2413.0 | 2391.1 | 2347.2 | 2303.2 |
| 2040.6 | 45°   | 2089.6 | 2138.6 | 2202.9 | 2267.2 | 2291.0 | 2314.7 | 2294.9 | 2275.1 | 2224.8 | 2174.6 |
| 1933.5 | 47.5° | 1981.5 | 2029.4 | 2092.8 | 2156.2 | 2183.6 | 2211.0 | 2197.1 | 2183.3 | 2138.6 | 2093.9 |
| 1855.7 | 50°   | 1900.9 | 1946.1 | 2002.8 | 2059.6 | 2094.8 | 2130.0 | 2129.1 | 2128.5 | 2092.8 | 2057.0 |
| 1804.5 | 52.5° | 1846.0 | 1887.4 | 1940.3 | 1993.3 | 2035.0 | 2076.6 | 2084.1 | 2091.6 | 2062.5 | 2033.4 |
| 1765.9 | 55°   | 1810.6 | 1855.3 | 1901.7 | 1947.9 | 1992.0 | 2036.3 | 2046.7 | 2057.0 | 2031.7 | 2006.3 |
| 1713.7 | 57.5° | 1766.2 | 1818.6 | 1864.5 | 1910.5 | 1955.0 | 1999.4 | 2009.9 | 2020.4 | 1994.8 | 1969.1 |
| 1643.4 | 60°   | 1703.6 | 1763.9 | 1810.4 | 1857.1 | 1901.8 | 1946.5 | 1958.0 | 1969.5 | 1944.5 | 1919.5 |
| 1544.4 | 62.5° | 1614.6 | 1684.9 | 1734.6 | 1784.3 | 1825.3 | 1866.2 | 1877.3 | 1888.4 | 1865.8 | 1843.1 |
| 1438.4 | 65°   | 1513.7 | 1589.0 | 1636.6 | 1684.2 | 1720.2 | 1756.2 | 1767.6 | 1778.9 | 1757.1 | 1735.3 |
| 1340.4 | 67.5° | 1409.9 | 1479.5 | 1524.6 | 1569.6 | 1600.7 | 1631.8 | 1642.9 | 1653.9 | 1633.9 | 1614.0 |
| 1242.7 | 70°   | 1303.8 | 1364.9 | 1403.8 | 1442.7 | 1470.9 | 1499.0 | 1509.6 | 1520.3 | 1504.0 | 1487.7 |
| 1126.4 | 72.5° | 1174.5 | 1222.5 | 1257.7 | 1292.9 | 1320.4 | 1347.9 | 1360.6 | 1373.3 | 1359.7 | 1346.2 |
| 986.1  | 75°   | 1021.9 | 1057.6 | 1089.5 | 1121.3 | 1146.4 | 1171.5 | 1184.8 | 1198.0 | 1191.4 | 1184.8 |
| 837.7  | 77.5° | 866.8  | 895.8  | 923.2  | 950.5  | 976.9  | 1003.2 | 1015.5 | 1027.9 | 1018.7 | 1009.2 |
| 668.8  | 80°   | 693.0  | 717.1  | 740.1  | 763.2  | 783.2  | 803.1  | 819.5  | 836.0  | 831.9  | 828.0  |
| 503.0  | 82.5° | 501.0  | 499.0  | 490.9  | 482.8  | 525.5  | 568.2  | 596.1  | 624.1  | 622.4  | 620.5  |
| 312.8  | 85°   | 302.4  | 291.9  | 269.5  | 247.2  | 287.1  | 327.2  | 361.8  | 396.4  | 393.5  | 390.6  |
| 145.3  | 87.5° | 144.9  | 144.4  | 127.4  | 110.3  | 127.0  | 143.8  | 157.8  | 171.8  | 168.3  | 164.6  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P951581

CATALOG NUMBER: GLAN-SB5C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3756.0 | 0°    | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 |
| 3432.3 | 2.5°  | 3422.4 | 3410.1 | 3422.4 | 3432.3 | 3442.1 | 3452.8 | 3463.5 | 3477.2 | 3490.8 | 3507.9 |
| 3215.7 | 5°    | 3205.5 | 3195.4 | 3205.5 | 3215.7 | 3225.9 | 3239.3 | 3252.7 | 3271.6 | 3290.5 | 3317.6 |
| 3086.0 | 7.5°  | 3076.9 | 3070.0 | 3076.9 | 3086.0 | 3095.2 | 3110.5 | 3125.9 | 3148.4 | 3170.9 | 3202.9 |
| 3050.7 | 10°   | 3042.9 | 3039.7 | 3042.9 | 3050.7 | 3058.5 | 3073.0 | 3087.6 | 3112.9 | 3138.0 | 3176.5 |
| 3105.2 | 12.5° | 3098.5 | 3097.4 | 3098.5 | 3105.2 | 3111.8 | 3127.9 | 3144.2 | 3176.6 | 3209.1 | 3258.1 |
| 3207.6 | 15°   | 3199.0 | 3198.3 | 3199.0 | 3207.6 | 3216.3 | 3238.8 | 3261.4 | 3310.7 | 3360.0 | 3429.7 |
| 3296.1 | 17.5° | 3285.0 | 3283.3 | 3285.0 | 3296.1 | 3307.1 | 3340.7 | 3374.1 | 3446.7 | 3519.4 | 3611.8 |
| 3343.1 | 20°   | 3329.4 | 3325.1 | 3329.4 | 3343.1 | 3356.8 | 3399.8 | 3442.6 | 3531.5 | 3620.6 | 3726.1 |
| 3339.5 | 22.5° | 3324.4 | 3317.9 | 3324.4 | 3339.5 | 3354.6 | 3399.9 | 3445.0 | 3536.8 | 3628.5 | 3729.4 |
| 3282.7 | 25°   | 3268.6 | 3260.2 | 3268.6 | 3282.7 | 3297.0 | 3336.1 | 3375.3 | 3456.5 | 3538.1 | 3620.7 |
| 3179.5 | 27.5° | 3173.0 | 3170.9 | 3173.0 | 3179.5 | 3186.0 | 3212.4 | 3238.6 | 3301.9 | 3365.2 | 3424.0 |
| 3043.3 | 30°   | 3043.3 | 3045.5 | 3043.3 | 3043.3 | 3043.3 | 3056.9 | 3070.3 | 3115.8 | 3161.1 | 3206.0 |
| 2884.9 | 32.5° | 2886.2 | 2888.4 | 2886.2 | 2884.9 | 2883.8 | 2892.6 | 2901.4 | 2937.5 | 2973.7 | 3015.1 |
| 2722.6 | 35°   | 2719.7 | 2718.3 | 2719.7 | 2722.6 | 2725.5 | 2738.8 | 2752.2 | 2785.5 | 2818.9 | 2848.2 |
| 2563.9 | 37.5° | 2551.1 | 2543.9 | 2551.1 | 2563.9 | 2576.8 | 2601.0 | 2625.3 | 2656.2 | 2686.9 | 2700.4 |
| 2414.5 | 40°   | 2390.8 | 2376.7 | 2390.8 | 2414.5 | 2438.4 | 2473.6 | 2509.0 | 2535.1 | 2561.2 | 2558.0 |
| 2268.5 | 42.5° | 2233.7 | 2211.0 | 2233.7 | 2268.5 | 2303.2 | 2347.2 | 2391.1 | 2413.0 | 2435.1 | 2418.5 |
| 2133.9 | 45°   | 2093.1 | 2066.8 | 2093.1 | 2133.9 | 2174.6 | 2224.8 | 2275.1 | 2294.9 | 2314.7 | 2291.0 |
| 2056.2 | 47.5° | 2018.6 | 1993.3 | 2018.6 | 2056.2 | 2093.9 | 2138.6 | 2183.3 | 2197.1 | 2211.0 | 2183.6 |
| 2022.2 | 50°   | 1987.3 | 1963.1 | 1987.3 | 2022.2 | 2057.0 | 2092.8 | 2128.5 | 2129.1 | 2130.0 | 2094.8 |
| 2002.1 | 52.5° | 1971.0 | 1948.6 | 1971.0 | 2002.1 | 2033.4 | 2062.5 | 2091.6 | 2084.1 | 2076.6 | 2035.0 |
| 1978.9 | 55°   | 1951.5 | 1931.4 | 1951.5 | 1978.9 | 2006.3 | 2031.7 | 2057.0 | 2046.7 | 2036.3 | 1992.0 |
| 1942.0 | 57.5° | 1914.8 | 1893.9 | 1914.8 | 1942.0 | 1969.1 | 1994.8 | 2020.4 | 2009.9 | 1999.4 | 1955.0 |
| 1891.6 | 60°   | 1863.6 | 1842.0 | 1863.6 | 1891.6 | 1919.5 | 1944.5 | 1969.5 | 1958.0 | 1946.5 | 1901.8 |
| 1813.7 | 62.5° | 1784.3 | 1758.4 | 1784.3 | 1813.7 | 1843.1 | 1865.8 | 1888.4 | 1877.3 | 1866.2 | 1825.3 |
| 1706.8 | 65°   | 1678.4 | 1656.1 | 1678.4 | 1706.8 | 1735.3 | 1757.1 | 1778.9 | 1767.6 | 1756.2 | 1720.2 |
| 1587.5 | 67.5° | 1560.9 | 1540.8 | 1560.9 | 1587.5 | 1614.0 | 1633.9 | 1653.9 | 1642.9 | 1631.8 | 1600.7 |
| 1462.4 | 70°   | 1437.0 | 1413.9 | 1437.0 | 1462.4 | 1487.7 | 1504.0 | 1520.3 | 1509.6 | 1499.0 | 1470.9 |
| 1322.0 | 72.5° | 1297.9 | 1275.6 | 1297.9 | 1322.0 | 1346.2 | 1359.7 | 1373.3 | 1360.6 | 1347.9 | 1320.4 |
| 1164.4 | 75°   | 1144.1 | 1122.8 | 1144.1 | 1164.4 | 1184.8 | 1191.4 | 1198.0 | 1184.8 | 1171.5 | 1146.4 |
| 988.7  | 77.5° | 968.3  | 951.3  | 968.3  | 988.7  | 1009.2 | 1018.7 | 1027.9 | 1015.5 | 1003.2 | 976.9  |
| 800.5  | 80°   | 772.8  | 740.8  | 772.8  | 800.5  | 828.0  | 831.9  | 836.0  | 819.5  | 803.1  | 783.2  |
| 597.3  | 82.5° | 573.9  | 553.5  | 573.9  | 597.3  | 620.5  | 622.4  | 624.1  | 596.1  | 568.2  | 525.5  |
| 372.4  | 85°   | 354.3  | 335.8  | 354.3  | 372.4  | 390.6  | 393.5  | 396.4  | 361.8  | 327.2  | 287.1  |
| 155.4  | 87.5° | 145.9  | 136.9  | 145.9  | 155.4  | 164.6  | 168.3  | 171.8  | 157.8  | 143.8  | 127.0  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P951581

CATALOG NUMBER: GLAN-SB5C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 270°   |       | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3756.0 | 0°    | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 |
| 3524.7 | 2.5°  | 3546.5 | 3568.4 | 3590.2 | 3611.9 | 3636.7 | 3661.6 | 3689.2 | 3716.8 | 3751.0 | 3781.7 |
| 3344.6 | 5°    | 3379.7 | 3414.7 | 3453.4 | 3492.0 | 3535.7 | 3579.5 | 3631.8 | 3684.0 | 3743.8 | 3804.3 |
| 3235.0 | 7.5°  | 3277.8 | 3320.8 | 3369.5 | 3418.1 | 3475.7 | 3533.4 | 3602.7 | 3672.2 | 3749.6 | 3832.1 |
| 3214.8 | 10°   | 3263.1 | 3311.4 | 3363.9 | 3416.2 | 3473.8 | 3531.5 | 3604.7 | 3677.9 | 3761.1 | 3863.0 |
| 3307.1 | 12.5° | 3356.9 | 3407.0 | 3447.9 | 3489.1 | 3527.2 | 3565.5 | 3625.2 | 3685.1 | 3762.5 | 3869.6 |
| 3499.5 | 15°   | 3542.9 | 3586.3 | 3596.9 | 3607.6 | 3602.4 | 3597.2 | 3625.8 | 3654.4 | 3716.4 | 3835.0 |
| 3704.2 | 17.5° | 3739.0 | 3774.1 | 3740.8 | 3707.3 | 3644.5 | 3581.6 | 3571.3 | 3560.8 | 3598.9 | 3738.5 |
| 3831.7 | 20°   | 3848.0 | 3864.1 | 3794.2 | 3724.3 | 3615.1 | 3506.0 | 3457.0 | 3408.0 | 3418.1 | 3580.5 |
| 3830.3 | 22.5° | 3820.6 | 3810.8 | 3719.9 | 3628.9 | 3504.1 | 3379.6 | 3307.1 | 3234.6 | 3214.8 | 3399.8 |
| 3703.4 | 25°   | 3670.1 | 3636.7 | 3547.2 | 3457.7 | 3345.6 | 3233.6 | 3150.0 | 3066.4 | 3013.1 | 3202.6 |
| 3482.9 | 27.5° | 3445.6 | 3408.4 | 3336.6 | 3264.9 | 3172.9 | 3080.8 | 3000.1 | 2919.4 | 2854.5 | 3027.0 |
| 3250.9 | 30°   | 3220.6 | 3190.3 | 3130.7 | 3071.1 | 2994.7 | 2918.4 | 2854.1 | 2790.1 | 2739.2 | 2884.1 |
| 3056.3 | 32.5° | 3022.6 | 2989.0 | 2931.8 | 2874.7 | 2813.6 | 2752.6 | 2714.7 | 2676.8 | 2654.2 | 2770.9 |
| 2877.6 | 35°   | 2837.2 | 2796.9 | 2740.2 | 2683.7 | 2637.3 | 2590.8 | 2580.2 | 2569.9 | 2579.2 | 2676.5 |
| 2714.0 | 37.5° | 2664.1 | 2614.2 | 2557.7 | 2501.4 | 2468.1 | 2434.7 | 2446.2 | 2457.7 | 2492.0 | 2577.1 |
| 2554.7 | 40°   | 2497.2 | 2439.8 | 2385.4 | 2330.9 | 2306.8 | 2282.7 | 2308.8 | 2334.9 | 2387.5 | 2464.6 |
| 2401.9 | 42.5° | 2340.0 | 2278.0 | 2226.2 | 2174.6 | 2154.9 | 2135.3 | 2169.9 | 2204.5 | 2270.8 | 2341.8 |
| 2267.2 | 45°   | 2202.9 | 2138.6 | 2089.6 | 2040.6 | 2023.9 | 2007.5 | 2041.0 | 2074.8 | 2138.9 | 2211.0 |
| 2156.2 | 47.5° | 2092.8 | 2029.4 | 1981.5 | 1933.5 | 1918.1 | 1902.5 | 1930.8 | 1959.0 | 2014.2 | 2107.2 |
| 2059.6 | 50°   | 2002.8 | 1946.1 | 1900.9 | 1855.7 | 1831.3 | 1807.1 | 1832.0 | 1857.1 | 1921.3 | 2043.5 |
| 1993.3 | 52.5° | 1940.3 | 1887.4 | 1846.0 | 1804.5 | 1768.2 | 1731.7 | 1756.4 | 1781.2 | 1870.8 | 2011.3 |
| 1947.9 | 55°   | 1901.7 | 1855.3 | 1810.6 | 1765.9 | 1714.3 | 1662.5 | 1701.6 | 1740.8 | 1875.9 | 2006.6 |
| 1910.5 | 57.5° | 1864.5 | 1818.6 | 1766.2 | 1713.7 | 1658.1 | 1602.4 | 1659.5 | 1716.6 | 1880.9 | 1996.2 |
| 1857.1 | 60°   | 1810.4 | 1763.9 | 1703.6 | 1643.4 | 1594.7 | 1545.8 | 1619.9 | 1693.8 | 1865.1 | 1941.2 |
| 1784.3 | 62.5° | 1734.6 | 1684.9 | 1614.6 | 1544.4 | 1513.4 | 1482.4 | 1574.8 | 1667.3 | 1826.1 | 1835.5 |
| 1684.2 | 65°   | 1636.6 | 1589.0 | 1513.7 | 1438.4 | 1426.6 | 1414.6 | 1513.1 | 1611.4 | 1732.5 | 1731.3 |
| 1569.6 | 67.5° | 1524.6 | 1479.5 | 1409.9 | 1340.4 | 1344.2 | 1347.9 | 1429.8 | 1511.6 | 1579.7 | 1582.8 |
| 1442.7 | 70°   | 1403.8 | 1364.9 | 1303.8 | 1242.7 | 1255.7 | 1268.6 | 1326.9 | 1385.1 | 1407.4 | 1407.4 |
| 1292.9 | 72.5° | 1257.7 | 1222.5 | 1174.5 | 1126.4 | 1145.3 | 1164.3 | 1204.2 | 1244.1 | 1243.8 | 1229.7 |
| 1121.3 | 75°   | 1089.5 | 1057.6 | 1021.9 | 986.1  | 1004.4 | 1022.6 | 1053.5 | 1084.2 | 1089.6 | 1024.5 |
| 950.5  | 77.5° | 923.2  | 895.8  | 866.8  | 837.7  | 856.1  | 874.6  | 899.2  | 923.9  | 926.8  | 819.4  |
| 763.2  | 80°   | 740.1  | 717.1  | 693.0  | 668.8  | 684.3  | 699.8  | 720.5  | 741.1  | 741.6  | 613.3  |
| 482.8  | 82.5° | 490.9  | 499.0  | 501.0  | 503.0  | 514.0  | 524.9  | 535.0  | 545.1  | 539.0  | 429.5  |
| 247.2  | 85°   | 269.5  | 291.9  | 302.4  | 312.8  | 325.0  | 337.3  | 348.1  | 358.9  | 351.0  | 269.5  |
| 110.3  | 87.5° | 127.4  | 144.4  | 144.9  | 145.3  | 147.6  | 149.9  | 154.2  | 158.5  | 148.5  | 114.6  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P951581

CATALOG NUMBER: GLAN-SB5C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 325°   |       | 330°   | 335°   | 340°   | 345°   | 350°   | 355°    | 360°    |
|--------|-------|--------|--------|--------|--------|--------|---------|---------|
| 3756.0 | 0°    | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0 | 3756.0  | 3756.0  |
| 3813.4 | 2.5°  | 3845.1 | 3878.3 | 3911.4 | 3944.3 | 3977.3 | 4008.3  | 4039.3  |
| 3868.5 | 5°    | 3932.6 | 4001.2 | 4070.0 | 4138.1 | 4206.5 | 4274.9  | 4343.4  |
| 3921.7 | 7.5°  | 4011.2 | 4112.8 | 4214.4 | 4318.7 | 4423.1 | 4535.9  | 4648.9  |
| 3969.1 | 10°   | 4074.9 | 4198.4 | 4321.8 | 4459.6 | 4597.5 | 4740.3  | 4883.2  |
| 3989.4 | 12.5° | 4109.2 | 4254.7 | 4400.3 | 4556.6 | 4712.8 | 4869.6  | 5026.6  |
| 3973.7 | 15°   | 4112.3 | 4280.0 | 4447.6 | 4617.1 | 4786.6 | 4950.2  | 5113.8  |
| 3905.2 | 17.5° | 4072.0 | 4266.6 | 4461.1 | 4646.1 | 4831.0 | 4996.9  | 5162.8  |
| 3787.2 | 20°   | 3993.9 | 4229.7 | 4465.5 | 4668.7 | 4871.9 | 5044.4  | 5216.8  |
| 3648.7 | 22.5° | 3897.6 | 4184.4 | 4471.2 | 4699.2 | 4927.1 | 5103.4  | 5279.5  |
| 3494.0 | 25°   | 3785.6 | 4139.7 | 4494.0 | 4754.6 | 5015.0 | 5187.6  | 5360.2  |
| 3352.6 | 27.5° | 3678.2 | 4109.9 | 4541.6 | 4841.1 | 5140.4 | 5305.2  | 5469.8  |
| 3234.4 | 30°   | 3584.8 | 4095.9 | 4606.7 | 4953.1 | 5299.4 | 5458.4  | 5617.5  |
| 3132.5 | 32.5° | 3494.0 | 4078.6 | 4662.9 | 5069.9 | 5477.0 | 5634.4  | 5791.9  |
| 3032.4 | 35°   | 3388.2 | 4046.0 | 4704.1 | 5203.1 | 5702.1 | 5853.0  | 6003.8  |
| 2914.5 | 37.5° | 3251.9 | 3990.3 | 4728.6 | 5352.3 | 5975.9 | 6168.2  | 6360.5  |
| 2773.8 | 40°   | 3083.0 | 3913.4 | 4744.1 | 5541.7 | 6339.2 | 6619.3  | 6899.5  |
| 2618.6 | 42.5° | 2895.3 | 3834.2 | 4773.3 | 5789.4 | 6805.6 | 7210.0  | 7614.4  |
| 2453.7 | 45°   | 2696.4 | 3760.5 | 4824.8 | 6115.5 | 7406.2 | 7951.7  | 8497.2  |
| 2323.2 | 47.5° | 2539.3 | 3699.7 | 4860.1 | 6462.8 | 8065.6 | 8833.5  | 9601.3  |
| 2236.6 | 50°   | 2429.8 | 3633.4 | 4837.0 | 6785.1 | 8733.2 | 9890.8  | 11048.3 |
| 2179.5 | 52.5° | 2347.9 | 3521.4 | 4695.1 | 6994.4 | 9293.6 | 11001.5 | 12709.5 |
| 2138.2 | 55°   | 2269.8 | 3335.8 | 4401.8 | 6948.3 | 9494.6 | 11986.2 | 14477.9 |
| 2089.2 | 57.5° | 2182.1 | 3074.0 | 3965.8 | 6623.7 | 9281.7 | 12684.1 | 16086.4 |
| 2014.2 | 60°   | 2087.3 | 2734.2 | 3381.0 | 6019.6 | 8658.2 | 12858.5 | 17058.6 |
| 1883.9 | 62.5° | 1932.5 | 2327.4 | 2722.3 | 5202.8 | 7683.3 | 12124.1 | 16564.9 |
| 1754.2 | 65°   | 1777.1 | 1961.5 | 2145.8 | 4369.5 | 6593.3 | 11085.1 | 15576.9 |
| 1570.2 | 67.5° | 1557.3 | 1609.8 | 1662.1 | 3553.1 | 5444.1 | 9848.6  | 14253.1 |
| 1348.2 | 70°   | 1288.8 | 1274.0 | 1259.0 | 2797.6 | 4336.2 | 8499.4  | 12662.6 |
| 1145.7 | 72.5° | 1061.5 | 1016.3 | 971.2  | 2138.8 | 3306.4 | 7036.8  | 10767.3 |
| 930.2  | 75°   | 836.0  | 795.0  | 754.1  | 1552.3 | 2350.5 | 5360.1  | 8369.7  |
| 727.9  | 77.5° | 636.3  | 608.4  | 580.6  | 1051.9 | 1523.2 | 3751.6  | 5980.0  |
| 535.9  | 80°   | 458.3  | 446.8  | 435.3  | 677.7  | 920.3  | 2417.1  | 3913.9  |
| 372.4  | 82.5° | 315.4  | 313.1  | 311.0  | 416.8  | 522.9  | 1398.9  | 2275.1  |
| 227.7  | 85°   | 185.9  | 187.1  | 188.1  | 222.8  | 257.7  | 629.3   | 1001.0  |
| 97.4   | 87.5° | 80.4   | 81.4   | 82.4   | 92.4   | 102.3  | 206.1   | 309.9   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |

(END OF REPORT)