

Scaled data based on original data using
LM-46-04 Photometric Testing of Indoor Luminaires Using High Intensity Discharge
or Incandescent Filament Lamps (Reaffirmed 2012)

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: 769295_400MP

Luminaire Tested: **GMX40PXXAR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-46-04
Report Number: 769295_400MP
Test Lab: COOPER LIGHTING
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GMX40PXXAR
Description: MEDIUM ARCHITECTURAL AREA LUMINAIRE- VERTICAL LAMP, ROUND DISTRIBUTION
Light Source: 400 WATT PULSE-START CLEAR ED-37 VBU BURN
Ballast/Driver: -

Summary

Lumens per Lamp: 44000 (1 lamp)
Luminaire Lumens: 29705.9 lumens
Efficiency: 67.5%
Efficacy: 65.7 lumens/watt
Luminous Opening: Circular (Dia: 1.6' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B5 - U3 - G5


Input Watts (W): 452
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: 769295_400MP
 CATALOG NUMBER: GMX40PXXAR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 --- 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.7 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: 769295_400MP
CATALOG NUMBER: GMX40PXXAR

Luminous Intensity Polar Plot



REPORT NUMBER: 769295_400MP

CATALOG NUMBER: GMX40PXXAR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	14821.5	31.5	14853.0
	% Lamp	33.7	0.1	33.8
Street Side	Lumens	14821.5	31.5	14853.0
	% Lamp	33.7	0.1	33.8
Total	Lumens	29643.0	63.0	29705.9
	% Lamp	67.4	0.1	67.5

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	130.7	0.4	0.3
10°-20°	469.5	1.6	1.1
20°-30°	973.2	3.3	2.2
30°-40°	1827.8	6.2	4.2
40°-50°	3549.3	11.9	8.1
50°-60°	5378.8	18.1	12.2
60°-70°	7948.2	26.8	18.1
70°-80°	7776.7	26.2	17.7
80°-90°	1588.8	5.3	3.6
90°-100°	56.1	0.2	0.1
100°-110°	6.9	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-90°	29643.0	99.8	67.4
0°-180°	29705.9	100.0	67.5

Coefficient of Utilization




REPORT NUMBER: 769295_400MP
CATALOG NUMBER: GMX40PXXAR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Lamp	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	786.7	1.8			
FM	(30°-60°)	5377.9	12.2			
FH	(60°-80°)	7862.5	17.9			G4/12000
FVH	(80°-90°)	794.4	1.8			G5
BL	(0°-30°)	786.7	1.8	B2/1000		
BM	(30°-60°)	5377.9	12.2	B4/8500		
BH	(60°-80°)	7862.5	17.9	B5		G4/12000
BVH	(80°-90°)	794.4	1.8			G5
UL	(90°-100°)	56.1	0.1		U3/500	
UH	(100°-180°)	31.5	0.1		U2/50	
Trapped Light		14294.1	32.5			

BUG Rating: B5-U3-G5
Type V Short





REPORT NUMBER: 769295_400MP
CATALOG NUMBER: GMX40PXXAR

CANDELA DISTRIBUTION (FULL):

0°	
0°	1590.1
2.5°	1431.2
5°	1298.0
7.5°	1344.4
10°	1425.1
12.5°	1577.9
15°	1746.6
17.5°	1661.0
20°	1749.0
22.5°	1910.3
25°	2086.3
27.5°	2251.3
30°	2417.6
32.5°	2602.1
35°	2828.2
37.5°	3126.4
40°	3572.6
42.5°	4145.8
45°	4640.8
47.5°	5025.8
50°	5277.6
52.5°	5595.3
55°	5662.6
57.5°	6464.3
60°	7104.8
62.5°	7549.7
65°	7981.1
67.5°	8450.4
70°	8900.2
72.5°	8604.4
75°	7794.1
77.5°	6399.6
80°	4439.1
82.5°	2285.6
85°	993.7
87.5°	294.6
90°	105.1
92.5°	64.8
95°	42.8
97.5°	33.0
100°	24.4
102.5°	11.0
105°	2.4
107.5°	0.0
110°	0.0



REPORT NUMBER: 769295_400MP

CATALOG NUMBER: GMX40PXXAR

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)