

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P1461229

Luminaire Tested: USSL-50-727-U-5WQ

Issue Date: 06/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1461229  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 6/11/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: USSL-50-727-U-5WQ  
Description: USSL DISCRETE LED 1 SQUARE 50W 70CRI 2700K FIXTURE w/ TYPE V SQUARE WIDE DISTRIBUTION OPTIC  
Light Source: (40) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8085.5 lumens  
Efficiency: N/A  
Efficacy: 155.5 lumens/watt  
Luminous Opening: Rectangular (W 0.67' x L: 0.67' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G2


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.98  
Total Harmonic Distortion (THDi): 3.35%  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1461229

CATALOG NUMBER: USSL-50-727-U-5WQ

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 --- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 6.3 fc  
 Type V - Short - N/A

REPORT NUMBER: P1461229

CATALOG NUMBER: USSL-50-727-U-5WQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P1461229

CATALOG NUMBER: USSL-50-727-U-5WQ


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 4042.7   | 0.0    | 4042.7 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 4042.7   | 0.0    | 4042.7 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 8085.5   | 0.0    | 8085.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 59.6   | 0.7       |
| 10°-20°   | 186.1  | 2.3       |
| 20°-30°   | 362.5  | 4.5       |
| 30°-40°   | 643.0  | 8.0       |
| 40°-50°   | 1109.3 | 13.7      |
| 50°-60°   | 1675.2 | 20.7      |
| 60°-70°   | 2230.4 | 27.6      |
| 70°-80°   | 1617.8 | 20.0      |
| 80°-90°   | 201.6  | 2.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 8085.5 | 100.0     |
| 0°-180°   | 8085.5 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P1461229


CATALOG NUMBER: USSL-50-727-U-5WQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 304.1  | 3.8       |                         |      |         |
| FM   | (30°-60°)   | 1713.7 | 21.2      |                         |      |         |
| FH   | (60°-80°)   | 1924.1 | 23.8      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 100.8  | 1.2       |                         |      | G2/225  |
| BL   | (0°-30°)    | 304.1  | 3.8       | B1/500                  |      |         |
| BM   | (30°-60°)   | 1713.7 | 21.2      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 1924.1 | 23.8      | B3/2500                 |      | G2/5000 |
| BVH  | (80°-90°)   | 100.8  | 1.2       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G2**

Type V Short



REPORT NUMBER: P1461229

CATALOG NUMBER: USSL-50-727-U-5WQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 628.6  | 628.6  | 628.6  | 628.6  | 628.6  | 628.6  | 628.6  | 628.6  | 628.6  | 628.6  | 628.6  |
| 2.5°  | 629.0  | 629.0  | 629.0  | 629.0  | 628.6  | 628.2  | 627.9  | 627.9  | 627.9  | 627.5  | 627.5  |
| 5°    | 630.4  | 630.1  | 630.1  | 629.7  | 629.7  | 628.2  | 626.8  | 625.7  | 624.6  | 623.5  | 623.8  |
| 7.5°  | 624.6  | 625.3  | 624.9  | 625.7  | 626.4  | 625.7  | 622.7  | 619.4  | 616.5  | 613.9  | 613.9  |
| 10°   | 625.3  | 624.9  | 624.6  | 624.9  | 625.7  | 625.3  | 622.4  | 618.0  | 613.9  | 611.0  | 610.6  |
| 12.5° | 635.6  | 635.6  | 633.7  | 632.3  | 633.0  | 632.3  | 630.1  | 624.9  | 621.6  | 618.7  | 619.1  |
| 15°   | 655.8  | 655.0  | 652.5  | 650.2  | 649.1  | 648.8  | 647.3  | 643.6  | 639.6  | 636.3  | 637.4  |
| 17.5° | 680.3  | 680.3  | 675.2  | 674.1  | 673.0  | 675.9  | 672.6  | 667.5  | 664.2  | 662.4  | 662.4  |
| 20°   | 710.1  | 710.8  | 706.4  | 704.2  | 704.6  | 704.9  | 703.5  | 698.0  | 693.9  | 692.1  | 692.8  |
| 22.5° | 743.5  | 742.0  | 740.9  | 739.8  | 742.0  | 742.4  | 739.4  | 732.8  | 730.2  | 726.6  | 727.7  |
| 25°   | 772.8  | 772.8  | 773.2  | 779.1  | 782.7  | 788.2  | 783.8  | 773.5  | 764.0  | 760.3  | 760.0  |
| 27.5° | 804.7  | 804.0  | 808.4  | 816.8  | 828.6  | 833.7  | 828.2  | 815.4  | 804.4  | 798.9  | 796.3  |
| 30°   | 857.2  | 856.8  | 857.6  | 868.2  | 881.1  | 888.8  | 882.5  | 871.9  | 862.0  | 856.8  | 859.0  |
| 32.5° | 935.0  | 930.6  | 937.2  | 948.2  | 958.5  | 961.8  | 962.5  | 950.4  | 937.9  | 933.5  | 935.4  |
| 35°   | 978.7  | 977.6  | 984.9  | 998.1  | 1016.5 | 1031.5 | 1019.8 | 1009.1 | 1003.3 | 997.0  | 995.6  |
| 37.5° | 1078.1 | 1077.8 | 1083.6 | 1082.5 | 1085.5 | 1082.2 | 1087.7 | 1092.1 | 1097.6 | 1092.8 | 1093.9 |
| 40°   | 1198.9 | 1195.9 | 1194.8 | 1192.6 | 1184.5 | 1179.4 | 1189.7 | 1197.4 | 1204.0 | 1213.2 | 1208.8 |
| 42.5° | 1325.5 | 1320.7 | 1317.0 | 1310.4 | 1302.0 | 1298.3 | 1299.8 | 1313.7 | 1319.6 | 1320.7 | 1321.0 |
| 45°   | 1469.7 | 1460.9 | 1445.4 | 1433.7 | 1422.0 | 1420.9 | 1420.1 | 1423.1 | 1423.4 | 1423.4 | 1429.3 |
| 47.5° | 1596.3 | 1595.2 | 1573.1 | 1553.0 | 1529.5 | 1529.5 | 1521.4 | 1520.3 | 1525.1 | 1531.3 | 1528.0 |
| 50°   | 1703.8 | 1700.1 | 1680.7 | 1663.4 | 1650.9 | 1635.9 | 1624.2 | 1615.0 | 1621.6 | 1627.1 | 1630.0 |
| 52.5° | 1790.8 | 1790.4 | 1777.2 | 1770.6 | 1765.8 | 1756.6 | 1729.5 | 1713.0 | 1714.4 | 1721.0 | 1719.2 |
| 55°   | 1867.4 | 1872.6 | 1873.3 | 1881.8 | 1890.6 | 1884.0 | 1857.9 | 1833.0 | 1820.1 | 1810.6 | 1810.2 |
| 57.5° | 1955.2 | 1958.5 | 1968.7 | 1995.9 | 2021.2 | 2027.1 | 2000.7 | 1963.6 | 1928.0 | 1904.5 | 1895.7 |
| 60°   | 2046.5 | 2047.3 | 2074.0 | 2117.0 | 2163.2 | 2182.7 | 2159.2 | 2098.3 | 2033.7 | 1982.7 | 1973.5 |
| 62.5° | 2128.7 | 2126.9 | 2167.3 | 2232.2 | 2310.0 | 2341.6 | 2310.4 | 2221.2 | 2109.6 | 2038.5 | 2026.3 |
| 65°   | 2164.3 | 2169.1 | 2222.3 | 2322.1 | 2432.2 | 2493.8 | 2453.5 | 2305.2 | 2143.0 | 2046.9 | 2032.2 |
| 67.5° | 2099.7 | 2113.3 | 2198.4 | 2355.1 | 2527.6 | 2635.9 | 2565.0 | 2339.7 | 2115.1 | 1990.4 | 1970.9 |
| 69°   | 2007.3 | 2010.6 | 2121.0 | 2326.1 | 2553.3 | 2685.4 | 2595.9 | 2321.7 | 2059.0 | 1900.5 | 1879.9 |
| 70°   | 1892.0 | 1915.2 | 2045.8 | 2279.5 | 2548.9 | 2700.8 | 2595.5 | 2287.6 | 1990.7 | 1823.8 | 1787.5 |
| 72.5° | 1536.1 | 1544.5 | 1730.2 | 2088.0 | 2441.0 | 2616.8 | 2471.5 | 2099.0 | 1729.1 | 1480.7 | 1471.1 |
| 75°   | 1029.0 | 1069.7 | 1293.2 | 1725.4 | 2132.0 | 2315.5 | 2133.9 | 1723.2 | 1296.5 | 986.4  | 943.1  |
| 77.5° | 533.6  | 556.7  | 755.2  | 1124.4 | 1550.0 | 1766.5 | 1591.1 | 1205.8 | 798.5  | 482.2  | 457.6  |
| 80°   | 262.4  | 274.9  | 349.0  | 518.5  | 802.9  | 973.5  | 891.7  | 633.7  | 373.9  | 238.9  | 224.6  |
| 82.5° | 147.5  | 152.3  | 193.8  | 241.5  | 334.7  | 389.7  | 364.8  | 309.0  | 187.9  | 141.6  | 137.6  |
| 85°   | 76.7   | 80.7   | 120.7  | 149.0  | 166.6  | 168.4  | 168.1  | 165.9  | 118.5  | 86.6   | 82.6   |
| 87.5° | 36.3   | 40.0   | 62.0   | 81.8   | 86.2   | 83.3   | 88.4   | 76.7   | 56.1   | 39.3   | 34.5   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-3

Test Date: 04/09/2025

Luminaire Tested: GKO-PB1E-727-U-T4W

Data in this report applies to families of products including GKO-PB1E-727-U-T4W


### Test Information

Test Method: LM-79-2019  
 Report Number: SP2-2501-321-3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP2 - 165CM SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/10/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GKO-PB1E-727-U-T4W**  
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

### Spectral Parameters

CCT (K): 2769  
 CIE  $u'$ : 0.2596  
 CIE  $v'$ : 0.5253  
 Duv: -0.0005  
 CIE x: 0.4535  
 CIE y: 0.4078  
 CIE z: 0.1387  
 Peak Wavelength (nm): 597  
 Dominant Wavelength (nm): 584  
 Purity: 58.54014  
 R<sub>f</sub>: 75.7  
 R<sub>g</sub>: 93.2

CRI (Ra): 71.7  
 R1: 68.0  
 R2: 84.0  
 R3: 94.6  
 R4: 65.9  
 R5: 67.3  
 R6: 78.7  
 R7: 75.2  
 R8: 39.8  
 R9: -34.5  
 R10: 64.3  
 R11: 60.9  
 R12: 54.4  
 R13: 71.2  
 R14: 97.6  
 R15: 59.5



### Test Conditions


Stabilization Time: 36M  
 Operation Time: 1H 36M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP2-2501-321-3


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN2187                | 1/6/2025         | 7/6/2025             |
| Power Meter                    | INXT2011002           | 1/21/2025        | 1/21/2026            |
| AC Power Source                | IN0458                | 10/22/2024       | 10/22/2025           |
| DC Power Source                | IN0212                | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | IN4036B               | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | IN0046                | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP2-2501-321-3

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-3

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 114                                    | NR                             | 620               | 844                                    | NR                             | 750               | 22                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 138                                    | NR                             | 625               | 785                                    | NR                             | 755               | 19                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 176                                    | NR                             | 630               | 722                                    | NR                             | 760               | 16                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 222                                    | NR                             | 635               | 655                                    | NR                             | 765               | 14                                     | NR                             | 895               | 0                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 268                                    | NR                             | 640               | 591                                    | NR                             | 770               | 12                                     | NR                             | 900               | 0                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 311                                    | NR                             | 645               | 527                                    | NR                             | 775               | 10                                     | NR                             | 905               | 0                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 348                                    | NR                             | 650               | 467                                    | NR                             | 780               | 9                                      | NR                             | 910               | 0                                      | NR                             |
| 395               | 0                                      | NR                             | 525               | 381                                    | NR                             | 655               | 412                                    | NR                             | 785               | 8                                      | NR                             | 915               | 0                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 410                                    | NR                             | 660               | 360                                    | NR                             | 790               | 7                                      | NR                             | 920               | 0                                      | NR                             |
| 405               | 4                                      | NR                             | 535               | 438                                    | NR                             | 665               | 314                                    | NR                             | 795               | 6                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 7                                      | NR                             | 540               | 469                                    | NR                             | 670               | 272                                    | NR                             | 800               | 5                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 13                                     | NR                             | 545               | 503                                    | NR                             | 675               | 236                                    | NR                             | 805               | 4                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 25                                     | NR                             | 550               | 544                                    | NR                             | 680               | 203                                    | NR                             | 810               | 4                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 46                                     | NR                             | 555               | 594                                    | NR                             | 685               | 175                                    | NR                             | 815               | 3                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 79                                     | NR                             | 560               | 652                                    | NR                             | 690               | 149                                    | NR                             | 820               | 3                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 128                                    | NR                             | 565               | 714                                    | NR                             | 695               | 128                                    | NR                             | 825               | 2                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 196                                    | NR                             | 570               | 783                                    | NR                             | 700               | 109                                    | NR                             | 830               | 2                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 299                                    | NR                             | 575               | 847                                    | NR                             | 705               | 93                                     | NR                             | 835               | 2                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 433                                    | NR                             | 580               | 906                                    | NR                             | 710               | 80                                     | NR                             | 840               | 2                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 433                                    | NR                             | 585               | 953                                    | NR                             | 715               | 68                                     | NR                             | 845               | 1                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 293                                    | NR                             | 590               | 985                                    | NR                             | 720               | 58                                     | NR                             | 850               | 1                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 215                                    | NR                             | 595               | 998                                    | NR                             | 725               | 50                                     | NR                             | 855               | 1                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 173                                    | NR                             | 600               | 997                                    | NR                             | 730               | 42                                     | NR                             | 860               | 1                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 127                                    | NR                             | 605               | 978                                    | NR                             | 735               | 36                                     | NR                             | 865               | 1                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 104                                    | NR                             | 610               | 945                                    | NR                             | 740               | 30                                     | NR                             | 870               | 1                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 104                                    | NR                             | 615               | 902                                    | NR                             | 745               | 26                                     | NR                             | 875               | 1                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP2-2501-321-3

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.14

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 114                                  | NR                             | 620               | 844                                  | NR                             | 750               | 22                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 138                                  | NR                             | 625               | 785                                  | NR                             | 755               | 19                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 176                                  | NR                             | 630               | 722                                  | NR                             | 760               | 16                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 222                                  | NR                             | 635               | 655                                  | NR                             | 765               | 14                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 268                                  | NR                             | 640               | 591                                  | NR                             | 770               | 12                                   | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 311                                  | NR                             | 645               | 527                                  | NR                             | 775               | 10                                   | NR                             | 905               | 0                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 348                                  | NR                             | 650               | 467                                  | NR                             | 780               | 9                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 381                                  | NR                             | 655               | 412                                  | NR                             | 785               | 8                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 2                                    | NR                             | 530               | 410                                  | NR                             | 660               | 360                                  | NR                             | 790               | 7                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 4                                    | NR                             | 535               | 438                                  | NR                             | 665               | 314                                  | NR                             | 795               | 6                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 469                                  | NR                             | 670               | 272                                  | NR                             | 800               | 5                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 13                                   | NR                             | 545               | 503                                  | NR                             | 675               | 236                                  | NR                             | 805               | 4                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 25                                   | NR                             | 550               | 544                                  | NR                             | 680               | 203                                  | NR                             | 810               | 4                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 46                                   | NR                             | 555               | 594                                  | NR                             | 685               | 175                                  | NR                             | 815               | 3                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 79                                   | NR                             | 560               | 652                                  | NR                             | 690               | 149                                  | NR                             | 820               | 3                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 128                                  | NR                             | 565               | 714                                  | NR                             | 695               | 128                                  | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 196                                  | NR                             | 570               | 783                                  | NR                             | 700               | 109                                  | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 299                                  | NR                             | 575               | 847                                  | NR                             | 705               | 93                                   | NR                             | 835               | 2                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 433                                  | NR                             | 580               | 906                                  | NR                             | 710               | 80                                   | NR                             | 840               | 2                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 433                                  | NR                             | 585               | 953                                  | NR                             | 715               | 68                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 293                                  | NR                             | 590               | 985                                  | NR                             | 720               | 58                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 215                                  | NR                             | 595               | 998                                  | NR                             | 725               | 50                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 173                                  | NR                             | 600               | 997                                  | NR                             | 730               | 42                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 127                                  | NR                             | 605               | 978                                  | NR                             | 735               | 36                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 104                                  | NR                             | 610               | 945                                  | NR                             | 740               | 30                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 104                                  | NR                             | 615               | 902                                  | NR                             | 745               | 26                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP2-2501-321-3

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.08


| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 114                         | NR               | 620       | 844                         | NR               | 750       | 22                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 138                         | NR               | 625       | 785                         | NR               | 755       | 19                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 176                         | NR               | 630       | 722                         | NR               | 760       | 16                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 222                         | NR               | 635       | 655                         | NR               | 765       | 14                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 268                         | NR               | 640       | 591                         | NR               | 770       | 12                          | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 311                         | NR               | 645       | 527                         | NR               | 775       | 10                          | NR               | 905       | 0                           | NR               |
| 390       | 0                           | NR               | 520       | 348                         | NR               | 650       | 467                         | NR               | 780       | 9                           | NR               | 910       | 0                           | NR               |
| 395       | 0                           | NR               | 525       | 381                         | NR               | 655       | 412                         | NR               | 785       | 8                           | NR               | 915       | 0                           | NR               |
| 400       | 2                           | NR               | 530       | 410                         | NR               | 660       | 360                         | NR               | 790       | 7                           | NR               | 920       | 0                           | NR               |
| 405       | 4                           | NR               | 535       | 438                         | NR               | 665       | 314                         | NR               | 795       | 6                           | NR               | 925       | 0                           | NR               |
| 410       | 7                           | NR               | 540       | 469                         | NR               | 670       | 272                         | NR               | 800       | 5                           | NR               | 930       | 0                           | NR               |
| 415       | 13                          | NR               | 545       | 503                         | NR               | 675       | 236                         | NR               | 805       | 4                           | NR               | 935       | 0                           | NR               |
| 420       | 25                          | NR               | 550       | 544                         | NR               | 680       | 203                         | NR               | 810       | 4                           | NR               | 940       | 0                           | NR               |
| 425       | 46                          | NR               | 555       | 594                         | NR               | 685       | 175                         | NR               | 815       | 3                           | NR               | 945       | 0                           | NR               |
| 430       | 79                          | NR               | 560       | 652                         | NR               | 690       | 149                         | NR               | 820       | 3                           | NR               | 950       | 0                           | NR               |
| 435       | 128                         | NR               | 565       | 714                         | NR               | 695       | 128                         | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 196                         | NR               | 570       | 783                         | NR               | 700       | 109                         | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 299                         | NR               | 575       | 847                         | NR               | 705       | 93                          | NR               | 835       | 2                           | NR               | 965       | 0                           | NR               |
| 450       | 433                         | NR               | 580       | 906                         | NR               | 710       | 80                          | NR               | 840       | 2                           | NR               | 970       | 0                           | NR               |
| 455       | 433                         | NR               | 585       | 953                         | NR               | 715       | 68                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 293                         | NR               | 590       | 985                         | NR               | 720       | 58                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 215                         | NR               | 595       | 998                         | NR               | 725       | 50                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 173                         | NR               | 600       | 997                         | NR               | 730       | 42                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 127                         | NR               | 605       | 978                         | NR               | 735       | 36                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 104                         | NR               | 610       | 945                         | NR               | 740       | 30                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 104                         | NR               | 615       | 902                         | NR               | 745       | 26                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP2-2501-321-3





TM-30-18

### Summary

$R_f = 75.7$   
 $R_g = 93.2$   
 $CIE R_a = 71.7$   
 $R_g = -34.5$







### Color Vector Graphics





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 87 | CES76 = 64 |
| CES02 = 63 | CES27 = 91 | CES52 = 84 | CES77 = 79 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 72 | CES54 = 86 | CES79 = 87 |
| CES05 = 50 | CES30 = 86 | CES55 = 84 | CES80 = 85 |
| CES06 = 52 | CES31 = 75 | CES56 = 75 | CES81 = 68 |
| CES07 = 42 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 41 | CES33 = 81 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 79 | CES59 = 84 | CES84 = 89 |
| CES10 = 77 | CES35 = 89 | CES60 = 90 | CES85 = 73 |
| CES11 = 60 | CES36 = 92 | CES61 = 81 | CES86 = 59 |
| CES12 = 66 | CES37 = 88 | CES62 = 90 | CES87 = 77 |
| CES13 = 43 | CES38 = 95 | CES63 = 78 | CES88 = 79 |
| CES14 = 74 | CES39 = 97 | CES64 = 66 | CES89 = 65 |
| CES15 = 72 | CES40 = 93 | CES65 = 67 | CES90 = 80 |
| CES16 = 48 | CES41 = 94 | CES66 = 63 | CES91 = 80 |
| CES17 = 50 | CES42 = 89 | CES67 = 61 | CES92 = 55 |
| CES18 = 57 | CES43 = 79 | CES68 = 68 | CES93 = 72 |
| CES19 = 73 | CES44 = 99 | CES69 = 77 | CES94 = 48 |
| CES20 = 67 | CES45 = 85 | CES70 = 63 | CES95 = 67 |
| CES21 = 87 | CES46 = 81 | CES71 = 62 | CES96 = 76 |
| CES22 = 80 | CES47 = 88 | CES72 = 86 | CES97 = 81 |
| CES23 = 92 | CES48 = 74 | CES73 = 57 | CES98 = 76 |
| CES24 = 91 | CES49 = 80 | CES74 = 93 | CES99 = 64 |
| CES25 = 73 | CES50 = 86 | CES75 = 66 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)