

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P1461283

Luminaire Tested: USSL-110-727-U-T4W-HSS

Issue Date: 06/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1461283  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 6/11/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: USSL-110-727-U-T4W-HSS  
Description: USSL DISCRETE LED 1 SQUARE 110W 70CRI 2700K FIXTURE w/ TYPE IV WIDE DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD  
Light Source: (40) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10642.4 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Luminous Opening: Rectangular (W 0.67' x L: 0.67' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G1

Input Watts (W): 111  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.98  
Total Harmonic Distortion (THDi): 2.87%  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT


REPORT NUMBER: P1461283

CATALOG NUMBER: USSL-110-727-U-T4W-HSS

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 3.7 fc

Type V - Short - N/A

REPORT NUMBER: P1461283

CATALOG NUMBER: USSL-110-727-U-T4W-HSS

## Luminous Intensity Polar Plot



REPORT NUMBER: P1461283

CATALOG NUMBER: USSL-110-727-U-T4W-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 5321.2   | 0.0    | 5321.2  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 5321.2   | 0.0    | 5321.2  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 10642.4  | 0.0    | 10642.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 140.8   | 1.3       |
| 10°-20°   | 447.5   | 4.2       |
| 20°-30°   | 803.2   | 7.5       |
| 30°-40°   | 1265.6  | 11.9      |
| 40°-50°   | 1967.3  | 18.5      |
| 50°-60°   | 2554.3  | 24.0      |
| 60°-70°   | 2304.1  | 21.7      |
| 70°-80°   | 1017.3  | 9.6       |
| 80°-90°   | 142.2   | 1.3       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 10642.4 | 100.0     |
| 0°-180°   | 10642.4 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P1461283


CATALOG NUMBER: USSL-110-727-U-T4W-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 695.7  | 6.5       |                         |      |         |
| FM   | (30°-60°)   | 2893.6 | 27.2      |                         |      |         |
| FH   | (60°-80°)   | 1660.7 | 15.6      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 71.1   | 0.7       |                         |      | G1/100  |
| BL   | (0°-30°)    | 695.7  | 6.5       | B2/1000                 |      |         |
| BM   | (30°-60°)   | 2893.6 | 27.2      | B3/5000                 |      |         |
| BH   | (60°-80°)   | 1660.7 | 15.6      | B3/2500                 |      | G1/1800 |
| BVH  | (80°-90°)   | 71.1   | 0.7       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G1**

Type V Short



REPORT NUMBER: P1461283

CATALOG NUMBER: USSL-110-727-U-T4W-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1440.1 | 1440.1 | 1440.1 | 1440.1 | 1440.1 |
| 2.5°  | 1445.9 | 1443.7 | 1449.5 | 1444.4 | 1445.2 |
| 5°    | 1472.9 | 1473.6 | 1461.9 | 1451.7 | 1444.4 |
| 7.5°  | 1511.5 | 1502.7 | 1478.7 | 1456.8 | 1448.1 |
| 10°   | 1547.2 | 1534.1 | 1508.6 | 1474.3 | 1453.2 |
| 12.5° | 1596.8 | 1577.1 | 1541.4 | 1496.9 | 1464.8 |
| 15°   | 1645.6 | 1624.4 | 1579.3 | 1517.3 | 1480.1 |
| 17.5° | 1676.2 | 1667.4 | 1621.5 | 1545.0 | 1501.3 |
| 20°   | 1702.4 | 1701.0 | 1675.5 | 1580.7 | 1530.4 |
| 22.5° | 1717.7 | 1723.6 | 1722.8 | 1624.4 | 1577.1 |
| 25°   | 1734.5 | 1748.3 | 1774.6 | 1681.3 | 1636.8 |
| 27.5° | 1781.9 | 1779.7 | 1816.1 | 1746.9 | 1711.2 |
| 30°   | 1846.0 | 1828.5 | 1878.1 | 1833.6 | 1824.9 |
| 32.5° | 1903.6 | 1905.8 | 1955.3 | 1919.6 | 1907.2 |
| 35°   | 1952.4 | 1949.5 | 2031.8 | 1967.7 | 2028.9 |
| 37.5° | 2129.5 | 2085.0 | 2050.8 | 2056.6 | 2180.5 |
| 40°   | 2363.4 | 2254.1 | 2136.8 | 2162.3 | 2374.4 |
| 42.5° | 2585.7 | 2445.8 | 2249.0 | 2265.8 | 2563.8 |
| 45°   | 2886.7 | 2676.1 | 2377.3 | 2378.7 | 2734.4 |
| 47.5° | 2824.0 | 2859.0 | 2512.8 | 2486.6 | 2884.5 |
| 50°   | 2878.7 | 2955.9 | 2648.4 | 2593.7 | 3002.6 |
| 52.5° | 2863.4 | 2906.4 | 2766.4 | 2688.5 | 3091.5 |
| 55°   | 2815.3 | 2918.8 | 2878.7 | 2761.3 | 3125.0 |
| 57.5° | 2690.6 | 2850.2 | 2990.9 | 2819.6 | 3048.5 |
| 60°   | 2396.9 | 2703.0 | 3047.7 | 2820.4 | 2779.6 |
| 62.5° | 2063.9 | 2480.8 | 3048.5 | 2757.0 | 2383.1 |
| 65°   | 1743.2 | 2169.6 | 2891.8 | 2611.2 | 1956.8 |
| 67.5° | 1430.6 | 1816.8 | 2555.1 | 2376.5 | 1594.6 |
| 70°   | 1167.5 | 1437.1 | 2034.7 | 2054.4 | 1298.0 |
| 72.5° | 854.1  | 1091.0 | 1542.8 | 1628.8 | 1015.9 |
| 75°   | 589.6  | 774.0  | 1104.8 | 1177.0 | 761.6  |
| 77.5° | 338.2  | 513.1  | 774.0  | 750.6  | 481.0  |
| 80°   | 194.6  | 298.8  | 480.3  | 395.7  | 290.8  |
| 82.5° | 119.5  | 188.8  | 256.5  | 222.3  | 180.0  |
| 85°   | 66.3   | 93.3   | 126.8  | 122.4  | 92.6   |
| 87.5° | 27.0   | 42.3   | 41.5   | 36.4   | 21.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-3

Test Date: 04/09/2025

Luminaire Tested: GKO-PB1E-727-U-T4W

Data in this report applies to families of products including GKO-PB1E-727-U-T4W


### Test Information

Test Method: LM-79-2019  
 Report Number: SP2-2501-321-3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP2 - 165CM SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/10/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GKO-PB1E-727-U-T4W**  
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

### Spectral Parameters

CCT (K): 2769  
 CIE  $u'$ : 0.2596  
 CIE  $v'$ : 0.5253  
 Duv: -0.0005  
 CIE x: 0.4535  
 CIE y: 0.4078  
 CIE z: 0.1387  
 Peak Wavelength (nm): 597  
 Dominant Wavelength (nm): 584  
 Purity: 58.54014  
 R<sub>f</sub>: 75.7  
 R<sub>g</sub>: 93.2

CRI (Ra): 71.7  
 R1: 68.0  
 R2: 84.0  
 R3: 94.6  
 R4: 65.9  
 R5: 67.3  
 R6: 78.7  
 R7: 75.2  
 R8: 39.8  
 R9: -34.5  
 R10: 64.3  
 R11: 60.9  
 R12: 54.4  
 R13: 71.2  
 R14: 97.6  
 R15: 59.5



### Test Conditions


Stabilization Time: 36M  
 Operation Time: 1H 36M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP2-2501-321-3


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN2187                | 1/6/2025         | 7/6/2025             |
| Power Meter                    | INXT2011002           | 1/21/2025        | 1/21/2026            |
| AC Power Source                | IN0458                | 10/22/2024       | 10/22/2025           |
| DC Power Source                | IN0212                | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | IN4036B               | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | IN0046                | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP2-2501-321-3

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-3

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 114                                    | NR                             | 620               | 844                                    | NR                             | 750               | 22                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 138                                    | NR                             | 625               | 785                                    | NR                             | 755               | 19                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 176                                    | NR                             | 630               | 722                                    | NR                             | 760               | 16                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 222                                    | NR                             | 635               | 655                                    | NR                             | 765               | 14                                     | NR                             | 895               | 0                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 268                                    | NR                             | 640               | 591                                    | NR                             | 770               | 12                                     | NR                             | 900               | 0                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 311                                    | NR                             | 645               | 527                                    | NR                             | 775               | 10                                     | NR                             | 905               | 0                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 348                                    | NR                             | 650               | 467                                    | NR                             | 780               | 9                                      | NR                             | 910               | 0                                      | NR                             |
| 395               | 0                                      | NR                             | 525               | 381                                    | NR                             | 655               | 412                                    | NR                             | 785               | 8                                      | NR                             | 915               | 0                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 410                                    | NR                             | 660               | 360                                    | NR                             | 790               | 7                                      | NR                             | 920               | 0                                      | NR                             |
| 405               | 4                                      | NR                             | 535               | 438                                    | NR                             | 665               | 314                                    | NR                             | 795               | 6                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 7                                      | NR                             | 540               | 469                                    | NR                             | 670               | 272                                    | NR                             | 800               | 5                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 13                                     | NR                             | 545               | 503                                    | NR                             | 675               | 236                                    | NR                             | 805               | 4                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 25                                     | NR                             | 550               | 544                                    | NR                             | 680               | 203                                    | NR                             | 810               | 4                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 46                                     | NR                             | 555               | 594                                    | NR                             | 685               | 175                                    | NR                             | 815               | 3                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 79                                     | NR                             | 560               | 652                                    | NR                             | 690               | 149                                    | NR                             | 820               | 3                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 128                                    | NR                             | 565               | 714                                    | NR                             | 695               | 128                                    | NR                             | 825               | 2                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 196                                    | NR                             | 570               | 783                                    | NR                             | 700               | 109                                    | NR                             | 830               | 2                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 299                                    | NR                             | 575               | 847                                    | NR                             | 705               | 93                                     | NR                             | 835               | 2                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 433                                    | NR                             | 580               | 906                                    | NR                             | 710               | 80                                     | NR                             | 840               | 2                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 433                                    | NR                             | 585               | 953                                    | NR                             | 715               | 68                                     | NR                             | 845               | 1                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 293                                    | NR                             | 590               | 985                                    | NR                             | 720               | 58                                     | NR                             | 850               | 1                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 215                                    | NR                             | 595               | 998                                    | NR                             | 725               | 50                                     | NR                             | 855               | 1                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 173                                    | NR                             | 600               | 997                                    | NR                             | 730               | 42                                     | NR                             | 860               | 1                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 127                                    | NR                             | 605               | 978                                    | NR                             | 735               | 36                                     | NR                             | 865               | 1                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 104                                    | NR                             | 610               | 945                                    | NR                             | 740               | 30                                     | NR                             | 870               | 1                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 104                                    | NR                             | 615               | 902                                    | NR                             | 745               | 26                                     | NR                             | 875               | 1                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP2-2501-321-3

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.14

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 114                      | NR            | 620    | 844                      | NR            | 750    | 22                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 138                      | NR            | 625    | 785                      | NR            | 755    | 19                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 176                      | NR            | 630    | 722                      | NR            | 760    | 16                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 222                      | NR            | 635    | 655                      | NR            | 765    | 14                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 268                      | NR            | 640    | 591                      | NR            | 770    | 12                       | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 311                      | NR            | 645    | 527                      | NR            | 775    | 10                       | NR            | 905    | 0                        | NR            |
| 390    | 0                        | NR            | 520    | 348                      | NR            | 650    | 467                      | NR            | 780    | 9                        | NR            | 910    | 0                        | NR            |
| 395    | 0                        | NR            | 525    | 381                      | NR            | 655    | 412                      | NR            | 785    | 8                        | NR            | 915    | 0                        | NR            |
| 400    | 2                        | NR            | 530    | 410                      | NR            | 660    | 360                      | NR            | 790    | 7                        | NR            | 920    | 0                        | NR            |
| 405    | 4                        | NR            | 535    | 438                      | NR            | 665    | 314                      | NR            | 795    | 6                        | NR            | 925    | 0                        | NR            |
| 410    | 7                        | NR            | 540    | 469                      | NR            | 670    | 272                      | NR            | 800    | 5                        | NR            | 930    | 0                        | NR            |
| 415    | 13                       | NR            | 545    | 503                      | NR            | 675    | 236                      | NR            | 805    | 4                        | NR            | 935    | 0                        | NR            |
| 420    | 25                       | NR            | 550    | 544                      | NR            | 680    | 203                      | NR            | 810    | 4                        | NR            | 940    | 0                        | NR            |
| 425    | 46                       | NR            | 555    | 594                      | NR            | 685    | 175                      | NR            | 815    | 3                        | NR            | 945    | 0                        | NR            |
| 430    | 79                       | NR            | 560    | 652                      | NR            | 690    | 149                      | NR            | 820    | 3                        | NR            | 950    | 0                        | NR            |
| 435    | 128                      | NR            | 565    | 714                      | NR            | 695    | 128                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 196                      | NR            | 570    | 783                      | NR            | 700    | 109                      | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 299                      | NR            | 575    | 847                      | NR            | 705    | 93                       | NR            | 835    | 2                        | NR            | 965    | 0                        | NR            |
| 450    | 433                      | NR            | 580    | 906                      | NR            | 710    | 80                       | NR            | 840    | 2                        | NR            | 970    | 0                        | NR            |
| 455    | 433                      | NR            | 585    | 953                      | NR            | 715    | 68                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 293                      | NR            | 590    | 985                      | NR            | 720    | 58                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 215                      | NR            | 595    | 998                      | NR            | 725    | 50                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 173                      | NR            | 600    | 997                      | NR            | 730    | 42                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 127                      | NR            | 605    | 978                      | NR            | 735    | 36                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 104                      | NR            | 610    | 945                      | NR            | 740    | 30                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 104                      | NR            | 615    | 902                      | NR            | 745    | 26                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP2-2501-321-3

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.08


| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 114                                    | NR                             | 620               | 844                                    | NR                             | 750               | 22                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 138                                    | NR                             | 625               | 785                                    | NR                             | 755               | 19                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 176                                    | NR                             | 630               | 722                                    | NR                             | 760               | 16                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 222                                    | NR                             | 635               | 655                                    | NR                             | 765               | 14                                     | NR                             | 895               | 0                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 268                                    | NR                             | 640               | 591                                    | NR                             | 770               | 12                                     | NR                             | 900               | 0                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 311                                    | NR                             | 645               | 527                                    | NR                             | 775               | 10                                     | NR                             | 905               | 0                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 348                                    | NR                             | 650               | 467                                    | NR                             | 780               | 9                                      | NR                             | 910               | 0                                      | NR                             |
| 395               | 0                                      | NR                             | 525               | 381                                    | NR                             | 655               | 412                                    | NR                             | 785               | 8                                      | NR                             | 915               | 0                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 410                                    | NR                             | 660               | 360                                    | NR                             | 790               | 7                                      | NR                             | 920               | 0                                      | NR                             |
| 405               | 4                                      | NR                             | 535               | 438                                    | NR                             | 665               | 314                                    | NR                             | 795               | 6                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 7                                      | NR                             | 540               | 469                                    | NR                             | 670               | 272                                    | NR                             | 800               | 5                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 13                                     | NR                             | 545               | 503                                    | NR                             | 675               | 236                                    | NR                             | 805               | 4                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 25                                     | NR                             | 550               | 544                                    | NR                             | 680               | 203                                    | NR                             | 810               | 4                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 46                                     | NR                             | 555               | 594                                    | NR                             | 685               | 175                                    | NR                             | 815               | 3                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 79                                     | NR                             | 560               | 652                                    | NR                             | 690               | 149                                    | NR                             | 820               | 3                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 128                                    | NR                             | 565               | 714                                    | NR                             | 695               | 128                                    | NR                             | 825               | 2                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 196                                    | NR                             | 570               | 783                                    | NR                             | 700               | 109                                    | NR                             | 830               | 2                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 299                                    | NR                             | 575               | 847                                    | NR                             | 705               | 93                                     | NR                             | 835               | 2                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 433                                    | NR                             | 580               | 906                                    | NR                             | 710               | 80                                     | NR                             | 840               | 2                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 433                                    | NR                             | 585               | 953                                    | NR                             | 715               | 68                                     | NR                             | 845               | 1                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 293                                    | NR                             | 590               | 985                                    | NR                             | 720               | 58                                     | NR                             | 850               | 1                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 215                                    | NR                             | 595               | 998                                    | NR                             | 725               | 50                                     | NR                             | 855               | 1                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 173                                    | NR                             | 600               | 997                                    | NR                             | 730               | 42                                     | NR                             | 860               | 1                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 127                                    | NR                             | 605               | 978                                    | NR                             | 735               | 36                                     | NR                             | 865               | 1                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 104                                    | NR                             | 610               | 945                                    | NR                             | 740               | 30                                     | NR                             | 870               | 1                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 104                                    | NR                             | 615               | 902                                    | NR                             | 745               | 26                                     | NR                             | 875               | 1                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP2-2501-321-3





TM-30-18

### Summary

$R_f = 75.7$   
 $R_g = 93.2$   
 $CIE R_a = 71.7$   
 $R_g = -34.5$







### Color Vector Graphics





Individual Sample Fidelity Index ( $R_{f,i}$ )

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 87 | CES76 = 64 |
| CES02 = 63 | CES27 = 91 | CES52 = 84 | CES77 = 79 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 72 | CES54 = 86 | CES79 = 87 |
| CES05 = 50 | CES30 = 86 | CES55 = 84 | CES80 = 85 |
| CES06 = 52 | CES31 = 75 | CES56 = 75 | CES81 = 68 |
| CES07 = 42 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 41 | CES33 = 81 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 79 | CES59 = 84 | CES84 = 89 |
| CES10 = 77 | CES35 = 89 | CES60 = 90 | CES85 = 73 |
| CES11 = 60 | CES36 = 92 | CES61 = 81 | CES86 = 59 |
| CES12 = 66 | CES37 = 88 | CES62 = 90 | CES87 = 77 |
| CES13 = 43 | CES38 = 95 | CES63 = 78 | CES88 = 79 |
| CES14 = 74 | CES39 = 97 | CES64 = 66 | CES89 = 65 |
| CES15 = 72 | CES40 = 93 | CES65 = 67 | CES90 = 80 |
| CES16 = 48 | CES41 = 94 | CES66 = 63 | CES91 = 80 |
| CES17 = 50 | CES42 = 89 | CES67 = 61 | CES92 = 55 |
| CES18 = 57 | CES43 = 79 | CES68 = 68 | CES93 = 72 |
| CES19 = 73 | CES44 = 99 | CES69 = 77 | CES94 = 48 |
| CES20 = 67 | CES45 = 85 | CES70 = 63 | CES95 = 67 |
| CES21 = 87 | CES46 = 81 | CES71 = 62 | CES96 = 76 |
| CES22 = 80 | CES47 = 88 | CES72 = 86 | CES97 = 81 |
| CES23 = 92 | CES48 = 74 | CES73 = 57 | CES98 = 76 |
| CES24 = 91 | CES49 = 80 | CES74 = 93 | CES99 = 64 |
| CES25 = 73 | CES50 = 86 | CES75 = 66 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)