Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981316

Luminaire Tested: **FFX-CLB-100-722-U-FG-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981316
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-100-722-U-FG-T5
Description:	FAIRFAX POST TOP FIXTURE w/ FROSTED GLOBE
Light Source:	(6) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	13509.7 lumens
Efficiency:	N/A
Efficacy:	139.3 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.58' x H: 1.5')
IES Classification:	Type V - Short
BUG Rating:	B3 - U5 - G5


Input Watts (W):	97
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	5.42%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981316
CATALOG NUMBER: FFX-CLB-100-722-U-FG-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 2.2 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981316
CATALOG NUMBER: FFX-CLB-100-722-U-FG-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981316
CATALOG NUMBER: FFX-CLB-100-722-U-FG-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3799.7	2955.2	6754.8
	% Fixture	28.1	21.9	50.0
Street Side	Lumens	3799.7	2955.2	6754.8
	% Fixture	28.1	21.9	50.0
Total	Lumens	7599.3	5910.4	13509.7
	% Fixture	56.3	43.7	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.6	0.1
10°-20°	110.4	0.8
20°-30°	295.4	2.2
30°-40°	568.5	4.2
40°-50°	884.8	6.5
50°-60°	1175.9	8.7
60°-70°	1401.5	10.4
70°-80°	1545.8	11.4
80°-90°	1598.4	11.8
90°-100°	1547.2	11.5
100°-110°	1390.7	10.3
110°-120°	1133.4	8.4
120°-130°	814.9	6.0
130°-140°	517.2	3.8
140°-150°	287.0	2.1
150°-160°	140.3	1.0
160°-170°	62.0	0.5
170°-180°	17.7	0.1
0°-90°	7599.3	56.3
0°-180°	13509.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981316
CATALOG NUMBER: FFX-CLB-100-722-U-FG-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	212.2	1.6			
FM	(30°-60°)	1314.6	9.7			
FH	(60°-80°)	1473.6	10.9			G1/1800
FVH	(80°-90°)	799.2	5.9			G5
BL	(0°-30°)	212.2	1.6	B1/500		
BM	(30°-60°)	1314.6	9.7	B2/2500		
BH	(60°-80°)	1473.6	10.9	B3/2500		G1/1800
BVH	(80°-90°)	799.2	5.9			G5
UL	(90°-100°)	1547.2	11.5		U5	
UH	(100°-180°)	4363.2	32.3		U5	

BUG Rating: B3-U5-G5
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981316
CATALOG NUMBER: FFX-CLB-100-722-U-FG-T5

CANDELA DISTRIBUTION (FULL):

	0°
0°	148.9
2.5°	144.0
5°	161.2
7.5°	202.1
10°	255.3
12.5°	312.6
15°	376.5
17.5°	439.5
20°	501.7
22.5°	564.7
25°	629.3
27.5°	695.6
30°	763.6
32.5°	832.3
35°	901.9
37.5°	967.3
40°	1031.2
42.5°	1088.5
45°	1143.3
47.5°	1192.4
50°	1238.2
52.5°	1277.5
55°	1311.9
57.5°	1343.8
60°	1370.8
62.5°	1393.7
65°	1414.2
67.5°	1430.6
70°	1443.7
72.5°	1455.1
75°	1463.3
77.5°	1468.2
80°	1471.5
82.5°	1470.7
85°	1467.4
87.5°	1460.8
90°	1451.0
92.5°	1437.9
95°	1419.9
97.5°	1400.3
100°	1376.5
102.5°	1348.7
105°	1316.8
107.5°	1281.6
110°	1242.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981316
CATALOG NUMBER: FFX-CLB-100-722-U-FG-T5

CANDELA DISTRIBUTION (continued):

	0°
112.5°	*1195.7*
115°	*1144.1*
117.5°	*1086.8*
120°	*1027.9*
122.5°	*967.3*
125°	*905.1*
127.5°	*845.4*
130°	*784.0*
132.5°	*722.6*
135°	*662.1*
137.5°	*606.4*
140°	*550.8*
142.5°	*499.2*
145°	*450.9*
147.5°	*405.1*
150°	*364.2*
152.5°	*328.2*
155°	*296.3*
157.5°	*269.3*
160°	*246.3*
162.5°	*228.3*
165°	*213.6*
167.5°	*202.1*
170°	*194.0*
172.5°	*186.6*
175°	*181.7*
177.5°	*179.2*
180°	*177.6*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-2

Test Date: 03/20/2025

Luminaire Tested: FFX-CLB-100-722-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-722-U-FR-T5


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-722-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	2219	CRI (Ra):	73.3		
CIE u':	0.2889	R1:	71.2	R9:	-25.6
CIE v':	0.5348	R2:	89.1	R10:	78.7
Duv:	-0.0006	R3:	88.3	R11:	66.6
CIE x:	0.5023	R4:	68.0	R12:	77.1
CIE y:	0.4133	R5:	71.8	R13:	75.0
CIE z:	0.0844	R6:	89.6	R14:	93.9
Peak Wavelength (nm):	606	R7:	71.4	R15:	61.0
Dominant Wavelength (nm):	587	R8:	37.3		
Purity:	74.84521				
Rf:	78.8				
Rg:	94.5				



Test Conditions


Stabilization Time:	61M
Operation Time:	2H 1M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2501-332-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2219K
CIE x = 0.5023
CIE y = 0.4133
Duv = -0.0006

Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	926	NR	750	26	NR	880	1	NR
365	0	NR	495	143	NR	625	872	NR	755	23	NR	885	1	NR
370	0	NR	500	167	NR	630	813	NR	760	19	NR	890	0	NR
375	0	NR	505	190	NR	635	748	NR	765	17	NR	895	0	NR
380	0	NR	510	208	NR	640	681	NR	770	14	NR	900	0	NR
385	0	NR	515	224	NR	645	616	NR	775	12	NR	905	0	NR
390	0	NR	520	239	NR	650	548	NR	780	10	NR	910	0	NR
395	0	NR	525	254	NR	655	486	NR	785	9	NR	915	0	NR
400	1	NR	530	269	NR	660	429	NR	790	8	NR	920	0	NR
405	2	NR	535	288	NR	665	375	NR	795	7	NR	925	0	NR
410	5	NR	540	311	NR	670	326	NR	800	6	NR	930	0	NR
415	10	NR	545	339	NR	675	282	NR	805	5	NR	935	0	NR
420	16	NR	550	372	NR	680	245	NR	810	4	NR	940	0	NR
425	27	NR	555	413	NR	685	210	NR	815	4	NR	945	0	NR
430	42	NR	560	466	NR	690	180	NR	820	3	NR	950	0	NR
435	63	NR	565	526	NR	695	154	NR	825	3	NR	955	0	NR
440	94	NR	570	597	NR	700	132	NR	830	2	NR	960	0	NR
445	150	NR	575	674	NR	705	113	NR	835	2	NR	965	0	NR
450	198	NR	580	756	NR	710	96	NR	840	2	NR	970	0	NR
455	162	NR	585	831	NR	715	82	NR	845	2	NR	975	0	NR
460	117	NR	590	900	NR	720	69	NR	850	1	NR	980	0	NR
465	103	NR	595	952	NR	725	59	NR	855	1	NR	985	0	NR
470	85	NR	600	987	NR	730	50	NR	860	1	NR	990	0	NR
475	76	NR	605	999	NR	735	43	NR	865	1	NR	995	0	NR
480	84	NR	610	991	NR	740	36	NR	870	1	NR	1000	0	NR
485	98	NR	615	964	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.94**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	926	NR	750	26	NR	880	1	NR
365	0	NR	495	143	NR	625	872	NR	755	23	NR	885	1	NR
370	0	NR	500	167	NR	630	813	NR	760	19	NR	890	0	NR
375	0	NR	505	190	NR	635	748	NR	765	17	NR	895	0	NR
380	0	NR	510	208	NR	640	681	NR	770	14	NR	900	0	NR
385	0	NR	515	224	NR	645	616	NR	775	12	NR	905	0	NR
390	0	NR	520	239	NR	650	548	NR	780	10	NR	910	0	NR
395	0	NR	525	254	NR	655	486	NR	785	9	NR	915	0	NR
400	1	NR	530	269	NR	660	429	NR	790	8	NR	920	0	NR
405	2	NR	535	288	NR	665	375	NR	795	7	NR	925	0	NR
410	5	NR	540	311	NR	670	326	NR	800	6	NR	930	0	NR
415	10	NR	545	339	NR	675	282	NR	805	5	NR	935	0	NR
420	16	NR	550	372	NR	680	245	NR	810	4	NR	940	0	NR
425	27	NR	555	413	NR	685	210	NR	815	4	NR	945	0	NR
430	42	NR	560	466	NR	690	180	NR	820	3	NR	950	0	NR
435	63	NR	565	526	NR	695	154	NR	825	3	NR	955	0	NR
440	94	NR	570	597	NR	700	132	NR	830	2	NR	960	0	NR
445	150	NR	575	674	NR	705	113	NR	835	2	NR	965	0	NR
450	198	NR	580	756	NR	710	96	NR	840	2	NR	970	0	NR
455	162	NR	585	831	NR	715	82	NR	845	2	NR	975	0	NR
460	117	NR	590	900	NR	720	69	NR	850	1	NR	980	0	NR
465	103	NR	595	952	NR	725	59	NR	855	1	NR	985	0	NR
470	85	NR	600	987	NR	730	50	NR	860	1	NR	990	0	NR
475	76	NR	605	999	NR	735	43	NR	865	1	NR	995	0	NR
480	84	NR	610	991	NR	740	36	NR	870	1	NR	1000	0	NR
485	98	NR	615	964	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.65**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	926	NR	750	26	NR	880	1	NR
365	0	NR	495	143	NR	625	872	NR	755	23	NR	885	1	NR
370	0	NR	500	167	NR	630	813	NR	760	19	NR	890	0	NR
375	0	NR	505	190	NR	635	748	NR	765	17	NR	895	0	NR
380	0	NR	510	208	NR	640	681	NR	770	14	NR	900	0	NR
385	0	NR	515	224	NR	645	616	NR	775	12	NR	905	0	NR
390	0	NR	520	239	NR	650	548	NR	780	10	NR	910	0	NR
395	0	NR	525	254	NR	655	486	NR	785	9	NR	915	0	NR
400	1	NR	530	269	NR	660	429	NR	790	8	NR	920	0	NR
405	2	NR	535	288	NR	665	375	NR	795	7	NR	925	0	NR
410	5	NR	540	311	NR	670	326	NR	800	6	NR	930	0	NR
415	10	NR	545	339	NR	675	282	NR	805	5	NR	935	0	NR
420	16	NR	550	372	NR	680	245	NR	810	4	NR	940	0	NR
425	27	NR	555	413	NR	685	210	NR	815	4	NR	945	0	NR
430	42	NR	560	466	NR	690	180	NR	820	3	NR	950	0	NR
435	63	NR	565	526	NR	695	154	NR	825	3	NR	955	0	NR
440	94	NR	570	597	NR	700	132	NR	830	2	NR	960	0	NR
445	150	NR	575	674	NR	705	113	NR	835	2	NR	965	0	NR
450	198	NR	580	756	NR	710	96	NR	840	2	NR	970	0	NR
455	162	NR	585	831	NR	715	82	NR	845	2	NR	975	0	NR
460	117	NR	590	900	NR	720	69	NR	850	1	NR	980	0	NR
465	103	NR	595	952	NR	725	59	NR	855	1	NR	985	0	NR
470	85	NR	600	987	NR	730	50	NR	860	1	NR	990	0	NR
475	76	NR	605	999	NR	735	43	NR	865	1	NR	995	0	NR
480	84	NR	610	991	NR	740	36	NR	870	1	NR	1000	0	NR
485	98	NR	615	964	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2501-332-2

TM-30-18


Summary


R_f = 78.8
R_g = 94.5
CIE R_a = 73.3
R_9 = -25.6


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 76	CES51 = 90	CES76 = 80
CES02 = 65	CES27 = 93	CES52 = 87	CES77 = 77
CES03 = 32	CES28 = 93	CES53 = 82	CES78 = 81
CES04 = 72	CES29 = 77	CES54 = 88	CES79 = 83
CES05 = 52	CES30 = 83	CES55 = 88	CES80 = 83
CES06 = 52	CES31 = 79	CES56 = 81	CES81 = 53
CES07 = 44	CES32 = 74	CES57 = 80	CES82 = 93
CES08 = 42	CES33 = 82	CES58 = 82	CES83 = 88
CES09 = 29	CES34 = 89	CES59 = 87	CES84 = 91
CES10 = 79	CES35 = 95	CES60 = 95	CES85 = 69
CES11 = 62	CES36 = 98	CES61 = 86	CES86 = 50
CES12 = 68	CES37 = 96	CES62 = 95	CES87 = 78
CES13 = 45	CES38 = 90	CES63 = 84	CES88 = 79
CES14 = 75	CES39 = 96	CES64 = 77	CES89 = 64
CES15 = 72	CES40 = 93	CES65 = 74	CES90 = 80
CES16 = 49	CES41 = 91	CES66 = 78	CES91 = 88
CES17 = 51	CES42 = 90	CES67 = 77	CES92 = 57
CES18 = 57	CES43 = 81	CES68 = 79	CES93 = 72
CES19 = 74	CES44 = 99	CES69 = 88	CES94 = 48
CES20 = 68	CES45 = 85	CES70 = 76	CES95 = 70
CES21 = 88	CES46 = 81	CES71 = 80	CES96 = 77
CES22 = 81	CES47 = 83	CES72 = 91	CES97 = 79
CES23 = 92	CES48 = 72	CES73 = 72	CES98 = 75
CES24 = 92	CES49 = 82	CES74 = 85	CES99 = 66
CES25 = 73	CES50 = 89	CES75 = 83	





REPORT NUMBER: SP1-2501-332-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-2

TM-30-18

Measure Comparisons





(END OF REPORT)