Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981325

Luminaire Tested: **FFX-CLB-100-727-U-FG-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981325
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-100-727-U-FG-T5
Description:	FAIRFAX POST TOP FIXTURE w/ FROSTED GLOBE
Light Source:	(6) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	15198.4 lumens
Efficiency:	N/A
Efficacy:	156.7 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.58' x H: 1.5')
IES Classification:	Type V - Short
BUG Rating:	B3 - U5 - G5


Input Watts (W):	97
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	5.42%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981325
CATALOG NUMBER: FFX-CLB-100-727-U-FG-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 2.5 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981325
CATALOG NUMBER: FFX-CLB-100-727-U-FG-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981325
CATALOG NUMBER: FFX-CLB-100-727-U-FG-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4274.6	3324.6	7599.2
	% Fixture	28.1	21.9	50.0
Street Side	Lumens	4274.6	3324.6	7599.2
	% Fixture	28.1	21.9	50.0
Total	Lumens	8549.2	6649.2	15198.4
	% Fixture	56.3	43.7	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.9	0.1
10°-20°	124.2	0.8
20°-30°	332.3	2.2
30°-40°	639.6	4.2
40°-50°	995.5	6.5
50°-60°	1322.9	8.7
60°-70°	1576.7	10.4
70°-80°	1739.0	11.4
80°-90°	1798.2	11.8
90°-100°	1740.6	11.5
100°-110°	1564.6	10.3
110°-120°	1275.0	8.4
120°-130°	916.8	6.0
130°-140°	581.8	3.8
140°-150°	322.8	2.1
150°-160°	157.9	1.0
160°-170°	69.8	0.5
170°-180°	19.9	0.1
0°-90°	8549.2	56.3
0°-180°	15198.4	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981325
CATALOG NUMBER: FFX-CLB-100-727-U-FG-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	238.7	1.6			
FM	(30°-60°)	1479.0	9.7			
FH	(60°-80°)	1657.8	10.9			G1/1800
FVH	(80°-90°)	899.1	5.9			G5
BL	(0°-30°)	238.7	1.6	B1/500		
BM	(30°-60°)	1479.0	9.7	B2/2500		
BH	(60°-80°)	1657.8	10.9	B3/2500		G1/1800
BVH	(80°-90°)	899.1	5.9			G5
UL	(90°-100°)	1740.6	11.5		U5	
UH	(100°-180°)	4908.6	32.3		U5	

BUG Rating: B3-U5-G5
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981325
CATALOG NUMBER: FFX-CLB-100-727-U-FG-T5

CANDELA DISTRIBUTION (FULL):

	0°
0°	167.6
2.5°	162.0
5°	181.4
7.5°	227.4
10°	287.3
12.5°	351.7
15°	423.5
17.5°	494.4
20°	564.4
22.5°	635.3
25°	708.0
27.5°	782.6
30°	859.0
32.5°	936.3
35°	1014.6
37.5°	1088.3
40°	1160.1
42.5°	1224.5
45°	1286.2
47.5°	1341.5
50°	1393.0
52.5°	1437.2
55°	1475.9
57.5°	1511.8
60°	1542.2
62.5°	1567.9
65°	1591.0
67.5°	1609.4
70°	1624.1
72.5°	1637.0
75°	1646.2
77.5°	1651.7
80°	1655.4
82.5°	1654.5
85°	1650.8
87.5°	1643.4
90°	1632.4
92.5°	1617.7
95°	1597.4
97.5°	1575.3
100°	1548.6
102.5°	1517.3
105°	1481.4
107.5°	1441.8
110°	1397.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981325
CATALOG NUMBER: FFX-CLB-100-727-U-FG-T5

CANDELA DISTRIBUTION (continued):

	0°
112.5°	*1345.1*
115°	*1287.1*
117.5°	*1222.7*
120°	*1156.4*
122.5°	*1088.3*
125°	*1018.3*
127.5°	*951.1*
130°	*882.0*
132.5°	*813.0*
135°	*744.8*
137.5°	*682.2*
140°	*619.6*
142.5°	*561.6*
145°	*507.3*
147.5°	*455.7*
150°	*409.7*
152.5°	*369.2*
155°	*333.3*
157.5°	*302.9*
160°	*277.1*
162.5°	*256.9*
165°	*240.3*
167.5°	*227.4*
170°	*218.2*
172.5°	*209.9*
175°	*204.4*
177.5°	*201.6*
180°	*199.8*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-3

Test Date: 03/21/2025

Luminaire Tested: FFX-CLB-100-727-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-727-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-727-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	2726	CRI (Ra):	72.7		
CIE u':	0.2616	R1:	69.3	R9:	-32.4
CIE v':	0.5257	R2:	86.2	R10:	70.6
Duv:	-0.0008	R3:	92.5	R11:	63.6
CIE x:	0.4564	R4:	67.2	R12:	64.8
CIE y:	0.4077	R5:	69.7	R13:	72.8
CIE z:	0.1358	R6:	82.9	R14:	96.1
Peak Wavelength (nm):	599	R7:	74.2	R15:	60.3
Dominant Wavelength (nm):	584	R8:	39.5		
Purity:	59.39437				

Rf:	77.8
Rg:	93.1



Test Conditions


Stabilization Time:	75M
Operation Time:	2H 15M
Sphere Temperature (°C):	24.9

REPORT NUMBER: SP1-2501-332-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2726K
CIE x = 0.4564
CIE y = 0.4077
Duv = -0.0008

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	172	NR	620	849	NR	750	22	NR	880	1	NR
365	0	NR	495	205	NR	625	786	NR	755	19	NR	885	0	NR
370	0	NR	500	239	NR	630	724	NR	760	17	NR	890	0	NR
375	0	NR	505	268	NR	635	659	NR	765	14	NR	895	0	NR
380	0	NR	510	291	NR	640	594	NR	770	12	NR	900	0	NR
385	0	NR	515	313	NR	645	533	NR	775	10	NR	905	0	NR
390	0	NR	520	332	NR	650	472	NR	780	9	NR	910	0	NR
395	1	NR	525	352	NR	655	416	NR	785	8	NR	915	0	NR
400	3	NR	530	374	NR	660	364	NR	790	7	NR	920	0	NR
405	5	NR	535	399	NR	665	317	NR	795	6	NR	925	0	NR
410	10	NR	540	432	NR	670	275	NR	800	5	NR	930	0	NR
415	18	NR	545	471	NR	675	238	NR	805	4	NR	935	0	NR
420	31	NR	550	513	NR	680	206	NR	810	4	NR	940	0	NR
425	52	NR	555	565	NR	685	177	NR	815	3	NR	945	0	NR
430	86	NR	560	628	NR	690	151	NR	820	3	NR	950	0	NR
435	134	NR	565	693	NR	695	130	NR	825	2	NR	955	0	NR
440	207	NR	570	763	NR	700	111	NR	830	2	NR	960	0	NR
445	330	NR	575	829	NR	705	94	NR	835	2	NR	965	0	NR
450	415	NR	580	893	NR	710	80	NR	840	2	NR	970	0	NR
455	323	NR	585	942	NR	715	68	NR	845	1	NR	975	0	NR
460	228	NR	590	979	NR	720	58	NR	850	1	NR	980	0	NR
465	189	NR	595	996	NR	725	50	NR	855	1	NR	985	0	NR
470	146	NR	600	998	NR	730	43	NR	860	1	NR	990	0	NR
475	125	NR	605	980	NR	735	36	NR	865	1	NR	995	0	NR
480	131	NR	610	947	NR	740	31	NR	870	1	NR	1000	0	NR
485	147	NR	615	902	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.16**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	172	NR	620	849	NR	750	22	NR	880	1	NR
365	0	NR	495	205	NR	625	786	NR	755	19	NR	885	0	NR
370	0	NR	500	239	NR	630	724	NR	760	17	NR	890	0	NR
375	0	NR	505	268	NR	635	659	NR	765	14	NR	895	0	NR
380	0	NR	510	291	NR	640	594	NR	770	12	NR	900	0	NR
385	0	NR	515	313	NR	645	533	NR	775	10	NR	905	0	NR
390	0	NR	520	332	NR	650	472	NR	780	9	NR	910	0	NR
395	1	NR	525	352	NR	655	416	NR	785	8	NR	915	0	NR
400	3	NR	530	374	NR	660	364	NR	790	7	NR	920	0	NR
405	5	NR	535	399	NR	665	317	NR	795	6	NR	925	0	NR
410	10	NR	540	432	NR	670	275	NR	800	5	NR	930	0	NR
415	18	NR	545	471	NR	675	238	NR	805	4	NR	935	0	NR
420	31	NR	550	513	NR	680	206	NR	810	4	NR	940	0	NR
425	52	NR	555	565	NR	685	177	NR	815	3	NR	945	0	NR
430	86	NR	560	628	NR	690	151	NR	820	3	NR	950	0	NR
435	134	NR	565	693	NR	695	130	NR	825	2	NR	955	0	NR
440	207	NR	570	763	NR	700	111	NR	830	2	NR	960	0	NR
445	330	NR	575	829	NR	705	94	NR	835	2	NR	965	0	NR
450	415	NR	580	893	NR	710	80	NR	840	2	NR	970	0	NR
455	323	NR	585	942	NR	715	68	NR	845	1	NR	975	0	NR
460	228	NR	590	979	NR	720	58	NR	850	1	NR	980	0	NR
465	189	NR	595	996	NR	725	50	NR	855	1	NR	985	0	NR
470	146	NR	600	998	NR	730	43	NR	860	1	NR	990	0	NR
475	125	NR	605	980	NR	735	36	NR	865	1	NR	995	0	NR
480	131	NR	610	947	NR	740	31	NR	870	1	NR	1000	0	NR
485	147	NR	615	902	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.15**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	172	NR	620	849	NR	750	22	NR	880	1	NR
365	0	NR	495	205	NR	625	786	NR	755	19	NR	885	0	NR
370	0	NR	500	239	NR	630	724	NR	760	17	NR	890	0	NR
375	0	NR	505	268	NR	635	659	NR	765	14	NR	895	0	NR
380	0	NR	510	291	NR	640	594	NR	770	12	NR	900	0	NR
385	0	NR	515	313	NR	645	533	NR	775	10	NR	905	0	NR
390	0	NR	520	332	NR	650	472	NR	780	9	NR	910	0	NR
395	1	NR	525	352	NR	655	416	NR	785	8	NR	915	0	NR
400	3	NR	530	374	NR	660	364	NR	790	7	NR	920	0	NR
405	5	NR	535	399	NR	665	317	NR	795	6	NR	925	0	NR
410	10	NR	540	432	NR	670	275	NR	800	5	NR	930	0	NR
415	18	NR	545	471	NR	675	238	NR	805	4	NR	935	0	NR
420	31	NR	550	513	NR	680	206	NR	810	4	NR	940	0	NR
425	52	NR	555	565	NR	685	177	NR	815	3	NR	945	0	NR
430	86	NR	560	628	NR	690	151	NR	820	3	NR	950	0	NR
435	134	NR	565	693	NR	695	130	NR	825	2	NR	955	0	NR
440	207	NR	570	763	NR	700	111	NR	830	2	NR	960	0	NR
445	330	NR	575	829	NR	705	94	NR	835	2	NR	965	0	NR
450	415	NR	580	893	NR	710	80	NR	840	2	NR	970	0	NR
455	323	NR	585	942	NR	715	68	NR	845	1	NR	975	0	NR
460	228	NR	590	979	NR	720	58	NR	850	1	NR	980	0	NR
465	189	NR	595	996	NR	725	50	NR	855	1	NR	985	0	NR
470	146	NR	600	998	NR	730	43	NR	860	1	NR	990	0	NR
475	125	NR	605	980	NR	735	36	NR	865	1	NR	995	0	NR
480	131	NR	610	947	NR	740	31	NR	870	1	NR	1000	0	NR
485	147	NR	615	902	NR	745	26	NR	875	1	NR			


REPORT NUMBER: SP1-2501-332-3

TM-30-18


Summary


R_f = 77.8
R_g = 93.1
CIE R_a = 72.7
R_9 = -32.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 72	CES51 = 88	CES76 = 71
CES02 = 63	CES27 = 92	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 91	CES53 = 80	CES78 = 73
CES04 = 71	CES29 = 75	CES54 = 87	CES79 = 88
CES05 = 50	CES30 = 84	CES55 = 86	CES80 = 87
CES06 = 52	CES31 = 78	CES56 = 78	CES81 = 65
CES07 = 42	CES32 = 72	CES57 = 77	CES82 = 94
CES08 = 41	CES33 = 82	CES58 = 79	CES83 = 91
CES09 = 29	CES34 = 84	CES59 = 85	CES84 = 89
CES10 = 77	CES35 = 92	CES60 = 92	CES85 = 73
CES11 = 60	CES36 = 95	CES61 = 83	CES86 = 57
CES12 = 66	CES37 = 92	CES62 = 95	CES87 = 78
CES13 = 44	CES38 = 93	CES63 = 82	CES88 = 79
CES14 = 74	CES39 = 97	CES64 = 72	CES89 = 66
CES15 = 72	CES40 = 94	CES65 = 71	CES90 = 80
CES16 = 48	CES41 = 93	CES66 = 71	CES91 = 83
CES17 = 51	CES42 = 92	CES67 = 69	CES92 = 56
CES18 = 57	CES43 = 82	CES68 = 73	CES93 = 73
CES19 = 73	CES44 = 99	CES69 = 82	CES94 = 49
CES20 = 67	CES45 = 86	CES70 = 70	CES95 = 68
CES21 = 87	CES46 = 82	CES71 = 71	CES96 = 77
CES22 = 80	CES47 = 88	CES72 = 89	CES97 = 81
CES23 = 92	CES48 = 74	CES73 = 64	CES98 = 76
CES24 = 91	CES49 = 82	CES74 = 92	CES99 = 65
CES25 = 73	CES50 = 88	CES75 = 74	





REPORT NUMBER: SP1-2501-332-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-3

TM-30-18

Measure Comparisons





(END OF REPORT)