Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981363

Luminaire Tested: **FFX-CLB-80-722-U-PG-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981363
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-80-722-U-PG-T5
Description:	FAIRFAX POST TOP FIXTURE w/ PRISMATIC GLOBE
Light Source:	(4) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	10994.7 lumens
Efficiency:	N/A
Efficacy:	134.4 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.58' x H: 1.5')
IES Classification:	Type V - Short
BUG Rating:	B3 - U5 - G4

Input Watts (W):	81.8
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	6.01%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981363
CATALOG NUMBER: FFX-CLB-80-722-U-PG-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 1.5 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981363
CATALOG NUMBER: FFX-CLB-80-722-U-PG-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981363
CATALOG NUMBER: FFX-CLB-80-722-U-PG-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3228.1	2269.3	5497.3
	% Fixture	29.4	20.6	50.0
Street Side	Lumens	3228.1	2269.3	5497.3
	% Fixture	29.4	20.6	50.0
Total	Lumens	6456.1	4538.6	10994.7
	% Fixture	58.7	41.3	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.9	0.1
10°-20°	20.7	0.2
20°-30°	97.4	0.9
30°-40°	345.3	3.1
40°-50°	709.4	6.5
50°-60°	1079.4	9.8
60°-70°	1335.5	12.1
70°-80°	1425.5	13.0
80°-90°	1436.2	13.1
90°-100°	1337.3	12.2
100°-110°	1202.3	10.9
110°-120°	828.7	7.5
120°-130°	572.0	5.2
130°-140°	331.4	3.0
140°-150°	157.7	1.4
150°-160°	68.9	0.6
160°-170°	30.8	0.3
170°-180°	9.6	0.1
0°-90°	6456.1	58.7
0°-180°	10994.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981363
CATALOG NUMBER: FFX-CLB-80-722-U-PG-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	62.5	0.6			
FM	(30°-60°)	1067.0	9.7			
FH	(60°-80°)	1380.5	12.6			G1/1800
FVH	(80°-90°)	718.1	6.5			G4/750
BL	(0°-30°)	62.5	0.6	B0/110		
BM	(30°-60°)	1067.0	9.7	B2/2500		
BH	(60°-80°)	1380.5	12.6	B3/2500		G1/1800
BVH	(80°-90°)	718.1	6.5			G4/750
UL	(90°-100°)	1337.3	12.2		U5	
UH	(100°-180°)	3201.3	29.1		U5	

BUG Rating: B3-U5-G4
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981363
CATALOG NUMBER: FFX-CLB-80-722-U-PG-T5

CANDELA DISTRIBUTION (FULL):

	0°
0°	83.7
2.5°	82.3
5°	76.1
7.5°	67.9
10°	67.2
12.5°	65.2
15°	65.9
17.5°	74.1
20°	96.0
22.5°	136.5
25°	192.1
27.5°	262.0
30°	347.8
32.5°	441.1
35°	541.2
37.5°	641.4
40°	740.2
42.5°	832.1
45°	915.1
47.5°	992.6
50°	1072.2
52.5°	1144.2
55°	1208.0
57.5°	1262.9
60°	1304.7
62.5°	1331.5
65°	1350.0
67.5°	1363.7
70°	1365.1
72.5°	1357.5
75°	1347.9
77.5°	1338.3
80°	1328.0
82.5°	1316.4
85°	1306.1
87.5°	1321.2
90°	1315.0
92.5°	1305.4
95°	1255.3
97.5°	1131.2
100°	1103.7
102.5°	1214.9
105°	1214.9
107.5°	1073.5
110°	975.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981363
CATALOG NUMBER: FFX-CLB-80-722-U-PG-T5

CANDELA DISTRIBUTION (continued):

	0°
112.5°	*884.9*
115°	*821.1*
117.5°	*774.5*
120°	*730.6*
122.5°	*686.0*
125°	*637.3*
127.5°	*587.2*
130°	*533.7*
132.5°	*476.1*
135°	*421.9*
137.5°	*372.5*
140°	*325.8*
142.5°	*282.6*
145°	*244.2*
147.5°	*211.3*
150°	*183.8*
152.5°	*161.9*
155°	*144.1*
157.5°	*130.3*
160°	*119.4*
162.5°	*111.1*
165°	*106.3*
167.5°	*102.9*
170°	*101.5*
172.5°	*100.8*
175°	*100.2*
177.5°	*100.2*
180°	*100.2*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-2

Test Date: 03/20/2025

Luminaire Tested: FFX-CLB-100-722-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-722-U-FR-T5


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-722-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	2219	CRI (Ra):	73.3		
CIE u':	0.2889	R1:	71.2	R9:	-25.6
CIE v':	0.5348	R2:	89.1	R10:	78.7
Duv:	-0.0006	R3:	88.3	R11:	66.6
CIE x:	0.5023	R4:	68.0	R12:	77.1
CIE y:	0.4133	R5:	71.8	R13:	75.0
CIE z:	0.0844	R6:	89.6	R14:	93.9
Peak Wavelength (nm):	606	R7:	71.4	R15:	61.0
Dominant Wavelength (nm):	587	R8:	37.3		
Purity:	74.84521				
Rf:	78.8				
Rg:	94.5				



Test Conditions


Stabilization Time:	61M
Operation Time:	2H 1M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2501-332-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2219K
CIE x = 0.5023
CIE y = 0.4133
Duv = -0.0006

Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	926	NR	750	26	NR	880	1	NR
365	0	NR	495	143	NR	625	872	NR	755	23	NR	885	1	NR
370	0	NR	500	167	NR	630	813	NR	760	19	NR	890	0	NR
375	0	NR	505	190	NR	635	748	NR	765	17	NR	895	0	NR
380	0	NR	510	208	NR	640	681	NR	770	14	NR	900	0	NR
385	0	NR	515	224	NR	645	616	NR	775	12	NR	905	0	NR
390	0	NR	520	239	NR	650	548	NR	780	10	NR	910	0	NR
395	0	NR	525	254	NR	655	486	NR	785	9	NR	915	0	NR
400	1	NR	530	269	NR	660	429	NR	790	8	NR	920	0	NR
405	2	NR	535	288	NR	665	375	NR	795	7	NR	925	0	NR
410	5	NR	540	311	NR	670	326	NR	800	6	NR	930	0	NR
415	10	NR	545	339	NR	675	282	NR	805	5	NR	935	0	NR
420	16	NR	550	372	NR	680	245	NR	810	4	NR	940	0	NR
425	27	NR	555	413	NR	685	210	NR	815	4	NR	945	0	NR
430	42	NR	560	466	NR	690	180	NR	820	3	NR	950	0	NR
435	63	NR	565	526	NR	695	154	NR	825	3	NR	955	0	NR
440	94	NR	570	597	NR	700	132	NR	830	2	NR	960	0	NR
445	150	NR	575	674	NR	705	113	NR	835	2	NR	965	0	NR
450	198	NR	580	756	NR	710	96	NR	840	2	NR	970	0	NR
455	162	NR	585	831	NR	715	82	NR	845	2	NR	975	0	NR
460	117	NR	590	900	NR	720	69	NR	850	1	NR	980	0	NR
465	103	NR	595	952	NR	725	59	NR	855	1	NR	985	0	NR
470	85	NR	600	987	NR	730	50	NR	860	1	NR	990	0	NR
475	76	NR	605	999	NR	735	43	NR	865	1	NR	995	0	NR
480	84	NR	610	991	NR	740	36	NR	870	1	NR	1000	0	NR
485	98	NR	615	964	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.94**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	926	NR	750	26	NR	880	1	NR
365	0	NR	495	143	NR	625	872	NR	755	23	NR	885	1	NR
370	0	NR	500	167	NR	630	813	NR	760	19	NR	890	0	NR
375	0	NR	505	190	NR	635	748	NR	765	17	NR	895	0	NR
380	0	NR	510	208	NR	640	681	NR	770	14	NR	900	0	NR
385	0	NR	515	224	NR	645	616	NR	775	12	NR	905	0	NR
390	0	NR	520	239	NR	650	548	NR	780	10	NR	910	0	NR
395	0	NR	525	254	NR	655	486	NR	785	9	NR	915	0	NR
400	1	NR	530	269	NR	660	429	NR	790	8	NR	920	0	NR
405	2	NR	535	288	NR	665	375	NR	795	7	NR	925	0	NR
410	5	NR	540	311	NR	670	326	NR	800	6	NR	930	0	NR
415	10	NR	545	339	NR	675	282	NR	805	5	NR	935	0	NR
420	16	NR	550	372	NR	680	245	NR	810	4	NR	940	0	NR
425	27	NR	555	413	NR	685	210	NR	815	4	NR	945	0	NR
430	42	NR	560	466	NR	690	180	NR	820	3	NR	950	0	NR
435	63	NR	565	526	NR	695	154	NR	825	3	NR	955	0	NR
440	94	NR	570	597	NR	700	132	NR	830	2	NR	960	0	NR
445	150	NR	575	674	NR	705	113	NR	835	2	NR	965	0	NR
450	198	NR	580	756	NR	710	96	NR	840	2	NR	970	0	NR
455	162	NR	585	831	NR	715	82	NR	845	2	NR	975	0	NR
460	117	NR	590	900	NR	720	69	NR	850	1	NR	980	0	NR
465	103	NR	595	952	NR	725	59	NR	855	1	NR	985	0	NR
470	85	NR	600	987	NR	730	50	NR	860	1	NR	990	0	NR
475	76	NR	605	999	NR	735	43	NR	865	1	NR	995	0	NR
480	84	NR	610	991	NR	740	36	NR	870	1	NR	1000	0	NR
485	98	NR	615	964	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.65**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	926	NR	750	26	NR	880	1	NR
365	0	NR	495	143	NR	625	872	NR	755	23	NR	885	1	NR
370	0	NR	500	167	NR	630	813	NR	760	19	NR	890	0	NR
375	0	NR	505	190	NR	635	748	NR	765	17	NR	895	0	NR
380	0	NR	510	208	NR	640	681	NR	770	14	NR	900	0	NR
385	0	NR	515	224	NR	645	616	NR	775	12	NR	905	0	NR
390	0	NR	520	239	NR	650	548	NR	780	10	NR	910	0	NR
395	0	NR	525	254	NR	655	486	NR	785	9	NR	915	0	NR
400	1	NR	530	269	NR	660	429	NR	790	8	NR	920	0	NR
405	2	NR	535	288	NR	665	375	NR	795	7	NR	925	0	NR
410	5	NR	540	311	NR	670	326	NR	800	6	NR	930	0	NR
415	10	NR	545	339	NR	675	282	NR	805	5	NR	935	0	NR
420	16	NR	550	372	NR	680	245	NR	810	4	NR	940	0	NR
425	27	NR	555	413	NR	685	210	NR	815	4	NR	945	0	NR
430	42	NR	560	466	NR	690	180	NR	820	3	NR	950	0	NR
435	63	NR	565	526	NR	695	154	NR	825	3	NR	955	0	NR
440	94	NR	570	597	NR	700	132	NR	830	2	NR	960	0	NR
445	150	NR	575	674	NR	705	113	NR	835	2	NR	965	0	NR
450	198	NR	580	756	NR	710	96	NR	840	2	NR	970	0	NR
455	162	NR	585	831	NR	715	82	NR	845	2	NR	975	0	NR
460	117	NR	590	900	NR	720	69	NR	850	1	NR	980	0	NR
465	103	NR	595	952	NR	725	59	NR	855	1	NR	985	0	NR
470	85	NR	600	987	NR	730	50	NR	860	1	NR	990	0	NR
475	76	NR	605	999	NR	735	43	NR	865	1	NR	995	0	NR
480	84	NR	610	991	NR	740	36	NR	870	1	NR	1000	0	NR
485	98	NR	615	964	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2501-332-2

TM-30-18


Summary


R_f = 78.8
R_g = 94.5
CIE R_a = 73.3
R_9 = -25.6


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 76	CES51 = 90	CES76 = 80
CES02 = 65	CES27 = 93	CES52 = 87	CES77 = 77
CES03 = 32	CES28 = 93	CES53 = 82	CES78 = 81
CES04 = 72	CES29 = 77	CES54 = 88	CES79 = 83
CES05 = 52	CES30 = 83	CES55 = 88	CES80 = 83
CES06 = 52	CES31 = 79	CES56 = 81	CES81 = 53
CES07 = 44	CES32 = 74	CES57 = 80	CES82 = 93
CES08 = 42	CES33 = 82	CES58 = 82	CES83 = 88
CES09 = 29	CES34 = 89	CES59 = 87	CES84 = 91
CES10 = 79	CES35 = 95	CES60 = 95	CES85 = 69
CES11 = 62	CES36 = 98	CES61 = 86	CES86 = 50
CES12 = 68	CES37 = 96	CES62 = 95	CES87 = 78
CES13 = 45	CES38 = 90	CES63 = 84	CES88 = 79
CES14 = 75	CES39 = 96	CES64 = 77	CES89 = 64
CES15 = 72	CES40 = 93	CES65 = 74	CES90 = 80
CES16 = 49	CES41 = 91	CES66 = 78	CES91 = 88
CES17 = 51	CES42 = 90	CES67 = 77	CES92 = 57
CES18 = 57	CES43 = 81	CES68 = 79	CES93 = 72
CES19 = 74	CES44 = 99	CES69 = 88	CES94 = 48
CES20 = 68	CES45 = 85	CES70 = 76	CES95 = 70
CES21 = 88	CES46 = 81	CES71 = 80	CES96 = 77
CES22 = 81	CES47 = 83	CES72 = 91	CES97 = 79
CES23 = 92	CES48 = 72	CES73 = 72	CES98 = 75
CES24 = 92	CES49 = 82	CES74 = 85	CES99 = 66
CES25 = 73	CES50 = 89	CES75 = 83	





REPORT NUMBER: SP1-2501-332-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-2

TM-30-18

Measure Comparisons





(END OF REPORT)