Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981371

Luminaire Tested: **FFX-CLB-90-727-U-PG-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981371
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-90-727-U-PG-T5
Description:	FAIRFAX POST TOP FIXTURE w/ PRISMATIC GLOBE
Light Source:	(4) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	13947.9 lumens
Efficiency:	N/A
Efficacy:	154.0 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.58' x H: 1.5')
IES Classification:	Type V - Short
BUG Rating:	B3 - U5 - G5


Input Watts (W):	90.6
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	5.42%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981371
CATALOG NUMBER: FFX-CLB-90-727-U-PG-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 1.9 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981371
CATALOG NUMBER: FFX-CLB-90-727-U-PG-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981371
CATALOG NUMBER: FFX-CLB-90-727-U-PG-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4095.2	2878.8	6974.0
	% Fixture	29.4	20.6	50.0
Street Side	Lumens	4095.2	2878.8	6974.0
	% Fixture	29.4	20.6	50.0
Total	Lumens	8190.4	5757.6	13947.9
	% Fixture	58.7	41.3	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.7	0.1
10°-20°	26.2	0.2
20°-30°	123.6	0.9
30°-40°	438.0	3.1
40°-50°	899.9	6.5
50°-60°	1369.4	9.8
60°-70°	1694.2	12.1
70°-80°	1808.4	13.0
80°-90°	1821.9	13.1
90°-100°	1696.5	12.2
100°-110°	1525.2	10.9
110°-120°	1051.3	7.5
120°-130°	725.6	5.2
130°-140°	420.4	3.0
140°-150°	200.0	1.4
150°-160°	87.4	0.6
160°-170°	39.0	0.3
170°-180°	12.2	0.1
0°-90°	8.190.4	58.7
0°-180°	13947.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981371
CATALOG NUMBER: FFX-CLB-90-727-U-PG-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	79.3	0.6			
FM	(30°-60°)	1353.6	9.7			
FH	(60°-80°)	1751.3	12.6			G1/1800
FVH	(80°-90°)	911.0	6.5			G5
BL	(0°-30°)	79.3	0.6	B0/110		
BM	(30°-60°)	1353.6	9.7	B2/2500		
BH	(60°-80°)	1751.3	12.6	B3/2500		G1/1800
BVH	(80°-90°)	911.0	6.5			G5
UL	(90°-100°)	1696.5	12.2		U5	
UH	(100°-180°)	4061.1	29.1		U5	

BUG Rating: B3-U5-G5
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981371
CATALOG NUMBER: FFX-CLB-90-727-U-PG-T5

CANDELA DISTRIBUTION (FULL):

	0°
0°	106.2
2.5°	104.4
5°	96.6
7.5°	86.2
10°	85.3
12.5°	82.7
15°	83.5
17.5°	94.0
20°	121.8
22.5°	173.2
25°	243.7
27.5°	332.4
30°	441.2
32.5°	559.6
35°	686.6
37.5°	813.7
40°	939.0
42.5°	1055.6
45°	1160.9
47.5°	1259.2
50°	1360.2
52.5°	1451.6
55°	1532.5
57.5°	1602.1
60°	1655.2
62.5°	1689.1
65°	1712.6
67.5°	1730.0
70°	1731.8
72.5°	1722.2
75°	1710.0
77.5°	1697.8
80°	1684.8
82.5°	1670.0
85°	1656.9
87.5°	1676.1
90°	1668.2
92.5°	1656.1
95°	1592.5
97.5°	1435.0
100°	1400.2
102.5°	1541.2
105°	1541.2
107.5°	1361.9
110°	1237.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981371
CATALOG NUMBER: FFX-CLB-90-727-U-PG-T5

CANDELA DISTRIBUTION (continued):

	0°
112.5°	*1122.6*
115°	*1041.7*
117.5°	*982.5*
120°	*926.8*
122.5°	*870.2*
125°	*808.4*
127.5°	*744.9*
130°	*677.0*
132.5°	*603.9*
135°	*535.2*
137.5°	*472.5*
140°	*413.4*
142.5°	*358.5*
145°	*309.8*
147.5°	*268.0*
150°	*233.2*
152.5°	*205.4*
155°	*182.7*
157.5°	*165.3*
160°	*151.4*
162.5°	*141.0*
165°	*134.9*
167.5°	*130.5*
170°	*128.8*
172.5°	*127.9*
175°	*127.1*
177.5°	*127.1*
180°	*127.1*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-3

Test Date: 03/21/2025

Luminaire Tested: FFX-CLB-100-727-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-727-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-727-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	2726	CRI (Ra):	72.7		
CIE u':	0.2616	R1:	69.3	R9:	-32.4
CIE v':	0.5257	R2:	86.2	R10:	70.6
Duv:	-0.0008	R3:	92.5	R11:	63.6
CIE x:	0.4564	R4:	67.2	R12:	64.8
CIE y:	0.4077	R5:	69.7	R13:	72.8
CIE z:	0.1358	R6:	82.9	R14:	96.1
Peak Wavelength (nm):	599	R7:	74.2	R15:	60.3
Dominant Wavelength (nm):	584	R8:	39.5		
Purity:	59.39437				

Rf:	77.8
Rg:	93.1



Test Conditions


Stabilization Time:	75M
Operation Time:	2H 15M
Sphere Temperature (°C):	24.9

REPORT NUMBER: SP1-2501-332-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2726K
CIE x = 0.4564
CIE y = 0.4077
Duv = -0.0008

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	172	NR	620	849	NR	750	22	NR	880	1	NR
365	0	NR	495	205	NR	625	786	NR	755	19	NR	885	0	NR
370	0	NR	500	239	NR	630	724	NR	760	17	NR	890	0	NR
375	0	NR	505	268	NR	635	659	NR	765	14	NR	895	0	NR
380	0	NR	510	291	NR	640	594	NR	770	12	NR	900	0	NR
385	0	NR	515	313	NR	645	533	NR	775	10	NR	905	0	NR
390	0	NR	520	332	NR	650	472	NR	780	9	NR	910	0	NR
395	1	NR	525	352	NR	655	416	NR	785	8	NR	915	0	NR
400	3	NR	530	374	NR	660	364	NR	790	7	NR	920	0	NR
405	5	NR	535	399	NR	665	317	NR	795	6	NR	925	0	NR
410	10	NR	540	432	NR	670	275	NR	800	5	NR	930	0	NR
415	18	NR	545	471	NR	675	238	NR	805	4	NR	935	0	NR
420	31	NR	550	513	NR	680	206	NR	810	4	NR	940	0	NR
425	52	NR	555	565	NR	685	177	NR	815	3	NR	945	0	NR
430	86	NR	560	628	NR	690	151	NR	820	3	NR	950	0	NR
435	134	NR	565	693	NR	695	130	NR	825	2	NR	955	0	NR
440	207	NR	570	763	NR	700	111	NR	830	2	NR	960	0	NR
445	330	NR	575	829	NR	705	94	NR	835	2	NR	965	0	NR
450	415	NR	580	893	NR	710	80	NR	840	2	NR	970	0	NR
455	323	NR	585	942	NR	715	68	NR	845	1	NR	975	0	NR
460	228	NR	590	979	NR	720	58	NR	850	1	NR	980	0	NR
465	189	NR	595	996	NR	725	50	NR	855	1	NR	985	0	NR
470	146	NR	600	998	NR	730	43	NR	860	1	NR	990	0	NR
475	125	NR	605	980	NR	735	36	NR	865	1	NR	995	0	NR
480	131	NR	610	947	NR	740	31	NR	870	1	NR	1000	0	NR
485	147	NR	615	902	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.16**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	172	NR	620	849	NR	750	22	NR	880	1	NR
365	0	NR	495	205	NR	625	786	NR	755	19	NR	885	0	NR
370	0	NR	500	239	NR	630	724	NR	760	17	NR	890	0	NR
375	0	NR	505	268	NR	635	659	NR	765	14	NR	895	0	NR
380	0	NR	510	291	NR	640	594	NR	770	12	NR	900	0	NR
385	0	NR	515	313	NR	645	533	NR	775	10	NR	905	0	NR
390	0	NR	520	332	NR	650	472	NR	780	9	NR	910	0	NR
395	1	NR	525	352	NR	655	416	NR	785	8	NR	915	0	NR
400	3	NR	530	374	NR	660	364	NR	790	7	NR	920	0	NR
405	5	NR	535	399	NR	665	317	NR	795	6	NR	925	0	NR
410	10	NR	540	432	NR	670	275	NR	800	5	NR	930	0	NR
415	18	NR	545	471	NR	675	238	NR	805	4	NR	935	0	NR
420	31	NR	550	513	NR	680	206	NR	810	4	NR	940	0	NR
425	52	NR	555	565	NR	685	177	NR	815	3	NR	945	0	NR
430	86	NR	560	628	NR	690	151	NR	820	3	NR	950	0	NR
435	134	NR	565	693	NR	695	130	NR	825	2	NR	955	0	NR
440	207	NR	570	763	NR	700	111	NR	830	2	NR	960	0	NR
445	330	NR	575	829	NR	705	94	NR	835	2	NR	965	0	NR
450	415	NR	580	893	NR	710	80	NR	840	2	NR	970	0	NR
455	323	NR	585	942	NR	715	68	NR	845	1	NR	975	0	NR
460	228	NR	590	979	NR	720	58	NR	850	1	NR	980	0	NR
465	189	NR	595	996	NR	725	50	NR	855	1	NR	985	0	NR
470	146	NR	600	998	NR	730	43	NR	860	1	NR	990	0	NR
475	125	NR	605	980	NR	735	36	NR	865	1	NR	995	0	NR
480	131	NR	610	947	NR	740	31	NR	870	1	NR	1000	0	NR
485	147	NR	615	902	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.15**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	172	NR	620	849	NR	750	22	NR	880	1	NR
365	0	NR	495	205	NR	625	786	NR	755	19	NR	885	0	NR
370	0	NR	500	239	NR	630	724	NR	760	17	NR	890	0	NR
375	0	NR	505	268	NR	635	659	NR	765	14	NR	895	0	NR
380	0	NR	510	291	NR	640	594	NR	770	12	NR	900	0	NR
385	0	NR	515	313	NR	645	533	NR	775	10	NR	905	0	NR
390	0	NR	520	332	NR	650	472	NR	780	9	NR	910	0	NR
395	1	NR	525	352	NR	655	416	NR	785	8	NR	915	0	NR
400	3	NR	530	374	NR	660	364	NR	790	7	NR	920	0	NR
405	5	NR	535	399	NR	665	317	NR	795	6	NR	925	0	NR
410	10	NR	540	432	NR	670	275	NR	800	5	NR	930	0	NR
415	18	NR	545	471	NR	675	238	NR	805	4	NR	935	0	NR
420	31	NR	550	513	NR	680	206	NR	810	4	NR	940	0	NR
425	52	NR	555	565	NR	685	177	NR	815	3	NR	945	0	NR
430	86	NR	560	628	NR	690	151	NR	820	3	NR	950	0	NR
435	134	NR	565	693	NR	695	130	NR	825	2	NR	955	0	NR
440	207	NR	570	763	NR	700	111	NR	830	2	NR	960	0	NR
445	330	NR	575	829	NR	705	94	NR	835	2	NR	965	0	NR
450	415	NR	580	893	NR	710	80	NR	840	2	NR	970	0	NR
455	323	NR	585	942	NR	715	68	NR	845	1	NR	975	0	NR
460	228	NR	590	979	NR	720	58	NR	850	1	NR	980	0	NR
465	189	NR	595	996	NR	725	50	NR	855	1	NR	985	0	NR
470	146	NR	600	998	NR	730	43	NR	860	1	NR	990	0	NR
475	125	NR	605	980	NR	735	36	NR	865	1	NR	995	0	NR
480	131	NR	610	947	NR	740	31	NR	870	1	NR	1000	0	NR
485	147	NR	615	902	NR	745	26	NR	875	1	NR			


REPORT NUMBER: SP1-2501-332-3

TM-30-18


Summary


R_f = 77.8
R_g = 93.1
CIE R_a = 72.7
R_9 = -32.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 72	CES51 = 88	CES76 = 71
CES02 = 63	CES27 = 92	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 91	CES53 = 80	CES78 = 73
CES04 = 71	CES29 = 75	CES54 = 87	CES79 = 88
CES05 = 50	CES30 = 84	CES55 = 86	CES80 = 87
CES06 = 52	CES31 = 78	CES56 = 78	CES81 = 65
CES07 = 42	CES32 = 72	CES57 = 77	CES82 = 94
CES08 = 41	CES33 = 82	CES58 = 79	CES83 = 91
CES09 = 29	CES34 = 84	CES59 = 85	CES84 = 89
CES10 = 77	CES35 = 92	CES60 = 92	CES85 = 73
CES11 = 60	CES36 = 95	CES61 = 83	CES86 = 57
CES12 = 66	CES37 = 92	CES62 = 95	CES87 = 78
CES13 = 44	CES38 = 93	CES63 = 82	CES88 = 79
CES14 = 74	CES39 = 97	CES64 = 72	CES89 = 66
CES15 = 72	CES40 = 94	CES65 = 71	CES90 = 80
CES16 = 48	CES41 = 93	CES66 = 71	CES91 = 83
CES17 = 51	CES42 = 92	CES67 = 69	CES92 = 56
CES18 = 57	CES43 = 82	CES68 = 73	CES93 = 73
CES19 = 73	CES44 = 99	CES69 = 82	CES94 = 49
CES20 = 67	CES45 = 86	CES70 = 70	CES95 = 68
CES21 = 87	CES46 = 82	CES71 = 71	CES96 = 77
CES22 = 80	CES47 = 88	CES72 = 89	CES97 = 81
CES23 = 92	CES48 = 74	CES73 = 64	CES98 = 76
CES24 = 91	CES49 = 82	CES74 = 92	CES99 = 65
CES25 = 73	CES50 = 88	CES75 = 74	





REPORT NUMBER: SP1-2501-332-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-3

TM-30-18

Measure Comparisons





(END OF REPORT)