Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981379

Luminaire Tested: **FFX-CLB-100-730-U-PG-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981379
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-100-730-U-PG-T5
Description:	FAIRFAX POST TOP FIXTURE w/ PRISMATIC GLOBE
Light Source:	(4) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	15570.8 lumens
Efficiency:	N/A
Efficacy:	160.5 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.58' x H: 1.5')
IES Classification:	Type V - Short
BUG Rating:	B3 - U5 - G5


Input Watts (W):	97
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	5.42%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981379
CATALOG NUMBER: FFX-CLB-100-730-U-PG-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 2.1 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981379
CATALOG NUMBER: FFX-CLB-100-730-U-PG-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981379
CATALOG NUMBER: FFX-CLB-100-730-U-PG-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4571.7	3213.8	7785.4
	% Fixture	29.4	20.6	50.0
Street Side	Lumens	4571.7	3213.8	7785.4
	% Fixture	29.4	20.6	50.0
Total	Lumens	9143.3	6427.5	15570.8
	% Fixture	58.7	41.3	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.7	0.1
10°-20°	29.3	0.2
20°-30°	138.0	0.9
30°-40°	489.0	3.1
40°-50°	1004.6	6.5
50°-60°	1528.7	9.8
60°-70°	1891.4	12.1
70°-80°	2018.8	13.0
80°-90°	2033.9	13.1
90°-100°	1893.8	12.2
100°-110°	1702.7	10.9
110°-120°	1173.6	7.5
120°-130°	810.0	5.2
130°-140°	469.3	3.0
140°-150°	223.3	1.4
150°-160°	97.6	0.6
160°-170°	43.6	0.3
170°-180°	13.6	0.1
0°-90°	9143.3	58.7
0°-180°	15570.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981379
CATALOG NUMBER: FFX-CLB-100-730-U-PG-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	88.5	0.6			
FM	(30°-60°)	1511.1	9.7			
FH	(60°-80°)	1955.1	12.6			G2/5000
FVH	(80°-90°)	1017.0	6.5			G5
BL	(0°-30°)	88.5	0.6	B0/110		
BM	(30°-60°)	1511.1	9.7	B2/2500		
BH	(60°-80°)	1955.1	12.6	B3/2500		G2/5000
BVH	(80°-90°)	1017.0	6.5			G5
UL	(90°-100°)	1893.8	12.2		U5	
UH	(100°-180°)	4533.7	29.1		U5	

BUG Rating: B3-U5-G5
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981379
CATALOG NUMBER: FFX-CLB-100-730-U-PG-T5

CANDELA DISTRIBUTION (FULL):

	0°
0°	118.5
2.5°	116.6
5°	107.8
7.5°	96.2
10°	95.2
12.5°	92.3
15°	93.3
17.5°	104.9
20°	136.0
22.5°	193.3
25°	272.0
27.5°	371.1
30°	492.5
32.5°	624.7
35°	766.5
37.5°	908.3
40°	1048.2
42.5°	1178.4
45°	1296.0
47.5°	1405.7
50°	1518.4
52.5°	1620.4
55°	1710.8
57.5°	1788.5
60°	1847.8
62.5°	1885.7
65°	1911.9
67.5°	1931.3
70°	1933.3
72.5°	1922.6
75°	1909.0
77.5°	1895.4
80°	1880.8
82.5°	1864.3
85°	1849.7
87.5°	1871.1
90°	1862.3
92.5°	1848.7
95°	1777.8
97.5°	1602.0
100°	1563.1
102.5°	1720.5
105°	1720.5
107.5°	1520.4
110°	1381.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981379
CATALOG NUMBER: FFX-CLB-100-730-U-PG-T5

CANDELA DISTRIBUTION (continued):

	0°
112.5°	*1253.2*
115°	*1162.9*
117.5°	*1096.8*
120°	*1034.6*
122.5°	*971.5*
125°	*902.5*
127.5°	*831.6*
130°	*755.8*
132.5°	*674.2*
135°	*597.5*
137.5°	*527.5*
140°	*461.5*
142.5°	*400.3*
145°	*345.8*
147.5°	*299.2*
150°	*260.4*
152.5°	*229.3*
155°	*204.0*
157.5°	*184.6*
160°	*169.0*
162.5°	*157.4*
165°	*150.6*
167.5°	*145.7*
170°	*143.8*
172.5°	*142.8*
175°	*141.8*
177.5°	*141.8*
180°	*141.8*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-4

Test Date: 03/21/2025

Luminaire Tested: FFX-CLB-100-730-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-730-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-730-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	3061	CRI (Ra):	71.7		
CIE u':	0.2489	R1:	67.8	R9:	-40.3
CIE v':	0.5187	R2:	85.0	R10:	67.2
Duv:	-0.0011	R3:	92.9	R11:	61.6
CIE x:	0.4312	R4:	66.0	R12:	59.9
CIE y:	0.3995	R5:	68.5	R13:	71.4
CIE z:	0.1693	R6:	80.2	R14:	96.3
Peak Wavelength (nm):	592	R7:	74.5	R15:	58.8
Dominant Wavelength (nm):	582	R8:	39.0		
Purity:	49.32381				

Rf:	76.8
Rg:	92.2



Test Conditions


Stabilization Time:	56M
Operation Time:	1H 56M
Sphere Temperature (°C):	24.8

REPORT NUMBER: SP1-2501-332-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3061K
CIE x = 0.4312
CIE y = 0.3995
Duv = -0.0011

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			


REPORT NUMBER: SP1-2501-332-4

TM-30-18


Summary


R_f = 76.8
R_g = 92.2
CIE R_a = 71.7
R_9 = -40.3


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 71	CES51 = 88	CES76 = 68
CES02 = 62	CES27 = 92	CES52 = 85	CES77 = 80
CES03 = 31	CES28 = 90	CES53 = 79	CES78 = 70
CES04 = 71	CES29 = 75	CES54 = 86	CES79 = 88
CES05 = 49	CES30 = 87	CES55 = 84	CES80 = 87
CES06 = 51	CES31 = 79	CES56 = 76	CES81 = 69
CES07 = 41	CES32 = 72	CES57 = 76	CES82 = 94
CES08 = 40	CES33 = 84	CES58 = 77	CES83 = 92
CES09 = 29	CES34 = 83	CES59 = 84	CES84 = 88
CES10 = 76	CES35 = 91	CES60 = 90	CES85 = 73
CES11 = 59	CES36 = 92	CES61 = 81	CES86 = 60
CES12 = 65	CES37 = 91	CES62 = 91	CES87 = 77
CES13 = 43	CES38 = 97	CES63 = 81	CES88 = 79
CES14 = 74	CES39 = 98	CES64 = 69	CES89 = 66
CES15 = 71	CES40 = 94	CES65 = 69	CES90 = 80
CES16 = 47	CES41 = 95	CES66 = 67	CES91 = 79
CES17 = 50	CES42 = 92	CES67 = 65	CES92 = 53
CES18 = 56	CES43 = 83	CES68 = 70	CES93 = 71
CES19 = 73	CES44 = 99	CES69 = 78	CES94 = 47
CES20 = 66	CES45 = 87	CES70 = 66	CES95 = 65
CES21 = 87	CES46 = 83	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 91	CES72 = 87	CES97 = 81
CES23 = 92	CES48 = 75	CES73 = 60	CES98 = 76
CES24 = 91	CES49 = 83	CES74 = 94	CES99 = 63
CES25 = 73	CES50 = 87	CES75 = 70	





REPORT NUMBER: SP1-2501-332-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-4

TM-30-18

Measure Comparisons





(END OF REPORT)