Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981342

Luminaire Tested: **FFX-CLB-20-730-U-FG-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981342
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-20-730-U-FG-T5
Description:	FAIRFAX POST TOP FIXTURE w/ FROSTED GLOBE
Light Source:	(6) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3462.3 lumens
Efficiency:	N/A
Efficacy:	174.9 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.58' x H: 1.5')
IES Classification:	Type V - Short
BUG Rating:	B1 - U5 - G2

Input Watts (W):	19.8
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	9.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981342
CATALOG NUMBER: FFX-CLB-20-730-U-FG-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 0.6 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981342
CATALOG NUMBER: FFX-CLB-20-730-U-FG-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981342
CATALOG NUMBER: FFX-CLB-20-730-U-FG-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	973.8	757.4	1731.2
	% Fixture	28.1	21.9	50.0
Street Side	Lumens	973.8	757.4	1731.2
	% Fixture	28.1	21.9	50.0
Total	Lumens	1947.6	1514.8	3462.3
	% Fixture	56.3	43.7	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4.8	0.1
10°-20°	28.3	0.8
20°-30°	75.7	2.2
30°-40°	145.7	4.2
40°-50°	226.8	6.5
50°-60°	301.4	8.7
60°-70°	359.2	10.4
70°-80°	396.1	11.4
80°-90°	409.7	11.8
90°-100°	396.5	11.5
100°-110°	356.5	10.3
110°-120°	290.4	8.4
120°-130°	208.8	6.0
130°-140°	132.5	3.8
140°-150°	73.5	2.1
150°-160°	36.0	1.0
160°-170°	15.9	0.5
170°-180°	4.5	0.1
0°-90°	1947.6	56.3
0°-180°	3462.3	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981342
CATALOG NUMBER: FFX-CLB-20-730-U-FG-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	54.4	1.6			
FM	(30°-60°)	336.9	9.7			
FH	(60°-80°)	377.7	10.9			G0/660
FVH	(80°-90°)	204.8	5.9			G2/225
BL	(0°-30°)	54.4	1.6	B0/110		
BM	(30°-60°)	336.9	9.7	B1/1000		
BH	(60°-80°)	377.7	10.9	B1/500		G0/660
BVH	(80°-90°)	204.8	5.9			G2/225
UL	(90°-100°)	396.5	11.5		U3/500	
UH	(100°-180°)	1118.2	32.3		U5	

BUG Rating: B1-U5-G2
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981342
CATALOG NUMBER: FFX-CLB-20-730-U-FG-T5

CANDELA DISTRIBUTION (FULL):

	0°
0°	38.2
2.5°	36.9
5°	41.3
7.5°	51.8
10°	65.4
12.5°	80.1
15°	96.5
17.5°	112.6
20°	128.6
22.5°	144.7
25°	161.3
27.5°	178.3
30°	195.7
32.5°	213.3
35°	231.1
37.5°	247.9
40°	264.3
42.5°	279.0
45°	293.0
47.5°	305.6
50°	317.3
52.5°	327.4
55°	336.2
57.5°	344.4
60°	351.3
62.5°	357.2
65°	362.4
67.5°	366.6
70°	370.0
72.5°	372.9
75°	375.0
77.5°	376.3
80°	377.1
82.5°	376.9
85°	376.1
87.5°	374.4
90°	371.9
92.5°	368.5
95°	363.9
97.5°	358.9
100°	352.8
102.5°	345.7
105°	337.5
107.5°	328.5
110°	318.4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981342
CATALOG NUMBER: FFX-CLB-20-730-U-FG-T5

CANDELA DISTRIBUTION (continued):

	0°
112.5°	*306.4*
115°	*293.2*
117.5°	*278.5*
120°	*263.4*
122.5°	*247.9*
125°	*232.0*
127.5°	*216.7*
130°	*200.9*
132.5°	*185.2*
135°	*169.7*
137.5°	*155.4*
140°	*141.2*
142.5°	*127.9*
145°	*115.6*
147.5°	*103.8*
150°	*93.3*
152.5°	*84.1*
155°	*75.9*
157.5°	*69.0*
160°	*63.1*
162.5°	*58.5*
165°	*54.7*
167.5°	*51.8*
170°	*49.7*
172.5°	*47.8*
175°	*46.6*
177.5°	*45.9*
180°	*45.5*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-4

Test Date: 03/21/2025

Luminaire Tested: FFX-CLB-100-730-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-730-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-730-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	3061	CRI (Ra):	71.7		
CIE u':	0.2489	R1:	67.8	R9:	-40.3
CIE v':	0.5187	R2:	85.0	R10:	67.2
Duv:	-0.0011	R3:	92.9	R11:	61.6
CIE x:	0.4312	R4:	66.0	R12:	59.9
CIE y:	0.3995	R5:	68.5	R13:	71.4
CIE z:	0.1693	R6:	80.2	R14:	96.3
Peak Wavelength (nm):	592	R7:	74.5	R15:	58.8
Dominant Wavelength (nm):	582	R8:	39.0		
Purity:	49.32381				

Rf:	76.8
Rg:	92.2



Test Conditions


Stabilization Time:	56M
Operation Time:	1H 56M
Sphere Temperature (°C):	24.8

REPORT NUMBER: SP1-2501-332-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3061K
CIE x = 0.4312
CIE y = 0.3995
Duv = -0.0011

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			


REPORT NUMBER: SP1-2501-332-4

TM-30-18


Summary


R_f = 76.8
R_g = 92.2
CIE R_a = 71.7
R_9 = -40.3


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 71	CES51 = 88	CES76 = 68
CES02 = 62	CES27 = 92	CES52 = 85	CES77 = 80
CES03 = 31	CES28 = 90	CES53 = 79	CES78 = 70
CES04 = 71	CES29 = 75	CES54 = 86	CES79 = 88
CES05 = 49	CES30 = 87	CES55 = 84	CES80 = 87
CES06 = 51	CES31 = 79	CES56 = 76	CES81 = 69
CES07 = 41	CES32 = 72	CES57 = 76	CES82 = 94
CES08 = 40	CES33 = 84	CES58 = 77	CES83 = 92
CES09 = 29	CES34 = 83	CES59 = 84	CES84 = 88
CES10 = 76	CES35 = 91	CES60 = 90	CES85 = 73
CES11 = 59	CES36 = 92	CES61 = 81	CES86 = 60
CES12 = 65	CES37 = 91	CES62 = 91	CES87 = 77
CES13 = 43	CES38 = 97	CES63 = 81	CES88 = 79
CES14 = 74	CES39 = 98	CES64 = 69	CES89 = 66
CES15 = 71	CES40 = 94	CES65 = 69	CES90 = 80
CES16 = 47	CES41 = 95	CES66 = 67	CES91 = 79
CES17 = 50	CES42 = 92	CES67 = 65	CES92 = 53
CES18 = 56	CES43 = 83	CES68 = 70	CES93 = 71
CES19 = 73	CES44 = 99	CES69 = 78	CES94 = 47
CES20 = 66	CES45 = 87	CES70 = 66	CES95 = 65
CES21 = 87	CES46 = 83	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 91	CES72 = 87	CES97 = 81
CES23 = 92	CES48 = 75	CES73 = 60	CES98 = 76
CES24 = 91	CES49 = 83	CES74 = 94	CES99 = 63
CES25 = 73	CES50 = 87	CES75 = 70	





REPORT NUMBER: SP1-2501-332-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-4

TM-30-18

Measure Comparisons





(END OF REPORT)