Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981383

Luminaire Tested: **FFX-CLB-60-730-U-PG-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981383
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-60-730-U-PG-T5
Description:	FAIRFAX POST TOP FIXTURE w/ PRISMATIC GLOBE
Light Source:	(4) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	9818.8 lumens
Efficiency:	N/A
Efficacy:	162.0 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.58' x H: 1.5')
IES Classification:	Type V - Short
BUG Rating:	B3 - U5 - G4

Input Watts (W):	60.6
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	8.53%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981383
CATALOG NUMBER: FFX-CLB-60-730-U-PG-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 1.3 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981383
CATALOG NUMBER: FFX-CLB-60-730-U-PG-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981383
CATALOG NUMBER: FFX-CLB-60-730-U-PG-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2882.9	2026.6	4909.4
	% Fixture	29.4	20.6	50.0
Street Side	Lumens	2882.9	2026.6	4909.4
	% Fixture	29.4	20.6	50.0
Total	Lumens	5765.7	4053.1	9818.8
	% Fixture	58.7	41.3	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.1	0.1
10°-20°	18.5	0.2
20°-30°	87.0	0.9
30°-40°	308.4	3.1
40°-50°	633.5	6.5
50°-60°	963.9	9.8
60°-70°	1192.7	12.1
70°-80°	1273.1	13.0
80°-90°	1282.6	13.1
90°-100°	1194.3	12.2
100°-110°	1073.7	10.9
110°-120°	740.1	7.5
120°-130°	510.8	5.2
130°-140°	296.0	3.0
140°-150°	140.8	1.4
150°-160°	61.5	0.6
160°-170°	27.5	0.3
170°-180°	8.6	0.1
0°-90°	5765.7	58.7
0°-180°	9818.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981383
CATALOG NUMBER: FFX-CLB-60-730-U-PG-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	55.8	0.6			
FM	(30°-60°)	952.9	9.7			
FH	(60°-80°)	1232.9	12.6			G1/1800
FVH	(80°-90°)	641.3	6.5			G4/750
BL	(0°-30°)	55.8	0.6	B0/110		
BM	(30°-60°)	952.9	9.7	B1/1000		
BH	(60°-80°)	1232.9	12.6	B3/2500		G1/1800
BVH	(80°-90°)	641.3	6.5			G4/750
UL	(90°-100°)	1194.3	12.2		U5	
UH	(100°-180°)	2858.9	29.1		U5	

BUG Rating: B3-U5-G4
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981383
CATALOG NUMBER: FFX-CLB-60-730-U-PG-T5

CANDELA DISTRIBUTION (FULL):

	0°
0°	74.7
2.5°	73.5
5°	68.0
7.5°	60.6
10°	60.0
12.5°	58.2
15°	58.8
17.5°	66.2
20°	85.8
22.5°	121.9
25°	171.5
27.5°	234.0
30°	310.6
32.5°	393.9
35°	483.4
37.5°	572.8
40°	661.0
42.5°	743.1
45°	817.2
47.5°	886.5
50°	957.5
52.5°	1021.8
55°	1078.8
57.5°	1127.8
60°	1165.2
62.5°	1189.1
65°	1205.6
67.5°	1217.9
70°	1219.1
72.5°	1212.4
75°	1203.8
77.5°	1195.2
80°	1186.0
82.5°	1175.6
85°	1166.4
87.5°	1179.9
90°	1174.4
92.5°	1165.8
95°	1121.1
97.5°	1010.2
100°	985.7
102.5°	1084.9
105°	1084.9
107.5°	958.7
110°	871.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981383
CATALOG NUMBER: FFX-CLB-60-730-U-PG-T5

CANDELA DISTRIBUTION (continued):

	0°
112.5°	*790.3*
115°	*733.3*
117.5°	*691.6*
120°	*652.4*
122.5°	*612.6*
125°	*569.1*
127.5°	*524.4*
130°	*476.6*
132.5°	*425.2*
135°	*376.8*
137.5°	*332.7*
140°	*291.0*
142.5°	*252.4*
145°	*218.1*
147.5°	*188.7*
150°	*164.2*
152.5°	*144.6*
155°	*128.6*
157.5°	*116.4*
160°	*106.6*
162.5°	*99.2*
165°	*95.0*
167.5°	*91.9*
170°	*90.7*
172.5°	*90.1*
175°	*89.4*
177.5°	*89.4*
180°	*89.4*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-4

Test Date: 03/21/2025

Luminaire Tested: FFX-CLB-100-730-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-730-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-730-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	3061	CRI (Ra):	71.7		
CIE u':	0.2489	R1:	67.8	R9:	-40.3
CIE v':	0.5187	R2:	85.0	R10:	67.2
Duv:	-0.0011	R3:	92.9	R11:	61.6
CIE x:	0.4312	R4:	66.0	R12:	59.9
CIE y:	0.3995	R5:	68.5	R13:	71.4
CIE z:	0.1693	R6:	80.2	R14:	96.3
Peak Wavelength (nm):	592	R7:	74.5	R15:	58.8
Dominant Wavelength (nm):	582	R8:	39.0		
Purity:	49.32381				

Rf:	76.8
Rg:	92.2



Test Conditions


Stabilization Time:	56M
Operation Time:	1H 56M
Sphere Temperature (°C):	24.8

REPORT NUMBER: SP1-2501-332-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3061K
CIE x = 0.4312
CIE y = 0.3995
Duv = -0.0011

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			


REPORT NUMBER: SP1-2501-332-4

TM-30-18


Summary


R_f = 76.8
R_g = 92.2
CIE R_a = 71.7
R_9 = -40.3


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 71	CES51 = 88	CES76 = 68
CES02 = 62	CES27 = 92	CES52 = 85	CES77 = 80
CES03 = 31	CES28 = 90	CES53 = 79	CES78 = 70
CES04 = 71	CES29 = 75	CES54 = 86	CES79 = 88
CES05 = 49	CES30 = 87	CES55 = 84	CES80 = 87
CES06 = 51	CES31 = 79	CES56 = 76	CES81 = 69
CES07 = 41	CES32 = 72	CES57 = 76	CES82 = 94
CES08 = 40	CES33 = 84	CES58 = 77	CES83 = 92
CES09 = 29	CES34 = 83	CES59 = 84	CES84 = 88
CES10 = 76	CES35 = 91	CES60 = 90	CES85 = 73
CES11 = 59	CES36 = 92	CES61 = 81	CES86 = 60
CES12 = 65	CES37 = 91	CES62 = 91	CES87 = 77
CES13 = 43	CES38 = 97	CES63 = 81	CES88 = 79
CES14 = 74	CES39 = 98	CES64 = 69	CES89 = 66
CES15 = 71	CES40 = 94	CES65 = 69	CES90 = 80
CES16 = 47	CES41 = 95	CES66 = 67	CES91 = 79
CES17 = 50	CES42 = 92	CES67 = 65	CES92 = 53
CES18 = 56	CES43 = 83	CES68 = 70	CES93 = 71
CES19 = 73	CES44 = 99	CES69 = 78	CES94 = 47
CES20 = 66	CES45 = 87	CES70 = 66	CES95 = 65
CES21 = 87	CES46 = 83	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 91	CES72 = 87	CES97 = 81
CES23 = 92	CES48 = 75	CES73 = 60	CES98 = 76
CES24 = 91	CES49 = 83	CES74 = 94	CES99 = 63
CES25 = 73	CES50 = 87	CES75 = 70	





REPORT NUMBER: SP1-2501-332-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-4

TM-30-18

Measure Comparisons





(END OF REPORT)