Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981335

Luminaire Tested: **FFX-CLB-90-730-U-FG-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981335
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-90-730-U-FG-T5
Description:	FAIRFAX POST TOP FIXTURE w/ FROSTED GLOBE
Light Source:	(6) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	15169.3 lumens
Efficiency:	N/A
Efficacy:	167.4 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.58' x H: 1.5')
IES Classification:	Type V - Short
BUG Rating:	B3 - U5 - G5


Input Watts (W):	90.6
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	5.42%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981335
CATALOG NUMBER: FFX-CLB-90-730-U-FG-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 2.5 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981335
CATALOG NUMBER: FFX-CLB-90-730-U-FG-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981335
CATALOG NUMBER: FFX-CLB-90-730-U-FG-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4266.4	3318.2	7584.6
	% Fixture	28.1	21.9	50.0
Street Side	Lumens	4266.4	3318.2	7584.6
	% Fixture	28.1	21.9	50.0
Total	Lumens	8532.8	6636.5	15169.3
	% Fixture	56.3	43.7	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.9	0.1
10°-20°	124.0	0.8
20°-30°	331.7	2.2
30°-40°	638.3	4.2
40°-50°	993.5	6.5
50°-60°	1320.3	8.7
60°-70°	1573.6	10.4
70°-80°	1735.7	11.4
80°-90°	1794.8	11.8
90°-100°	1737.3	11.5
100°-110°	1561.6	10.3
110°-120°	1272.6	8.4
120°-130°	915.0	6.0
130°-140°	580.7	3.8
140°-150°	322.2	2.1
150°-160°	157.6	1.0
160°-170°	69.6	0.5
170°-180°	19.9	0.1
0°-90°	8532.8	56.3
0°-180°	15169.3	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981335
CATALOG NUMBER: FFX-CLB-90-730-U-FG-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	238.3	1.6			
FM	(30°-60°)	1476.1	9.7			
FH	(60°-80°)	1654.6	10.9			G1/1800
FVH	(80°-90°)	897.4	5.9			G5
BL	(0°-30°)	238.3	1.6	B1/500		
BM	(30°-60°)	1476.1	9.7	B2/2500		
BH	(60°-80°)	1654.6	10.9	B3/2500		G1/1800
BVH	(80°-90°)	897.4	5.9			G5
UL	(90°-100°)	1737.3	11.5		U5	
UH	(100°-180°)	4899.2	32.3		U5	

BUG Rating: B3-U5-G5
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981335
CATALOG NUMBER: FFX-CLB-90-730-U-FG-T5

CANDELA DISTRIBUTION (FULL):

	0°
0°	167.2
2.5°	161.7
5°	181.0
7.5°	227.0
10°	286.7
12.5°	351.0
15°	422.7
17.5°	493.5
20°	563.3
22.5°	634.1
25°	706.7
27.5°	781.1
30°	857.4
32.5°	934.5
35°	1012.7
37.5°	1086.2
40°	1157.8
42.5°	1222.2
45°	1283.7
47.5°	1338.9
50°	1390.3
52.5°	1434.4
55°	1473.0
57.5°	1508.9
60°	1539.2
62.5°	1564.9
65°	1587.9
67.5°	1606.3
70°	1621.0
72.5°	1633.9
75°	1643.0
77.5°	1648.6
80°	1652.2
82.5°	1651.3
85°	1647.6
87.5°	1640.3
90°	1629.3
92.5°	1614.6
95°	1594.3
97.5°	1572.3
100°	1545.6
102.5°	1514.4
105°	1478.6
107.5°	1439.0
110°	1394.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981335
CATALOG NUMBER: FFX-CLB-90-730-U-FG-T5

CANDELA DISTRIBUTION (continued):

	0°
112.5°	*1342.6*
115°	*1284.7*
117.5°	*1220.3*
120°	*1154.2*
122.5°	*1086.2*
125°	*1016.3*
127.5°	*949.3*
130°	*880.3*
132.5°	*811.4*
135°	*743.4*
137.5°	*680.9*
140°	*618.4*
142.5°	*560.5*
145°	*506.3*
147.5°	*454.9*
150°	*408.9*
152.5°	*368.5*
155°	*332.7*
157.5°	*302.3*
160°	*276.6*
162.5°	*256.4*
165°	*239.8*
167.5°	*227.0*
170°	*217.8*
172.5°	*209.5*
175°	*204.0*
177.5°	*201.2*
180°	*199.4*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-4

Test Date: 03/21/2025

Luminaire Tested: FFX-CLB-100-730-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-730-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-730-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	3061	CRI (Ra):	71.7		
CIE u':	0.2489	R1:	67.8	R9:	-40.3
CIE v':	0.5187	R2:	85.0	R10:	67.2
Duv:	-0.0011	R3:	92.9	R11:	61.6
CIE x:	0.4312	R4:	66.0	R12:	59.9
CIE y:	0.3995	R5:	68.5	R13:	71.4
CIE z:	0.1693	R6:	80.2	R14:	96.3
Peak Wavelength (nm):	592	R7:	74.5	R15:	58.8
Dominant Wavelength (nm):	582	R8:	39.0		
Purity:	49.32381				

Rf:	76.8
Rg:	92.2



Test Conditions


Stabilization Time:	56M
Operation Time:	1H 56M
Sphere Temperature (°C):	24.8

REPORT NUMBER: SP1-2501-332-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3061K
CIE x = 0.4312
CIE y = 0.3995
Duv = -0.0011

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2501-332-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	207	NR	620	786	NR	750	18	NR	880	0	NR
365	0	NR	495	241	NR	625	718	NR	755	15	NR	885	0	NR
370	0	NR	500	277	NR	630	654	NR	760	13	NR	890	0	NR
375	0	NR	505	309	NR	635	588	NR	765	11	NR	895	0	NR
380	0	NR	510	333	NR	640	523	NR	770	10	NR	900	0	NR
385	0	NR	515	356	NR	645	465	NR	775	8	NR	905	0	NR
390	0	NR	520	376	NR	650	407	NR	780	7	NR	910	0	NR
395	2	NR	525	398	NR	655	356	NR	785	6	NR	915	0	NR
400	4	NR	530	422	NR	660	308	NR	790	5	NR	920	0	NR
405	6	NR	535	450	NR	665	267	NR	795	5	NR	925	0	NR
410	12	NR	540	486	NR	670	229	NR	800	4	NR	930	0	NR
415	22	NR	545	530	NR	675	197	NR	805	3	NR	935	0	NR
420	39	NR	550	577	NR	680	169	NR	810	3	NR	940	0	NR
425	68	NR	555	633	NR	685	145	NR	815	3	NR	945	0	NR
430	111	NR	560	700	NR	690	123	NR	820	2	NR	950	0	NR
435	175	NR	565	766	NR	695	105	NR	825	2	NR	955	0	NR
440	269	NR	570	832	NR	700	89	NR	830	2	NR	960	0	NR
445	434	NR	575	893	NR	705	76	NR	835	2	NR	965	0	NR
450	579	NR	580	945	NR	710	64	NR	840	1	NR	970	0	NR
455	468	NR	585	979	NR	715	55	NR	845	1	NR	975	0	NR
460	320	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	264	NR	595	998	NR	725	40	NR	855	1	NR	985	0	NR
470	204	NR	600	981	NR	730	33	NR	860	1	NR	990	0	NR
475	164	NR	605	949	NR	735	28	NR	865	1	NR	995	0	NR
480	166	NR	610	903	NR	740	24	NR	870	1	NR	1000	0	NR
485	183	NR	615	847	NR	745	21	NR	875	1	NR			


REPORT NUMBER: SP1-2501-332-4

TM-30-18


Summary


R_f = 76.8
R_g = 92.2
CIE R_a = 71.7
R_9 = -40.3


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 71	CES51 = 88	CES76 = 68
CES02 = 62	CES27 = 92	CES52 = 85	CES77 = 80
CES03 = 31	CES28 = 90	CES53 = 79	CES78 = 70
CES04 = 71	CES29 = 75	CES54 = 86	CES79 = 88
CES05 = 49	CES30 = 87	CES55 = 84	CES80 = 87
CES06 = 51	CES31 = 79	CES56 = 76	CES81 = 69
CES07 = 41	CES32 = 72	CES57 = 76	CES82 = 94
CES08 = 40	CES33 = 84	CES58 = 77	CES83 = 92
CES09 = 29	CES34 = 83	CES59 = 84	CES84 = 88
CES10 = 76	CES35 = 91	CES60 = 90	CES85 = 73
CES11 = 59	CES36 = 92	CES61 = 81	CES86 = 60
CES12 = 65	CES37 = 91	CES62 = 91	CES87 = 77
CES13 = 43	CES38 = 97	CES63 = 81	CES88 = 79
CES14 = 74	CES39 = 98	CES64 = 69	CES89 = 66
CES15 = 71	CES40 = 94	CES65 = 69	CES90 = 80
CES16 = 47	CES41 = 95	CES66 = 67	CES91 = 79
CES17 = 50	CES42 = 92	CES67 = 65	CES92 = 53
CES18 = 56	CES43 = 83	CES68 = 70	CES93 = 71
CES19 = 73	CES44 = 99	CES69 = 78	CES94 = 47
CES20 = 66	CES45 = 87	CES70 = 66	CES95 = 65
CES21 = 87	CES46 = 83	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 91	CES72 = 87	CES97 = 81
CES23 = 92	CES48 = 75	CES73 = 60	CES98 = 76
CES24 = 91	CES49 = 83	CES74 = 94	CES99 = 63
CES25 = 73	CES50 = 87	CES75 = 70	





REPORT NUMBER: SP1-2501-332-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-4

TM-30-18

Measure Comparisons





(END OF REPORT)