Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981315

Luminaire Tested: **FFX-CLB-20-750-U-VM9-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981315
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-20-750-U-VM9-T5
Description:	FAIRFAX POST TOP FIXTURE w/ ULA ACORN 9 INCH NECK
Light Source:	(6) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3554.2 lumens
Efficiency:	N/A
Efficacy:	179.5 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.33' x H: 2.08')
IES Classification:	Type V - Short
BUG Rating:	B1 - U5 - G2

Input Watts (W):	19.8
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	9.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981315
CATALOG NUMBER: FFX-CLB-20-750-U-VM9-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 0.7 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981315
CATALOG NUMBER: FFX-CLB-20-750-U-VM9-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981315
CATALOG NUMBER: FFX-CLB-20-750-U-VM9-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1052.1	725.0	1777.1
	% Fixture	29.6	20.4	50.0
Street Side	Lumens	1052.1	725.0	1777.1
	% Fixture	29.6	20.4	50.0
Total	Lumens	2104.3	1449.9	3554.2
	% Fixture	59.2	40.8	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4.2	0.1
10°-20°	28.4	0.8
20°-30°	83.4	2.3
30°-40°	169.6	4.8
40°-50°	263.2	7.4
50°-60°	339.9	9.6
60°-70°	390.8	11.0
70°-80°	414.1	11.7
80°-90°	410.7	11.6
90°-100°	381.8	10.7
100°-110°	332.8	9.4
110°-120°	271.8	7.6
120°-130°	201.5	5.7
130°-140°	130.4	3.7
140°-150°	73.8	2.1
150°-160°	36.8	1.0
160°-170°	16.3	0.5
170°-180°	4.6	0.1
0°-90°	2104.3	59.2
0°-180°	3554.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981315
CATALOG NUMBER: FFX-CLB-20-750-U-VM9-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	58.0	1.6			
FM	(30°-60°)	386.3	10.9			
FH	(60°-80°)	402.5	11.3			G0/660
FVH	(80°-90°)	205.3	5.8			G2/225
BL	(0°-30°)	58.0	1.6	B0/110		
BM	(30°-60°)	386.3	10.9	B1/1000		
BH	(60°-80°)	402.5	11.3	B1/500		G0/660
BVH	(80°-90°)	205.3	5.8			G2/225
UL	(90°-100°)	381.8	10.7		U3/500	
UH	(100°-180°)	1068.1	30.1		U5	

BUG Rating: B1-U5-G2
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981315
CATALOG NUMBER: FFX-CLB-20-750-U-VM9-T5

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3
2.5°	28.3	28.3	28.3	28.3	28.0	28.0	28.0	28.0	28.0	28.0	28.0
5°	34.9	34.7	34.7	34.9	34.9	34.9	34.7	34.9	34.5	34.2	34.7
7.5°	46.8	46.8	46.8	46.8	46.4	46.4	47.0	46.6	46.8	46.6	47.0
10°	61.2	61.2	61.0	61.4	61.6	61.4	61.2	61.8	61.4	61.4	61.8
12.5°	77.5	77.7	77.7	78.0	78.4	77.7	78.4	78.4	78.4	78.0	77.7
15°	96.3	96.1	96.5	96.3	95.4	96.3	96.5	96.1	96.3	96.5	96.7
17.5°	113.7	113.5	113.7	113.5	114.4	114.6	114.4	114.4	114.4	114.6	114.2
20°	132.9	133.2	132.5	133.2	133.2	133.6	134.5	134.3	134.5	133.8	133.2
22.5°	153.9	154.1	153.5	153.3	154.6	154.4	154.4	155.0	155.5	155.5	155.0
25°	176.5	176.0	176.0	176.7	176.7	176.5	177.6	178.0	177.8	178.4	178.9
27.5°	199.0	198.5	198.5	199.4	199.4	199.4	199.4	201.4	201.6	202.1	202.3
30°	220.8	222.4	222.4	221.9	222.6	223.7	224.4	224.4	225.0	225.0	225.3
32.5°	244.7	244.7	245.1	245.8	245.8	247.8	246.7	248.4	248.0	249.3	250.2
35°	267.2	267.7	267.7	269.0	269.0	269.4	269.6	270.7	272.3	272.1	272.3
37.5°	288.2	288.0	287.5	289.5	290.0	289.7	290.0	291.7	292.2	292.8	292.4
40°	307.4	306.7	307.8	309.0	309.0	309.4	309.8	310.7	311.6	312.0	312.7
42.5°	323.5	323.3	324.4	325.3	325.5	325.7	325.7	326.4	328.6	329.3	329.7
45°	337.7	337.4	338.8	339.9	340.5	340.5	339.9	340.8	342.7	343.4	343.6
47.5°	349.8	350.0	351.8	353.1	353.6	352.9	352.5	353.3	354.9	356.7	356.4
50°	360.0	360.2	362.2	364.4	364.6	363.9	362.8	363.5	365.7	367.0	367.3
52.5°	368.6	368.8	371.2	373.4	373.7	372.6	371.2	372.3	374.3	375.9	376.3
55°	375.4	376.1	378.5	380.9	381.6	380.1	378.3	379.0	381.2	383.6	383.8
57.5°	380.5	380.7	383.8	386.5	387.4	385.1	383.8	383.8	386.5	388.7	389.1
60°	384.0	384.9	388.5	391.5	392.0	390.0	387.6	388.0	390.9	393.3	394.0
62.5°	387.1	388.0	391.3	395.1	395.5	392.9	390.4	390.7	394.0	396.4	397.3
65°	388.7	389.3	393.3	397.1	397.5	394.9	392.0	392.2	395.3	398.2	398.4
67.5°	389.1	389.8	394.0	398.4	398.6	395.7	392.4	393.1	396.2	399.1	399.5
70°	388.7	389.6	393.8	398.4	398.8	395.3	392.0	392.4	396.0	398.8	399.7
72.5°	387.1	388.2	392.4	397.3	397.5	394.2	390.9	390.9	394.9	398.0	398.4
75°	385.1	386.2	390.9	395.7	396.0	392.4	388.9	389.3	393.1	396.0	396.4
77.5°	382.9	383.6	388.2	393.3	393.8	390.0	386.5	386.9	390.4	393.5	394.0
80°	379.4	380.1	384.9	389.8	390.2	386.5	382.7	383.6	387.1	390.0	390.0
82.5°	375.2	375.6	380.5	385.8	386.0	382.3	379.0	379.4	382.9	385.8	385.8
85°	370.3	371.0	375.9	380.9	380.9	377.4	373.9	374.8	378.1	380.7	381.6
87.5°	365.0	365.3	370.1	374.8	375.0	371.5	368.4	369.0	372.3	374.8	375.0
90°	358.9	359.3	363.9	368.4	368.6	365.0	362.2	363.1	365.7	367.9	368.6
92.5°	352.0	352.7	357.1	361.3	361.1	358.0	355.6	356.7	358.9	361.1	361.1
95°	345.0	345.8	349.4	353.3	352.9	350.3	348.3	349.1	351.4	353.1	353.6
97.5°	337.4	337.7	341.4	344.3	344.3	341.9	340.3	341.0	343.2	344.3	344.7
100°	329.3	329.5	332.4	335.2	335.2	333.0	331.9	332.6	334.3	335.2	335.5
102.5°	321.1	320.9	323.3	325.7	325.7	324.0	323.1	324.4	325.3	326.0	326.4
105°	311.8	311.6	313.8	316.0	315.6	314.5	313.6	314.7	315.8	316.2	316.2
107.5°	301.7	302.5	303.9	305.6	305.4	304.5	304.5	305.2	305.9	306.1	306.3
110°	293.1	292.8	294.2	295.0	295.3	294.8	295.3	295.5	295.7	295.7	295.7

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981315
CATALOG NUMBER: FFX-CLB-20-750-U-VM9-T5

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	283.1	283.1	283.6	284.2	284.4	284.7	284.9	285.8	285.3	285.5	*285.1*
115°	272.3	272.5	273.0	273.2	273.6	273.8	274.9	274.9	275.2	274.7	*274.1*
117.5°	261.5	261.9	261.7	261.5	262.4	263.0	263.7	264.1	264.1	263.2	*262.8*
120°	249.8	249.3	249.3	249.3	250.0	251.1	252.0	252.2	252.0	250.9	*250.7*
122.5°	237.0	237.4	236.7	237.0	237.2	238.7	239.4	239.8	239.2	237.8	*238.3*
125°	223.7	224.2	223.0	223.0	224.2	224.8	225.5	226.1	225.0	224.4	*223.9*
127.5°	209.6	209.6	209.4	208.7	210.0	210.7	212.0	212.0	211.1	210.2	*210.7*
130°	195.2	195.0	195.4	195.0	195.2	196.5	197.7	197.2	196.8	196.3	*196.3*
132.5°	180.4	180.9	180.4	180.2	181.3	181.8	182.9	183.3	182.4	181.3	*181.8*
135°	166.5	166.3	166.1	166.1	166.7	167.8	168.5	168.3	168.3	167.8	*167.4*
137.5°	152.2	152.8	152.4	152.4	152.8	153.9	155.0	154.8	154.6	153.7	*153.3*
140°	139.3	138.9	139.1	139.1	140.2	140.2	141.3	141.3	141.1	140.5	*140.9*
142.5°	126.5	126.3	127.2	126.8	127.2	128.3	128.7	128.5	128.1	128.3	*128.5*
145°	114.8	115.1	114.8	115.1	115.7	116.4	117.3	116.8	116.8	116.2	*115.9*
147.5°	103.8	103.8	103.6	104.5	104.7	105.6	105.8	106.0	105.6	105.1	*105.8*
150°	94.1	93.9	93.9	94.1	94.5	95.2	95.6	95.6	95.8	95.4	*95.2*
152.5°	85.0	84.6	84.8	85.2	85.5	86.1	86.1	86.6	86.3	86.1	*86.1*
155°	76.9	77.1	77.1	77.3	77.7	78.0	78.4	78.2	78.4	78.2	*78.2*
157.5°	70.2	70.7	70.7	70.9	70.7	70.9	71.1	71.3	71.3	71.3	*71.3*
160°	64.9	64.7	64.7	64.7	64.7	64.9	65.4	65.1	65.4	65.1	*64.9*
162.5°	60.1	60.1	60.1	60.1	60.3	60.3	60.3	60.5	60.3	60.3	*60.3*
165°	56.1	56.3	56.1	56.1	56.1	56.3	56.3	56.3	56.3	56.3	*56.3*
167.5°	53.0	53.2	53.2	53.2	53.2	53.2	53.4	53.2	53.2	53.2	*53.2*
170°	50.6	50.8	50.8	50.6	50.8	50.6	50.6	50.8	50.6	50.6	*50.6*
172.5°	48.8	48.8	48.8	48.8	48.8	48.8	48.8	48.8	48.8	48.6	*48.6*
175°	47.3	47.3	47.3	47.3	47.3	47.3	47.3	47.3	47.3	47.3	*47.3*
177.5°	46.4	46.4	46.6	46.4	46.4	46.4	46.4	46.4	46.4	46.4	*46.4*
180°	46.2	46.2	46.2	46.2	46.2	46.2	46.2	46.2	46.2	46.2	*46.2*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-5

Test Date: 03/25/2025

Luminaire Tested: FFX-CLB-100-750-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-750-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-750-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	4987	CRI (Ra):	75.8		
CIE u':	0.2094	R1:	71.6	R9:	-30.4
CIE v':	0.4882	R2:	82.8	R10:	59.9
Duv:	0.0031	R3:	91.2	R11:	70.9
CIE x:	0.3461	R4:	73.8	R12:	51.2
CIE y:	0.3586	R5:	73.0	R13:	74.2
CIE z:	0.2954	R6:	76.1	R14:	95.3
Peak Wavelength (nm):	450	R7:	82.9	R15:	63.7
Dominant Wavelength (nm):	570	R8:	54.9		
Purity:	11.4				

Rf:	78.3
Rg:	93.4



Test Conditions


Stabilization Time:	67M
Operation Time:	2H 7M
Sphere Temperature (°C):	24.9

REPORT NUMBER: SP1-2501-332-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4987K
CIE x = 0.3461
CIE y = 0.3586
Duv = 0.0031

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.87**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.92**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			


REPORT NUMBER: SP1-2501-332-5

TM-30-18


Summary


R_f = 78.3
R_g = 93.4
CIE R_a = 75.8
R_9 = -30.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 71	CES51 = 92	CES76 = 63
CES02 = 60	CES27 = 92	CES52 = 91	CES77 = 76
CES03 = 30	CES28 = 86	CES53 = 83	CES78 = 64
CES04 = 69	CES29 = 75	CES54 = 86	CES79 = 86
CES05 = 46	CES30 = 89	CES55 = 85	CES80 = 84
CES06 = 50	CES31 = 78	CES56 = 79	CES81 = 80
CES07 = 39	CES32 = 71	CES57 = 78	CES82 = 93
CES08 = 38	CES33 = 85	CES58 = 79	CES83 = 93
CES09 = 29	CES34 = 78	CES59 = 88	CES84 = 87
CES10 = 73	CES35 = 88	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 89	CES61 = 84	CES86 = 73
CES12 = 61	CES37 = 86	CES62 = 87	CES87 = 79
CES13 = 41	CES38 = 98	CES63 = 82	CES88 = 81
CES14 = 74	CES39 = 97	CES64 = 72	CES89 = 74
CES15 = 70	CES40 = 93	CES65 = 69	CES90 = 81
CES16 = 46	CES41 = 97	CES66 = 68	CES91 = 76
CES17 = 49	CES42 = 88	CES67 = 66	CES92 = 58
CES18 = 55	CES43 = 85	CES68 = 71	CES93 = 75
CES19 = 71	CES44 = 99	CES69 = 78	CES94 = 54
CES20 = 64	CES45 = 90	CES70 = 65	CES95 = 66
CES21 = 85	CES46 = 87	CES71 = 61	CES96 = 78
CES22 = 77	CES47 = 92	CES72 = 86	CES97 = 88
CES23 = 91	CES48 = 81	CES73 = 57	CES98 = 78
CES24 = 90	CES49 = 86	CES74 = 93	CES99 = 64
CES25 = 71	CES50 = 91	CES75 = 63	





REPORT NUMBER: SP1-2501-332-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-5

TM-30-18

Measure Comparisons





(END OF REPORT)