Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981089

Luminaire Tested: **FFX-CLB-30-750-U-FR-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981089
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-30-750-U-FR-T5
Description:	FAIRFAX POST TOP FIXTURE w/ FAIRFAX REFRACTOR T5 DISTRIBUTION LENS
Light Source:	(6) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5198.7 lumens
Efficiency:	N/A
Efficacy:	169.9 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.17' x H: 1.67')
IES Classification:	Type V - Short
BUG Rating:	B3 - U4 - G2

Input Watts (W):	30.6
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	10.8%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981089
CATALOG NUMBER: FFX-CLB-30-750-U-FR-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 1 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981089
CATALOG NUMBER: FFX-CLB-30-750-U-FR-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981089
CATALOG NUMBER: FFX-CLB-30-750-U-FR-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2105.3	494.0	2599.3
	% Fixture	40.5	9.5	50.0
Street Side	Lumens	2105.3	494.0	2599.3
	% Fixture	40.5	9.5	50.0
Total	Lumens	4210.6	988.1	5198.7
	% Fixture	81.0	19.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	5.4	0.1
10°-20°	28.9	0.6
20°-30°	61.4	1.2
30°-40°	124.2	2.4
40°-50°	277.4	5.3
50°-60°	978.4	18.8
60°-70°	1601.3	30.8
70°-80°	823.8	15.8
80°-90°	309.9	6.0
90°-100°	199.5	3.8
100°-110°	133.0	2.6
110°-120°	142.9	2.7
120°-130°	233.8	4.5
130°-140°	139.9	2.7
140°-150°	72.7	1.4
150°-160°	38.0	0.7
160°-170°	20.6	0.4
170°-180°	7.7	0.1
0°-90°	4210.6	81.0
0°-180°	5198.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981089
CATALOG NUMBER: FFX-CLB-30-750-U-FR-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	47.8	0.9			
FM	(30°-60°)	690.0	13.3			
FH	(60°-80°)	1212.5	23.3			G1/1800
FVH	(80°-90°)	155.0	3.0			G2/225
BL	(0°-30°)	47.8	0.9	B0/110		
BM	(30°-60°)	690.0	13.3	B1/1000		
BH	(60°-80°)	1212.5	23.3	B3/2500		G1/1800
BVH	(80°-90°)	155.0	3.0			G2/225
UL	(90°-100°)	199.5	3.8		U3/500	
UH	(100°-180°)	788.6	15.2		U4/1000	

BUG Rating: B3-U4-G2
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981089
CATALOG NUMBER: FFX-CLB-30-750-U-FR-T5

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3
2.5°	29.6	29.9	30.9	31.6	31.9	31.3	31.6	32.3	32.3	32.6	32.6
5°	43.9	44.3	43.9	43.6	43.3	43.9	44.3	43.9	42.9	43.3	42.9
7.5°	64.9	64.9	62.2	61.6	60.9	63.9	65.6	64.9	61.6	58.6	57.9
10°	79.9	79.5	77.2	74.2	73.9	75.9	80.2	81.2	75.9	72.2	71.5
12.5°	94.8	92.5	91.2	88.2	88.5	89.8	92.8	93.2	89.5	86.5	84.5
15°	103.8	104.2	104.2	102.5	101.8	103.2	104.5	105.5	102.8	100.5	99.2
17.5°	107.8	108.1	109.1	110.1	110.1	109.5	109.5	109.8	109.8	109.8	109.5
20°	116.1	116.5	116.1	116.8	117.8	117.1	116.1	116.5	116.1	116.5	116.1
22.5°	122.8	122.5	122.5	123.5	124.1	123.8	122.8	123.1	122.5	122.8	122.8
25°	129.8	130.1	130.8	131.1	131.4	131.4	131.1	131.8	131.4	130.8	130.8
27.5°	139.4	139.4	139.4	139.4	140.8	140.8	140.1	140.4	139.4	138.8	138.4
30°	148.7	149.1	148.4	149.1	150.4	149.7	149.4	150.1	148.7	148.4	148.4
32.5°	157.4	157.4	157.1	159.1	159.4	158.7	159.7	160.4	161.1	160.7	162.4
35°	172.0	172.7	178.4	183.4	185.0	184.7	186.0	186.7	185.4	185.4	184.4
37.5°	242.9	242.6	234.6	226.9	230.6	235.3	230.6	229.3	226.6	225.3	224.6
40°	271.2	271.2	263.9	264.6	261.9	262.2	263.9	269.2	266.2	260.9	261.2
42.5°	279.9	282.5	291.2	306.8	301.2	292.2	281.5	285.2	292.8	297.5	298.5
45°	329.1	332.8	333.4	332.8	330.1	333.8	331.1	333.1	334.1	340.1	342.8
47.5°	387.0	385.7	386.0	394.3	391.3	393.7	398.7	398.0	402.3	401.7	404.0
50°	518.8	522.4	517.1	527.8	530.4	526.4	545.7	545.7	547.7	539.1	540.1
52.5°	745.7	737.1	737.1	739.7	740.4	752.7	766.4	766.0	771.0	766.4	776.7
55°	1037.9	1035.9	1040.2	1071.2	1074.5	1063.9	1066.9	1053.2	1097.1	1085.8	1094.1
57.5°	1409.6	1414.6	1408.9	1409.3	1406.6	1403.6	1420.3	1392.0	1413.3	1389.3	1390.0
60°	1694.1	1687.5	1668.8	1632.2	1629.2	1640.2	1658.9	1659.8	1638.6	1625.2	1613.9
62.5°	1757.0	1754.7	1754.0	1751.0	1734.1	1729.4	1725.7	1740.7	1728.1	1737.7	1732.1
65°	1716.8	1706.8	1715.8	1730.1	1719.1	1697.5	1678.8	1704.8	1696.5	1732.4	1713.8
67.5°	1577.3	1568.0	1564.3	1592.6	1579.0	1544.7	1532.1	1538.1	1528.4	1568.0	1560.7
70°	1251.9	1252.2	1259.5	1296.1	1282.5	1257.2	1241.9	1245.9	1255.5	1288.8	1279.5
72.5°	949.7	947.7	956.4	965.7	966.4	964.4	960.4	963.4	969.0	987.3	992.0
75°	749.4	748.7	734.8	739.7	737.7	746.7	760.0	758.0	761.0	747.1	743.1
77.5°	567.0	567.7	562.4	560.0	558.1	572.7	594.0	595.0	580.7	570.4	566.0
80°	392.3	395.0	411.0	411.3	414.3	414.3	431.3	429.3	424.3	423.9	423.9
82.5°	260.2	264.9	281.2	299.8	302.8	299.2	308.5	311.1	317.5	322.1	323.5
85°	250.2	258.6	253.2	261.2	261.6	263.9	267.5	268.9	268.2	269.2	267.2
87.5°	234.3	244.6	243.3	248.6	249.9	253.6	257.6	259.2	255.9	253.2	252.6
90°	208.0	217.6	222.3	226.6	227.9	226.9	229.6	230.3	229.9	226.9	226.3
92.5°	197.0	200.7	203.3	206.6	210.6	208.3	210.0	208.3	211.0	210.3	211.0
95°	183.0	184.4	182.7	184.7	185.4	183.0	182.7	182.7	181.4	179.7	180.4
97.5°	154.7	157.1	156.4	156.4	156.7	155.7	156.1	155.7	156.4	155.4	155.1
100°	144.4	144.4	143.8	143.4	143.1	142.1	141.8	140.8	140.8	139.8	139.1
102.5°	133.8	134.8	133.8	133.4	133.4	131.8	132.1	132.1	131.4	131.1	129.4
105°	126.1	125.8	125.1	123.8	122.5	122.5	123.1	122.8	121.8	121.5	120.1
107.5°	119.1	118.5	117.5	115.5	114.8	115.1	116.1	116.5	116.1	114.8	113.8
110°	120.5	119.5	117.8	117.1	118.1	118.8	119.1	119.8	121.8	122.5	121.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981089
CATALOG NUMBER: FFX-CLB-30-750-U-FR-T5

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	*145.1*	143.4	142.4	138.1	141.4	142.1	141.4	141.8	142.8	141.4	142.1
115°	*165.7*	167.4	167.7	154.4	154.7	152.7	150.7	150.1	147.1	149.4	157.1
117.5°	*153.1*	158.4	146.8	140.8	137.1	135.8	139.1	139.8	136.8	140.4	151.4
120°	*175.7*	178.0	154.1	142.4	142.1	147.7	156.7	159.4	156.1	163.1	175.7
122.5°	*238.6*	236.9	234.6	236.6	231.3	230.9	238.3	237.3	228.3	229.3	232.3
125°	*325.1*	324.4	320.1	315.8	312.1	314.1	311.1	307.5	300.8	299.8	299.8
127.5°	*311.1*	311.1	308.1	305.8	302.2	302.5	302.2	295.5	292.8	293.2	293.2
130°	*228.9*	229.3	238.6	246.9	244.6	245.6	239.6	237.6	246.2	254.2	254.2
132.5°	*194.0*	194.7	205.0	211.3	208.0	201.3	195.0	195.7	201.0	209.0	208.6
135°	*173.4*	174.7	175.4	174.7	172.7	171.0	170.7	172.4	173.7	179.4	180.7
137.5°	*157.1*	156.1	152.7	149.7	147.4	151.7	154.4	153.7	152.4	151.4	152.1
140°	*138.1*	136.8	132.1	131.4	132.8	134.8	135.4	136.1	136.4	135.8	135.4
142.5°	*107.8*	108.8	113.1	118.5	118.8	115.5	115.8	115.8	117.1	118.8	118.1
145°	*108.1*	108.8	110.5	114.5	114.5	111.8	110.8	111.8	114.8	118.1	118.1
147.5°	*120.5*	119.5	117.1	116.1	115.1	114.8	114.8	112.5	112.8	112.8	112.8
150°	*102.5*	102.2	100.8	100.2	99.8	99.5	101.2	100.8	101.5	100.8	100.5
152.5°	*84.5*	84.2	82.9	81.9	82.2	84.2	86.9	87.9	87.2	85.9	85.2
155°	*80.2*	80.5	78.5	77.9	78.2	79.2	79.9	79.9	78.5	76.9	76.9
157.5°	*75.9*	76.2	75.2	74.5	74.9	75.5	76.5	76.9	75.9	74.5	74.2
160°	*72.5*	72.2	71.9	71.9	71.9	71.9	72.2	72.5	72.2	71.9	71.5
162.5°	*70.9*	70.9	70.9	70.9	71.2	70.9	70.9	70.9	70.9	70.9	70.9
165°	*70.5*	70.5	70.9	71.5	71.9	71.5	71.5	71.5	71.9	72.5	72.5
167.5°	*73.5*	73.2	74.2	74.5	74.9	74.5	74.2	73.9	74.2	74.9	74.9
170°	*76.9*	77.2	77.2	77.5	77.5	77.2	76.9	77.2	76.9	77.2	77.2
172.5°	*80.2*	80.2	80.2	79.9	79.9	79.9	79.9	79.9	79.9	79.5	79.5
175°	*82.9*	82.9	82.9	82.9	82.5	82.9	83.2	83.2	82.9	82.9	82.2
177.5°	*85.2*	85.2	85.2	85.2	85.2	85.2	85.2	84.9	84.9	84.9	84.5
180°	*85.5*	85.5	85.5	85.5	85.5	85.5	85.5	85.5	85.5	85.5	85.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-5

Test Date: 03/25/2025

Luminaire Tested: FFX-CLB-100-750-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-750-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-750-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	4987	CRI (Ra):	75.8		
CIE u':	0.2094	R1:	71.6	R9:	-30.4
CIE v':	0.4882	R2:	82.8	R10:	59.9
Duv:	0.0031	R3:	91.2	R11:	70.9
CIE x:	0.3461	R4:	73.8	R12:	51.2
CIE y:	0.3586	R5:	73.0	R13:	74.2
CIE z:	0.2954	R6:	76.1	R14:	95.3
Peak Wavelength (nm):	450	R7:	82.9	R15:	63.7
Dominant Wavelength (nm):	570	R8:	54.9		
Purity:	11.4				

Rf:	78.3
Rg:	93.4



Test Conditions


Stabilization Time:	67M
Operation Time:	2H 7M
Sphere Temperature (°C):	24.9

REPORT NUMBER: SP1-2501-332-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4987K
CIE x = 0.3461
CIE y = 0.3586
Duv = 0.0031

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.87**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.92**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			


REPORT NUMBER: SP1-2501-332-5

TM-30-18


Summary


R_f = 78.3
R_g = 93.4
CIE R_a = 75.8
R_9 = -30.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 71	CES51 = 92	CES76 = 63
CES02 = 60	CES27 = 92	CES52 = 91	CES77 = 76
CES03 = 30	CES28 = 86	CES53 = 83	CES78 = 64
CES04 = 69	CES29 = 75	CES54 = 86	CES79 = 86
CES05 = 46	CES30 = 89	CES55 = 85	CES80 = 84
CES06 = 50	CES31 = 78	CES56 = 79	CES81 = 80
CES07 = 39	CES32 = 71	CES57 = 78	CES82 = 93
CES08 = 38	CES33 = 85	CES58 = 79	CES83 = 93
CES09 = 29	CES34 = 78	CES59 = 88	CES84 = 87
CES10 = 73	CES35 = 88	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 89	CES61 = 84	CES86 = 73
CES12 = 61	CES37 = 86	CES62 = 87	CES87 = 79
CES13 = 41	CES38 = 98	CES63 = 82	CES88 = 81
CES14 = 74	CES39 = 97	CES64 = 72	CES89 = 74
CES15 = 70	CES40 = 93	CES65 = 69	CES90 = 81
CES16 = 46	CES41 = 97	CES66 = 68	CES91 = 76
CES17 = 49	CES42 = 88	CES67 = 66	CES92 = 58
CES18 = 55	CES43 = 85	CES68 = 71	CES93 = 75
CES19 = 71	CES44 = 99	CES69 = 78	CES94 = 54
CES20 = 64	CES45 = 90	CES70 = 65	CES95 = 66
CES21 = 85	CES46 = 87	CES71 = 61	CES96 = 78
CES22 = 77	CES47 = 92	CES72 = 86	CES97 = 88
CES23 = 91	CES48 = 81	CES73 = 57	CES98 = 78
CES24 = 90	CES49 = 86	CES74 = 93	CES99 = 64
CES25 = 71	CES50 = 91	CES75 = 63	





REPORT NUMBER: SP1-2501-332-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-5

TM-30-18

Measure Comparisons





(END OF REPORT)