Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981314

Luminaire Tested: **FFX-CLB-30-750-U-VM9-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981314
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-30-750-U-VM9-T5
Description:	FAIRFAX POST TOP FIXTURE w/ ULA ACORN 9 INCH NECK
Light Source:	(6) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5355.1 lumens
Efficiency:	N/A
Efficacy:	175.0 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.33' x H: 2.08')
IES Classification:	Type V - Short
BUG Rating:	B2 - U5 - G3

Input Watts (W):	30.6
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	10.8%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981314
CATALOG NUMBER: FFX-CLB-30-750-U-VM9-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 1 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981314
CATALOG NUMBER: FFX-CLB-30-750-U-VM9-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981314
CATALOG NUMBER: FFX-CLB-30-750-U-VM9-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1585.3	1092.3	2677.6
	% Fixture	29.6	20.4	50.0
Street Side	Lumens	1585.3	1092.3	2677.6
	% Fixture	29.6	20.4	50.0
Total	Lumens	3170.6	2184.6	5355.1
	% Fixture	59.2	40.8	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.3	0.1
10°-20°	42.8	0.8
20°-30°	125.7	2.3
30°-40°	255.6	4.8
40°-50°	396.5	7.4
50°-60°	512.1	9.6
60°-70°	588.8	11.0
70°-80°	624.0	11.7
80°-90°	618.8	11.6
90°-100°	575.2	10.7
100°-110°	501.5	9.4
110°-120°	409.5	7.6
120°-130°	303.6	5.7
130°-140°	196.5	3.7
140°-150°	111.2	2.1
150°-160°	55.4	1.0
160°-170°	24.6	0.5
170°-180°	7.0	0.1
0°-90°	3170.6	59.2
0°-180°	5355.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981314
CATALOG NUMBER: FFX-CLB-30-750-U-VM9-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	87.4	1.6			
FM	(30°-60°)	582.1	10.9			
FH	(60°-80°)	606.4	11.3			G0/660
FVH	(80°-90°)	309.4	5.8			G3/500
BL	(0°-30°)	87.4	1.6	B0/110		
BM	(30°-60°)	582.1	10.9	B1/1000		
BH	(60°-80°)	606.4	11.3	B2/1000		G0/660
BVH	(80°-90°)	309.4	5.8			G3/500
UL	(90°-100°)	575.2	10.7		U4/1000	
UH	(100°-180°)	1609.4	30.1		U5	

BUG Rating: B2-U5-G3
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981314
CATALOG NUMBER: FFX-CLB-30-750-U-VM9-T5

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6	*42.6*
2.5°	42.6	42.6	42.6	42.6	42.3	42.3	42.3	42.3	42.3	42.3	*42.3*
5°	52.6	52.2	52.2	52.6	52.6	52.6	52.2	52.6	51.9	51.6	*52.2*
7.5°	70.5	70.5	70.5	70.5	69.9	69.9	70.9	70.2	70.5	70.2	*70.9*
10°	92.2	92.2	91.8	92.5	92.8	92.5	92.2	93.2	92.5	92.5	*93.2*
12.5°	116.8	117.1	117.1	117.5	118.1	117.1	118.1	118.1	118.1	117.5	*117.1*
15°	145.1	144.7	145.4	145.1	143.7	145.1	145.4	144.7	145.1	145.4	*145.7*
17.5°	171.4	171.0	171.4	171.0	172.4	172.7	172.4	172.4	172.4	172.7	*172.0*
20°	200.3	200.6	199.6	200.6	200.6	201.3	202.6	202.3	202.6	201.6	*200.6*
22.5°	231.9	232.3	231.3	230.9	232.9	232.6	232.6	233.6	234.2	234.2	*233.6*
25°	265.9	265.2	265.2	266.2	266.2	265.9	267.5	268.2	267.9	268.9	*269.5*
27.5°	299.8	299.1	299.1	300.5	300.5	300.5	300.5	303.5	303.8	304.5	*304.8*
30°	332.7	335.1	335.1	334.4	335.4	337.1	338.1	338.1	339.1	339.1	*339.4*
32.5°	368.7	368.7	369.3	370.3	370.3	373.3	371.7	374.3	373.7	375.7	*377.0*
35°	402.6	403.3	403.3	405.3	405.3	405.9	406.3	407.9	410.3	409.9	*410.3*
37.5°	434.2	433.9	433.2	436.2	436.9	436.6	436.9	439.5	440.2	441.2	*440.5*
40°	463.2	462.2	463.8	465.5	465.5	466.2	466.8	468.2	469.5	470.2	*471.2*
42.5°	487.5	487.1	488.8	490.1	490.5	490.8	490.8	491.8	495.1	496.1	*496.8*
45°	508.8	508.4	510.4	512.1	513.1	513.1	512.1	513.4	516.4	517.4	*517.7*
47.5°	527.1	527.4	530.1	532.1	532.7	531.7	531.1	532.4	534.7	537.4	*537.0*
50°	542.4	542.7	545.7	549.0	549.4	548.4	546.7	547.7	551.0	553.0	*553.3*
52.5°	555.3	555.7	559.3	562.7	563.0	561.3	559.3	561.0	564.0	566.3	*567.0*
55°	565.7	566.7	570.3	574.0	575.0	572.6	570.0	571.0	574.3	578.0	*578.3*
57.5°	573.3	573.6	578.3	582.3	583.6	580.3	578.3	578.3	582.3	585.6	*586.3*
60°	578.6	580.0	585.3	589.9	590.6	587.6	584.0	584.6	589.0	592.6	*593.6*
62.5°	583.3	584.6	589.6	595.3	595.9	591.9	588.3	588.6	593.6	597.3	*598.6*
65°	585.6	586.6	592.6	598.3	598.9	594.9	590.6	590.9	595.6	599.9	*600.3*
67.5°	586.3	587.3	593.6	600.3	600.6	596.3	591.3	592.3	596.9	601.3	*601.9*
70°	*585.6*	*587.0*	*593.3*	*600.3*	*600.9*	*595.6*	*590.6*	*591.3*	*596.6*	*600.9*	*602.3*
72.5°	583.3	585.0	591.3	598.6	598.9	593.9	589.0	589.0	594.9	599.6	*600.3*
75°	580.3	582.0	589.0	596.3	596.6	591.3	586.0	586.6	592.3	596.6	*597.3*
77.5°	577.0	578.0	585.0	592.6	593.3	587.6	582.3	583.0	588.3	592.9	*593.6*
80°	571.6	572.6	580.0	587.3	588.0	582.3	576.6	578.0	583.3	587.6	*587.6*
82.5°	565.3	566.0	573.3	581.3	581.6	576.0	571.0	571.6	577.0	581.3	*581.3*
85°	558.0	559.0	566.3	574.0	574.0	568.7	563.3	564.7	569.7	573.6	*575.0*
87.5°	550.0	550.4	557.7	564.7	565.0	559.7	555.0	556.0	561.0	564.7	*565.0*
90°	540.7	541.4	548.4	555.0	555.3	550.0	545.7	547.0	551.0	554.3	*555.3*
92.5°	530.4	531.4	538.0	544.4	544.0	539.4	535.7	537.4	540.7	544.0	*544.0*
95°	519.7	521.1	526.4	532.4	531.7	527.7	524.7	526.1	529.4	532.1	*532.7*
97.5°	508.4	508.8	514.4	518.7	518.7	515.1	512.8	513.8	517.1	518.7	*519.4*
100°	496.1	496.4	500.8	505.1	505.1	501.8	500.1	501.1	503.8	505.1	*505.4*
102.5°	483.8	483.5	487.1	490.8	490.8	488.1	486.8	488.8	490.1	491.1	*491.8*
105°	469.8	469.5	472.8	476.2	475.5	473.8	472.5	474.2	475.8	476.5	*476.5*
107.5°	454.5	455.9	457.9	460.5	460.2	458.8	458.8	459.8	460.8	461.2	*461.5*
110°	441.5	441.2	443.2	444.5	444.9	444.2	444.9	445.2	445.5	445.5	*445.5*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981314
CATALOG NUMBER: FFX-CLB-30-750-U-VM9-T5

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	426.6	426.6	427.2	428.2	428.6	428.9	429.2	430.6	429.9	430.2	*429.6*
115°	410.3	410.6	411.3	411.6	412.3	412.6	414.3	414.3	414.6	413.9	*412.9*
117.5°	394.0	394.6	394.3	394.0	395.3	396.3	397.3	398.0	398.0	396.6	*396.0*
120°	376.3	375.7	375.7	375.7	376.7	378.3	379.7	380.0	379.7	378.0	*377.7*
122.5°	357.0	357.7	356.7	357.0	357.4	359.7	360.7	361.4	360.4	358.4	*359.0*
125°	337.1	337.7	336.1	336.1	337.7	338.7	339.7	340.7	339.1	338.1	*337.4*
127.5°	315.8	315.8	315.4	314.4	316.4	317.4	319.4	319.4	318.1	316.8	*317.4*
130°	294.1	293.8	294.5	293.8	294.1	296.1	297.8	297.1	296.5	295.8	*295.8*
132.5°	271.8	272.5	271.8	271.5	273.2	273.8	275.5	276.2	274.8	273.2	*273.8*
135°	250.9	250.6	250.2	250.2	251.2	252.9	253.9	253.5	253.5	252.9	*252.2*
137.5°	229.3	230.3	229.6	229.6	230.3	231.9	233.6	233.3	232.9	231.6	*230.9*
140°	210.0	209.3	209.6	209.6	211.3	211.3	213.0	213.0	212.6	211.6	*212.3*
142.5°	190.7	190.3	191.7	191.0	191.7	193.3	194.0	193.7	193.0	193.3	*193.7*
145°	173.0	173.4	173.0	173.4	174.4	175.4	176.7	176.0	176.0	175.0	*174.7*
147.5°	156.4	156.4	156.1	157.4	157.7	159.0	159.4	159.7	159.0	158.4	*159.4*
150°	141.7	141.4	141.4	141.7	142.4	143.4	144.1	144.1	144.4	143.7	*143.4*
152.5°	128.1	127.4	127.8	128.4	128.8	129.8	129.8	130.4	130.1	129.8	*129.8*
155°	115.8	116.1	116.1	116.5	117.1	117.5	118.1	117.8	118.1	117.8	*117.8*
157.5°	105.8	106.5	106.5	106.8	106.5	106.8	107.1	107.5	107.5	107.5	*107.5*
160°	97.8	97.5	97.5	97.5	97.5	97.8	98.5	98.2	98.5	98.2	*97.8*
162.5°	90.5	90.5	90.5	90.5	90.8	90.8	90.8	91.2	90.8	90.8	*90.8*
165°	84.5	84.8	84.5	84.5	84.5	84.8	84.8	84.8	84.8	84.8	*84.8*
167.5°	79.9	80.2	80.2	80.2	80.2	80.2	80.5	80.2	80.2	80.2	*80.2*
170°	76.2	76.5	76.5	76.2	76.5	76.2	76.2	76.5	76.2	76.2	*76.2*
172.5°	73.5	73.5	73.5	73.5	73.5	73.5	73.5	73.5	73.5	73.2	*73.2*
175°	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	*71.2*
177.5°	69.9	69.9	70.2	69.9	69.9	69.9	69.9	69.9	69.9	69.9	*69.9*
180°	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	*69.5*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-5

Test Date: 03/25/2025

Luminaire Tested: FFX-CLB-100-750-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-750-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-750-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	4987	CRI (Ra):	75.8		
CIE u':	0.2094	R1:	71.6	R9:	-30.4
CIE v':	0.4882	R2:	82.8	R10:	59.9
Duv:	0.0031	R3:	91.2	R11:	70.9
CIE x:	0.3461	R4:	73.8	R12:	51.2
CIE y:	0.3586	R5:	73.0	R13:	74.2
CIE z:	0.2954	R6:	76.1	R14:	95.3
Peak Wavelength (nm):	450	R7:	82.9	R15:	63.7
Dominant Wavelength (nm):	570	R8:	54.9		
Purity:	11.4				

Rf:	78.3
Rg:	93.4



Test Conditions


Stabilization Time:	67M
Operation Time:	2H 7M
Sphere Temperature (°C):	24.9

REPORT NUMBER: SP1-2501-332-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4987K
CIE x = 0.3461
CIE y = 0.3586
Duv = 0.0031

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.87**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.92**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			


REPORT NUMBER: SP1-2501-332-5

TM-30-18


Summary


R_f = 78.3
R_g = 93.4
CIE R_a = 75.8
R_9 = -30.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 71	CES51 = 92	CES76 = 63
CES02 = 60	CES27 = 92	CES52 = 91	CES77 = 76
CES03 = 30	CES28 = 86	CES53 = 83	CES78 = 64
CES04 = 69	CES29 = 75	CES54 = 86	CES79 = 86
CES05 = 46	CES30 = 89	CES55 = 85	CES80 = 84
CES06 = 50	CES31 = 78	CES56 = 79	CES81 = 80
CES07 = 39	CES32 = 71	CES57 = 78	CES82 = 93
CES08 = 38	CES33 = 85	CES58 = 79	CES83 = 93
CES09 = 29	CES34 = 78	CES59 = 88	CES84 = 87
CES10 = 73	CES35 = 88	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 89	CES61 = 84	CES86 = 73
CES12 = 61	CES37 = 86	CES62 = 87	CES87 = 79
CES13 = 41	CES38 = 98	CES63 = 82	CES88 = 81
CES14 = 74	CES39 = 97	CES64 = 72	CES89 = 74
CES15 = 70	CES40 = 93	CES65 = 69	CES90 = 81
CES16 = 46	CES41 = 97	CES66 = 68	CES91 = 76
CES17 = 49	CES42 = 88	CES67 = 66	CES92 = 58
CES18 = 55	CES43 = 85	CES68 = 71	CES93 = 75
CES19 = 71	CES44 = 99	CES69 = 78	CES94 = 54
CES20 = 64	CES45 = 90	CES70 = 65	CES95 = 66
CES21 = 85	CES46 = 87	CES71 = 61	CES96 = 78
CES22 = 77	CES47 = 92	CES72 = 86	CES97 = 88
CES23 = 91	CES48 = 81	CES73 = 57	CES98 = 78
CES24 = 90	CES49 = 86	CES74 = 93	CES99 = 64
CES25 = 71	CES50 = 91	CES75 = 63	





REPORT NUMBER: SP1-2501-332-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-5

TM-30-18

Measure Comparisons





(END OF REPORT)