Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981088

Luminaire Tested: **FFX-CLB-40-750-U-FR-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981088
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-40-750-U-FR-T5
Description:	FAIRFAX POST TOP FIXTURE w/ FAIRFAX REFRACTOR T5 DISTRIBUTION LENS
Light Source:	(6) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	6694.8 lumens
Efficiency:	N/A
Efficacy:	169.9 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.17' x H: 1.67')
IES Classification:	Type V - Short
BUG Rating:	B3 - U5 - G2

Input Watts (W):	39.4
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	8.2%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981088
CATALOG NUMBER: FFX-CLB-40-750-U-FR-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 1.2 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981088
CATALOG NUMBER: FFX-CLB-40-750-U-FR-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981088
CATALOG NUMBER: FFX-CLB-40-750-U-FR-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2711.2	636.2	3347.4
	% Fixture	40.5	9.5	50.0
Street Side	Lumens	2711.2	636.2	3347.4
	% Fixture	40.5	9.5	50.0
Total	Lumens	5422.4	1272.4	6694.8
	% Fixture	81.0	19.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.9	0.1
10°-20°	37.2	0.6
20°-30°	79.1	1.2
30°-40°	159.9	2.4
40°-50°	357.3	5.3
50°-60°	1260.0	18.8
60°-70°	2062.1	30.8
70°-80°	1060.8	15.8
80°-90°	399.1	6.0
90°-100°	256.9	3.8
100°-110°	171.3	2.6
110°-120°	184.0	2.7
120°-130°	301.1	4.5
130°-140°	180.2	2.7
140°-150°	93.6	1.4
150°-160°	48.9	0.7
160°-170°	26.5	0.4
170°-180°	9.9	0.1
0°-90°	5422.4	81.0
0°-180°	6694.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981088
CATALOG NUMBER: FFX-CLB-40-750-U-FR-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	61.6	0.9			
FM	(30°-60°)	888.6	13.3			
FH	(60°-80°)	1561.5	23.3			G1/1800
FVH	(80°-90°)	199.6	3.0			G2/225
BL	(0°-30°)	61.6	0.9	B0/110		
BM	(30°-60°)	888.6	13.3	B1/1000		
BH	(60°-80°)	1561.5	23.3	B3/2500		G1/1800
BVH	(80°-90°)	199.6	3.0			G2/225
UL	(90°-100°)	256.9	3.8		U3/500	
UH	(100°-180°)	1015.5	15.2		U5	

BUG Rating: B3-U5-G2
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981088
CATALOG NUMBER: FFX-CLB-40-750-U-FR-T5

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6
2.5°	38.1	38.6	39.9	40.7	41.1	40.3	40.7	41.6	41.6	42.0	42.0
5°	56.6	57.0	56.6	56.1	55.7	56.6	57.0	56.6	55.3	55.7	55.3
7.5°	83.6	83.6	80.1	79.3	78.4	82.3	84.4	83.6	79.3	75.4	74.6
10°	102.8	102.4	99.4	95.6	95.1	97.7	103.3	104.6	97.7	93.0	92.1
12.5°	122.1	119.1	117.4	113.6	114.0	115.7	119.6	120.0	115.3	111.4	108.8
15°	133.7	134.1	134.1	132.0	131.1	132.8	134.6	135.8	132.4	129.4	127.7
17.5°	138.8	139.3	140.6	141.8	141.8	141.0	141.0	141.4	141.4	141.4	141.0
20°	149.6	150.0	149.6	150.4	151.7	150.8	149.6	150.0	149.6	150.0	149.6
22.5°	158.1	157.7	157.7	159.0	159.8	159.4	158.1	158.6	157.7	158.1	158.1
25°	167.1	167.6	168.4	168.8	169.3	169.3	168.8	169.7	169.3	168.4	168.4
27.5°	179.6	179.6	179.6	179.6	181.3	181.3	180.4	180.8	179.6	178.7	178.3
30°	191.6	192.0	191.1	192.0	193.7	192.8	192.4	193.3	191.6	191.1	191.1
32.5°	202.7	202.7	202.3	204.8	205.3	204.4	205.7	206.6	207.4	207.0	209.1
35°	221.6	222.4	229.7	236.1	238.3	237.8	239.6	240.4	238.7	238.7	237.4
37.5°	312.8	312.4	302.1	292.3	297.0	303.0	297.0	295.3	291.8	290.1	289.3
40°	349.3	349.3	339.8	340.7	337.3	337.7	339.8	346.7	342.8	336.0	336.4
42.5°	360.4	363.8	375.0	395.1	387.8	376.3	362.5	367.3	377.1	383.1	384.4
45°	423.8	428.5	429.4	428.5	425.1	429.8	426.4	429.0	430.3	438.0	441.4
47.5°	498.4	496.7	497.1	507.8	504.0	507.0	513.4	512.5	518.1	517.2	520.2
50°	668.1	672.8	666.0	679.7	683.1	678.0	702.8	702.8	705.4	694.2	695.5
52.5°	960.4	949.2	949.2	952.6	953.5	969.4	986.9	986.5	992.9	986.9	1000.2
55°	1336.6	1334.0	1339.6	1379.5	1383.8	1370.0	1373.9	1356.3	1412.9	1398.3	1409.0
57.5°	1815.3	1821.7	1814.4	1814.9	1811.4	1807.6	1829.0	1792.6	1820.0	1789.2	1790.0
60°	2181.7	2173.1	2149.1	2102.0	2098.1	2112.3	2136.3	2137.6	2110.1	2093.0	2078.4
62.5°	2262.7	2259.7	2258.8	2255.0	2233.1	2227.1	2222.4	2241.7	2225.4	2237.8	2230.6
65°	2210.8	2198.0	2209.6	2228.0	2213.8	2186.0	2162.0	2195.4	2184.7	2231.0	2207.0
67.5°	2031.3	2019.3	2014.6	2051.0	2033.4	1989.3	1973.0	1980.7	1968.3	2019.3	2009.9
70°	1612.2	1612.6	1622.0	1669.2	1651.6	1619.0	1599.3	1604.5	1616.9	1659.7	1647.7
72.5°	1223.1	1220.5	1231.6	1243.6	1244.5	1241.9	1236.8	1240.6	1247.9	1271.5	1277.5
75°	965.1	964.2	946.2	952.6	950.1	961.6	978.8	976.2	980.1	962.1	956.9
77.5°	730.2	731.1	724.2	721.2	718.7	737.5	764.9	766.2	747.8	734.5	728.9
80°	505.3	508.7	529.2	529.7	533.5	533.5	555.4	552.8	546.4	546.0	546.0
82.5°	335.1	341.1	362.1	386.1	390.0	385.3	397.3	400.7	408.8	414.8	416.5
85°	322.3	333.0	326.1	336.4	336.8	339.8	344.5	346.3	345.4	346.7	344.1
87.5°	301.7	315.0	313.3	320.1	321.8	326.5	331.7	333.8	329.5	326.1	325.3
90°	267.8	280.3	286.3	291.8	293.6	292.3	295.7	296.6	296.1	292.3	291.4
92.5°	253.7	258.4	261.8	266.1	271.3	268.3	270.4	268.3	271.7	270.8	271.7
95°	235.7	237.4	235.3	237.8	238.7	235.7	235.3	235.3	233.6	231.4	232.3
97.5°	199.3	202.3	201.4	201.4	201.8	200.6	201.0	200.6	201.4	200.1	199.7
100°	186.0	186.0	185.1	184.7	184.3	183.0	182.6	181.3	181.3	180.0	179.1
102.5°	172.3	173.6	172.3	171.8	171.8	169.7	170.1	170.1	169.3	168.8	166.7
105°	162.4	162.0	161.1	159.4	157.7	157.7	158.6	158.1	156.8	156.4	154.7
107.5°	153.4	152.6	151.3	148.7	147.8	148.3	149.6	150.0	149.6	147.8	146.6
110°	155.1	153.8	151.7	150.8	152.1	153.0	153.4	154.3	156.8	157.7	156.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981088
CATALOG NUMBER: FFX-CLB-40-750-U-FR-T5

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	*186.8*	184.7	183.4	177.8	182.1	183.0	182.1	182.6	183.8	182.1	183.0
115°	*213.4*	215.6	216.0	198.8	199.3	196.7	194.1	193.3	189.4	192.4	202.3
117.5°	*197.1*	204.0	189.0	181.3	176.6	174.8	179.1	180.0	176.1	180.8	195.0
120°	*226.3*	229.3	198.4	183.4	183.0	190.3	201.8	205.3	201.0	210.0	226.3
122.5°	*307.3*	305.1	302.1	304.7	297.8	297.4	306.8	305.6	294.0	295.3	299.1
125°	*418.7*	417.8	412.3	406.7	402.0	404.5	400.7	396.0	387.4	386.1	386.1
127.5°	*400.7*	400.7	396.8	393.8	389.1	389.5	389.1	380.5	377.1	377.5	377.5
130°	*294.8*	295.3	307.3	318.0	315.0	316.3	308.5	306.0	317.1	327.4	327.4
132.5°	*249.8*	250.7	264.0	272.1	267.8	259.3	251.1	252.0	258.8	269.1	268.7
135°	*223.3*	225.0	225.8	225.0	222.4	220.3	219.8	222.0	223.7	231.0	232.7
137.5°	*202.3*	201.0	196.7	192.8	189.8	195.4	198.8	198.0	196.3	195.0	195.8
140°	*177.8*	176.1	170.1	169.3	171.0	173.6	174.4	175.3	175.7	174.8	174.4
142.5°	*138.8*	140.1	145.7	152.6	153.0	148.7	149.1	149.1	150.8	153.0	152.1
145°	*139.3*	140.1	142.3	147.4	147.4	144.0	142.7	144.0	147.8	152.1	152.1
147.5°	*155.1*	153.8	150.8	149.6	148.3	147.8	147.8	144.8	145.3	145.3	145.3
150°	*132.0*	131.6	129.8	129.0	128.6	128.1	130.3	129.8	130.7	129.8	129.4
152.5°	*108.8*	108.4	106.7	105.4	105.8	108.4	111.8	113.1	112.3	110.6	109.7
155°	*103.3*	103.7	101.1	100.3	100.7	102.0	102.8	102.8	101.1	99.0	99.0
157.5°	*97.7*	98.1	96.9	96.0	96.4	97.3	98.6	99.0	97.7	96.0	95.6
160°	*93.4*	93.0	92.6	92.6	92.6	92.6	93.0	93.4	93.0	92.6	92.1
162.5°	*91.3*	91.3	91.3	91.3	91.7	91.3	91.3	91.3	91.3	91.3	91.3
165°	*90.9*	90.9	91.3	92.1	92.6	92.1	92.1	92.1	92.6	93.4	93.4
167.5°	*94.7*	94.3	95.6	96.0	96.4	96.0	95.6	95.1	95.6	96.4	96.4
170°	*99.0*	99.4	99.4	99.9	99.9	99.4	99.0	99.4	99.0	99.4	99.4
172.5°	*103.3*	103.3	103.3	102.8	102.8	102.8	102.8	102.8	102.8	102.4	102.4
175°	*106.7*	106.7	106.7	106.7	106.3	106.7	107.1	107.1	106.7	106.7	105.8
177.5°	*109.7*	109.7	109.7	109.7	109.7	109.7	109.7	109.3	109.3	109.3	108.8
180°	*110.1*	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-5

Test Date: 03/25/2025

Luminaire Tested: FFX-CLB-100-750-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-750-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-750-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	4987	CRI (Ra):	75.8		
CIE u':	0.2094	R1:	71.6	R9:	-30.4
CIE v':	0.4882	R2:	82.8	R10:	59.9
Duv:	0.0031	R3:	91.2	R11:	70.9
CIE x:	0.3461	R4:	73.8	R12:	51.2
CIE y:	0.3586	R5:	73.0	R13:	74.2
CIE z:	0.2954	R6:	76.1	R14:	95.3
Peak Wavelength (nm):	450	R7:	82.9	R15:	63.7
Dominant Wavelength (nm):	570	R8:	54.9		
Purity:	11.4				

Rf:	78.3
Rg:	93.4



Test Conditions


Stabilization Time:	67M
Operation Time:	2H 7M
Sphere Temperature (°C):	24.9

REPORT NUMBER: SP1-2501-332-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4987K
CIE x = 0.3461
CIE y = 0.3586
Duv = 0.0031

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.87**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.92**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			


REPORT NUMBER: SP1-2501-332-5

TM-30-18


Summary


R_f = 78.3
R_g = 93.4
CIE R_a = 75.8
R_9 = -30.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 71	CES51 = 92	CES76 = 63
CES02 = 60	CES27 = 92	CES52 = 91	CES77 = 76
CES03 = 30	CES28 = 86	CES53 = 83	CES78 = 64
CES04 = 69	CES29 = 75	CES54 = 86	CES79 = 86
CES05 = 46	CES30 = 89	CES55 = 85	CES80 = 84
CES06 = 50	CES31 = 78	CES56 = 79	CES81 = 80
CES07 = 39	CES32 = 71	CES57 = 78	CES82 = 93
CES08 = 38	CES33 = 85	CES58 = 79	CES83 = 93
CES09 = 29	CES34 = 78	CES59 = 88	CES84 = 87
CES10 = 73	CES35 = 88	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 89	CES61 = 84	CES86 = 73
CES12 = 61	CES37 = 86	CES62 = 87	CES87 = 79
CES13 = 41	CES38 = 98	CES63 = 82	CES88 = 81
CES14 = 74	CES39 = 97	CES64 = 72	CES89 = 74
CES15 = 70	CES40 = 93	CES65 = 69	CES90 = 81
CES16 = 46	CES41 = 97	CES66 = 68	CES91 = 76
CES17 = 49	CES42 = 88	CES67 = 66	CES92 = 58
CES18 = 55	CES43 = 85	CES68 = 71	CES93 = 75
CES19 = 71	CES44 = 99	CES69 = 78	CES94 = 54
CES20 = 64	CES45 = 90	CES70 = 65	CES95 = 66
CES21 = 85	CES46 = 87	CES71 = 61	CES96 = 78
CES22 = 77	CES47 = 92	CES72 = 86	CES97 = 88
CES23 = 91	CES48 = 81	CES73 = 57	CES98 = 78
CES24 = 90	CES49 = 86	CES74 = 93	CES99 = 64
CES25 = 71	CES50 = 91	CES75 = 63	





REPORT NUMBER: SP1-2501-332-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-5

TM-30-18

Measure Comparisons





(END OF REPORT)