Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981087

Luminaire Tested: **FFX-CLB-50-750-U-FR-T5**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981087
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-50-750-U-FR-T5
Description:	FAIRFAX POST TOP FIXTURE w/ FAIRFAX REFRACTOR T5 DISTRIBUTION LENS
Light Source:	(6) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	8488.5 lumens
Efficiency:	N/A
Efficacy:	167.8 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.17' x H: 1.67')
IES Classification:	Type V - Short
BUG Rating:	B3 - U5 - G3

Input Watts (W):	50.6
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	6.12%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981087
CATALOG NUMBER: FFX-CLB-50-750-U-FR-T5

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 1.6 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981087
CATALOG NUMBER: FFX-CLB-50-750-U-FR-T5

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981087
CATALOG NUMBER: FFX-CLB-50-750-U-FR-T5

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3437.6	806.7	4244.2
	% Fixture	40.5	9.5	50.0
Street Side	Lumens	3437.6	806.7	4244.2
	% Fixture	40.5	9.5	50.0
Total	Lumens	6875.2	1613.3	8488.5
	% Fixture	81.0	19.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.7	0.1
10°-20°	47.2	0.6
20°-30°	100.3	1.2
30°-40°	202.7	2.4
40°-50°	453.0	5.3
50°-60°	1597.5	18.8
60°-70°	2614.6	30.8
70°-80°	1345.0	15.8
80°-90°	506.1	6.0
90°-100°	325.7	3.8
100°-110°	217.2	2.6
110°-120°	233.3	2.7
120°-130°	381.7	4.5
130°-140°	228.5	2.7
140°-150°	118.7	1.4
150°-160°	62.1	0.7
160°-170°	33.6	0.4
170°-180°	12.6	0.1
0°-90°	6875.2	81.0
0°-180°	8488.5	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981087
CATALOG NUMBER: FFX-CLB-50-750-U-FR-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	78.1	0.9			
FM	(30°-60°)	1126.6	13.3			
FH	(60°-80°)	1979.8	23.3			G2/5000
FVH	(80°-90°)	253.0	3.0			G3/500
BL	(0°-30°)	78.1	0.9	B0/110		
BM	(30°-60°)	1126.6	13.3	B2/2500		
BH	(60°-80°)	1979.8	23.3	B3/2500		G2/5000
BVH	(80°-90°)	253.0	3.0			G3/500
UL	(90°-100°)	325.7	3.8		U3/500	
UH	(100°-180°)	1287.6	15.2		U5	

BUG Rating: B3-U5-G3
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981087
CATALOG NUMBER: FFX-CLB-50-750-U-FR-T5

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	52.7	52.7	52.7	52.7	52.7	52.7	52.7	52.7	52.7	52.7	52.7
2.5°	48.4	48.9	50.5	51.6	52.2	51.1	51.6	52.7	52.7	53.2	53.2
5°	71.7	72.3	71.7	71.2	70.6	71.7	72.3	71.7	70.1	70.6	70.1
7.5°	106.0	106.0	101.6	100.5	99.4	104.3	107.0	106.0	100.5	95.6	94.5
10°	130.4	129.9	126.1	121.2	120.6	123.9	130.9	132.6	123.9	117.9	116.8
12.5°	154.9	151.1	148.9	144.0	144.5	146.7	151.6	152.1	146.2	141.3	138.0
15°	169.5	170.1	170.1	167.4	166.3	168.4	170.6	172.2	167.9	164.1	161.9
17.5°	176.0	176.6	178.2	179.8	179.8	178.8	178.8	179.3	179.3	179.3	178.8
20°	189.6	190.2	189.6	190.7	192.3	191.3	189.6	190.2	189.6	190.2	189.6
22.5°	200.5	200.0	200.0	201.6	202.7	202.1	200.5	201.0	200.0	200.5	200.5
25°	211.9	212.5	213.5	214.1	214.6	214.6	214.1	215.2	214.6	213.5	213.5
27.5°	227.7	227.7	227.7	227.7	229.8	229.8	228.8	229.3	227.7	226.6	226.0
30°	242.9	243.4	242.3	243.4	245.6	244.5	244.0	245.1	242.9	242.3	242.3
32.5°	257.0	257.0	256.5	259.7	260.3	259.2	260.8	261.9	263.0	262.4	265.2
35°	280.9	282.0	291.2	299.4	302.1	301.6	303.7	304.8	302.6	302.6	301.0
37.5°	396.6	396.1	383.1	370.6	376.5	384.1	376.5	374.4	370.0	367.8	366.8
40°	442.8	442.8	430.9	432.0	427.6	428.2	430.9	439.6	434.7	426.0	426.5
42.5°	457.0	461.3	475.4	501.0	491.7	477.1	459.7	465.7	478.1	485.8	487.4
45°	537.4	543.4	544.4	543.4	539.0	545.0	540.6	543.9	545.5	555.3	559.7
47.5°	631.9	629.7	630.3	643.9	639.0	642.8	650.9	649.8	656.9	655.8	659.6
50°	847.1	853.1	844.4	861.8	866.1	859.6	891.1	891.1	894.4	880.2	881.9
52.5°	1217.6	1203.5	1203.5	1207.9	1209.0	1229.1	1251.3	1250.8	1258.9	1251.3	1268.2
55°	1694.7	1691.5	1698.5	1749.0	1754.5	1737.1	1742.0	1719.7	1791.4	1773.0	1786.5
57.5°	2301.6	2309.8	2300.5	2301.1	2296.7	2291.9	2319.0	2272.8	2307.6	2268.5	2269.6
60°	2766.2	2755.3	2724.9	2665.1	2660.2	2678.2	2708.6	2710.2	2675.5	2653.7	2635.2
62.5°	2868.9	2865.1	2864.0	2859.1	2831.4	2823.8	2817.8	2842.3	2821.6	2837.4	2828.1
65°	2803.1	2786.8	2801.5	2824.9	2806.9	2771.6	2741.2	2783.6	2770.0	2828.7	2798.3
67.5°	2575.5	2560.3	2554.3	2600.5	2578.2	2522.2	2501.6	2511.4	2495.6	2560.3	2548.3
70°	2044.1	2044.6	2056.6	2116.4	2094.1	2052.8	2027.8	2034.3	2050.1	2104.4	2089.2
72.5°	1550.7	1547.5	1561.6	1576.8	1577.9	1574.6	1568.1	1573.0	1582.2	1612.1	1619.7
75°	1223.6	1222.5	1199.7	1207.9	1204.6	1219.3	1241.0	1237.8	1242.6	1219.8	1213.3
77.5°	925.9	927.0	918.3	914.5	911.2	935.1	969.9	971.5	948.1	931.3	924.2
80°	640.6	645.0	671.0	671.6	676.5	676.5	704.2	700.9	692.8	692.2	692.2
82.5°	424.9	432.5	459.1	489.6	494.4	488.5	503.7	508.0	518.4	526.0	528.1
85°	408.6	422.2	413.5	426.5	427.1	430.9	436.9	439.0	437.9	439.6	436.3
87.5°	382.5	399.4	397.2	405.9	408.1	414.0	420.6	423.3	417.8	413.5	412.4
90°	339.6	355.4	363.0	370.0	372.2	370.6	374.9	376.0	375.5	370.6	369.5
92.5°	321.7	327.6	332.0	337.4	343.9	340.1	342.9	340.1	344.5	343.4	344.5
95°	298.8	301.0	298.3	301.6	302.6	298.8	298.3	298.3	296.1	293.4	294.5
97.5°	252.7	256.5	255.4	255.4	255.9	254.3	254.8	254.3	255.4	253.7	253.2
100°	235.8	235.8	234.7	234.2	233.6	232.0	231.5	229.8	229.8	228.2	227.1
102.5°	218.4	220.1	218.4	217.9	217.9	215.2	215.7	215.7	214.6	214.1	211.4
105°	205.9	205.4	204.3	202.1	200.0	200.0	201.0	200.5	198.9	198.3	196.1
107.5°	194.5	193.4	191.8	188.5	187.5	188.0	189.6	190.2	189.6	187.5	185.8
110°	196.7	195.1	192.3	191.3	192.9	194.0	194.5	195.6	198.9	200.0	197.8

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981087
CATALOG NUMBER: FFX-CLB-50-750-U-FR-T5

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	*236.9*	234.2	232.6	225.5	230.9	232.0	230.9	231.5	233.1	230.9	232.0
115°	*270.6*	273.3	273.8	252.1	252.7	249.4	246.1	245.1	240.2	244.0	256.5
117.5°	*249.9*	258.6	239.6	229.8	223.9	221.7	227.1	228.2	223.3	229.3	247.2
120°	*286.9*	290.7	251.6	232.6	232.0	241.2	255.9	260.3	254.8	266.2	286.9
122.5°	*389.6*	386.9	383.1	386.3	377.6	377.1	389.0	387.4	372.7	374.4	379.3
125°	*530.9*	529.8	522.7	515.6	509.7	512.9	508.0	502.1	491.2	489.6	489.6
127.5°	*508.0*	508.0	503.1	499.3	493.4	493.9	493.4	482.5	478.1	478.7	478.7
130°	*373.8*	374.4	389.6	403.2	399.4	401.0	391.2	388.0	402.1	415.1	415.1
132.5°	*316.8*	317.9	334.7	345.0	339.6	328.7	318.4	319.5	328.2	341.2	340.7
135°	*283.1*	285.3	286.3	285.3	282.0	279.3	278.7	281.5	283.6	292.9	295.0
137.5°	*256.5*	254.8	249.4	244.5	240.7	247.8	252.1	251.0	248.9	247.2	248.3
140°	*225.5*	223.3	215.7	214.6	216.8	220.1	221.1	222.2	222.8	221.7	221.1
142.5°	*176.0*	177.7	184.7	193.4	194.0	188.5	189.1	189.1	191.3	194.0	192.9
145°	*176.6*	177.7	180.4	186.9	186.9	182.6	180.9	182.6	187.5	192.9	192.9
147.5°	*196.7*	195.1	191.3	189.6	188.0	187.5	187.5	183.7	184.2	184.2	184.2
150°	*167.4*	166.8	164.6	163.5	163.0	162.5	165.2	164.6	165.7	164.6	164.1
152.5°	*138.0*	137.5	135.3	133.7	134.2	137.5	141.8	143.4	142.4	140.2	139.1
155°	*130.9*	131.5	128.2	127.1	127.7	129.3	130.4	130.4	128.2	125.5	125.5
157.5°	*123.9*	124.4	122.8	121.7	122.3	123.3	125.0	125.5	123.9	121.7	121.2
160°	*118.5*	117.9	117.4	117.4	117.4	117.4	117.9	118.5	117.9	117.4	116.8
162.5°	*115.7*	115.7	115.7	115.7	116.3	115.7	115.7	115.7	115.7	115.7	115.7
165°	*115.2*	115.2	115.7	116.8	117.4	116.8	116.8	116.8	117.4	118.5	118.5
167.5°	*120.1*	119.5	121.2	121.7	122.3	121.7	121.2	120.6	121.2	122.3	122.3
170°	*125.5*	126.1	126.1	126.6	126.6	126.1	125.5	126.1	125.5	126.1	126.1
172.5°	*130.9*	130.9	130.9	130.4	130.4	130.4	130.4	130.4	130.4	129.9	129.9
175°	*135.3*	135.3	135.3	135.3	134.8	135.3	135.8	135.8	135.3	135.3	134.2
177.5°	*139.1*	139.1	139.1	139.1	139.1	139.1	139.1	138.6	138.6	138.6	138.0
180°	*139.6*	139.6	139.6	139.6	139.6	139.6	139.6	139.6	139.6	139.6	139.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-5

Test Date: 03/25/2025

Luminaire Tested: FFX-CLB-100-750-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-750-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-750-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	4987	CRI (Ra):	75.8		
CIE u':	0.2094	R1:	71.6	R9:	-30.4
CIE v':	0.4882	R2:	82.8	R10:	59.9
Duv:	0.0031	R3:	91.2	R11:	70.9
CIE x:	0.3461	R4:	73.8	R12:	51.2
CIE y:	0.3586	R5:	73.0	R13:	74.2
CIE z:	0.2954	R6:	76.1	R14:	95.3
Peak Wavelength (nm):	450	R7:	82.9	R15:	63.7
Dominant Wavelength (nm):	570	R8:	54.9		
Purity:	11.4				

Rf:	78.3
Rg:	93.4



Test Conditions


Stabilization Time:	67M
Operation Time:	2H 7M
Sphere Temperature (°C):	24.9

REPORT NUMBER: SP1-2501-332-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4987K
CIE x = 0.3461
CIE y = 0.3586
Duv = 0.0031

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.87**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.92**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			


REPORT NUMBER: SP1-2501-332-5

TM-30-18


Summary


R_f = 78.3
R_g = 93.4
CIE R_a = 75.8
R_9 = -30.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 71	CES51 = 92	CES76 = 63
CES02 = 60	CES27 = 92	CES52 = 91	CES77 = 76
CES03 = 30	CES28 = 86	CES53 = 83	CES78 = 64
CES04 = 69	CES29 = 75	CES54 = 86	CES79 = 86
CES05 = 46	CES30 = 89	CES55 = 85	CES80 = 84
CES06 = 50	CES31 = 78	CES56 = 79	CES81 = 80
CES07 = 39	CES32 = 71	CES57 = 78	CES82 = 93
CES08 = 38	CES33 = 85	CES58 = 79	CES83 = 93
CES09 = 29	CES34 = 78	CES59 = 88	CES84 = 87
CES10 = 73	CES35 = 88	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 89	CES61 = 84	CES86 = 73
CES12 = 61	CES37 = 86	CES62 = 87	CES87 = 79
CES13 = 41	CES38 = 98	CES63 = 82	CES88 = 81
CES14 = 74	CES39 = 97	CES64 = 72	CES89 = 74
CES15 = 70	CES40 = 93	CES65 = 69	CES90 = 81
CES16 = 46	CES41 = 97	CES66 = 68	CES91 = 76
CES17 = 49	CES42 = 88	CES67 = 66	CES92 = 58
CES18 = 55	CES43 = 85	CES68 = 71	CES93 = 75
CES19 = 71	CES44 = 99	CES69 = 78	CES94 = 54
CES20 = 64	CES45 = 90	CES70 = 65	CES95 = 66
CES21 = 85	CES46 = 87	CES71 = 61	CES96 = 78
CES22 = 77	CES47 = 92	CES72 = 86	CES97 = 88
CES23 = 91	CES48 = 81	CES73 = 57	CES98 = 78
CES24 = 90	CES49 = 86	CES74 = 93	CES99 = 64
CES25 = 71	CES50 = 91	CES75 = 63	





REPORT NUMBER: SP1-2501-332-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-5

TM-30-18

Measure Comparisons





(END OF REPORT)