Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P981128

Luminaire Tested: **FFX-CLB-90-750-U-FR-T5-UPLR**

Issue Date: 04/15/2025

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P981128
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	04/15/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	FFX-CLB-90-750-U-FR-T5-UPLR
Description:	FAIRFAX POST TOP FIXTURE w/ FAIRFAX REFRACTOR T5 DISTRIBUTION LENS AND UPLIGHT REFLECTOR
Light Source:	(6) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	14337.6 lumens
Efficiency:	N/A
Efficacy:	158.3 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.17' x H: 1.67')
IES Classification:	Type V - Short
BUG Rating:	B4 - U5 - G3


Input Watts (W):	90.6
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.99
Total Harmonic Distortion (THDi):	5.42%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981128
CATALOG NUMBER: FFX-CLB-90-750-U-FR-T5-UPLR

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 2.7 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981128
CATALOG NUMBER: FFX-CLB-90-750-U-FR-T5-UPLR

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P981128
CATALOG NUMBER: FFX-CLB-90-750-U-FR-T5-UPLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6240.3	928.4	7168.8
	% Fixture	43.5	6.5	50.0
Street Side	Lumens	6240.3	928.4	7168.8
	% Fixture	43.5	6.5	50.0
Total	Lumens	12480.7	1856.9	14337.6
	% Fixture	87.0	13.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.5	0.2
10°-20°	90.9	0.6
20°-30°	199.3	1.4
30°-40°	409.5	2.9
40°-50°	845.5	5.9
50°-60°	2761.7	19.3
60°-70°	4656.3	32.5
70°-80°	2534.6	17.7
80°-90°	958.5	6.7
90°-100°	582.6	4.1
100°-110°	367.5	2.6
110°-120°	279.5	1.9
120°-130°	239.0	1.7
130°-140°	160.6	1.1
140°-150°	132.2	0.9
150°-160°	62.5	0.4
160°-170°	24.8	0.2
170°-180°	8.2	0.1
0°-90°	12480.7	87.0
0°-180°	14337.6	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P981128
CATALOG NUMBER: FFX-CLB-90-750-U-FR-T5-UPLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	157.3	1.1			
FM	(30°-60°)	2008.3	14.0			
FH	(60°-80°)	3595.4	25.1			G2/5000
FVH	(80°-90°)	479.3	3.3			G3/500
BL	(0°-30°)	157.3	1.1	B1/500		
BM	(30°-60°)	2008.3	14.0	B2/2500		
BH	(60°-80°)	3595.4	25.1	B4/5000		G2/5000
BVH	(80°-90°)	479.3	3.3			G3/500
UL	(90°-100°)	582.6	4.1		U4/1000	
UH	(100°-180°)	1274.2	8.9		U5	

BUG Rating: B4-U5-G3
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981128
CATALOG NUMBER: FFX-CLB-90-750-U-FR-T5-UPLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	390.4	390.4	390.4	390.4	390.4	390.4	390.4	390.4	390.4	390.4	390.4
2.5°	260.0	270.4	328.0	375.3	374.3	341.3	298.7	302.5	328.0	350.7	356.4
5°	261.8	258.1	255.2	243.9	240.1	245.8	242.0	230.7	225.9	226.9	244.8
7.5°	272.2	267.5	240.1	219.3	216.5	228.8	255.2	255.2	226.9	205.1	204.2
10°	244.8	243.9	253.3	262.8	265.6	254.3	242.9	237.3	235.4	233.5	231.6
12.5°	323.3	319.5	299.7	287.4	285.5	291.2	299.7	296.8	282.6	275.1	275.1
15°	321.4	323.3	326.1	321.4	320.5	321.4	326.1	323.3	318.6	312.9	312.9
17.5°	339.4	340.3	341.3	343.1	341.3	338.4	338.4	337.5	338.4	340.3	340.3
20°	366.8	367.7	367.7	367.7	366.8	361.1	361.1	362.1	361.1	363.0	362.1
22.5°	397.0	396.1	396.1	396.1	393.2	388.5	387.6	388.5	385.7	385.7	385.7
25°	426.3	428.2	431.1	430.1	425.4	421.6	418.8	419.7	417.8	417.8	417.8
27.5°	463.2	461.3	467.0	465.1	460.4	460.4	457.5	457.5	454.7	453.7	452.8
30°	504.8	503.8	503.8	504.8	502.9	501.0	501.0	499.1	494.4	495.3	497.2
32.5°	545.4	544.5	542.6	543.6	542.6	539.8	544.5	544.5	542.6	543.6	549.2
35°	585.1	590.8	604.0	613.5	616.3	615.4	619.2	625.8	621.1	618.2	621.1
37.5°	774.2	770.4	756.2	747.7	749.6	754.4	744.0	736.4	731.7	730.7	735.4
40°	873.5	869.7	848.9	850.8	836.6	841.3	846.0	852.7	847.9	837.5	837.5
42.5°	882.0	882.9	912.2	956.6	943.4	915.1	888.6	901.8	921.7	934.0	938.7
45°	1012.4	1024.7	1024.7	1027.5	1028.5	1029.4	1010.5	1019.0	1035.1	1055.0	1054.0
47.5°	1162.7	1170.3	1175.0	1180.7	1177.8	1180.7	1205.3	1198.6	1216.6	1214.7	1212.8
50°	1477.5	1509.7	1515.3	1537.1	1523.8	1526.7	1572.0	1575.8	1575.8	1573.0	1576.8
52.5°	2096.7	2125.0	2120.3	2072.1	2095.7	2138.3	2187.4	2152.5	2202.6	2178.0	2166.6
55°	2883.2	2884.1	2915.3	2982.4	3013.6	2980.5	3007.0	2941.8	3051.4	3064.7	3031.6
57.5°	3926.8	3946.6	3953.3	3970.3	3945.7	3941.9	3960.8	3920.2	3971.2	3921.1	3941.0
60°	4819.2	4793.6	4720.9	4617.8	4629.2	4669.8	4743.5	4718.0	4682.1	4612.1	4596.1
62.5°	5051.7	5047.9	5032.8	4995.0	4972.3	4954.3	4963.8	5002.6	4957.2	4988.4	4946.8
65°	4956.2	4953.4	4967.6	5000.7	4976.1	4915.6	4862.6	4926.0	4897.6	5001.6	4971.4
67.5°	4650.9	4638.6	4624.4	4685.9	4647.1	4560.2	4521.4	4527.1	4510.0	4614.0	4583.8
70°	3836.0	3816.2	3842.7	3940.0	3884.3	3806.7	3762.3	3781.2	3785.9	3852.1	3862.5
72.5°	2874.7	2899.3	2925.7	2990.9	2977.7	2935.2	2959.7	2988.1	3015.5	3040.1	3029.7
75°	2275.3	2304.7	2251.7	2283.9	2272.5	2305.6	2328.3	2341.5	2338.7	2313.2	2301.8
77.5°	1729.9	1753.5	1741.3	1731.8	1740.3	1773.4	1845.2	1836.7	1796.1	1752.6	1761.1
80°	1244.0	1285.6	1290.3	1286.6	1304.5	1309.2	1369.7	1353.7	1320.6	1319.6	1329.1
82.5°	814.9	833.8	893.3	946.3	960.4	936.8	976.5	991.6	1000.1	1001.1	998.2
85°	754.4	775.2	761.0	789.3	795.9	802.6	809.2	814.9	824.3	832.8	836.6
87.5°	712.8	746.8	744.9	763.8	761.9	775.2	787.4	791.2	779.9	767.6	763.8
90°	637.1	664.5	674.9	686.3	692.0	690.1	700.5	700.5	692.9	687.2	685.3
92.5°	571.9	587.0	596.5	610.7	614.4	612.6	623.0	618.2	619.2	621.1	623.0
95°	540.7	547.3	544.5	550.2	542.6	536.0	539.8	534.1	531.3	526.5	526.5
97.5°	451.9	450.9	450.9	452.8	449.0	443.3	446.2	445.2	446.2	446.2	442.4
100°	396.1	395.1	389.5	388.5	387.6	385.7	382.8	383.8	383.8	382.8	383.8
102.5°	395.1	386.6	374.3	361.1	361.1	358.3	359.2	358.3	357.3	351.7	348.8
105°	402.7	389.5	368.7	342.2	338.4	339.4	342.2	341.3	337.5	331.8	328.0
107.5°	372.5	357.3	345.0	328.0	323.3	322.3	324.2	325.2	321.4	313.8	308.2
110°	329.9	324.2	318.6	312.0	307.2	306.3	306.3	306.3	302.5	299.7	293.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P981128
CATALOG NUMBER: FFX-CLB-90-750-U-FR-T5-UPLR

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	*311.0*	304.4	297.8	292.1	289.3	288.3	286.4	284.5	281.7	278.9	275.1
115°	*293.0*	293.0	288.3	267.5	262.8	261.8	260.9	260.9	260.9	260.9	260.0
117.5°	*317.6*	314.8	296.8	270.4	261.8	257.1	253.3	255.2	254.3	260.9	259.0
120°	*363.9*	343.1	304.4	285.5	277.9	274.1	275.1	276.0	275.1	273.2	269.4
122.5°	*360.2*	337.5	313.8	299.7	291.2	290.2	294.0	293.0	284.5	271.3	260.9
125°	*316.7*	304.4	290.2	277.0	272.2	270.4	272.2	269.4	263.7	257.1	246.7
127.5°	*245.8*	243.9	236.3	230.7	231.6	234.4	239.2	239.2	236.3	232.5	226.9
130°	*220.3*	218.4	219.3	221.2	220.3	220.3	215.5	211.7	218.4	224.0	221.2
132.5°	*203.2*	204.2	213.6	227.8	225.0	217.4	206.1	204.2	214.6	225.9	225.0
135°	*195.7*	196.6	204.2	218.4	214.6	205.1	200.4	201.3	207.0	212.7	211.7
137.5°	*195.7*	195.7	193.8	198.5	198.5	198.5	197.6	200.4	204.2	204.2	201.3
140°	*192.8*	194.7	189.1	190.0	192.8	195.7	196.6	200.4	201.3	200.4	196.6
142.5°	*176.8*	178.7	184.3	191.9	193.8	195.7	201.3	200.4	200.4	200.4	198.5
145°	*217.4*	217.4	222.1	228.8	225.9	222.1	224.0	225.0	226.9	228.8	226.9
147.5°	*240.1*	240.1	234.4	232.5	227.8	227.8	233.5	232.5	231.6	229.7	230.7
150°	*198.5*	197.6	192.8	191.0	191.0	189.1	191.9	191.9	189.1	187.2	188.1
152.5°	*141.8*	142.7	140.9	142.7	145.6	148.4	151.2	153.1	153.1	153.1	151.2
155°	*128.6*	126.7	125.7	127.6	128.6	127.6	125.7	125.7	125.7	123.8	122.9
157.5°	*111.5*	110.6	109.7	110.6	110.6	111.5	112.5	113.4	113.4	111.5	110.6
160°	*96.4*	96.4	96.4	97.4	97.4	96.4	95.5	96.4	98.3	98.3	98.3
162.5°	*87.0*	87.9	88.9	90.7	90.7	88.9	87.0	87.0	88.9	90.7	90.7
165°	*80.4*	80.4	82.2	86.0	87.0	84.1	81.3	81.3	84.1	87.9	88.9
167.5°	*80.4*	81.3	84.1	87.0	86.0	83.2	80.4	80.4	83.2	86.0	86.0
170°	*86.0*	86.0	85.1	84.1	83.2	83.2	83.2	84.1	85.1	84.1	84.1
172.5°	*90.7*	89.8	87.0	84.1	83.2	86.0	87.9	87.0	86.0	84.1	84.1
175°	*92.6*	91.7	89.8	87.9	87.9	89.8	90.7	88.9	87.0	86.0	85.1
177.5°	*83.2*	83.2	82.2	82.2	83.2	82.2	82.2	82.2	81.3	80.4	79.4
180°	*71.8*	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-5

Test Date: 03/25/2025

Luminaire Tested: FFX-CLB-100-750-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-750-U-FR-T5

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2501-332-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	03/31/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**FFX-CLB-100-750-U-FR-T5**
Description:	FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K):	4987	CRI (Ra):	75.8		
CIE u':	0.2094	R1:	71.6	R9:	-30.4
CIE v':	0.4882	R2:	82.8	R10:	59.9
Duv:	0.0031	R3:	91.2	R11:	70.9
CIE x:	0.3461	R4:	73.8	R12:	51.2
CIE y:	0.3586	R5:	73.0	R13:	74.2
CIE z:	0.2954	R6:	76.1	R14:	95.3
Peak Wavelength (nm):	450	R7:	82.9	R15:	63.7
Dominant Wavelength (nm):	570	R8:	54.9		
Purity:	11.4				

Rf:	78.3
Rg:	93.4



Test Conditions


Stabilization Time:	67M
Operation Time:	2H 7M
Sphere Temperature (°C):	24.9

REPORT NUMBER: SP1-2501-332-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4987K
CIE x = 0.3461
CIE y = 0.3586
Duv = 0.0031

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2501-332-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.87**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.92**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	255	NR	620	445	NR	750	11	NR	880	0	NR
365	0	NR	495	298	NR	625	403	NR	755	9	NR	885	0	NR
370	0	NR	500	345	NR	630	362	NR	760	8	NR	890	0	NR
375	0	NR	505	387	NR	635	323	NR	765	7	NR	895	0	NR
380	1	NR	510	417	NR	640	287	NR	770	6	NR	900	0	NR
385	2	NR	515	445	NR	645	254	NR	775	5	NR	905	0	NR
390	3	NR	520	464	NR	650	222	NR	780	4	NR	910	0	NR
395	5	NR	525	483	NR	655	194	NR	785	4	NR	915	0	NR
400	7	NR	530	503	NR	660	168	NR	790	3	NR	920	0	NR
405	12	NR	535	519	NR	665	146	NR	795	3	NR	925	0	NR
410	21	NR	540	539	NR	670	126	NR	800	3	NR	930	0	NR
415	38	NR	545	561	NR	675	108	NR	805	2	NR	935	0	NR
420	68	NR	550	580	NR	680	93	NR	810	2	NR	940	0	NR
425	119	NR	555	602	NR	685	80	NR	815	2	NR	945	0	NR
430	199	NR	560	624	NR	690	69	NR	820	2	NR	950	0	NR
435	315	NR	565	641	NR	695	59	NR	825	1	NR	955	0	NR
440	489	NR	570	657	NR	700	50	NR	830	1	NR	960	0	NR
445	787	NR	575	663	NR	705	43	NR	835	1	NR	965	0	NR
450	1000	NR	580	666	NR	710	36	NR	840	1	NR	970	0	NR
455	757	NR	585	657	NR	715	31	NR	845	1	NR	975	0	NR
460	503	NR	590	646	NR	720	27	NR	850	1	NR	980	0	NR
465	398	NR	595	624	NR	725	23	NR	855	1	NR	985	0	NR
470	290	NR	600	597	NR	730	20	NR	860	1	NR	990	0	NR
475	222	NR	605	564	NR	735	17	NR	865	0	NR	995	0	NR
480	215	NR	610	525	NR	740	14	NR	870	0	NR	1000	0	NR
485	228	NR	615	486	NR	745	12	NR	875	0	NR			


REPORT NUMBER: SP1-2501-332-5

TM-30-18


Summary


R_f = 78.3
R_g = 93.4
CIE R_a = 75.8
R_9 = -30.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2501-332-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 71	CES51 = 92	CES76 = 63
CES02 = 60	CES27 = 92	CES52 = 91	CES77 = 76
CES03 = 30	CES28 = 86	CES53 = 83	CES78 = 64
CES04 = 69	CES29 = 75	CES54 = 86	CES79 = 86
CES05 = 46	CES30 = 89	CES55 = 85	CES80 = 84
CES06 = 50	CES31 = 78	CES56 = 79	CES81 = 80
CES07 = 39	CES32 = 71	CES57 = 78	CES82 = 93
CES08 = 38	CES33 = 85	CES58 = 79	CES83 = 93
CES09 = 29	CES34 = 78	CES59 = 88	CES84 = 87
CES10 = 73	CES35 = 88	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 89	CES61 = 84	CES86 = 73
CES12 = 61	CES37 = 86	CES62 = 87	CES87 = 79
CES13 = 41	CES38 = 98	CES63 = 82	CES88 = 81
CES14 = 74	CES39 = 97	CES64 = 72	CES89 = 74
CES15 = 70	CES40 = 93	CES65 = 69	CES90 = 81
CES16 = 46	CES41 = 97	CES66 = 68	CES91 = 76
CES17 = 49	CES42 = 88	CES67 = 66	CES92 = 58
CES18 = 55	CES43 = 85	CES68 = 71	CES93 = 75
CES19 = 71	CES44 = 99	CES69 = 78	CES94 = 54
CES20 = 64	CES45 = 90	CES70 = 65	CES95 = 66
CES21 = 85	CES46 = 87	CES71 = 61	CES96 = 78
CES22 = 77	CES47 = 92	CES72 = 86	CES97 = 88
CES23 = 91	CES48 = 81	CES73 = 57	CES98 = 78
CES24 = 90	CES49 = 86	CES74 = 93	CES99 = 64
CES25 = 71	CES50 = 91	CES75 = 63	





REPORT NUMBER: SP1-2501-332-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2501-332-5

TM-30-18

Measure Comparisons





(END OF REPORT)