

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P559788

Luminaire Tested: **SDL-PA1-100-722-U-T2R-HSS**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P559788  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-100-722-U-T2R-HSS  
Description: Springdale  
(1) 70 CRI, 2200K, 1200mA LIGHT ENGINE WITH 24 LEDS AND TYPE II R OPTICS  
WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6177.2 lumens  
Efficiency: N/A  
Efficacy: 65.9 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type II - Medium  
BUG Rating: B0 - U0 - G2

Input Watts (W): 93.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 16.9 fc  
 Type II - Medium - N/A

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

## Luminous Intensity Polar Plot



REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 326.3    | 0.0    | 326.3  |
|                    | % Fixture | 5.3      | 0.0    | 5.3    |
| <b>Street Side</b> | Lumens    | 5850.9   | 0.0    | 5850.9 |
|                    | % Fixture | 94.7     | 0.0    | 94.7   |
| <b>Total</b>       | Lumens    | 6177.2   | 0.0    | 6177.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 71.6   | 1.2       |
| 10°-20°   | 178.2  | 2.9       |
| 20°-30°   | 338.8  | 5.5       |
| 30°-40°   | 752.9  | 12.2      |
| 40°-50°   | 1213.9 | 19.7      |
| 50°-60°   | 1463.0 | 23.7      |
| 60°-70°   | 1326.0 | 21.5      |
| 70°-80°   | 790.2  | 12.8      |
| 80°-90°   | 42.6   | 0.7       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6177.2 | 100.0     |
| 0°-180°   | 6177.2 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P559788


CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 506.7  | 8.2       |                         |      |         |
| FM   | (30°-60°)   | 3277.0 | 53.1      |                         |      |         |
| FH   | (60°-80°)   | 2028.3 | 32.8      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 38.9   | 0.6       |                         |      | G1/100  |
| BL   | (0°-30°)    | 82.0   | 1.3       | B0/110                  |      |         |
| BM   | (30°-60°)   | 152.7  | 2.5       | B0/220                  |      |         |
| BH   | (60°-80°)   | 87.9   | 1.4       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 3.7    | 0.1       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type II Medium



REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  |
| 2.5°  | 1005.9 | 1028.0 | 1050.1 | 1058.4 | 1069.4 | 1077.7 | 1086.0 | 1094.3 | 1102.6 | 1108.1 | 1116.4 |
| 5°    | 1144.0 | 1141.3 | 1138.5 | 1135.7 | 1135.7 | 1133.0 | 1130.2 | 1127.5 | 1124.7 | 1119.2 | 1116.4 |
| 7.5°  | 1003.1 | 1074.9 | 1144.0 | 1146.8 | 1149.6 | 1149.6 | 1152.3 | 1168.9 | 1185.5 | 1199.3 | 1215.9 |
| 10°   | 1304.3 | 1304.3 | 1304.3 | 1304.3 | 1304.3 | 1301.5 | 1301.5 | 1304.3 | 1304.3 | 1307.1 | 1307.1 |
| 12.5° | 1097.1 | 1113.6 | 1127.5 | 1177.2 | 1224.2 | 1273.9 | 1320.9 | 1331.9 | 1343.0 | 1351.3 | 1362.3 |
| 15°   | 1326.4 | 1331.9 | 1337.5 | 1340.2 | 1343.0 | 1343.0 | 1345.8 | 1304.3 | 1262.9 | 1221.4 | 1180.0 |
| 17.5° | 1050.1 | 1055.6 | 1058.4 | 1094.3 | 1130.2 | 1166.1 | 1202.1 | 1221.4 | 1243.5 | 1262.9 | 1282.2 |
| 20°   | 1345.8 | 1348.5 | 1351.3 | 1354.0 | 1356.8 | 1356.8 | 1359.6 | 1271.1 | 1182.7 | 1094.3 | 1005.9 |
| 22.5° | 1124.7 | 1127.5 | 1127.5 | 1135.7 | 1141.3 | 1149.6 | 1155.1 | 1188.2 | 1221.4 | 1254.6 | 1287.7 |
| 25°   | 1544.7 | 1544.7 | 1542.0 | 1528.1 | 1517.1 | 1503.3 | 1489.5 | 1406.6 | 1323.7 | 1238.0 | 1155.1 |
| 27.5° | 1436.9 | 1439.7 | 1439.7 | 1428.7 | 1417.6 | 1406.6 | 1395.5 | 1412.1 | 1431.4 | 1448.0 | 1464.6 |
| 30°   | 2072.5 | 2072.5 | 2072.5 | 2058.7 | 2042.1 | 2028.3 | 2011.7 | 1890.1 | 1768.6 | 1644.2 | 1522.6 |
| 32.5° | 2785.5 | 2735.7 | 2683.2 | 2583.7 | 2484.3 | 2382.0 | 2282.5 | 2207.9 | 2133.3 | 2055.9 | 1981.3 |
| 35°   | 3103.3 | 3095.0 | 3086.7 | 3050.8 | 3014.8 | 2976.1 | 2940.2 | 2796.5 | 2652.8 | 2506.4 | 2362.7 |
| 37.5° | 3371.3 | 3360.2 | 3346.4 | 3318.8 | 3291.2 | 3263.5 | 3235.9 | 3089.4 | 2940.2 | 2793.8 | 2644.5 |
| 40°   | 3586.8 | 3578.6 | 3570.3 | 3548.2 | 3526.0 | 3503.9 | 3481.8 | 3324.3 | 3166.8 | 3009.3 | 2851.8 |
| 42.5° | 3741.6 | 3741.6 | 3738.8 | 3722.2 | 3702.9 | 3686.3 | 3667.0 | 3509.5 | 3352.0 | 3194.4 | 3036.9 |
| 45°   | 3857.7 | 3857.7 | 3857.7 | 3846.6 | 3832.8 | 3821.7 | 3807.9 | 3669.7 | 3534.3 | 3396.2 | 3258.0 |
| 47.5° | 3874.2 | 3877.0 | 3879.8 | 3879.8 | 3879.8 | 3879.8 | 3879.8 | 3749.9 | 3622.8 | 3492.9 | 3363.0 |
| 50°   | 3722.2 | 3730.5 | 3738.8 | 3752.6 | 3769.2 | 3783.0 | 3796.9 | 3733.3 | 3667.0 | 3603.4 | 3537.1 |
| 52.5° | 3316.0 | 3352.0 | 3385.1 | 3421.0 | 3457.0 | 3490.1 | 3526.0 | 3501.2 | 3476.3 | 3451.4 | 3426.6 |
| 55°   | 2522.9 | 2545.1 | 2564.4 | 2666.6 | 2768.9 | 2871.1 | 2973.4 | 3017.6 | 3059.0 | 3103.3 | 3144.7 |
| 57.5° | 1959.2 | 1967.5 | 1973.0 | 2039.4 | 2105.7 | 2169.2 | 2235.6 | 2346.1 | 2456.6 | 2564.4 | 2674.9 |
| 60°   | 1575.1 | 1575.1 | 1575.1 | 1613.8 | 1649.7 | 1688.4 | 1724.3 | 1823.8 | 1923.3 | 2022.8 | 2122.3 |
| 62.5° | 1171.7 | 1182.7 | 1193.8 | 1232.5 | 1268.4 | 1307.1 | 1343.0 | 1392.7 | 1442.5 | 1492.2 | 1542.0 |
| 65°   | 812.4  | 826.2  | 837.3  | 862.2  | 889.8  | 914.7  | 939.5  | 981.0  | 1025.2 | 1066.7 | 1108.1 |
| 67.5° | 572.0  | 577.5  | 583.1  | 596.9  | 607.9  | 621.8  | 632.8  | 660.4  | 685.3  | 712.9  | 737.8  |
| 70°   | 406.2  | 409.0  | 409.0  | 420.0  | 431.1  | 442.1  | 453.2  | 464.2  | 475.3  | 483.6  | 494.6  |
| 72.5° | 295.7  | 298.4  | 301.2  | 309.5  | 315.0  | 323.3  | 328.8  | 334.4  | 339.9  | 345.4  | 350.9  |
| 75°   | 152.0  | 157.5  | 160.3  | 182.4  | 204.5  | 226.6  | 248.7  | 251.5  | 254.2  | 254.2  | 257.0  |
| 77.5° | 127.1  | 129.9  | 129.9  | 132.6  | 135.4  | 138.2  | 140.9  | 154.7  | 171.3  | 185.1  | 199.0  |
| 80°   | 91.2   | 91.2   | 88.4   | 94.0   | 99.5   | 105.0  | 110.5  | 116.1  | 121.6  | 124.4  | 129.9  |
| 82.5° | 52.5   | 55.3   | 55.3   | 58.0   | 60.8   | 63.6   | 66.3   | 71.8   | 80.1   | 85.7   | 91.2   |
| 85°   | 5.5    | 8.3    | 11.1   | 16.6   | 22.1   | 27.6   | 33.2   | 41.5   | 47.0   | 55.3   | 60.8   |
| 87.5° | 2.8    | 2.8    | 2.8    | 2.8    | 5.5    | 5.5    | 5.5    | 8.3    | 8.3    | 11.1   | 11.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  |
| 2.5°  | 1121.9 | 1127.5 | 1130.2 | 1135.7 | 1133.0 | 1127.5 | 1124.7 | 1119.2 | 1110.9 | 1102.6 | 1091.5 |
| 5°    | 1110.9 | 1105.3 | 1099.8 | 1094.3 | 1086.0 | 1080.5 | 1072.2 | 1063.9 | 1052.8 | 1044.6 | 1033.5 |
| 7.5°  | 1215.9 | 1213.1 | 1213.1 | 1210.4 | 1202.1 | 1196.5 | 1188.2 | 1180.0 | 1166.1 | 1152.3 | 1138.5 |
| 10°   | 1246.3 | 1185.5 | 1121.9 | 1061.1 | 1074.9 | 1088.8 | 1102.6 | 1116.4 | 1074.9 | 1033.5 | 989.3  |
| 12.5° | 1334.7 | 1307.1 | 1279.4 | 1251.8 | 1207.6 | 1160.6 | 1116.4 | 1069.4 | 1047.3 | 1022.4 | 1000.3 |
| 15°   | 1149.6 | 1121.9 | 1091.5 | 1061.1 | 1080.5 | 1099.8 | 1119.2 | 1138.5 | 1074.9 | 1008.6 | 945.1  |
| 17.5° | 1257.3 | 1229.7 | 1204.8 | 1177.2 | 1099.8 | 1022.4 | 942.3  | 864.9  | 931.3  | 994.8  | 1061.1 |
| 20°   | 1028.0 | 1050.1 | 1069.4 | 1091.5 | 1119.2 | 1146.8 | 1171.7 | 1199.3 | 1166.1 | 1133.0 | 1099.8 |
| 22.5° | 1243.5 | 1202.1 | 1157.8 | 1113.6 | 1133.0 | 1152.3 | 1168.9 | 1188.2 | 1149.6 | 1110.9 | 1069.4 |
| 25°   | 1199.3 | 1246.3 | 1290.5 | 1334.7 | 1265.6 | 1199.3 | 1130.2 | 1061.1 | 1121.9 | 1182.7 | 1243.5 |
| 27.5° | 1401.0 | 1337.5 | 1271.1 | 1207.6 | 1265.6 | 1323.7 | 1378.9 | 1436.9 | 1384.4 | 1329.2 | 1276.7 |
| 30°   | 1514.3 | 1506.0 | 1495.0 | 1486.7 | 1456.3 | 1428.7 | 1398.3 | 1367.9 | 1384.4 | 1401.0 | 1417.6 |
| 32.5° | 1887.4 | 1796.2 | 1702.2 | 1608.3 | 1630.4 | 1652.5 | 1671.8 | 1693.9 | 1669.1 | 1644.2 | 1616.6 |
| 35°   | 2241.1 | 2119.5 | 1995.1 | 1873.6 | 1870.8 | 1865.3 | 1862.5 | 1857.0 | 1845.9 | 1834.9 | 1823.8 |
| 37.5° | 2506.4 | 2368.2 | 2230.0 | 2091.9 | 2094.6 | 2094.6 | 2097.4 | 2097.4 | 2058.7 | 2020.0 | 1981.3 |
| 40°   | 2724.7 | 2597.6 | 2470.4 | 2343.3 | 2332.3 | 2321.2 | 2310.2 | 2299.1 | 2246.6 | 2191.3 | 2138.8 |
| 42.5° | 2909.8 | 2785.5 | 2658.4 | 2531.2 | 2511.9 | 2495.3 | 2476.0 | 2456.6 | 2412.4 | 2365.4 | 2321.2 |
| 45°   | 3111.5 | 2965.1 | 2818.6 | 2672.2 | 2655.6 | 2639.0 | 2622.4 | 2605.8 | 2569.9 | 2534.0 | 2498.1 |
| 47.5° | 3216.6 | 3070.1 | 2920.9 | 2774.4 | 2763.4 | 2749.5 | 2738.5 | 2724.7 | 2705.3 | 2683.2 | 2663.9 |
| 50°   | 3365.8 | 3197.2 | 3025.9 | 2854.6 | 2849.0 | 2843.5 | 2835.2 | 2829.7 | 2824.2 | 2821.4 | 2815.9 |
| 52.5° | 3296.7 | 3164.0 | 3034.2 | 2901.5 | 2904.3 | 2904.3 | 2907.1 | 2907.1 | 2920.9 | 2934.7 | 2948.5 |
| 55°   | 3075.6 | 3009.3 | 2940.2 | 2871.1 | 2884.9 | 2901.5 | 2915.3 | 2929.2 | 2965.1 | 2998.2 | 3034.2 |
| 57.5° | 2686.0 | 2697.0 | 2708.1 | 2719.1 | 2768.9 | 2815.9 | 2865.6 | 2912.6 | 2965.1 | 3014.8 | 3067.3 |
| 60°   | 2183.1 | 2243.8 | 2301.9 | 2362.7 | 2478.7 | 2594.8 | 2710.9 | 2826.9 | 2907.1 | 2984.4 | 3064.6 |
| 62.5° | 1627.6 | 1713.3 | 1798.9 | 1884.6 | 2064.2 | 2246.6 | 2426.2 | 2605.8 | 2727.4 | 2846.3 | 2967.8 |
| 65°   | 1188.2 | 1268.4 | 1345.8 | 1425.9 | 1641.4 | 1857.0 | 2072.5 | 2288.1 | 2462.2 | 2633.5 | 2807.6 |
| 67.5° | 795.8  | 853.9  | 909.1  | 967.2  | 1185.5 | 1403.8 | 1622.1 | 1840.4 | 2080.8 | 2321.2 | 2558.9 |
| 70°   | 525.0  | 552.7  | 583.1  | 610.7  | 798.6  | 983.8  | 1171.7 | 1356.8 | 1641.4 | 1923.3 | 2207.9 |
| 72.5° | 359.2  | 367.5  | 375.8  | 384.1  | 511.2  | 638.3  | 765.5  | 892.6  | 1180.0 | 1467.3 | 1752.0 |
| 75°   | 257.0  | 254.2  | 254.2  | 251.5  | 326.1  | 400.7  | 472.5  | 547.1  | 771.0  | 992.0  | 1215.9 |
| 77.5° | 196.2  | 190.7  | 187.9  | 182.4  | 218.3  | 254.2  | 290.2  | 326.1  | 431.1  | 538.9  | 643.9  |
| 80°   | 124.4  | 118.8  | 110.5  | 105.0  | 118.8  | 132.6  | 146.5  | 160.3  | 176.9  | 193.4  | 210.0  |
| 82.5° | 91.2   | 91.2   | 91.2   | 91.2   | 91.2   | 94.0   | 94.0   | 94.0   | 88.4   | 82.9   | 74.6   |
| 85°   | 58.0   | 55.3   | 52.5   | 49.7   | 44.2   | 38.7   | 33.2   | 27.6   | 30.4   | 33.2   | 33.2   |
| 87.5° | 11.1   | 8.3    | 8.3    | 5.5    | 5.5    | 5.5    | 5.5    | 5.5    | 8.3    | 8.3    | 11.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  |
| 2.5°  | 1083.2 | 1072.2 | 1061.1 | 1050.1 | 1039.0 | 1028.0 | 1016.9 | 1005.9 | 994.8  | 978.2  | 964.4  |
| 5°    | 1022.4 | 1052.8 | 1086.0 | 1116.4 | 1146.8 | 1130.2 | 1113.6 | 1097.1 | 1080.5 | 1052.8 | 1025.2 |
| 7.5°  | 1124.7 | 1088.8 | 1055.6 | 1022.4 | 986.5  | 994.8  | 1003.1 | 1011.4 | 1019.7 | 994.8  | 961.6  |
| 10°   | 947.8  | 928.5  | 909.1  | 889.8  | 870.5  | 859.4  | 845.6  | 834.5  | 820.7  | 889.8  | 862.2  |
| 12.5° | 975.5  | 967.2  | 958.9  | 947.8  | 939.5  | 884.3  | 831.8  | 776.5  | 721.2  | 699.1  | 707.4  |
| 15°   | 878.7  | 870.5  | 862.2  | 853.9  | 845.6  | 873.2  | 903.6  | 931.3  | 958.9  | 953.4  | 947.8  |
| 17.5° | 1124.7 | 1088.8 | 1055.6 | 1019.7 | 983.8  | 967.2  | 947.8  | 931.3  | 911.9  | 881.5  | 873.2  |
| 20°   | 1066.7 | 1028.0 | 989.3  | 950.6  | 911.9  | 950.6  | 986.5  | 1025.2 | 1061.1 | 1124.7 | 1105.3 |
| 22.5° | 1030.7 | 1094.3 | 1160.6 | 1224.2 | 1287.7 | 1226.9 | 1168.9 | 1108.1 | 1047.3 | 1066.7 | 972.7  |
| 25°   | 1304.3 | 1257.3 | 1213.1 | 1166.1 | 1119.2 | 1180.0 | 1240.7 | 1301.5 | 1362.3 | 1334.7 | 1290.5 |
| 27.5° | 1221.4 | 1268.4 | 1312.6 | 1359.6 | 1403.8 | 1425.9 | 1450.8 | 1472.9 | 1495.0 | 1439.7 | 1450.8 |
| 30°   | 1434.2 | 1492.2 | 1547.5 | 1605.5 | 1660.8 | 1763.0 | 1862.5 | 1964.7 | 2064.2 | 2042.1 | 1953.7 |
| 32.5° | 1591.7 | 1688.4 | 1785.1 | 1879.1 | 1975.8 | 2033.8 | 2094.6 | 2152.7 | 2210.7 | 2216.2 | 2105.7 |
| 35°   | 1812.8 | 1879.1 | 1945.4 | 2011.7 | 2078.0 | 2166.5 | 2252.1 | 2340.6 | 2426.2 | 2376.5 | 2252.1 |
| 37.5° | 1942.6 | 2011.7 | 2083.6 | 2152.7 | 2221.7 | 2329.5 | 2437.3 | 2542.3 | 2650.1 | 2542.3 | 2406.9 |
| 40°   | 2083.6 | 2158.2 | 2235.6 | 2310.2 | 2384.8 | 2495.3 | 2603.1 | 2713.6 | 2821.4 | 2815.9 | 2630.7 |
| 42.5° | 2274.2 | 2348.9 | 2426.2 | 2500.8 | 2575.5 | 2691.5 | 2807.6 | 2920.9 | 3036.9 | 3034.2 | 2824.2 |
| 45°   | 2462.2 | 2531.2 | 2597.6 | 2666.6 | 2733.0 | 2865.6 | 2998.2 | 3130.9 | 3263.5 | 3277.3 | 3039.7 |
| 47.5° | 2641.8 | 2702.6 | 2763.4 | 2824.2 | 2884.9 | 3067.3 | 3246.9 | 3429.3 | 3608.9 | 3523.3 | 3266.3 |
| 50°   | 2810.3 | 2871.1 | 2931.9 | 2992.7 | 3053.5 | 3266.3 | 3481.8 | 3694.6 | 3907.4 | 3794.1 | 3517.8 |
| 52.5° | 2962.3 | 3036.9 | 3114.3 | 3188.9 | 3263.5 | 3495.7 | 3727.8 | 3959.9 | 4192.0 | 4076.0 | 3791.3 |
| 55°   | 3067.3 | 3172.3 | 3274.6 | 3379.6 | 3481.8 | 3738.8 | 3998.6 | 4255.6 | 4512.6 | 4379.9 | 4051.1 |
| 57.5° | 3117.1 | 3241.4 | 3368.5 | 3492.9 | 3617.2 | 3882.5 | 4150.6 | 4415.9 | 4681.1 | 4548.5 | 4211.4 |
| 60°   | 3141.9 | 3285.6 | 3429.3 | 3570.3 | 3714.0 | 4001.3 | 4291.5 | 4578.9 | 4866.3 | 4753.0 | 4410.3 |
| 62.5° | 3086.7 | 3269.1 | 3454.2 | 3636.6 | 3819.0 | 4125.7 | 4432.4 | 4736.4 | 5043.1 | 4968.5 | 4642.4 |
| 65°   | 2978.9 | 3219.3 | 3462.5 | 3702.9 | 3943.3 | 4308.1 | 4672.8 | 5034.8 | 5399.6 | 5319.5 | 4993.4 |
| 67.5° | 2799.3 | 3114.3 | 3429.3 | 3744.4 | 4059.4 | 4512.6 | 4963.0 | 5416.2 | 5866.6 | 5786.5 | 5413.4 |
| 70°   | 2489.8 | 2884.9 | 3280.1 | 3672.5 | 4067.7 | 4598.2 | 5131.6 | 5662.1 | 6192.7 | 6087.7 | 5645.5 |
| 72.5° | 2039.4 | 2484.3 | 2929.2 | 3371.3 | 3816.2 | 4382.7 | 4951.9 | 5518.4 | 6084.9 | 5886.0 | 5383.0 |
| 75°   | 1436.9 | 1843.2 | 2249.4 | 2652.8 | 3059.0 | 3556.4 | 4053.9 | 4548.5 | 5045.9 | 4791.7 | 4299.8 |
| 77.5° | 748.9  | 1000.3 | 1249.0 | 1500.5 | 1749.2 | 2138.8 | 2525.7 | 2915.3 | 3302.2 | 2846.3 | 2476.0 |
| 80°   | 226.6  | 331.6  | 433.8  | 538.9  | 641.1  | 732.3  | 823.5  | 911.9  | 1003.1 | 746.1  | 619.0  |
| 82.5° | 69.1   | 91.2   | 110.5  | 132.6  | 152.0  | 152.0  | 152.0  | 149.2  | 149.2  | 118.8  | 99.5   |
| 85°   | 35.9   | 38.7   | 38.7   | 41.5   | 41.5   | 41.5   | 38.7   | 38.7   | 35.9   | 35.9   | 30.4   |
| 87.5° | 11.1   | 11.1   | 13.8   | 13.8   | 13.8   | 13.8   | 13.8   | 11.1   | 11.1   | 11.1   | 11.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°   | 97.5° | 100°  | 102.5° | 105°  | 107.5° |
|-------|--------|--------|--------|--------|--------|-------|-------|-------|--------|-------|--------|
| 0°    | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4 | 906.4 | 906.4 | 906.4  | 906.4 | 906.4  |
| 2.5°  | 953.4  | 939.5  | 925.7  | 909.1  | 892.6  | 876.0 | 859.4 | 842.8 | 826.2  | 809.7 | 795.8  |
| 5°    | 1000.3 | 972.7  | 945.1  | 914.7  | 881.5  | 848.4 | 818.0 | 787.6 | 754.4  | 724.0 | 696.4  |
| 7.5°  | 928.5  | 895.3  | 853.9  | 812.4  | 771.0  | 729.5 | 685.3 | 643.9 | 599.6  | 555.4 | 519.5  |
| 10°   | 831.8  | 804.1  | 759.9  | 712.9  | 663.2  | 610.7 | 552.7 | 494.6 | 436.6  | 378.6 | 353.7  |
| 12.5° | 712.9  | 721.2  | 674.3  | 627.3  | 574.8  | 522.3 | 467.0 | 411.7 | 353.7  | 298.4 | 281.9  |
| 15°   | 942.3  | 936.8  | 876.0  | 815.2  | 735.1  | 654.9 | 574.8 | 491.9 | 411.7  | 328.8 | 287.4  |
| 17.5° | 862.2  | 853.9  | 787.6  | 721.2  | 649.4  | 577.5 | 502.9 | 425.6 | 350.9  | 273.6 | 234.9  |
| 20°   | 1088.8 | 1069.4 | 986.5  | 900.9  | 795.8  | 688.1 | 583.1 | 478.1 | 373.1  | 268.0 | 223.8  |
| 22.5° | 878.7  | 784.8  | 718.5  | 652.2  | 569.3  | 483.6 | 414.5 | 342.7 | 273.6  | 201.7 | 174.1  |
| 25°   | 1243.5 | 1199.3 | 1086.0 | 969.9  | 823.5  | 677.0 | 558.2 | 439.4 | 320.5  | 201.7 | 168.6  |
| 27.5° | 1461.8 | 1472.9 | 1318.1 | 1163.4 | 978.2  | 793.1 | 638.3 | 483.6 | 328.8  | 174.1 | 149.2  |
| 30°   | 1865.3 | 1776.8 | 1594.5 | 1409.3 | 1149.6 | 887.0 | 704.7 | 522.3 | 339.9  | 157.5 | 135.4  |
| 32.5° | 1997.9 | 1887.4 | 1680.1 | 1470.1 | 1166.1 | 859.4 | 677.0 | 494.6 | 309.5  | 127.1 | 113.3  |
| 35°   | 2130.6 | 2006.2 | 1768.6 | 1530.9 | 1182.7 | 831.8 | 649.4 | 469.8 | 287.4  | 105.0 | 96.7   |
| 37.5° | 2271.5 | 2136.1 | 1870.8 | 1602.7 | 1199.3 | 795.8 | 621.8 | 444.9 | 270.8  | 94.0  | 85.7   |
| 40°   | 2448.3 | 2263.2 | 1970.3 | 1674.6 | 1215.9 | 757.2 | 588.6 | 422.8 | 254.2  | 85.7  | 77.4   |
| 42.5° | 2616.9 | 2406.9 | 2080.8 | 1752.0 | 1235.2 | 718.5 | 558.2 | 400.7 | 240.4  | 80.1  | 71.8   |
| 45°   | 2804.8 | 2567.2 | 2213.5 | 1857.0 | 1262.9 | 668.7 | 519.5 | 370.3 | 221.1  | 71.8  | 63.6   |
| 47.5° | 3009.3 | 2752.3 | 2357.1 | 1962.0 | 1290.5 | 619.0 | 480.8 | 345.4 | 207.3  | 69.1  | 60.8   |
| 50°   | 3241.4 | 2965.1 | 2531.2 | 2094.6 | 1345.8 | 594.1 | 461.5 | 328.8 | 196.2  | 63.6  | 55.3   |
| 52.5° | 3509.5 | 3224.8 | 2738.5 | 2249.4 | 1412.1 | 572.0 | 444.9 | 315.0 | 187.9  | 58.0  | 49.7   |
| 55°   | 3725.0 | 3396.2 | 2857.3 | 2315.7 | 1425.9 | 533.3 | 414.5 | 292.9 | 174.1  | 52.5  | 47.0   |
| 57.5° | 3877.0 | 3539.9 | 2970.6 | 2401.4 | 1450.8 | 497.4 | 384.1 | 273.6 | 160.3  | 47.0  | 41.5   |
| 60°   | 4064.9 | 3722.2 | 3111.5 | 2498.1 | 1481.2 | 464.2 | 359.2 | 254.2 | 146.5  | 41.5  | 35.9   |
| 62.5° | 4316.4 | 3990.3 | 3313.3 | 2633.5 | 1530.9 | 425.6 | 328.8 | 232.1 | 132.6  | 35.9  | 33.2   |
| 65°   | 4664.6 | 4338.5 | 3550.9 | 2763.4 | 1577.9 | 389.6 | 301.2 | 212.8 | 121.6  | 33.2  | 30.4   |
| 67.5° | 5037.6 | 4664.6 | 3738.8 | 2810.3 | 1577.9 | 345.4 | 268.0 | 187.9 | 110.5  | 30.4  | 27.6   |
| 70°   | 5203.4 | 4761.3 | 3708.4 | 2652.8 | 1464.6 | 276.3 | 215.5 | 152.0 | 91.2   | 27.6  | 24.9   |
| 72.5° | 4882.9 | 4379.9 | 3296.7 | 2213.5 | 1193.8 | 174.1 | 135.4 | 99.5  | 60.8   | 22.1  | 19.3   |
| 75°   | 3805.1 | 3313.3 | 2459.4 | 1602.7 | 845.6  | 85.7  | 69.1  | 52.5  | 33.2   | 16.6  | 13.8   |
| 77.5° | 2108.4 | 1738.2 | 1262.9 | 787.6  | 420.0  | 49.7  | 41.5  | 33.2  | 22.1   | 13.8  | 13.8   |
| 80°   | 494.6  | 367.5  | 268.0  | 165.8  | 99.5   | 30.4  | 24.9  | 22.1  | 16.6   | 11.1  | 11.1   |
| 82.5° | 80.1   | 60.8   | 44.2   | 27.6   | 22.1   | 16.6  | 13.8  | 13.8  | 11.1   | 8.3   | 8.3    |
| 85°   | 24.9   | 19.3   | 16.6   | 11.1   | 11.1   | 8.3   | 8.3   | 8.3   | 5.5    | 5.5   | 5.5    |
| 87.5° | 8.3    | 8.3    | 8.3    | 5.5    | 5.5    | 5.5   | 5.5   | 5.5   | 5.5    | 5.5   | 5.5    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° | 135°  |
|-------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°    | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 |
| 2.5°  | 779.3 | 765.5  | 748.9 | 737.8  | 726.8 | 712.9  | 701.9 | 690.8  | 679.8 | 668.7  | 657.7 |
| 5°    | 668.7 | 638.3  | 610.7 | 574.8  | 536.1 | 500.2  | 461.5 | 444.9  | 431.1 | 414.5  | 397.9 |
| 7.5°  | 483.6 | 447.7  | 411.7 | 397.9  | 384.1 | 367.5  | 353.7 | 339.9  | 326.1 | 312.3  | 298.4 |
| 10°   | 331.6 | 306.7  | 281.9 | 270.8  | 259.8 | 245.9  | 234.9 | 223.8  | 212.8 | 199.0  | 187.9 |
| 12.5° | 265.3 | 245.9  | 229.4 | 210.0  | 190.7 | 171.3  | 152.0 | 146.5  | 140.9 | 132.6  | 127.1 |
| 15°   | 243.2 | 201.7  | 157.5 | 143.7  | 132.6 | 118.8  | 105.0 | 102.2  | 102.2 | 99.5   | 96.7  |
| 17.5° | 196.2 | 157.5  | 118.8 | 113.3  | 105.0 | 99.5   | 91.2  | 85.7   | 80.1  | 74.6   | 69.1  |
| 20°   | 179.6 | 135.4  | 91.2  | 88.4   | 85.7  | 80.1   | 77.4  | 74.6   | 74.6  | 71.8   | 69.1  |
| 22.5° | 149.2 | 121.6  | 94.0  | 85.7   | 77.4  | 69.1   | 60.8  | 60.8   | 63.6  | 63.6   | 63.6  |
| 25°   | 135.4 | 102.2  | 69.1  | 69.1   | 66.3  | 66.3   | 63.6  | 60.8   | 55.3  | 52.5   | 47.0  |
| 27.5° | 124.4 | 99.5   | 74.6  | 69.1   | 63.6  | 58.0   | 52.5  | 52.5   | 49.7  | 49.7   | 47.0  |
| 30°   | 116.1 | 94.0   | 71.8  | 66.3   | 63.6  | 58.0   | 52.5  | 49.7   | 47.0  | 41.5   | 38.7  |
| 32.5° | 102.2 | 88.4   | 74.6  | 69.1   | 60.8  | 55.3   | 47.0  | 44.2   | 41.5  | 35.9   | 33.2  |
| 35°   | 88.4  | 77.4   | 69.1  | 63.6   | 55.3  | 49.7   | 41.5  | 38.7   | 35.9  | 33.2   | 30.4  |
| 37.5° | 77.4  | 69.1   | 60.8  | 55.3   | 49.7  | 41.5   | 35.9  | 33.2   | 30.4  | 27.6   | 24.9  |
| 40°   | 69.1  | 60.8   | 52.5  | 47.0   | 41.5  | 35.9   | 30.4  | 27.6   | 27.6  | 24.9   | 22.1  |
| 42.5° | 63.6  | 55.3   | 47.0  | 41.5   | 38.7  | 33.2   | 27.6  | 24.9   | 22.1  | 19.3   | 16.6  |
| 45°   | 58.0  | 49.7   | 41.5  | 38.7   | 33.2  | 30.4   | 24.9  | 22.1   | 19.3  | 16.6   | 13.8  |
| 47.5° | 52.5  | 44.2   | 35.9  | 33.2   | 30.4  | 24.9   | 22.1  | 19.3   | 16.6  | 13.8   | 11.1  |
| 50°   | 49.7  | 41.5   | 33.2  | 30.4   | 27.6  | 22.1   | 19.3  | 16.6   | 16.6  | 13.8   | 11.1  |
| 52.5° | 44.2  | 35.9   | 27.6  | 24.9   | 22.1  | 19.3   | 16.6  | 13.8   | 13.8  | 11.1   | 8.3   |
| 55°   | 38.7  | 33.2   | 24.9  | 22.1   | 19.3  | 16.6   | 13.8  | 11.1   | 11.1  | 8.3    | 5.5   |
| 57.5° | 35.9  | 27.6   | 22.1  | 19.3   | 16.6  | 13.8   | 11.1  | 11.1   | 8.3   | 8.3    | 5.5   |
| 60°   | 30.4  | 24.9   | 19.3  | 16.6   | 13.8  | 11.1   | 8.3   | 8.3    | 5.5   | 5.5    | 2.8   |
| 62.5° | 27.6  | 24.9   | 19.3  | 16.6   | 13.8  | 11.1   | 8.3   | 8.3    | 5.5   | 5.5    | 2.8   |
| 65°   | 24.9  | 22.1   | 16.6  | 13.8   | 13.8  | 11.1   | 8.3   | 8.3    | 5.5   | 5.5    | 2.8   |
| 67.5° | 24.9  | 19.3   | 16.6  | 13.8   | 11.1  | 8.3    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   |
| 70°   | 19.3  | 16.6   | 11.1  | 11.1   | 8.3   | 8.3    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   |
| 72.5° | 16.6  | 13.8   | 11.1  | 11.1   | 8.3   | 8.3    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   |
| 75°   | 13.8  | 11.1   | 8.3   | 8.3    | 8.3   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   |
| 77.5° | 11.1  | 11.1   | 8.3   | 8.3    | 8.3   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   |
| 80°   | 8.3   | 8.3    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   |
| 82.5° | 8.3   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   |
| 85°   | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   |
| 87.5° | 5.5   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 5.5   | 5.5    | 2.8   |
| 90°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  | 162.5° |
|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°    | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  |
| 2.5°  | 646.6  | 632.8 | 621.8  | 607.9 | 588.6  | 566.5 | 547.1  | 525.0 | 522.3  | 519.5 | 514.0  |
| 5°    | 389.6  | 381.3 | 373.1  | 364.8 | 359.2  | 353.7 | 348.2  | 342.7 | 337.1  | 334.4 | 328.8  |
| 7.5°  | 287.4  | 276.3 | 265.3  | 254.2 | 245.9  | 240.4 | 232.1  | 223.8 | 218.3  | 210.0 | 204.5  |
| 10°   | 176.9  | 163.0 | 152.0  | 138.2 | 143.7  | 149.2 | 152.0  | 157.5 | 157.5  | 154.7 | 154.7  |
| 12.5° | 127.1  | 127.1 | 127.1  | 127.1 | 127.1  | 127.1 | 124.4  | 124.4 | 124.4  | 121.6 | 121.6  |
| 15°   | 94.0   | 91.2  | 88.4   | 85.7  | 85.7   | 85.7  | 82.9   | 82.9  | 88.4   | 91.2  | 96.7   |
| 17.5° | 71.8   | 74.6  | 74.6   | 77.4  | 80.1   | 82.9  | 82.9   | 85.7  | 85.7   | 88.4  | 88.4   |
| 20°   | 69.1   | 69.1  | 66.3   | 66.3  | 63.6   | 63.6  | 60.8   | 58.0  | 60.8   | 66.3  | 69.1   |
| 22.5° | 60.8   | 55.3  | 52.5   | 47.0  | 49.7   | 55.3  | 58.0   | 60.8  | 60.8   | 60.8  | 60.8   |
| 25°   | 49.7   | 49.7  | 52.5   | 52.5  | 49.7   | 47.0  | 44.2   | 41.5  | 44.2   | 47.0  | 47.0   |
| 27.5° | 44.2   | 41.5  | 38.7   | 35.9  | 38.7   | 38.7  | 41.5   | 41.5  | 41.5   | 41.5  | 38.7   |
| 30°   | 38.7   | 38.7  | 35.9   | 35.9  | 35.9   | 33.2  | 33.2   | 30.4  | 33.2   | 33.2  | 35.9   |
| 32.5° | 33.2   | 30.4  | 30.4   | 27.6  | 27.6   | 30.4  | 30.4   | 30.4  | 30.4   | 30.4  | 30.4   |
| 35°   | 30.4   | 27.6  | 27.6   | 24.9  | 24.9   | 24.9  | 24.9   | 24.9  | 27.6   | 27.6  | 30.4   |
| 37.5° | 24.9   | 22.1  | 22.1   | 19.3  | 19.3   | 22.1  | 22.1   | 22.1  | 22.1   | 24.9  | 24.9   |
| 40°   | 22.1   | 19.3  | 19.3   | 16.6  | 16.6   | 19.3  | 19.3   | 19.3  | 19.3   | 22.1  | 22.1   |
| 42.5° | 16.6   | 16.6  | 13.8   | 13.8  | 13.8   | 16.6  | 16.6   | 16.6  | 16.6   | 19.3  | 19.3   |
| 45°   | 13.8   | 13.8  | 11.1   | 11.1  | 11.1   | 13.8  | 13.8   | 13.8  | 13.8   | 13.8  | 13.8   |
| 47.5° | 11.1   | 11.1  | 8.3    | 8.3   | 8.3    | 11.1  | 11.1   | 11.1  | 11.1   | 11.1  | 11.1   |
| 50°   | 11.1   | 8.3   | 8.3    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    |
| 52.5° | 8.3    | 8.3   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    |
| 55°   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    |
| 57.5° | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    |
| 60°   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    |
| 62.5° | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    |
| 65°   | 2.8    | 2.8   | 2.8    | 2.8   | 5.5    | 5.5   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    |
| 67.5° | 2.8    | 2.8   | 2.8    | 2.8   | 5.5    | 5.5   | 8.3    | 8.3   | 8.3    | 5.5   | 5.5    |
| 70°   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    |
| 72.5° | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    |
| 75°   | 5.5    | 5.5   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    |
| 77.5° | 5.5    | 5.5   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    |
| 80°   | 5.5    | 5.5   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    |
| 82.5° | 5.5    | 5.5   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    |
| 85°   | 5.5    | 8.3   | 8.3    | 11.1  | 11.1   | 11.1  | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    |
| 87.5° | 5.5    | 8.3   | 8.3    | 11.1  | 11.1   | 11.1  | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    |
| 90°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° | 190°  |
|-------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°    | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 |
| 2.5°  | 511.2 | 505.7  | 500.2 | 491.9  | 486.4 | 491.9  | 497.4 | 491.9  | 486.4 | 491.9  | 500.2 |
| 5°    | 323.3 | 320.5  | 320.5 | 317.8  | 315.0 | 315.0  | 312.3 | 315.0  | 315.0 | 317.8  | 320.5 |
| 7.5°  | 196.2 | 193.4  | 190.7 | 185.1  | 182.4 | 187.9  | 190.7 | 187.9  | 182.4 | 185.1  | 190.7 |
| 10°   | 152.0 | 152.0  | 149.2 | 149.2  | 146.5 | 146.5  | 146.5 | 146.5  | 146.5 | 149.2  | 149.2 |
| 12.5° | 118.8 | 116.1  | 113.3 | 110.5  | 107.8 | 113.3  | 116.1 | 113.3  | 107.8 | 110.5  | 113.3 |
| 15°   | 99.5  | 99.5   | 102.2 | 102.2  | 102.2 | 102.2  | 102.2 | 102.2  | 102.2 | 102.2  | 102.2 |
| 17.5° | 88.4  | 85.7   | 85.7  | 82.9   | 80.1  | 80.1   | 77.4  | 80.1   | 80.1  | 82.9   | 85.7  |
| 20°   | 71.8  | 71.8   | 74.6  | 74.6   | 74.6  | 74.6   | 74.6  | 74.6   | 74.6  | 74.6   | 74.6  |
| 22.5° | 60.8  | 58.0   | 58.0  | 55.3   | 52.5  | 52.5   | 49.7  | 52.5   | 52.5  | 55.3   | 58.0  |
| 25°   | 49.7  | 49.7   | 52.5  | 52.5   | 52.5  | 52.5   | 52.5  | 52.5   | 52.5  | 52.5   | 52.5  |
| 27.5° | 38.7  | 38.7   | 38.7  | 35.9   | 35.9  | 35.9   | 35.9  | 35.9   | 35.9  | 35.9   | 38.7  |
| 30°   | 35.9  | 35.9   | 35.9  | 35.9   | 35.9  | 35.9   | 35.9  | 35.9   | 35.9  | 35.9   | 35.9  |
| 32.5° | 30.4  | 30.4   | 30.4  | 30.4   | 30.4  | 30.4   | 30.4  | 30.4   | 30.4  | 30.4   | 30.4  |
| 35°   | 30.4  | 30.4   | 30.4  | 27.6   | 27.6  | 27.6   | 27.6  | 27.6   | 27.6  | 27.6   | 30.4  |
| 37.5° | 24.9  | 24.9   | 24.9  | 24.9   | 24.9  | 24.9   | 24.9  | 24.9   | 24.9  | 24.9   | 24.9  |
| 40°   | 22.1  | 22.1   | 22.1  | 22.1   | 22.1  | 22.1   | 22.1  | 22.1   | 22.1  | 22.1   | 22.1  |
| 42.5° | 19.3  | 19.3   | 19.3  | 19.3   | 19.3  | 19.3   | 19.3  | 19.3   | 19.3  | 19.3   | 19.3  |
| 45°   | 13.8  | 13.8   | 13.8  | 13.8   | 13.8  | 13.8   | 13.8  | 13.8   | 13.8  | 13.8   | 13.8  |
| 47.5° | 11.1  | 11.1   | 11.1  | 11.1   | 11.1  | 11.1   | 11.1  | 11.1   | 11.1  | 11.1   | 11.1  |
| 50°   | 8.3   | 8.3    | 8.3   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 8.3   |
| 52.5° | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 5.5   |
| 55°   | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   |
| 57.5° | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   |
| 60°   | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   |
| 62.5° | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 2.8   | 2.8    | 5.5   |
| 65°   | 5.5   | 5.5    | 2.8   | 2.8    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.8    | 2.8   |
| 67.5° | 2.8   | 2.8    | 2.8   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 2.8   |
| 70°   | 5.5   | 5.5    | 2.8   | 2.8    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.8    | 2.8   |
| 72.5° | 5.5   | 5.5    | 2.8   | 2.8    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.8    | 2.8   |
| 75°   | 5.5   | 5.5    | 2.8   | 2.8    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.8    | 2.8   |
| 77.5° | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    | 0.0   | 2.8    | 2.8   | 2.8    | 5.5   |
| 80°   | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    | 0.0   | 2.8    | 2.8   | 2.8    | 5.5   |
| 82.5° | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    | 0.0   | 2.8    | 2.8   | 2.8    | 5.5   |
| 85°   | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    | 0.0   | 2.8    | 2.8   | 2.8    | 5.5   |
| 87.5° | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    | 0.0   | 2.8    | 2.8   | 2.8    | 5.5   |
| 90°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  | 217.5° |
|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°    | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  |
| 2.5°  | 505.7  | 511.2 | 514.0  | 519.5 | 522.3  | 525.0 | 547.1  | 566.5 | 588.6  | 607.9 | 621.8  |
| 5°    | 320.5  | 323.3 | 328.8  | 334.4 | 337.1  | 342.7 | 348.2  | 353.7 | 359.2  | 364.8 | 373.1  |
| 7.5°  | 193.4  | 196.2 | 204.5  | 210.0 | 218.3  | 223.8 | 232.1  | 240.4 | 245.9  | 254.2 | 265.3  |
| 10°   | 152.0  | 152.0 | 154.7  | 154.7 | 157.5  | 157.5 | 152.0  | 149.2 | 143.7  | 138.2 | 152.0  |
| 12.5° | 116.1  | 118.8 | 121.6  | 121.6 | 124.4  | 124.4 | 124.4  | 127.1 | 127.1  | 127.1 | 127.1  |
| 15°   | 99.5   | 99.5  | 96.7   | 91.2  | 88.4   | 82.9  | 82.9   | 85.7  | 85.7   | 85.7  | 88.4   |
| 17.5° | 85.7   | 88.4  | 88.4   | 88.4  | 85.7   | 85.7  | 82.9   | 82.9  | 80.1   | 77.4  | 74.6   |
| 20°   | 71.8   | 71.8  | 69.1   | 66.3  | 60.8   | 58.0  | 60.8   | 63.6  | 63.6   | 66.3  | 66.3   |
| 22.5° | 58.0   | 60.8  | 60.8   | 60.8  | 60.8   | 60.8  | 58.0   | 55.3  | 49.7   | 47.0  | 52.5   |
| 25°   | 49.7   | 49.7  | 47.0   | 47.0  | 44.2   | 41.5  | 44.2   | 47.0  | 49.7   | 52.5  | 52.5   |
| 27.5° | 38.7   | 38.7  | 38.7   | 41.5  | 41.5   | 41.5  | 41.5   | 38.7  | 38.7   | 35.9  | 38.7   |
| 30°   | 35.9   | 35.9  | 35.9   | 33.2  | 33.2   | 30.4  | 33.2   | 33.2  | 35.9   | 35.9  | 35.9   |
| 32.5° | 30.4   | 30.4  | 30.4   | 30.4  | 30.4   | 30.4  | 30.4   | 30.4  | 27.6   | 27.6  | 30.4   |
| 35°   | 30.4   | 30.4  | 30.4   | 27.6  | 27.6   | 24.9  | 24.9   | 24.9  | 24.9   | 24.9  | 27.6   |
| 37.5° | 24.9   | 24.9  | 24.9   | 24.9  | 22.1   | 22.1  | 22.1   | 22.1  | 19.3   | 19.3  | 22.1   |
| 40°   | 22.1   | 22.1  | 22.1   | 22.1  | 19.3   | 19.3  | 19.3   | 19.3  | 16.6   | 16.6  | 19.3   |
| 42.5° | 19.3   | 19.3  | 19.3   | 19.3  | 16.6   | 16.6  | 16.6   | 16.6  | 13.8   | 13.8  | 13.8   |
| 45°   | 13.8   | 13.8  | 13.8   | 13.8  | 13.8   | 13.8  | 13.8   | 13.8  | 11.1   | 11.1  | 11.1   |
| 47.5° | 11.1   | 11.1  | 11.1   | 11.1  | 11.1   | 11.1  | 11.1   | 11.1  | 8.3    | 8.3   | 8.3    |
| 50°   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    | 5.5   | 8.3    |
| 52.5° | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    |
| 55°   | 2.8    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    |
| 57.5° | 2.8    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    |
| 60°   | 2.8    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    |
| 62.5° | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 2.8    | 2.8   | 2.8    |
| 65°   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 5.5   | 5.5    | 2.8   | 2.8    |
| 67.5° | 2.8    | 2.8   | 5.5    | 5.5   | 8.3    | 8.3   | 8.3    | 5.5   | 5.5    | 2.8   | 2.8    |
| 70°   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    | 5.5   | 5.5    |
| 72.5° | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    | 5.5   | 5.5    |
| 75°   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    |
| 77.5° | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    |
| 80°   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    |
| 82.5° | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    |
| 85°   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 11.1  | 11.1   | 11.1  | 8.3    |
| 87.5° | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 11.1  | 11.1   | 11.1  | 8.3    |
| 90°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° | 245°  |
|-------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°    | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 |
| 2.5°  | 632.8 | 646.6  | 657.7 | 668.7  | 679.8 | 690.8  | 701.9 | 712.9  | 726.8 | 737.8  | 748.9 |
| 5°    | 381.3 | 389.6  | 397.9 | 414.5  | 431.1 | 444.9  | 461.5 | 500.2  | 536.1 | 574.8  | 610.7 |
| 7.5°  | 276.3 | 287.4  | 298.4 | 312.3  | 326.1 | 339.9  | 353.7 | 367.5  | 384.1 | 397.9  | 411.7 |
| 10°   | 163.0 | 176.9  | 187.9 | 199.0  | 212.8 | 223.8  | 234.9 | 245.9  | 259.8 | 270.8  | 281.9 |
| 12.5° | 127.1 | 127.1  | 127.1 | 132.6  | 140.9 | 146.5  | 152.0 | 171.3  | 190.7 | 210.0  | 229.4 |
| 15°   | 91.2  | 94.0   | 96.7  | 99.5   | 102.2 | 102.2  | 105.0 | 118.8  | 132.6 | 143.7  | 157.5 |
| 17.5° | 74.6  | 71.8   | 69.1  | 74.6   | 80.1  | 85.7   | 91.2  | 99.5   | 105.0 | 113.3  | 118.8 |
| 20°   | 69.1  | 69.1   | 69.1  | 71.8   | 74.6  | 74.6   | 77.4  | 80.1   | 85.7  | 88.4   | 91.2  |
| 22.5° | 55.3  | 60.8   | 63.6  | 63.6   | 63.6  | 60.8   | 60.8  | 69.1   | 77.4  | 85.7   | 94.0  |
| 25°   | 49.7  | 49.7   | 47.0  | 52.5   | 55.3  | 60.8   | 63.6  | 66.3   | 66.3  | 69.1   | 69.1  |
| 27.5° | 41.5  | 44.2   | 47.0  | 49.7   | 49.7  | 52.5   | 52.5  | 58.0   | 63.6  | 69.1   | 74.6  |
| 30°   | 38.7  | 38.7   | 38.7  | 41.5   | 47.0  | 49.7   | 52.5  | 58.0   | 63.6  | 66.3   | 71.8  |
| 32.5° | 30.4  | 33.2   | 33.2  | 35.9   | 41.5  | 44.2   | 47.0  | 55.3   | 60.8  | 69.1   | 74.6  |
| 35°   | 27.6  | 30.4   | 30.4  | 33.2   | 35.9  | 38.7   | 41.5  | 49.7   | 55.3  | 63.6   | 69.1  |
| 37.5° | 22.1  | 24.9   | 24.9  | 27.6   | 30.4  | 33.2   | 35.9  | 41.5   | 49.7  | 55.3   | 60.8  |
| 40°   | 19.3  | 22.1   | 22.1  | 24.9   | 27.6  | 27.6   | 30.4  | 35.9   | 41.5  | 47.0   | 52.5  |
| 42.5° | 16.6  | 16.6   | 16.6  | 19.3   | 22.1  | 24.9   | 27.6  | 33.2   | 38.7  | 41.5   | 47.0  |
| 45°   | 13.8  | 13.8   | 13.8  | 16.6   | 19.3  | 22.1   | 24.9  | 30.4   | 33.2  | 38.7   | 41.5  |
| 47.5° | 11.1  | 11.1   | 11.1  | 13.8   | 16.6  | 19.3   | 22.1  | 24.9   | 30.4  | 33.2   | 35.9  |
| 50°   | 8.3   | 11.1   | 11.1  | 13.8   | 16.6  | 16.6   | 19.3  | 22.1   | 27.6  | 30.4   | 33.2  |
| 52.5° | 8.3   | 8.3    | 8.3   | 11.1   | 13.8  | 13.8   | 16.6  | 19.3   | 22.1  | 24.9   | 27.6  |
| 55°   | 5.5   | 5.5    | 5.5   | 8.3    | 11.1  | 11.1   | 13.8  | 16.6   | 19.3  | 22.1   | 24.9  |
| 57.5° | 5.5   | 5.5    | 5.5   | 8.3    | 8.3   | 11.1   | 11.1  | 13.8   | 16.6  | 19.3   | 22.1  |
| 60°   | 2.8   | 2.8    | 2.8   | 5.5    | 5.5   | 8.3    | 8.3   | 11.1   | 13.8  | 16.6   | 19.3  |
| 62.5° | 2.8   | 2.8    | 2.8   | 5.5    | 5.5   | 8.3    | 8.3   | 11.1   | 13.8  | 16.6   | 19.3  |
| 65°   | 2.8   | 2.8    | 2.8   | 5.5    | 5.5   | 8.3    | 8.3   | 11.1   | 13.8  | 13.8   | 16.6  |
| 67.5° | 2.8   | 2.8    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 8.3    | 11.1  | 13.8   | 16.6  |
| 70°   | 5.5   | 2.8    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 8.3    | 8.3   | 11.1   | 11.1  |
| 72.5° | 5.5   | 2.8    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 8.3    | 8.3   | 11.1   | 11.1  |
| 75°   | 5.5   | 5.5    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   |
| 77.5° | 5.5   | 5.5    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   |
| 80°   | 5.5   | 5.5    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   |
| 82.5° | 5.5   | 5.5    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   |
| 85°   | 8.3   | 5.5    | 2.8   | 2.8    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   |
| 87.5° | 8.3   | 5.5    | 2.8   | 5.5    | 5.5   | 8.3    | 8.3   | 8.3    | 8.3   | 5.5    | 5.5   |
| 90°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   | 272.5° |
|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|--------|
| 0°    | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4 | 906.4  | 906.4  | 906.4  |
| 2.5°  | 765.5  | 779.3 | 795.8  | 809.7 | 826.2  | 842.8 | 859.4  | 876.0 | 892.6  | 909.1  | 925.7  |
| 5°    | 638.3  | 668.7 | 696.4  | 724.0 | 754.4  | 787.6 | 818.0  | 848.4 | 881.5  | 914.7  | 945.1  |
| 7.5°  | 447.7  | 483.6 | 519.5  | 555.4 | 599.6  | 643.9 | 685.3  | 729.5 | 771.0  | 812.4  | 853.9  |
| 10°   | 306.7  | 331.6 | 353.7  | 378.6 | 436.6  | 494.6 | 552.7  | 610.7 | 663.2  | 712.9  | 759.9  |
| 12.5° | 245.9  | 265.3 | 281.9  | 298.4 | 353.7  | 411.7 | 467.0  | 522.3 | 574.8  | 627.3  | 674.3  |
| 15°   | 201.7  | 243.2 | 287.4  | 328.8 | 411.7  | 491.9 | 574.8  | 654.9 | 735.1  | 815.2  | 876.0  |
| 17.5° | 157.5  | 196.2 | 234.9  | 273.6 | 350.9  | 425.6 | 502.9  | 577.5 | 649.4  | 721.2  | 787.6  |
| 20°   | 135.4  | 179.6 | 223.8  | 268.0 | 373.1  | 478.1 | 583.1  | 688.1 | 795.8  | 900.9  | 986.5  |
| 22.5° | 121.6  | 149.2 | 174.1  | 201.7 | 273.6  | 342.7 | 414.5  | 483.6 | 569.3  | 652.2  | 718.5  |
| 25°   | 102.2  | 135.4 | 168.6  | 201.7 | 320.5  | 439.4 | 558.2  | 677.0 | 823.5  | 969.9  | 1086.0 |
| 27.5° | 99.5   | 124.4 | 149.2  | 174.1 | 328.8  | 483.6 | 638.3  | 793.1 | 978.2  | 1163.4 | 1318.1 |
| 30°   | 94.0   | 116.1 | 135.4  | 157.5 | 339.9  | 522.3 | 704.7  | 887.0 | 1149.6 | 1409.3 | 1594.5 |
| 32.5° | 88.4   | 102.2 | 113.3  | 127.1 | 309.5  | 494.6 | 677.0  | 859.4 | 1166.1 | 1470.1 | 1680.1 |
| 35°   | 77.4   | 88.4  | 96.7   | 105.0 | 287.4  | 469.8 | 649.4  | 831.8 | 1182.7 | 1530.9 | 1768.6 |
| 37.5° | 69.1   | 77.4  | 85.7   | 94.0  | 270.8  | 444.9 | 621.8  | 795.8 | 1199.3 | 1602.7 | 1870.8 |
| 40°   | 60.8   | 69.1  | 77.4   | 85.7  | 254.2  | 422.8 | 588.6  | 757.2 | 1215.9 | 1674.6 | 1970.3 |
| 42.5° | 55.3   | 63.6  | 71.8   | 80.1  | 240.4  | 400.7 | 558.2  | 718.5 | 1235.2 | 1752.0 | 2080.8 |
| 45°   | 49.7   | 58.0  | 63.6   | 71.8  | 221.1  | 370.3 | 519.5  | 668.7 | 1262.9 | 1857.0 | 2213.5 |
| 47.5° | 44.2   | 52.5  | 60.8   | 69.1  | 207.3  | 345.4 | 480.8  | 619.0 | 1290.5 | 1962.0 | 2357.1 |
| 50°   | 41.5   | 49.7  | 55.3   | 63.6  | 196.2  | 328.8 | 461.5  | 594.1 | 1345.8 | 2094.6 | 2531.2 |
| 52.5° | 35.9   | 44.2  | 49.7   | 58.0  | 187.9  | 315.0 | 444.9  | 572.0 | 1412.1 | 2249.4 | 2738.5 |
| 55°   | 33.2   | 38.7  | 47.0   | 52.5  | 174.1  | 292.9 | 414.5  | 533.3 | 1425.9 | 2315.7 | 2857.3 |
| 57.5° | 27.6   | 35.9  | 41.5   | 47.0  | 160.3  | 273.6 | 384.1  | 497.4 | 1450.8 | 2401.4 | 2970.6 |
| 60°   | 24.9   | 30.4  | 35.9   | 41.5  | 146.5  | 254.2 | 359.2  | 464.2 | 1481.2 | 2498.1 | 3111.5 |
| 62.5° | 24.9   | 27.6  | 33.2   | 35.9  | 132.6  | 232.1 | 328.8  | 425.6 | 1530.9 | 2633.5 | 3313.3 |
| 65°   | 22.1   | 24.9  | 30.4   | 33.2  | 121.6  | 212.8 | 301.2  | 389.6 | 1577.9 | 2763.4 | 3550.9 |
| 67.5° | 19.3   | 24.9  | 27.6   | 30.4  | 110.5  | 187.9 | 268.0  | 345.4 | 1577.9 | 2810.3 | 3738.8 |
| 70°   | 16.6   | 19.3  | 24.9   | 27.6  | 91.2   | 152.0 | 215.5  | 276.3 | 1464.6 | 2652.8 | 3708.4 |
| 72.5° | 13.8   | 16.6  | 19.3   | 22.1  | 60.8   | 99.5  | 135.4  | 174.1 | 1193.8 | 2213.5 | 3296.7 |
| 75°   | 11.1   | 13.8  | 13.8   | 16.6  | 33.2   | 52.5  | 69.1   | 85.7  | 845.6  | 1602.7 | 2459.4 |
| 77.5° | 11.1   | 11.1  | 13.8   | 13.8  | 22.1   | 33.2  | 41.5   | 49.7  | 420.0  | 787.6  | 1262.9 |
| 80°   | 8.3    | 8.3   | 11.1   | 11.1  | 16.6   | 22.1  | 24.9   | 30.4  | 99.5   | 165.8  | 268.0  |
| 82.5° | 5.5    | 8.3   | 8.3    | 8.3   | 11.1   | 13.8  | 13.8   | 16.6  | 22.1   | 27.6   | 44.2   |
| 85°   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 11.1   | 11.1   | 16.6   |
| 87.5° | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5    | 8.3    |
| 90°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  |
| 2.5°  | 939.5  | 953.4  | 964.4  | 978.2  | 994.8  | 1005.9 | 1016.9 | 1028.0 | 1039.0 | 1050.1 | 1061.1 |
| 5°    | 972.7  | 1000.3 | 1025.2 | 1052.8 | 1080.5 | 1097.1 | 1113.6 | 1130.2 | 1146.8 | 1116.4 | 1086.0 |
| 7.5°  | 895.3  | 928.5  | 961.6  | 994.8  | 1019.7 | 1011.4 | 1003.1 | 994.8  | 986.5  | 1022.4 | 1055.6 |
| 10°   | 804.1  | 831.8  | 862.2  | 889.8  | 820.7  | 834.5  | 845.6  | 859.4  | 870.5  | 889.8  | 909.1  |
| 12.5° | 721.2  | 712.9  | 707.4  | 699.1  | 721.2  | 776.5  | 831.8  | 884.3  | 939.5  | 947.8  | 958.9  |
| 15°   | 936.8  | 942.3  | 947.8  | 953.4  | 958.9  | 931.3  | 903.6  | 873.2  | 845.6  | 853.9  | 862.2  |
| 17.5° | 853.9  | 862.2  | 873.2  | 881.5  | 911.9  | 931.3  | 947.8  | 967.2  | 983.8  | 1019.7 | 1055.6 |
| 20°   | 1069.4 | 1088.8 | 1105.3 | 1124.7 | 1061.1 | 1025.2 | 986.5  | 950.6  | 911.9  | 950.6  | 989.3  |
| 22.5° | 784.8  | 878.7  | 972.7  | 1066.7 | 1047.3 | 1108.1 | 1168.9 | 1226.9 | 1287.7 | 1224.2 | 1160.6 |
| 25°   | 1199.3 | 1243.5 | 1290.5 | 1334.7 | 1362.3 | 1301.5 | 1240.7 | 1180.0 | 1119.2 | 1166.1 | 1213.1 |
| 27.5° | 1472.9 | 1461.8 | 1450.8 | 1439.7 | 1495.0 | 1472.9 | 1450.8 | 1425.9 | 1403.8 | 1359.6 | 1312.6 |
| 30°   | 1776.8 | 1865.3 | 1953.7 | 2042.1 | 2064.2 | 1964.7 | 1862.5 | 1763.0 | 1660.8 | 1605.5 | 1547.5 |
| 32.5° | 1887.4 | 1997.9 | 2105.7 | 2216.2 | 2210.7 | 2152.7 | 2094.6 | 2033.8 | 1975.8 | 1879.1 | 1785.1 |
| 35°   | 2006.2 | 2130.6 | 2252.1 | 2376.5 | 2426.2 | 2340.6 | 2252.1 | 2166.5 | 2078.0 | 2011.7 | 1945.4 |
| 37.5° | 2136.1 | 2271.5 | 2406.9 | 2542.3 | 2650.1 | 2542.3 | 2437.3 | 2329.5 | 2221.7 | 2152.7 | 2083.6 |
| 40°   | 2263.2 | 2448.3 | 2630.7 | 2815.9 | 2821.4 | 2713.6 | 2603.1 | 2495.3 | 2384.8 | 2310.2 | 2235.6 |
| 42.5° | 2406.9 | 2616.9 | 2824.2 | 3034.2 | 3036.9 | 2920.9 | 2807.6 | 2691.5 | 2575.5 | 2500.8 | 2426.2 |
| 45°   | 2567.2 | 2804.8 | 3039.7 | 3277.3 | 3263.5 | 3130.9 | 2998.2 | 2865.6 | 2733.0 | 2666.6 | 2597.6 |
| 47.5° | 2752.3 | 3009.3 | 3266.3 | 3523.3 | 3608.9 | 3429.3 | 3246.9 | 3067.3 | 2884.9 | 2824.2 | 2763.4 |
| 50°   | 2965.1 | 3241.4 | 3517.8 | 3794.1 | 3907.4 | 3694.6 | 3481.8 | 3266.3 | 3053.5 | 2992.7 | 2931.9 |
| 52.5° | 3224.8 | 3509.5 | 3791.3 | 4076.0 | 4192.0 | 3959.9 | 3727.8 | 3495.7 | 3263.5 | 3188.9 | 3114.3 |
| 55°   | 3396.2 | 3725.0 | 4051.1 | 4379.9 | 4512.6 | 4255.6 | 3998.6 | 3738.8 | 3481.8 | 3379.6 | 3274.6 |
| 57.5° | 3539.9 | 3877.0 | 4211.4 | 4548.5 | 4681.1 | 4415.9 | 4150.6 | 3882.5 | 3617.2 | 3492.9 | 3368.5 |
| 60°   | 3722.2 | 4064.9 | 4410.3 | 4753.0 | 4866.3 | 4578.9 | 4291.5 | 4001.3 | 3714.0 | 3570.3 | 3429.3 |
| 62.5° | 3990.3 | 4316.4 | 4642.4 | 4968.5 | 5043.1 | 4736.4 | 4432.4 | 4125.7 | 3819.0 | 3636.6 | 3454.2 |
| 65°   | 4338.5 | 4664.6 | 4993.4 | 5319.5 | 5399.6 | 5034.8 | 4672.8 | 4308.1 | 3943.3 | 3702.9 | 3462.5 |
| 67.5° | 4664.6 | 5037.6 | 5413.4 | 5786.5 | 5866.6 | 5416.2 | 4963.0 | 4512.6 | 4059.4 | 3744.4 | 3429.3 |
| 70°   | 4761.3 | 5203.4 | 5645.5 | 6087.7 | 6192.7 | 5662.1 | 5131.6 | 4598.2 | 4067.7 | 3672.5 | 3280.1 |
| 72.5° | 4379.9 | 4882.9 | 5383.0 | 5886.0 | 6084.9 | 5518.4 | 4951.9 | 4382.7 | 3816.2 | 3371.3 | 2929.2 |
| 75°   | 3313.3 | 3805.1 | 4299.8 | 4791.7 | 5045.9 | 4548.5 | 4053.9 | 3556.4 | 3059.0 | 2652.8 | 2249.4 |
| 77.5° | 1738.2 | 2108.4 | 2476.0 | 2846.3 | 3302.2 | 2915.3 | 2525.7 | 2138.8 | 1749.2 | 1500.5 | 1249.0 |
| 80°   | 367.5  | 494.6  | 619.0  | 746.1  | 1003.1 | 911.9  | 823.5  | 732.3  | 641.1  | 538.9  | 433.8  |
| 82.5° | 60.8   | 80.1   | 99.5   | 118.8  | 149.2  | 149.2  | 152.0  | 152.0  | 152.0  | 132.6  | 110.5  |
| 85°   | 19.3   | 24.9   | 30.4   | 35.9   | 35.9   | 38.7   | 38.7   | 41.5   | 41.5   | 41.5   | 38.7   |
| 87.5° | 8.3    | 8.3    | 11.1   | 11.1   | 11.1   | 11.1   | 13.8   | 13.8   | 13.8   | 13.8   | 13.8   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  |
| 2.5°  | 1072.2 | 1083.2 | 1091.5 | 1102.6 | 1110.9 | 1119.2 | 1124.7 | 1127.5 | 1133.0 | 1135.7 | 1130.2 |
| 5°    | 1052.8 | 1022.4 | 1033.5 | 1044.6 | 1052.8 | 1063.9 | 1072.2 | 1080.5 | 1086.0 | 1094.3 | 1099.8 |
| 7.5°  | 1091.5 | 1124.7 | 1138.5 | 1152.3 | 1166.1 | 1180.0 | 1188.2 | 1196.5 | 1202.1 | 1210.4 | 1213.1 |
| 10°   | 928.5  | 947.8  | 989.3  | 1033.5 | 1074.9 | 1116.4 | 1102.6 | 1088.8 | 1074.9 | 1061.1 | 1121.9 |
| 12.5° | 967.2  | 975.5  | 1000.3 | 1022.4 | 1047.3 | 1069.4 | 1116.4 | 1160.6 | 1207.6 | 1251.8 | 1279.4 |
| 15°   | 870.5  | 878.7  | 945.1  | 1008.6 | 1074.9 | 1138.5 | 1119.2 | 1099.8 | 1080.5 | 1061.1 | 1091.5 |
| 17.5° | 1088.8 | 1124.7 | 1061.1 | 994.8  | 931.3  | 864.9  | 942.3  | 1022.4 | 1099.8 | 1177.2 | 1204.8 |
| 20°   | 1028.0 | 1066.7 | 1099.8 | 1133.0 | 1166.1 | 1199.3 | 1171.7 | 1146.8 | 1119.2 | 1091.5 | 1069.4 |
| 22.5° | 1094.3 | 1030.7 | 1069.4 | 1110.9 | 1149.6 | 1188.2 | 1168.9 | 1152.3 | 1133.0 | 1113.6 | 1157.8 |
| 25°   | 1257.3 | 1304.3 | 1243.5 | 1182.7 | 1121.9 | 1061.1 | 1130.2 | 1199.3 | 1265.6 | 1334.7 | 1290.5 |
| 27.5° | 1268.4 | 1221.4 | 1276.7 | 1329.2 | 1384.4 | 1436.9 | 1378.9 | 1323.7 | 1265.6 | 1207.6 | 1271.1 |
| 30°   | 1492.2 | 1434.2 | 1417.6 | 1401.0 | 1384.4 | 1367.9 | 1398.3 | 1428.7 | 1456.3 | 1486.7 | 1495.0 |
| 32.5° | 1688.4 | 1591.7 | 1616.6 | 1644.2 | 1669.1 | 1693.9 | 1671.8 | 1652.5 | 1630.4 | 1608.3 | 1702.2 |
| 35°   | 1879.1 | 1812.8 | 1823.8 | 1834.9 | 1845.9 | 1857.0 | 1862.5 | 1865.3 | 1870.8 | 1873.6 | 1995.1 |
| 37.5° | 2011.7 | 1942.6 | 1981.3 | 2020.0 | 2058.7 | 2097.4 | 2097.4 | 2094.6 | 2094.6 | 2091.9 | 2230.0 |
| 40°   | 2158.2 | 2083.6 | 2138.8 | 2191.3 | 2246.6 | 2299.1 | 2310.2 | 2321.2 | 2332.3 | 2343.3 | 2470.4 |
| 42.5° | 2348.9 | 2274.2 | 2321.2 | 2365.4 | 2412.4 | 2456.6 | 2476.0 | 2495.3 | 2511.9 | 2531.2 | 2658.4 |
| 45°   | 2531.2 | 2462.2 | 2498.1 | 2534.0 | 2569.9 | 2605.8 | 2622.4 | 2639.0 | 2655.6 | 2672.2 | 2818.6 |
| 47.5° | 2702.6 | 2641.8 | 2663.9 | 2683.2 | 2705.3 | 2724.7 | 2738.5 | 2749.5 | 2763.4 | 2774.4 | 2920.9 |
| 50°   | 2871.1 | 2810.3 | 2815.9 | 2821.4 | 2824.2 | 2829.7 | 2835.2 | 2843.5 | 2849.0 | 2854.6 | 3025.9 |
| 52.5° | 3036.9 | 2962.3 | 2948.5 | 2934.7 | 2920.9 | 2907.1 | 2907.1 | 2904.3 | 2904.3 | 2901.5 | 3034.2 |
| 55°   | 3172.3 | 3067.3 | 3034.2 | 2998.2 | 2965.1 | 2929.2 | 2915.3 | 2901.5 | 2884.9 | 2871.1 | 2940.2 |
| 57.5° | 3241.4 | 3117.1 | 3067.3 | 3014.8 | 2965.1 | 2912.6 | 2865.6 | 2815.9 | 2768.9 | 2719.1 | 2708.1 |
| 60°   | 3285.6 | 3141.9 | 3064.6 | 2984.4 | 2907.1 | 2826.9 | 2710.9 | 2594.8 | 2478.7 | 2362.7 | 2301.9 |
| 62.5° | 3269.1 | 3086.7 | 2967.8 | 2846.3 | 2727.4 | 2605.8 | 2426.2 | 2246.6 | 2064.2 | 1884.6 | 1798.9 |
| 65°   | 3219.3 | 2978.9 | 2807.6 | 2633.5 | 2462.2 | 2288.1 | 2072.5 | 1857.0 | 1641.4 | 1425.9 | 1345.8 |
| 67.5° | 3114.3 | 2799.3 | 2558.9 | 2321.2 | 2080.8 | 1840.4 | 1622.1 | 1403.8 | 1185.5 | 967.2  | 909.1  |
| 70°   | 2884.9 | 2489.8 | 2207.9 | 1923.3 | 1641.4 | 1356.8 | 1171.7 | 983.8  | 798.6  | 610.7  | 583.1  |
| 72.5° | 2484.3 | 2039.4 | 1752.0 | 1467.3 | 1180.0 | 892.6  | 765.5  | 638.3  | 511.2  | 384.1  | 375.8  |
| 75°   | 1843.2 | 1436.9 | 1215.9 | 992.0  | 771.0  | 547.1  | 472.5  | 400.7  | 326.1  | 251.5  | 254.2  |
| 77.5° | 1000.3 | 748.9  | 643.9  | 538.9  | 431.1  | 326.1  | 290.2  | 254.2  | 218.3  | 182.4  | 187.9  |
| 80°   | 331.6  | 226.6  | 210.0  | 193.4  | 176.9  | 160.3  | 146.5  | 132.6  | 118.8  | 105.0  | 110.5  |
| 82.5° | 91.2   | 69.1   | 74.6   | 82.9   | 88.4   | 94.0   | 94.0   | 94.0   | 91.2   | 91.2   | 91.2   |
| 85°   | 38.7   | 35.9   | 33.2   | 33.2   | 30.4   | 27.6   | 33.2   | 38.7   | 44.2   | 49.7   | 52.5   |
| 87.5° | 11.1   | 11.1   | 11.1   | 8.3    | 8.3    | 5.5    | 5.5    | 5.5    | 5.5    | 5.5    | 8.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  | 906.4  |
| 2.5°  | 1127.5 | 1121.9 | 1116.4 | 1108.1 | 1102.6 | 1094.3 | 1086.0 | 1077.7 | 1069.4 | 1058.4 | 1050.1 |
| 5°    | 1105.3 | 1110.9 | 1116.4 | 1119.2 | 1124.7 | 1127.5 | 1130.2 | 1133.0 | 1135.7 | 1135.7 | 1138.5 |
| 7.5°  | 1213.1 | 1215.9 | 1215.9 | 1199.3 | 1185.5 | 1168.9 | 1152.3 | 1149.6 | 1149.6 | 1146.8 | 1144.0 |
| 10°   | 1185.5 | 1246.3 | 1307.1 | 1307.1 | 1304.3 | 1304.3 | 1301.5 | 1301.5 | 1304.3 | 1304.3 | 1304.3 |
| 12.5° | 1307.1 | 1334.7 | 1362.3 | 1351.3 | 1343.0 | 1331.9 | 1320.9 | 1273.9 | 1224.2 | 1177.2 | 1127.5 |
| 15°   | 1121.9 | 1149.6 | 1180.0 | 1221.4 | 1262.9 | 1304.3 | 1345.8 | 1343.0 | 1343.0 | 1340.2 | 1337.5 |
| 17.5° | 1229.7 | 1257.3 | 1282.2 | 1262.9 | 1243.5 | 1221.4 | 1202.1 | 1166.1 | 1130.2 | 1094.3 | 1058.4 |
| 20°   | 1050.1 | 1028.0 | 1005.9 | 1094.3 | 1182.7 | 1271.1 | 1359.6 | 1356.8 | 1356.8 | 1354.0 | 1351.3 |
| 22.5° | 1202.1 | 1243.5 | 1287.7 | 1254.6 | 1221.4 | 1188.2 | 1155.1 | 1149.6 | 1141.3 | 1135.7 | 1127.5 |
| 25°   | 1246.3 | 1199.3 | 1155.1 | 1238.0 | 1323.7 | 1406.6 | 1489.5 | 1503.3 | 1517.1 | 1528.1 | 1542.0 |
| 27.5° | 1337.5 | 1401.0 | 1464.6 | 1448.0 | 1431.4 | 1412.1 | 1395.5 | 1406.6 | 1417.6 | 1428.7 | 1439.7 |
| 30°   | 1506.0 | 1514.3 | 1522.6 | 1644.2 | 1768.6 | 1890.1 | 2011.7 | 2028.3 | 2042.1 | 2058.7 | 2072.5 |
| 32.5° | 1796.2 | 1887.4 | 1981.3 | 2055.9 | 2133.3 | 2207.9 | 2282.5 | 2382.0 | 2484.3 | 2583.7 | 2683.2 |
| 35°   | 2119.5 | 2241.1 | 2362.7 | 2506.4 | 2652.8 | 2796.5 | 2940.2 | 2976.1 | 3014.8 | 3050.8 | 3086.7 |
| 37.5° | 2368.2 | 2506.4 | 2644.5 | 2793.8 | 2940.2 | 3089.4 | 3235.9 | 3263.5 | 3291.2 | 3318.8 | 3346.4 |
| 40°   | 2597.6 | 2724.7 | 2851.8 | 3009.3 | 3166.8 | 3324.3 | 3481.8 | 3503.9 | 3526.0 | 3548.2 | 3570.3 |
| 42.5° | 2785.5 | 2909.8 | 3036.9 | 3194.4 | 3352.0 | 3509.5 | 3667.0 | 3686.3 | 3702.9 | 3722.2 | 3738.8 |
| 45°   | 2965.1 | 3111.5 | 3258.0 | 3396.2 | 3534.3 | 3669.7 | 3807.9 | 3821.7 | 3832.8 | 3846.6 | 3857.7 |
| 47.5° | 3070.1 | 3216.6 | 3363.0 | 3492.9 | 3622.8 | 3749.9 | 3879.8 | 3879.8 | 3879.8 | 3879.8 | 3879.8 |
| 50°   | 3197.2 | 3365.8 | 3537.1 | 3603.4 | 3667.0 | 3733.3 | 3796.9 | 3783.0 | 3769.2 | 3752.6 | 3738.8 |
| 52.5° | 3164.0 | 3296.7 | 3426.6 | 3451.4 | 3476.3 | 3501.2 | 3526.0 | 3490.1 | 3457.0 | 3421.0 | 3385.1 |
| 55°   | 3009.3 | 3075.6 | 3144.7 | 3103.3 | 3059.0 | 3017.6 | 2973.4 | 2871.1 | 2768.9 | 2666.6 | 2564.4 |
| 57.5° | 2697.0 | 2686.0 | 2674.9 | 2564.4 | 2456.6 | 2346.1 | 2235.6 | 2169.2 | 2105.7 | 2039.4 | 1973.0 |
| 60°   | 2243.8 | 2183.1 | 2122.3 | 2022.8 | 1923.3 | 1823.8 | 1724.3 | 1688.4 | 1649.7 | 1613.8 | 1575.1 |
| 62.5° | 1713.3 | 1627.6 | 1542.0 | 1492.2 | 1442.5 | 1392.7 | 1343.0 | 1307.1 | 1268.4 | 1232.5 | 1193.8 |
| 65°   | 1268.4 | 1188.2 | 1108.1 | 1066.7 | 1025.2 | 981.0  | 939.5  | 914.7  | 889.8  | 862.2  | 837.3  |
| 67.5° | 853.9  | 795.8  | 737.8  | 712.9  | 685.3  | 660.4  | 632.8  | 621.8  | 607.9  | 596.9  | 583.1  |
| 70°   | 552.7  | 525.0  | 494.6  | 483.6  | 475.3  | 464.2  | 453.2  | 442.1  | 431.1  | 420.0  | 409.0  |
| 72.5° | 367.5  | 359.2  | 350.9  | 345.4  | 339.9  | 334.4  | 328.8  | 323.3  | 315.0  | 309.5  | 301.2  |
| 75°   | 254.2  | 257.0  | 257.0  | 254.2  | 254.2  | 251.5  | 248.7  | 226.6  | 204.5  | 182.4  | 160.3  |
| 77.5° | 190.7  | 196.2  | 199.0  | 185.1  | 171.3  | 154.7  | 140.9  | 138.2  | 135.4  | 132.6  | 129.9  |
| 80°   | 118.8  | 124.4  | 129.9  | 124.4  | 121.6  | 116.1  | 110.5  | 105.0  | 99.5   | 94.0   | 88.4   |
| 82.5° | 91.2   | 91.2   | 91.2   | 85.7   | 80.1   | 71.8   | 66.3   | 63.6   | 60.8   | 58.0   | 55.3   |
| 85°   | 55.3   | 58.0   | 60.8   | 55.3   | 47.0   | 41.5   | 33.2   | 27.6   | 22.1   | 16.6   | 11.1   |
| 87.5° | 8.3    | 11.1   | 11.1   | 11.1   | 8.3    | 8.3    | 5.5    | 5.5    | 5.5    | 2.8    | 2.8    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P559788

CATALOG NUMBER: SDL-PA1-100-722-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 357.5° | 360°   |
|-------|--------|--------|
| 0°    | 906.4  | 906.4  |
| 2.5°  | 1028.0 | 1005.9 |
| 5°    | 1141.3 | 1144.0 |
| 7.5°  | 1074.9 | 1003.1 |
| 10°   | 1304.3 | 1304.3 |
| 12.5° | 1113.6 | 1097.1 |
| 15°   | 1331.9 | 1326.4 |
| 17.5° | 1055.6 | 1050.1 |
| 20°   | 1348.5 | 1345.8 |
| 22.5° | 1127.5 | 1124.7 |
| 25°   | 1544.7 | 1544.7 |
| 27.5° | 1439.7 | 1436.9 |
| 30°   | 2072.5 | 2072.5 |
| 32.5° | 2735.7 | 2785.5 |
| 35°   | 3095.0 | 3103.3 |
| 37.5° | 3360.2 | 3371.3 |
| 40°   | 3578.6 | 3586.8 |
| 42.5° | 3741.6 | 3741.6 |
| 45°   | 3857.7 | 3857.7 |
| 47.5° | 3877.0 | 3874.2 |
| 50°   | 3730.5 | 3722.2 |
| 52.5° | 3352.0 | 3316.0 |
| 55°   | 2545.1 | 2522.9 |
| 57.5° | 1967.5 | 1959.2 |
| 60°   | 1575.1 | 1575.1 |
| 62.5° | 1182.7 | 1171.7 |
| 65°   | 826.2  | 812.4  |
| 67.5° | 577.5  | 572.0  |
| 70°   | 409.0  | 406.2  |
| 72.5° | 298.4  | 295.7  |
| 75°   | 157.5  | 152.0  |
| 77.5° | 129.9  | 127.1  |
| 80°   | 91.2   | 91.2   |
| 82.5° | 55.3   | 52.5   |
| 85°   | 8.3    | 5.5    |
| 87.5° | 2.8    | 2.8    |
| 90°   | 0.0    | 0.0    |

(END OF REPORT)