

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560871

Luminaire Tested: **SDL-PA1-70-727-U-T2U**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560871  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-70-727-U-T2U  
Description: Springdale  
(1) 70 CRI, 2700K, 930mA LIGHT ENGINE WITH 24 LEDS AND TYPE II U OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7191.4 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type II - Medium  
BUG Rating: B2 - U0 - G2

Input Watts (W): 72.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P560871

CATALOG NUMBER: SDL-PA1-70-727-U-T2U

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 13 fc  
Type II - Medium - N/A

REPORT NUMBER: P560871

CATALOG NUMBER: SDL-PA1-70-727-U-T2U

## Luminous Intensity Polar Plot



— Vertical Plane Through 70-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P560871

CATALOG NUMBER: SDL-PA1-70-727-U-T2U


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 2108.9   | 0.0    | 2108.9 |
|                    | % Fixture | 29.3     | 0.0    | 29.3   |
| <b>Street Side</b> | Lumens    | 5082.5   | 0.0    | 5082.5 |
|                    | % Fixture | 70.7     | 0.0    | 70.7   |
| <b>Total</b>       | Lumens    | 7191.4   | 0.0    | 7191.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 80.2   | 1.1       |
| 10°-20°   | 188.3  | 2.6       |
| 20°-30°   | 334.5  | 4.7       |
| 30°-40°   | 707.2  | 9.8       |
| 40°-50°   | 1294.6 | 18.0      |
| 50°-60°   | 1766.1 | 24.6      |
| 60°-70°   | 1664.9 | 23.2      |
| 70°-80°   | 1007.6 | 14.0      |
| 80°-90°   | 148.0  | 2.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 7191.4 | 100.0     |
| 0°-180°   | 7191.4 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P560871


CATALOG NUMBER: SDL-PA1-70-727-U-T2U

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 306.0  | 4.3       |                         |      |         |
| FM   | (30°-60°)   | 2851.0 | 39.6      |                         |      |         |
| FH   | (60°-80°)   | 1834.7 | 25.5      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 90.8   | 1.3       |                         |      | G1/100  |
| BL   | (0°-30°)    | 297.0  | 4.1       | B1/500                  |      |         |
| BM   | (30°-60°)   | 916.8  | 12.7      | B1/1000                 |      |         |
| BH   | (60°-80°)   | 837.8  | 11.7      | B2/1000                 |      | G2/1000 |
| BVH  | (80°-90°)   | 57.3   | 0.8       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G2**

Type II Medium





REPORT NUMBER: P560871

CATALOG NUMBER: SDL-PA1-70-727-U-T2U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    | 50°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 |
| 2.5°  | 840.9  | 848.7  | 900.4  | 952.2  | 954.7  | 954.7  | 957.3  | 959.9  | 967.7  | 972.9  | 978.0  |
| 5°    | 784.0  | 789.2  | 789.2  | 789.2  | 791.7  | 794.3  | 796.9  | 796.9  | 802.1  | 804.7  | 809.9  |
| 7.5°  | 657.2  | 708.9  | 727.1  | 742.6  | 752.9  | 760.7  | 765.9  | 771.0  | 776.2  | 781.4  | 786.6  |
| 10°   | 747.8  | 747.8  | 750.3  | 750.3  | 750.3  | 747.8  | 696.0  | 641.7  | 667.5  | 693.4  | 654.6  |
| 12.5° | 615.8  | 626.1  | 672.7  | 716.7  | 729.6  | 740.0  | 714.1  | 685.7  | 639.1  | 592.5  | 587.3  |
| 15°   | 732.2  | 732.2  | 732.2  | 729.6  | 683.1  | 633.9  | 584.7  | 533.0  | 564.1  | 595.1  | 548.5  |
| 17.5° | 633.9  | 633.9  | 672.7  | 708.9  | 706.4  | 701.2  | 657.2  | 610.6  | 538.2  | 463.1  | 522.7  |
| 20°   | 799.5  | 796.9  | 784.0  | 768.5  | 672.7  | 577.0  | 597.7  | 618.4  | 623.6  | 626.1  | 608.0  |
| 22.5° | 714.1  | 716.7  | 732.2  | 747.8  | 750.3  | 752.9  | 641.7  | 527.8  | 592.5  | 657.2  | 595.1  |
| 25°   | 993.6  | 988.4  | 965.1  | 939.2  | 833.1  | 724.5  | 745.2  | 765.9  | 659.8  | 551.1  | 618.4  |
| 27.5° | 944.4  | 928.9  | 918.5  | 908.2  | 926.3  | 944.4  | 846.1  | 745.2  | 768.5  | 791.7  | 706.4  |
| 30°   | 1350.6 | 1350.6 | 1324.7 | 1296.3 | 1135.9 | 972.9  | 947.0  | 921.1  | 859.0  | 794.3  | 809.9  |
| 32.5° | 1710.3 | 1710.3 | 1614.5 | 1516.2 | 1420.5 | 1324.7 | 1198.0 | 1071.2 | 1045.3 | 1016.8 | 991.0  |
| 35°   | 2152.7 | 2139.8 | 2085.4 | 2028.5 | 1821.5 | 1614.5 | 1451.5 | 1288.5 | 1236.8 | 1185.0 | 1159.1 |
| 37.5° | 2566.7 | 2538.2 | 2463.2 | 2385.6 | 2168.2 | 1948.3 | 1733.5 | 1518.8 | 1461.9 | 1405.0 | 1348.0 |
| 40°   | 2908.2 | 2892.7 | 2840.9 | 2786.6 | 2540.8 | 2295.0 | 2051.8 | 1806.0 | 1731.0 | 1655.9 | 1573.1 |
| 42.5° | 3221.3 | 3208.4 | 3161.8 | 3112.6 | 2869.4 | 2623.6 | 2393.3 | 2160.5 | 2049.2 | 1938.0 | 1839.6 |
| 45°   | 3451.6 | 3430.9 | 3399.8 | 3366.2 | 3172.1 | 2975.5 | 2742.6 | 2507.2 | 2463.2 | 2419.2 | 2227.7 |
| 47.5° | 3524.0 | 3487.8 | 3482.6 | 3477.4 | 3322.2 | 3167.0 | 2980.7 | 2794.4 | 2802.1 | 2809.9 | 2587.4 |
| 50°   | 3417.9 | 3363.6 | 3386.9 | 3410.2 | 3348.1 | 3283.4 | 3138.5 | 2993.6 | 3058.3 | 3120.4 | 2944.4 |
| 52.5° | 3032.4 | 3019.5 | 3079.0 | 3135.9 | 3151.4 | 3167.0 | 3135.9 | 3102.3 | 3221.3 | 3340.3 | 3275.6 |
| 55°   | 2502.0 | 2558.9 | 2641.7 | 2724.5 | 2789.2 | 2851.3 | 2941.9 | 3032.4 | 3236.8 | 3441.2 | 3487.8 |
| 57.5° | 1971.6 | 2031.1 | 2126.8 | 2222.6 | 2297.6 | 2372.6 | 2558.9 | 2745.2 | 3053.1 | 3361.0 | 3570.6 |
| 60°   | 1327.3 | 1389.4 | 1547.3 | 1702.5 | 1808.6 | 1914.7 | 2082.8 | 2251.0 | 2639.1 | 3027.2 | 3451.6 |
| 62.5° | 884.9  | 864.2  | 996.1  | 1125.5 | 1296.3 | 1467.0 | 1542.1 | 1614.5 | 2020.7 | 2424.4 | 3110.0 |
| 65°   | 543.4  | 545.9  | 597.7  | 646.8  | 835.7  | 1022.0 | 1081.5 | 1138.4 | 1368.7 | 1599.0 | 2533.1 |
| 67.5° | 364.8  | 372.6  | 395.9  | 419.2  | 509.7  | 600.3  | 703.8  | 807.3  | 861.6  | 913.3  | 1847.4 |
| 70°   | 323.4  | 326.0  | 336.4  | 346.7  | 372.6  | 398.5  | 494.2  | 589.9  | 558.9  | 525.2  | 1047.9 |
| 72.5° | 284.6  | 287.2  | 305.3  | 320.8  | 333.8  | 346.7  | 403.6  | 460.6  | 424.3  | 388.1  | 522.7  |
| 75°   | 232.9  | 240.6  | 258.7  | 274.3  | 300.1  | 323.4  | 336.4  | 349.3  | 331.2  | 310.5  | 336.4  |
| 77.5° | 191.5  | 196.6  | 209.6  | 222.5  | 248.4  | 271.7  | 284.6  | 297.5  | 269.1  | 240.6  | 256.2  |
| 80°   | 150.1  | 152.7  | 163.0  | 173.4  | 194.1  | 212.2  | 227.7  | 240.6  | 214.8  | 186.3  | 194.1  |
| 82.5° | 90.6   | 93.1   | 108.7  | 121.6  | 139.7  | 155.2  | 165.6  | 173.4  | 181.1  | 186.3  | 163.0  |
| 85°   | 49.2   | 49.2   | 59.5   | 69.9   | 72.4   | 75.0   | 85.4   | 93.1   | 116.4  | 137.1  | 119.0  |
| 87.5° | 7.8    | 7.8    | 10.3   | 10.3   | 15.5   | 18.1   | 20.7   | 20.7   | 23.3   | 23.3   | 25.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560871

CATALOG NUMBER: SDL-PA1-70-727-U-T2U

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   | 105°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 |
| 2.5°  | 980.6  | 983.2  | 983.2  | 983.2  | 985.8  | 988.4  | 991.0  | 991.0  | 993.6  | 996.1  | 998.7  |
| 5°    | 815.0  | 882.3  | 947.0  | 957.3  | 965.1  | 970.3  | 975.4  | 978.0  | 983.2  | 988.4  | 991.0  |
| 7.5°  | 791.7  | 791.7  | 791.7  | 773.6  | 840.9  | 848.7  | 856.4  | 861.6  | 866.8  | 861.6  | 853.8  |
| 10°   | 613.2  | 613.2  | 610.6  | 615.8  | 644.3  | 693.4  | 740.0  | 745.2  | 750.3  | 708.9  | 665.0  |
| 12.5° | 579.6  | 587.3  | 595.1  | 582.2  | 530.4  | 574.4  | 618.4  | 626.1  | 628.7  | 592.5  | 553.7  |
| 15°   | 499.4  | 502.0  | 504.5  | 522.7  | 628.7  | 672.7  | 716.7  | 724.5  | 732.2  | 693.4  | 652.0  |
| 17.5° | 579.6  | 561.5  | 540.8  | 589.9  | 548.5  | 577.0  | 602.9  | 540.8  | 597.7  | 587.3  | 577.0  |
| 20°   | 589.9  | 527.8  | 463.1  | 551.1  | 644.3  | 688.2  | 729.6  | 734.8  | 737.4  | 706.4  | 672.7  |
| 22.5° | 533.0  | 592.5  | 652.0  | 592.5  | 556.3  | 551.1  | 545.9  | 543.4  | 545.9  | 564.1  | 579.6  |
| 25°   | 685.7  | 610.6  | 535.6  | 672.7  | 758.1  | 778.8  | 799.5  | 789.2  | 784.0  | 745.2  | 706.4  |
| 27.5° | 621.0  | 680.5  | 737.4  | 794.3  | 820.2  | 848.7  | 874.5  | 882.3  | 840.9  | 799.5  | 758.1  |
| 30°   | 822.8  | 859.0  | 892.6  | 1009.1 | 1094.5 | 1120.3 | 1146.2 | 1120.3 | 1104.8 | 1053.1 | 998.7  |
| 32.5° | 962.5  | 1035.0 | 1107.4 | 1104.8 | 1185.0 | 1205.7 | 1223.8 | 1190.2 | 1161.7 | 1104.8 | 1045.3 |
| 35°   | 1133.3 | 1179.8 | 1226.4 | 1252.3 | 1332.5 | 1340.3 | 1348.0 | 1304.0 | 1262.6 | 1195.4 | 1128.1 |
| 37.5° | 1291.1 | 1350.6 | 1407.5 | 1472.2 | 1542.1 | 1526.6 | 1508.4 | 1454.1 | 1386.8 | 1335.1 | 1283.3 |
| 40°   | 1487.7 | 1560.2 | 1632.6 | 1715.4 | 1756.8 | 1733.5 | 1707.7 | 1624.9 | 1560.2 | 1505.9 | 1451.5 |
| 42.5° | 1738.7 | 1816.3 | 1891.4 | 1963.8 | 1979.4 | 1953.5 | 1925.0 | 1834.5 | 1736.1 | 1681.8 | 1624.9 |
| 45°   | 2033.7 | 2095.8 | 2157.9 | 2232.9 | 2264.0 | 2217.4 | 2168.2 | 2054.4 | 1938.0 | 1860.3 | 1782.7 |
| 47.5° | 2362.3 | 2390.7 | 2419.2 | 2548.6 | 2590.0 | 2512.4 | 2432.1 | 2307.9 | 2144.9 | 2044.0 | 1940.5 |
| 50°   | 2768.5 | 2760.7 | 2750.4 | 2864.2 | 2960.0 | 2830.6 | 2698.6 | 2553.7 | 2393.3 | 2251.0 | 2106.1 |
| 52.5° | 3210.9 | 3135.9 | 3058.3 | 3210.9 | 3257.5 | 3102.3 | 2947.0 | 2791.8 | 2631.4 | 2447.7 | 2261.4 |
| 55°   | 3534.4 | 3493.0 | 3451.6 | 3560.2 | 3555.1 | 3374.0 | 3190.2 | 3006.5 | 2874.6 | 2628.8 | 2383.0 |
| 57.5° | 3777.6 | 3813.8 | 3847.4 | 3956.1 | 3831.9 | 3624.9 | 3417.9 | 3234.2 | 3120.4 | 2812.5 | 2504.6 |
| 60°   | 3873.3 | 4059.6 | 4243.3 | 4308.0 | 4119.1 | 3886.3 | 3650.8 | 3469.7 | 3374.0 | 3001.4 | 2628.8 |
| 62.5° | 3795.7 | 4207.1 | 4618.5 | 4631.4 | 4383.0 | 4121.7 | 3860.4 | 3712.9 | 3663.7 | 3205.8 | 2745.2 |
| 65°   | 3467.1 | 4145.0 | 4820.3 | 4866.9 | 4587.4 | 4313.2 | 4036.3 | 3927.7 | 3958.7 | 3397.2 | 2833.2 |
| 67.5° | 2778.9 | 3767.2 | 4753.0 | 4905.7 | 4636.6 | 4346.8 | 4057.0 | 4018.2 | 4134.6 | 3490.4 | 2846.1 |
| 70°   | 1570.5 | 2895.3 | 4217.4 | 4641.8 | 4499.5 | 4212.3 | 3922.5 | 3940.6 | 4113.9 | 3438.6 | 2763.3 |
| 72.5° | 654.6  | 2002.6 | 3350.7 | 4015.6 | 4139.8 | 3896.6 | 3650.8 | 3718.1 | 3837.1 | 3195.4 | 2551.2 |
| 75°   | 362.2  | 1278.2 | 2194.1 | 3079.0 | 3461.9 | 3397.2 | 3330.0 | 3405.0 | 3348.1 | 2727.1 | 2106.1 |
| 77.5° | 269.1  | 690.8  | 1112.6 | 2062.1 | 2605.5 | 2753.0 | 2897.9 | 2934.1 | 2615.8 | 1992.3 | 1368.7 |
| 80°   | 201.8  | 328.6  | 452.8  | 1053.1 | 1397.2 | 1661.1 | 1925.0 | 1762.0 | 1539.5 | 1076.4 | 613.2  |
| 82.5° | 139.7  | 188.9  | 238.0  | 338.9  | 543.4  | 626.1  | 706.4  | 672.7  | 504.5  | 354.5  | 201.8  |
| 85°   | 98.3   | 124.2  | 150.1  | 186.3  | 232.9  | 186.3  | 139.7  | 113.8  | 132.0  | 121.6  | 111.3  |
| 87.5° | 25.9   | 25.9   | 23.3   | 25.9   | 18.1   | 15.5   | 12.9   | 10.3   | 10.3   | 10.3   | 10.3   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P560871

CATALOG NUMBER: SDL-PA1-70-727-U-T2U

**CANDELA DISTRIBUTION (continued):**

|       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   | 160°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 | 1001.3 |
| 2.5°  | 1001.3 | 1003.9 | 1003.9 | 1003.9 | 1003.9 | 1001.3 | 988.4  | 975.4  | 944.4  | 913.3  | 903.0  |
| 5°    | 957.3  | 923.7  | 897.8  | 871.9  | 871.9  | 871.9  | 877.1  | 882.3  | 884.9  | 887.5  | 890.1  |
| 7.5°  | 853.8  | 851.2  | 861.6  | 871.9  | 879.7  | 887.5  | 892.6  | 897.8  | 887.5  | 877.1  | 853.8  |
| 10°   | 667.5  | 667.5  | 680.5  | 690.8  | 708.9  | 727.1  | 778.8  | 830.6  | 874.5  | 918.5  | 926.3  |
| 12.5° | 605.4  | 654.6  | 626.1  | 595.1  | 659.8  | 724.5  | 781.4  | 835.7  | 879.7  | 921.1  | 887.5  |
| 15°   | 608.0  | 561.5  | 571.8  | 582.2  | 652.0  | 721.9  | 670.1  | 615.8  | 719.3  | 820.2  | 843.5  |
| 17.5° | 579.6  | 582.2  | 628.7  | 675.3  | 605.4  | 533.0  | 623.6  | 714.1  | 752.9  | 789.2  | 755.5  |
| 20°   | 595.1  | 514.9  | 569.2  | 623.6  | 672.7  | 719.3  | 672.7  | 623.6  | 636.5  | 649.4  | 737.4  |
| 22.5° | 628.7  | 677.9  | 631.3  | 584.7  | 641.7  | 696.0  | 672.7  | 649.4  | 690.8  | 729.6  | 693.4  |
| 25°   | 626.1  | 543.4  | 621.0  | 698.6  | 646.8  | 592.5  | 621.0  | 649.4  | 628.7  | 605.4  | 672.7  |
| 27.5° | 721.9  | 685.7  | 665.0  | 641.7  | 670.1  | 698.6  | 639.1  | 579.6  | 579.6  | 579.6  | 571.8  |
| 30°   | 903.0  | 807.3  | 765.9  | 721.9  | 652.0  | 582.2  | 561.5  | 540.8  | 543.4  | 545.9  | 584.7  |
| 32.5° | 1009.1 | 972.9  | 848.7  | 724.5  | 659.8  | 595.1  | 540.8  | 486.4  | 491.6  | 496.8  | 545.9  |
| 35°   | 1102.2 | 1073.8 | 908.2  | 740.0  | 633.9  | 525.2  | 478.7  | 429.5  | 452.8  | 473.5  | 514.9  |
| 37.5° | 1208.3 | 1130.7 | 905.6  | 677.9  | 564.1  | 450.2  | 421.7  | 393.3  | 408.8  | 421.7  | 447.6  |
| 40°   | 1304.0 | 1154.0 | 882.3  | 608.0  | 494.2  | 377.8  | 364.8  | 349.3  | 362.2  | 375.2  | 390.7  |
| 42.5° | 1407.5 | 1187.6 | 848.7  | 507.1  | 416.6  | 326.0  | 320.8  | 315.7  | 328.6  | 341.5  | 351.9  |
| 45°   | 1487.7 | 1192.8 | 804.7  | 414.0  | 354.5  | 295.0  | 295.0  | 292.4  | 305.3  | 315.7  | 320.8  |
| 47.5° | 1539.5 | 1135.9 | 734.8  | 331.2  | 305.3  | 279.4  | 282.0  | 282.0  | 292.4  | 300.1  | 302.7  |
| 50°   | 1575.7 | 1042.7 | 667.5  | 292.4  | 279.4  | 266.5  | 266.5  | 266.5  | 276.9  | 284.6  | 289.8  |
| 52.5° | 1601.6 | 939.2  | 605.4  | 269.1  | 263.9  | 256.2  | 256.2  | 253.6  | 266.5  | 279.4  | 282.0  |
| 55°   | 1609.4 | 833.1  | 543.4  | 251.0  | 245.8  | 240.6  | 245.8  | 248.4  | 263.9  | 276.9  | 279.4  |
| 57.5° | 1627.5 | 750.3  | 491.6  | 232.9  | 230.3  | 227.7  | 235.5  | 243.2  | 258.7  | 274.3  | 274.3  |
| 60°   | 1663.7 | 696.0  | 455.4  | 214.8  | 214.8  | 214.8  | 227.7  | 238.0  | 253.6  | 269.1  | 266.5  |
| 62.5° | 1697.3 | 646.8  | 421.7  | 196.6  | 199.2  | 201.8  | 217.3  | 232.9  | 248.4  | 263.9  | 261.3  |
| 65°   | 1702.5 | 569.2  | 375.2  | 181.1  | 186.3  | 188.9  | 207.0  | 225.1  | 240.6  | 256.2  | 251.0  |
| 67.5° | 1645.6 | 445.0  | 305.3  | 165.6  | 173.4  | 178.5  | 199.2  | 217.3  | 232.9  | 245.8  | 240.6  |
| 70°   | 1542.1 | 318.2  | 235.5  | 152.7  | 160.4  | 165.6  | 186.3  | 204.4  | 217.3  | 230.3  | 225.1  |
| 72.5° | 1389.4 | 227.7  | 183.7  | 139.7  | 144.9  | 150.1  | 168.2  | 186.3  | 201.8  | 214.8  | 209.6  |
| 75°   | 1146.2 | 183.7  | 155.2  | 126.8  | 132.0  | 134.5  | 152.7  | 168.2  | 183.7  | 196.6  | 188.9  |
| 77.5° | 760.7  | 150.1  | 132.0  | 113.8  | 116.4  | 119.0  | 134.5  | 147.5  | 160.4  | 170.8  | 165.6  |
| 80°   | 367.4  | 121.6  | 111.3  | 98.3   | 100.9  | 100.9  | 113.8  | 126.8  | 137.1  | 144.9  | 142.3  |
| 82.5° | 150.1  | 95.7   | 88.0   | 80.2   | 80.2   | 80.2   | 93.1   | 103.5  | 113.8  | 121.6  | 116.4  |
| 85°   | 93.1   | 75.0   | 69.9   | 62.1   | 59.5   | 56.9   | 62.1   | 67.3   | 72.4   | 75.0   | 72.4   |
| 87.5° | 12.9   | 12.9   | 15.5   | 18.1   | 15.5   | 10.3   | 15.5   | 20.7   | 20.7   | 18.1   | 15.5   |
| 90°   | 0.0    | 0.0    | 7.8    | 7.8    | 5.2    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560871

CATALOG NUMBER: SDL-PA1-70-727-U-T2U

**CANDELA DISTRIBUTION (continued):**

|       | 165°   | 170°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|
| 0°    | 1001.3 | 1001.3 | 1001.3 | 1001.3 |
| 2.5°  | 892.6  | 892.6  | 892.6  | 897.8  |
| 5°    | 890.1  | 890.1  | 890.1  | 895.2  |
| 7.5°  | 830.6  | 804.7  | 778.8  | 781.4  |
| 10°   | 931.5  | 934.0  | 934.0  | 936.6  |
| 12.5° | 851.2  | 809.9  | 768.5  | 773.6  |
| 15°   | 866.8  | 866.8  | 864.2  | 866.8  |
| 17.5° | 721.9  | 708.9  | 696.0  | 696.0  |
| 20°   | 825.4  | 825.4  | 825.4  | 825.4  |
| 22.5° | 657.2  | 654.6  | 652.0  | 654.6  |
| 25°   | 740.0  | 742.6  | 742.6  | 740.0  |
| 27.5° | 564.1  | 597.7  | 628.7  | 631.3  |
| 30°   | 621.0  | 621.0  | 621.0  | 621.0  |
| 32.5° | 595.1  | 621.0  | 646.8  | 649.4  |
| 35°   | 553.7  | 551.1  | 548.5  | 556.3  |
| 37.5° | 470.9  | 465.7  | 460.6  | 460.6  |
| 40°   | 406.2  | 395.9  | 385.5  | 385.5  |
| 42.5° | 359.6  | 351.9  | 341.5  | 338.9  |
| 45°   | 326.0  | 318.2  | 307.9  | 307.9  |
| 47.5° | 302.7  | 297.5  | 292.4  | 289.8  |
| 50°   | 292.4  | 287.2  | 282.0  | 282.0  |
| 52.5° | 284.6  | 282.0  | 276.9  | 276.9  |
| 55°   | 279.4  | 276.9  | 271.7  | 271.7  |
| 57.5° | 274.3  | 271.7  | 266.5  | 266.5  |
| 60°   | 263.9  | 261.3  | 258.7  | 258.7  |
| 62.5° | 256.2  | 253.6  | 251.0  | 251.0  |
| 65°   | 245.8  | 245.8  | 243.2  | 240.6  |
| 67.5° | 232.9  | 232.9  | 232.9  | 227.7  |
| 70°   | 217.3  | 217.3  | 217.3  | 212.2  |
| 72.5° | 201.8  | 201.8  | 199.2  | 191.5  |
| 75°   | 181.1  | 178.5  | 175.9  | 170.8  |
| 77.5° | 160.4  | 155.2  | 150.1  | 147.5  |
| 80°   | 137.1  | 132.0  | 126.8  | 121.6  |
| 82.5° | 108.7  | 106.1  | 100.9  | 88.0   |
| 85°   | 67.3   | 59.5   | 49.2   | 44.0   |
| 87.5° | 12.9   | 10.3   | 7.8    | 2.6    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    |



Report Generated By 670245982









--- HS --- SS



u











(END OF REPORT)