

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P561231

Luminaire Tested: **SDL-PA1-90-727-U-T4W**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P561231  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-90-727-U-T4W  
Description: Springdale  
(1) 70 CRI, 2700K, 1180mA LIGHT ENGINE WITH 24 LEDS AND TYPE IV WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8505.9 lumens  
Efficiency: N/A  
Efficacy: 92.1 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type IV - Medium  
BUG Rating: B2 - U0 - G3

Input Watts (W): 92.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P561231

CATALOG NUMBER: SDL-PA1-90-727-U-T4W

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 9.9 fc  
 Type IV - Medium - N/A

REPORT NUMBER: P561231

CATALOG NUMBER: SDL-PA1-90-727-U-T4W

## Luminous Intensity Polar Plot



REPORT NUMBER: P561231

CATALOG NUMBER: SDL-PA1-90-727-U-T4W


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1828.8   | 0.0    | 1828.8 |
|                    | % Fixture | 21.5     | 0.0    | 21.5   |
| <b>Street Side</b> | Lumens    | 6677.0   | 0.0    | 6677.0 |
|                    | % Fixture | 78.5     | 0.0    | 78.5   |
| <b>Total</b>       | Lumens    | 8505.9   | 0.0    | 8505.9 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 82.2   | 1.0       |
| 10°-20°   | 207.0  | 2.4       |
| 20°-30°   | 361.9  | 4.3       |
| 30°-40°   | 637.4  | 7.5       |
| 40°-50°   | 961.6  | 11.3      |
| 50°-60°   | 1529.6 | 18.0      |
| 60°-70°   | 2243.0 | 26.4      |
| 70°-80°   | 2103.3 | 24.7      |
| 80°-90°   | 379.8  | 4.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 8505.9 | 100.0     |
| 0°-180°   | 8505.9 | 100.0     |



REPORT NUMBER: P561231


CATALOG NUMBER: SDL-PA1-90-727-U-T4W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 350.7  | 4.1       |                         |      |         |
| FM   | (30°-60°)   | 2291.5 | 26.9      |                         |      |         |
| FH   | (60°-80°)   | 3722.1 | 43.8      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 312.7  | 3.7       |                         |      | G3/500  |
| BL   | (0°-30°)    | 300.3  | 3.5       | B1/500                  |      |         |
| BM   | (30°-60°)   | 837.2  | 9.8       | B1/1000                 |      |         |
| BH   | (60°-80°)   | 624.3  | 7.3       | B2/1000                 |      | G2/1000 |
| BVH  | (80°-90°)   | 67.1   | 0.8       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G3**

Type IV Medium





REPORT NUMBER: P561231

CATALOG NUMBER: SDL-PA1-90-727-U-T4W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    | 50°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  |
| 2.5°  | 898.0  | 935.7  | 954.5  | 973.4  | 979.7  | 985.9  | 985.9  | 982.8  | 982.8  | 982.8  | 989.1  |
| 5°    | 913.7  | 910.6  | 910.6  | 910.6  | 907.4  | 904.3  | 901.2  | 894.9  | 891.7  | 885.5  | 882.3  |
| 7.5°  | 838.4  | 901.2  | 904.3  | 907.4  | 907.4  | 904.3  | 910.6  | 916.9  | 910.6  | 901.2  | 888.6  |
| 10°   | 995.4  | 992.2  | 985.9  | 979.7  | 970.2  | 960.8  | 888.6  | 813.2  | 819.5  | 825.8  | 766.1  |
| 12.5° | 863.5  | 923.1  | 948.3  | 973.4  | 976.5  | 976.5  | 926.3  | 872.9  | 803.8  | 734.8  | 706.5  |
| 15°   | 1055.0 | 1048.7 | 1036.2 | 1023.6 | 938.8  | 850.9  | 800.7  | 750.5  | 750.5  | 750.5  | 665.7  |
| 17.5° | 888.6  | 885.5  | 942.0  | 998.5  | 967.1  | 935.7  | 863.5  | 791.3  | 684.5  | 574.6  | 643.7  |
| 20°   | 1089.6 | 1089.6 | 1073.9 | 1058.2 | 913.7  | 766.1  | 775.6  | 781.8  | 785.0  | 785.0  | 753.6  |
| 22.5° | 913.7  | 907.4  | 913.7  | 916.9  | 916.9  | 916.9  | 785.0  | 653.1  | 725.3  | 794.4  | 722.2  |
| 25°   | 1089.6 | 1092.7 | 1089.6 | 1086.4 | 954.5  | 819.5  | 841.5  | 863.5  | 763.0  | 659.4  | 728.5  |
| 27.5° | 951.4  | 948.3  | 932.6  | 916.9  | 920.0  | 923.1  | 854.1  | 781.8  | 822.7  | 863.5  | 791.3  |
| 30°   | 1164.9 | 1168.1 | 1158.6 | 1146.1 | 1014.2 | 882.3  | 876.0  | 866.6  | 838.4  | 810.1  | 835.2  |
| 32.5° | 1406.7 | 1406.7 | 1309.4 | 1212.0 | 1130.4 | 1045.6 | 976.5  | 907.4  | 935.7  | 964.0  | 932.6  |
| 35°   | 1535.4 | 1529.2 | 1497.8 | 1463.2 | 1312.5 | 1158.6 | 1064.4 | 967.1  | 976.5  | 982.8  | 982.8  |
| 37.5° | 1764.7 | 1761.5 | 1717.6 | 1673.6 | 1469.5 | 1262.3 | 1139.8 | 1014.2 | 1033.0 | 1048.7 | 1026.8 |
| 40°   | 2050.4 | 2050.4 | 2015.9 | 1978.2 | 1717.6 | 1453.8 | 1281.1 | 1108.4 | 1105.3 | 1099.0 | 1073.9 |
| 42.5° | 2326.7 | 2336.1 | 2314.1 | 2292.2 | 1987.6 | 1683.0 | 1456.9 | 1230.9 | 1202.6 | 1174.3 | 1149.2 |
| 45°   | 2508.8 | 2521.4 | 2540.2 | 2559.1 | 2257.6 | 1956.2 | 1692.4 | 1425.5 | 1372.2 | 1315.6 | 1271.7 |
| 47.5° | 2694.1 | 2675.2 | 2700.4 | 2725.5 | 2468.0 | 2210.5 | 1921.7 | 1632.8 | 1544.9 | 1456.9 | 1409.8 |
| 50°   | 2866.8 | 2860.5 | 2869.9 | 2879.3 | 2669.0 | 2458.6 | 2160.3 | 1862.0 | 1755.2 | 1645.3 | 1592.0 |
| 52.5° | 3092.9 | 3070.9 | 3058.3 | 3045.8 | 2866.8 | 2687.8 | 2405.2 | 2119.5 | 1993.9 | 1865.1 | 1802.3 |
| 55°   | 3309.5 | 3300.1 | 3281.3 | 3259.3 | 3105.4 | 2951.6 | 2653.3 | 2355.0 | 2223.1 | 2091.2 | 2019.0 |
| 57.5° | 3532.5 | 3526.2 | 3523.0 | 3519.9 | 3384.9 | 3249.9 | 2945.3 | 2637.6 | 2486.8 | 2333.0 | 2273.3 |
| 60°   | 3742.8 | 3746.0 | 3771.1 | 3793.1 | 3689.5 | 3585.8 | 3278.1 | 2970.4 | 2778.9 | 2584.2 | 2524.5 |
| 62.5° | 3868.4 | 3877.8 | 3940.6 | 4000.3 | 3943.8 | 3887.3 | 3570.1 | 3249.9 | 3048.9 | 2844.8 | 2804.0 |
| 65°   | 3708.3 | 3755.4 | 3937.5 | 4119.6 | 4119.6 | 4119.6 | 3830.7 | 3538.7 | 3362.9 | 3187.1 | 3152.5 |
| 67.5° | 3350.3 | 3397.4 | 3658.1 | 3915.5 | 4050.5 | 4185.6 | 3997.2 | 3808.8 | 3689.5 | 3567.0 | 3523.0 |
| 70°   | 3055.2 | 3083.4 | 3328.4 | 3570.1 | 3909.2 | 4248.4 | 4125.9 | 4000.3 | 3994.0 | 3984.6 | 3865.3 |
| 72.5° | 2807.1 | 2869.9 | 3070.9 | 3268.7 | 3736.6 | 4204.4 | 4201.3 | 4198.1 | 4326.9 | 4455.6 | 4226.4 |
| 75°   | 2245.1 | 2238.8 | 2427.2 | 2615.6 | 3143.1 | 3667.5 | 3962.6 | 4254.6 | 4625.2 | 4992.5 | 4640.9 |
| 77.5° | 1001.6 | 1070.7 | 1249.7 | 1428.7 | 1902.8 | 2373.8 | 2942.1 | 3510.5 | 4326.9 | 5140.1 | 4782.2 |
| 80°   | 285.7  | 301.4  | 351.7  | 398.8  | 621.7  | 841.5  | 1438.1 | 2031.6 | 3058.3 | 4081.9 | 3840.2 |
| 82.5° | 150.7  | 157.0  | 188.4  | 216.7  | 279.5  | 339.1  | 565.2  | 788.1  | 1670.5 | 2549.6 | 2329.8 |
| 85°   | 72.2   | 65.9   | 84.8   | 100.5  | 135.0  | 169.6  | 260.6  | 351.7  | 646.8  | 942.0  | 813.2  |
| 87.5° | 15.7   | 15.7   | 18.8   | 18.8   | 28.3   | 37.7   | 56.5   | 75.4   | 72.2   | 65.9   | 78.5   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P561231

CATALOG NUMBER: SDL-PA1-90-727-U-T4W

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   | 105°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  | 989.1  |
| 2.5°  | 992.2  | 995.4  | 998.5  | 995.4  | 992.2  | 989.1  | 989.1  | 985.9  | 985.9  | 982.8  | 976.5  |
| 5°    | 879.2  | 923.1  | 967.1  | 970.2  | 973.4  | 973.4  | 970.2  | 967.1  | 960.8  | 957.7  | 951.4  |
| 7.5°  | 876.0  | 860.3  | 844.6  | 847.8  | 850.9  | 854.1  | 854.1  | 844.6  | 841.5  | 816.4  | 791.3  |
| 10°   | 703.4  | 687.7  | 672.0  | 681.4  | 690.8  | 725.3  | 744.2  | 737.9  | 731.6  | 687.7  | 640.6  |
| 12.5° | 678.2  | 672.0  | 665.7  | 618.6  | 571.5  | 612.3  | 640.6  | 637.4  | 628.0  | 587.2  | 546.4  |
| 15°   | 580.9  | 584.0  | 584.0  | 637.4  | 690.8  | 725.3  | 750.5  | 744.2  | 737.9  | 687.7  | 637.4  |
| 17.5° | 709.6  | 675.1  | 637.4  | 628.0  | 618.6  | 634.3  | 612.3  | 577.8  | 599.7  | 593.5  | 587.2  |
| 20°   | 719.1  | 634.3  | 546.4  | 634.3  | 722.2  | 744.2  | 791.3  | 788.1  | 778.7  | 734.8  | 690.8  |
| 22.5° | 650.0  | 700.2  | 747.3  | 700.2  | 653.1  | 621.7  | 606.0  | 599.7  | 596.6  | 609.2  | 618.6  |
| 25°   | 797.5  | 703.4  | 606.0  | 722.2  | 835.2  | 860.3  | 872.9  | 863.5  | 860.3  | 803.8  | 747.3  |
| 27.5° | 715.9  | 766.1  | 816.4  | 854.1  | 891.7  | 923.1  | 1017.3 | 926.3  | 923.1  | 869.8  | 813.2  |
| 30°   | 857.2  | 910.6  | 964.0  | 1061.3 | 1158.6 | 1212.0 | 1230.9 | 1224.6 | 1208.9 | 1124.1 | 1039.3 |
| 32.5° | 901.2  | 1007.9 | 1111.5 | 1155.5 | 1196.3 | 1252.8 | 1281.1 | 1278.0 | 1262.3 | 1161.8 | 1058.2 |
| 35°   | 982.8  | 1061.3 | 1139.8 | 1199.5 | 1256.0 | 1309.4 | 1334.5 | 1343.9 | 1325.1 | 1199.5 | 1070.7 |
| 37.5° | 1004.8 | 1105.3 | 1205.7 | 1268.5 | 1331.3 | 1372.2 | 1394.1 | 1422.4 | 1400.4 | 1249.7 | 1095.8 |
| 40°   | 1048.7 | 1168.1 | 1284.2 | 1347.0 | 1406.7 | 1444.4 | 1482.1 | 1516.6 | 1488.3 | 1306.2 | 1121.0 |
| 42.5° | 1121.0 | 1243.4 | 1362.7 | 1435.0 | 1504.0 | 1557.4 | 1601.4 | 1648.5 | 1595.1 | 1359.6 | 1121.0 |
| 45°   | 1227.7 | 1340.8 | 1453.8 | 1551.1 | 1645.3 | 1711.3 | 1774.1 | 1840.0 | 1733.3 | 1428.7 | 1121.0 |
| 47.5° | 1362.7 | 1472.6 | 1579.4 | 1733.3 | 1887.1 | 1946.8 | 2022.1 | 2084.9 | 1912.2 | 1516.6 | 1121.0 |
| 50°   | 1535.4 | 1657.9 | 1780.4 | 1984.5 | 2185.4 | 2241.9 | 2336.1 | 2383.2 | 2150.9 | 1651.6 | 1149.2 |
| 52.5° | 1736.4 | 1871.4 | 2003.3 | 2241.9 | 2480.6 | 2574.8 | 2700.4 | 2731.8 | 2392.6 | 1786.6 | 1177.5 |
| 55°   | 1946.8 | 2128.9 | 2307.9 | 2571.6 | 2832.2 | 2923.3 | 3102.3 | 3127.4 | 2703.5 | 1953.1 | 1199.5 |
| 57.5° | 2213.7 | 2427.2 | 2637.6 | 2895.0 | 3149.4 | 3278.1 | 3557.6 | 3567.0 | 3064.6 | 2157.2 | 1246.6 |
| 60°   | 2464.9 | 2731.8 | 2995.5 | 3240.4 | 3485.4 | 3686.3 | 4009.7 | 4012.9 | 3403.7 | 2311.0 | 1215.2 |
| 62.5° | 2763.2 | 3080.3 | 3394.3 | 3604.7 | 3815.0 | 4063.1 | 4452.5 | 4395.9 | 3642.4 | 2329.8 | 1017.3 |
| 65°   | 3114.8 | 3441.4 | 3768.0 | 3946.9 | 4122.8 | 4405.4 | 4826.1 | 4609.5 | 3708.3 | 2223.1 | 734.8  |
| 67.5° | 3475.9 | 3780.5 | 4085.1 | 4226.4 | 4367.7 | 4725.6 | 5099.3 | 4634.6 | 3611.0 | 2063.0 | 511.8  |
| 70°   | 3746.0 | 4031.7 | 4317.4 | 4439.9 | 4562.4 | 4948.6 | 5180.9 | 4471.3 | 3337.8 | 1868.3 | 398.8  |
| 72.5° | 3994.0 | 4264.1 | 4531.0 | 4593.8 | 4653.4 | 4851.2 | 4766.5 | 3940.6 | 2813.4 | 1573.1 | 329.7  |
| 75°   | 4289.2 | 4461.9 | 4631.4 | 4518.4 | 4405.4 | 4138.5 | 3658.1 | 2873.1 | 2059.8 | 1171.2 | 282.6  |
| 77.5° | 4424.2 | 4383.4 | 4339.4 | 3953.2 | 3567.0 | 2851.1 | 2273.3 | 1661.0 | 1045.6 | 643.7  | 241.8  |
| 80°   | 3598.4 | 3435.1 | 3268.7 | 2621.9 | 1975.0 | 1350.2 | 885.5  | 562.1  | 383.1  | 288.9  | 194.7  |
| 82.5° | 2106.9 | 1727.0 | 1347.0 | 989.1  | 631.1  | 442.7  | 288.9  | 229.2  | 179.0  | 169.6  | 157.0  |
| 85°   | 681.4  | 602.9  | 524.4  | 414.5  | 304.6  | 188.4  | 109.9  | 100.5  | 94.2   | 103.6  | 109.9  |
| 87.5° | 91.1   | 91.1   | 87.9   | 65.9   | 40.8   | 22.0   | 12.6   | 9.4    | 9.4    | 12.6   | 12.6   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P561231

CATALOG NUMBER: SDL-PA1-90-727-U-T4W

**CANDELA DISTRIBUTION (continued):**

|       | 110°  | 115°  | 120°  | 125°  | 130°  | 135°  | 140°  | 145°  | 150°  | 155°  | 160°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 989.1 | 989.1 | 989.1 | 989.1 | 989.1 | 989.1 | 989.1 | 989.1 | 989.1 | 989.1 | 989.1 |
| 2.5°  | 976.5 | 973.4 | 970.2 | 967.1 | 964.0 | 957.7 | 932.6 | 907.4 | 898.0 | 885.5 | 876.0 |
| 5°    | 920.0 | 888.6 | 866.6 | 844.6 | 835.2 | 822.7 | 825.8 | 828.9 | 832.1 | 832.1 | 832.1 |
| 7.5°  | 797.5 | 803.8 | 807.0 | 807.0 | 816.4 | 822.7 | 828.9 | 832.1 | 819.5 | 807.0 | 791.3 |
| 10°   | 634.3 | 624.9 | 637.4 | 646.8 | 662.5 | 675.1 | 715.9 | 756.7 | 794.4 | 832.1 | 847.8 |
| 12.5° | 577.8 | 609.2 | 584.0 | 558.9 | 609.2 | 656.3 | 712.8 | 769.3 | 803.8 | 835.2 | 807.0 |
| 15°   | 587.2 | 533.8 | 540.1 | 543.2 | 606.0 | 665.7 | 631.1 | 596.6 | 693.9 | 788.1 | 816.4 |
| 17.5° | 577.8 | 568.3 | 602.9 | 634.3 | 574.6 | 515.0 | 599.7 | 681.4 | 725.3 | 769.3 | 756.7 |
| 20°   | 624.9 | 555.8 | 555.8 | 555.8 | 609.2 | 662.5 | 621.7 | 580.9 | 628.0 | 675.1 | 753.6 |
| 22.5° | 646.8 | 672.0 | 621.7 | 568.3 | 602.9 | 637.4 | 637.4 | 634.3 | 687.7 | 737.9 | 725.3 |
| 25°   | 653.1 | 558.9 | 602.9 | 643.7 | 621.7 | 596.6 | 624.9 | 650.0 | 665.7 | 681.4 | 750.5 |
| 27.5° | 747.3 | 681.4 | 631.1 | 577.8 | 618.6 | 659.4 | 650.0 | 640.6 | 653.1 | 665.7 | 681.4 |
| 30°   | 885.5 | 731.6 | 675.1 | 615.4 | 593.5 | 568.3 | 596.6 | 621.7 | 668.8 | 715.9 | 778.7 |
| 32.5° | 926.3 | 791.3 | 700.2 | 606.0 | 602.9 | 596.6 | 606.0 | 612.3 | 665.7 | 715.9 | 803.8 |
| 35°   | 920.0 | 766.1 | 678.2 | 587.2 | 568.3 | 549.5 | 565.2 | 577.8 | 656.3 | 734.8 | 819.5 |
| 37.5° | 913.7 | 728.5 | 637.4 | 546.4 | 533.8 | 518.1 | 533.8 | 549.5 | 609.2 | 668.8 | 747.3 |
| 40°   | 904.3 | 684.5 | 596.6 | 505.5 | 489.8 | 474.1 | 489.8 | 502.4 | 549.5 | 596.6 | 659.4 |
| 42.5° | 882.3 | 640.6 | 552.6 | 461.6 | 449.0 | 433.3 | 445.9 | 458.4 | 499.3 | 540.1 | 577.8 |
| 45°   | 857.2 | 590.3 | 505.5 | 420.8 | 408.2 | 395.6 | 405.1 | 411.3 | 449.0 | 483.6 | 502.4 |
| 47.5° | 828.9 | 536.9 | 458.4 | 379.9 | 367.4 | 354.8 | 364.2 | 370.5 | 398.8 | 427.0 | 433.3 |
| 50°   | 822.7 | 493.0 | 420.8 | 345.4 | 336.0 | 323.4 | 329.7 | 336.0 | 358.0 | 376.8 | 376.8 |
| 52.5° | 810.1 | 439.6 | 379.9 | 317.1 | 310.9 | 301.4 | 304.6 | 307.7 | 323.4 | 339.1 | 336.0 |
| 55°   | 800.7 | 401.9 | 348.5 | 295.2 | 288.9 | 279.5 | 282.6 | 285.7 | 301.4 | 314.0 | 310.9 |
| 57.5° | 810.1 | 370.5 | 323.4 | 273.2 | 266.9 | 260.6 | 266.9 | 273.2 | 288.9 | 304.6 | 304.6 |
| 60°   | 778.7 | 339.1 | 295.2 | 251.2 | 248.1 | 241.8 | 257.5 | 270.0 | 295.2 | 317.1 | 323.4 |
| 62.5° | 665.7 | 310.9 | 273.2 | 235.5 | 238.6 | 238.6 | 266.9 | 292.0 | 326.6 | 358.0 | 364.2 |
| 65°   | 511.8 | 288.9 | 257.5 | 222.9 | 238.6 | 254.3 | 292.0 | 329.7 | 361.1 | 392.5 | 383.1 |
| 67.5° | 392.5 | 273.2 | 248.1 | 219.8 | 254.3 | 285.7 | 320.3 | 354.8 | 370.5 | 383.1 | 367.4 |
| 70°   | 329.7 | 257.5 | 238.6 | 216.7 | 251.2 | 285.7 | 320.3 | 354.8 | 361.1 | 367.4 | 351.7 |
| 72.5° | 288.9 | 244.9 | 226.1 | 207.2 | 235.5 | 263.8 | 304.6 | 342.3 | 348.5 | 351.7 | 336.0 |
| 75°   | 257.5 | 229.2 | 207.2 | 185.3 | 213.5 | 238.6 | 279.5 | 320.3 | 326.6 | 329.7 | 317.1 |
| 77.5° | 226.1 | 210.4 | 185.3 | 160.1 | 188.4 | 216.7 | 254.3 | 292.0 | 301.4 | 310.9 | 295.2 |
| 80°   | 188.4 | 179.0 | 160.1 | 141.3 | 172.7 | 201.0 | 235.5 | 270.0 | 279.5 | 288.9 | 273.2 |
| 82.5° | 150.7 | 144.4 | 131.9 | 119.3 | 150.7 | 182.1 | 216.7 | 248.1 | 257.5 | 263.8 | 244.9 |
| 85°   | 109.9 | 109.9 | 103.6 | 97.3  | 128.7 | 157.0 | 179.0 | 201.0 | 197.8 | 194.7 | 182.1 |
| 87.5° | 15.7  | 15.7  | 22.0  | 28.3  | 37.7  | 44.0  | 56.5  | 65.9  | 69.1  | 69.1  | 53.4  |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

REPORT NUMBER: P561231

CATALOG NUMBER: SDL-PA1-90-727-U-T4W

**CANDELA DISTRIBUTION (continued):**

|       | 165°  | 170°  | 175°  | 180°  |
|-------|-------|-------|-------|-------|
| 0°    | 989.1 | 989.1 | 989.1 | 989.1 |
| 2.5°  | 866.6 | 866.6 | 863.5 | 869.8 |
| 5°    | 832.1 | 835.2 | 835.2 | 838.4 |
| 7.5°  | 775.6 | 759.9 | 741.0 | 744.2 |
| 10°   | 863.5 | 866.6 | 869.8 | 869.8 |
| 12.5° | 775.6 | 763.0 | 747.3 | 750.5 |
| 15°   | 841.5 | 850.9 | 860.3 | 863.5 |
| 17.5° | 741.0 | 737.9 | 734.8 | 731.6 |
| 20°   | 828.9 | 844.6 | 860.3 | 860.3 |
| 22.5° | 712.8 | 712.8 | 712.8 | 715.9 |
| 25°   | 819.5 | 838.4 | 854.1 | 854.1 |
| 27.5° | 693.9 | 737.9 | 781.8 | 816.4 |
| 30°   | 838.4 | 847.8 | 857.2 | 860.3 |
| 32.5° | 888.6 | 935.7 | 979.7 | 989.1 |
| 35°   | 901.2 | 923.1 | 942.0 | 951.4 |
| 37.5° | 825.8 | 844.6 | 863.5 | 876.0 |
| 40°   | 719.1 | 734.8 | 750.5 | 759.9 |
| 42.5° | 612.3 | 615.4 | 618.6 | 634.3 |
| 45°   | 521.2 | 505.5 | 489.8 | 486.7 |
| 47.5° | 436.5 | 414.5 | 392.5 | 389.4 |
| 50°   | 373.7 | 354.8 | 336.0 | 336.0 |
| 52.5° | 329.7 | 317.1 | 304.6 | 304.6 |
| 55°   | 307.7 | 301.4 | 292.0 | 292.0 |
| 57.5° | 304.6 | 301.4 | 298.3 | 298.3 |
| 60°   | 326.6 | 329.7 | 329.7 | 329.7 |
| 62.5° | 367.4 | 370.5 | 370.5 | 370.5 |
| 65°   | 370.5 | 364.2 | 358.0 | 358.0 |
| 67.5° | 351.7 | 342.3 | 332.8 | 326.6 |
| 70°   | 332.8 | 326.6 | 317.1 | 307.7 |
| 72.5° | 317.1 | 310.9 | 301.4 | 292.0 |
| 75°   | 301.4 | 292.0 | 279.5 | 273.2 |
| 77.5° | 279.5 | 273.2 | 263.8 | 257.5 |
| 80°   | 254.3 | 248.1 | 238.6 | 226.1 |
| 82.5° | 226.1 | 229.2 | 229.2 | 197.8 |
| 85°   | 166.4 | 157.0 | 144.4 | 119.3 |
| 87.5° | 34.5  | 31.4  | 25.1  | 22.0  |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   |



Report Generated By 670245982









--- HS --- SS

u











(END OF REPORT)