

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560532

Luminaire Tested: **SDL-PA1-50-730-U-SL3-HSS**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560532  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-50-730-U-SL3-HSS  
Description: Springdale  
(1) 70 CRI, 3000K, 670mA LIGHT ENGINE WITH 24 LEDS AND TYPE III SPILL  
LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4892.6 lumens  
Efficiency: N/A  
Efficacy: 93.4 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type IV - Medium  
BUG Rating: B1 - U0 - G2

Input Watts (W): 52.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P560532

CATALOG NUMBER: SDL-PA1-50-730-U-SL3-HSS

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 13.9 fc  
Type IV - Medium - N/A

REPORT NUMBER: P560532

CATALOG NUMBER: SDL-PA1-50-730-U-SL3-HSS

## Luminous Intensity Polar Plot



— Vertical Plane Through 60-Deg Lateral      - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P560532

CATALOG NUMBER: SDL-PA1-50-730-U-SL3-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 398.6    | 0.0    | 398.6  |
|                    | % Fixture | 8.1      | 0.0    | 8.1    |
| <b>Street Side</b> | Lumens    | 4494.0   | 0.0    | 4494.0 |
|                    | % Fixture | 91.9     | 0.0    | 91.9   |
| <b>Total</b>       | Lumens    | 4892.6   | 0.0    | 4892.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 96.4   | 2.0       |
| 10°-20°   | 160.1  | 3.3       |
| 20°-30°   | 229.3  | 4.7       |
| 30°-40°   | 408.3  | 8.3       |
| 40°-50°   | 672.1  | 13.7      |
| 50°-60°   | 1036.4 | 21.2      |
| 60°-70°   | 1207.8 | 24.7      |
| 70°-80°   | 936.0  | 19.1      |
| 80°-90°   | 146.2  | 3.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4892.6 | 100.0     |
| 0°-180°   | 4892.6 | 100.0     |



REPORT NUMBER: P560532


CATALOG NUMBER: SDL-PA1-50-730-U-SL3-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 367.1  | 7.5       |                         |      |         |
| FM   | (30°-60°)   | 1959.0 | 40.0      |                         |      |         |
| FH   | (60°-80°)   | 2025.8 | 41.4      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 142.1  | 2.9       |                         |      | G2/225  |
| BL   | (0°-30°)    | 118.8  | 2.4       | B1/500                  |      |         |
| BM   | (30°-60°)   | 157.8  | 3.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 117.9  | 2.4       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 4.0    | 0.1       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type IV Medium



REPORT NUMBER: P560532

CATALOG NUMBER: SDL-PA1-50-730-U-SL3-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    | 50°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 |
| 2.5°  | 1302.8 | 1351.7 | 1381.4 | 1409.1 | 1445.2 | 1481.3 | 1483.4 | 1485.6 | 1485.6 | 1485.6 | 1483.4 |
| 5°    | 1258.2 | 1262.4 | 1262.4 | 1262.4 | 1268.8 | 1275.2 | 1279.4 | 1281.5 | 1283.7 | 1283.7 | 1281.5 |
| 7.5°  | 984.0  | 1062.6 | 1111.5 | 1158.3 | 1171.0 | 1183.8 | 1200.8 | 1215.7 | 1228.4 | 1239.0 | 1247.5 |
| 10°   | 1090.3 | 1098.8 | 1098.8 | 1096.6 | 1107.3 | 1115.8 | 1032.9 | 947.9  | 981.9  | 1015.9 | 973.4  |
| 12.5° | 841.6  | 884.1  | 937.2  | 988.3  | 1022.3 | 1056.3 | 1018.0 | 979.8  | 920.2  | 858.6  | 854.4  |
| 15°   | 984.0  | 990.4  | 992.5  | 994.6  | 937.2  | 877.7  | 807.6  | 735.3  | 784.2  | 833.1  | 763.0  |
| 17.5° | 756.6  | 763.0  | 822.5  | 882.0  | 888.4  | 894.7  | 850.1  | 803.4  | 701.3  | 599.3  | 695.0  |
| 20°   | 905.4  | 909.6  | 909.6  | 909.6  | 797.0  | 684.3  | 692.8  | 699.2  | 731.1  | 763.0  | 739.6  |
| 22.5° | 729.0  | 720.5  | 724.7  | 726.8  | 760.8  | 792.7  | 726.8  | 658.8  | 707.7  | 754.5  | 714.1  |
| 25°   | 911.7  | 913.9  | 901.1  | 886.2  | 786.4  | 684.3  | 720.5  | 754.5  | 697.1  | 637.6  | 695.0  |
| 27.5° | 824.6  | 816.1  | 786.4  | 756.6  | 771.5  | 786.4  | 718.3  | 648.2  | 703.5  | 756.6  | 731.1  |
| 30°   | 1086.0 | 1081.8 | 1043.5 | 1003.1 | 884.1  | 763.0  | 750.2  | 735.3  | 703.5  | 669.5  | 714.1  |
| 32.5° | 1449.4 | 1398.4 | 1256.0 | 1111.5 | 1037.1 | 960.6  | 867.1  | 773.6  | 784.2  | 792.7  | 799.1  |
| 35°   | 1530.2 | 1506.8 | 1445.2 | 1383.6 | 1268.8 | 1151.9 | 1024.4 | 894.7  | 865.0  | 835.2  | 852.2  |
| 37.5° | 1551.4 | 1542.9 | 1534.4 | 1523.8 | 1387.8 | 1251.8 | 1124.3 | 994.6  | 971.2  | 945.7  | 926.6  |
| 40°   | 1572.7 | 1581.2 | 1606.7 | 1630.1 | 1502.6 | 1375.1 | 1256.0 | 1134.9 | 1107.3 | 1079.6 | 1030.8 |
| 42.5° | 1657.7 | 1664.1 | 1702.3 | 1740.6 | 1617.3 | 1491.9 | 1387.8 | 1283.7 | 1243.3 | 1202.9 | 1158.3 |
| 45°   | 1838.4 | 1844.7 | 1866.0 | 1887.2 | 1772.5 | 1655.6 | 1540.8 | 1423.9 | 1392.1 | 1358.0 | 1307.0 |
| 47.5° | 2089.1 | 2095.5 | 2084.9 | 2074.3 | 1942.5 | 1808.6 | 1672.6 | 1536.6 | 1525.9 | 1515.3 | 1462.2 |
| 50°   | 2376.1 | 2367.6 | 2310.2 | 2252.8 | 2108.3 | 1963.8 | 1804.4 | 1642.8 | 1651.3 | 1659.8 | 1621.6 |
| 52.5° | 2507.8 | 2503.6 | 2437.7 | 2371.8 | 2223.0 | 2072.1 | 1906.4 | 1738.5 | 1768.2 | 1795.9 | 1774.6 |
| 55°   | 2499.3 | 2497.2 | 2452.6 | 2407.9 | 2267.7 | 2127.4 | 1972.3 | 1817.1 | 1885.1 | 1951.0 | 1938.2 |
| 57.5° | 2405.8 | 2410.1 | 2403.7 | 2397.3 | 2274.0 | 2150.8 | 2025.4 | 1900.0 | 2002.0 | 2101.9 | 2118.9 |
| 60°   | 2259.2 | 2259.2 | 2291.0 | 2320.8 | 2248.5 | 2174.2 | 2070.0 | 1963.8 | 2104.0 | 2244.3 | 2286.8 |
| 62.5° | 1953.1 | 1987.1 | 2055.1 | 2123.1 | 2146.5 | 2169.9 | 2084.9 | 1999.9 | 2193.3 | 2386.7 | 2448.3 |
| 65°   | 1504.7 | 1519.6 | 1642.8 | 1766.1 | 1880.9 | 1993.5 | 1999.9 | 2006.3 | 2301.7 | 2595.0 | 2616.2 |
| 67.5° | 873.5  | 935.1  | 1071.1 | 1205.0 | 1430.3 | 1653.5 | 1768.2 | 1883.0 | 2348.4 | 2811.7 | 2835.1 |
| 70°   | 459.1  | 484.6  | 550.4  | 614.2  | 816.1  | 1015.9 | 1300.7 | 1583.3 | 2240.0 | 2894.6 | 3098.6 |
| 72.5° | 314.5  | 337.9  | 374.0  | 410.2  | 486.7  | 561.1  | 765.1  | 967.0  | 1783.1 | 2599.2 | 3232.5 |
| 75°   | 184.9  | 191.3  | 235.9  | 280.5  | 363.4  | 446.3  | 520.7  | 593.0  | 1134.9 | 1674.7 | 2701.2 |
| 77.5° | 74.4   | 80.8   | 99.9   | 119.0  | 235.9  | 350.7  | 427.2  | 503.7  | 633.3  | 763.0  | 1855.4 |
| 80°   | 40.4   | 40.4   | 48.9   | 55.3   | 106.3  | 155.1  | 286.9  | 418.7  | 482.4  | 546.2  | 1202.9 |
| 82.5° | 23.4   | 23.4   | 29.8   | 34.0   | 53.1   | 72.3   | 163.6  | 255.0  | 376.2  | 495.2  | 811.9  |
| 85°   | 8.5    | 8.5    | 10.6   | 12.8   | 25.5   | 36.1   | 59.5   | 80.8   | 233.8  | 384.7  | 467.6  |
| 87.5° | 2.1    | 2.1    | 4.3    | 4.3    | 6.4    | 8.5    | 10.6   | 10.6   | 8.5    | 6.4    | 42.5   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560532

CATALOG NUMBER: SDL-PA1-50-730-U-SL3-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   | 105°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 |
| 2.5°  | 1479.2 | 1466.4 | 1457.9 | 1443.1 | 1428.2 | 1415.4 | 1400.6 | 1381.4 | 1366.6 | 1347.4 | 1328.3 |
| 5°    | 1279.4 | 1368.7 | 1460.1 | 1451.6 | 1440.9 | 1411.2 | 1381.4 | 1347.4 | 1315.5 | 1277.3 | 1239.0 |
| 7.5°  | 1253.9 | 1251.8 | 1164.6 | 1209.3 | 1251.8 | 1217.8 | 1183.8 | 1145.5 | 1103.0 | 1028.6 | 954.2  |
| 10°   | 930.9  | 937.2  | 935.1  | 945.7  | 956.4  | 984.0  | 1009.5 | 954.2  | 901.1  | 784.2  | 665.2  |
| 12.5° | 850.1  | 890.5  | 901.1  | 828.9  | 756.6  | 786.4  | 816.1  | 760.8  | 707.7  | 599.3  | 490.9  |
| 15°   | 690.7  | 586.6  | 735.3  | 833.1  | 928.7  | 943.6  | 956.4  | 884.1  | 799.1  | 650.3  | 499.4  |
| 17.5° | 788.5  | 824.6  | 782.1  | 784.2  | 784.2  | 786.4  | 788.5  | 722.6  | 637.6  | 524.9  | 412.3  |
| 20°   | 716.2  | 705.6  | 709.8  | 780.0  | 850.1  | 896.9  | 941.5  | 841.6  | 733.2  | 558.9  | 382.5  |
| 22.5° | 673.7  | 811.9  | 871.4  | 841.6  | 811.9  | 737.5  | 661.0  | 584.5  | 495.2  | 408.1  | 318.8  |
| 25°   | 750.2  | 678.0  | 724.7  | 839.5  | 954.2  | 954.2  | 954.2  | 822.5  | 675.8  | 488.8  | 301.8  |
| 27.5° | 705.6  | 805.5  | 852.2  | 943.6  | 1032.9 | 1071.1 | 1107.3 | 939.4  | 746.0  | 514.3  | 280.5  |
| 30°   | 758.7  | 805.5  | 971.2  | 1154.0 | 1336.8 | 1304.9 | 1270.9 | 1056.3 | 811.9  | 539.8  | 267.8  |
| 32.5° | 805.5  | 937.2  | 1083.9 | 1222.0 | 1360.2 | 1324.0 | 1285.8 | 1047.8 | 773.6  | 486.7  | 199.8  |
| 35°   | 869.2  | 954.2  | 1090.3 | 1258.2 | 1426.1 | 1370.8 | 1313.4 | 1052.0 | 743.8  | 446.3  | 148.8  |
| 37.5° | 907.5  | 1001.0 | 1147.6 | 1324.0 | 1498.3 | 1430.3 | 1362.3 | 1071.1 | 718.3  | 416.6  | 114.8  |
| 40°   | 979.8  | 1073.3 | 1219.9 | 1404.8 | 1589.7 | 1511.1 | 1430.3 | 1105.1 | 703.5  | 399.6  | 95.6   |
| 42.5° | 1113.6 | 1156.1 | 1319.8 | 1515.3 | 1710.8 | 1628.0 | 1542.9 | 1177.4 | 699.2  | 391.1  | 82.9   |
| 45°   | 1253.9 | 1281.5 | 1426.1 | 1645.0 | 1861.7 | 1776.7 | 1689.6 | 1266.7 | 714.1  | 397.4  | 78.6   |
| 47.5° | 1406.9 | 1421.8 | 1553.6 | 1825.6 | 2097.6 | 1980.8 | 1863.9 | 1389.9 | 746.0  | 410.2  | 74.4   |
| 50°   | 1583.3 | 1583.3 | 1710.8 | 2004.1 | 2297.4 | 2176.3 | 2055.1 | 1534.4 | 786.4  | 429.3  | 72.3   |
| 52.5° | 1751.2 | 1774.6 | 1872.4 | 2172.0 | 2471.7 | 2359.1 | 2244.3 | 1693.8 | 839.5  | 454.8  | 68.0   |
| 55°   | 1923.4 | 1997.8 | 2033.9 | 2339.9 | 2646.0 | 2516.3 | 2386.7 | 1810.7 | 871.4  | 467.6  | 63.8   |
| 57.5° | 2135.9 | 2214.5 | 2233.7 | 2492.9 | 2752.2 | 2626.8 | 2499.3 | 1910.6 | 894.7  | 478.2  | 61.6   |
| 60°   | 2329.3 | 2418.6 | 2456.8 | 2648.1 | 2837.2 | 2707.6 | 2578.0 | 1997.8 | 916.0  | 486.7  | 55.3   |
| 62.5° | 2507.8 | 2575.8 | 2635.3 | 2758.6 | 2881.9 | 2760.7 | 2637.5 | 2074.3 | 928.7  | 488.8  | 48.9   |
| 65°   | 2637.5 | 2699.1 | 2784.1 | 2854.2 | 2924.4 | 2833.0 | 2741.6 | 2206.0 | 964.9  | 501.6  | 36.1   |
| 67.5° | 2856.4 | 2862.7 | 2911.6 | 2969.0 | 3026.4 | 2977.5 | 2928.6 | 2388.8 | 1007.4 | 518.6  | 27.6   |
| 70°   | 3300.5 | 3228.3 | 3164.5 | 3221.9 | 3277.2 | 3209.2 | 3141.2 | 2441.9 | 909.6  | 465.4  | 21.3   |
| 72.5° | 3865.9 | 3987.0 | 3678.8 | 3559.8 | 3438.7 | 3187.9 | 2935.0 | 2101.9 | 646.1  | 331.5  | 17.0   |
| 75°   | 3727.7 | 4341.9 | 4038.0 | 3559.8 | 3081.6 | 2694.8 | 2305.9 | 1577.0 | 397.4  | 206.2  | 12.8   |
| 77.5° | 2945.6 | 3604.5 | 3496.1 | 3003.0 | 2507.8 | 2031.8 | 1555.7 | 969.1  | 140.3  | 76.5   | 12.8   |
| 80°   | 1859.6 | 2492.9 | 2399.4 | 1951.0 | 1500.4 | 1066.9 | 633.3  | 295.4  | 53.1   | 34.0   | 14.9   |
| 82.5° | 1128.5 | 1485.6 | 1166.8 | 731.1  | 295.4  | 208.3  | 121.1  | 63.8   | 17.0   | 14.9   | 12.8   |
| 85°   | 548.3  | 614.2  | 401.7  | 231.7  | 59.5   | 55.3   | 48.9   | 31.9   | 8.5    | 8.5    | 6.4    |
| 87.5° | 76.5   | 55.3   | 34.0   | 23.4   | 10.6   | 10.6   | 10.6   | 6.4    | 6.4    | 6.4    | 4.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P560532

CATALOG NUMBER: SDL-PA1-50-730-U-SL3-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   | 160°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 | 1394.2 |
| 2.5°  | 1313.4 | 1296.4 | 1277.3 | 1258.2 | 1236.9 | 1215.7 | 1154.0 | 1090.3 | 1056.3 | 1020.1 | 1011.6 |
| 5°    | 1168.9 | 1098.8 | 1011.6 | 922.4  | 884.1  | 845.9  | 826.7  | 805.5  | 792.7  | 777.9  | 765.1  |
| 7.5°  | 856.5  | 756.6  | 756.6  | 754.5  | 722.6  | 690.7  | 654.6  | 616.3  | 593.0  | 569.6  | 507.9  |
| 10°   | 612.1  | 556.8  | 518.6  | 480.3  | 465.4  | 450.6  | 403.8  | 354.9  | 359.2  | 361.3  | 348.5  |
| 12.5° | 473.9  | 454.8  | 384.7  | 314.5  | 291.2  | 267.8  | 252.9  | 238.0  | 216.8  | 195.5  | 180.6  |
| 15°   | 405.9  | 312.4  | 259.3  | 206.2  | 182.8  | 157.3  | 136.0  | 112.6  | 106.3  | 97.8   | 108.4  |
| 17.5° | 333.7  | 252.9  | 201.9  | 150.9  | 116.9  | 82.9   | 87.1   | 91.4   | 99.9   | 108.4  | 112.6  |
| 20°   | 286.9  | 191.3  | 146.6  | 102.0  | 91.4   | 80.8   | 85.0   | 87.1   | 85.0   | 80.8   | 93.5   |
| 22.5° | 233.8  | 148.8  | 112.6  | 74.4   | 76.5   | 78.6   | 72.3   | 65.9   | 78.6   | 91.4   | 91.4   |
| 25°   | 199.8  | 97.8   | 87.1   | 76.5   | 70.1   | 63.8   | 72.3   | 78.6   | 74.4   | 70.1   | 80.8   |
| 27.5° | 182.8  | 85.0   | 74.4   | 63.8   | 65.9   | 68.0   | 65.9   | 61.6   | 68.0   | 74.4   | 72.3   |
| 30°   | 174.3  | 78.6   | 72.3   | 63.8   | 61.6   | 57.4   | 59.5   | 59.5   | 57.4   | 55.3   | 61.6   |
| 32.5° | 140.3  | 80.8   | 70.1   | 57.4   | 55.3   | 51.0   | 48.9   | 46.8   | 48.9   | 51.0   | 53.1   |
| 35°   | 112.6  | 74.4   | 65.9   | 55.3   | 51.0   | 46.8   | 44.6   | 40.4   | 40.4   | 40.4   | 42.5   |
| 37.5° | 91.4   | 68.0   | 59.5   | 48.9   | 44.6   | 40.4   | 38.3   | 34.0   | 34.0   | 34.0   | 34.0   |
| 40°   | 80.8   | 63.8   | 55.3   | 44.6   | 40.4   | 34.0   | 31.9   | 27.6   | 27.6   | 25.5   | 25.5   |
| 42.5° | 70.1   | 57.4   | 48.9   | 38.3   | 34.0   | 29.8   | 25.5   | 21.3   | 21.3   | 19.1   | 19.1   |
| 45°   | 65.9   | 53.1   | 44.6   | 36.1   | 29.8   | 23.4   | 21.3   | 17.0   | 17.0   | 14.9   | 14.9   |
| 47.5° | 63.8   | 51.0   | 42.5   | 31.9   | 25.5   | 19.1   | 17.0   | 12.8   | 12.8   | 12.8   | 12.8   |
| 50°   | 59.5   | 46.8   | 38.3   | 27.6   | 23.4   | 17.0   | 14.9   | 10.6   | 10.6   | 10.6   | 10.6   |
| 52.5° | 57.4   | 44.6   | 34.0   | 23.4   | 19.1   | 12.8   | 10.6   | 8.5    | 8.5    | 8.5    | 8.5    |
| 55°   | 55.3   | 46.8   | 34.0   | 21.3   | 17.0   | 10.6   | 8.5    | 6.4    | 6.4    | 6.4    | 6.4    |
| 57.5° | 53.1   | 44.6   | 31.9   | 17.0   | 12.8   | 8.5    | 6.4    | 4.3    | 4.3    | 4.3    | 4.3    |
| 60°   | 46.8   | 38.3   | 25.5   | 12.8   | 10.6   | 6.4    | 4.3    | 2.1    | 4.3    | 4.3    | 4.3    |
| 62.5° | 40.4   | 29.8   | 21.3   | 10.6   | 8.5    | 4.3    | 4.3    | 2.1    | 4.3    | 4.3    | 4.3    |
| 65°   | 29.8   | 23.4   | 17.0   | 8.5    | 6.4    | 2.1    | 2.1    | 2.1    | 4.3    | 4.3    | 4.3    |
| 67.5° | 23.4   | 17.0   | 12.8   | 6.4    | 4.3    | 2.1    | 2.1    | 2.1    | 4.3    | 4.3    | 4.3    |
| 70°   | 17.0   | 12.8   | 8.5    | 4.3    | 4.3    | 2.1    | 2.1    | 2.1    | 4.3    | 4.3    | 4.3    |
| 72.5° | 12.8   | 8.5    | 6.4    | 4.3    | 4.3    | 2.1    | 4.3    | 4.3    | 4.3    | 4.3    | 4.3    |
| 75°   | 10.6   | 8.5    | 6.4    | 4.3    | 4.3    | 2.1    | 4.3    | 4.3    | 6.4    | 6.4    | 6.4    |
| 77.5° | 10.6   | 6.4    | 6.4    | 4.3    | 4.3    | 2.1    | 4.3    | 6.4    | 6.4    | 6.4    | 6.4    |
| 80°   | 10.6   | 6.4    | 6.4    | 4.3    | 4.3    | 2.1    | 4.3    | 6.4    | 6.4    | 6.4    | 6.4    |
| 82.5° | 10.6   | 6.4    | 6.4    | 4.3    | 4.3    | 2.1    | 4.3    | 6.4    | 6.4    | 6.4    | 6.4    |
| 85°   | 6.4    | 6.4    | 6.4    | 6.4    | 4.3    | 2.1    | 6.4    | 8.5    | 8.5    | 6.4    | 6.4    |
| 87.5° | 4.3    | 4.3    | 6.4    | 6.4    | 4.3    | 2.1    | 6.4    | 8.5    | 8.5    | 6.4    | 6.4    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560532

CATALOG NUMBER: SDL-PA1-50-730-U-SL3-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 165°   | 170°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|
| 0°    | 1394.2 | 1394.2 | 1394.2 | 1394.2 |
| 2.5°  | 1001.0 | 990.4  | 977.6  | 1003.1 |
| 5°    | 752.3  | 743.8  | 735.3  | 750.2  |
| 7.5°  | 446.3  | 448.4  | 448.4  | 425.1  |
| 10°   | 333.7  | 314.5  | 293.3  | 293.3  |
| 12.5° | 165.8  | 153.0  | 140.3  | 138.1  |
| 15°   | 119.0  | 121.1  | 123.3  | 123.3  |
| 17.5° | 116.9  | 112.6  | 106.3  | 102.0  |
| 20°   | 104.1  | 108.4  | 110.5  | 110.5  |
| 22.5° | 91.4   | 89.3   | 85.0   | 85.0   |
| 25°   | 91.4   | 93.5   | 95.6   | 95.6   |
| 27.5° | 70.1   | 70.1   | 68.0   | 68.0   |
| 30°   | 68.0   | 68.0   | 68.0   | 68.0   |
| 32.5° | 53.1   | 55.3   | 55.3   | 55.3   |
| 35°   | 44.6   | 44.6   | 44.6   | 44.6   |
| 37.5° | 34.0   | 34.0   | 34.0   | 31.9   |
| 40°   | 25.5   | 25.5   | 25.5   | 25.5   |
| 42.5° | 19.1   | 19.1   | 19.1   | 19.1   |
| 45°   | 14.9   | 14.9   | 14.9   | 14.9   |
| 47.5° | 12.8   | 12.8   | 10.6   | 10.6   |
| 50°   | 8.5    | 8.5    | 8.5    | 8.5    |
| 52.5° | 6.4    | 6.4    | 6.4    | 6.4    |
| 55°   | 4.3    | 4.3    | 4.3    | 4.3    |
| 57.5° | 4.3    | 4.3    | 4.3    | 4.3    |
| 60°   | 2.1    | 2.1    | 2.1    | 2.1    |
| 62.5° | 2.1    | 2.1    | 2.1    | 2.1    |
| 65°   | 2.1    | 2.1    | 2.1    | 2.1    |
| 67.5° | 2.1    | 2.1    | 2.1    | 2.1    |
| 70°   | 2.1    | 2.1    | 2.1    | 2.1    |
| 72.5° | 4.3    | 4.3    | 2.1    | 2.1    |
| 75°   | 4.3    | 4.3    | 2.1    | 2.1    |
| 77.5° | 4.3    | 4.3    | 2.1    | 2.1    |
| 80°   | 4.3    | 4.3    | 2.1    | 2.1    |
| 82.5° | 4.3    | 4.3    | 2.1    | 2.1    |
| 85°   | 4.3    | 4.3    | 4.3    | 2.1    |
| 87.5° | 4.3    | 4.3    | 4.3    | 2.1    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    |



Report Generated By 670245982









--- HS --- SS



u











(END OF REPORT)