

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P559881

Luminaire Tested: **SDL-PA1-100-750-U-T2U**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P559881  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-100-750-U-T2U  
Description: Springdale  
(1) 70 CRI, 5000K, 1200mA LIGHT ENGINE WITH 24 LEDS AND TYPE II U OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10440.1 lumens  
Efficiency: N/A  
Efficacy: 111.3 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type II - Medium  
BUG Rating: B3 - U0 - G3

Input Watts (W): 93.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P559881

CATALOG NUMBER: SDL-PA1-100-750-U-T2U

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 4.7 fc

Type II - Medium - N/A

REPORT NUMBER: P559881

CATALOG NUMBER: SDL-PA1-100-750-U-T2U

## Luminous Intensity Polar Plot



REPORT NUMBER: P559881

CATALOG NUMBER: SDL-PA1-100-750-U-T2U


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 3061.6   | 0.0    | 3061.6  |
|                    | % Fixture | 29.3     | 0.0    | 29.3    |
| <b>Street Side</b> | Lumens    | 7378.5   | 0.0    | 7378.5  |
|                    | % Fixture | 70.7     | 0.0    | 70.7    |
| <b>Total</b>       | Lumens    | 10440.1  | 0.0    | 10440.1 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 116.5   | 1.1       |
| 10°-20°   | 273.4   | 2.6       |
| 20°-30°   | 485.6   | 4.7       |
| 30°-40°   | 1026.6  | 9.8       |
| 40°-50°   | 1879.4  | 18.0      |
| 50°-60°   | 2563.9  | 24.6      |
| 60°-70°   | 2417.1  | 23.2      |
| 70°-80°   | 1462.8  | 14.0      |
| 80°-90°   | 214.9   | 2.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 10440.1 | 100.0     |
| 0°-180°   | 10440.1 | 100.0     |



REPORT NUMBER: P559881


CATALOG NUMBER: SDL-PA1-100-750-U-T2U

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 444.3  | 4.3       |                         |      |         |
| FM   | (30°-60°)   | 4138.9 | 39.6      |                         |      |         |
| FH   | (60°-80°)   | 2663.5 | 25.5      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 131.8  | 1.3       |                         |      | G2/225  |
| BL   | (0°-30°)    | 431.2  | 4.1       | B1/500                  |      |         |
| BM   | (30°-60°)   | 1330.9 | 12.7      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 1216.3 | 11.7      | B3/2500                 |      | G3/2500 |
| BVH  | (80°-90°)   | 83.1   | 0.8       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G3**

Type II Medium



REPORT NUMBER: P559881

CATALOG NUMBER: SDL-PA1-100-750-U-T2U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    | 50°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 |
| 2.5°  | 1220.8 | 1232.0 | 1307.2 | 1382.3 | 1386.0 | 1386.0 | 1389.8 | 1393.5 | 1404.8 | 1412.3 | 1419.8 |
| 5°    | 1138.1 | 1145.6 | 1145.6 | 1145.6 | 1149.4 | 1153.2 | 1156.9 | 1156.9 | 1164.4 | 1168.2 | 1175.7 |
| 7.5°  | 954.1  | 1029.2 | 1055.5 | 1078.0 | 1093.1 | 1104.3 | 1111.8 | 1119.3 | 1126.9 | 1134.4 | 1141.9 |
| 10°   | 1085.5 | 1085.5 | 1089.3 | 1089.3 | 1089.3 | 1085.5 | 1010.4 | 931.5  | 969.1  | 1006.7 | 950.3  |
| 12.5° | 894.0  | 909.0  | 976.6  | 1040.5 | 1059.2 | 1074.3 | 1036.7 | 995.4  | 927.8  | 860.2  | 852.7  |
| 15°   | 1063.0 | 1063.0 | 1063.0 | 1059.2 | 991.6  | 920.3  | 848.9  | 773.8  | 818.9  | 863.9  | 796.3  |
| 17.5° | 920.3  | 920.3  | 976.6  | 1029.2 | 1025.4 | 1017.9 | 954.1  | 886.5  | 781.3  | 672.4  | 758.8  |
| 20°   | 1160.7 | 1156.9 | 1138.1 | 1115.6 | 976.6  | 837.6  | 867.7  | 897.7  | 905.2  | 909.0  | 882.7  |
| 22.5° | 1036.7 | 1040.5 | 1063.0 | 1085.5 | 1089.3 | 1093.1 | 931.5  | 766.3  | 860.2  | 954.1  | 863.9  |
| 25°   | 1442.4 | 1434.9 | 1401.1 | 1363.5 | 1209.5 | 1051.7 | 1081.8 | 1111.8 | 957.8  | 800.1  | 897.7  |
| 27.5° | 1371.0 | 1348.5 | 1333.4 | 1318.4 | 1344.7 | 1371.0 | 1228.3 | 1081.8 | 1115.6 | 1149.4 | 1025.4 |
| 30°   | 1960.7 | 1960.7 | 1923.2 | 1881.9 | 1649.0 | 1412.3 | 1374.8 | 1337.2 | 1247.1 | 1153.2 | 1175.7 |
| 32.5° | 2482.8 | 2482.8 | 2343.9 | 2201.1 | 2062.2 | 1923.2 | 1739.1 | 1555.1 | 1517.5 | 1476.2 | 1438.6 |
| 35°   | 3125.2 | 3106.4 | 3027.5 | 2944.9 | 2644.4 | 2343.9 | 2107.2 | 1870.6 | 1795.5 | 1720.3 | 1682.8 |
| 37.5° | 3726.1 | 3684.8 | 3575.9 | 3463.2 | 3147.7 | 2828.4 | 2516.7 | 2204.9 | 2122.3 | 2039.6 | 1957.0 |
| 40°   | 4222.0 | 4199.4 | 4124.3 | 4045.4 | 3688.6 | 3331.7 | 2978.7 | 2621.8 | 2512.9 | 2404.0 | 2283.8 |
| 42.5° | 4676.5 | 4657.7 | 4590.1 | 4518.7 | 4165.6 | 3808.8 | 3474.5 | 3136.4 | 2974.9 | 2813.4 | 2670.7 |
| 45°   | 5010.8 | 4980.7 | 4935.6 | 4886.8 | 4605.1 | 4319.6 | 3981.6 | 3639.8 | 3575.9 | 3512.0 | 3234.1 |
| 47.5° | 5115.9 | 5063.4 | 5055.8 | 5048.3 | 4823.0 | 4597.6 | 4327.1 | 4056.7 | 4068.0 | 4079.2 | 3756.2 |
| 50°   | 4961.9 | 4883.1 | 4916.9 | 4950.7 | 4860.5 | 4766.6 | 4556.3 | 4345.9 | 4439.8 | 4530.0 | 4274.5 |
| 52.5° | 4402.3 | 4383.5 | 4469.9 | 4552.5 | 4575.0 | 4597.6 | 4552.5 | 4503.7 | 4676.5 | 4849.2 | 4755.3 |
| 55°   | 3632.2 | 3714.9 | 3835.1 | 3955.3 | 4049.2 | 4139.3 | 4270.8 | 4402.3 | 4699.0 | 4995.7 | 5063.4 |
| 57.5° | 2862.2 | 2948.6 | 3087.6 | 3226.6 | 3335.5 | 3444.4 | 3714.9 | 3985.3 | 4432.3 | 4879.3 | 5183.5 |
| 60°   | 1926.9 | 2017.1 | 2246.2 | 2471.6 | 2625.6 | 2779.6 | 3023.7 | 3267.9 | 3831.3 | 4394.7 | 5010.8 |
| 62.5° | 1284.6 | 1254.6 | 1446.1 | 1633.9 | 1881.9 | 2129.8 | 2238.7 | 2343.9 | 2933.6 | 3519.6 | 4514.9 |
| 65°   | 788.8  | 792.6  | 867.7  | 939.0  | 1213.3 | 1483.7 | 1570.1 | 1652.7 | 1987.0 | 2321.3 | 3677.3 |
| 67.5° | 529.6  | 540.9  | 574.7  | 608.5  | 740.0  | 871.4  | 1021.7 | 1171.9 | 1250.8 | 1325.9 | 2681.9 |
| 70°   | 469.5  | 473.3  | 488.3  | 503.3  | 540.9  | 578.5  | 717.4  | 856.4  | 811.3  | 762.5  | 1521.3 |
| 72.5° | 413.2  | 416.9  | 443.2  | 465.8  | 484.5  | 503.3  | 586.0  | 668.6  | 616.0  | 563.4  | 758.8  |
| 75°   | 338.1  | 349.3  | 375.6  | 398.2  | 435.7  | 469.5  | 488.3  | 507.1  | 480.8  | 450.7  | 488.3  |
| 77.5° | 278.0  | 285.5  | 304.3  | 323.0  | 360.6  | 394.4  | 413.2  | 432.0  | 390.6  | 349.3  | 371.9  |
| 80°   | 217.9  | 221.6  | 236.6  | 251.7  | 281.7  | 308.0  | 330.5  | 349.3  | 311.8  | 270.4  | 281.7  |
| 82.5° | 131.5  | 135.2  | 157.8  | 176.5  | 202.8  | 225.4  | 240.4  | 251.7  | 262.9  | 270.4  | 236.6  |
| 85°   | 71.4   | 71.4   | 86.4   | 101.4  | 105.2  | 108.9  | 124.0  | 135.2  | 169.0  | 199.1  | 172.8  |
| 87.5° | 11.3   | 11.3   | 15.0   | 15.0   | 22.5   | 26.3   | 30.0   | 30.0   | 33.8   | 33.8   | 37.6   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P559881

CATALOG NUMBER: SDL-PA1-100-750-U-T2U

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   | 105°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 |
| 2.5°  | 1423.6 | 1427.4 | 1427.4 | 1427.4 | 1431.1 | 1434.9 | 1438.6 | 1438.6 | 1442.4 | 1446.1 | 1449.9 |
| 5°    | 1183.2 | 1280.9 | 1374.8 | 1389.8 | 1401.1 | 1408.6 | 1416.1 | 1419.8 | 1427.4 | 1434.9 | 1438.6 |
| 7.5°  | 1149.4 | 1149.4 | 1149.4 | 1123.1 | 1220.8 | 1232.0 | 1243.3 | 1250.8 | 1258.3 | 1250.8 | 1239.5 |
| 10°   | 890.2  | 890.2  | 886.5  | 894.0  | 935.3  | 1006.7 | 1074.3 | 1081.8 | 1089.3 | 1029.2 | 965.3  |
| 12.5° | 841.4  | 852.7  | 863.9  | 845.1  | 770.0  | 833.9  | 897.7  | 909.0  | 912.8  | 860.2  | 803.8  |
| 15°   | 724.9  | 728.7  | 732.5  | 758.8  | 912.8  | 976.6  | 1040.5 | 1051.7 | 1063.0 | 1006.7 | 946.6  |
| 17.5° | 841.4  | 815.1  | 785.0  | 856.4  | 796.3  | 837.6  | 875.2  | 785.0  | 867.7  | 852.7  | 837.6  |
| 20°   | 856.4  | 766.3  | 672.4  | 800.1  | 935.3  | 999.1  | 1059.2 | 1066.8 | 1070.5 | 1025.4 | 976.6  |
| 22.5° | 773.8  | 860.2  | 946.6  | 860.2  | 807.6  | 800.1  | 792.6  | 788.8  | 792.6  | 818.9  | 841.4  |
| 25°   | 995.4  | 886.5  | 777.5  | 976.6  | 1100.6 | 1130.6 | 1160.7 | 1145.6 | 1138.1 | 1081.8 | 1025.4 |
| 27.5° | 901.5  | 987.9  | 1070.5 | 1153.2 | 1190.7 | 1232.0 | 1269.6 | 1280.9 | 1220.8 | 1160.7 | 1100.6 |
| 30°   | 1194.5 | 1247.1 | 1295.9 | 1464.9 | 1588.9 | 1626.4 | 1664.0 | 1626.4 | 1603.9 | 1528.8 | 1449.9 |
| 32.5° | 1397.3 | 1502.5 | 1607.7 | 1603.9 | 1720.3 | 1750.4 | 1776.7 | 1727.8 | 1686.5 | 1603.9 | 1517.5 |
| 35°   | 1645.2 | 1712.8 | 1780.4 | 1818.0 | 1934.4 | 1945.7 | 1957.0 | 1893.1 | 1833.0 | 1735.4 | 1637.7 |
| 37.5° | 1874.3 | 1960.7 | 2043.4 | 2137.3 | 2238.7 | 2216.2 | 2189.9 | 2111.0 | 2013.3 | 1938.2 | 1863.1 |
| 40°   | 2159.8 | 2265.0 | 2370.2 | 2490.4 | 2550.5 | 2516.7 | 2479.1 | 2358.9 | 2265.0 | 2186.1 | 2107.2 |
| 42.5° | 2524.2 | 2636.8 | 2745.8 | 2851.0 | 2873.5 | 2835.9 | 2794.6 | 2663.1 | 2520.4 | 2441.5 | 2358.9 |
| 45°   | 2952.4 | 3042.5 | 3132.7 | 3241.6 | 3286.7 | 3219.1 | 3147.7 | 2982.4 | 2813.4 | 2700.7 | 2588.0 |
| 47.5° | 3429.4 | 3470.7 | 3512.0 | 3699.9 | 3760.0 | 3647.3 | 3530.8 | 3350.5 | 3113.9 | 2967.4 | 2817.1 |
| 50°   | 4019.1 | 4007.9 | 3992.8 | 4158.1 | 4297.1 | 4109.3 | 3917.7 | 3707.4 | 3474.5 | 3267.9 | 3057.5 |
| 52.5° | 4661.4 | 4552.5 | 4439.8 | 4661.4 | 4729.0 | 4503.7 | 4278.3 | 4052.9 | 3820.1 | 3553.4 | 3282.9 |
| 55°   | 5131.0 | 5070.9 | 5010.8 | 5168.5 | 5161.0 | 4898.1 | 4631.4 | 4364.7 | 4173.1 | 3816.3 | 3459.5 |
| 57.5° | 5484.0 | 5536.6 | 5585.5 | 5743.2 | 5562.9 | 5262.4 | 4961.9 | 4695.2 | 4530.0 | 4083.0 | 3636.0 |
| 60°   | 5623.0 | 5893.5 | 6160.2 | 6254.1 | 5979.9 | 5641.8 | 5300.0 | 5037.1 | 4898.1 | 4357.2 | 3816.3 |
| 62.5° | 5510.3 | 6107.6 | 6704.8 | 6723.6 | 6363.0 | 5983.6 | 5604.2 | 5390.1 | 5318.8 | 4653.9 | 3985.3 |
| 65°   | 5033.3 | 6017.4 | 6997.8 | 7065.4 | 6659.7 | 6261.6 | 5859.7 | 5701.9 | 5747.0 | 4931.9 | 4113.0 |
| 67.5° | 4034.2 | 5469.0 | 6900.1 | 7121.7 | 6731.1 | 6310.4 | 5889.7 | 5833.4 | 6002.4 | 5067.1 | 4131.8 |
| 70°   | 2280.0 | 4203.2 | 6122.6 | 6738.6 | 6532.0 | 6115.1 | 5694.4 | 5720.7 | 5972.3 | 4992.0 | 4011.6 |
| 72.5° | 950.3  | 2907.3 | 4864.3 | 5829.6 | 6009.9 | 5656.8 | 5300.0 | 5397.7 | 5570.4 | 4638.9 | 3703.6 |
| 75°   | 525.9  | 1855.6 | 3185.3 | 4469.9 | 5025.8 | 4931.9 | 4834.2 | 4943.2 | 4860.5 | 3959.0 | 3057.5 |
| 77.5° | 390.6  | 1002.9 | 1615.2 | 2993.7 | 3782.5 | 3996.6 | 4206.9 | 4259.5 | 3797.5 | 2892.3 | 1987.0 |
| 80°   | 293.0  | 477.0  | 657.3  | 1528.8 | 2028.3 | 2411.5 | 2794.6 | 2558.0 | 2234.9 | 1562.6 | 890.2  |
| 82.5° | 202.8  | 274.2  | 345.6  | 492.1  | 788.8  | 909.0  | 1025.4 | 976.6  | 732.5  | 514.6  | 293.0  |
| 85°   | 142.7  | 180.3  | 217.9  | 270.4  | 338.1  | 270.4  | 202.8  | 165.3  | 191.6  | 176.5  | 161.5  |
| 87.5° | 37.6   | 37.6   | 33.8   | 37.6   | 26.3   | 22.5   | 18.8   | 15.0   | 15.0   | 15.0   | 15.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P559881

CATALOG NUMBER: SDL-PA1-100-750-U-T2U

**CANDELA DISTRIBUTION (continued):**

|       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   | 160°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 | 1453.6 |
| 2.5°  | 1453.6 | 1457.4 | 1457.4 | 1457.4 | 1457.4 | 1453.6 | 1434.9 | 1416.1 | 1371.0 | 1325.9 | 1310.9 |
| 5°    | 1389.8 | 1341.0 | 1303.4 | 1265.8 | 1265.8 | 1265.8 | 1273.4 | 1280.9 | 1284.6 | 1288.4 | 1292.1 |
| 7.5°  | 1239.5 | 1235.8 | 1250.8 | 1265.8 | 1277.1 | 1288.4 | 1295.9 | 1303.4 | 1288.4 | 1273.4 | 1239.5 |
| 10°   | 969.1  | 969.1  | 987.9  | 1002.9 | 1029.2 | 1055.5 | 1130.6 | 1205.7 | 1269.6 | 1333.4 | 1344.7 |
| 12.5° | 878.9  | 950.3  | 909.0  | 863.9  | 957.8  | 1051.7 | 1134.4 | 1213.3 | 1277.1 | 1337.2 | 1288.4 |
| 15°   | 882.7  | 815.1  | 830.1  | 845.1  | 946.6  | 1048.0 | 972.9  | 894.0  | 1044.2 | 1190.7 | 1224.5 |
| 17.5° | 841.4  | 845.1  | 912.8  | 980.4  | 878.9  | 773.8  | 905.2  | 1036.7 | 1093.1 | 1145.6 | 1096.8 |
| 20°   | 863.9  | 747.5  | 826.4  | 905.2  | 976.6  | 1044.2 | 976.6  | 905.2  | 924.0  | 942.8  | 1070.5 |
| 22.5° | 912.8  | 984.1  | 916.5  | 848.9  | 931.5  | 1010.4 | 976.6  | 942.8  | 1002.9 | 1059.2 | 1006.7 |
| 25°   | 909.0  | 788.8  | 901.5  | 1014.2 | 939.0  | 860.2  | 901.5  | 942.8  | 912.8  | 878.9  | 976.6  |
| 27.5° | 1048.0 | 995.4  | 965.3  | 931.5  | 972.9  | 1014.2 | 927.8  | 841.4  | 841.4  | 841.4  | 830.1  |
| 30°   | 1310.9 | 1171.9 | 1111.8 | 1048.0 | 946.6  | 845.1  | 815.1  | 785.0  | 788.8  | 792.6  | 848.9  |
| 32.5° | 1464.9 | 1412.3 | 1232.0 | 1051.7 | 957.8  | 863.9  | 785.0  | 706.2  | 713.7  | 721.2  | 792.6  |
| 35°   | 1600.1 | 1558.8 | 1318.4 | 1074.3 | 920.3  | 762.5  | 694.9  | 623.5  | 657.3  | 687.4  | 747.5  |
| 37.5° | 1754.1 | 1641.5 | 1314.7 | 984.1  | 818.9  | 653.6  | 612.3  | 570.9  | 593.5  | 612.3  | 649.8  |
| 40°   | 1893.1 | 1675.3 | 1280.9 | 882.7  | 717.4  | 548.4  | 529.6  | 507.1  | 525.9  | 544.6  | 567.2  |
| 42.5° | 2043.4 | 1724.1 | 1232.0 | 736.2  | 604.7  | 473.3  | 465.8  | 458.3  | 477.0  | 495.8  | 510.8  |
| 45°   | 2159.8 | 1731.6 | 1168.2 | 601.0  | 514.6  | 428.2  | 428.2  | 424.5  | 443.2  | 458.3  | 465.8  |
| 47.5° | 2234.9 | 1649.0 | 1066.8 | 480.8  | 443.2  | 405.7  | 409.4  | 409.4  | 424.5  | 435.7  | 439.5  |
| 50°   | 2287.5 | 1513.7 | 969.1  | 424.5  | 405.7  | 386.9  | 386.9  | 386.9  | 401.9  | 413.2  | 420.7  |
| 52.5° | 2325.1 | 1363.5 | 878.9  | 390.6  | 383.1  | 371.9  | 371.9  | 368.1  | 386.9  | 405.7  | 409.4  |
| 55°   | 2336.4 | 1209.5 | 788.8  | 364.4  | 356.8  | 349.3  | 356.8  | 360.6  | 383.1  | 401.9  | 405.7  |
| 57.5° | 2362.6 | 1089.3 | 713.7  | 338.1  | 334.3  | 330.5  | 341.8  | 353.1  | 375.6  | 398.2  | 398.2  |
| 60°   | 2415.2 | 1010.4 | 661.1  | 311.8  | 311.8  | 311.8  | 330.5  | 345.6  | 368.1  | 390.6  | 386.9  |
| 62.5° | 2464.1 | 939.0  | 612.3  | 285.5  | 289.2  | 293.0  | 315.5  | 338.1  | 360.6  | 383.1  | 379.4  |
| 65°   | 2471.6 | 826.4  | 544.6  | 262.9  | 270.4  | 274.2  | 300.5  | 326.8  | 349.3  | 371.9  | 364.4  |
| 67.5° | 2388.9 | 646.1  | 443.2  | 240.4  | 251.7  | 259.2  | 289.2  | 315.5  | 338.1  | 356.8  | 349.3  |
| 70°   | 2238.7 | 462.0  | 341.8  | 221.6  | 232.9  | 240.4  | 270.4  | 296.7  | 315.5  | 334.3  | 326.8  |
| 72.5° | 2017.1 | 330.5  | 266.7  | 202.8  | 210.3  | 217.9  | 244.2  | 270.4  | 293.0  | 311.8  | 304.3  |
| 75°   | 1664.0 | 266.7  | 225.4  | 184.1  | 191.6  | 195.3  | 221.6  | 244.2  | 266.7  | 285.5  | 274.2  |
| 77.5° | 1104.3 | 217.9  | 191.6  | 165.3  | 169.0  | 172.8  | 195.3  | 214.1  | 232.9  | 247.9  | 240.4  |
| 80°   | 533.4  | 176.5  | 161.5  | 142.7  | 146.5  | 146.5  | 165.3  | 184.1  | 199.1  | 210.3  | 206.6  |
| 82.5° | 217.9  | 139.0  | 127.7  | 116.4  | 116.4  | 116.4  | 135.2  | 150.2  | 165.3  | 176.5  | 169.0  |
| 85°   | 135.2  | 108.9  | 101.4  | 90.1   | 86.4   | 82.6   | 90.1   | 97.7   | 105.2  | 108.9  | 105.2  |
| 87.5° | 18.8   | 18.8   | 22.5   | 26.3   | 22.5   | 15.0   | 22.5   | 30.0   | 30.0   | 26.3   | 22.5   |
| 90°   | 0.0    | 0.0    | 11.3   | 11.3   | 7.5    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P559881

CATALOG NUMBER: SDL-PA1-100-750-U-T2U

**CANDELA DISTRIBUTION (continued):**

|       | 165°   | 170°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|
| 0°    | 1453.6 | 1453.6 | 1453.6 | 1453.6 |
| 2.5°  | 1295.9 | 1295.9 | 1295.9 | 1303.4 |
| 5°    | 1292.1 | 1292.1 | 1292.1 | 1299.6 |
| 7.5°  | 1205.7 | 1168.2 | 1130.6 | 1134.4 |
| 10°   | 1352.2 | 1356.0 | 1356.0 | 1359.7 |
| 12.5° | 1235.8 | 1175.7 | 1115.6 | 1123.1 |
| 15°   | 1258.3 | 1258.3 | 1254.6 | 1258.3 |
| 17.5° | 1048.0 | 1029.2 | 1010.4 | 1010.4 |
| 20°   | 1198.2 | 1198.2 | 1198.2 | 1198.2 |
| 22.5° | 954.1  | 950.3  | 946.6  | 950.3  |
| 25°   | 1074.3 | 1078.0 | 1078.0 | 1074.3 |
| 27.5° | 818.9  | 867.7  | 912.8  | 916.5  |
| 30°   | 901.5  | 901.5  | 901.5  | 901.5  |
| 32.5° | 863.9  | 901.5  | 939.0  | 942.8  |
| 35°   | 803.8  | 800.1  | 796.3  | 807.6  |
| 37.5° | 683.6  | 676.1  | 668.6  | 668.6  |
| 40°   | 589.7  | 574.7  | 559.7  | 559.7  |
| 42.5° | 522.1  | 510.8  | 495.8  | 492.1  |
| 45°   | 473.3  | 462.0  | 447.0  | 447.0  |
| 47.5° | 439.5  | 432.0  | 424.5  | 420.7  |
| 50°   | 424.5  | 416.9  | 409.4  | 409.4  |
| 52.5° | 413.2  | 409.4  | 401.9  | 401.9  |
| 55°   | 405.7  | 401.9  | 394.4  | 394.4  |
| 57.5° | 398.2  | 394.4  | 386.9  | 386.9  |
| 60°   | 383.1  | 379.4  | 375.6  | 375.6  |
| 62.5° | 371.9  | 368.1  | 364.4  | 364.4  |
| 65°   | 356.8  | 356.8  | 353.1  | 349.3  |
| 67.5° | 338.1  | 338.1  | 338.1  | 330.5  |
| 70°   | 315.5  | 315.5  | 315.5  | 308.0  |
| 72.5° | 293.0  | 293.0  | 289.2  | 278.0  |
| 75°   | 262.9  | 259.2  | 255.4  | 247.9  |
| 77.5° | 232.9  | 225.4  | 217.9  | 214.1  |
| 80°   | 199.1  | 191.6  | 184.1  | 176.5  |
| 82.5° | 157.8  | 154.0  | 146.5  | 127.7  |
| 85°   | 97.7   | 86.4   | 71.4   | 63.9   |
| 87.5° | 18.8   | 15.0   | 11.3   | 3.8    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    |



Report Generated By 670245982









--- HS --- SS

u











(END OF REPORT)