

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560203

Luminaire Tested: **SDL-PA1-30-740-U-SL3**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560203  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-30-740-U-SL3  
Description: Springdale  
(1) 70 CRI, 4000K, 375mA LIGHT ENGINE WITH 24 LEDS AND TYPE III SPILL  
LIGHT ELIMINATOR OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3781.8 lumens  
Efficiency: N/A  
Efficacy: 125.6 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type III - Medium  
BUG Rating: B1 - U0 - G2

Input Watts (W): 30.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P560203

CATALOG NUMBER: SDL-PA1-30-740-U-SL3

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 10.8 fc  
 Type III - Medium - N/A

REPORT NUMBER: P560203

CATALOG NUMBER: SDL-PA1-30-740-U-SL3

## Luminous Intensity Polar Plot



— Vertical Plane Through 60-Deg Lateral      - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P560203

CATALOG NUMBER: SDL-PA1-30-740-U-SL3


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 607.9    | 0.0    | 607.9  |
|                    | % Fixture | 16.1     | 0.0    | 16.1   |
| <b>Street Side</b> | Lumens    | 3173.9   | 0.0    | 3173.9 |
|                    | % Fixture | 83.9     | 0.0    | 83.9   |
| <b>Total</b>       | Lumens    | 3781.8   | 0.0    | 3781.8 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 78.7   | 2.1       |
| 10°-20°   | 142.0  | 3.8       |
| 20°-30°   | 186.0  | 4.9       |
| 30°-40°   | 306.9  | 8.1       |
| 40°-50°   | 479.3  | 12.7      |
| 50°-60°   | 729.6  | 19.3      |
| 60°-70°   | 904.1  | 23.9      |
| 70°-80°   | 798.7  | 21.1      |
| 80°-90°   | 156.6  | 4.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 3781.8 | 100.0     |
| 0°-180°   | 3781.8 | 100.0     |



REPORT NUMBER: P560203


CATALOG NUMBER: SDL-PA1-30-740-U-SL3

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 248.3  | 6.6       |                         |      |         |
| FM   | (30°-60°)   | 1298.0 | 34.3      |                         |      |         |
| FH   | (60°-80°)   | 1486.0 | 39.3      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 141.6  | 3.7       |                         |      | G2/225  |
| BL   | (0°-30°)    | 158.4  | 4.2       | B1/500                  |      |         |
| BM   | (30°-60°)   | 217.8  | 5.8       | B0/220                  |      |         |
| BH   | (60°-80°)   | 216.8  | 5.7       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 14.9   | 0.4       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type III Medium





REPORT NUMBER: P560203

CATALOG NUMBER: SDL-PA1-30-740-U-SL3

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    | 50°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 |
| 2.5°  | 895.9  | 997.0  | 973.5  | 949.9  | 985.9  | 1020.5 | 1031.6 | 1041.3 | 1046.9 | 1052.4 | 1057.9 |
| 5°    | 832.2  | 833.6  | 835.0  | 836.4  | 840.5  | 843.3  | 848.8  | 854.4  | 859.9  | 864.1  | 869.6  |
| 7.5°  | 642.5  | 664.7  | 700.7  | 736.7  | 758.8  | 779.6  | 792.1  | 803.1  | 811.5  | 819.8  | 828.1  |
| 10°   | 714.5  | 718.7  | 720.1  | 720.1  | 727.0  | 733.9  | 681.3  | 627.3  | 653.6  | 679.9  | 650.8  |
| 12.5° | 560.8  | 576.0  | 621.7  | 666.1  | 679.9  | 692.4  | 667.4  | 642.5  | 603.7  | 563.6  | 560.8  |
| 15°   | 643.9  | 648.1  | 649.4  | 649.4  | 606.5  | 563.6  | 534.5  | 504.0  | 527.6  | 549.7  | 498.5  |
| 17.5° | 498.5  | 502.7  | 538.7  | 574.7  | 581.6  | 588.5  | 558.0  | 527.6  | 459.7  | 390.5  | 455.6  |
| 20°   | 592.7  | 595.4  | 595.4  | 595.4  | 523.4  | 451.4  | 457.0  | 461.1  | 483.3  | 505.4  | 487.4  |
| 22.5° | 477.7  | 477.7  | 477.7  | 477.7  | 499.9  | 520.7  | 476.3  | 432.0  | 457.0  | 481.9  | 459.7  |
| 25°   | 601.0  | 605.1  | 595.4  | 584.4  | 517.9  | 451.4  | 472.2  | 493.0  | 455.6  | 418.2  | 451.4  |
| 27.5° | 548.4  | 544.2  | 524.8  | 504.0  | 513.7  | 523.4  | 477.7  | 432.0  | 461.1  | 490.2  | 476.3  |
| 30°   | 728.4  | 715.9  | 695.1  | 674.4  | 595.4  | 516.5  | 504.0  | 491.6  | 466.7  | 440.3  | 469.4  |
| 32.5° | 967.9  | 936.1  | 839.1  | 742.2  | 693.8  | 645.3  | 583.0  | 520.7  | 515.1  | 508.2  | 516.5  |
| 35°   | 1031.6 | 1010.9 | 970.7  | 929.2  | 846.1  | 761.6  | 682.7  | 602.4  | 576.0  | 548.4  | 553.9  |
| 37.5° | 1044.1 | 1037.2 | 1028.9 | 1019.2 | 934.7  | 850.2  | 764.4  | 678.5  | 650.8  | 621.7  | 601.0  |
| 40°   | 1053.8 | 1059.3 | 1074.6 | 1088.4 | 1003.9 | 918.1  | 840.5  | 761.6  | 732.5  | 702.1  | 666.1  |
| 42.5° | 1098.1 | 1113.3 | 1132.7 | 1150.7 | 1073.2 | 995.6  | 927.8  | 859.9  | 822.5  | 785.1  | 751.9  |
| 45°   | 1200.6 | 1208.9 | 1229.6 | 1249.0 | 1175.6 | 1100.9 | 1023.3 | 944.4  | 912.5  | 880.7  | 847.5  |
| 47.5° | 1350.1 | 1364.0 | 1362.6 | 1361.2 | 1279.5 | 1196.4 | 1109.2 | 1020.5 | 999.8  | 977.6  | 945.8  |
| 50°   | 1538.4 | 1528.7 | 1502.4 | 1476.1 | 1387.5 | 1297.5 | 1195.0 | 1091.2 | 1081.5 | 1070.4 | 1044.1 |
| 52.5° | 1632.6 | 1625.7 | 1589.7 | 1552.3 | 1462.3 | 1372.3 | 1261.5 | 1149.3 | 1161.8 | 1174.3 | 1149.3 |
| 55°   | 1638.1 | 1634.0 | 1607.7 | 1581.4 | 1494.1 | 1406.9 | 1308.6 | 1210.3 | 1240.7 | 1271.2 | 1261.5 |
| 57.5° | 1598.0 | 1599.4 | 1591.1 | 1581.4 | 1503.8 | 1426.3 | 1344.6 | 1262.9 | 1315.5 | 1366.7 | 1376.4 |
| 60°   | 1495.5 | 1516.3 | 1530.1 | 1544.0 | 1495.5 | 1447.0 | 1376.4 | 1305.8 | 1386.1 | 1466.4 | 1492.7 |
| 62.5° | 1305.8 | 1323.8 | 1373.7 | 1422.1 | 1431.8 | 1440.1 | 1393.0 | 1344.6 | 1452.6 | 1559.2 | 1602.1 |
| 65°   | 1012.2 | 1037.2 | 1111.9 | 1186.7 | 1264.3 | 1341.8 | 1352.9 | 1364.0 | 1546.7 | 1729.5 | 1765.5 |
| 67.5° | 631.4  | 645.3  | 724.2  | 801.8  | 958.2  | 1113.3 | 1201.9 | 1290.6 | 1606.3 | 1920.6 | 1977.4 |
| 70°   | 333.7  | 354.5  | 393.3  | 430.7  | 565.0  | 699.3  | 879.3  | 1059.3 | 1516.3 | 1973.2 | 2205.9 |
| 72.5° | 253.4  | 261.7  | 282.5  | 303.3  | 350.3  | 397.4  | 511.0  | 624.5  | 1186.7 | 1747.5 | 2283.4 |
| 75°   | 182.8  | 189.7  | 211.9  | 232.6  | 279.7  | 325.4  | 372.5  | 418.2  | 732.5  | 1046.9 | 1892.9 |
| 77.5° | 106.6  | 109.4  | 120.5  | 130.2  | 203.6  | 276.9  | 328.2  | 378.0  | 454.2  | 529.0  | 1351.5 |
| 80°   | 73.4   | 74.8   | 78.9   | 83.1   | 114.9  | 146.8  | 245.1  | 343.4  | 378.0  | 411.3  | 895.9  |
| 82.5° | 48.5   | 55.4   | 58.2   | 60.9   | 72.0   | 83.1   | 144.0  | 203.6  | 299.1  | 393.3  | 612.1  |
| 85°   | 24.9   | 27.7   | 33.2   | 37.4   | 42.9   | 47.1   | 65.1   | 81.7   | 247.9  | 412.7  | 440.3  |
| 87.5° | 2.8    | 4.2    | 5.5    | 5.5    | 6.9    | 8.3    | 12.5   | 16.6   | 74.8   | 132.9  | 113.5  |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560203

CATALOG NUMBER: SDL-PA1-30-740-U-SL3

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   | 105°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 |
| 2.5°  | 1063.5 | 1066.2 | 1064.9 | 1067.6 | 1069.0 | 1070.4 | 1071.8 | 1071.8 | 1070.4 | 1067.6 | 1064.9 |
| 5°    | 875.2  | 930.5  | 1024.7 | 1034.4 | 1044.1 | 1046.9 | 1049.6 | 1051.0 | 1048.2 | 1044.1 | 1039.9 |
| 7.5°  | 835.0  | 843.3  | 758.8  | 826.7  | 893.2  | 898.7  | 902.8  | 900.1  | 901.5  | 864.1  | 825.3  |
| 10°   | 621.7  | 628.7  | 631.4  | 652.2  | 671.6  | 717.3  | 763.0  | 756.1  | 750.5  | 684.1  | 616.2  |
| 12.5° | 558.0  | 594.1  | 602.4  | 567.7  | 533.1  | 580.2  | 627.3  | 621.7  | 612.1  | 551.1  | 490.2  |
| 15°   | 447.3  | 409.9  | 490.2  | 565.0  | 638.4  | 682.7  | 725.6  | 713.1  | 702.1  | 624.5  | 545.6  |
| 17.5° | 519.3  | 541.4  | 515.1  | 526.2  | 537.3  | 570.5  | 602.4  | 583.0  | 576.0  | 522.0  | 466.7  |
| 20°   | 469.4  | 468.0  | 450.0  | 515.1  | 580.2  | 645.3  | 709.0  | 689.6  | 656.4  | 551.1  | 444.5  |
| 22.5° | 437.6  | 527.6  | 566.4  | 558.0  | 548.4  | 523.4  | 497.1  | 480.5  | 455.6  | 432.0  | 407.1  |
| 25°   | 483.3  | 445.9  | 476.3  | 576.0  | 674.4  | 692.4  | 710.4  | 668.8  | 614.8  | 508.2  | 401.6  |
| 27.5° | 462.5  | 520.7  | 559.4  | 625.9  | 691.0  | 753.3  | 815.6  | 760.2  | 689.6  | 556.7  | 422.3  |
| 30°   | 498.5  | 530.4  | 638.4  | 763.0  | 887.6  | 909.8  | 930.5  | 854.4  | 760.2  | 625.9  | 491.6  |
| 32.5° | 524.8  | 609.3  | 704.8  | 801.8  | 897.3  | 913.9  | 930.5  | 844.7  | 736.7  | 588.5  | 440.3  |
| 35°   | 558.0  | 620.4  | 707.6  | 821.1  | 934.7  | 938.8  | 941.6  | 841.9  | 720.1  | 552.5  | 383.6  |
| 37.5° | 580.2  | 650.8  | 745.0  | 865.5  | 985.9  | 977.6  | 967.9  | 854.4  | 714.5  | 527.6  | 340.6  |
| 40°   | 630.1  | 691.0  | 792.1  | 915.3  | 1038.5 | 1024.7 | 1010.9 | 880.7  | 715.9  | 502.7  | 288.0  |
| 42.5° | 717.3  | 740.8  | 850.2  | 981.8  | 1113.3 | 1098.1 | 1081.5 | 926.4  | 732.5  | 488.8  | 243.7  |
| 45°   | 812.8  | 823.9  | 918.1  | 1067.6 | 1217.2 | 1197.8 | 1178.4 | 997.0  | 763.0  | 481.9  | 200.8  |
| 47.5° | 912.5  | 909.8  | 997.0  | 1178.4 | 1358.4 | 1316.9 | 1275.3 | 1080.1 | 819.8  | 495.7  | 171.7  |
| 50°   | 1016.4 | 1012.2 | 1096.7 | 1292.0 | 1487.2 | 1442.9 | 1398.6 | 1179.8 | 884.8  | 520.7  | 155.1  |
| 52.5° | 1123.0 | 1132.7 | 1195.0 | 1398.6 | 1600.8 | 1560.6 | 1519.1 | 1287.8 | 948.5  | 548.4  | 148.2  |
| 55°   | 1250.4 | 1280.9 | 1305.8 | 1509.4 | 1712.9 | 1672.8 | 1631.2 | 1398.6 | 1037.2 | 591.3  | 145.4  |
| 57.5° | 1384.7 | 1424.9 | 1436.0 | 1621.5 | 1807.1 | 1780.8 | 1753.1 | 1503.8 | 1127.2 | 641.1  | 153.7  |
| 60°   | 1519.1 | 1571.7 | 1611.8 | 1761.4 | 1909.5 | 1879.1 | 1848.6 | 1610.4 | 1211.6 | 696.5  | 181.4  |
| 62.5° | 1643.7 | 1717.1 | 1782.2 | 1891.5 | 1999.6 | 1963.6 | 1927.5 | 1703.2 | 1307.2 | 772.7  | 236.8  |
| 65°   | 1800.2 | 1865.2 | 1935.9 | 2007.9 | 2078.5 | 2043.9 | 2009.2 | 1819.5 | 1434.6 | 868.2  | 300.5  |
| 67.5° | 2034.2 | 2053.6 | 2089.6 | 2133.9 | 2176.8 | 2156.0 | 2133.9 | 1962.2 | 1545.4 | 923.6  | 300.5  |
| 70°   | 2437.1 | 2394.2 | 2340.2 | 2338.8 | 2336.0 | 2302.8 | 2268.2 | 2042.5 | 1552.3 | 901.5  | 250.6  |
| 72.5° | 2817.9 | 2964.7 | 2793.0 | 2668.4 | 2543.8 | 2397.0 | 2248.8 | 1934.5 | 1370.9 | 785.1  | 199.4  |
| 75°   | 2737.6 | 3308.1 | 3225.0 | 2887.2 | 2549.3 | 2283.4 | 2017.6 | 1685.2 | 1128.6 | 649.4  | 170.3  |
| 77.5° | 2172.6 | 2919.0 | 2997.9 | 2687.8 | 2376.2 | 2016.2 | 1654.8 | 1303.0 | 782.4  | 462.5  | 142.6  |
| 80°   | 1379.2 | 2182.3 | 2196.2 | 1908.2 | 1618.8 | 1232.4 | 846.1  | 567.7  | 376.6  | 245.1  | 113.5  |
| 82.5° | 830.8  | 1292.0 | 1124.4 | 805.9  | 487.4  | 337.9  | 186.9  | 180.0  | 138.5  | 102.5  | 66.5   |
| 85°   | 468.0  | 632.8  | 454.2  | 297.7  | 141.2  | 101.1  | 59.5   | 63.7   | 60.9   | 49.9   | 37.4   |
| 87.5° | 92.8   | 109.4  | 74.8   | 42.9   | 11.1   | 11.1   | 9.7    | 9.7    | 6.9    | 6.9    | 5.5    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P560203

CATALOG NUMBER: SDL-PA1-30-740-U-SL3

**CANDELA DISTRIBUTION (continued):**

|       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   | 160°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 | 1078.7 |
| 2.5°  | 1064.9 | 1064.9 | 1062.1 | 1059.3 | 1057.9 | 1056.6 | 1015.0 | 973.5  | 945.8  | 916.7  | 909.8  |
| 5°    | 988.7  | 937.5  | 898.7  | 859.9  | 851.6  | 843.3  | 841.9  | 840.5  | 836.4  | 830.8  | 829.5  |
| 7.5°  | 781.0  | 735.3  | 767.1  | 797.6  | 792.1  | 785.1  | 781.0  | 775.5  | 765.8  | 756.1  | 707.6  |
| 10°   | 601.0  | 585.7  | 585.7  | 584.4  | 573.3  | 562.2  | 587.1  | 612.1  | 639.7  | 667.4  | 664.7  |
| 12.5° | 512.4  | 533.1  | 479.1  | 423.7  | 454.2  | 483.3  | 511.0  | 537.3  | 551.1  | 565.0  | 522.0  |
| 15°   | 483.3  | 419.6  | 401.6  | 383.6  | 397.4  | 411.3  | 371.1  | 329.6  | 361.4  | 393.3  | 400.2  |
| 17.5° | 433.4  | 400.2  | 382.2  | 362.8  | 310.2  | 256.2  | 274.2  | 292.2  | 290.8  | 289.4  | 282.5  |
| 20°   | 404.3  | 362.8  | 331.0  | 297.7  | 272.8  | 247.9  | 221.6  | 193.9  | 181.4  | 167.6  | 200.8  |
| 22.5° | 385.0  | 362.8  | 296.3  | 229.9  | 210.5  | 191.1  | 170.3  | 148.2  | 156.5  | 163.4  | 168.9  |
| 25°   | 336.5  | 270.0  | 232.6  | 195.2  | 164.8  | 132.9  | 134.3  | 135.7  | 128.8  | 121.9  | 153.7  |
| 27.5° | 340.6  | 257.6  | 199.4  | 141.2  | 130.2  | 117.7  | 110.8  | 102.5  | 113.5  | 123.2  | 126.0  |
| 30°   | 357.3  | 222.9  | 168.9  | 114.9  | 102.5  | 90.0   | 94.2   | 96.9   | 96.9   | 96.9   | 110.8  |
| 32.5° | 317.1  | 193.9  | 144.0  | 92.8   | 85.9   | 77.5   | 78.9   | 78.9   | 85.9   | 92.8   | 99.7   |
| 35°   | 268.6  | 152.3  | 117.7  | 81.7   | 74.8   | 67.9   | 70.6   | 73.4   | 80.3   | 87.2   | 96.9   |
| 37.5° | 231.3  | 120.5  | 96.9   | 73.4   | 69.2   | 65.1   | 66.5   | 67.9   | 74.8   | 80.3   | 88.6   |
| 40°   | 195.2  | 101.1  | 85.9   | 70.6   | 66.5   | 62.3   | 63.7   | 63.7   | 69.2   | 74.8   | 80.3   |
| 42.5° | 168.9  | 92.8   | 81.7   | 69.2   | 65.1   | 59.5   | 60.9   | 60.9   | 65.1   | 69.2   | 73.4   |
| 45°   | 145.4  | 88.6   | 78.9   | 67.9   | 63.7   | 58.2   | 58.2   | 56.8   | 60.9   | 63.7   | 66.5   |
| 47.5° | 130.2  | 87.2   | 77.5   | 67.9   | 62.3   | 55.4   | 54.0   | 52.6   | 56.8   | 59.5   | 63.7   |
| 50°   | 121.9  | 87.2   | 77.5   | 66.5   | 59.5   | 52.6   | 51.2   | 49.9   | 55.4   | 59.5   | 66.5   |
| 52.5° | 119.1  | 88.6   | 77.5   | 66.5   | 58.2   | 49.9   | 49.9   | 49.9   | 59.5   | 69.2   | 72.0   |
| 55°   | 119.1  | 91.4   | 78.9   | 65.1   | 56.8   | 48.5   | 51.2   | 54.0   | 56.8   | 59.5   | 59.5   |
| 57.5° | 121.9  | 90.0   | 76.2   | 62.3   | 56.8   | 49.9   | 48.5   | 47.1   | 48.5   | 49.9   | 49.9   |
| 60°   | 134.3  | 87.2   | 73.4   | 59.5   | 52.6   | 45.7   | 44.3   | 42.9   | 45.7   | 47.1   | 47.1   |
| 62.5° | 162.0  | 85.9   | 73.4   | 59.5   | 51.2   | 42.9   | 42.9   | 41.5   | 42.9   | 44.3   | 45.7   |
| 65°   | 198.0  | 95.5   | 77.5   | 59.5   | 51.2   | 42.9   | 40.2   | 37.4   | 40.2   | 41.5   | 41.5   |
| 67.5° | 206.3  | 112.2  | 90.0   | 66.5   | 54.0   | 41.5   | 38.8   | 36.0   | 38.8   | 40.2   | 40.2   |
| 70°   | 186.9  | 123.2  | 96.9   | 70.6   | 56.8   | 41.5   | 38.8   | 34.6   | 36.0   | 37.4   | 36.0   |
| 72.5° | 160.6  | 120.5  | 95.5   | 69.2   | 55.4   | 40.2   | 37.4   | 33.2   | 34.6   | 34.6   | 33.2   |
| 75°   | 137.1  | 103.9  | 81.7   | 58.2   | 47.1   | 34.6   | 31.8   | 29.1   | 30.5   | 30.5   | 30.5   |
| 77.5° | 114.9  | 85.9   | 66.5   | 45.7   | 37.4   | 27.7   | 26.3   | 24.9   | 26.3   | 27.7   | 26.3   |
| 80°   | 90.0   | 65.1   | 49.9   | 33.2   | 27.7   | 20.8   | 22.2   | 22.2   | 23.5   | 23.5   | 23.5   |
| 82.5° | 52.6   | 38.8   | 31.8   | 23.5   | 19.4   | 15.2   | 16.6   | 18.0   | 19.4   | 19.4   | 19.4   |
| 85°   | 31.8   | 24.9   | 20.8   | 16.6   | 13.8   | 9.7    | 12.5   | 13.8   | 13.8   | 13.8   | 12.5   |
| 87.5° | 5.5    | 5.5    | 5.5    | 5.5    | 4.2    | 2.8    | 5.5    | 6.9    | 6.9    | 6.9    | 5.5    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560203

CATALOG NUMBER: SDL-PA1-30-740-U-SL3

**CANDELA DISTRIBUTION (continued):**

|       | 165°   | 170°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|
| 0°    | 1078.7 | 1078.7 | 1078.7 | 1078.7 |
| 2.5°  | 901.5  | 901.5  | 900.1  | 900.1  |
| 5°    | 828.1  | 825.3  | 822.5  | 825.3  |
| 7.5°  | 659.1  | 639.7  | 620.4  | 625.9  |
| 10°   | 660.5  | 659.1  | 657.7  | 656.4  |
| 12.5° | 477.7  | 462.5  | 447.3  | 437.6  |
| 15°   | 405.7  | 401.6  | 396.0  | 396.0  |
| 17.5° | 274.2  | 261.7  | 249.3  | 240.9  |
| 20°   | 234.0  | 240.9  | 246.5  | 249.3  |
| 22.5° | 174.5  | 180.0  | 185.6  | 188.3  |
| 25°   | 184.2  | 198.0  | 210.5  | 211.9  |
| 27.5° | 127.4  | 134.3  | 139.9  | 137.1  |
| 30°   | 124.6  | 128.8  | 132.9  | 132.9  |
| 32.5° | 106.6  | 117.7  | 128.8  | 130.2  |
| 35°   | 106.6  | 112.2  | 117.7  | 119.1  |
| 37.5° | 95.5   | 99.7   | 102.5  | 103.9  |
| 40°   | 85.9   | 88.6   | 90.0   | 90.0   |
| 42.5° | 76.2   | 83.1   | 88.6   | 88.6   |
| 45°   | 67.9   | 85.9   | 103.9  | 109.4  |
| 47.5° | 66.5   | 92.8   | 119.1  | 124.6  |
| 50°   | 72.0   | 96.9   | 120.5  | 123.2  |
| 52.5° | 73.4   | 87.2   | 99.7   | 99.7   |
| 55°   | 58.2   | 65.1   | 70.6   | 69.2   |
| 57.5° | 49.9   | 55.4   | 59.5   | 59.5   |
| 60°   | 47.1   | 54.0   | 59.5   | 60.9   |
| 62.5° | 45.7   | 48.5   | 51.2   | 54.0   |
| 65°   | 41.5   | 41.5   | 41.5   | 41.5   |
| 67.5° | 38.8   | 38.8   | 37.4   | 37.4   |
| 70°   | 34.6   | 34.6   | 34.6   | 34.6   |
| 72.5° | 31.8   | 31.8   | 31.8   | 30.5   |
| 75°   | 29.1   | 29.1   | 27.7   | 27.7   |
| 77.5° | 24.9   | 24.9   | 24.9   | 24.9   |
| 80°   | 22.2   | 22.2   | 20.8   | 20.8   |
| 82.5° | 18.0   | 18.0   | 16.6   | 15.2   |
| 85°   | 11.1   | 11.1   | 9.7    | 8.3    |
| 87.5° | 4.2    | 4.2    | 2.8    | 1.4    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    |



Report Generated By 670245982









--- HS --- SS



u











(END OF REPORT)