

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560945

Luminaire Tested: **SDL-PA1-70-750-U-T4W**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-70-750-U-T4W  
Description: Springdale  
(1) 70 CRI, 5000K, 930mA LIGHT ENGINE WITH 24 LEDS AND TYPE IV WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8454.1 lumens  
Efficiency: N/A  
Efficacy: 117.1 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type IV - Medium  
BUG Rating: B2 - U0 - G3

Input Watts (W): 72.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P560945

CATALOG NUMBER: SDL-PA1-70-750-U-T4W

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 9.8 fc  
Type IV - Medium - N/A

REPORT NUMBER: P560945

CATALOG NUMBER: SDL-PA1-70-750-U-T4W

## Luminous Intensity Polar Plot



REPORT NUMBER: P560945

CATALOG NUMBER: SDL-PA1-70-750-U-T4W


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1817.7   | 0.0    | 1817.7 |
|                    | % Fixture | 21.5     | 0.0    | 21.5   |
| <b>Street Side</b> | Lumens    | 6636.4   | 0.0    | 6636.4 |
|                    | % Fixture | 78.5     | 0.0    | 78.5   |
| <b>Total</b>       | Lumens    | 8454.1   | 0.0    | 8454.1 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 81.7   | 1.0       |
| 10°-20°   | 205.7  | 2.4       |
| 20°-30°   | 359.7  | 4.3       |
| 30°-40°   | 633.5  | 7.5       |
| 40°-50°   | 955.8  | 11.3      |
| 50°-60°   | 1520.3 | 18.0      |
| 60°-70°   | 2229.4 | 26.4      |
| 70°-80°   | 2090.5 | 24.7      |
| 80°-90°   | 377.5  | 4.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 8454.1 | 100.0     |
| 0°-180°   | 8454.1 | 100.0     |



REPORT NUMBER: P560945


CATALOG NUMBER: SDL-PA1-70-750-U-T4W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 348.6  | 4.1       |                         |      |         |
| FM   | (30°-60°)   | 2277.6 | 26.9      |                         |      |         |
| FH   | (60°-80°)   | 3699.4 | 43.8      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 310.8  | 3.7       |                         |      | G3/500  |
| BL   | (0°-30°)    | 298.5  | 3.5       | B1/500                  |      |         |
| BM   | (30°-60°)   | 832.1  | 9.8       | B1/1000                 |      |         |
| BH   | (60°-80°)   | 620.5  | 7.3       | B2/1000                 |      | G2/1000 |
| BVH  | (80°-90°)   | 66.7   | 0.8       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G3**

Type IV Medium



REPORT NUMBER: P560945

CATALOG NUMBER: SDL-PA1-70-750-U-T4W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    | 50°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  |
| 2.5°  | 892.6  | 930.0  | 948.7  | 967.5  | 973.7  | 979.9  | 979.9  | 976.8  | 976.8  | 976.8  | 983.1  |
| 5°    | 908.2  | 905.0  | 905.0  | 905.0  | 901.9  | 898.8  | 895.7  | 889.4  | 886.3  | 880.1  | 877.0  |
| 7.5°  | 833.3  | 895.7  | 898.8  | 901.9  | 901.9  | 898.8  | 905.0  | 911.3  | 905.0  | 895.7  | 883.2  |
| 10°   | 989.3  | 986.2  | 979.9  | 973.7  | 964.3  | 955.0  | 883.2  | 808.3  | 814.5  | 820.8  | 761.5  |
| 12.5° | 858.2  | 917.5  | 942.5  | 967.5  | 970.6  | 970.6  | 920.6  | 867.6  | 798.9  | 730.3  | 702.2  |
| 15°   | 1048.6 | 1042.4 | 1029.9 | 1017.4 | 933.1  | 845.7  | 795.8  | 745.9  | 745.9  | 745.9  | 661.6  |
| 17.5° | 883.2  | 880.1  | 936.3  | 992.4  | 961.2  | 930.0  | 858.2  | 786.5  | 680.3  | 571.1  | 639.8  |
| 20°   | 1082.9 | 1082.9 | 1067.3 | 1051.7 | 908.2  | 761.5  | 770.8  | 777.1  | 780.2  | 780.2  | 749.0  |
| 22.5° | 908.2  | 901.9  | 908.2  | 911.3  | 911.3  | 911.3  | 780.2  | 649.1  | 720.9  | 789.6  | 717.8  |
| 25°   | 1082.9 | 1086.1 | 1082.9 | 1079.8 | 948.7  | 814.5  | 836.4  | 858.2  | 758.4  | 655.4  | 724.0  |
| 27.5° | 945.6  | 942.5  | 926.9  | 911.3  | 914.4  | 917.5  | 848.9  | 777.1  | 817.7  | 858.2  | 786.5  |
| 30°   | 1157.8 | 1161.0 | 1151.6 | 1139.1 | 1008.0 | 877.0  | 870.7  | 861.4  | 833.3  | 805.2  | 830.1  |
| 32.5° | 1398.1 | 1398.1 | 1301.4 | 1204.6 | 1123.5 | 1039.2 | 970.6  | 901.9  | 930.0  | 958.1  | 926.9  |
| 35°   | 1526.1 | 1519.9 | 1488.6 | 1454.3 | 1304.5 | 1151.6 | 1058.0 | 961.2  | 970.6  | 976.8  | 976.8  |
| 37.5° | 1753.9 | 1750.8 | 1707.1 | 1663.4 | 1460.6 | 1254.6 | 1132.9 | 1008.0 | 1026.8 | 1042.4 | 1020.5 |
| 40°   | 2037.9 | 2037.9 | 2003.6 | 1966.1 | 1707.1 | 1445.0 | 1273.3 | 1101.7 | 1098.5 | 1092.3 | 1067.3 |
| 42.5° | 2312.5 | 2321.9 | 2300.1 | 2278.2 | 1975.5 | 1672.8 | 1448.1 | 1223.4 | 1195.3 | 1167.2 | 1142.2 |
| 45°   | 2493.6 | 2506.0 | 2524.8 | 2543.5 | 2243.9 | 1944.3 | 1682.1 | 1416.9 | 1363.8 | 1307.6 | 1263.9 |
| 47.5° | 2677.7 | 2659.0 | 2683.9 | 2708.9 | 2453.0 | 2197.1 | 1910.0 | 1622.8 | 1535.5 | 1448.1 | 1401.3 |
| 50°   | 2849.3 | 2843.1 | 2852.5 | 2861.8 | 2652.7 | 2443.6 | 2147.1 | 1850.7 | 1744.6 | 1635.3 | 1582.3 |
| 52.5° | 3074.0 | 3052.2 | 3039.7 | 3027.2 | 2849.3 | 2671.4 | 2390.6 | 2106.6 | 1981.7 | 1853.8 | 1791.4 |
| 55°   | 3289.4 | 3280.0 | 3261.3 | 3239.4 | 3086.5 | 2933.6 | 2637.1 | 2340.6 | 2209.6 | 2078.5 | 2006.7 |
| 57.5° | 3511.0 | 3504.7 | 3501.6 | 3498.5 | 3364.3 | 3230.1 | 2927.4 | 2621.5 | 2471.7 | 2318.8 | 2259.5 |
| 60°   | 3720.0 | 3723.2 | 3748.1 | 3770.0 | 3667.0 | 3564.0 | 3258.2 | 2952.3 | 2761.9 | 2568.5 | 2509.2 |
| 62.5° | 3844.9 | 3854.2 | 3916.7 | 3976.0 | 3919.8 | 3863.6 | 3548.4 | 3230.1 | 3030.3 | 2827.5 | 2786.9 |
| 65°   | 3685.7 | 3732.5 | 3913.5 | 4094.6 | 4094.6 | 4094.6 | 3807.4 | 3517.2 | 3342.4 | 3167.7 | 3133.3 |
| 67.5° | 3329.9 | 3376.8 | 3635.8 | 3891.7 | 4025.9 | 4160.1 | 3972.8 | 3785.6 | 3667.0 | 3545.3 | 3501.6 |
| 70°   | 3036.6 | 3064.7 | 3308.1 | 3548.4 | 3885.5 | 4222.5 | 4100.8 | 3976.0 | 3969.7 | 3960.4 | 3841.8 |
| 72.5° | 2790.0 | 2852.5 | 3052.2 | 3248.8 | 3713.8 | 4178.8 | 4175.7 | 4172.6 | 4300.5 | 4428.5 | 4200.7 |
| 75°   | 2231.4 | 2225.2 | 2412.4 | 2599.7 | 3124.0 | 3645.1 | 3938.5 | 4228.7 | 4597.0 | 4962.1 | 4612.6 |
| 77.5° | 995.6  | 1064.2 | 1242.1 | 1420.0 | 1891.2 | 2359.4 | 2924.2 | 3489.1 | 4300.5 | 5108.8 | 4753.0 |
| 80°   | 284.0  | 299.6  | 349.5  | 396.3  | 617.9  | 836.4  | 1429.3 | 2019.2 | 3039.7 | 4057.1 | 3816.8 |
| 82.5° | 149.8  | 156.0  | 187.3  | 215.3  | 277.8  | 337.1  | 561.8  | 783.3  | 1660.3 | 2534.1 | 2315.7 |
| 85°   | 71.8   | 65.5   | 84.3   | 99.9   | 134.2  | 168.5  | 259.0  | 349.5  | 642.9  | 936.3  | 808.3  |
| 87.5° | 15.6   | 15.6   | 18.7   | 18.7   | 28.1   | 37.5   | 56.2   | 74.9   | 71.8   | 65.5   | 78.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560945

CATALOG NUMBER: SDL-PA1-70-750-U-T4W

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   | 105°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  | 983.1  |
| 2.5°  | 986.2  | 989.3  | 992.4  | 989.3  | 986.2  | 983.1  | 983.1  | 979.9  | 979.9  | 976.8  | 970.6  |
| 5°    | 873.8  | 917.5  | 961.2  | 964.3  | 967.5  | 967.5  | 964.3  | 961.2  | 955.0  | 951.9  | 945.6  |
| 7.5°  | 870.7  | 855.1  | 839.5  | 842.6  | 845.7  | 848.9  | 848.9  | 839.5  | 836.4  | 811.4  | 786.5  |
| 10°   | 699.1  | 683.5  | 667.9  | 677.2  | 686.6  | 720.9  | 739.6  | 733.4  | 727.2  | 683.5  | 636.7  |
| 12.5° | 674.1  | 667.9  | 661.6  | 614.8  | 568.0  | 608.6  | 636.7  | 633.5  | 624.2  | 583.6  | 543.0  |
| 15°   | 577.4  | 580.5  | 580.5  | 633.5  | 686.6  | 720.9  | 745.9  | 739.6  | 733.4  | 683.5  | 633.5  |
| 17.5° | 705.3  | 671.0  | 633.5  | 624.2  | 614.8  | 630.4  | 608.6  | 574.2  | 596.1  | 589.8  | 583.6  |
| 20°   | 714.7  | 630.4  | 543.0  | 630.4  | 717.8  | 739.6  | 786.5  | 783.3  | 774.0  | 730.3  | 686.6  |
| 22.5° | 646.0  | 695.9  | 742.8  | 695.9  | 649.1  | 617.9  | 602.3  | 596.1  | 593.0  | 605.4  | 614.8  |
| 25°   | 792.7  | 699.1  | 602.3  | 717.8  | 830.1  | 855.1  | 867.6  | 858.2  | 855.1  | 798.9  | 742.8  |
| 27.5° | 711.6  | 761.5  | 811.4  | 848.9  | 886.3  | 917.5  | 1011.2 | 920.6  | 917.5  | 864.5  | 808.3  |
| 30°   | 852.0  | 905.0  | 958.1  | 1054.8 | 1151.6 | 1204.6 | 1223.4 | 1217.1 | 1201.5 | 1117.3 | 1033.0 |
| 32.5° | 895.7  | 1001.8 | 1104.8 | 1148.5 | 1189.0 | 1245.2 | 1273.3 | 1270.2 | 1254.6 | 1154.7 | 1051.7 |
| 35°   | 976.8  | 1054.8 | 1132.9 | 1192.2 | 1248.3 | 1301.4 | 1326.4 | 1335.7 | 1317.0 | 1192.2 | 1064.2 |
| 37.5° | 998.7  | 1098.5 | 1198.4 | 1260.8 | 1323.2 | 1363.8 | 1385.7 | 1413.7 | 1391.9 | 1242.1 | 1089.2 |
| 40°   | 1042.4 | 1161.0 | 1276.4 | 1338.8 | 1398.1 | 1435.6 | 1473.0 | 1507.4 | 1479.3 | 1298.3 | 1114.1 |
| 42.5° | 1114.1 | 1235.9 | 1354.4 | 1426.2 | 1494.9 | 1547.9 | 1591.6 | 1638.4 | 1585.4 | 1351.3 | 1114.1 |
| 45°   | 1220.3 | 1332.6 | 1445.0 | 1541.7 | 1635.3 | 1700.9 | 1763.3 | 1828.8 | 1722.7 | 1420.0 | 1114.1 |
| 47.5° | 1354.4 | 1463.7 | 1569.8 | 1722.7 | 1875.6 | 1934.9 | 2009.8 | 2072.2 | 1900.6 | 1507.4 | 1114.1 |
| 50°   | 1526.1 | 1647.8 | 1769.5 | 1972.4 | 2172.1 | 2228.3 | 2321.9 | 2368.7 | 2137.8 | 1641.6 | 1142.2 |
| 52.5° | 1725.8 | 1860.0 | 1991.1 | 2228.3 | 2465.5 | 2559.1 | 2683.9 | 2715.1 | 2378.1 | 1775.8 | 1170.3 |
| 55°   | 1934.9 | 2115.9 | 2293.8 | 2556.0 | 2815.0 | 2905.5 | 3083.4 | 3108.4 | 2687.0 | 1941.2 | 1192.2 |
| 57.5° | 2200.2 | 2412.4 | 2621.5 | 2877.4 | 3130.2 | 3258.2 | 3535.9 | 3545.3 | 3045.9 | 2144.0 | 1239.0 |
| 60°   | 2449.9 | 2715.1 | 2977.3 | 3220.7 | 3464.1 | 3663.9 | 3985.3 | 3988.4 | 3383.0 | 2296.9 | 1207.8 |
| 62.5° | 2746.3 | 3061.6 | 3373.6 | 3582.7 | 3791.8 | 4038.4 | 4425.4 | 4369.2 | 3620.2 | 2315.7 | 1011.2 |
| 65°   | 3095.9 | 3420.4 | 3745.0 | 3922.9 | 4097.7 | 4378.5 | 4796.7 | 4581.4 | 3685.7 | 2209.6 | 730.3  |
| 67.5° | 3454.8 | 3757.5 | 4060.2 | 4200.7 | 4341.1 | 4696.9 | 5068.3 | 4606.4 | 3589.0 | 2050.4 | 508.7  |
| 70°   | 3723.2 | 4007.2 | 4291.2 | 4412.9 | 4534.6 | 4918.5 | 5149.4 | 4444.1 | 3317.5 | 1856.9 | 396.3  |
| 72.5° | 3969.7 | 4238.1 | 4503.4 | 4565.8 | 4625.1 | 4821.7 | 4737.4 | 3916.7 | 2796.3 | 1563.5 | 327.7  |
| 75°   | 4263.1 | 4434.7 | 4603.2 | 4490.9 | 4378.5 | 4113.3 | 3635.8 | 2855.6 | 2047.3 | 1164.1 | 280.9  |
| 77.5° | 4397.3 | 4356.7 | 4313.0 | 3929.1 | 3545.3 | 2833.7 | 2259.5 | 1650.9 | 1039.2 | 639.8  | 240.3  |
| 80°   | 3576.5 | 3414.2 | 3248.8 | 2605.9 | 1963.0 | 1342.0 | 880.1  | 558.6  | 380.7  | 287.1  | 193.5  |
| 82.5° | 2094.1 | 1716.5 | 1338.8 | 983.1  | 627.3  | 440.0  | 287.1  | 227.8  | 177.9  | 168.5  | 156.0  |
| 85°   | 677.2  | 599.2  | 521.2  | 412.0  | 302.7  | 187.3  | 109.2  | 99.9   | 93.6   | 103.0  | 109.2  |
| 87.5° | 90.5   | 90.5   | 87.4   | 65.5   | 40.6   | 21.8   | 12.5   | 9.4    | 9.4    | 12.5   | 12.5   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560945

CATALOG NUMBER: SDL-PA1-70-750-U-T4W

**CANDELA DISTRIBUTION (continued):**

|       | 110°  | 115°  | 120°  | 125°  | 130°  | 135°  | 140°  | 145°  | 150°  | 155°  | 160°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 983.1 | 983.1 | 983.1 | 983.1 | 983.1 | 983.1 | 983.1 | 983.1 | 983.1 | 983.1 | 983.1 |
| 2.5°  | 970.6 | 967.5 | 964.3 | 961.2 | 958.1 | 951.9 | 926.9 | 901.9 | 892.6 | 880.1 | 870.7 |
| 5°    | 914.4 | 883.2 | 861.4 | 839.5 | 830.1 | 817.7 | 820.8 | 823.9 | 827.0 | 827.0 | 827.0 |
| 7.5°  | 792.7 | 798.9 | 802.1 | 802.1 | 811.4 | 817.7 | 823.9 | 827.0 | 814.5 | 802.1 | 786.5 |
| 10°   | 630.4 | 621.0 | 633.5 | 642.9 | 658.5 | 671.0 | 711.6 | 752.1 | 789.6 | 827.0 | 842.6 |
| 12.5° | 574.2 | 605.4 | 580.5 | 555.5 | 605.4 | 652.3 | 708.4 | 764.6 | 798.9 | 830.1 | 802.1 |
| 15°   | 583.6 | 530.5 | 536.8 | 539.9 | 602.3 | 661.6 | 627.3 | 593.0 | 689.7 | 783.3 | 811.4 |
| 17.5° | 574.2 | 564.9 | 599.2 | 630.4 | 571.1 | 511.8 | 596.1 | 677.2 | 720.9 | 764.6 | 752.1 |
| 20°   | 621.0 | 552.4 | 552.4 | 552.4 | 605.4 | 658.5 | 617.9 | 577.4 | 624.2 | 671.0 | 749.0 |
| 22.5° | 642.9 | 667.9 | 617.9 | 564.9 | 599.2 | 633.5 | 633.5 | 630.4 | 683.5 | 733.4 | 720.9 |
| 25°   | 649.1 | 555.5 | 599.2 | 639.8 | 617.9 | 593.0 | 621.0 | 646.0 | 661.6 | 677.2 | 745.9 |
| 27.5° | 742.8 | 677.2 | 627.3 | 574.2 | 614.8 | 655.4 | 646.0 | 636.7 | 649.1 | 661.6 | 677.2 |
| 30°   | 880.1 | 727.2 | 671.0 | 611.7 | 589.8 | 564.9 | 593.0 | 617.9 | 664.7 | 711.6 | 774.0 |
| 32.5° | 920.6 | 786.5 | 695.9 | 602.3 | 599.2 | 593.0 | 602.3 | 608.6 | 661.6 | 711.6 | 798.9 |
| 35°   | 914.4 | 761.5 | 674.1 | 583.6 | 564.9 | 546.1 | 561.8 | 574.2 | 652.3 | 730.3 | 814.5 |
| 37.5° | 908.2 | 724.0 | 633.5 | 543.0 | 530.5 | 514.9 | 530.5 | 546.1 | 605.4 | 664.7 | 742.8 |
| 40°   | 898.8 | 680.3 | 593.0 | 502.5 | 486.9 | 471.2 | 486.9 | 499.3 | 546.1 | 593.0 | 655.4 |
| 42.5° | 877.0 | 636.7 | 549.3 | 458.8 | 446.3 | 430.7 | 443.2 | 455.6 | 496.2 | 536.8 | 574.2 |
| 45°   | 852.0 | 586.7 | 502.5 | 418.2 | 405.7 | 393.2 | 402.6 | 408.8 | 446.3 | 480.6 | 499.3 |
| 47.5° | 823.9 | 533.7 | 455.6 | 377.6 | 365.1 | 352.7 | 362.0 | 368.3 | 396.3 | 424.4 | 430.7 |
| 50°   | 817.7 | 490.0 | 418.2 | 343.3 | 333.9 | 321.4 | 327.7 | 333.9 | 355.8 | 374.5 | 374.5 |
| 52.5° | 805.2 | 436.9 | 377.6 | 315.2 | 309.0 | 299.6 | 302.7 | 305.8 | 321.4 | 337.1 | 333.9 |
| 55°   | 795.8 | 399.5 | 346.4 | 293.4 | 287.1 | 277.8 | 280.9 | 284.0 | 299.6 | 312.1 | 309.0 |
| 57.5° | 805.2 | 368.3 | 321.4 | 271.5 | 265.3 | 259.0 | 265.3 | 271.5 | 287.1 | 302.7 | 302.7 |
| 60°   | 774.0 | 337.1 | 293.4 | 249.7 | 246.5 | 240.3 | 255.9 | 268.4 | 293.4 | 315.2 | 321.4 |
| 62.5° | 661.6 | 309.0 | 271.5 | 234.1 | 237.2 | 237.2 | 265.3 | 290.2 | 324.6 | 355.8 | 362.0 |
| 65°   | 508.7 | 287.1 | 255.9 | 221.6 | 237.2 | 252.8 | 290.2 | 327.7 | 358.9 | 390.1 | 380.7 |
| 67.5° | 390.1 | 271.5 | 246.5 | 218.5 | 252.8 | 284.0 | 318.3 | 352.7 | 368.3 | 380.7 | 365.1 |
| 70°   | 327.7 | 255.9 | 237.2 | 215.3 | 249.7 | 284.0 | 318.3 | 352.7 | 358.9 | 365.1 | 349.5 |
| 72.5° | 287.1 | 243.4 | 224.7 | 206.0 | 234.1 | 262.2 | 302.7 | 340.2 | 346.4 | 349.5 | 333.9 |
| 75°   | 255.9 | 227.8 | 206.0 | 184.1 | 212.2 | 237.2 | 277.8 | 318.3 | 324.6 | 327.7 | 315.2 |
| 77.5° | 224.7 | 209.1 | 184.1 | 159.2 | 187.3 | 215.3 | 252.8 | 290.2 | 299.6 | 309.0 | 293.4 |
| 80°   | 187.3 | 177.9 | 159.2 | 140.4 | 171.6 | 199.7 | 234.1 | 268.4 | 277.8 | 287.1 | 271.5 |
| 82.5° | 149.8 | 143.6 | 131.1 | 118.6 | 149.8 | 181.0 | 215.3 | 246.5 | 255.9 | 262.2 | 243.4 |
| 85°   | 109.2 | 109.2 | 103.0 | 96.7  | 128.0 | 156.0 | 177.9 | 199.7 | 196.6 | 193.5 | 181.0 |
| 87.5° | 15.6  | 15.6  | 21.8  | 28.1  | 37.5  | 43.7  | 56.2  | 65.5  | 68.7  | 68.7  | 53.1  |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

REPORT NUMBER: P560945

CATALOG NUMBER: SDL-PA1-70-750-U-T4W

**CANDELA DISTRIBUTION (continued):**

|       | 165°  | 170°  | 175°  | 180°  |
|-------|-------|-------|-------|-------|
| 0°    | 983.1 | 983.1 | 983.1 | 983.1 |
| 2.5°  | 861.4 | 861.4 | 858.2 | 864.5 |
| 5°    | 827.0 | 830.1 | 830.1 | 833.3 |
| 7.5°  | 770.8 | 755.2 | 736.5 | 739.6 |
| 10°   | 858.2 | 861.4 | 864.5 | 864.5 |
| 12.5° | 770.8 | 758.4 | 742.8 | 745.9 |
| 15°   | 836.4 | 845.7 | 855.1 | 858.2 |
| 17.5° | 736.5 | 733.4 | 730.3 | 727.2 |
| 20°   | 823.9 | 839.5 | 855.1 | 855.1 |
| 22.5° | 708.4 | 708.4 | 708.4 | 711.6 |
| 25°   | 814.5 | 833.3 | 848.9 | 848.9 |
| 27.5° | 689.7 | 733.4 | 777.1 | 811.4 |
| 30°   | 833.3 | 842.6 | 852.0 | 855.1 |
| 32.5° | 883.2 | 930.0 | 973.7 | 983.1 |
| 35°   | 895.7 | 917.5 | 936.3 | 945.6 |
| 37.5° | 820.8 | 839.5 | 858.2 | 870.7 |
| 40°   | 714.7 | 730.3 | 745.9 | 755.2 |
| 42.5° | 608.6 | 611.7 | 614.8 | 630.4 |
| 45°   | 518.1 | 502.5 | 486.9 | 483.7 |
| 47.5° | 433.8 | 412.0 | 390.1 | 387.0 |
| 50°   | 371.4 | 352.7 | 333.9 | 333.9 |
| 52.5° | 327.7 | 315.2 | 302.7 | 302.7 |
| 55°   | 305.8 | 299.6 | 290.2 | 290.2 |
| 57.5° | 302.7 | 299.6 | 296.5 | 296.5 |
| 60°   | 324.6 | 327.7 | 327.7 | 327.7 |
| 62.5° | 365.1 | 368.3 | 368.3 | 368.3 |
| 65°   | 368.3 | 362.0 | 355.8 | 355.8 |
| 67.5° | 349.5 | 340.2 | 330.8 | 324.6 |
| 70°   | 330.8 | 324.6 | 315.2 | 305.8 |
| 72.5° | 315.2 | 309.0 | 299.6 | 290.2 |
| 75°   | 299.6 | 290.2 | 277.8 | 271.5 |
| 77.5° | 277.8 | 271.5 | 262.2 | 255.9 |
| 80°   | 252.8 | 246.5 | 237.2 | 224.7 |
| 82.5° | 224.7 | 227.8 | 227.8 | 196.6 |
| 85°   | 165.4 | 156.0 | 143.6 | 118.6 |
| 87.5° | 34.3  | 31.2  | 25.0  | 21.8  |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   |



Report Generated By 670245982









--- HS --- SS



u









(END OF REPORT)