

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560049

Luminaire Tested: **SDL-PA1-20-750-U-SL3**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560049  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-20-750-U-SL3  
Description: Springdale  
(1) 70 CRI, 5000K, 260mA LIGHT ENGINE WITH 24 LEDS AND TYPE III SPILL  
LIGHT ELIMINATOR OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2741 lumens  
Efficiency: N/A  
Efficacy: 130.5 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type III - Medium  
BUG Rating: B1 - U0 - G2

Input Watts (W): 21  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P560049

CATALOG NUMBER: SDL-PA1-20-750-U-SL3

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 7.8 fc  
 Type III - Medium - N/A

REPORT NUMBER: P560049

CATALOG NUMBER: SDL-PA1-20-750-U-SL3

## Luminous Intensity Polar Plot



— Vertical Plane Through 60-Deg Lateral      - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P560049

CATALOG NUMBER: SDL-PA1-20-750-U-SL3


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 440.6    | 0.0    | 440.6  |
|                    | % Fixture | 16.1     | 0.0    | 16.1   |
| <b>Street Side</b> | Lumens    | 2300.4   | 0.0    | 2300.4 |
|                    | % Fixture | 83.9     | 0.0    | 83.9   |
| <b>Total</b>       | Lumens    | 2741.0   | 0.0    | 2741.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 57.0   | 2.1       |
| 10°-20°   | 102.9  | 3.8       |
| 20°-30°   | 134.8  | 4.9       |
| 30°-40°   | 222.4  | 8.1       |
| 40°-50°   | 347.4  | 12.7      |
| 50°-60°   | 528.8  | 19.3      |
| 60°-70°   | 655.3  | 23.9      |
| 70°-80°   | 578.9  | 21.1      |
| 80°-90°   | 113.5  | 4.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 2741.0 | 100.0     |
| 0°-180°   | 2741.0 | 100.0     |



REPORT NUMBER: P560049


CATALOG NUMBER: SDL-PA1-20-750-U-SL3

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 180.0  | 6.6       |                         |      |         |
| FM   | (30°-60°)   | 940.8  | 34.3      |                         |      |         |
| FH   | (60°-80°)   | 1077.0 | 39.3      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 102.7  | 3.7       |                         |      | G2/225  |
| BL   | (0°-30°)    | 114.8  | 4.2       | B1/500                  |      |         |
| BM   | (30°-60°)   | 157.9  | 5.8       | B0/220                  |      |         |
| BH   | (60°-80°)   | 157.1  | 5.7       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 10.8   | 0.4       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type III Medium



REPORT NUMBER: P560049

CATALOG NUMBER: SDL-PA1-20-750-U-SL3

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°   | 40°    | 45°    | 50°    |
|-------|--------|--------|--------|--------|--------|--------|--------|-------|--------|--------|--------|
| 0°    | 781.8  | 781.8  | 781.8  | 781.8  | 781.8  | 781.8  | 781.8  | 781.8 | 781.8  | 781.8  | 781.8  |
| 2.5°  | 649.4  | 722.6  | 705.6  | 688.5  | 714.6  | 739.7  | 747.7  | 754.7 | 758.8  | 762.8  | 766.8  |
| 5°    | 603.2  | 604.2  | 605.2  | 606.2  | 609.2  | 611.2  | 615.2  | 619.3 | 623.3  | 626.3  | 630.3  |
| 7.5°  | 465.7  | 481.8  | 507.8  | 533.9  | 550.0  | 565.1  | 574.1  | 582.1 | 588.1  | 594.2  | 600.2  |
| 10°   | 517.9  | 520.9  | 521.9  | 521.9  | 526.9  | 531.9  | 493.8  | 454.7 | 473.7  | 492.8  | 471.7  |
| 12.5° | 406.5  | 417.5  | 450.6  | 482.8  | 492.8  | 501.8  | 483.8  | 465.7 | 437.6  | 408.5  | 406.5  |
| 15°   | 466.7  | 469.7  | 470.7  | 470.7  | 439.6  | 408.5  | 387.4  | 365.3 | 382.4  | 398.4  | 361.3  |
| 17.5° | 361.3  | 364.3  | 390.4  | 416.5  | 421.5  | 426.6  | 404.5  | 382.4 | 333.2  | 283.0  | 330.2  |
| 20°   | 429.6  | 431.6  | 431.6  | 431.6  | 379.4  | 327.2  | 331.2  | 334.2 | 350.3  | 366.3  | 353.3  |
| 22.5° | 346.3  | 346.3  | 346.3  | 346.3  | 362.3  | 377.4  | 345.3  | 313.1 | 331.2  | 349.3  | 333.2  |
| 25°   | 435.6  | 438.6  | 431.6  | 423.5  | 375.4  | 327.2  | 342.2  | 357.3 | 330.2  | 303.1  | 327.2  |
| 27.5° | 397.4  | 394.4  | 380.4  | 365.3  | 372.4  | 379.4  | 346.3  | 313.1 | 334.2  | 355.3  | 345.3  |
| 30°   | 527.9  | 518.9  | 503.8  | 488.8  | 431.6  | 374.4  | 365.3  | 356.3 | 338.2  | 319.2  | 340.2  |
| 32.5° | 701.6  | 678.5  | 608.2  | 538.0  | 502.8  | 467.7  | 422.5  | 377.4 | 373.4  | 368.3  | 374.4  |
| 35°   | 747.7  | 732.7  | 703.6  | 673.4  | 613.2  | 552.0  | 494.8  | 436.6 | 417.5  | 397.4  | 401.5  |
| 37.5° | 756.8  | 751.7  | 745.7  | 738.7  | 677.5  | 616.2  | 554.0  | 491.8 | 471.7  | 450.6  | 435.6  |
| 40°   | 763.8  | 767.8  | 778.8  | 788.9  | 727.6  | 665.4  | 609.2  | 552.0 | 530.9  | 508.9  | 482.8  |
| 42.5° | 795.9  | 806.9  | 821.0  | 834.0  | 777.8  | 721.6  | 672.4  | 623.3 | 596.2  | 569.1  | 545.0  |
| 45°   | 870.2  | 876.2  | 891.2  | 905.3  | 852.1  | 797.9  | 741.7  | 684.5 | 661.4  | 638.3  | 614.2  |
| 47.5° | 978.6  | 988.6  | 987.6  | 986.6  | 927.4  | 867.2  | 803.9  | 739.7 | 724.6  | 708.6  | 685.5  |
| 50°   | 1115.1 | 1108.0 | 1089.0 | 1069.9 | 1005.7 | 940.4  | 866.1  | 790.9 | 783.8  | 775.8  | 756.8  |
| 52.5° | 1183.3 | 1178.3 | 1152.2 | 1125.1 | 1059.9 | 994.6  | 914.3  | 833.0 | 842.1  | 851.1  | 833.0  |
| 55°   | 1187.3 | 1184.3 | 1165.2 | 1146.2 | 1082.9 | 1019.7 | 948.4  | 877.2 | 899.3  | 921.3  | 914.3  |
| 57.5° | 1158.2 | 1159.2 | 1153.2 | 1146.2 | 1090.0 | 1033.8 | 974.5  | 915.3 | 953.5  | 990.6  | 997.6  |
| 60°   | 1083.9 | 1099.0 | 1109.0 | 1119.1 | 1083.9 | 1048.8 | 997.6  | 946.4 | 1004.7 | 1062.9 | 1081.9 |
| 62.5° | 946.4  | 959.5  | 995.6  | 1030.7 | 1037.8 | 1043.8 | 1009.7 | 974.5 | 1052.8 | 1130.1 | 1161.2 |
| 65°   | 733.7  | 751.7  | 805.9  | 860.1  | 916.3  | 972.5  | 980.6  | 988.6 | 1121.1 | 1253.6 | 1279.7 |
| 67.5° | 457.7  | 467.7  | 524.9  | 581.1  | 694.5  | 806.9  | 871.2  | 935.4 | 1164.2 | 1392.1 | 1433.2 |
| 70°   | 241.9  | 256.9  | 285.0  | 312.1  | 409.5  | 506.8  | 637.3  | 767.8 | 1099.0 | 1430.2 | 1598.8 |
| 72.5° | 183.7  | 189.7  | 204.7  | 219.8  | 253.9  | 288.0  | 370.3  | 452.6 | 860.1  | 1266.6 | 1655.0 |
| 75°   | 132.5  | 137.5  | 153.6  | 168.6  | 202.7  | 235.9  | 270.0  | 303.1 | 530.9  | 758.8  | 1372.0 |
| 77.5° | 77.3   | 79.3   | 87.3   | 94.3   | 147.5  | 200.7  | 237.9  | 274.0 | 329.2  | 383.4  | 979.6  |
| 80°   | 53.2   | 54.2   | 57.2   | 60.2   | 83.3   | 106.4  | 177.6  | 248.9 | 274.0  | 298.1  | 649.4  |
| 82.5° | 35.1   | 40.1   | 42.2   | 44.2   | 52.2   | 60.2   | 104.4  | 147.5 | 216.8  | 285.0  | 443.6  |
| 85°   | 18.1   | 20.1   | 24.1   | 27.1   | 31.1   | 34.1   | 47.2   | 59.2  | 179.7  | 299.1  | 319.2  |
| 87.5° | 2.0    | 3.0    | 4.0    | 4.0    | 5.0    | 6.0    | 9.0    | 12.0  | 54.2   | 96.4   | 82.3   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560049

CATALOG NUMBER: SDL-PA1-20-750-U-SL3

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°  | 105°  |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|-------|
| 0°    | 781.8  | 781.8  | 781.8  | 781.8  | 781.8  | 781.8  | 781.8  | 781.8  | 781.8  | 781.8 | 781.8 |
| 2.5°  | 770.8  | 772.8  | 771.8  | 773.8  | 774.8  | 775.8  | 776.8  | 776.8  | 775.8  | 773.8 | 771.8 |
| 5°    | 634.3  | 674.5  | 742.7  | 749.7  | 756.8  | 758.8  | 760.8  | 761.8  | 759.8  | 756.8 | 753.7 |
| 7.5°  | 605.2  | 611.2  | 550.0  | 599.2  | 647.4  | 651.4  | 654.4  | 652.4  | 653.4  | 626.3 | 598.2 |
| 10°   | 450.6  | 455.7  | 457.7  | 472.7  | 486.8  | 519.9  | 553.0  | 548.0  | 544.0  | 495.8 | 446.6 |
| 12.5° | 404.5  | 430.6  | 436.6  | 411.5  | 386.4  | 420.5  | 454.7  | 450.6  | 443.6  | 399.5 | 355.3 |
| 15°   | 324.2  | 297.1  | 355.3  | 409.5  | 462.7  | 494.8  | 525.9  | 516.9  | 508.9  | 452.6 | 395.4 |
| 17.5° | 376.4  | 392.4  | 373.4  | 381.4  | 389.4  | 413.5  | 436.6  | 422.5  | 417.5  | 378.4 | 338.2 |
| 20°   | 340.2  | 339.2  | 326.2  | 373.4  | 420.5  | 467.7  | 513.9  | 499.8  | 475.7  | 399.5 | 322.2 |
| 22.5° | 317.2  | 382.4  | 410.5  | 404.5  | 397.4  | 379.4  | 360.3  | 348.3  | 330.2  | 313.1 | 295.1 |
| 25°   | 350.3  | 323.2  | 345.3  | 417.5  | 488.8  | 501.8  | 514.9  | 484.8  | 445.6  | 368.3 | 291.1 |
| 27.5° | 335.2  | 377.4  | 405.5  | 453.6  | 500.8  | 546.0  | 591.1  | 551.0  | 499.8  | 403.5 | 306.1 |
| 30°   | 361.3  | 384.4  | 462.7  | 553.0  | 643.3  | 659.4  | 674.5  | 619.3  | 551.0  | 453.6 | 356.3 |
| 32.5° | 380.4  | 441.6  | 510.9  | 581.1  | 650.4  | 662.4  | 674.5  | 612.2  | 533.9  | 426.6 | 319.2 |
| 35°   | 404.5  | 449.6  | 512.9  | 595.2  | 677.5  | 680.5  | 682.5  | 610.2  | 521.9  | 400.5 | 278.0 |
| 37.5° | 420.5  | 471.7  | 540.0  | 627.3  | 714.6  | 708.6  | 701.6  | 619.3  | 517.9  | 382.4 | 246.9 |
| 40°   | 456.7  | 500.8  | 574.1  | 663.4  | 752.7  | 742.7  | 732.7  | 638.3  | 518.9  | 364.3 | 208.8 |
| 42.5° | 519.9  | 537.0  | 616.2  | 711.6  | 806.9  | 795.9  | 783.8  | 671.4  | 530.9  | 354.3 | 176.6 |
| 45°   | 589.1  | 597.2  | 665.4  | 773.8  | 882.2  | 868.2  | 854.1  | 722.6  | 553.0  | 349.3 | 145.5 |
| 47.5° | 661.4  | 659.4  | 722.6  | 854.1  | 984.6  | 954.5  | 924.4  | 782.8  | 594.2  | 359.3 | 124.5 |
| 50°   | 736.7  | 733.7  | 794.9  | 936.4  | 1077.9 | 1045.8 | 1013.7 | 855.1  | 641.3  | 377.4 | 112.4 |
| 52.5° | 814.0  | 821.0  | 866.1  | 1013.7 | 1160.2 | 1131.1 | 1101.0 | 933.4  | 687.5  | 397.4 | 107.4 |
| 55°   | 906.3  | 928.4  | 946.4  | 1094.0 | 1241.5 | 1212.4 | 1182.3 | 1013.7 | 751.7  | 428.6 | 105.4 |
| 57.5° | 1003.6 | 1032.8 | 1040.8 | 1175.3 | 1309.8 | 1290.7 | 1270.6 | 1090.0 | 817.0  | 464.7 | 111.4 |
| 60°   | 1101.0 | 1139.1 | 1168.2 | 1276.6 | 1384.0 | 1362.0 | 1339.9 | 1167.2 | 878.2  | 504.8 | 131.5 |
| 62.5° | 1191.3 | 1244.5 | 1291.7 | 1371.0 | 1449.3 | 1423.2 | 1397.1 | 1234.5 | 947.4  | 560.0 | 171.6 |
| 65°   | 1304.7 | 1351.9 | 1403.1 | 1455.3 | 1506.5 | 1481.4 | 1456.3 | 1318.8 | 1039.8 | 629.3 | 217.8 |
| 67.5° | 1474.4 | 1488.4 | 1514.5 | 1546.6 | 1577.7 | 1562.7 | 1546.6 | 1422.2 | 1120.1 | 669.4 | 217.8 |
| 70°   | 1766.4 | 1735.3 | 1696.2 | 1695.2 | 1693.2 | 1669.1 | 1644.0 | 1480.4 | 1125.1 | 653.4 | 181.7 |
| 72.5° | 2042.4 | 2148.8 | 2024.4 | 1934.0 | 1843.7 | 1737.3 | 1629.9 | 1402.1 | 993.6  | 569.1 | 144.5 |
| 75°   | 1984.2 | 2397.7 | 2337.5 | 2092.6 | 1847.7 | 1655.0 | 1462.3 | 1221.4 | 818.0  | 470.7 | 123.4 |
| 77.5° | 1574.7 | 2115.7 | 2172.9 | 1948.1 | 1722.3 | 1461.3 | 1199.4 | 944.4  | 567.1  | 335.2 | 103.4 |
| 80°   | 999.6  | 1581.8 | 1591.8 | 1383.0 | 1173.3 | 893.2  | 613.2  | 411.5  | 273.0  | 177.6 | 82.3  |
| 82.5° | 602.2  | 936.4  | 815.0  | 584.1  | 353.3  | 244.9  | 135.5  | 130.5  | 100.4  | 74.3  | 48.2  |
| 85°   | 339.2  | 458.7  | 329.2  | 215.8  | 102.4  | 73.3   | 43.2   | 46.2   | 44.2   | 36.1  | 27.1  |
| 87.5° | 67.2   | 79.3   | 54.2   | 31.1   | 8.0    | 8.0    | 7.0    | 7.0    | 5.0    | 5.0   | 4.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |



REPORT NUMBER: P560049

CATALOG NUMBER: SDL-PA1-20-750-U-SL3

**CANDELA DISTRIBUTION (continued):**

|       | 110°  | 115°  | 120°  | 125°  | 130°  | 135°  | 140°  | 145°  | 150°  | 155°  | 160°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 781.8 | 781.8 | 781.8 | 781.8 | 781.8 | 781.8 | 781.8 | 781.8 | 781.8 | 781.8 | 781.8 |
| 2.5°  | 771.8 | 771.8 | 769.8 | 767.8 | 766.8 | 765.8 | 735.7 | 705.6 | 685.5 | 664.4 | 659.4 |
| 5°    | 716.6 | 679.5 | 651.4 | 623.3 | 617.2 | 611.2 | 610.2 | 609.2 | 606.2 | 602.2 | 601.2 |
| 7.5°  | 566.1 | 532.9 | 556.0 | 578.1 | 574.1 | 569.1 | 566.1 | 562.0 | 555.0 | 548.0 | 512.9 |
| 10°   | 435.6 | 424.5 | 424.5 | 423.5 | 415.5 | 407.5 | 425.5 | 443.6 | 463.7 | 483.8 | 481.8 |
| 12.5° | 371.4 | 386.4 | 347.3 | 307.1 | 329.2 | 350.3 | 370.3 | 389.4 | 399.5 | 409.5 | 378.4 |
| 15°   | 350.3 | 304.1 | 291.1 | 278.0 | 288.0 | 298.1 | 269.0 | 238.9 | 262.0 | 285.0 | 290.1 |
| 17.5° | 314.1 | 290.1 | 277.0 | 263.0 | 224.8 | 185.7 | 198.7 | 211.8 | 210.8 | 209.8 | 204.7 |
| 20°   | 293.1 | 263.0 | 239.9 | 215.8 | 197.7 | 179.7 | 160.6 | 140.5 | 131.5 | 121.4 | 145.5 |
| 22.5° | 279.0 | 263.0 | 214.8 | 166.6 | 152.6 | 138.5 | 123.4 | 107.4 | 113.4 | 118.4 | 122.4 |
| 25°   | 243.9 | 195.7 | 168.6 | 141.5 | 119.4 | 96.4  | 97.4  | 98.4  | 93.3  | 88.3  | 111.4 |
| 27.5° | 246.9 | 186.7 | 144.5 | 102.4 | 94.3  | 85.3  | 80.3  | 74.3  | 82.3  | 89.3  | 91.3  |
| 30°   | 258.9 | 161.6 | 122.4 | 83.3  | 74.3  | 65.2  | 68.2  | 70.3  | 70.3  | 70.3  | 80.3  |
| 32.5° | 229.8 | 140.5 | 104.4 | 67.2  | 62.2  | 56.2  | 57.2  | 57.2  | 62.2  | 67.2  | 72.3  |
| 35°   | 194.7 | 110.4 | 85.3  | 59.2  | 54.2  | 49.2  | 51.2  | 53.2  | 58.2  | 63.2  | 70.3  |
| 37.5° | 167.6 | 87.3  | 70.3  | 53.2  | 50.2  | 47.2  | 48.2  | 49.2  | 54.2  | 58.2  | 64.2  |
| 40°   | 141.5 | 73.3  | 62.2  | 51.2  | 48.2  | 45.2  | 46.2  | 46.2  | 50.2  | 54.2  | 58.2  |
| 42.5° | 122.4 | 67.2  | 59.2  | 50.2  | 47.2  | 43.2  | 44.2  | 44.2  | 47.2  | 50.2  | 53.2  |
| 45°   | 105.4 | 64.2  | 57.2  | 49.2  | 46.2  | 42.2  | 42.2  | 41.1  | 44.2  | 46.2  | 48.2  |
| 47.5° | 94.3  | 63.2  | 56.2  | 49.2  | 45.2  | 40.1  | 39.1  | 38.1  | 41.1  | 43.2  | 46.2  |
| 50°   | 88.3  | 63.2  | 56.2  | 48.2  | 43.2  | 38.1  | 37.1  | 36.1  | 40.1  | 43.2  | 48.2  |
| 52.5° | 86.3  | 64.2  | 56.2  | 48.2  | 42.2  | 36.1  | 36.1  | 36.1  | 43.2  | 50.2  | 52.2  |
| 55°   | 86.3  | 66.2  | 57.2  | 47.2  | 41.1  | 35.1  | 37.1  | 39.1  | 41.1  | 43.2  | 43.2  |
| 57.5° | 88.3  | 65.2  | 55.2  | 45.2  | 41.1  | 36.1  | 35.1  | 34.1  | 35.1  | 36.1  | 36.1  |
| 60°   | 97.4  | 63.2  | 53.2  | 43.2  | 38.1  | 33.1  | 32.1  | 31.1  | 33.1  | 34.1  | 34.1  |
| 62.5° | 117.4 | 62.2  | 53.2  | 43.2  | 37.1  | 31.1  | 31.1  | 30.1  | 31.1  | 32.1  | 33.1  |
| 65°   | 143.5 | 69.3  | 56.2  | 43.2  | 37.1  | 31.1  | 29.1  | 27.1  | 29.1  | 30.1  | 30.1  |
| 67.5° | 149.5 | 81.3  | 65.2  | 48.2  | 39.1  | 30.1  | 28.1  | 26.1  | 28.1  | 29.1  | 29.1  |
| 70°   | 135.5 | 89.3  | 70.3  | 51.2  | 41.1  | 30.1  | 28.1  | 25.1  | 26.1  | 27.1  | 26.1  |
| 72.5° | 116.4 | 87.3  | 69.3  | 50.2  | 40.1  | 29.1  | 27.1  | 24.1  | 25.1  | 25.1  | 24.1  |
| 75°   | 99.4  | 75.3  | 59.2  | 42.2  | 34.1  | 25.1  | 23.1  | 21.1  | 22.1  | 22.1  | 22.1  |
| 77.5° | 83.3  | 62.2  | 48.2  | 33.1  | 27.1  | 20.1  | 19.1  | 18.1  | 19.1  | 20.1  | 19.1  |
| 80°   | 65.2  | 47.2  | 36.1  | 24.1  | 20.1  | 15.1  | 16.1  | 16.1  | 17.1  | 17.1  | 17.1  |
| 82.5° | 38.1  | 28.1  | 23.1  | 17.1  | 14.1  | 11.0  | 12.0  | 13.0  | 14.1  | 14.1  | 14.1  |
| 85°   | 23.1  | 18.1  | 15.1  | 12.0  | 10.0  | 7.0   | 9.0   | 10.0  | 10.0  | 10.0  | 9.0   |
| 87.5° | 4.0   | 4.0   | 4.0   | 4.0   | 3.0   | 2.0   | 4.0   | 5.0   | 5.0   | 5.0   | 4.0   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

REPORT NUMBER: P560049

CATALOG NUMBER: SDL-PA1-20-750-U-SL3

**CANDELA DISTRIBUTION (continued):**

|       | 165°  | 170°  | 175°  | 180°  |
|-------|-------|-------|-------|-------|
| 0°    | 781.8 | 781.8 | 781.8 | 781.8 |
| 2.5°  | 653.4 | 653.4 | 652.4 | 652.4 |
| 5°    | 600.2 | 598.2 | 596.2 | 598.2 |
| 7.5°  | 477.7 | 463.7 | 449.6 | 453.6 |
| 10°   | 478.7 | 477.7 | 476.7 | 475.7 |
| 12.5° | 346.3 | 335.2 | 324.2 | 317.2 |
| 15°   | 294.1 | 291.1 | 287.0 | 287.0 |
| 17.5° | 198.7 | 189.7 | 180.7 | 174.6 |
| 20°   | 169.6 | 174.6 | 178.6 | 180.7 |
| 22.5° | 126.5 | 130.5 | 134.5 | 136.5 |
| 25°   | 133.5 | 143.5 | 152.6 | 153.6 |
| 27.5° | 92.3  | 97.4  | 101.4 | 99.4  |
| 30°   | 90.3  | 93.3  | 96.4  | 96.4  |
| 32.5° | 77.3  | 85.3  | 93.3  | 94.3  |
| 35°   | 77.3  | 81.3  | 85.3  | 86.3  |
| 37.5° | 69.3  | 72.3  | 74.3  | 75.3  |
| 40°   | 62.2  | 64.2  | 65.2  | 65.2  |
| 42.5° | 55.2  | 60.2  | 64.2  | 64.2  |
| 45°   | 49.2  | 62.2  | 75.3  | 79.3  |
| 47.5° | 48.2  | 67.2  | 86.3  | 90.3  |
| 50°   | 52.2  | 70.3  | 87.3  | 89.3  |
| 52.5° | 53.2  | 63.2  | 72.3  | 72.3  |
| 55°   | 42.2  | 47.2  | 51.2  | 50.2  |
| 57.5° | 36.1  | 40.1  | 43.2  | 43.2  |
| 60°   | 34.1  | 39.1  | 43.2  | 44.2  |
| 62.5° | 33.1  | 35.1  | 37.1  | 39.1  |
| 65°   | 30.1  | 30.1  | 30.1  | 30.1  |
| 67.5° | 28.1  | 28.1  | 27.1  | 27.1  |
| 70°   | 25.1  | 25.1  | 25.1  | 25.1  |
| 72.5° | 23.1  | 23.1  | 23.1  | 22.1  |
| 75°   | 21.1  | 21.1  | 20.1  | 20.1  |
| 77.5° | 18.1  | 18.1  | 18.1  | 18.1  |
| 80°   | 16.1  | 16.1  | 15.1  | 15.1  |
| 82.5° | 13.0  | 13.0  | 12.0  | 11.0  |
| 85°   | 8.0   | 8.0   | 7.0   | 6.0   |
| 87.5° | 3.0   | 3.0   | 2.0   | 1.0   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   |



Report Generated By 670245982









--- HS --- SS



u









(END OF REPORT)