

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560221

Luminaire Tested: **SDL-PA1-30-750-U-5WQ**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560221  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-30-750-U-5WQ  
Description: Springdale  
(1) 70 CRI, 5000K, 375mA LIGHT ENGINE WITH 24 LEDS AND TYPE V WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3928 lumens  
Efficiency: N/A  
Efficacy: 130.5 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G2

Input Watts (W): 30.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.4 fc  
 Type V - Short - N/A

REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

## Luminous Intensity Polar Plot



— Vertical Plane Through 15-Deg Lateral      - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1964.0   | 0.0    | 1964.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 1964.0   | 0.0    | 1964.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 3928.0   | 0.0    | 3928.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 26.7   | 0.7       |
| 10°-20°   | 62.0   | 1.6       |
| 20°-30°   | 110.6  | 2.8       |
| 30°-40°   | 211.6  | 5.4       |
| 40°-50°   | 360.4  | 9.2       |
| 50°-60°   | 631.0  | 16.1      |
| 60°-70°   | 1064.7 | 27.1      |
| 70°-80°   | 1241.9 | 31.6      |
| 80°-90°   | 219.1  | 5.6       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 3928.0 | 100.0     |
| 0°-180°   | 3928.0 | 100.0     |



REPORT NUMBER: P560221


CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 99.7   | 2.5       |                         |      |         |
| FM   | (30°-60°)   | 601.5  | 15.3      |                         |      |         |
| FH   | (60°-80°)   | 1153.3 | 29.4      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 109.5  | 2.8       |                         |      | G2/225  |
| BL   | (0°-30°)    | 99.7   | 2.5       | B0/110                  |      |         |
| BM   | (30°-60°)   | 601.5  | 15.3      | B1/1000                 |      |         |
| BH   | (60°-80°)   | 1153.3 | 29.4      | B3/2500                 |      | G1/1800 |
| BVH  | (80°-90°)   | 109.5  | 2.8       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G2**

Type V Short





REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 301.4  | 302.8  | 302.8  | 302.8  | 302.8  | 301.4  | 301.4  | 305.5  | 309.7  | 313.8  | 318.0  |
| 5°    | 284.8  | 284.8  | 284.8  | 284.8  | 284.8  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  |
| 7.5°  | 243.3  | 246.1  | 247.5  | 253.0  | 257.1  | 262.7  | 266.8  | 268.2  | 269.6  | 269.6  | 271.0  |
| 10°   | 273.7  | 273.7  | 273.7  | 273.7  | 273.7  | 272.3  | 272.3  | 269.6  | 268.2  | 265.4  | 262.7  |
| 12.5° | 240.5  | 239.2  | 237.8  | 244.7  | 250.2  | 257.1  | 262.7  | 264.1  | 265.4  | 266.8  | 268.2  |
| 15°   | 276.5  | 276.5  | 276.5  | 275.1  | 273.7  | 272.3  | 271.0  | 261.3  | 251.6  | 240.5  | 230.9  |
| 17.5° | 235.0  | 236.4  | 236.4  | 243.3  | 248.8  | 255.8  | 261.3  | 258.5  | 255.8  | 251.6  | 248.8  |
| 20°   | 282.0  | 282.0  | 282.0  | 279.3  | 277.9  | 275.1  | 272.3  | 255.8  | 239.2  | 221.2  | 204.6  |
| 22.5° | 239.2  | 239.2  | 239.2  | 239.2  | 240.5  | 240.5  | 240.5  | 241.9  | 243.3  | 244.7  | 246.1  |
| 25°   | 291.7  | 293.1  | 293.1  | 290.3  | 288.9  | 286.2  | 283.4  | 269.6  | 254.4  | 240.5  | 225.3  |
| 27.5° | 251.6  | 251.6  | 251.6  | 250.2  | 248.8  | 246.1  | 244.7  | 247.5  | 251.6  | 254.4  | 257.1  |
| 30°   | 308.3  | 308.3  | 308.3  | 306.9  | 306.9  | 305.5  | 304.1  | 290.3  | 275.1  | 261.3  | 246.1  |
| 32.5° | 374.6  | 373.3  | 371.9  | 359.4  | 347.0  | 333.2  | 320.7  | 313.8  | 306.9  | 298.6  | 291.7  |
| 35°   | 398.1  | 398.1  | 396.8  | 394.0  | 391.2  | 387.1  | 384.3  | 370.5  | 356.7  | 342.9  | 329.0  |
| 37.5° | 421.7  | 421.7  | 420.3  | 418.9  | 416.1  | 414.7  | 412.0  | 396.8  | 382.9  | 367.7  | 352.5  |
| 40°   | 450.7  | 452.1  | 452.1  | 450.7  | 447.9  | 446.5  | 443.8  | 427.2  | 412.0  | 395.4  | 378.8  |
| 42.5° | 486.6  | 486.6  | 485.2  | 483.9  | 482.5  | 479.7  | 478.3  | 463.1  | 446.5  | 431.3  | 414.7  |
| 45°   | 529.5  | 529.5  | 528.1  | 526.7  | 526.7  | 525.3  | 524.0  | 510.1  | 494.9  | 481.1  | 465.9  |
| 47.5° | 582.0  | 580.6  | 579.3  | 577.9  | 575.1  | 573.7  | 571.0  | 555.8  | 541.9  | 526.7  | 511.5  |
| 50°   | 637.3  | 637.3  | 637.3  | 635.9  | 634.6  | 631.8  | 630.4  | 616.6  | 602.8  | 587.5  | 573.7  |
| 52.5° | 696.8  | 698.1  | 698.1  | 698.1  | 696.8  | 696.8  | 695.4  | 681.6  | 667.7  | 652.5  | 638.7  |
| 55°   | 767.3  | 767.3  | 767.3  | 767.3  | 768.7  | 768.7  | 768.7  | 754.8  | 741.0  | 727.2  | 713.4  |
| 57.5° | 847.5  | 853.0  | 857.1  | 857.1  | 857.1  | 857.1  | 857.1  | 843.3  | 829.5  | 815.7  | 801.8  |
| 60°   | 940.1  | 941.5  | 942.8  | 947.0  | 949.8  | 953.9  | 956.7  | 944.2  | 931.8  | 919.3  | 906.9  |
| 62.5° | 1031.3 | 1034.1 | 1035.5 | 1041.0 | 1045.1 | 1050.7 | 1054.8 | 1046.5 | 1036.8 | 1028.6 | 1018.9 |
| 65°   | 1125.3 | 1128.1 | 1129.5 | 1136.4 | 1144.7 | 1151.6 | 1158.5 | 1151.6 | 1146.1 | 1139.2 | 1132.2 |
| 67.5° | 1224.9 | 1227.6 | 1229.0 | 1235.9 | 1244.2 | 1251.1 | 1258.0 | 1255.3 | 1252.5 | 1249.7 | 1247.0 |
| 70°   | 1331.3 | 1332.7 | 1332.7 | 1339.6 | 1347.9 | 1354.8 | 1361.7 | 1360.3 | 1359.0 | 1357.6 | 1356.2 |
| 72.5° | 1389.4 | 1393.5 | 1397.7 | 1404.6 | 1411.5 | 1417.0 | 1423.9 | 1421.2 | 1417.0 | 1414.3 | 1410.1 |
| 75°   | 1314.7 | 1317.5 | 1320.3 | 1331.3 | 1343.8 | 1354.8 | 1365.9 | 1370.0 | 1375.6 | 1379.7 | 1383.8 |
| 77.5° | 1029.9 | 1042.4 | 1053.4 | 1065.9 | 1076.9 | 1089.4 | 1100.4 | 1123.9 | 1146.1 | 1169.6 | 1191.7 |
| 80°   | 510.1  | 517.0  | 524.0  | 551.6  | 579.3  | 606.9  | 634.6  | 676.0  | 718.9  | 760.4  | 801.8  |
| 82.5° | 123.0  | 123.0  | 123.0  | 138.2  | 152.1  | 167.3  | 181.1  | 218.4  | 257.1  | 294.5  | 331.8  |
| 85°   | 24.9   | 26.3   | 27.6   | 34.6   | 41.5   | 47.0   | 53.9   | 59.4   | 65.0   | 70.5   | 76.0   |
| 87.5° | 4.1    | 4.1    | 4.1    | 4.1    | 5.5    | 5.5    | 5.5    | 6.9    | 8.3    | 8.3    | 9.7    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 319.3  | 322.1  | 323.5  | 324.9  | 326.3  | 327.6  | 329.0  | 330.4  | 331.8  | 331.8  | 333.2  |
| 5°    | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 284.8  | 286.2  | 287.6  |
| 7.5°  | 272.3  | 273.7  | 275.1  | 276.5  | 276.5  | 276.5  | 275.1  | 275.1  | 273.7  | 273.7  | 272.3  |
| 10°   | 255.8  | 248.8  | 240.5  | 233.6  | 233.6  | 235.0  | 235.0  | 235.0  | 230.9  | 228.1  | 224.0  |
| 12.5° | 262.7  | 257.1  | 250.2  | 244.7  | 235.0  | 226.7  | 217.0  | 207.4  | 204.6  | 201.8  | 199.1  |
| 15°   | 222.6  | 215.7  | 207.4  | 199.1  | 194.9  | 189.4  | 185.3  | 179.7  | 178.3  | 177.0  | 174.2  |
| 17.5° | 241.9  | 235.0  | 226.7  | 219.8  | 206.0  | 192.2  | 178.3  | 164.5  | 171.4  | 179.7  | 186.6  |
| 20°   | 206.0  | 206.0  | 207.4  | 207.4  | 207.4  | 206.0  | 206.0  | 204.6  | 200.5  | 194.9  | 190.8  |
| 22.5° | 235.0  | 222.6  | 211.5  | 199.1  | 201.8  | 204.6  | 207.4  | 210.1  | 203.2  | 196.3  | 188.0  |
| 25°   | 229.5  | 233.6  | 236.4  | 240.5  | 229.5  | 218.4  | 206.0  | 194.9  | 200.5  | 206.0  | 211.5  |
| 27.5° | 248.8  | 240.5  | 230.9  | 222.6  | 226.7  | 230.9  | 233.6  | 237.8  | 230.9  | 224.0  | 217.0  |
| 30°   | 247.5  | 248.8  | 248.8  | 250.2  | 244.7  | 237.8  | 232.3  | 225.3  | 228.1  | 232.3  | 235.0  |
| 32.5° | 283.4  | 273.7  | 265.4  | 255.8  | 255.8  | 255.8  | 254.4  | 254.4  | 254.4  | 255.8  | 255.8  |
| 35°   | 316.6  | 305.5  | 293.1  | 280.6  | 277.9  | 276.5  | 273.7  | 271.0  | 273.7  | 276.5  | 279.3  |
| 37.5° | 340.1  | 326.3  | 313.8  | 300.0  | 298.6  | 297.2  | 294.5  | 293.1  | 293.1  | 293.1  | 293.1  |
| 40°   | 366.4  | 353.9  | 341.5  | 329.0  | 326.3  | 323.5  | 319.3  | 316.6  | 315.2  | 313.8  | 311.1  |
| 42.5° | 402.3  | 388.5  | 376.0  | 362.2  | 358.1  | 352.5  | 348.4  | 342.9  | 341.5  | 340.1  | 337.3  |
| 45°   | 449.3  | 431.3  | 414.7  | 396.8  | 391.2  | 387.1  | 381.6  | 376.0  | 374.6  | 371.9  | 370.5  |
| 47.5° | 492.2  | 474.2  | 454.8  | 435.5  | 432.7  | 428.6  | 425.8  | 421.7  | 418.9  | 414.7  | 412.0  |
| 50°   | 550.2  | 525.3  | 501.8  | 477.0  | 477.0  | 475.6  | 475.6  | 474.2  | 468.7  | 463.1  | 457.6  |
| 52.5° | 615.2  | 590.3  | 566.8  | 541.9  | 539.2  | 537.8  | 535.0  | 532.2  | 526.7  | 521.2  | 514.3  |
| 55°   | 688.5  | 663.6  | 638.7  | 613.8  | 612.4  | 612.4  | 611.0  | 609.7  | 601.4  | 593.1  | 584.8  |
| 57.5° | 776.9  | 753.4  | 728.6  | 703.7  | 705.1  | 705.1  | 706.4  | 706.4  | 695.4  | 684.3  | 671.9  |
| 60°   | 879.2  | 851.6  | 822.6  | 794.9  | 799.1  | 804.6  | 808.7  | 812.9  | 799.1  | 785.2  | 770.0  |
| 62.5° | 991.2  | 962.2  | 934.5  | 905.5  | 913.8  | 922.1  | 929.0  | 937.3  | 916.6  | 895.8  | 875.1  |
| 65°   | 1099.1 | 1065.9 | 1032.7 | 999.5  | 1014.7 | 1031.3 | 1046.5 | 1061.7 | 1036.8 | 1012.0 | 987.1  |
| 67.5° | 1208.3 | 1170.9 | 1132.2 | 1093.5 | 1111.5 | 1129.5 | 1147.4 | 1165.4 | 1140.5 | 1114.3 | 1089.4 |
| 70°   | 1309.2 | 1262.2 | 1215.2 | 1168.2 | 1186.2 | 1204.1 | 1222.1 | 1240.1 | 1216.6 | 1193.1 | 1169.6 |
| 72.5° | 1363.1 | 1314.7 | 1267.7 | 1219.3 | 1237.3 | 1256.7 | 1274.6 | 1292.6 | 1263.6 | 1234.5 | 1204.1 |
| 75°   | 1342.4 | 1299.5 | 1258.0 | 1215.2 | 1241.5 | 1267.7 | 1294.0 | 1320.3 | 1281.5 | 1241.5 | 1202.7 |
| 77.5° | 1170.9 | 1151.6 | 1130.9 | 1110.1 | 1157.1 | 1204.1 | 1251.1 | 1298.1 | 1242.8 | 1186.2 | 1130.9 |
| 80°   | 815.7  | 830.9  | 844.7  | 858.5  | 926.3  | 994.0  | 1060.4 | 1128.1 | 1063.1 | 999.5  | 934.5  |
| 82.5° | 374.6  | 417.5  | 459.0  | 501.8  | 569.6  | 637.3  | 703.7  | 771.4  | 699.5  | 627.6  | 554.4  |
| 85°   | 89.9   | 103.7  | 116.1  | 130.0  | 164.5  | 199.1  | 233.6  | 268.2  | 239.2  | 210.1  | 181.1  |
| 87.5° | 11.1   | 12.4   | 12.4   | 13.8   | 12.4   | 12.4   | 11.1   | 9.7    | 11.1   | 11.1   | 12.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 333.2  | 334.6  | 334.6  | 335.9  | 335.9  | 335.9  | 335.9  | 334.6  | 334.6  | 334.6  | 335.9  |
| 5°    | 288.9  | 295.8  | 301.4  | 308.3  | 313.8  | 316.6  | 320.7  | 323.5  | 326.3  | 327.6  | 327.6  |
| 7.5°  | 271.0  | 268.2  | 264.1  | 261.3  | 257.1  | 262.7  | 269.6  | 275.1  | 280.6  | 282.0  | 283.4  |
| 10°   | 219.8  | 218.4  | 215.7  | 214.3  | 211.5  | 212.9  | 215.7  | 217.0  | 218.4  | 225.3  | 233.6  |
| 12.5° | 196.3  | 197.7  | 199.1  | 200.5  | 201.8  | 197.7  | 193.5  | 188.0  | 183.9  | 190.8  | 197.7  |
| 15°   | 172.8  | 172.8  | 174.2  | 174.2  | 174.2  | 179.7  | 185.3  | 190.8  | 196.3  | 206.0  | 217.0  |
| 17.5° | 193.5  | 190.8  | 188.0  | 183.9  | 181.1  | 182.5  | 182.5  | 183.9  | 183.9  | 189.4  | 193.5  |
| 20°   | 185.3  | 181.1  | 178.3  | 174.2  | 170.0  | 177.0  | 183.9  | 190.8  | 197.7  | 208.8  | 219.8  |
| 22.5° | 181.1  | 189.4  | 196.3  | 204.6  | 211.5  | 207.4  | 203.2  | 197.7  | 193.5  | 193.5  | 193.5  |
| 25°   | 217.0  | 210.1  | 203.2  | 196.3  | 189.4  | 201.8  | 212.9  | 225.3  | 236.4  | 244.7  | 251.6  |
| 27.5° | 210.1  | 215.7  | 221.2  | 225.3  | 230.9  | 237.8  | 244.7  | 251.6  | 258.5  | 271.0  | 282.0  |
| 30°   | 237.8  | 244.7  | 251.6  | 257.1  | 264.1  | 282.0  | 298.6  | 316.6  | 333.2  | 341.5  | 349.8  |
| 32.5° | 255.8  | 269.6  | 282.0  | 295.8  | 308.3  | 318.0  | 327.6  | 337.3  | 347.0  | 355.3  | 365.0  |
| 35°   | 282.0  | 293.1  | 302.8  | 313.8  | 323.5  | 334.6  | 345.6  | 355.3  | 366.4  | 374.6  | 382.9  |
| 37.5° | 293.1  | 305.5  | 318.0  | 329.0  | 341.5  | 355.3  | 367.7  | 381.6  | 394.0  | 400.9  | 406.4  |
| 40°   | 309.7  | 324.9  | 340.1  | 355.3  | 370.5  | 384.3  | 398.1  | 412.0  | 425.8  | 431.3  | 436.9  |
| 42.5° | 335.9  | 352.5  | 369.1  | 384.3  | 400.9  | 416.1  | 429.9  | 445.2  | 459.0  | 464.5  | 470.0  |
| 45°   | 367.7  | 384.3  | 400.9  | 417.5  | 434.1  | 450.7  | 467.3  | 483.9  | 500.5  | 507.4  | 514.3  |
| 47.5° | 407.8  | 424.4  | 442.4  | 459.0  | 475.6  | 496.3  | 515.7  | 536.4  | 555.8  | 561.3  | 566.8  |
| 50°   | 452.1  | 468.7  | 485.2  | 501.8  | 518.4  | 544.7  | 569.6  | 595.8  | 620.7  | 623.5  | 627.6  |
| 52.5° | 508.7  | 525.3  | 540.5  | 557.1  | 572.3  | 601.4  | 630.4  | 658.1  | 687.1  | 688.5  | 691.2  |
| 55°   | 576.5  | 591.7  | 608.3  | 623.5  | 638.7  | 670.5  | 700.9  | 732.7  | 763.1  | 763.1  | 764.5  |
| 57.5° | 660.8  | 677.4  | 694.0  | 709.2  | 725.8  | 756.2  | 786.6  | 815.7  | 846.1  | 844.7  | 843.3  |
| 60°   | 756.2  | 771.4  | 785.2  | 800.4  | 814.3  | 843.3  | 873.7  | 902.7  | 931.8  | 929.0  | 924.9  |
| 62.5° | 854.4  | 871.0  | 887.5  | 902.7  | 919.3  | 942.8  | 967.7  | 991.2  | 1014.7 | 1009.2 | 1003.7 |
| 65°   | 962.2  | 978.8  | 996.8  | 1013.3 | 1029.9 | 1047.9 | 1067.3 | 1085.2 | 1103.2 | 1097.7 | 1093.5 |
| 67.5° | 1063.1 | 1082.5 | 1101.8 | 1119.8 | 1139.2 | 1153.0 | 1166.8 | 1179.2 | 1193.1 | 1186.2 | 1179.2 |
| 70°   | 1146.1 | 1162.7 | 1179.2 | 1195.8 | 1212.4 | 1226.2 | 1240.1 | 1253.9 | 1267.7 | 1260.8 | 1253.9 |
| 72.5° | 1175.1 | 1194.4 | 1213.8 | 1231.8 | 1251.1 | 1267.7 | 1284.3 | 1300.9 | 1317.5 | 1313.3 | 1307.8 |
| 75°   | 1162.7 | 1176.5 | 1190.3 | 1204.1 | 1218.0 | 1230.4 | 1244.2 | 1256.7 | 1269.1 | 1262.2 | 1255.3 |
| 77.5° | 1074.2 | 1072.8 | 1070.0 | 1068.6 | 1065.9 | 1065.9 | 1067.3 | 1067.3 | 1067.3 | 1059.0 | 1050.7 |
| 80°   | 869.6  | 844.7  | 819.8  | 794.9  | 770.0  | 741.0  | 712.0  | 682.9  | 653.9  | 626.3  | 598.6  |
| 82.5° | 482.5  | 425.8  | 370.5  | 313.8  | 257.1  | 233.6  | 208.8  | 185.3  | 160.4  | 149.3  | 136.9  |
| 85°   | 152.1  | 132.7  | 113.4  | 94.0   | 74.7   | 70.5   | 66.4   | 60.8   | 56.7   | 52.5   | 48.4   |
| 87.5° | 12.4   | 11.1   | 11.1   | 9.7    | 8.3    | 6.9    | 6.9    | 5.5    | 4.1    | 4.1    | 4.1    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°    | 97.5°  | 100°   | 102.5° | 105°   | 107.5° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 335.9  | 335.9  | 335.9  | 335.9  | 335.9  | 335.9  | 335.9  | 335.9  | 334.6  | 334.6  | 334.6  |
| 5°    | 329.0  | 329.0  | 329.0  | 329.0  | 329.0  | 329.0  | 329.0  | 327.6  | 327.6  | 326.3  | 323.5  |
| 7.5°  | 283.4  | 284.8  | 284.8  | 283.4  | 284.8  | 284.8  | 283.4  | 283.4  | 282.0  | 280.6  | 275.1  |
| 10°   | 240.5  | 247.5  | 247.5  | 247.5  | 247.5  | 247.5  | 240.5  | 233.6  | 225.3  | 218.4  | 217.0  |
| 12.5° | 204.6  | 211.5  | 211.5  | 211.5  | 211.5  | 211.5  | 204.6  | 197.7  | 190.8  | 183.9  | 188.0  |
| 15°   | 226.7  | 236.4  | 236.4  | 236.4  | 236.4  | 236.4  | 226.7  | 217.0  | 206.0  | 196.3  | 190.8  |
| 17.5° | 199.1  | 203.2  | 204.6  | 204.6  | 204.6  | 203.2  | 199.1  | 193.5  | 189.4  | 183.9  | 183.9  |
| 20°   | 229.5  | 240.5  | 241.9  | 243.3  | 241.9  | 240.5  | 229.5  | 219.8  | 208.8  | 197.7  | 190.8  |
| 22.5° | 192.2  | 192.2  | 193.5  | 193.5  | 193.5  | 192.2  | 192.2  | 193.5  | 193.5  | 193.5  | 197.7  |
| 25°   | 259.9  | 266.8  | 266.8  | 265.4  | 266.8  | 266.8  | 259.9  | 251.6  | 244.7  | 236.4  | 225.3  |
| 27.5° | 294.5  | 305.5  | 308.3  | 309.7  | 308.3  | 305.5  | 294.5  | 282.0  | 271.0  | 258.5  | 251.6  |
| 30°   | 358.1  | 366.4  | 366.4  | 366.4  | 366.4  | 366.4  | 358.1  | 349.8  | 341.5  | 333.2  | 316.6  |
| 32.5° | 373.3  | 381.6  | 381.6  | 381.6  | 381.6  | 381.6  | 373.3  | 365.0  | 355.3  | 347.0  | 337.3  |
| 35°   | 389.9  | 398.1  | 399.5  | 399.5  | 399.5  | 398.1  | 389.9  | 382.9  | 374.6  | 366.4  | 355.3  |
| 37.5° | 413.4  | 418.9  | 420.3  | 421.7  | 420.3  | 418.9  | 413.4  | 406.4  | 400.9  | 394.0  | 381.6  |
| 40°   | 441.0  | 446.5  | 446.5  | 446.5  | 446.5  | 446.5  | 441.0  | 436.9  | 431.3  | 425.8  | 412.0  |
| 42.5° | 475.6  | 481.1  | 482.5  | 483.9  | 482.5  | 481.1  | 475.6  | 470.0  | 464.5  | 459.0  | 445.2  |
| 45°   | 519.8  | 526.7  | 528.1  | 529.5  | 528.1  | 526.7  | 519.8  | 514.3  | 507.4  | 500.5  | 483.9  |
| 47.5° | 572.3  | 577.9  | 577.9  | 577.9  | 577.9  | 577.9  | 572.3  | 566.8  | 561.3  | 555.8  | 536.4  |
| 50°   | 630.4  | 633.2  | 634.6  | 634.6  | 634.6  | 633.2  | 630.4  | 627.6  | 623.5  | 620.7  | 595.8  |
| 52.5° | 692.6  | 694.0  | 694.0  | 692.6  | 694.0  | 694.0  | 692.6  | 691.2  | 688.5  | 687.1  | 658.1  |
| 55°   | 764.5  | 764.5  | 763.1  | 760.4  | 763.1  | 764.5  | 764.5  | 764.5  | 763.1  | 763.1  | 732.7  |
| 57.5° | 841.9  | 840.5  | 840.5  | 839.2  | 840.5  | 840.5  | 841.9  | 843.3  | 844.7  | 846.1  | 815.7  |
| 60°   | 922.1  | 918.0  | 916.6  | 913.8  | 916.6  | 918.0  | 922.1  | 924.9  | 929.0  | 931.8  | 902.7  |
| 62.5° | 998.1  | 992.6  | 992.6  | 992.6  | 992.6  | 992.6  | 998.1  | 1003.7 | 1009.2 | 1014.7 | 991.2  |
| 65°   | 1088.0 | 1082.5 | 1079.7 | 1076.9 | 1079.7 | 1082.5 | 1088.0 | 1093.5 | 1097.7 | 1103.2 | 1085.2 |
| 67.5° | 1172.3 | 1165.4 | 1162.7 | 1158.5 | 1162.7 | 1165.4 | 1172.3 | 1179.2 | 1186.2 | 1193.1 | 1179.2 |
| 70°   | 1245.6 | 1238.7 | 1237.3 | 1235.9 | 1237.3 | 1238.7 | 1245.6 | 1253.9 | 1260.8 | 1267.7 | 1253.9 |
| 72.5° | 1303.7 | 1298.1 | 1296.8 | 1294.0 | 1296.8 | 1298.1 | 1303.7 | 1307.8 | 1313.3 | 1317.5 | 1300.9 |
| 75°   | 1248.4 | 1241.5 | 1237.3 | 1231.8 | 1237.3 | 1241.5 | 1248.4 | 1255.3 | 1262.2 | 1269.1 | 1256.7 |
| 77.5° | 1042.4 | 1034.1 | 1031.3 | 1027.2 | 1031.3 | 1034.1 | 1042.4 | 1050.7 | 1059.0 | 1067.3 | 1067.3 |
| 80°   | 571.0  | 543.3  | 536.4  | 528.1  | 536.4  | 543.3  | 571.0  | 598.6  | 626.3  | 653.9  | 682.9  |
| 82.5° | 125.8  | 113.4  | 109.2  | 103.7  | 109.2  | 113.4  | 125.8  | 136.9  | 149.3  | 160.4  | 185.3  |
| 85°   | 42.9   | 38.7   | 35.9   | 33.2   | 35.9   | 38.7   | 42.9   | 48.4   | 52.5   | 56.7   | 60.8   |
| 87.5° | 4.1    | 4.1    | 4.1    | 2.8    | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    | 5.5    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 110°   | 112.5° | 115°   | 117.5° | 120°   | 122.5° | 125°   | 127.5° | 130°   | 132.5° | 135°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 335.9  | 335.9  | 335.9  | 335.9  | 334.6  | 334.6  | 333.2  | 333.2  | 331.8  | 331.8  | 330.4  |
| 5°    | 320.7  | 316.6  | 313.8  | 308.3  | 301.4  | 295.8  | 288.9  | 287.6  | 286.2  | 284.8  | 283.4  |
| 7.5°  | 269.6  | 262.7  | 257.1  | 261.3  | 264.1  | 268.2  | 271.0  | 272.3  | 273.7  | 273.7  | 275.1  |
| 10°   | 215.7  | 212.9  | 211.5  | 214.3  | 215.7  | 218.4  | 219.8  | 224.0  | 228.1  | 230.9  | 235.0  |
| 12.5° | 193.5  | 197.7  | 201.8  | 200.5  | 199.1  | 197.7  | 196.3  | 199.1  | 201.8  | 204.6  | 207.4  |
| 15°   | 185.3  | 179.7  | 174.2  | 174.2  | 174.2  | 172.8  | 172.8  | 174.2  | 177.0  | 178.3  | 179.7  |
| 17.5° | 182.5  | 182.5  | 181.1  | 183.9  | 188.0  | 190.8  | 193.5  | 186.6  | 179.7  | 171.4  | 164.5  |
| 20°   | 183.9  | 177.0  | 170.0  | 174.2  | 178.3  | 181.1  | 185.3  | 190.8  | 194.9  | 200.5  | 204.6  |
| 22.5° | 203.2  | 207.4  | 211.5  | 204.6  | 196.3  | 189.4  | 181.1  | 188.0  | 196.3  | 203.2  | 210.1  |
| 25°   | 212.9  | 201.8  | 189.4  | 196.3  | 203.2  | 210.1  | 217.0  | 211.5  | 206.0  | 200.5  | 194.9  |
| 27.5° | 244.7  | 237.8  | 230.9  | 225.3  | 221.2  | 215.7  | 210.1  | 217.0  | 224.0  | 230.9  | 237.8  |
| 30°   | 298.6  | 282.0  | 264.1  | 257.1  | 251.6  | 244.7  | 237.8  | 235.0  | 232.3  | 228.1  | 225.3  |
| 32.5° | 327.6  | 318.0  | 308.3  | 295.8  | 282.0  | 269.6  | 255.8  | 255.8  | 255.8  | 254.4  | 254.4  |
| 35°   | 345.6  | 334.6  | 323.5  | 313.8  | 302.8  | 293.1  | 282.0  | 279.3  | 276.5  | 273.7  | 271.0  |
| 37.5° | 367.7  | 355.3  | 341.5  | 329.0  | 318.0  | 305.5  | 293.1  | 293.1  | 293.1  | 293.1  | 293.1  |
| 40°   | 398.1  | 384.3  | 370.5  | 355.3  | 340.1  | 324.9  | 309.7  | 311.1  | 313.8  | 315.2  | 316.6  |
| 42.5° | 429.9  | 416.1  | 400.9  | 384.3  | 369.1  | 352.5  | 335.9  | 337.3  | 340.1  | 341.5  | 342.9  |
| 45°   | 467.3  | 450.7  | 434.1  | 417.5  | 400.9  | 384.3  | 367.7  | 370.5  | 371.9  | 374.6  | 376.0  |
| 47.5° | 515.7  | 496.3  | 475.6  | 459.0  | 442.4  | 424.4  | 407.8  | 412.0  | 414.7  | 418.9  | 421.7  |
| 50°   | 569.6  | 544.7  | 518.4  | 501.8  | 485.2  | 468.7  | 452.1  | 457.6  | 463.1  | 468.7  | 474.2  |
| 52.5° | 630.4  | 601.4  | 572.3  | 557.1  | 540.5  | 525.3  | 508.7  | 514.3  | 521.2  | 526.7  | 532.2  |
| 55°   | 700.9  | 670.5  | 638.7  | 623.5  | 608.3  | 591.7  | 576.5  | 584.8  | 593.1  | 601.4  | 609.7  |
| 57.5° | 786.6  | 756.2  | 725.8  | 709.2  | 694.0  | 677.4  | 660.8  | 671.9  | 684.3  | 695.4  | 706.4  |
| 60°   | 873.7  | 843.3  | 814.3  | 800.4  | 785.2  | 771.4  | 756.2  | 770.0  | 785.2  | 799.1  | 812.9  |
| 62.5° | 967.7  | 942.8  | 919.3  | 902.7  | 887.5  | 871.0  | 854.4  | 875.1  | 895.8  | 916.6  | 937.3  |
| 65°   | 1067.3 | 1047.9 | 1029.9 | 1013.3 | 996.8  | 978.8  | 962.2  | 987.1  | 1012.0 | 1036.8 | 1061.7 |
| 67.5° | 1166.8 | 1153.0 | 1139.2 | 1119.8 | 1101.8 | 1082.5 | 1063.1 | 1089.4 | 1114.3 | 1140.5 | 1165.4 |
| 70°   | 1240.1 | 1226.2 | 1212.4 | 1195.8 | 1179.2 | 1162.7 | 1146.1 | 1169.6 | 1193.1 | 1216.6 | 1240.1 |
| 72.5° | 1284.3 | 1267.7 | 1251.1 | 1231.8 | 1213.8 | 1194.4 | 1175.1 | 1204.1 | 1234.5 | 1263.6 | 1292.6 |
| 75°   | 1244.2 | 1230.4 | 1218.0 | 1204.1 | 1190.3 | 1176.5 | 1162.7 | 1202.7 | 1241.5 | 1281.5 | 1320.3 |
| 77.5° | 1067.3 | 1065.9 | 1065.9 | 1068.6 | 1070.0 | 1072.8 | 1074.2 | 1130.9 | 1186.2 | 1242.8 | 1298.1 |
| 80°   | 712.0  | 741.0  | 770.0  | 794.9  | 819.8  | 844.7  | 869.6  | 934.5  | 999.5  | 1063.1 | 1128.1 |
| 82.5° | 208.8  | 233.6  | 257.1  | 313.8  | 370.5  | 425.8  | 482.5  | 554.4  | 627.6  | 699.5  | 771.4  |
| 85°   | 66.4   | 70.5   | 74.7   | 94.0   | 113.4  | 132.7  | 152.1  | 181.1  | 210.1  | 239.2  | 268.2  |
| 87.5° | 6.9    | 6.9    | 8.3    | 9.7    | 11.1   | 11.1   | 12.4   | 12.4   | 11.1   | 11.1   | 9.7    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 137.5° | 140°   | 142.5° | 145°   | 147.5° | 150°   | 152.5° | 155°   | 157.5° | 160°   | 162.5° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 329.0  | 327.6  | 326.3  | 324.9  | 323.5  | 322.1  | 319.3  | 318.0  | 313.8  | 309.7  | 305.5  |
| 5°    | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  |
| 7.5°  | 275.1  | 276.5  | 276.5  | 276.5  | 275.1  | 273.7  | 272.3  | 271.0  | 269.6  | 269.6  | 268.2  |
| 10°   | 235.0  | 235.0  | 233.6  | 233.6  | 240.5  | 248.8  | 255.8  | 262.7  | 265.4  | 268.2  | 269.6  |
| 12.5° | 217.0  | 226.7  | 235.0  | 244.7  | 250.2  | 257.1  | 262.7  | 268.2  | 266.8  | 265.4  | 264.1  |
| 15°   | 185.3  | 189.4  | 194.9  | 199.1  | 207.4  | 215.7  | 222.6  | 230.9  | 240.5  | 251.6  | 261.3  |
| 17.5° | 178.3  | 192.2  | 206.0  | 219.8  | 226.7  | 235.0  | 241.9  | 248.8  | 251.6  | 255.8  | 258.5  |
| 20°   | 206.0  | 206.0  | 207.4  | 207.4  | 207.4  | 206.0  | 206.0  | 204.6  | 221.2  | 239.2  | 255.8  |
| 22.5° | 207.4  | 204.6  | 201.8  | 199.1  | 211.5  | 222.6  | 235.0  | 246.1  | 244.7  | 243.3  | 241.9  |
| 25°   | 206.0  | 218.4  | 229.5  | 240.5  | 236.4  | 233.6  | 229.5  | 225.3  | 240.5  | 254.4  | 269.6  |
| 27.5° | 233.6  | 230.9  | 226.7  | 222.6  | 230.9  | 240.5  | 248.8  | 257.1  | 254.4  | 251.6  | 247.5  |
| 30°   | 232.3  | 237.8  | 244.7  | 250.2  | 248.8  | 248.8  | 247.5  | 246.1  | 261.3  | 275.1  | 290.3  |
| 32.5° | 254.4  | 255.8  | 255.8  | 255.8  | 265.4  | 273.7  | 283.4  | 291.7  | 298.6  | 306.9  | 313.8  |
| 35°   | 273.7  | 276.5  | 277.9  | 280.6  | 293.1  | 305.5  | 316.6  | 329.0  | 342.9  | 356.7  | 370.5  |
| 37.5° | 294.5  | 297.2  | 298.6  | 300.0  | 313.8  | 326.3  | 340.1  | 352.5  | 367.7  | 382.9  | 396.8  |
| 40°   | 319.3  | 323.5  | 326.3  | 329.0  | 341.5  | 353.9  | 366.4  | 378.8  | 395.4  | 412.0  | 427.2  |
| 42.5° | 348.4  | 352.5  | 358.1  | 362.2  | 376.0  | 388.5  | 402.3  | 414.7  | 431.3  | 446.5  | 463.1  |
| 45°   | 381.6  | 387.1  | 391.2  | 396.8  | 414.7  | 431.3  | 449.3  | 465.9  | 481.1  | 494.9  | 510.1  |
| 47.5° | 425.8  | 428.6  | 432.7  | 435.5  | 454.8  | 474.2  | 492.2  | 511.5  | 526.7  | 541.9  | 555.8  |
| 50°   | 475.6  | 475.6  | 477.0  | 477.0  | 501.8  | 525.3  | 550.2  | 573.7  | 587.5  | 602.8  | 616.6  |
| 52.5° | 535.0  | 537.8  | 539.2  | 541.9  | 566.8  | 590.3  | 615.2  | 638.7  | 652.5  | 667.7  | 681.6  |
| 55°   | 611.0  | 612.4  | 612.4  | 613.8  | 638.7  | 663.6  | 688.5  | 713.4  | 727.2  | 741.0  | 754.8  |
| 57.5° | 706.4  | 705.1  | 705.1  | 703.7  | 728.6  | 753.4  | 776.9  | 801.8  | 815.7  | 829.5  | 843.3  |
| 60°   | 808.7  | 804.6  | 799.1  | 794.9  | 822.6  | 851.6  | 879.2  | 906.9  | 919.3  | 931.8  | 944.2  |
| 62.5° | 929.0  | 922.1  | 913.8  | 905.5  | 934.5  | 962.2  | 991.2  | 1018.9 | 1028.6 | 1036.8 | 1046.5 |
| 65°   | 1046.5 | 1031.3 | 1014.7 | 999.5  | 1032.7 | 1065.9 | 1099.1 | 1132.2 | 1139.2 | 1146.1 | 1151.6 |
| 67.5° | 1147.4 | 1129.5 | 1111.5 | 1093.5 | 1132.2 | 1170.9 | 1208.3 | 1247.0 | 1249.7 | 1252.5 | 1255.3 |
| 70°   | 1222.1 | 1204.1 | 1186.2 | 1168.2 | 1215.2 | 1262.2 | 1309.2 | 1356.2 | 1357.6 | 1359.0 | 1360.3 |
| 72.5° | 1274.6 | 1256.7 | 1237.3 | 1219.3 | 1267.7 | 1314.7 | 1363.1 | 1410.1 | 1414.3 | 1417.0 | 1421.2 |
| 75°   | 1294.0 | 1267.7 | 1241.5 | 1215.2 | 1258.0 | 1299.5 | 1342.4 | 1383.8 | 1379.7 | 1375.6 | 1370.0 |
| 77.5° | 1251.1 | 1204.1 | 1157.1 | 1110.1 | 1130.9 | 1151.6 | 1170.9 | 1191.7 | 1169.6 | 1146.1 | 1123.9 |
| 80°   | 1060.4 | 994.0  | 926.3  | 858.5  | 844.7  | 830.9  | 815.7  | 801.8  | 760.4  | 718.9  | 676.0  |
| 82.5° | 703.7  | 637.3  | 569.6  | 501.8  | 459.0  | 417.5  | 374.6  | 331.8  | 294.5  | 257.1  | 218.4  |
| 85°   | 233.6  | 199.1  | 164.5  | 130.0  | 116.1  | 103.7  | 89.9   | 76.0   | 70.5   | 65.0   | 59.4   |
| 87.5° | 11.1   | 12.4   | 12.4   | 13.8   | 12.4   | 12.4   | 11.1   | 9.7    | 8.3    | 8.3    | 6.9    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 165°   | 167.5° | 170°   | 172.5° | 175°   | 177.5° | 180°   | 182.5° | 185°   | 187.5° | 190°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 301.4  | 301.4  | 302.8  | 302.8  | 302.8  | 302.8  | 301.4  | 302.8  | 302.8  | 302.8  | 302.8  |
| 5°    | 283.4  | 283.4  | 284.8  | 284.8  | 284.8  | 284.8  | 284.8  | 284.8  | 284.8  | 284.8  | 284.8  |
| 7.5°  | 266.8  | 262.7  | 257.1  | 253.0  | 247.5  | 246.1  | 243.3  | 246.1  | 247.5  | 253.0  | 257.1  |
| 10°   | 272.3  | 272.3  | 273.7  | 273.7  | 273.7  | 273.7  | 273.7  | 273.7  | 273.7  | 273.7  | 273.7  |
| 12.5° | 262.7  | 257.1  | 250.2  | 244.7  | 237.8  | 239.2  | 240.5  | 239.2  | 237.8  | 244.7  | 250.2  |
| 15°   | 271.0  | 272.3  | 273.7  | 275.1  | 276.5  | 276.5  | 276.5  | 276.5  | 276.5  | 275.1  | 273.7  |
| 17.5° | 261.3  | 255.8  | 248.8  | 243.3  | 236.4  | 236.4  | 235.0  | 236.4  | 236.4  | 243.3  | 248.8  |
| 20°   | 272.3  | 275.1  | 277.9  | 279.3  | 282.0  | 282.0  | 282.0  | 282.0  | 282.0  | 279.3  | 277.9  |
| 22.5° | 240.5  | 240.5  | 240.5  | 239.2  | 239.2  | 239.2  | 239.2  | 239.2  | 239.2  | 239.2  | 240.5  |
| 25°   | 283.4  | 286.2  | 288.9  | 290.3  | 293.1  | 293.1  | 291.7  | 293.1  | 293.1  | 290.3  | 288.9  |
| 27.5° | 244.7  | 246.1  | 248.8  | 250.2  | 251.6  | 251.6  | 251.6  | 251.6  | 251.6  | 250.2  | 248.8  |
| 30°   | 304.1  | 305.5  | 306.9  | 306.9  | 308.3  | 308.3  | 308.3  | 308.3  | 308.3  | 306.9  | 306.9  |
| 32.5° | 320.7  | 333.2  | 347.0  | 359.4  | 371.9  | 373.3  | 374.6  | 373.3  | 371.9  | 359.4  | 347.0  |
| 35°   | 384.3  | 387.1  | 391.2  | 394.0  | 396.8  | 398.1  | 398.1  | 398.1  | 396.8  | 394.0  | 391.2  |
| 37.5° | 412.0  | 414.7  | 416.1  | 418.9  | 420.3  | 421.7  | 421.7  | 421.7  | 420.3  | 418.9  | 416.1  |
| 40°   | 443.8  | 446.5  | 447.9  | 450.7  | 452.1  | 452.1  | 450.7  | 452.1  | 452.1  | 450.7  | 447.9  |
| 42.5° | 478.3  | 479.7  | 482.5  | 483.9  | 485.2  | 486.6  | 486.6  | 486.6  | 485.2  | 483.9  | 482.5  |
| 45°   | 524.0  | 525.3  | 526.7  | 526.7  | 528.1  | 529.5  | 529.5  | 529.5  | 528.1  | 526.7  | 526.7  |
| 47.5° | 571.0  | 573.7  | 575.1  | 577.9  | 579.3  | 580.6  | 582.0  | 580.6  | 579.3  | 577.9  | 575.1  |
| 50°   | 630.4  | 631.8  | 634.6  | 635.9  | 637.3  | 637.3  | 637.3  | 637.3  | 637.3  | 635.9  | 634.6  |
| 52.5° | 695.4  | 696.8  | 696.8  | 698.1  | 698.1  | 698.1  | 696.8  | 698.1  | 698.1  | 698.1  | 696.8  |
| 55°   | 768.7  | 768.7  | 768.7  | 767.3  | 767.3  | 767.3  | 767.3  | 767.3  | 767.3  | 767.3  | 768.7  |
| 57.5° | 857.1  | 857.1  | 857.1  | 857.1  | 857.1  | 853.0  | 847.5  | 853.0  | 857.1  | 857.1  | 857.1  |
| 60°   | 956.7  | 953.9  | 949.8  | 947.0  | 942.8  | 941.5  | 940.1  | 941.5  | 942.8  | 947.0  | 949.8  |
| 62.5° | 1054.8 | 1050.7 | 1045.1 | 1041.0 | 1035.5 | 1034.1 | 1031.3 | 1034.1 | 1035.5 | 1041.0 | 1045.1 |
| 65°   | 1158.5 | 1151.6 | 1144.7 | 1136.4 | 1129.5 | 1128.1 | 1125.3 | 1128.1 | 1129.5 | 1136.4 | 1144.7 |
| 67.5° | 1258.0 | 1251.1 | 1244.2 | 1235.9 | 1229.0 | 1227.6 | 1224.9 | 1227.6 | 1229.0 | 1235.9 | 1244.2 |
| 70°   | 1361.7 | 1354.8 | 1347.9 | 1339.6 | 1332.7 | 1332.7 | 1331.3 | 1332.7 | 1332.7 | 1339.6 | 1347.9 |
| 72.5° | 1423.9 | 1417.0 | 1411.5 | 1404.6 | 1397.7 | 1393.5 | 1389.4 | 1393.5 | 1397.7 | 1404.6 | 1411.5 |
| 75°   | 1365.9 | 1354.8 | 1343.8 | 1331.3 | 1320.3 | 1317.5 | 1314.7 | 1317.5 | 1320.3 | 1331.3 | 1343.8 |
| 77.5° | 1100.4 | 1089.4 | 1076.9 | 1065.9 | 1053.4 | 1042.4 | 1029.9 | 1042.4 | 1053.4 | 1065.9 | 1076.9 |
| 80°   | 634.6  | 606.9  | 579.3  | 551.6  | 524.0  | 517.0  | 510.1  | 517.0  | 524.0  | 551.6  | 579.3  |
| 82.5° | 181.1  | 167.3  | 152.1  | 138.2  | 123.0  | 123.0  | 123.0  | 123.0  | 123.0  | 138.2  | 152.1  |
| 85°   | 53.9   | 47.0   | 41.5   | 34.6   | 27.6   | 26.3   | 24.9   | 26.3   | 27.6   | 34.6   | 41.5   |
| 87.5° | 5.5    | 5.5    | 5.5    | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    | 5.5    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 192.5° | 195°   | 197.5° | 200°   | 202.5° | 205°   | 207.5° | 210°   | 212.5° | 215°   | 217.5° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 301.4  | 301.4  | 305.5  | 309.7  | 313.8  | 318.0  | 319.3  | 322.1  | 323.5  | 324.9  | 326.3  |
| 5°    | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  |
| 7.5°  | 262.7  | 266.8  | 268.2  | 269.6  | 269.6  | 271.0  | 272.3  | 273.7  | 275.1  | 276.5  | 276.5  |
| 10°   | 272.3  | 272.3  | 269.6  | 268.2  | 265.4  | 262.7  | 255.8  | 248.8  | 240.5  | 233.6  | 233.6  |
| 12.5° | 257.1  | 262.7  | 264.1  | 265.4  | 266.8  | 268.2  | 262.7  | 257.1  | 250.2  | 244.7  | 235.0  |
| 15°   | 272.3  | 271.0  | 261.3  | 251.6  | 240.5  | 230.9  | 222.6  | 215.7  | 207.4  | 199.1  | 194.9  |
| 17.5° | 255.8  | 261.3  | 258.5  | 255.8  | 251.6  | 248.8  | 241.9  | 235.0  | 226.7  | 219.8  | 206.0  |
| 20°   | 275.1  | 272.3  | 255.8  | 239.2  | 221.2  | 204.6  | 206.0  | 206.0  | 207.4  | 207.4  | 207.4  |
| 22.5° | 240.5  | 240.5  | 241.9  | 243.3  | 244.7  | 246.1  | 235.0  | 222.6  | 211.5  | 199.1  | 201.8  |
| 25°   | 286.2  | 283.4  | 269.6  | 254.4  | 240.5  | 225.3  | 229.5  | 233.6  | 236.4  | 240.5  | 229.5  |
| 27.5° | 246.1  | 244.7  | 247.5  | 251.6  | 254.4  | 257.1  | 248.8  | 240.5  | 230.9  | 222.6  | 226.7  |
| 30°   | 305.5  | 304.1  | 290.3  | 275.1  | 261.3  | 246.1  | 247.5  | 248.8  | 248.8  | 250.2  | 244.7  |
| 32.5° | 333.2  | 320.7  | 313.8  | 306.9  | 298.6  | 291.7  | 283.4  | 273.7  | 265.4  | 255.8  | 255.8  |
| 35°   | 387.1  | 384.3  | 370.5  | 356.7  | 342.9  | 329.0  | 316.6  | 305.5  | 293.1  | 280.6  | 277.9  |
| 37.5° | 414.7  | 412.0  | 396.8  | 382.9  | 367.7  | 352.5  | 340.1  | 326.3  | 313.8  | 300.0  | 298.6  |
| 40°   | 446.5  | 443.8  | 427.2  | 412.0  | 395.4  | 378.8  | 366.4  | 353.9  | 341.5  | 329.0  | 326.3  |
| 42.5° | 479.7  | 478.3  | 463.1  | 446.5  | 431.3  | 414.7  | 402.3  | 388.5  | 376.0  | 362.2  | 358.1  |
| 45°   | 525.3  | 524.0  | 510.1  | 494.9  | 481.1  | 465.9  | 449.3  | 431.3  | 414.7  | 396.8  | 391.2  |
| 47.5° | 573.7  | 571.0  | 555.8  | 541.9  | 526.7  | 511.5  | 492.2  | 474.2  | 454.8  | 435.5  | 432.7  |
| 50°   | 631.8  | 630.4  | 616.6  | 602.8  | 587.5  | 573.7  | 550.2  | 525.3  | 501.8  | 477.0  | 477.0  |
| 52.5° | 696.8  | 695.4  | 681.6  | 667.7  | 652.5  | 638.7  | 615.2  | 590.3  | 566.8  | 541.9  | 539.2  |
| 55°   | 768.7  | 768.7  | 754.8  | 741.0  | 727.2  | 713.4  | 688.5  | 663.6  | 638.7  | 613.8  | 612.4  |
| 57.5° | 857.1  | 857.1  | 843.3  | 829.5  | 815.7  | 801.8  | 776.9  | 753.4  | 728.6  | 703.7  | 705.1  |
| 60°   | 953.9  | 956.7  | 944.2  | 931.8  | 919.3  | 906.9  | 879.2  | 851.6  | 822.6  | 794.9  | 799.1  |
| 62.5° | 1050.7 | 1054.8 | 1046.5 | 1036.8 | 1028.6 | 1018.9 | 991.2  | 962.2  | 934.5  | 905.5  | 913.8  |
| 65°   | 1151.6 | 1158.5 | 1151.6 | 1146.1 | 1139.2 | 1132.2 | 1099.1 | 1065.9 | 1032.7 | 999.5  | 1014.7 |
| 67.5° | 1251.1 | 1258.0 | 1255.3 | 1252.5 | 1249.7 | 1247.0 | 1208.3 | 1170.9 | 1132.2 | 1093.5 | 1111.5 |
| 70°   | 1354.8 | 1361.7 | 1360.3 | 1359.0 | 1357.6 | 1356.2 | 1309.2 | 1262.2 | 1215.2 | 1168.2 | 1186.2 |
| 72.5° | 1417.0 | 1423.9 | 1421.2 | 1417.0 | 1414.3 | 1410.1 | 1363.1 | 1314.7 | 1267.7 | 1219.3 | 1237.3 |
| 75°   | 1354.8 | 1365.9 | 1370.0 | 1375.6 | 1379.7 | 1383.8 | 1342.4 | 1299.5 | 1258.0 | 1215.2 | 1241.5 |
| 77.5° | 1089.4 | 1100.4 | 1123.9 | 1146.1 | 1169.6 | 1191.7 | 1170.9 | 1151.6 | 1130.9 | 1110.1 | 1157.1 |
| 80°   | 606.9  | 634.6  | 676.0  | 718.9  | 760.4  | 801.8  | 815.7  | 830.9  | 844.7  | 858.5  | 926.3  |
| 82.5° | 167.3  | 181.1  | 218.4  | 257.1  | 294.5  | 331.8  | 374.6  | 417.5  | 459.0  | 501.8  | 569.6  |
| 85°   | 47.0   | 53.9   | 59.4   | 65.0   | 70.5   | 76.0   | 89.9   | 103.7  | 116.1  | 130.0  | 164.5  |
| 87.5° | 5.5    | 5.5    | 6.9    | 8.3    | 8.3    | 9.7    | 11.1   | 12.4   | 12.4   | 13.8   | 12.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 220°   | 222.5° | 225°   | 227.5° | 230°   | 232.5° | 235°   | 237.5° | 240°   | 242.5° | 245°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 327.6  | 329.0  | 330.4  | 331.8  | 331.8  | 333.2  | 333.2  | 334.6  | 334.6  | 335.9  | 335.9  |
| 5°    | 283.4  | 283.4  | 283.4  | 284.8  | 286.2  | 287.6  | 288.9  | 295.8  | 301.4  | 308.3  | 313.8  |
| 7.5°  | 276.5  | 275.1  | 275.1  | 273.7  | 273.7  | 272.3  | 271.0  | 268.2  | 264.1  | 261.3  | 257.1  |
| 10°   | 235.0  | 235.0  | 235.0  | 230.9  | 228.1  | 224.0  | 219.8  | 218.4  | 215.7  | 214.3  | 211.5  |
| 12.5° | 226.7  | 217.0  | 207.4  | 204.6  | 201.8  | 199.1  | 196.3  | 197.7  | 199.1  | 200.5  | 201.8  |
| 15°   | 189.4  | 185.3  | 179.7  | 178.3  | 177.0  | 174.2  | 172.8  | 172.8  | 174.2  | 174.2  | 174.2  |
| 17.5° | 192.2  | 178.3  | 164.5  | 171.4  | 179.7  | 186.6  | 193.5  | 190.8  | 188.0  | 183.9  | 181.1  |
| 20°   | 206.0  | 206.0  | 204.6  | 200.5  | 194.9  | 190.8  | 185.3  | 181.1  | 178.3  | 174.2  | 170.0  |
| 22.5° | 204.6  | 207.4  | 210.1  | 203.2  | 196.3  | 188.0  | 181.1  | 189.4  | 196.3  | 204.6  | 211.5  |
| 25°   | 218.4  | 206.0  | 194.9  | 200.5  | 206.0  | 211.5  | 217.0  | 210.1  | 203.2  | 196.3  | 189.4  |
| 27.5° | 230.9  | 233.6  | 237.8  | 230.9  | 224.0  | 217.0  | 210.1  | 215.7  | 221.2  | 225.3  | 230.9  |
| 30°   | 237.8  | 232.3  | 225.3  | 228.1  | 232.3  | 235.0  | 237.8  | 244.7  | 251.6  | 257.1  | 264.1  |
| 32.5° | 255.8  | 254.4  | 254.4  | 254.4  | 255.8  | 255.8  | 255.8  | 269.6  | 282.0  | 295.8  | 308.3  |
| 35°   | 276.5  | 273.7  | 271.0  | 273.7  | 276.5  | 279.3  | 282.0  | 293.1  | 302.8  | 313.8  | 323.5  |
| 37.5° | 297.2  | 294.5  | 293.1  | 293.1  | 293.1  | 293.1  | 293.1  | 305.5  | 318.0  | 329.0  | 341.5  |
| 40°   | 323.5  | 319.3  | 316.6  | 315.2  | 313.8  | 311.1  | 309.7  | 324.9  | 340.1  | 355.3  | 370.5  |
| 42.5° | 352.5  | 348.4  | 342.9  | 341.5  | 340.1  | 337.3  | 335.9  | 352.5  | 369.1  | 384.3  | 400.9  |
| 45°   | 387.1  | 381.6  | 376.0  | 374.6  | 371.9  | 370.5  | 367.7  | 384.3  | 400.9  | 417.5  | 434.1  |
| 47.5° | 428.6  | 425.8  | 421.7  | 418.9  | 414.7  | 412.0  | 407.8  | 424.4  | 442.4  | 459.0  | 475.6  |
| 50°   | 475.6  | 475.6  | 474.2  | 468.7  | 463.1  | 457.6  | 452.1  | 468.7  | 485.2  | 501.8  | 518.4  |
| 52.5° | 537.8  | 535.0  | 532.2  | 526.7  | 521.2  | 514.3  | 508.7  | 525.3  | 540.5  | 557.1  | 572.3  |
| 55°   | 612.4  | 611.0  | 609.7  | 601.4  | 593.1  | 584.8  | 576.5  | 591.7  | 608.3  | 623.5  | 638.7  |
| 57.5° | 705.1  | 706.4  | 706.4  | 695.4  | 684.3  | 671.9  | 660.8  | 677.4  | 694.0  | 709.2  | 725.8  |
| 60°   | 804.6  | 808.7  | 812.9  | 799.1  | 785.2  | 770.0  | 756.2  | 771.4  | 785.2  | 800.4  | 814.3  |
| 62.5° | 922.1  | 929.0  | 937.3  | 916.6  | 895.8  | 875.1  | 854.4  | 871.0  | 887.5  | 902.7  | 919.3  |
| 65°   | 1031.3 | 1046.5 | 1061.7 | 1036.8 | 1012.0 | 987.1  | 962.2  | 978.8  | 996.8  | 1013.3 | 1029.9 |
| 67.5° | 1129.5 | 1147.4 | 1165.4 | 1140.5 | 1114.3 | 1089.4 | 1063.1 | 1082.5 | 1101.8 | 1119.8 | 1139.2 |
| 70°   | 1204.1 | 1222.1 | 1240.1 | 1216.6 | 1193.1 | 1169.6 | 1146.1 | 1162.7 | 1179.2 | 1195.8 | 1212.4 |
| 72.5° | 1256.7 | 1274.6 | 1292.6 | 1263.6 | 1234.5 | 1204.1 | 1175.1 | 1194.4 | 1213.8 | 1231.8 | 1251.1 |
| 75°   | 1267.7 | 1294.0 | 1320.3 | 1281.5 | 1241.5 | 1202.7 | 1162.7 | 1176.5 | 1190.3 | 1204.1 | 1218.0 |
| 77.5° | 1204.1 | 1251.1 | 1298.1 | 1242.8 | 1186.2 | 1130.9 | 1074.2 | 1072.8 | 1070.0 | 1068.6 | 1065.9 |
| 80°   | 994.0  | 1060.4 | 1128.1 | 1063.1 | 999.5  | 934.5  | 869.6  | 844.7  | 819.8  | 794.9  | 770.0  |
| 82.5° | 637.3  | 703.7  | 771.4  | 699.5  | 627.6  | 554.4  | 482.5  | 425.8  | 370.5  | 313.8  | 257.1  |
| 85°   | 199.1  | 233.6  | 268.2  | 239.2  | 210.1  | 181.1  | 152.1  | 132.7  | 113.4  | 94.0   | 74.7   |
| 87.5° | 12.4   | 11.1   | 9.7    | 11.1   | 11.1   | 12.4   | 12.4   | 11.1   | 11.1   | 9.7    | 8.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5° | 265°   | 267.5° | 270°   | 272.5° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 335.9  | 335.9  | 334.6  | 334.6  | 334.6  | 335.9  | 335.9  | 335.9  | 335.9  | 335.9  | 335.9  |
| 5°    | 316.6  | 320.7  | 323.5  | 326.3  | 327.6  | 327.6  | 329.0  | 329.0  | 329.0  | 329.0  | 329.0  |
| 7.5°  | 262.7  | 269.6  | 275.1  | 280.6  | 282.0  | 283.4  | 283.4  | 284.8  | 284.8  | 283.4  | 284.8  |
| 10°   | 212.9  | 215.7  | 217.0  | 218.4  | 225.3  | 233.6  | 240.5  | 247.5  | 247.5  | 247.5  | 247.5  |
| 12.5° | 197.7  | 193.5  | 188.0  | 183.9  | 190.8  | 197.7  | 204.6  | 211.5  | 211.5  | 211.5  | 211.5  |
| 15°   | 179.7  | 185.3  | 190.8  | 196.3  | 206.0  | 217.0  | 226.7  | 236.4  | 236.4  | 236.4  | 236.4  |
| 17.5° | 182.5  | 182.5  | 183.9  | 183.9  | 189.4  | 193.5  | 199.1  | 203.2  | 204.6  | 204.6  | 204.6  |
| 20°   | 177.0  | 183.9  | 190.8  | 197.7  | 208.8  | 219.8  | 229.5  | 240.5  | 241.9  | 243.3  | 241.9  |
| 22.5° | 207.4  | 203.2  | 197.7  | 193.5  | 193.5  | 193.5  | 192.2  | 192.2  | 193.5  | 193.5  | 193.5  |
| 25°   | 201.8  | 212.9  | 225.3  | 236.4  | 244.7  | 251.6  | 259.9  | 266.8  | 266.8  | 265.4  | 266.8  |
| 27.5° | 237.8  | 244.7  | 251.6  | 258.5  | 271.0  | 282.0  | 294.5  | 305.5  | 308.3  | 309.7  | 308.3  |
| 30°   | 282.0  | 298.6  | 316.6  | 333.2  | 341.5  | 349.8  | 358.1  | 366.4  | 366.4  | 366.4  | 366.4  |
| 32.5° | 318.0  | 327.6  | 337.3  | 347.0  | 355.3  | 365.0  | 373.3  | 381.6  | 381.6  | 381.6  | 381.6  |
| 35°   | 334.6  | 345.6  | 355.3  | 366.4  | 374.6  | 382.9  | 389.9  | 398.1  | 399.5  | 399.5  | 399.5  |
| 37.5° | 355.3  | 367.7  | 381.6  | 394.0  | 400.9  | 406.4  | 413.4  | 418.9  | 420.3  | 421.7  | 420.3  |
| 40°   | 384.3  | 398.1  | 412.0  | 425.8  | 431.3  | 436.9  | 441.0  | 446.5  | 446.5  | 446.5  | 446.5  |
| 42.5° | 416.1  | 429.9  | 445.2  | 459.0  | 464.5  | 470.0  | 475.6  | 481.1  | 482.5  | 483.9  | 482.5  |
| 45°   | 450.7  | 467.3  | 483.9  | 500.5  | 507.4  | 514.3  | 519.8  | 526.7  | 528.1  | 529.5  | 528.1  |
| 47.5° | 496.3  | 515.7  | 536.4  | 555.8  | 561.3  | 566.8  | 572.3  | 577.9  | 577.9  | 577.9  | 577.9  |
| 50°   | 544.7  | 569.6  | 595.8  | 620.7  | 623.5  | 627.6  | 630.4  | 633.2  | 634.6  | 634.6  | 634.6  |
| 52.5° | 601.4  | 630.4  | 658.1  | 687.1  | 688.5  | 691.2  | 692.6  | 694.0  | 694.0  | 692.6  | 694.0  |
| 55°   | 670.5  | 700.9  | 732.7  | 763.1  | 763.1  | 764.5  | 764.5  | 764.5  | 763.1  | 760.4  | 763.1  |
| 57.5° | 756.2  | 786.6  | 815.7  | 846.1  | 844.7  | 843.3  | 841.9  | 840.5  | 840.5  | 839.2  | 840.5  |
| 60°   | 843.3  | 873.7  | 902.7  | 931.8  | 929.0  | 924.9  | 922.1  | 918.0  | 916.6  | 913.8  | 916.6  |
| 62.5° | 942.8  | 967.7  | 991.2  | 1014.7 | 1009.2 | 1003.7 | 998.1  | 992.6  | 992.6  | 992.6  | 992.6  |
| 65°   | 1047.9 | 1067.3 | 1085.2 | 1103.2 | 1097.7 | 1093.5 | 1088.0 | 1082.5 | 1079.7 | 1076.9 | 1079.7 |
| 67.5° | 1153.0 | 1166.8 | 1179.2 | 1193.1 | 1186.2 | 1179.2 | 1172.3 | 1165.4 | 1162.7 | 1158.5 | 1162.7 |
| 70°   | 1226.2 | 1240.1 | 1253.9 | 1267.7 | 1260.8 | 1253.9 | 1245.6 | 1238.7 | 1237.3 | 1235.9 | 1237.3 |
| 72.5° | 1267.7 | 1284.3 | 1300.9 | 1317.5 | 1313.3 | 1307.8 | 1303.7 | 1298.1 | 1296.8 | 1294.0 | 1296.8 |
| 75°   | 1230.4 | 1244.2 | 1256.7 | 1269.1 | 1262.2 | 1255.3 | 1248.4 | 1241.5 | 1237.3 | 1231.8 | 1237.3 |
| 77.5° | 1065.9 | 1067.3 | 1067.3 | 1067.3 | 1059.0 | 1050.7 | 1042.4 | 1034.1 | 1031.3 | 1027.2 | 1031.3 |
| 80°   | 741.0  | 712.0  | 682.9  | 653.9  | 626.3  | 598.6  | 571.0  | 543.3  | 536.4  | 528.1  | 536.4  |
| 82.5° | 233.6  | 208.8  | 185.3  | 160.4  | 149.3  | 136.9  | 125.8  | 113.4  | 109.2  | 103.7  | 109.2  |
| 85°   | 70.5   | 66.4   | 60.8   | 56.7   | 52.5   | 48.4   | 42.9   | 38.7   | 35.9   | 33.2   | 35.9   |
| 87.5° | 6.9    | 6.9    | 5.5    | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    | 2.8    | 4.1    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 335.9  | 335.9  | 335.9  | 334.6  | 334.6  | 334.6  | 335.9  | 335.9  | 335.9  | 335.9  | 334.6  |
| 5°    | 329.0  | 329.0  | 327.6  | 327.6  | 326.3  | 323.5  | 320.7  | 316.6  | 313.8  | 308.3  | 301.4  |
| 7.5°  | 284.8  | 283.4  | 283.4  | 282.0  | 280.6  | 275.1  | 269.6  | 262.7  | 257.1  | 261.3  | 264.1  |
| 10°   | 247.5  | 240.5  | 233.6  | 225.3  | 218.4  | 217.0  | 215.7  | 212.9  | 211.5  | 214.3  | 215.7  |
| 12.5° | 211.5  | 204.6  | 197.7  | 190.8  | 183.9  | 188.0  | 193.5  | 197.7  | 201.8  | 200.5  | 199.1  |
| 15°   | 236.4  | 226.7  | 217.0  | 206.0  | 196.3  | 190.8  | 185.3  | 179.7  | 174.2  | 174.2  | 174.2  |
| 17.5° | 203.2  | 199.1  | 193.5  | 189.4  | 183.9  | 183.9  | 182.5  | 182.5  | 181.1  | 183.9  | 188.0  |
| 20°   | 240.5  | 229.5  | 219.8  | 208.8  | 197.7  | 190.8  | 183.9  | 177.0  | 170.0  | 174.2  | 178.3  |
| 22.5° | 192.2  | 192.2  | 193.5  | 193.5  | 193.5  | 197.7  | 203.2  | 207.4  | 211.5  | 204.6  | 196.3  |
| 25°   | 266.8  | 259.9  | 251.6  | 244.7  | 236.4  | 225.3  | 212.9  | 201.8  | 189.4  | 196.3  | 203.2  |
| 27.5° | 305.5  | 294.5  | 282.0  | 271.0  | 258.5  | 251.6  | 244.7  | 237.8  | 230.9  | 225.3  | 221.2  |
| 30°   | 366.4  | 358.1  | 349.8  | 341.5  | 333.2  | 316.6  | 298.6  | 282.0  | 264.1  | 257.1  | 251.6  |
| 32.5° | 381.6  | 373.3  | 365.0  | 355.3  | 347.0  | 337.3  | 327.6  | 318.0  | 308.3  | 295.8  | 282.0  |
| 35°   | 398.1  | 389.9  | 382.9  | 374.6  | 366.4  | 355.3  | 345.6  | 334.6  | 323.5  | 313.8  | 302.8  |
| 37.5° | 418.9  | 413.4  | 406.4  | 400.9  | 394.0  | 381.6  | 367.7  | 355.3  | 341.5  | 329.0  | 318.0  |
| 40°   | 446.5  | 441.0  | 436.9  | 431.3  | 425.8  | 412.0  | 398.1  | 384.3  | 370.5  | 355.3  | 340.1  |
| 42.5° | 481.1  | 475.6  | 470.0  | 464.5  | 459.0  | 445.2  | 429.9  | 416.1  | 400.9  | 384.3  | 369.1  |
| 45°   | 526.7  | 519.8  | 514.3  | 507.4  | 500.5  | 483.9  | 467.3  | 450.7  | 434.1  | 417.5  | 400.9  |
| 47.5° | 577.9  | 572.3  | 566.8  | 561.3  | 555.8  | 536.4  | 515.7  | 496.3  | 475.6  | 459.0  | 442.4  |
| 50°   | 633.2  | 630.4  | 627.6  | 623.5  | 620.7  | 595.8  | 569.6  | 544.7  | 518.4  | 501.8  | 485.2  |
| 52.5° | 694.0  | 692.6  | 691.2  | 688.5  | 687.1  | 658.1  | 630.4  | 601.4  | 572.3  | 557.1  | 540.5  |
| 55°   | 764.5  | 764.5  | 764.5  | 763.1  | 763.1  | 732.7  | 700.9  | 670.5  | 638.7  | 623.5  | 608.3  |
| 57.5° | 840.5  | 841.9  | 843.3  | 844.7  | 846.1  | 815.7  | 786.6  | 756.2  | 725.8  | 709.2  | 694.0  |
| 60°   | 918.0  | 922.1  | 924.9  | 929.0  | 931.8  | 902.7  | 873.7  | 843.3  | 814.3  | 800.4  | 785.2  |
| 62.5° | 992.6  | 998.1  | 1003.7 | 1009.2 | 1014.7 | 991.2  | 967.7  | 942.8  | 919.3  | 902.7  | 887.5  |
| 65°   | 1082.5 | 1088.0 | 1093.5 | 1097.7 | 1103.2 | 1085.2 | 1067.3 | 1047.9 | 1029.9 | 1013.3 | 996.8  |
| 67.5° | 1165.4 | 1172.3 | 1179.2 | 1186.2 | 1193.1 | 1179.2 | 1166.8 | 1153.0 | 1139.2 | 1119.8 | 1101.8 |
| 70°   | 1238.7 | 1245.6 | 1253.9 | 1260.8 | 1267.7 | 1253.9 | 1240.1 | 1226.2 | 1212.4 | 1195.8 | 1179.2 |
| 72.5° | 1298.1 | 1303.7 | 1307.8 | 1313.3 | 1317.5 | 1300.9 | 1284.3 | 1267.7 | 1251.1 | 1231.8 | 1213.8 |
| 75°   | 1241.5 | 1248.4 | 1255.3 | 1262.2 | 1269.1 | 1256.7 | 1244.2 | 1230.4 | 1218.0 | 1204.1 | 1190.3 |
| 77.5° | 1034.1 | 1042.4 | 1050.7 | 1059.0 | 1067.3 | 1067.3 | 1067.3 | 1065.9 | 1065.9 | 1068.6 | 1070.0 |
| 80°   | 543.3  | 571.0  | 598.6  | 626.3  | 653.9  | 682.9  | 712.0  | 741.0  | 770.0  | 794.9  | 819.8  |
| 82.5° | 113.4  | 125.8  | 136.9  | 149.3  | 160.4  | 185.3  | 208.8  | 233.6  | 257.1  | 313.8  | 370.5  |
| 85°   | 38.7   | 42.9   | 48.4   | 52.5   | 56.7   | 60.8   | 66.4   | 70.5   | 74.7   | 94.0   | 113.4  |
| 87.5° | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    | 5.5    | 6.9    | 6.9    | 8.3    | 9.7    | 11.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 334.6  | 333.2  | 333.2  | 331.8  | 331.8  | 330.4  | 329.0  | 327.6  | 326.3  | 324.9  | 323.5  |
| 5°    | 295.8  | 288.9  | 287.6  | 286.2  | 284.8  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  |
| 7.5°  | 268.2  | 271.0  | 272.3  | 273.7  | 273.7  | 275.1  | 275.1  | 276.5  | 276.5  | 276.5  | 275.1  |
| 10°   | 218.4  | 219.8  | 224.0  | 228.1  | 230.9  | 235.0  | 235.0  | 235.0  | 233.6  | 233.6  | 240.5  |
| 12.5° | 197.7  | 196.3  | 199.1  | 201.8  | 204.6  | 207.4  | 217.0  | 226.7  | 235.0  | 244.7  | 250.2  |
| 15°   | 172.8  | 172.8  | 174.2  | 177.0  | 178.3  | 179.7  | 185.3  | 189.4  | 194.9  | 199.1  | 207.4  |
| 17.5° | 190.8  | 193.5  | 186.6  | 179.7  | 171.4  | 164.5  | 178.3  | 192.2  | 206.0  | 219.8  | 226.7  |
| 20°   | 181.1  | 185.3  | 190.8  | 194.9  | 200.5  | 204.6  | 206.0  | 206.0  | 207.4  | 207.4  | 207.4  |
| 22.5° | 189.4  | 181.1  | 188.0  | 196.3  | 203.2  | 210.1  | 207.4  | 204.6  | 201.8  | 199.1  | 211.5  |
| 25°   | 210.1  | 217.0  | 211.5  | 206.0  | 200.5  | 194.9  | 206.0  | 218.4  | 229.5  | 240.5  | 236.4  |
| 27.5° | 215.7  | 210.1  | 217.0  | 224.0  | 230.9  | 237.8  | 233.6  | 230.9  | 226.7  | 222.6  | 230.9  |
| 30°   | 244.7  | 237.8  | 235.0  | 232.3  | 228.1  | 225.3  | 232.3  | 237.8  | 244.7  | 250.2  | 248.8  |
| 32.5° | 269.6  | 255.8  | 255.8  | 255.8  | 254.4  | 254.4  | 254.4  | 255.8  | 255.8  | 255.8  | 265.4  |
| 35°   | 293.1  | 282.0  | 279.3  | 276.5  | 273.7  | 271.0  | 273.7  | 276.5  | 277.9  | 280.6  | 293.1  |
| 37.5° | 305.5  | 293.1  | 293.1  | 293.1  | 293.1  | 293.1  | 294.5  | 297.2  | 298.6  | 300.0  | 313.8  |
| 40°   | 324.9  | 309.7  | 311.1  | 313.8  | 315.2  | 316.6  | 319.3  | 323.5  | 326.3  | 329.0  | 341.5  |
| 42.5° | 352.5  | 335.9  | 337.3  | 340.1  | 341.5  | 342.9  | 348.4  | 352.5  | 358.1  | 362.2  | 376.0  |
| 45°   | 384.3  | 367.7  | 370.5  | 371.9  | 374.6  | 376.0  | 381.6  | 387.1  | 391.2  | 396.8  | 414.7  |
| 47.5° | 424.4  | 407.8  | 412.0  | 414.7  | 418.9  | 421.7  | 425.8  | 428.6  | 432.7  | 435.5  | 454.8  |
| 50°   | 468.7  | 452.1  | 457.6  | 463.1  | 468.7  | 474.2  | 475.6  | 475.6  | 477.0  | 477.0  | 501.8  |
| 52.5° | 525.3  | 508.7  | 514.3  | 521.2  | 526.7  | 532.2  | 535.0  | 537.8  | 539.2  | 541.9  | 566.8  |
| 55°   | 591.7  | 576.5  | 584.8  | 593.1  | 601.4  | 609.7  | 611.0  | 612.4  | 612.4  | 613.8  | 638.7  |
| 57.5° | 677.4  | 660.8  | 671.9  | 684.3  | 695.4  | 706.4  | 706.4  | 705.1  | 705.1  | 703.7  | 728.6  |
| 60°   | 771.4  | 756.2  | 770.0  | 785.2  | 799.1  | 812.9  | 808.7  | 804.6  | 799.1  | 794.9  | 822.6  |
| 62.5° | 871.0  | 854.4  | 875.1  | 895.8  | 916.6  | 937.3  | 929.0  | 922.1  | 913.8  | 905.5  | 934.5  |
| 65°   | 978.8  | 962.2  | 987.1  | 1012.0 | 1036.8 | 1061.7 | 1046.5 | 1031.3 | 1014.7 | 999.5  | 1032.7 |
| 67.5° | 1082.5 | 1063.1 | 1089.4 | 1114.3 | 1140.5 | 1165.4 | 1147.4 | 1129.5 | 1111.5 | 1093.5 | 1132.2 |
| 70°   | 1162.7 | 1146.1 | 1169.6 | 1193.1 | 1216.6 | 1240.1 | 1222.1 | 1204.1 | 1186.2 | 1168.2 | 1215.2 |
| 72.5° | 1194.4 | 1175.1 | 1204.1 | 1234.5 | 1263.6 | 1292.6 | 1274.6 | 1256.7 | 1237.3 | 1219.3 | 1267.7 |
| 75°   | 1176.5 | 1162.7 | 1202.7 | 1241.5 | 1281.5 | 1320.3 | 1294.0 | 1267.7 | 1241.5 | 1215.2 | 1258.0 |
| 77.5° | 1072.8 | 1074.2 | 1130.9 | 1186.2 | 1242.8 | 1298.1 | 1251.1 | 1204.1 | 1157.1 | 1110.1 | 1130.9 |
| 80°   | 844.7  | 869.6  | 934.5  | 999.5  | 1063.1 | 1128.1 | 1060.4 | 994.0  | 926.3  | 858.5  | 844.7  |
| 82.5° | 425.8  | 482.5  | 554.4  | 627.6  | 699.5  | 771.4  | 703.7  | 637.3  | 569.6  | 501.8  | 459.0  |
| 85°   | 132.7  | 152.1  | 181.1  | 210.1  | 239.2  | 268.2  | 233.6  | 199.1  | 164.5  | 130.0  | 116.1  |
| 87.5° | 11.1   | 12.4   | 12.4   | 11.1   | 11.1   | 9.7    | 11.1   | 12.4   | 12.4   | 13.8   | 12.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  | 340.1  |
| 2.5°  | 322.1  | 319.3  | 318.0  | 313.8  | 309.7  | 305.5  | 301.4  | 301.4  | 302.8  | 302.8  | 302.8  |
| 5°    | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 283.4  | 284.8  | 284.8  | 284.8  |
| 7.5°  | 273.7  | 272.3  | 271.0  | 269.6  | 269.6  | 268.2  | 266.8  | 262.7  | 257.1  | 253.0  | 247.5  |
| 10°   | 248.8  | 255.8  | 262.7  | 265.4  | 268.2  | 269.6  | 272.3  | 272.3  | 273.7  | 273.7  | 273.7  |
| 12.5° | 257.1  | 262.7  | 268.2  | 266.8  | 265.4  | 264.1  | 262.7  | 257.1  | 250.2  | 244.7  | 237.8  |
| 15°   | 215.7  | 222.6  | 230.9  | 240.5  | 251.6  | 261.3  | 271.0  | 272.3  | 273.7  | 275.1  | 276.5  |
| 17.5° | 235.0  | 241.9  | 248.8  | 251.6  | 255.8  | 258.5  | 261.3  | 255.8  | 248.8  | 243.3  | 236.4  |
| 20°   | 206.0  | 206.0  | 204.6  | 221.2  | 239.2  | 255.8  | 272.3  | 275.1  | 277.9  | 279.3  | 282.0  |
| 22.5° | 222.6  | 235.0  | 246.1  | 244.7  | 243.3  | 241.9  | 240.5  | 240.5  | 240.5  | 239.2  | 239.2  |
| 25°   | 233.6  | 229.5  | 225.3  | 240.5  | 254.4  | 269.6  | 283.4  | 286.2  | 288.9  | 290.3  | 293.1  |
| 27.5° | 240.5  | 248.8  | 257.1  | 254.4  | 251.6  | 247.5  | 244.7  | 246.1  | 248.8  | 250.2  | 251.6  |
| 30°   | 248.8  | 247.5  | 246.1  | 261.3  | 275.1  | 290.3  | 304.1  | 305.5  | 306.9  | 306.9  | 308.3  |
| 32.5° | 273.7  | 283.4  | 291.7  | 298.6  | 306.9  | 313.8  | 320.7  | 333.2  | 347.0  | 359.4  | 371.9  |
| 35°   | 305.5  | 316.6  | 329.0  | 342.9  | 356.7  | 370.5  | 384.3  | 387.1  | 391.2  | 394.0  | 396.8  |
| 37.5° | 326.3  | 340.1  | 352.5  | 367.7  | 382.9  | 396.8  | 412.0  | 414.7  | 416.1  | 418.9  | 420.3  |
| 40°   | 353.9  | 366.4  | 378.8  | 395.4  | 412.0  | 427.2  | 443.8  | 446.5  | 447.9  | 450.7  | 452.1  |
| 42.5° | 388.5  | 402.3  | 414.7  | 431.3  | 446.5  | 463.1  | 478.3  | 479.7  | 482.5  | 483.9  | 485.2  |
| 45°   | 431.3  | 449.3  | 465.9  | 481.1  | 494.9  | 510.1  | 524.0  | 525.3  | 526.7  | 526.7  | 528.1  |
| 47.5° | 474.2  | 492.2  | 511.5  | 526.7  | 541.9  | 555.8  | 571.0  | 573.7  | 575.1  | 577.9  | 579.3  |
| 50°   | 525.3  | 550.2  | 573.7  | 587.5  | 602.8  | 616.6  | 630.4  | 631.8  | 634.6  | 635.9  | 637.3  |
| 52.5° | 590.3  | 615.2  | 638.7  | 652.5  | 667.7  | 681.6  | 695.4  | 696.8  | 696.8  | 698.1  | 698.1  |
| 55°   | 663.6  | 688.5  | 713.4  | 727.2  | 741.0  | 754.8  | 768.7  | 768.7  | 768.7  | 767.3  | 767.3  |
| 57.5° | 753.4  | 776.9  | 801.8  | 815.7  | 829.5  | 843.3  | 857.1  | 857.1  | 857.1  | 857.1  | 857.1  |
| 60°   | 851.6  | 879.2  | 906.9  | 919.3  | 931.8  | 944.2  | 956.7  | 953.9  | 949.8  | 947.0  | 942.8  |
| 62.5° | 962.2  | 991.2  | 1018.9 | 1028.6 | 1036.8 | 1046.5 | 1054.8 | 1050.7 | 1045.1 | 1041.0 | 1035.5 |
| 65°   | 1065.9 | 1099.1 | 1132.2 | 1139.2 | 1146.1 | 1151.6 | 1158.5 | 1151.6 | 1144.7 | 1136.4 | 1129.5 |
| 67.5° | 1170.9 | 1208.3 | 1247.0 | 1249.7 | 1252.5 | 1255.3 | 1258.0 | 1251.1 | 1244.2 | 1235.9 | 1229.0 |
| 70°   | 1262.2 | 1309.2 | 1356.2 | 1357.6 | 1359.0 | 1360.3 | 1361.7 | 1354.8 | 1347.9 | 1339.6 | 1332.7 |
| 72.5° | 1314.7 | 1363.1 | 1410.1 | 1414.3 | 1417.0 | 1421.2 | 1423.9 | 1417.0 | 1411.5 | 1404.6 | 1397.7 |
| 75°   | 1299.5 | 1342.4 | 1383.8 | 1379.7 | 1375.6 | 1370.0 | 1365.9 | 1354.8 | 1343.8 | 1331.3 | 1320.3 |
| 77.5° | 1151.6 | 1170.9 | 1191.7 | 1169.6 | 1146.1 | 1123.9 | 1100.4 | 1089.4 | 1076.9 | 1065.9 | 1053.4 |
| 80°   | 830.9  | 815.7  | 801.8  | 760.4  | 718.9  | 676.0  | 634.6  | 606.9  | 579.3  | 551.6  | 524.0  |
| 82.5° | 417.5  | 374.6  | 331.8  | 294.5  | 257.1  | 218.4  | 181.1  | 167.3  | 152.1  | 138.2  | 123.0  |
| 85°   | 103.7  | 89.9   | 76.0   | 70.5   | 65.0   | 59.4   | 53.9   | 47.0   | 41.5   | 34.6   | 27.6   |
| 87.5° | 12.4   | 11.1   | 9.7    | 8.3    | 8.3    | 6.9    | 5.5    | 5.5    | 5.5    | 4.1    | 4.1    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560221

CATALOG NUMBER: SDL-PA1-30-750-U-5WQ

**CANDELA DISTRIBUTION (continued):**

|       | 357.5° | 360°   |
|-------|--------|--------|
| 0°    | 340.1  | 340.1  |
| 2.5°  | 302.8  | 301.4  |
| 5°    | 284.8  | 284.8  |
| 7.5°  | 246.1  | 243.3  |
| 10°   | 273.7  | 273.7  |
| 12.5° | 239.2  | 240.5  |
| 15°   | 276.5  | 276.5  |
| 17.5° | 236.4  | 235.0  |
| 20°   | 282.0  | 282.0  |
| 22.5° | 239.2  | 239.2  |
| 25°   | 293.1  | 291.7  |
| 27.5° | 251.6  | 251.6  |
| 30°   | 308.3  | 308.3  |
| 32.5° | 373.3  | 374.6  |
| 35°   | 398.1  | 398.1  |
| 37.5° | 421.7  | 421.7  |
| 40°   | 452.1  | 450.7  |
| 42.5° | 486.6  | 486.6  |
| 45°   | 529.5  | 529.5  |
| 47.5° | 580.6  | 582.0  |
| 50°   | 637.3  | 637.3  |
| 52.5° | 698.1  | 696.8  |
| 55°   | 767.3  | 767.3  |
| 57.5° | 853.0  | 847.5  |
| 60°   | 941.5  | 940.1  |
| 62.5° | 1034.1 | 1031.3 |
| 65°   | 1128.1 | 1125.3 |
| 67.5° | 1227.6 | 1224.9 |
| 70°   | 1332.7 | 1331.3 |
| 72.5° | 1393.5 | 1389.4 |
| 75°   | 1317.5 | 1314.7 |
| 77.5° | 1042.4 | 1029.9 |
| 80°   | 517.0  | 510.1  |
| 82.5° | 123.0  | 123.0  |
| 85°   | 26.3   | 24.9   |
| 87.5° | 4.1    | 4.1    |
| 90°   | 0.0    | 0.0    |

Report Generated By 670245982











--- HS --- SS



u





























(END OF REPORT)