

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560241

Luminaire Tested: **SDL-PA1-30-750-U-T4W**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560241  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-30-750-U-T4W  
Description: Springdale  
(1) 70 CRI, 5000K, 375mA LIGHT ENGINE WITH 24 LEDS AND TYPE IV WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3781.8 lumens  
Efficiency: N/A  
Efficacy: 125.6 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type IV - Medium  
BUG Rating: B1 - U0 - G2

Input Watts (W): 30.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P560241

CATALOG NUMBER: SDL-PA1-30-750-U-T4W

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.4 fc  
 Type IV - Medium - N/A

REPORT NUMBER: P560241

CATALOG NUMBER: SDL-PA1-30-750-U-T4W

## Luminous Intensity Polar Plot



REPORT NUMBER: P560241

CATALOG NUMBER: SDL-PA1-30-750-U-T4W


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 813.1    | 0.0    | 813.1  |
|                    | % Fixture | 21.5     | 0.0    | 21.5   |
| <b>Street Side</b> | Lumens    | 2968.7   | 0.0    | 2968.7 |
|                    | % Fixture | 78.5     | 0.0    | 78.5   |
| <b>Total</b>       | Lumens    | 3781.8   | 0.0    | 3781.8 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 36.5   | 1.0       |
| 10°-20°   | 92.0   | 2.4       |
| 20°-30°   | 160.9  | 4.3       |
| 30°-40°   | 283.4  | 7.5       |
| 40°-50°   | 427.5  | 11.3      |
| 50°-60°   | 680.1  | 18.0      |
| 60°-70°   | 997.3  | 26.4      |
| 70°-80°   | 935.1  | 24.7      |
| 80°-90°   | 168.9  | 4.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 3781.8 | 100.0     |
| 0°-180°   | 3781.8 | 100.0     |



REPORT NUMBER: P560241


CATALOG NUMBER: SDL-PA1-30-750-U-T4W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 155.9  | 4.1       |                         |      |         |
| FM   | (30°-60°)   | 1018.8 | 26.9      |                         |      |         |
| FH   | (60°-80°)   | 1654.9 | 43.8      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 139.0  | 3.7       |                         |      | G2/225  |
| BL   | (0°-30°)    | 133.5  | 3.5       | B1/500                  |      |         |
| BM   | (30°-60°)   | 372.2  | 9.8       | B1/1000                 |      |         |
| BH   | (60°-80°)   | 277.6  | 7.3       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 29.8   | 0.8       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type IV Medium





REPORT NUMBER: P560241

CATALOG NUMBER: SDL-PA1-30-750-U-T4W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    | 50°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  |
| 2.5°  | 399.3  | 416.0  | 424.4  | 432.8  | 435.6  | 438.4  | 438.4  | 437.0  | 437.0  | 437.0  | 439.8  |
| 5°    | 406.2  | 404.9  | 404.9  | 404.9  | 403.5  | 402.1  | 400.7  | 397.9  | 396.5  | 393.7  | 392.3  |
| 7.5°  | 372.7  | 400.7  | 402.1  | 403.5  | 403.5  | 402.1  | 404.9  | 407.6  | 404.9  | 400.7  | 395.1  |
| 10°   | 442.5  | 441.2  | 438.4  | 435.6  | 431.4  | 427.2  | 395.1  | 361.6  | 364.4  | 367.2  | 340.6  |
| 12.5° | 383.9  | 410.4  | 421.6  | 432.8  | 434.2  | 434.2  | 411.8  | 388.1  | 357.4  | 326.7  | 314.1  |
| 15°   | 469.1  | 466.3  | 460.7  | 455.1  | 417.4  | 378.3  | 356.0  | 333.7  | 333.7  | 333.7  | 296.0  |
| 17.5° | 395.1  | 393.7  | 418.8  | 443.9  | 430.0  | 416.0  | 383.9  | 351.8  | 304.3  | 255.5  | 286.2  |
| 20°   | 484.4  | 484.4  | 477.4  | 470.5  | 406.2  | 340.6  | 344.8  | 347.6  | 349.0  | 349.0  | 335.1  |
| 22.5° | 406.2  | 403.5  | 406.2  | 407.6  | 407.6  | 407.6  | 349.0  | 290.4  | 322.5  | 353.2  | 321.1  |
| 25°   | 484.4  | 485.8  | 484.4  | 483.0  | 424.4  | 364.4  | 374.1  | 383.9  | 339.2  | 293.2  | 323.9  |
| 27.5° | 423.0  | 421.6  | 414.6  | 407.6  | 409.0  | 410.4  | 379.7  | 347.6  | 365.8  | 383.9  | 351.8  |
| 30°   | 517.9  | 519.3  | 515.1  | 509.6  | 450.9  | 392.3  | 389.5  | 385.3  | 372.7  | 360.2  | 371.3  |
| 32.5° | 625.4  | 625.4  | 582.2  | 538.9  | 502.6  | 464.9  | 434.2  | 403.5  | 416.0  | 428.6  | 414.6  |
| 35°   | 682.7  | 679.9  | 665.9  | 650.6  | 583.5  | 515.1  | 473.3  | 430.0  | 434.2  | 437.0  | 437.0  |
| 37.5° | 784.6  | 783.2  | 763.6  | 744.1  | 653.3  | 561.2  | 506.8  | 450.9  | 459.3  | 466.3  | 456.5  |
| 40°   | 911.6  | 911.6  | 896.3  | 879.5  | 763.6  | 646.4  | 569.6  | 492.8  | 491.4  | 488.6  | 477.4  |
| 42.5° | 1034.5 | 1038.7 | 1028.9 | 1019.1 | 883.7  | 748.3  | 647.8  | 547.3  | 534.7  | 522.1  | 511.0  |
| 45°   | 1115.4 | 1121.0 | 1129.4 | 1137.8 | 1003.8 | 869.7  | 752.5  | 633.8  | 610.1  | 584.9  | 565.4  |
| 47.5° | 1197.8 | 1189.4 | 1200.6 | 1211.8 | 1097.3 | 982.8  | 854.4  | 725.9  | 686.9  | 647.8  | 626.8  |
| 50°   | 1274.6 | 1271.8 | 1276.0 | 1280.2 | 1186.6 | 1093.1 | 960.5  | 827.9  | 780.4  | 731.5  | 707.8  |
| 52.5° | 1375.1 | 1365.3 | 1359.7 | 1354.2 | 1274.6 | 1195.0 | 1069.4 | 942.3  | 886.5  | 829.3  | 801.3  |
| 55°   | 1471.4 | 1467.2 | 1458.9 | 1449.1 | 1380.7 | 1312.3 | 1179.7 | 1047.0 | 988.4  | 929.8  | 897.7  |
| 57.5° | 1570.6 | 1567.8 | 1566.4 | 1565.0 | 1504.9 | 1444.9 | 1309.5 | 1172.7 | 1105.7 | 1037.3 | 1010.7 |
| 60°   | 1664.1 | 1665.5 | 1676.7 | 1686.4 | 1640.4 | 1594.3 | 1457.5 | 1320.7 | 1235.5 | 1148.9 | 1122.4 |
| 62.5° | 1719.9 | 1724.1 | 1752.0 | 1778.6 | 1753.4 | 1728.3 | 1587.3 | 1444.9 | 1355.6 | 1264.8 | 1246.7 |
| 65°   | 1648.7 | 1669.7 | 1750.6 | 1831.6 | 1831.6 | 1831.6 | 1703.2 | 1573.3 | 1495.2 | 1417.0 | 1401.6 |
| 67.5° | 1489.6 | 1510.5 | 1626.4 | 1740.9 | 1800.9 | 1860.9 | 1777.2 | 1693.4 | 1640.4 | 1585.9 | 1566.4 |
| 70°   | 1358.4 | 1370.9 | 1479.8 | 1587.3 | 1738.1 | 1888.9 | 1834.4 | 1778.6 | 1775.8 | 1771.6 | 1718.5 |
| 72.5° | 1248.1 | 1276.0 | 1365.3 | 1453.3 | 1661.3 | 1869.3 | 1867.9 | 1866.5 | 1923.8 | 1981.0 | 1879.1 |
| 75°   | 998.2  | 995.4  | 1079.1 | 1162.9 | 1397.4 | 1630.6 | 1761.8 | 1891.6 | 2056.4 | 2219.7 | 2063.4 |
| 77.5° | 445.3  | 476.1  | 555.6  | 635.2  | 846.0  | 1055.4 | 1308.1 | 1560.8 | 1923.8 | 2285.3 | 2126.2 |
| 80°   | 127.0  | 134.0  | 156.4  | 177.3  | 276.4  | 374.1  | 639.4  | 903.2  | 1359.7 | 1814.9 | 1707.4 |
| 82.5° | 67.0   | 69.8   | 83.8   | 96.3   | 124.2  | 150.8  | 251.3  | 350.4  | 742.7  | 1133.6 | 1035.9 |
| 85°   | 32.1   | 29.3   | 37.7   | 44.7   | 60.0   | 75.4   | 115.9  | 156.4  | 287.6  | 418.8  | 361.6  |
| 87.5° | 7.0    | 7.0    | 8.4    | 8.4    | 12.6   | 16.8   | 25.1   | 33.5   | 32.1   | 29.3   | 34.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560241

CATALOG NUMBER: SDL-PA1-30-750-U-T4W

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   | 105°  |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|
| 0°    | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8  | 439.8 |
| 2.5°  | 441.2  | 442.5  | 443.9  | 442.5  | 441.2  | 439.8  | 439.8  | 438.4  | 438.4  | 437.0  | 434.2 |
| 5°    | 390.9  | 410.4  | 430.0  | 431.4  | 432.8  | 432.8  | 431.4  | 430.0  | 427.2  | 425.8  | 423.0 |
| 7.5°  | 389.5  | 382.5  | 375.5  | 376.9  | 378.3  | 379.7  | 379.7  | 375.5  | 374.1  | 363.0  | 351.8 |
| 10°   | 312.7  | 305.7  | 298.8  | 302.9  | 307.1  | 322.5  | 330.9  | 328.1  | 325.3  | 305.7  | 284.8 |
| 12.5° | 301.5  | 298.8  | 296.0  | 275.0  | 254.1  | 272.2  | 284.8  | 283.4  | 279.2  | 261.1  | 242.9 |
| 15°   | 258.3  | 259.7  | 259.7  | 283.4  | 307.1  | 322.5  | 333.7  | 330.9  | 328.1  | 305.7  | 283.4 |
| 17.5° | 315.5  | 300.2  | 283.4  | 279.2  | 275.0  | 282.0  | 272.2  | 256.9  | 266.6  | 263.9  | 261.1 |
| 20°   | 319.7  | 282.0  | 242.9  | 282.0  | 321.1  | 330.9  | 351.8  | 350.4  | 346.2  | 326.7  | 307.1 |
| 22.5° | 289.0  | 311.3  | 332.3  | 311.3  | 290.4  | 276.4  | 269.4  | 266.6  | 265.2  | 270.8  | 275.0 |
| 25°   | 354.6  | 312.7  | 269.4  | 321.1  | 371.3  | 382.5  | 388.1  | 383.9  | 382.5  | 357.4  | 332.3 |
| 27.5° | 318.3  | 340.6  | 363.0  | 379.7  | 396.5  | 410.4  | 452.3  | 411.8  | 410.4  | 386.7  | 361.6 |
| 30°   | 381.1  | 404.9  | 428.6  | 471.9  | 515.1  | 538.9  | 547.3  | 544.5  | 537.5  | 499.8  | 462.1 |
| 32.5° | 400.7  | 448.1  | 494.2  | 513.7  | 531.9  | 557.0  | 569.6  | 568.2  | 561.2  | 516.5  | 470.5 |
| 35°   | 437.0  | 471.9  | 506.8  | 533.3  | 558.4  | 582.2  | 593.3  | 597.5  | 589.1  | 533.3  | 476.1 |
| 37.5° | 446.7  | 491.4  | 536.1  | 564.0  | 591.9  | 610.1  | 619.8  | 632.4  | 622.6  | 555.6  | 487.2 |
| 40°   | 466.3  | 519.3  | 571.0  | 598.9  | 625.4  | 642.2  | 658.9  | 674.3  | 661.7  | 580.8  | 498.4 |
| 42.5° | 498.4  | 552.8  | 605.9  | 638.0  | 668.7  | 692.4  | 712.0  | 732.9  | 709.2  | 604.5  | 498.4 |
| 45°   | 545.9  | 596.1  | 646.4  | 689.6  | 731.5  | 760.8  | 788.8  | 818.1  | 770.6  | 635.2  | 498.4 |
| 47.5° | 605.9  | 654.7  | 702.2  | 770.6  | 839.0  | 865.5  | 899.1  | 927.0  | 850.2  | 674.3  | 498.4 |
| 50°   | 682.7  | 737.1  | 791.6  | 882.3  | 971.6  | 996.8  | 1038.7 | 1059.6 | 956.3  | 734.3  | 511.0 |
| 52.5° | 772.0  | 832.0  | 890.7  | 996.8  | 1102.9 | 1144.8 | 1200.6 | 1214.6 | 1063.8 | 794.4  | 523.5 |
| 55°   | 865.5  | 946.5  | 1026.1 | 1143.4 | 1259.2 | 1299.7 | 1379.3 | 1390.5 | 1202.0 | 868.3  | 533.3 |
| 57.5° | 984.2  | 1079.1 | 1172.7 | 1287.2 | 1400.2 | 1457.5 | 1581.7 | 1585.9 | 1362.5 | 959.1  | 554.2 |
| 60°   | 1095.9 | 1214.6 | 1331.8 | 1440.7 | 1549.6 | 1639.0 | 1782.8 | 1784.1 | 1513.3 | 1027.5 | 540.3 |
| 62.5° | 1228.5 | 1369.5 | 1509.1 | 1602.7 | 1696.2 | 1806.5 | 1979.6 | 1954.5 | 1619.4 | 1035.9 | 452.3 |
| 65°   | 1384.9 | 1530.1 | 1675.3 | 1754.8 | 1833.0 | 1958.7 | 2145.7 | 2049.4 | 1648.7 | 988.4  | 326.7 |
| 67.5° | 1545.4 | 1680.8 | 1816.3 | 1879.1 | 1941.9 | 2101.1 | 2267.2 | 2060.6 | 1605.5 | 917.2  | 227.6 |
| 70°   | 1665.5 | 1792.5 | 1919.6 | 1974.0 | 2028.5 | 2200.2 | 2303.5 | 1988.0 | 1484.0 | 830.6  | 177.3 |
| 72.5° | 1775.8 | 1895.8 | 2014.5 | 2042.4 | 2068.9 | 2156.9 | 2119.2 | 1752.0 | 1250.9 | 699.4  | 146.6 |
| 75°   | 1907.0 | 1983.8 | 2059.2 | 2008.9 | 1958.7 | 1840.0 | 1626.4 | 1277.4 | 915.8  | 520.7  | 125.6 |
| 77.5° | 1967.0 | 1948.9 | 1929.3 | 1757.6 | 1585.9 | 1267.6 | 1010.7 | 738.5  | 464.9  | 286.2  | 107.5 |
| 80°   | 1599.9 | 1527.3 | 1453.3 | 1165.7 | 878.1  | 600.3  | 393.7  | 249.9  | 170.3  | 128.4  | 86.6  |
| 82.5° | 936.7  | 767.8  | 598.9  | 439.8  | 280.6  | 196.8  | 128.4  | 101.9  | 79.6   | 75.4   | 69.8  |
| 85°   | 302.9  | 268.0  | 233.1  | 184.3  | 135.4  | 83.8   | 48.9   | 44.7   | 41.9   | 46.1   | 48.9  |
| 87.5° | 40.5   | 40.5   | 39.1   | 29.3   | 18.1   | 9.8    | 5.6    | 4.2    | 4.2    | 5.6    | 5.6   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   |



REPORT NUMBER: P560241

CATALOG NUMBER: SDL-PA1-30-750-U-T4W

**CANDELA DISTRIBUTION (continued):**

|       | 110°  | 115°  | 120°  | 125°  | 130°  | 135°  | 140°  | 145°  | 150°  | 155°  | 160°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 439.8 | 439.8 | 439.8 | 439.8 | 439.8 | 439.8 | 439.8 | 439.8 | 439.8 | 439.8 | 439.8 |
| 2.5°  | 434.2 | 432.8 | 431.4 | 430.0 | 428.6 | 425.8 | 414.6 | 403.5 | 399.3 | 393.7 | 389.5 |
| 5°    | 409.0 | 395.1 | 385.3 | 375.5 | 371.3 | 365.8 | 367.2 | 368.6 | 370.0 | 370.0 | 370.0 |
| 7.5°  | 354.6 | 357.4 | 358.8 | 358.8 | 363.0 | 365.8 | 368.6 | 370.0 | 364.4 | 358.8 | 351.8 |
| 10°   | 282.0 | 277.8 | 283.4 | 287.6 | 294.6 | 300.2 | 318.3 | 336.4 | 353.2 | 370.0 | 376.9 |
| 12.5° | 256.9 | 270.8 | 259.7 | 248.5 | 270.8 | 291.8 | 316.9 | 342.0 | 357.4 | 371.3 | 358.8 |
| 15°   | 261.1 | 237.3 | 240.1 | 241.5 | 269.4 | 296.0 | 280.6 | 265.2 | 308.5 | 350.4 | 363.0 |
| 17.5° | 256.9 | 252.7 | 268.0 | 282.0 | 255.5 | 229.0 | 266.6 | 302.9 | 322.5 | 342.0 | 336.4 |
| 20°   | 277.8 | 247.1 | 247.1 | 247.1 | 270.8 | 294.6 | 276.4 | 258.3 | 279.2 | 300.2 | 335.1 |
| 22.5° | 287.6 | 298.8 | 276.4 | 252.7 | 268.0 | 283.4 | 283.4 | 282.0 | 305.7 | 328.1 | 322.5 |
| 25°   | 290.4 | 248.5 | 268.0 | 286.2 | 276.4 | 265.2 | 277.8 | 289.0 | 296.0 | 302.9 | 333.7 |
| 27.5° | 332.3 | 302.9 | 280.6 | 256.9 | 275.0 | 293.2 | 289.0 | 284.8 | 290.4 | 296.0 | 302.9 |
| 30°   | 393.7 | 325.3 | 300.2 | 273.6 | 263.9 | 252.7 | 265.2 | 276.4 | 297.4 | 318.3 | 346.2 |
| 32.5° | 411.8 | 351.8 | 311.3 | 269.4 | 268.0 | 265.2 | 269.4 | 272.2 | 296.0 | 318.3 | 357.4 |
| 35°   | 409.0 | 340.6 | 301.5 | 261.1 | 252.7 | 244.3 | 251.3 | 256.9 | 291.8 | 326.7 | 364.4 |
| 37.5° | 406.2 | 323.9 | 283.4 | 242.9 | 237.3 | 230.3 | 237.3 | 244.3 | 270.8 | 297.4 | 332.3 |
| 40°   | 402.1 | 304.3 | 265.2 | 224.8 | 217.8 | 210.8 | 217.8 | 223.4 | 244.3 | 265.2 | 293.2 |
| 42.5° | 392.3 | 284.8 | 245.7 | 205.2 | 199.6 | 192.7 | 198.2 | 203.8 | 222.0 | 240.1 | 256.9 |
| 45°   | 381.1 | 262.5 | 224.8 | 187.1 | 181.5 | 175.9 | 180.1 | 182.9 | 199.6 | 215.0 | 223.4 |
| 47.5° | 368.6 | 238.7 | 203.8 | 168.9 | 163.3 | 157.8 | 161.9 | 164.7 | 177.3 | 189.9 | 192.7 |
| 50°   | 365.8 | 219.2 | 187.1 | 153.6 | 149.4 | 143.8 | 146.6 | 149.4 | 159.1 | 167.5 | 167.5 |
| 52.5° | 360.2 | 195.4 | 168.9 | 141.0 | 138.2 | 134.0 | 135.4 | 136.8 | 143.8 | 150.8 | 149.4 |
| 55°   | 356.0 | 178.7 | 155.0 | 131.2 | 128.4 | 124.2 | 125.6 | 127.0 | 134.0 | 139.6 | 138.2 |
| 57.5° | 360.2 | 164.7 | 143.8 | 121.5 | 118.7 | 115.9 | 118.7 | 121.5 | 128.4 | 135.4 | 135.4 |
| 60°   | 346.2 | 150.8 | 131.2 | 111.7 | 110.3 | 107.5 | 114.5 | 120.1 | 131.2 | 141.0 | 143.8 |
| 62.5° | 296.0 | 138.2 | 121.5 | 104.7 | 106.1 | 106.1 | 118.7 | 129.8 | 145.2 | 159.1 | 161.9 |
| 65°   | 227.6 | 128.4 | 114.5 | 99.1  | 106.1 | 113.1 | 129.8 | 146.6 | 160.5 | 174.5 | 170.3 |
| 67.5° | 174.5 | 121.5 | 110.3 | 97.7  | 113.1 | 127.0 | 142.4 | 157.8 | 164.7 | 170.3 | 163.3 |
| 70°   | 146.6 | 114.5 | 106.1 | 96.3  | 111.7 | 127.0 | 142.4 | 157.8 | 160.5 | 163.3 | 156.4 |
| 72.5° | 128.4 | 108.9 | 100.5 | 92.1  | 104.7 | 117.3 | 135.4 | 152.2 | 155.0 | 156.4 | 149.4 |
| 75°   | 114.5 | 101.9 | 92.1  | 82.4  | 94.9  | 106.1 | 124.2 | 142.4 | 145.2 | 146.6 | 141.0 |
| 77.5° | 100.5 | 93.5  | 82.4  | 71.2  | 83.8  | 96.3  | 113.1 | 129.8 | 134.0 | 138.2 | 131.2 |
| 80°   | 83.8  | 79.6  | 71.2  | 62.8  | 76.8  | 89.3  | 104.7 | 120.1 | 124.2 | 128.4 | 121.5 |
| 82.5° | 67.0  | 64.2  | 58.6  | 53.0  | 67.0  | 81.0  | 96.3  | 110.3 | 114.5 | 117.3 | 108.9 |
| 85°   | 48.9  | 48.9  | 46.1  | 43.3  | 57.2  | 69.8  | 79.6  | 89.3  | 88.0  | 86.6  | 81.0  |
| 87.5° | 7.0   | 7.0   | 9.8   | 12.6  | 16.8  | 19.5  | 25.1  | 29.3  | 30.7  | 30.7  | 23.7  |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

REPORT NUMBER: P560241

CATALOG NUMBER: SDL-PA1-30-750-U-T4W

**CANDELA DISTRIBUTION (continued):**

|       | 165°  | 170°  | 175°  | 180°  |
|-------|-------|-------|-------|-------|
| 0°    | 439.8 | 439.8 | 439.8 | 439.8 |
| 2.5°  | 385.3 | 385.3 | 383.9 | 386.7 |
| 5°    | 370.0 | 371.3 | 371.3 | 372.7 |
| 7.5°  | 344.8 | 337.8 | 329.5 | 330.9 |
| 10°   | 383.9 | 385.3 | 386.7 | 386.7 |
| 12.5° | 344.8 | 339.2 | 332.3 | 333.7 |
| 15°   | 374.1 | 378.3 | 382.5 | 383.9 |
| 17.5° | 329.5 | 328.1 | 326.7 | 325.3 |
| 20°   | 368.6 | 375.5 | 382.5 | 382.5 |
| 22.5° | 316.9 | 316.9 | 316.9 | 318.3 |
| 25°   | 364.4 | 372.7 | 379.7 | 379.7 |
| 27.5° | 308.5 | 328.1 | 347.6 | 363.0 |
| 30°   | 372.7 | 376.9 | 381.1 | 382.5 |
| 32.5° | 395.1 | 416.0 | 435.6 | 439.8 |
| 35°   | 400.7 | 410.4 | 418.8 | 423.0 |
| 37.5° | 367.2 | 375.5 | 383.9 | 389.5 |
| 40°   | 319.7 | 326.7 | 333.7 | 337.8 |
| 42.5° | 272.2 | 273.6 | 275.0 | 282.0 |
| 45°   | 231.7 | 224.8 | 217.8 | 216.4 |
| 47.5° | 194.1 | 184.3 | 174.5 | 173.1 |
| 50°   | 166.1 | 157.8 | 149.4 | 149.4 |
| 52.5° | 146.6 | 141.0 | 135.4 | 135.4 |
| 55°   | 136.8 | 134.0 | 129.8 | 129.8 |
| 57.5° | 135.4 | 134.0 | 132.6 | 132.6 |
| 60°   | 145.2 | 146.6 | 146.6 | 146.6 |
| 62.5° | 163.3 | 164.7 | 164.7 | 164.7 |
| 65°   | 164.7 | 161.9 | 159.1 | 159.1 |
| 67.5° | 156.4 | 152.2 | 148.0 | 145.2 |
| 70°   | 148.0 | 145.2 | 141.0 | 136.8 |
| 72.5° | 141.0 | 138.2 | 134.0 | 129.8 |
| 75°   | 134.0 | 129.8 | 124.2 | 121.5 |
| 77.5° | 124.2 | 121.5 | 117.3 | 114.5 |
| 80°   | 113.1 | 110.3 | 106.1 | 100.5 |
| 82.5° | 100.5 | 101.9 | 101.9 | 88.0  |
| 85°   | 74.0  | 69.8  | 64.2  | 53.0  |
| 87.5° | 15.4  | 14.0  | 11.2  | 9.8   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   |



Report Generated By 670245982









--- HS --- SS



u









(END OF REPORT)