

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P559902

Luminaire Tested: **SDL-PA1-100-760-U-T2U-HSS**

Issue Date: 7/26/2021

Test Information

Test Method: LM-79-08
Report Number: P559902
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/26/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: SDL-PA1-100-760-U-T2U-HSS
Description: Springdale
(1) 70 CRI, 5700K, 1200mA LIGHT ENGINE WITH 24 LEDS AND TYPE II U OPTICS
AND HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7455.6 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 93.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P559902

CATALOG NUMBER: SDL-PA1-100-760-U-T2U-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 16.5 fc
 Type II - Short - N/A

REPORT NUMBER: P559902
CATALOG NUMBER: SDL-PA1-100-760-U-T2U-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P559902

CATALOG NUMBER: SDL-PA1-100-760-U-T2U-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1008.1	0.0	1008.1
	% Fixture	13.5	0.0	13.5
Street Side	Lumens	6447.5	0.0	6447.5
	% Fixture	86.5	0.0	86.5
Total	Lumens	7455.6	0.0	7455.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.9	1.3
10°-20°	185.3	2.5
20°-30°	279.8	3.8
30°-40°	644.5	8.6
40°-50°	1413.9	19.0
50°-60°	2075.7	27.8
60°-70°	1802.9	24.2
70°-80°	894.0	12.0
80°-90°	63.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7455.6	100.0
0°-180°	7455.6	100.0



REPORT NUMBER: P559902


CATALOG NUMBER: SDL-PA1-100-760-U-T2U-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	369.5	5.0			
FM	(30°-60°)	3681.4	49.4			
FH	(60°-80°)	2340.7	31.4			G2/5000
FVH	(80°-90°)	55.8	0.7			G1/100
BL	(0°-30°)	191.5	2.6	B1/500		
BM	(30°-60°)	452.8	6.1	B1/1000		
BH	(60°-80°)	356.2	4.8	B1/500		G1/500
BVH	(80°-90°)	7.6	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type II Short





REPORT NUMBER: P559902

CATALOG NUMBER: SDL-PA1-100-760-U-T2U-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2
2.5°	1045.2	1131.7	1158.0	1184.3	1206.9	1229.4	1233.2	1236.9	1244.5	1248.2	1252.0
5°	1022.6	1026.4	1026.4	1022.6	1026.4	1030.2	1030.2	1030.2	1030.2	1030.2	1033.9
7.5°	819.6	917.4	947.4	973.8	988.8	1000.1	1007.6	1011.4	1015.1	1018.9	1022.6
10°	988.8	985.0	988.8	988.8	992.6	992.6	906.1	819.6	849.7	876.0	830.9
12.5°	785.8	864.7	898.6	932.4	955.0	973.8	936.2	894.8	815.9	733.1	736.9
15°	947.4	947.4	947.4	947.4	876.0	800.8	751.9	699.3	740.7	778.3	703.1
17.5°	763.2	763.2	830.9	898.6	898.6	894.8	845.9	793.3	688.0	582.8	676.7
20°	943.7	943.7	947.4	951.2	827.1	703.1	744.4	782.0	797.1	812.1	778.3
22.5°	770.7	770.7	782.0	789.5	834.7	879.8	759.5	639.2	736.9	834.7	767.0
25°	996.3	1000.1	1007.6	1011.4	898.6	782.0	834.7	887.3	782.0	676.7	782.0
27.5°	902.3	887.3	887.3	883.5	921.1	955.0	879.8	804.6	872.3	939.9	861.0
30°	1267.0	1255.7	1240.7	1225.7	1082.8	939.9	943.7	943.7	917.4	891.1	936.2
32.5°	1755.8	1737.0	1609.2	1481.3	1376.1	1270.8	1161.8	1052.7	1090.3	1124.2	1101.6
35°	2357.3	2357.3	2237.0	2116.7	1879.9	1643.0	1458.8	1270.8	1255.7	1240.7	1263.3
37.5°	3071.7	2996.5	2853.6	2710.8	2417.5	2120.5	1838.5	1556.5	1522.7	1485.1	1447.5
40°	3601.8	3590.5	3481.5	3372.5	3011.5	2650.6	2319.7	1985.1	1876.1	1763.3	1680.6
42.5°	4154.5	4113.1	4026.7	3936.4	3571.7	3203.3	2849.9	2492.7	2342.3	2191.9	2045.3
45°	4553.0	4541.7	4466.5	4391.3	4094.3	3793.5	3425.1	3052.9	2955.1	2857.4	2582.9
47.5°	4801.2	4737.2	4707.2	4673.3	4417.7	4162.0	3849.9	3534.1	3519.1	3500.3	3154.4
50°	4726.0	4669.6	4677.1	4684.6	4560.5	4436.5	4199.6	3959.0	4000.3	4041.7	3756.0
52.5°	4327.4	4278.6	4346.2	4410.1	4406.4	4402.6	4316.1	4225.9	4376.3	4522.9	4327.4
55°	3530.4	3564.2	3699.6	3834.9	3925.1	4011.6	4135.7	4256.0	4541.7	4823.7	4786.1
57.5°	2767.1	2842.3	2981.5	3116.8	3263.4	3406.3	3669.5	3932.7	4413.9	4891.4	5056.8
60°	1857.3	1906.2	2150.6	2391.2	2526.5	2661.9	2947.6	3229.6	3883.8	4534.2	4966.6
62.5°	1154.2	1180.5	1319.7	1458.8	1733.2	2007.7	2150.6	2289.7	2996.5	3699.6	4500.4
65°	710.6	703.1	759.5	812.1	1082.8	1349.7	1443.7	1534.0	2003.9	2470.1	3714.6
67.5°	424.8	421.1	451.2	481.2	605.3	729.4	876.0	1022.6	1188.1	1349.7	2752.1
70°	345.9	353.4	364.7	376.0	409.8	443.6	579.0	714.3	710.6	706.8	1654.3
72.5°	289.5	297.0	319.6	338.4	364.7	387.3	466.2	541.4	507.6	473.7	789.5
75°	214.3	218.1	248.1	274.5	315.8	353.4	372.2	387.3	372.2	357.2	398.5
77.5°	142.9	142.9	169.2	195.5	236.9	278.2	300.8	323.3	297.0	270.7	282.0
80°	90.2	90.2	105.3	116.6	157.9	199.3	225.6	251.9	229.3	203.0	199.3
82.5°	52.6	56.4	63.9	71.4	97.8	124.1	142.9	161.7	188.0	210.5	169.2
85°	22.6	26.3	33.8	37.6	52.6	63.9	75.2	86.5	109.0	131.6	109.0
87.5°	3.8	3.8	7.5	11.3	15.0	18.8	18.8	18.8	18.8	15.0	18.8
90°	0.0	0.0	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	7.5



REPORT NUMBER: P559902

CATALOG NUMBER: SDL-PA1-100-760-U-T2U-HSS

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2
2.5°	1252.0	1248.2	1244.5	1244.5	1244.5	1240.7	1236.9	1236.9	1236.9	1233.2	1229.4
5°	1033.9	1127.9	1221.9	1225.7	1233.2	1229.4	1225.7	1221.9	1218.1	1214.4	1206.9
7.5°	1022.6	1015.1	1007.6	981.3	1071.5	1071.5	1067.8	1067.8	1060.2	1030.2	1000.1
10°	782.0	778.3	770.7	782.0	800.8	864.7	924.9	921.1	909.9	838.4	767.0
12.5°	740.7	751.9	763.2	725.6	654.2	714.3	774.5	767.0	759.5	695.5	627.9
15°	627.9	635.4	642.9	703.1	812.1	868.5	921.1	913.6	906.1	830.9	751.9
17.5°	770.7	740.7	710.6	751.9	714.3	740.7	767.0	736.9	714.3	684.3	654.2
20°	740.7	661.7	582.8	703.1	842.2	887.3	932.4	921.1	898.6	827.1	751.9
22.5°	695.5	774.5	849.7	812.1	744.4	703.1	661.7	642.9	627.9	631.6	635.4
25°	883.5	782.0	676.7	857.2	966.2	981.3	992.6	958.7	921.1	842.2	759.5
27.5°	778.3	853.5	924.9	996.3	1033.9	1045.2	1052.7	1101.6	1022.6	917.4	812.1
30°	981.3	1045.2	1109.1	1267.0	1394.9	1417.4	1440.0	1383.6	1319.7	1191.8	1064.0
32.5°	1079.0	1225.7	1368.5	1443.7	1496.4	1515.2	1534.0	1458.8	1387.3	1221.9	1052.7
35°	1282.1	1391.1	1500.1	1586.6	1688.1	1691.9	1695.6	1612.9	1522.7	1282.1	1041.4
37.5°	1406.1	1549.0	1688.1	1785.9	1943.8	1932.5	1921.2	1823.5	1714.4	1376.1	1037.7
40°	1594.1	1778.3	1958.8	2052.8	2244.5	2210.7	2176.9	2064.1	1943.8	1477.6	1011.4
42.5°	1898.7	2094.2	2289.7	2368.6	2579.2	2541.6	2500.2	2349.8	2195.7	1560.3	924.9
45°	2304.7	2481.4	2658.1	2797.2	2962.7	2902.5	2842.3	2680.7	2455.1	1631.7	808.3
47.5°	2804.7	2936.3	3067.9	3342.4	3462.7	3342.4	3218.3	3022.8	2737.1	1691.9	646.7
50°	3470.2	3500.3	3526.6	3868.7	3989.1	3804.8	3620.6	3368.7	3026.6	1759.5	488.8
52.5°	4128.2	4071.8	4011.6	4380.1	4425.2	4180.8	3932.7	3669.5	3240.9	1797.1	349.7
55°	4748.5	4669.6	4586.8	4850.0	4819.9	4496.6	4173.3	3853.7	3372.5	1808.4	244.4
57.5°	5222.2	5173.4	5120.7	5241.0	5128.2	4748.5	4368.8	4049.2	3470.2	1827.2	180.5
60°	5395.2	5504.2	5613.2	5598.2	5391.4	4989.1	4586.8	4248.5	3530.4	1834.7	135.3
62.5°	5301.2	5654.6	6004.3	5861.4	5609.5	5184.6	4756.0	4428.9	3556.7	1831.0	105.3
65°	4959.1	5639.6	6316.3	6079.5	5763.6	5338.8	4913.9	4620.7	3586.8	1834.7	82.7
67.5°	4150.7	5278.6	6402.8	6252.4	5891.5	5440.3	4985.4	4748.5	3571.7	1819.7	67.7
70°	2598.0	4297.3	5996.7	6113.3	5891.5	5395.2	4898.9	4710.9	3436.4	1744.5	52.6
72.5°	1101.6	3034.1	4966.6	5474.1	5628.3	5147.0	4665.8	4432.7	3146.9	1594.1	41.4
75°	436.1	1744.5	3052.9	3857.5	4331.2	4128.2	3921.4	3609.3	2064.1	1049.0	30.1
77.5°	293.3	797.1	1300.9	1894.9	2259.6	2338.5	2417.5	2060.3	823.4	424.8	22.6
80°	195.5	319.6	443.6	680.5	812.1	767.0	718.1	590.3	251.9	135.3	18.8
82.5°	124.1	165.4	206.8	233.1	240.6	172.9	105.3	86.5	30.1	22.6	11.3
85°	82.7	97.8	112.8	116.6	116.6	82.7	45.1	22.6	11.3	11.3	7.5
87.5°	22.6	26.3	26.3	26.3	18.8	15.0	11.3	7.5	7.5	7.5	7.5
90°	11.3	15.0	15.0	15.0	11.3	11.3	7.5	7.5	7.5	7.5	7.5



REPORT NUMBER: P559902

CATALOG NUMBER: SDL-PA1-100-760-U-T2U-HSS

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2	1248.2
2.5°	1229.4	1229.4	1225.7	1221.9	1221.9	1218.1	1180.5	1139.2	1101.6	1060.2	1056.5
5°	1158.0	1105.4	1056.5	1007.6	1000.1	988.8	988.8	985.0	985.0	981.3	981.3
7.5°	992.6	985.0	977.5	970.0	966.2	958.7	955.0	947.4	943.7	936.2	894.8
10°	751.9	733.1	733.1	729.4	736.9	744.4	740.7	733.1	782.0	830.9	827.1
12.5°	669.2	706.8	673.0	635.4	646.7	654.2	665.5	676.7	673.0	665.5	609.1
15°	673.0	590.3	564.0	533.9	548.9	560.2	462.4	360.9	342.1	323.3	300.8
17.5°	627.9	601.6	582.8	560.2	428.6	293.3	263.2	233.1	206.8	176.7	172.9
20°	635.4	515.1	481.2	443.6	342.1	240.6	184.2	127.8	112.8	97.8	112.8
22.5°	620.4	601.6	439.9	278.2	206.8	135.3	112.8	86.5	94.0	101.5	101.5
25°	582.8	406.0	315.8	225.6	157.9	86.5	90.2	90.2	82.7	71.4	79.0
27.5°	631.6	447.4	285.7	120.3	105.3	86.5	79.0	67.7	67.7	67.7	63.9
30°	729.4	391.0	244.4	97.8	82.7	67.7	63.9	60.2	56.4	48.9	52.6
32.5°	691.8	330.9	206.8	82.7	71.4	60.2	52.6	45.1	45.1	45.1	45.1
35°	627.9	210.5	142.9	71.4	60.2	48.9	45.1	37.6	37.6	37.6	37.6
37.5°	586.5	135.3	97.8	56.4	48.9	41.4	37.6	30.1	30.1	30.1	33.8
40°	552.7	94.0	71.4	48.9	41.4	30.1	26.3	22.6	26.3	26.3	26.3
42.5°	503.8	79.0	60.2	41.4	33.8	26.3	22.6	18.8	22.6	22.6	22.6
45°	439.9	71.4	52.6	33.8	30.1	22.6	18.8	15.0	18.8	18.8	18.8
47.5°	353.4	60.2	45.1	30.1	26.3	18.8	18.8	15.0	15.0	15.0	15.0
50°	274.5	56.4	41.4	26.3	22.6	15.0	15.0	11.3	15.0	15.0	15.0
52.5°	199.3	48.9	37.6	22.6	18.8	11.3	11.3	11.3	11.3	11.3	11.3
55°	142.9	41.4	30.1	18.8	15.0	11.3	11.3	7.5	11.3	11.3	11.3
57.5°	109.0	37.6	26.3	15.0	11.3	7.5	7.5	7.5	7.5	7.5	7.5
60°	86.5	33.8	26.3	15.0	11.3	7.5	7.5	3.8	7.5	7.5	7.5
62.5°	67.7	26.3	22.6	15.0	11.3	7.5	7.5	3.8	7.5	7.5	7.5
65°	52.6	22.6	18.8	11.3	7.5	3.8	3.8	3.8	7.5	7.5	7.5
67.5°	45.1	18.8	15.0	11.3	7.5	3.8	7.5	7.5	7.5	7.5	7.5
70°	37.6	18.8	15.0	11.3	7.5	3.8	7.5	7.5	11.3	11.3	7.5
72.5°	30.1	15.0	11.3	7.5	7.5	3.8	7.5	7.5	11.3	11.3	7.5
75°	22.6	11.3	11.3	7.5	7.5	3.8	7.5	11.3	11.3	11.3	7.5
77.5°	18.8	11.3	11.3	7.5	7.5	3.8	7.5	11.3	11.3	11.3	11.3
80°	15.0	7.5	7.5	7.5	3.8	0.0	7.5	15.0	15.0	11.3	11.3
82.5°	11.3	7.5	7.5	7.5	3.8	0.0	7.5	15.0	15.0	11.3	11.3
85°	7.5	7.5	7.5	7.5	7.5	3.8	11.3	15.0	15.0	11.3	11.3
87.5°	7.5	7.5	7.5	7.5	7.5	3.8	7.5	11.3	11.3	11.3	11.3
90°	7.5	7.5	11.3	11.3	7.5	3.8	7.5	11.3	11.3	11.3	11.3

REPORT NUMBER: P559902

CATALOG NUMBER: SDL-PA1-100-760-U-T2U-HSS

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1248.2	1248.2	1248.2	1248.2
2.5°	1049.0	1056.5	1060.2	1052.7
5°	977.5	977.5	973.8	985.0
7.5°	849.7	827.1	800.8	782.0
10°	819.6	800.8	782.0	785.8
12.5°	548.9	492.5	436.1	454.9
15°	278.2	263.2	248.1	248.1
17.5°	165.4	150.4	131.6	135.3
20°	124.1	124.1	124.1	124.1
22.5°	97.8	94.0	86.5	82.7
25°	82.7	82.7	82.7	82.7
27.5°	60.2	60.2	56.4	52.6
30°	52.6	52.6	52.6	48.9
32.5°	41.4	45.1	45.1	45.1
35°	37.6	37.6	37.6	37.6
37.5°	33.8	33.8	30.1	30.1
40°	26.3	26.3	26.3	26.3
42.5°	22.6	22.6	22.6	22.6
45°	18.8	18.8	18.8	18.8
47.5°	15.0	15.0	15.0	15.0
50°	15.0	15.0	11.3	11.3
52.5°	11.3	11.3	7.5	7.5
55°	7.5	7.5	7.5	7.5
57.5°	7.5	7.5	3.8	3.8
60°	7.5	7.5	3.8	3.8
62.5°	3.8	3.8	3.8	3.8
65°	3.8	3.8	0.0	0.0
67.5°	3.8	3.8	0.0	0.0
70°	3.8	3.8	0.0	0.0
72.5°	3.8	3.8	0.0	0.0
75°	3.8	3.8	0.0	0.0
77.5°	7.5	3.8	0.0	0.0
80°	7.5	7.5	3.8	0.0
82.5°	7.5	7.5	3.8	0.0
85°	7.5	7.5	3.8	0.0
87.5°	7.5	7.5	3.8	0.0
90°	7.5	7.5	3.8	0.0



Report Generated By 670245982



--- HS --- SS



u



(END OF REPORT)