

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560602

Luminaire Tested: **SDL-PA1-50-760-U-T2R-HSS**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560602  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-50-760-U-T2R-HSS  
Description: Springdale  
(1) 70 CRI, 5700K, 670mA LIGHT ENGINE WITH 24 LEDS AND TYPE II R OPTICS  
WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5239.1 lumens  
Efficiency: N/A  
Efficacy: 100.0 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type II - Medium  
BUG Rating: B0 - U0 - G1

Input Watts (W): 52.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 14.3 fc  
 Type II - Medium - N/A

REPORT NUMBER: P560602  
CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

## Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral      - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 276.8    | 0.0    | 276.8  |
|                    | % Fixture | 5.3      | 0.0    | 5.3    |
| <b>Street Side</b> | Lumens    | 4962.4   | 0.0    | 4962.4 |
|                    | % Fixture | 94.7     | 0.0    | 94.7   |
| <b>Total</b>       | Lumens    | 5239.1   | 0.0    | 5239.1 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 60.7   | 1.2       |
| 10°-20°   | 151.2  | 2.9       |
| 20°-30°   | 287.4  | 5.5       |
| 30°-40°   | 638.6  | 12.2      |
| 40°-50°   | 1029.5 | 19.7      |
| 50°-60°   | 1240.8 | 23.7      |
| 60°-70°   | 1124.6 | 21.5      |
| 70°-80°   | 670.2  | 12.8      |
| 80°-90°   | 36.1   | 0.7       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5239.1 | 100.0     |
| 0°-180°   | 5239.1 | 100.0     |



REPORT NUMBER: P560602


CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 429.7  | 8.2       |                         |      |         |
| FM   | (30°-60°)   | 2779.4 | 53.1      |                         |      |         |
| FH   | (60°-80°)   | 1720.3 | 32.8      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 33.0   | 0.6       |                         |      | G1/100  |
| BL   | (0°-30°)    | 69.6   | 1.3       | B0/110                  |      |         |
| BM   | (30°-60°)   | 129.5  | 2.5       | B0/220                  |      |         |
| BH   | (60°-80°)   | 74.6   | 1.4       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 3.1    | 0.1       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G1**

Type II Medium



REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  |
| 2.5°  | 853.1  | 871.9  | 890.6  | 897.6  | 907.0  | 914.1  | 921.1  | 928.1  | 935.1  | 939.8  | 946.9  |
| 5°    | 970.3  | 968.0  | 965.6  | 963.3  | 963.3  | 960.9  | 958.6  | 956.2  | 953.9  | 949.2  | 946.9  |
| 7.5°  | 850.8  | 911.7  | 970.3  | 972.6  | 975.0  | 975.0  | 977.3  | 991.4  | 1005.5 | 1017.2 | 1031.2 |
| 10°   | 1106.2 | 1106.2 | 1106.2 | 1106.2 | 1106.2 | 1103.9 | 1103.9 | 1106.2 | 1106.2 | 1108.6 | 1108.6 |
| 12.5° | 930.5  | 944.5  | 956.2  | 998.4  | 1038.3 | 1080.5 | 1120.3 | 1129.7 | 1139.1 | 1146.1 | 1155.5 |
| 15°   | 1125.0 | 1129.7 | 1134.4 | 1136.7 | 1139.1 | 1139.1 | 1141.4 | 1106.2 | 1071.1 | 1035.9 | 1000.8 |
| 17.5° | 890.6  | 895.3  | 897.6  | 928.1  | 958.6  | 989.1  | 1019.5 | 1035.9 | 1054.7 | 1071.1 | 1087.5 |
| 20°   | 1141.4 | 1143.7 | 1146.1 | 1148.4 | 1150.8 | 1150.8 | 1153.1 | 1078.1 | 1003.1 | 928.1  | 853.1  |
| 22.5° | 953.9  | 956.2  | 956.2  | 963.3  | 968.0  | 975.0  | 979.7  | 1007.8 | 1035.9 | 1064.1 | 1092.2 |
| 25°   | 1310.1 | 1310.1 | 1307.8 | 1296.1 | 1286.7 | 1275.0 | 1263.3 | 1193.0 | 1122.6 | 1050.0 | 979.7  |
| 27.5° | 1218.7 | 1221.1 | 1221.1 | 1211.7 | 1202.3 | 1193.0 | 1183.6 | 1197.6 | 1214.1 | 1228.1 | 1242.2 |
| 30°   | 1757.8 | 1757.8 | 1757.8 | 1746.1 | 1732.0 | 1720.3 | 1706.2 | 1603.1 | 1500.0 | 1394.5 | 1291.4 |
| 32.5° | 2362.5 | 2320.3 | 2275.8 | 2191.4 | 2107.0 | 2020.3 | 1935.9 | 1872.6 | 1809.4 | 1743.7 | 1680.5 |
| 35°   | 2632.0 | 2625.0 | 2617.9 | 2587.5 | 2557.0 | 2524.2 | 2493.7 | 2371.9 | 2250.0 | 2125.8 | 2003.9 |
| 37.5° | 2859.4 | 2850.0 | 2838.3 | 2814.8 | 2791.4 | 2767.9 | 2744.5 | 2620.3 | 2493.7 | 2369.5 | 2243.0 |
| 40°   | 3042.2 | 3035.1 | 3028.1 | 3009.4 | 2990.6 | 2971.9 | 2953.1 | 2819.5 | 2685.9 | 2552.3 | 2418.7 |
| 42.5° | 3173.4 | 3173.4 | 3171.1 | 3157.0 | 3140.6 | 3126.5 | 3110.1 | 2976.5 | 2842.9 | 2709.4 | 2575.8 |
| 45°   | 3271.8 | 3271.8 | 3271.8 | 3262.5 | 3250.8 | 3241.4 | 3229.7 | 3112.5 | 2997.6 | 2880.4 | 2763.3 |
| 47.5° | 3285.9 | 3288.3 | 3290.6 | 3290.6 | 3290.6 | 3290.6 | 3290.6 | 3180.4 | 3072.6 | 2962.5 | 2852.3 |
| 50°   | 3157.0 | 3164.0 | 3171.1 | 3182.8 | 3196.8 | 3208.6 | 3220.3 | 3166.4 | 3110.1 | 3056.2 | 3000.0 |
| 52.5° | 2812.5 | 2842.9 | 2871.1 | 2901.5 | 2932.0 | 2960.1 | 2990.6 | 2969.5 | 2948.4 | 2927.3 | 2906.2 |
| 55°   | 2139.8 | 2158.6 | 2175.0 | 2261.7 | 2348.4 | 2435.1 | 2521.9 | 2559.4 | 2594.5 | 2632.0 | 2667.2 |
| 57.5° | 1661.7 | 1668.7 | 1673.4 | 1729.7 | 1785.9 | 1839.8 | 1896.1 | 1989.8 | 2083.6 | 2175.0 | 2268.7 |
| 60°   | 1335.9 | 1335.9 | 1335.9 | 1368.7 | 1399.2 | 1432.0 | 1462.5 | 1546.9 | 1631.2 | 1715.6 | 1800.0 |
| 62.5° | 993.7  | 1003.1 | 1012.5 | 1045.3 | 1075.8 | 1108.6 | 1139.1 | 1181.2 | 1223.4 | 1265.6 | 1307.8 |
| 65°   | 689.1  | 700.8  | 710.2  | 731.2  | 754.7  | 775.8  | 796.9  | 832.0  | 869.5  | 904.7  | 939.8  |
| 67.5° | 485.2  | 489.8  | 494.5  | 506.2  | 515.6  | 527.3  | 536.7  | 560.2  | 581.2  | 604.7  | 625.8  |
| 70°   | 344.5  | 346.9  | 346.9  | 356.2  | 365.6  | 375.0  | 384.4  | 393.7  | 403.1  | 410.2  | 419.5  |
| 72.5° | 250.8  | 253.1  | 255.5  | 262.5  | 267.2  | 274.2  | 278.9  | 283.6  | 288.3  | 293.0  | 297.7  |
| 75°   | 128.9  | 133.6  | 135.9  | 154.7  | 173.4  | 192.2  | 210.9  | 213.3  | 215.6  | 215.6  | 218.0  |
| 77.5° | 107.8  | 110.2  | 110.2  | 112.5  | 114.8  | 117.2  | 119.5  | 131.2  | 145.3  | 157.0  | 168.7  |
| 80°   | 77.3   | 77.3   | 75.0   | 79.7   | 84.4   | 89.1   | 93.7   | 98.4   | 103.1  | 105.5  | 110.2  |
| 82.5° | 44.5   | 46.9   | 46.9   | 49.2   | 51.6   | 53.9   | 56.2   | 60.9   | 68.0   | 72.7   | 77.3   |
| 85°   | 4.7    | 7.0    | 9.4    | 14.1   | 18.7   | 23.4   | 28.1   | 35.2   | 39.8   | 46.9   | 51.6   |
| 87.5° | 2.3    | 2.3    | 2.3    | 2.3    | 4.7    | 4.7    | 4.7    | 7.0    | 7.0    | 9.4    | 9.4    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  |
| 2.5°  | 951.6  | 956.2  | 958.6  | 963.3  | 960.9  | 956.2  | 953.9  | 949.2  | 942.2  | 935.1  | 925.8  |
| 5°    | 942.2  | 937.5  | 932.8  | 928.1  | 921.1  | 916.4  | 909.4  | 902.3  | 893.0  | 885.9  | 876.6  |
| 7.5°  | 1031.2 | 1028.9 | 1028.9 | 1026.6 | 1019.5 | 1014.8 | 1007.8 | 1000.8 | 989.1  | 977.3  | 965.6  |
| 10°   | 1057.0 | 1005.5 | 951.6  | 900.0  | 911.7  | 923.4  | 935.1  | 946.9  | 911.7  | 876.6  | 839.1  |
| 12.5° | 1132.0 | 1108.6 | 1085.1 | 1061.7 | 1024.2 | 984.4  | 946.9  | 907.0  | 888.3  | 867.2  | 848.4  |
| 15°   | 975.0  | 951.6  | 925.8  | 900.0  | 916.4  | 932.8  | 949.2  | 965.6  | 911.7  | 855.5  | 801.6  |
| 17.5° | 1066.4 | 1043.0 | 1021.9 | 998.4  | 932.8  | 867.2  | 799.2  | 733.6  | 789.8  | 843.7  | 900.0  |
| 20°   | 871.9  | 890.6  | 907.0  | 925.8  | 949.2  | 972.6  | 993.7  | 1017.2 | 989.1  | 960.9  | 932.8  |
| 22.5° | 1054.7 | 1019.5 | 982.0  | 944.5  | 960.9  | 977.3  | 991.4  | 1007.8 | 975.0  | 942.2  | 907.0  |
| 25°   | 1017.2 | 1057.0 | 1094.5 | 1132.0 | 1073.4 | 1017.2 | 958.6  | 900.0  | 951.6  | 1003.1 | 1054.7 |
| 27.5° | 1188.3 | 1134.4 | 1078.1 | 1024.2 | 1073.4 | 1122.6 | 1169.5 | 1218.7 | 1174.2 | 1127.3 | 1082.8 |
| 30°   | 1284.4 | 1277.3 | 1268.0 | 1260.9 | 1235.1 | 1211.7 | 1185.9 | 1160.1 | 1174.2 | 1188.3 | 1202.3 |
| 32.5° | 1600.8 | 1523.4 | 1443.7 | 1364.1 | 1382.8 | 1401.6 | 1418.0 | 1436.7 | 1415.6 | 1394.5 | 1371.1 |
| 35°   | 1900.8 | 1797.6 | 1692.2 | 1589.0 | 1586.7 | 1582.0 | 1579.7 | 1575.0 | 1565.6 | 1556.2 | 1546.9 |
| 37.5° | 2125.8 | 2008.6 | 1891.4 | 1774.2 | 1776.5 | 1776.5 | 1778.9 | 1778.9 | 1746.1 | 1713.3 | 1680.5 |
| 40°   | 2310.9 | 2203.1 | 2095.3 | 1987.5 | 1978.1 | 1968.7 | 1959.4 | 1950.0 | 1905.5 | 1858.6 | 1814.0 |
| 42.5° | 2467.9 | 2362.5 | 2254.7 | 2146.9 | 2130.5 | 2116.4 | 2100.0 | 2083.6 | 2046.1 | 2006.2 | 1968.7 |
| 45°   | 2639.0 | 2514.8 | 2390.6 | 2266.4 | 2252.3 | 2238.3 | 2224.2 | 2210.1 | 2179.7 | 2149.2 | 2118.7 |
| 47.5° | 2728.1 | 2603.9 | 2477.3 | 2353.1 | 2343.7 | 2332.0 | 2322.6 | 2310.9 | 2294.5 | 2275.8 | 2259.4 |
| 50°   | 2854.7 | 2711.7 | 2566.4 | 2421.1 | 2416.4 | 2411.7 | 2404.7 | 2400.0 | 2395.3 | 2392.9 | 2388.3 |
| 52.5° | 2796.1 | 2683.6 | 2573.4 | 2460.9 | 2463.3 | 2463.3 | 2465.6 | 2465.6 | 2477.3 | 2489.0 | 2500.8 |
| 55°   | 2608.6 | 2552.3 | 2493.7 | 2435.1 | 2446.9 | 2460.9 | 2472.6 | 2484.4 | 2514.8 | 2542.9 | 2573.4 |
| 57.5° | 2278.1 | 2287.5 | 2296.9 | 2306.2 | 2348.4 | 2388.3 | 2430.4 | 2470.3 | 2514.8 | 2557.0 | 2601.5 |
| 60°   | 1851.5 | 1903.1 | 1952.3 | 2003.9 | 2102.3 | 2200.8 | 2299.2 | 2397.6 | 2465.6 | 2531.2 | 2599.2 |
| 62.5° | 1380.5 | 1453.1 | 1525.8 | 1598.4 | 1750.8 | 1905.5 | 2057.8 | 2210.1 | 2313.3 | 2414.0 | 2517.2 |
| 65°   | 1007.8 | 1075.8 | 1141.4 | 1209.4 | 1392.2 | 1575.0 | 1757.8 | 1940.6 | 2088.3 | 2233.6 | 2381.2 |
| 67.5° | 675.0  | 724.2  | 771.1  | 820.3  | 1005.5 | 1190.6 | 1375.8 | 1560.9 | 1764.8 | 1968.7 | 2170.3 |
| 70°   | 445.3  | 468.7  | 494.5  | 518.0  | 677.3  | 834.4  | 993.7  | 1150.8 | 1392.2 | 1631.2 | 1872.6 |
| 72.5° | 304.7  | 311.7  | 318.7  | 325.8  | 433.6  | 541.4  | 649.2  | 757.0  | 1000.8 | 1244.5 | 1485.9 |
| 75°   | 218.0  | 215.6  | 215.6  | 213.3  | 276.6  | 339.8  | 400.8  | 464.1  | 653.9  | 841.4  | 1031.2 |
| 77.5° | 166.4  | 161.7  | 159.4  | 154.7  | 185.2  | 215.6  | 246.1  | 276.6  | 365.6  | 457.0  | 546.1  |
| 80°   | 105.5  | 100.8  | 93.7   | 89.1   | 100.8  | 112.5  | 124.2  | 135.9  | 150.0  | 164.1  | 178.1  |
| 82.5° | 77.3   | 77.3   | 77.3   | 77.3   | 77.3   | 79.7   | 79.7   | 79.7   | 75.0   | 70.3   | 63.3   |
| 85°   | 49.2   | 46.9   | 44.5   | 42.2   | 37.5   | 32.8   | 28.1   | 23.4   | 25.8   | 28.1   | 28.1   |
| 87.5° | 9.4    | 7.0    | 7.0    | 4.7    | 4.7    | 4.7    | 4.7    | 4.7    | 7.0    | 7.0    | 9.4    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  |
| 2.5°  | 918.7  | 909.4  | 900.0  | 890.6  | 881.2  | 871.9  | 862.5  | 853.1  | 843.7  | 829.7  | 818.0  |
| 5°    | 867.2  | 893.0  | 921.1  | 946.9  | 972.6  | 958.6  | 944.5  | 930.5  | 916.4  | 893.0  | 869.5  |
| 7.5°  | 953.9  | 923.4  | 895.3  | 867.2  | 836.7  | 843.7  | 850.8  | 857.8  | 864.8  | 843.7  | 815.6  |
| 10°   | 803.9  | 787.5  | 771.1  | 754.7  | 738.3  | 728.9  | 717.2  | 707.8  | 696.1  | 754.7  | 731.2  |
| 12.5° | 827.3  | 820.3  | 813.3  | 803.9  | 796.9  | 750.0  | 705.5  | 658.6  | 611.7  | 593.0  | 600.0  |
| 15°   | 745.3  | 738.3  | 731.2  | 724.2  | 717.2  | 740.6  | 766.4  | 789.8  | 813.3  | 808.6  | 803.9  |
| 17.5° | 953.9  | 923.4  | 895.3  | 864.8  | 834.4  | 820.3  | 803.9  | 789.8  | 773.4  | 747.7  | 740.6  |
| 20°   | 904.7  | 871.9  | 839.1  | 806.2  | 773.4  | 806.2  | 836.7  | 869.5  | 900.0  | 953.9  | 937.5  |
| 22.5° | 874.2  | 928.1  | 984.4  | 1038.3 | 1092.2 | 1040.6 | 991.4  | 939.8  | 888.3  | 904.7  | 825.0  |
| 25°   | 1106.2 | 1066.4 | 1028.9 | 989.1  | 949.2  | 1000.8 | 1052.3 | 1103.9 | 1155.5 | 1132.0 | 1094.5 |
| 27.5° | 1035.9 | 1075.8 | 1113.3 | 1153.1 | 1190.6 | 1209.4 | 1230.5 | 1249.2 | 1268.0 | 1221.1 | 1230.5 |
| 30°   | 1216.4 | 1265.6 | 1312.5 | 1361.7 | 1408.6 | 1495.3 | 1579.7 | 1666.4 | 1750.8 | 1732.0 | 1657.0 |
| 32.5° | 1350.0 | 1432.0 | 1514.1 | 1593.7 | 1675.8 | 1725.0 | 1776.5 | 1825.8 | 1875.0 | 1879.7 | 1785.9 |
| 35°   | 1537.5 | 1593.7 | 1650.0 | 1706.2 | 1762.5 | 1837.5 | 1910.1 | 1985.1 | 2057.8 | 2015.6 | 1910.1 |
| 37.5° | 1647.6 | 1706.2 | 1767.2 | 1825.8 | 1884.4 | 1975.8 | 2067.2 | 2156.2 | 2247.6 | 2156.2 | 2041.4 |
| 40°   | 1767.2 | 1830.5 | 1896.1 | 1959.4 | 2022.6 | 2116.4 | 2207.8 | 2301.5 | 2392.9 | 2388.3 | 2231.2 |
| 42.5° | 1928.9 | 1992.2 | 2057.8 | 2121.1 | 2184.4 | 2282.8 | 2381.2 | 2477.3 | 2575.8 | 2573.4 | 2395.3 |
| 45°   | 2088.3 | 2146.9 | 2203.1 | 2261.7 | 2317.9 | 2430.4 | 2542.9 | 2655.4 | 2767.9 | 2779.7 | 2578.1 |
| 47.5° | 2240.6 | 2292.2 | 2343.7 | 2395.3 | 2446.9 | 2601.5 | 2753.9 | 2908.6 | 3060.9 | 2988.3 | 2770.3 |
| 50°   | 2383.6 | 2435.1 | 2486.7 | 2538.3 | 2589.8 | 2770.3 | 2953.1 | 3133.6 | 3314.0 | 3217.9 | 2983.6 |
| 52.5° | 2512.5 | 2575.8 | 2641.4 | 2704.7 | 2767.9 | 2964.8 | 3161.7 | 3358.6 | 3555.4 | 3457.0 | 3215.6 |
| 55°   | 2601.5 | 2690.6 | 2777.3 | 2866.4 | 2953.1 | 3171.1 | 3391.4 | 3609.3 | 3827.3 | 3714.8 | 3435.9 |
| 57.5° | 2643.7 | 2749.2 | 2857.0 | 2962.5 | 3067.9 | 3292.9 | 3520.3 | 3745.3 | 3970.3 | 3857.8 | 3571.8 |
| 60°   | 2664.8 | 2786.7 | 2908.6 | 3028.1 | 3150.0 | 3393.7 | 3639.8 | 3883.6 | 4127.3 | 4031.2 | 3740.6 |
| 62.5° | 2617.9 | 2772.6 | 2929.7 | 3084.3 | 3239.0 | 3499.2 | 3759.3 | 4017.2 | 4277.3 | 4214.0 | 3937.5 |
| 65°   | 2526.5 | 2730.4 | 2936.7 | 3140.6 | 3344.5 | 3653.9 | 3963.2 | 4270.3 | 4579.6 | 4511.7 | 4235.1 |
| 67.5° | 2374.2 | 2641.4 | 2908.6 | 3175.8 | 3442.9 | 3827.3 | 4209.3 | 4593.7 | 4975.7 | 4907.8 | 4591.4 |
| 70°   | 2111.7 | 2446.9 | 2782.0 | 3114.8 | 3450.0 | 3900.0 | 4352.3 | 4802.3 | 5252.3 | 5163.2 | 4788.2 |
| 72.5° | 1729.7 | 2107.0 | 2484.4 | 2859.4 | 3236.7 | 3717.2 | 4200.0 | 4680.4 | 5160.9 | 4992.1 | 4565.6 |
| 75°   | 1218.7 | 1563.3 | 1907.8 | 2250.0 | 2594.5 | 3016.4 | 3438.3 | 3857.8 | 4279.7 | 4064.0 | 3646.8 |
| 77.5° | 635.2  | 848.4  | 1059.4 | 1272.6 | 1483.6 | 1814.0 | 2142.2 | 2472.6 | 2800.8 | 2414.0 | 2100.0 |
| 80°   | 192.2  | 281.2  | 368.0  | 457.0  | 543.7  | 621.1  | 698.4  | 773.4  | 850.8  | 632.8  | 525.0  |
| 82.5° | 58.6   | 77.3   | 93.7   | 112.5  | 128.9  | 128.9  | 128.9  | 126.6  | 126.6  | 100.8  | 84.4   |
| 85°   | 30.5   | 32.8   | 32.8   | 35.2   | 35.2   | 35.2   | 32.8   | 32.8   | 30.5   | 30.5   | 25.8   |
| 87.5° | 9.4    | 9.4    | 11.7   | 11.7   | 11.7   | 11.7   | 11.7   | 9.4    | 9.4    | 9.4    | 9.4    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°   | 97.5° | 100°  | 102.5° | 105°  | 107.5° |
|-------|--------|--------|--------|--------|--------|-------|-------|-------|--------|-------|--------|
| 0°    | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7 | 768.7 | 768.7 | 768.7  | 768.7 | 768.7  |
| 2.5°  | 808.6  | 796.9  | 785.1  | 771.1  | 757.0  | 743.0 | 728.9 | 714.8 | 700.8  | 686.7 | 675.0  |
| 5°    | 848.4  | 825.0  | 801.6  | 775.8  | 747.7  | 719.5 | 693.7 | 668.0 | 639.8  | 614.1 | 590.6  |
| 7.5°  | 787.5  | 759.4  | 724.2  | 689.1  | 653.9  | 618.7 | 581.2 | 546.1 | 508.6  | 471.1 | 440.6  |
| 10°   | 705.5  | 682.0  | 644.5  | 604.7  | 562.5  | 518.0 | 468.7 | 419.5 | 370.3  | 321.1 | 300.0  |
| 12.5° | 604.7  | 611.7  | 571.9  | 532.0  | 487.5  | 443.0 | 396.1 | 349.2 | 300.0  | 253.1 | 239.1  |
| 15°   | 799.2  | 794.5  | 743.0  | 691.4  | 623.4  | 555.5 | 487.5 | 417.2 | 349.2  | 278.9 | 243.7  |
| 17.5° | 731.2  | 724.2  | 668.0  | 611.7  | 550.8  | 489.8 | 426.6 | 360.9 | 297.7  | 232.0 | 199.2  |
| 20°   | 923.4  | 907.0  | 836.7  | 764.1  | 675.0  | 583.6 | 494.5 | 405.5 | 316.4  | 227.3 | 189.8  |
| 22.5° | 745.3  | 665.6  | 609.4  | 553.1  | 482.8  | 410.2 | 351.6 | 290.6 | 232.0  | 171.1 | 147.7  |
| 25°   | 1054.7 | 1017.2 | 921.1  | 822.6  | 698.4  | 574.2 | 473.4 | 372.7 | 271.9  | 171.1 | 143.0  |
| 27.5° | 1239.8 | 1249.2 | 1118.0 | 986.7  | 829.7  | 672.7 | 541.4 | 410.2 | 278.9  | 147.7 | 126.6  |
| 30°   | 1582.0 | 1507.0 | 1352.3 | 1195.3 | 975.0  | 752.3 | 597.7 | 443.0 | 288.3  | 133.6 | 114.8  |
| 32.5° | 1694.5 | 1600.8 | 1425.0 | 1246.9 | 989.1  | 728.9 | 574.2 | 419.5 | 262.5  | 107.8 | 96.1   |
| 35°   | 1807.0 | 1701.5 | 1500.0 | 1298.4 | 1003.1 | 705.5 | 550.8 | 398.4 | 243.7  | 89.1  | 82.0   |
| 37.5° | 1926.5 | 1811.7 | 1586.7 | 1359.4 | 1017.2 | 675.0 | 527.3 | 377.3 | 229.7  | 79.7  | 72.7   |
| 40°   | 2076.5 | 1919.5 | 1671.1 | 1420.3 | 1031.2 | 642.2 | 499.2 | 358.6 | 215.6  | 72.7  | 65.6   |
| 42.5° | 2219.5 | 2041.4 | 1764.8 | 1485.9 | 1047.6 | 609.4 | 473.4 | 339.8 | 203.9  | 68.0  | 60.9   |
| 45°   | 2378.9 | 2177.3 | 1877.3 | 1575.0 | 1071.1 | 567.2 | 440.6 | 314.1 | 187.5  | 60.9  | 53.9   |
| 47.5° | 2552.3 | 2334.4 | 1999.2 | 1664.0 | 1094.5 | 525.0 | 407.8 | 293.0 | 175.8  | 58.6  | 51.6   |
| 50°   | 2749.2 | 2514.8 | 2146.9 | 1776.5 | 1141.4 | 503.9 | 391.4 | 278.9 | 166.4  | 53.9  | 46.9   |
| 52.5° | 2976.5 | 2735.1 | 2322.6 | 1907.8 | 1197.6 | 485.2 | 377.3 | 267.2 | 159.4  | 49.2  | 42.2   |
| 55°   | 3159.3 | 2880.4 | 2423.4 | 1964.0 | 1209.4 | 452.3 | 351.6 | 248.4 | 147.7  | 44.5  | 39.8   |
| 57.5° | 3288.3 | 3002.3 | 2519.5 | 2036.7 | 1230.5 | 421.9 | 325.8 | 232.0 | 135.9  | 39.8  | 35.2   |
| 60°   | 3447.6 | 3157.0 | 2639.0 | 2118.7 | 1256.2 | 393.7 | 304.7 | 215.6 | 124.2  | 35.2  | 30.5   |
| 62.5° | 3660.9 | 3384.3 | 2810.1 | 2233.6 | 1298.4 | 360.9 | 278.9 | 196.9 | 112.5  | 30.5  | 28.1   |
| 65°   | 3956.2 | 3679.7 | 3011.7 | 2343.7 | 1338.3 | 330.5 | 255.5 | 180.5 | 103.1  | 28.1  | 25.8   |
| 67.5° | 4272.6 | 3956.2 | 3171.1 | 2383.6 | 1338.3 | 293.0 | 227.3 | 159.4 | 93.7   | 25.8  | 23.4   |
| 70°   | 4413.2 | 4038.2 | 3145.3 | 2250.0 | 1242.2 | 234.4 | 182.8 | 128.9 | 77.3   | 23.4  | 21.1   |
| 72.5° | 4141.4 | 3714.8 | 2796.1 | 1877.3 | 1012.5 | 147.7 | 114.8 | 84.4  | 51.6   | 18.7  | 16.4   |
| 75°   | 3227.3 | 2810.1 | 2085.9 | 1359.4 | 717.2  | 72.7  | 58.6  | 44.5  | 28.1   | 14.1  | 11.7   |
| 77.5° | 1788.3 | 1474.2 | 1071.1 | 668.0  | 356.2  | 42.2  | 35.2  | 28.1  | 18.7   | 11.7  | 11.7   |
| 80°   | 419.5  | 311.7  | 227.3  | 140.6  | 84.4   | 25.8  | 21.1  | 18.7  | 14.1   | 9.4   | 9.4    |
| 82.5° | 68.0   | 51.6   | 37.5   | 23.4   | 18.7   | 14.1  | 11.7  | 11.7  | 9.4    | 7.0   | 7.0    |
| 85°   | 21.1   | 16.4   | 14.1   | 9.4    | 9.4    | 7.0   | 7.0   | 7.0   | 4.7    | 4.7   | 4.7    |
| 87.5° | 7.0    | 7.0    | 7.0    | 4.7    | 4.7    | 4.7   | 4.7   | 4.7   | 4.7    | 4.7   | 4.7    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° | 135°  |
|-------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°    | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 |
| 2.5°  | 660.9 | 649.2  | 635.2 | 625.8  | 616.4 | 604.7  | 595.3 | 585.9  | 576.6 | 567.2  | 557.8 |
| 5°    | 567.2 | 541.4  | 518.0 | 487.5  | 454.7 | 424.2  | 391.4 | 377.3  | 365.6 | 351.6  | 337.5 |
| 7.5°  | 410.2 | 379.7  | 349.2 | 337.5  | 325.8 | 311.7  | 300.0 | 288.3  | 276.6 | 264.8  | 253.1 |
| 10°   | 281.2 | 260.2  | 239.1 | 229.7  | 220.3 | 208.6  | 199.2 | 189.8  | 180.5 | 168.7  | 159.4 |
| 12.5° | 225.0 | 208.6  | 194.5 | 178.1  | 161.7 | 145.3  | 128.9 | 124.2  | 119.5 | 112.5  | 107.8 |
| 15°   | 206.2 | 171.1  | 133.6 | 121.9  | 112.5 | 100.8  | 89.1  | 86.7   | 86.7  | 84.4   | 82.0  |
| 17.5° | 166.4 | 133.6  | 100.8 | 96.1   | 89.1  | 84.4   | 77.3  | 72.7   | 68.0  | 63.3   | 58.6  |
| 20°   | 152.3 | 114.8  | 77.3  | 75.0   | 72.7  | 68.0   | 65.6  | 63.3   | 63.3  | 60.9   | 58.6  |
| 22.5° | 126.6 | 103.1  | 79.7  | 72.7   | 65.6  | 58.6   | 51.6  | 51.6   | 53.9  | 53.9   | 53.9  |
| 25°   | 114.8 | 86.7   | 58.6  | 58.6   | 56.2  | 56.2   | 53.9  | 51.6   | 46.9  | 44.5   | 39.8  |
| 27.5° | 105.5 | 84.4   | 63.3  | 58.6   | 53.9  | 49.2   | 44.5  | 44.5   | 42.2  | 42.2   | 39.8  |
| 30°   | 98.4  | 79.7   | 60.9  | 56.2   | 53.9  | 49.2   | 44.5  | 42.2   | 39.8  | 35.2   | 32.8  |
| 32.5° | 86.7  | 75.0   | 63.3  | 58.6   | 51.6  | 46.9   | 39.8  | 37.5   | 35.2  | 30.5   | 28.1  |
| 35°   | 75.0  | 65.6   | 58.6  | 53.9   | 46.9  | 42.2   | 35.2  | 32.8   | 30.5  | 28.1   | 25.8  |
| 37.5° | 65.6  | 58.6   | 51.6  | 46.9   | 42.2  | 35.2   | 30.5  | 28.1   | 25.8  | 23.4   | 21.1  |
| 40°   | 58.6  | 51.6   | 44.5  | 39.8   | 35.2  | 30.5   | 25.8  | 23.4   | 23.4  | 21.1   | 18.7  |
| 42.5° | 53.9  | 46.9   | 39.8  | 35.2   | 32.8  | 28.1   | 23.4  | 21.1   | 18.7  | 16.4   | 14.1  |
| 45°   | 49.2  | 42.2   | 35.2  | 32.8   | 28.1  | 25.8   | 21.1  | 18.7   | 16.4  | 14.1   | 11.7  |
| 47.5° | 44.5  | 37.5   | 30.5  | 28.1   | 25.8  | 21.1   | 18.7  | 16.4   | 14.1  | 11.7   | 9.4   |
| 50°   | 42.2  | 35.2   | 28.1  | 25.8   | 23.4  | 18.7   | 16.4  | 14.1   | 14.1  | 11.7   | 9.4   |
| 52.5° | 37.5  | 30.5   | 23.4  | 21.1   | 18.7  | 16.4   | 14.1  | 11.7   | 11.7  | 9.4    | 7.0   |
| 55°   | 32.8  | 28.1   | 21.1  | 18.7   | 16.4  | 14.1   | 11.7  | 9.4    | 9.4   | 7.0    | 4.7   |
| 57.5° | 30.5  | 23.4   | 18.7  | 16.4   | 14.1  | 11.7   | 9.4   | 9.4    | 7.0   | 7.0    | 4.7   |
| 60°   | 25.8  | 21.1   | 16.4  | 14.1   | 11.7  | 9.4    | 7.0   | 7.0    | 4.7   | 4.7    | 2.3   |
| 62.5° | 23.4  | 21.1   | 16.4  | 14.1   | 11.7  | 9.4    | 7.0   | 7.0    | 4.7   | 4.7    | 2.3   |
| 65°   | 21.1  | 18.7   | 14.1  | 11.7   | 11.7  | 9.4    | 7.0   | 7.0    | 4.7   | 4.7    | 2.3   |
| 67.5° | 21.1  | 16.4   | 14.1  | 11.7   | 9.4   | 7.0    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   |
| 70°   | 16.4  | 14.1   | 9.4   | 9.4    | 7.0   | 7.0    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   |
| 72.5° | 14.1  | 11.7   | 9.4   | 9.4    | 7.0   | 7.0    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   |
| 75°   | 11.7  | 9.4    | 7.0   | 7.0    | 7.0   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   |
| 77.5° | 9.4   | 9.4    | 7.0   | 7.0    | 7.0   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   |
| 80°   | 7.0   | 7.0    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   |
| 82.5° | 7.0   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   |
| 85°   | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   |
| 87.5° | 4.7   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 4.7   | 4.7    | 2.3   |
| 90°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  | 162.5° |
|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°    | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  |
| 2.5°  | 548.4  | 536.7 | 527.3  | 515.6 | 499.2  | 480.5 | 464.1  | 445.3 | 443.0  | 440.6 | 435.9  |
| 5°    | 330.5  | 323.4 | 316.4  | 309.4 | 304.7  | 300.0 | 295.3  | 290.6 | 285.9  | 283.6 | 278.9  |
| 7.5°  | 243.7  | 234.4 | 225.0  | 215.6 | 208.6  | 203.9 | 196.9  | 189.8 | 185.2  | 178.1 | 173.4  |
| 10°   | 150.0  | 138.3 | 128.9  | 117.2 | 121.9  | 126.6 | 128.9  | 133.6 | 133.6  | 131.2 | 131.2  |
| 12.5° | 107.8  | 107.8 | 107.8  | 107.8 | 107.8  | 107.8 | 105.5  | 105.5 | 105.5  | 103.1 | 103.1  |
| 15°   | 79.7   | 77.3  | 75.0   | 72.7  | 72.7   | 72.7  | 70.3   | 70.3  | 75.0   | 77.3  | 82.0   |
| 17.5° | 60.9   | 63.3  | 63.3   | 65.6  | 68.0   | 70.3  | 70.3   | 72.7  | 72.7   | 75.0  | 75.0   |
| 20°   | 58.6   | 58.6  | 56.2   | 56.2  | 53.9   | 53.9  | 51.6   | 49.2  | 51.6   | 56.2  | 58.6   |
| 22.5° | 51.6   | 46.9  | 44.5   | 39.8  | 42.2   | 46.9  | 49.2   | 51.6  | 51.6   | 51.6  | 51.6   |
| 25°   | 42.2   | 42.2  | 44.5   | 44.5  | 42.2   | 39.8  | 37.5   | 35.2  | 37.5   | 39.8  | 39.8   |
| 27.5° | 37.5   | 35.2  | 32.8   | 30.5  | 32.8   | 32.8  | 35.2   | 35.2  | 35.2   | 35.2  | 32.8   |
| 30°   | 32.8   | 32.8  | 30.5   | 30.5  | 30.5   | 28.1  | 28.1   | 25.8  | 28.1   | 28.1  | 30.5   |
| 32.5° | 28.1   | 25.8  | 25.8   | 23.4  | 23.4   | 25.8  | 25.8   | 25.8  | 25.8   | 25.8  | 25.8   |
| 35°   | 25.8   | 23.4  | 23.4   | 21.1  | 21.1   | 21.1  | 21.1   | 21.1  | 23.4   | 23.4  | 25.8   |
| 37.5° | 21.1   | 18.7  | 18.7   | 16.4  | 16.4   | 18.7  | 18.7   | 18.7  | 18.7   | 21.1  | 21.1   |
| 40°   | 18.7   | 16.4  | 16.4   | 14.1  | 14.1   | 16.4  | 16.4   | 16.4  | 16.4   | 18.7  | 18.7   |
| 42.5° | 14.1   | 14.1  | 11.7   | 11.7  | 11.7   | 14.1  | 14.1   | 14.1  | 14.1   | 16.4  | 16.4   |
| 45°   | 11.7   | 11.7  | 9.4    | 9.4   | 9.4    | 11.7  | 11.7   | 11.7  | 11.7   | 11.7  | 11.7   |
| 47.5° | 9.4    | 9.4   | 7.0    | 7.0   | 7.0    | 9.4   | 9.4    | 9.4   | 9.4    | 9.4   | 9.4    |
| 50°   | 9.4    | 7.0   | 7.0    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    |
| 52.5° | 7.0    | 7.0   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    |
| 55°   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    |
| 57.5° | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    |
| 60°   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    |
| 62.5° | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    |
| 65°   | 2.3    | 2.3   | 2.3    | 2.3   | 4.7    | 4.7   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    |
| 67.5° | 2.3    | 2.3   | 2.3    | 2.3   | 4.7    | 4.7   | 7.0    | 7.0   | 7.0    | 4.7   | 4.7    |
| 70°   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    |
| 72.5° | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    |
| 75°   | 4.7    | 4.7   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    |
| 77.5° | 4.7    | 4.7   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    |
| 80°   | 4.7    | 4.7   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    |
| 82.5° | 4.7    | 4.7   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    |
| 85°   | 4.7    | 7.0   | 7.0    | 9.4   | 9.4    | 9.4   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    |
| 87.5° | 4.7    | 7.0   | 7.0    | 9.4   | 9.4    | 9.4   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    |
| 90°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° | 190°  |
|-------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°    | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 |
| 2.5°  | 433.6 | 428.9  | 424.2 | 417.2  | 412.5 | 417.2  | 421.9 | 417.2  | 412.5 | 417.2  | 424.2 |
| 5°    | 274.2 | 271.9  | 271.9 | 269.5  | 267.2 | 267.2  | 264.8 | 267.2  | 267.2 | 269.5  | 271.9 |
| 7.5°  | 166.4 | 164.1  | 161.7 | 157.0  | 154.7 | 159.4  | 161.7 | 159.4  | 154.7 | 157.0  | 161.7 |
| 10°   | 128.9 | 128.9  | 126.6 | 126.6  | 124.2 | 124.2  | 124.2 | 124.2  | 124.2 | 126.6  | 126.6 |
| 12.5° | 100.8 | 98.4   | 96.1  | 93.7   | 91.4  | 96.1   | 98.4  | 96.1   | 91.4  | 93.7   | 96.1  |
| 15°   | 84.4  | 84.4   | 86.7  | 86.7   | 86.7  | 86.7   | 86.7  | 86.7   | 86.7  | 86.7   | 86.7  |
| 17.5° | 75.0  | 72.7   | 72.7  | 70.3   | 68.0  | 68.0   | 65.6  | 68.0   | 68.0  | 70.3   | 72.7  |
| 20°   | 60.9  | 60.9   | 63.3  | 63.3   | 63.3  | 63.3   | 63.3  | 63.3   | 63.3  | 63.3   | 63.3  |
| 22.5° | 51.6  | 49.2   | 49.2  | 46.9   | 44.5  | 44.5   | 42.2  | 44.5   | 44.5  | 46.9   | 49.2  |
| 25°   | 42.2  | 42.2   | 44.5  | 44.5   | 44.5  | 44.5   | 44.5  | 44.5   | 44.5  | 44.5   | 44.5  |
| 27.5° | 32.8  | 32.8   | 32.8  | 30.5   | 30.5  | 30.5   | 30.5  | 30.5   | 30.5  | 30.5   | 32.8  |
| 30°   | 30.5  | 30.5   | 30.5  | 30.5   | 30.5  | 30.5   | 30.5  | 30.5   | 30.5  | 30.5   | 30.5  |
| 32.5° | 25.8  | 25.8   | 25.8  | 25.8   | 25.8  | 25.8   | 25.8  | 25.8   | 25.8  | 25.8   | 25.8  |
| 35°   | 25.8  | 25.8   | 25.8  | 23.4   | 23.4  | 23.4   | 23.4  | 23.4   | 23.4  | 23.4   | 25.8  |
| 37.5° | 21.1  | 21.1   | 21.1  | 21.1   | 21.1  | 21.1   | 21.1  | 21.1   | 21.1  | 21.1   | 21.1  |
| 40°   | 18.7  | 18.7   | 18.7  | 18.7   | 18.7  | 18.7   | 18.7  | 18.7   | 18.7  | 18.7   | 18.7  |
| 42.5° | 16.4  | 16.4   | 16.4  | 16.4   | 16.4  | 16.4   | 16.4  | 16.4   | 16.4  | 16.4   | 16.4  |
| 45°   | 11.7  | 11.7   | 11.7  | 11.7   | 11.7  | 11.7   | 11.7  | 11.7   | 11.7  | 11.7   | 11.7  |
| 47.5° | 9.4   | 9.4    | 9.4   | 9.4    | 9.4   | 9.4    | 9.4   | 9.4    | 9.4   | 9.4    | 9.4   |
| 50°   | 7.0   | 7.0    | 7.0   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 7.0   |
| 52.5° | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 4.7   |
| 55°   | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   |
| 57.5° | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   |
| 60°   | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   |
| 62.5° | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 2.3   | 2.3    | 4.7   |
| 65°   | 4.7   | 4.7    | 2.3   | 2.3    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.3    | 2.3   |
| 67.5° | 2.3   | 2.3    | 2.3   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 2.3   |
| 70°   | 4.7   | 4.7    | 2.3   | 2.3    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.3    | 2.3   |
| 72.5° | 4.7   | 4.7    | 2.3   | 2.3    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.3    | 2.3   |
| 75°   | 4.7   | 4.7    | 2.3   | 2.3    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.3    | 2.3   |
| 77.5° | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    | 0.0   | 2.3    | 2.3   | 2.3    | 4.7   |
| 80°   | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    | 0.0   | 2.3    | 2.3   | 2.3    | 4.7   |
| 82.5° | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    | 0.0   | 2.3    | 2.3   | 2.3    | 4.7   |
| 85°   | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    | 0.0   | 2.3    | 2.3   | 2.3    | 4.7   |
| 87.5° | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    | 0.0   | 2.3    | 2.3   | 2.3    | 4.7   |
| 90°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  | 217.5° |
|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°    | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  |
| 2.5°  | 428.9  | 433.6 | 435.9  | 440.6 | 443.0  | 445.3 | 464.1  | 480.5 | 499.2  | 515.6 | 527.3  |
| 5°    | 271.9  | 274.2 | 278.9  | 283.6 | 285.9  | 290.6 | 295.3  | 300.0 | 304.7  | 309.4 | 316.4  |
| 7.5°  | 164.1  | 166.4 | 173.4  | 178.1 | 185.2  | 189.8 | 196.9  | 203.9 | 208.6  | 215.6 | 225.0  |
| 10°   | 128.9  | 128.9 | 131.2  | 131.2 | 133.6  | 133.6 | 128.9  | 126.6 | 121.9  | 117.2 | 128.9  |
| 12.5° | 98.4   | 100.8 | 103.1  | 103.1 | 105.5  | 105.5 | 105.5  | 107.8 | 107.8  | 107.8 | 107.8  |
| 15°   | 84.4   | 84.4  | 82.0   | 77.3  | 75.0   | 70.3  | 70.3   | 72.7  | 72.7   | 72.7  | 75.0   |
| 17.5° | 72.7   | 75.0  | 75.0   | 75.0  | 72.7   | 72.7  | 70.3   | 70.3  | 68.0   | 65.6  | 63.3   |
| 20°   | 60.9   | 60.9  | 58.6   | 56.2  | 51.6   | 49.2  | 51.6   | 53.9  | 53.9   | 56.2  | 56.2   |
| 22.5° | 49.2   | 51.6  | 51.6   | 51.6  | 51.6   | 51.6  | 49.2   | 46.9  | 42.2   | 39.8  | 44.5   |
| 25°   | 42.2   | 42.2  | 39.8   | 39.8  | 37.5   | 35.2  | 37.5   | 39.8  | 42.2   | 44.5  | 44.5   |
| 27.5° | 32.8   | 32.8  | 32.8   | 35.2  | 35.2   | 35.2  | 35.2   | 32.8  | 32.8   | 30.5  | 32.8   |
| 30°   | 30.5   | 30.5  | 30.5   | 28.1  | 28.1   | 25.8  | 28.1   | 28.1  | 30.5   | 30.5  | 30.5   |
| 32.5° | 25.8   | 25.8  | 25.8   | 25.8  | 25.8   | 25.8  | 25.8   | 25.8  | 23.4   | 23.4  | 25.8   |
| 35°   | 25.8   | 25.8  | 25.8   | 23.4  | 23.4   | 21.1  | 21.1   | 21.1  | 21.1   | 21.1  | 23.4   |
| 37.5° | 21.1   | 21.1  | 21.1   | 21.1  | 18.7   | 18.7  | 18.7   | 18.7  | 16.4   | 16.4  | 18.7   |
| 40°   | 18.7   | 18.7  | 18.7   | 18.7  | 16.4   | 16.4  | 16.4   | 16.4  | 14.1   | 14.1  | 16.4   |
| 42.5° | 16.4   | 16.4  | 16.4   | 16.4  | 14.1   | 14.1  | 14.1   | 14.1  | 11.7   | 11.7  | 11.7   |
| 45°   | 11.7   | 11.7  | 11.7   | 11.7  | 11.7   | 11.7  | 11.7   | 11.7  | 9.4    | 9.4   | 9.4    |
| 47.5° | 9.4    | 9.4   | 9.4    | 9.4   | 9.4    | 9.4   | 9.4    | 9.4   | 7.0    | 7.0   | 7.0    |
| 50°   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    | 4.7   | 7.0    |
| 52.5° | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    |
| 55°   | 2.3    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    |
| 57.5° | 2.3    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    |
| 60°   | 2.3    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    |
| 62.5° | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 2.3    | 2.3   | 2.3    |
| 65°   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 4.7   | 4.7    | 2.3   | 2.3    |
| 67.5° | 2.3    | 2.3   | 4.7    | 4.7   | 7.0    | 7.0   | 7.0    | 4.7   | 4.7    | 2.3   | 2.3    |
| 70°   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    | 4.7   | 4.7    |
| 72.5° | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    | 4.7   | 4.7    |
| 75°   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    |
| 77.5° | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    |
| 80°   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    |
| 82.5° | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    | 7.0   | 7.0    |
| 85°   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 9.4   | 9.4    | 9.4   | 7.0    |
| 87.5° | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 7.0    | 9.4   | 9.4    | 9.4   | 7.0    |
| 90°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° | 245°  |
|-------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°    | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 |
| 2.5°  | 536.7 | 548.4  | 557.8 | 567.2  | 576.6 | 585.9  | 595.3 | 604.7  | 616.4 | 625.8  | 635.2 |
| 5°    | 323.4 | 330.5  | 337.5 | 351.6  | 365.6 | 377.3  | 391.4 | 424.2  | 454.7 | 487.5  | 518.0 |
| 7.5°  | 234.4 | 243.7  | 253.1 | 264.8  | 276.6 | 288.3  | 300.0 | 311.7  | 325.8 | 337.5  | 349.2 |
| 10°   | 138.3 | 150.0  | 159.4 | 168.7  | 180.5 | 189.8  | 199.2 | 208.6  | 220.3 | 229.7  | 239.1 |
| 12.5° | 107.8 | 107.8  | 107.8 | 112.5  | 119.5 | 124.2  | 128.9 | 145.3  | 161.7 | 178.1  | 194.5 |
| 15°   | 77.3  | 79.7   | 82.0  | 84.4   | 86.7  | 86.7   | 89.1  | 100.8  | 112.5 | 121.9  | 133.6 |
| 17.5° | 63.3  | 60.9   | 58.6  | 63.3   | 68.0  | 72.7   | 77.3  | 84.4   | 89.1  | 96.1   | 100.8 |
| 20°   | 58.6  | 58.6   | 58.6  | 60.9   | 63.3  | 63.3   | 65.6  | 68.0   | 72.7  | 75.0   | 77.3  |
| 22.5° | 46.9  | 51.6   | 53.9  | 53.9   | 53.9  | 51.6   | 51.6  | 58.6   | 65.6  | 72.7   | 79.7  |
| 25°   | 42.2  | 42.2   | 39.8  | 44.5   | 46.9  | 51.6   | 53.9  | 56.2   | 56.2  | 58.6   | 58.6  |
| 27.5° | 35.2  | 37.5   | 39.8  | 42.2   | 42.2  | 44.5   | 44.5  | 49.2   | 53.9  | 58.6   | 63.3  |
| 30°   | 32.8  | 32.8   | 32.8  | 35.2   | 39.8  | 42.2   | 44.5  | 49.2   | 53.9  | 56.2   | 60.9  |
| 32.5° | 25.8  | 28.1   | 28.1  | 30.5   | 35.2  | 37.5   | 39.8  | 46.9   | 51.6  | 58.6   | 63.3  |
| 35°   | 23.4  | 25.8   | 25.8  | 28.1   | 30.5  | 32.8   | 35.2  | 42.2   | 46.9  | 53.9   | 58.6  |
| 37.5° | 18.7  | 21.1   | 21.1  | 23.4   | 25.8  | 28.1   | 30.5  | 35.2   | 42.2  | 46.9   | 51.6  |
| 40°   | 16.4  | 18.7   | 18.7  | 21.1   | 23.4  | 23.4   | 25.8  | 30.5   | 35.2  | 39.8   | 44.5  |
| 42.5° | 14.1  | 14.1   | 14.1  | 16.4   | 18.7  | 21.1   | 23.4  | 28.1   | 32.8  | 35.2   | 39.8  |
| 45°   | 11.7  | 11.7   | 11.7  | 14.1   | 16.4  | 18.7   | 21.1  | 25.8   | 28.1  | 32.8   | 35.2  |
| 47.5° | 9.4   | 9.4    | 9.4   | 11.7   | 14.1  | 16.4   | 18.7  | 21.1   | 25.8  | 28.1   | 30.5  |
| 50°   | 7.0   | 9.4    | 9.4   | 11.7   | 14.1  | 14.1   | 16.4  | 18.7   | 23.4  | 25.8   | 28.1  |
| 52.5° | 7.0   | 7.0    | 7.0   | 9.4    | 11.7  | 11.7   | 14.1  | 16.4   | 18.7  | 21.1   | 23.4  |
| 55°   | 4.7   | 4.7    | 4.7   | 7.0    | 9.4   | 9.4    | 11.7  | 14.1   | 16.4  | 18.7   | 21.1  |
| 57.5° | 4.7   | 4.7    | 4.7   | 7.0    | 7.0   | 9.4    | 9.4   | 11.7   | 14.1  | 16.4   | 18.7  |
| 60°   | 2.3   | 2.3    | 2.3   | 4.7    | 4.7   | 7.0    | 7.0   | 9.4    | 11.7  | 14.1   | 16.4  |
| 62.5° | 2.3   | 2.3    | 2.3   | 4.7    | 4.7   | 7.0    | 7.0   | 9.4    | 11.7  | 14.1   | 16.4  |
| 65°   | 2.3   | 2.3    | 2.3   | 4.7    | 4.7   | 7.0    | 7.0   | 9.4    | 11.7  | 11.7   | 14.1  |
| 67.5° | 2.3   | 2.3    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 7.0    | 9.4   | 11.7   | 14.1  |
| 70°   | 4.7   | 2.3    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 7.0    | 7.0   | 9.4    | 9.4   |
| 72.5° | 4.7   | 2.3    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 7.0    | 7.0   | 9.4    | 9.4   |
| 75°   | 4.7   | 4.7    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   |
| 77.5° | 4.7   | 4.7    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   |
| 80°   | 4.7   | 4.7    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   |
| 82.5° | 4.7   | 4.7    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   |
| 85°   | 7.0   | 4.7    | 2.3   | 2.3    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   |
| 87.5° | 7.0   | 4.7    | 2.3   | 4.7    | 4.7   | 7.0    | 7.0   | 7.0    | 7.0   | 4.7    | 4.7   |
| 90°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   | 272.5° |
|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|--------|
| 0°    | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7 | 768.7  | 768.7  | 768.7  |
| 2.5°  | 649.2  | 660.9 | 675.0  | 686.7 | 700.8  | 714.8 | 728.9  | 743.0 | 757.0  | 771.1  | 785.1  |
| 5°    | 541.4  | 567.2 | 590.6  | 614.1 | 639.8  | 668.0 | 693.7  | 719.5 | 747.7  | 775.8  | 801.6  |
| 7.5°  | 379.7  | 410.2 | 440.6  | 471.1 | 508.6  | 546.1 | 581.2  | 618.7 | 653.9  | 689.1  | 724.2  |
| 10°   | 260.2  | 281.2 | 300.0  | 321.1 | 370.3  | 419.5 | 468.7  | 518.0 | 562.5  | 604.7  | 644.5  |
| 12.5° | 208.6  | 225.0 | 239.1  | 253.1 | 300.0  | 349.2 | 396.1  | 443.0 | 487.5  | 532.0  | 571.9  |
| 15°   | 171.1  | 206.2 | 243.7  | 278.9 | 349.2  | 417.2 | 487.5  | 555.5 | 623.4  | 691.4  | 743.0  |
| 17.5° | 133.6  | 166.4 | 199.2  | 232.0 | 297.7  | 360.9 | 426.6  | 489.8 | 550.8  | 611.7  | 668.0  |
| 20°   | 114.8  | 152.3 | 189.8  | 227.3 | 316.4  | 405.5 | 494.5  | 583.6 | 675.0  | 764.1  | 836.7  |
| 22.5° | 103.1  | 126.6 | 147.7  | 171.1 | 232.0  | 290.6 | 351.6  | 410.2 | 482.8  | 553.1  | 609.4  |
| 25°   | 86.7   | 114.8 | 143.0  | 171.1 | 271.9  | 372.7 | 473.4  | 574.2 | 698.4  | 822.6  | 921.1  |
| 27.5° | 84.4   | 105.5 | 126.6  | 147.7 | 278.9  | 410.2 | 541.4  | 672.7 | 829.7  | 986.7  | 1118.0 |
| 30°   | 79.7   | 98.4  | 114.8  | 133.6 | 288.3  | 443.0 | 597.7  | 752.3 | 975.0  | 1195.3 | 1352.3 |
| 32.5° | 75.0   | 86.7  | 96.1   | 107.8 | 262.5  | 419.5 | 574.2  | 728.9 | 989.1  | 1246.9 | 1425.0 |
| 35°   | 65.6   | 75.0  | 82.0   | 89.1  | 243.7  | 398.4 | 550.8  | 705.5 | 1003.1 | 1298.4 | 1500.0 |
| 37.5° | 58.6   | 65.6  | 72.7   | 79.7  | 229.7  | 377.3 | 527.3  | 675.0 | 1017.2 | 1359.4 | 1586.7 |
| 40°   | 51.6   | 58.6  | 65.6   | 72.7  | 215.6  | 358.6 | 499.2  | 642.2 | 1031.2 | 1420.3 | 1671.1 |
| 42.5° | 46.9   | 53.9  | 60.9   | 68.0  | 203.9  | 339.8 | 473.4  | 609.4 | 1047.6 | 1485.9 | 1764.8 |
| 45°   | 42.2   | 49.2  | 53.9   | 60.9  | 187.5  | 314.1 | 440.6  | 567.2 | 1071.1 | 1575.0 | 1877.3 |
| 47.5° | 37.5   | 44.5  | 51.6   | 58.6  | 175.8  | 293.0 | 407.8  | 525.0 | 1094.5 | 1664.0 | 1999.2 |
| 50°   | 35.2   | 42.2  | 46.9   | 53.9  | 166.4  | 278.9 | 391.4  | 503.9 | 1141.4 | 1776.5 | 2146.9 |
| 52.5° | 30.5   | 37.5  | 42.2   | 49.2  | 159.4  | 267.2 | 377.3  | 485.2 | 1197.6 | 1907.8 | 2322.6 |
| 55°   | 28.1   | 32.8  | 39.8   | 44.5  | 147.7  | 248.4 | 351.6  | 452.3 | 1209.4 | 1964.0 | 2423.4 |
| 57.5° | 23.4   | 30.5  | 35.2   | 39.8  | 135.9  | 232.0 | 325.8  | 421.9 | 1230.5 | 2036.7 | 2519.5 |
| 60°   | 21.1   | 25.8  | 30.5   | 35.2  | 124.2  | 215.6 | 304.7  | 393.7 | 1256.2 | 2118.7 | 2639.0 |
| 62.5° | 21.1   | 23.4  | 28.1   | 30.5  | 112.5  | 196.9 | 278.9  | 360.9 | 1298.4 | 2233.6 | 2810.1 |
| 65°   | 18.7   | 21.1  | 25.8   | 28.1  | 103.1  | 180.5 | 255.5  | 330.5 | 1338.3 | 2343.7 | 3011.7 |
| 67.5° | 16.4   | 21.1  | 23.4   | 25.8  | 93.7   | 159.4 | 227.3  | 293.0 | 1338.3 | 2383.6 | 3171.1 |
| 70°   | 14.1   | 16.4  | 21.1   | 23.4  | 77.3   | 128.9 | 182.8  | 234.4 | 1242.2 | 2250.0 | 3145.3 |
| 72.5° | 11.7   | 14.1  | 16.4   | 18.7  | 51.6   | 84.4  | 114.8  | 147.7 | 1012.5 | 1877.3 | 2796.1 |
| 75°   | 9.4    | 11.7  | 11.7   | 14.1  | 28.1   | 44.5  | 58.6   | 72.7  | 717.2  | 1359.4 | 2085.9 |
| 77.5° | 9.4    | 9.4   | 11.7   | 11.7  | 18.7   | 28.1  | 35.2   | 42.2  | 356.2  | 668.0  | 1071.1 |
| 80°   | 7.0    | 7.0   | 9.4    | 9.4   | 14.1   | 18.7  | 21.1   | 25.8  | 84.4   | 140.6  | 227.3  |
| 82.5° | 4.7    | 7.0   | 7.0    | 7.0   | 9.4    | 11.7  | 11.7   | 14.1  | 18.7   | 23.4   | 37.5   |
| 85°   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 7.0   | 7.0    | 7.0   | 9.4    | 9.4    | 14.1   |
| 87.5° | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7    | 7.0    |
| 90°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  |
| 2.5°  | 796.9  | 808.6  | 818.0  | 829.7  | 843.7  | 853.1  | 862.5  | 871.9  | 881.2  | 890.6  | 900.0  |
| 5°    | 825.0  | 848.4  | 869.5  | 893.0  | 916.4  | 930.5  | 944.5  | 958.6  | 972.6  | 946.9  | 921.1  |
| 7.5°  | 759.4  | 787.5  | 815.6  | 843.7  | 864.8  | 857.8  | 850.8  | 843.7  | 836.7  | 867.2  | 895.3  |
| 10°   | 682.0  | 705.5  | 731.2  | 754.7  | 696.1  | 707.8  | 717.2  | 728.9  | 738.3  | 754.7  | 771.1  |
| 12.5° | 611.7  | 604.7  | 600.0  | 593.0  | 611.7  | 658.6  | 705.5  | 750.0  | 796.9  | 803.9  | 813.3  |
| 15°   | 794.5  | 799.2  | 803.9  | 808.6  | 813.3  | 789.8  | 766.4  | 740.6  | 717.2  | 724.2  | 731.2  |
| 17.5° | 724.2  | 731.2  | 740.6  | 747.7  | 773.4  | 789.8  | 803.9  | 820.3  | 834.4  | 864.8  | 895.3  |
| 20°   | 907.0  | 923.4  | 937.5  | 953.9  | 900.0  | 869.5  | 836.7  | 806.2  | 773.4  | 806.2  | 839.1  |
| 22.5° | 665.6  | 745.3  | 825.0  | 904.7  | 888.3  | 939.8  | 991.4  | 1040.6 | 1092.2 | 1038.3 | 984.4  |
| 25°   | 1017.2 | 1054.7 | 1094.5 | 1132.0 | 1155.5 | 1103.9 | 1052.3 | 1000.8 | 949.2  | 989.1  | 1028.9 |
| 27.5° | 1249.2 | 1239.8 | 1230.5 | 1221.1 | 1268.0 | 1249.2 | 1230.5 | 1209.4 | 1190.6 | 1153.1 | 1113.3 |
| 30°   | 1507.0 | 1582.0 | 1657.0 | 1732.0 | 1750.8 | 1666.4 | 1579.7 | 1495.3 | 1408.6 | 1361.7 | 1312.5 |
| 32.5° | 1600.8 | 1694.5 | 1785.9 | 1879.7 | 1875.0 | 1825.8 | 1776.5 | 1725.0 | 1675.8 | 1593.7 | 1514.1 |
| 35°   | 1701.5 | 1807.0 | 1910.1 | 2015.6 | 2057.8 | 1985.1 | 1910.1 | 1837.5 | 1762.5 | 1706.2 | 1650.0 |
| 37.5° | 1811.7 | 1926.5 | 2041.4 | 2156.2 | 2247.6 | 2156.2 | 2067.2 | 1975.8 | 1884.4 | 1825.8 | 1767.2 |
| 40°   | 1919.5 | 2076.5 | 2231.2 | 2388.3 | 2392.9 | 2301.5 | 2207.8 | 2116.4 | 2022.6 | 1959.4 | 1896.1 |
| 42.5° | 2041.4 | 2219.5 | 2395.3 | 2573.4 | 2575.8 | 2477.3 | 2381.2 | 2282.8 | 2184.4 | 2121.1 | 2057.8 |
| 45°   | 2177.3 | 2378.9 | 2578.1 | 2779.7 | 2767.9 | 2655.4 | 2542.9 | 2430.4 | 2317.9 | 2261.7 | 2203.1 |
| 47.5° | 2334.4 | 2552.3 | 2770.3 | 2988.3 | 3060.9 | 2908.6 | 2753.9 | 2601.5 | 2446.9 | 2395.3 | 2343.7 |
| 50°   | 2514.8 | 2749.2 | 2983.6 | 3217.9 | 3314.0 | 3133.6 | 2953.1 | 2770.3 | 2589.8 | 2538.3 | 2486.7 |
| 52.5° | 2735.1 | 2976.5 | 3215.6 | 3457.0 | 3555.4 | 3358.6 | 3161.7 | 2964.8 | 2767.9 | 2704.7 | 2641.4 |
| 55°   | 2880.4 | 3159.3 | 3435.9 | 3714.8 | 3827.3 | 3609.3 | 3391.4 | 3171.1 | 2953.1 | 2866.4 | 2777.3 |
| 57.5° | 3002.3 | 3288.3 | 3571.8 | 3857.8 | 3970.3 | 3745.3 | 3520.3 | 3292.9 | 3067.9 | 2962.5 | 2857.0 |
| 60°   | 3157.0 | 3447.6 | 3740.6 | 4031.2 | 4127.3 | 3883.6 | 3639.8 | 3393.7 | 3150.0 | 3028.1 | 2908.6 |
| 62.5° | 3384.3 | 3660.9 | 3937.5 | 4214.0 | 4277.3 | 4017.2 | 3759.3 | 3499.2 | 3239.0 | 3084.3 | 2929.7 |
| 65°   | 3679.7 | 3956.2 | 4235.1 | 4511.7 | 4579.6 | 4270.3 | 3963.2 | 3653.9 | 3344.5 | 3140.6 | 2936.7 |
| 67.5° | 3956.2 | 4272.6 | 4591.4 | 4907.8 | 4975.7 | 4593.7 | 4209.3 | 3827.3 | 3442.9 | 3175.8 | 2908.6 |
| 70°   | 4038.2 | 4413.2 | 4788.2 | 5163.2 | 5252.3 | 4802.3 | 4352.3 | 3900.0 | 3450.0 | 3114.8 | 2782.0 |
| 72.5° | 3714.8 | 4141.4 | 4565.6 | 4992.1 | 5160.9 | 4680.4 | 4200.0 | 3717.2 | 3236.7 | 2859.4 | 2484.4 |
| 75°   | 2810.1 | 3227.3 | 3646.8 | 4064.0 | 4279.7 | 3857.8 | 3438.3 | 3016.4 | 2594.5 | 2250.0 | 1907.8 |
| 77.5° | 1474.2 | 1788.3 | 2100.0 | 2414.0 | 2800.8 | 2472.6 | 2142.2 | 1814.0 | 1483.6 | 1272.6 | 1059.4 |
| 80°   | 311.7  | 419.5  | 525.0  | 632.8  | 850.8  | 773.4  | 698.4  | 621.1  | 543.7  | 457.0  | 368.0  |
| 82.5° | 51.6   | 68.0   | 84.4   | 100.8  | 126.6  | 126.6  | 128.9  | 128.9  | 128.9  | 112.5  | 93.7   |
| 85°   | 16.4   | 21.1   | 25.8   | 30.5   | 30.5   | 32.8   | 32.8   | 35.2   | 35.2   | 35.2   | 32.8   |
| 87.5° | 7.0    | 7.0    | 9.4    | 9.4    | 9.4    | 9.4    | 11.7   | 11.7   | 11.7   | 11.7   | 11.7   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  |
| 2.5°  | 909.4  | 918.7  | 925.8  | 935.1  | 942.2  | 949.2  | 953.9  | 956.2  | 960.9  | 963.3  | 958.6  |
| 5°    | 893.0  | 867.2  | 876.6  | 885.9  | 893.0  | 902.3  | 909.4  | 916.4  | 921.1  | 928.1  | 932.8  |
| 7.5°  | 925.8  | 953.9  | 965.6  | 977.3  | 989.1  | 1000.8 | 1007.8 | 1014.8 | 1019.5 | 1026.6 | 1028.9 |
| 10°   | 787.5  | 803.9  | 839.1  | 876.6  | 911.7  | 946.9  | 935.1  | 923.4  | 911.7  | 900.0  | 951.6  |
| 12.5° | 820.3  | 827.3  | 848.4  | 867.2  | 888.3  | 907.0  | 946.9  | 984.4  | 1024.2 | 1061.7 | 1085.1 |
| 15°   | 738.3  | 745.3  | 801.6  | 855.5  | 911.7  | 965.6  | 949.2  | 932.8  | 916.4  | 900.0  | 925.8  |
| 17.5° | 923.4  | 953.9  | 900.0  | 843.7  | 789.8  | 733.6  | 799.2  | 867.2  | 932.8  | 998.4  | 1021.9 |
| 20°   | 871.9  | 904.7  | 932.8  | 960.9  | 989.1  | 1017.2 | 993.7  | 972.6  | 949.2  | 925.8  | 907.0  |
| 22.5° | 928.1  | 874.2  | 907.0  | 942.2  | 975.0  | 1007.8 | 991.4  | 977.3  | 960.9  | 944.5  | 982.0  |
| 25°   | 1066.4 | 1106.2 | 1054.7 | 1003.1 | 951.6  | 900.0  | 958.6  | 1017.2 | 1073.4 | 1132.0 | 1094.5 |
| 27.5° | 1075.8 | 1035.9 | 1082.8 | 1127.3 | 1174.2 | 1218.7 | 1169.5 | 1122.6 | 1073.4 | 1024.2 | 1078.1 |
| 30°   | 1265.6 | 1216.4 | 1202.3 | 1188.3 | 1174.2 | 1160.1 | 1185.9 | 1211.7 | 1235.1 | 1260.9 | 1268.0 |
| 32.5° | 1432.0 | 1350.0 | 1371.1 | 1394.5 | 1415.6 | 1436.7 | 1418.0 | 1401.6 | 1382.8 | 1364.1 | 1443.7 |
| 35°   | 1593.7 | 1537.5 | 1546.9 | 1556.2 | 1565.6 | 1575.0 | 1579.7 | 1582.0 | 1586.7 | 1589.0 | 1692.2 |
| 37.5° | 1706.2 | 1647.6 | 1680.5 | 1713.3 | 1746.1 | 1778.9 | 1778.9 | 1776.5 | 1776.5 | 1774.2 | 1891.4 |
| 40°   | 1830.5 | 1767.2 | 1814.0 | 1858.6 | 1905.5 | 1950.0 | 1959.4 | 1968.7 | 1978.1 | 1987.5 | 2095.3 |
| 42.5° | 1992.2 | 1928.9 | 1968.7 | 2006.2 | 2046.1 | 2083.6 | 2100.0 | 2116.4 | 2130.5 | 2146.9 | 2254.7 |
| 45°   | 2146.9 | 2088.3 | 2118.7 | 2149.2 | 2179.7 | 2210.1 | 2224.2 | 2238.3 | 2252.3 | 2266.4 | 2390.6 |
| 47.5° | 2292.2 | 2240.6 | 2259.4 | 2275.8 | 2294.5 | 2310.9 | 2322.6 | 2332.0 | 2343.7 | 2353.1 | 2477.3 |
| 50°   | 2435.1 | 2383.6 | 2388.3 | 2392.9 | 2395.3 | 2400.0 | 2404.7 | 2411.7 | 2416.4 | 2421.1 | 2566.4 |
| 52.5° | 2575.8 | 2512.5 | 2500.8 | 2489.0 | 2477.3 | 2465.6 | 2465.6 | 2463.3 | 2463.3 | 2460.9 | 2573.4 |
| 55°   | 2690.6 | 2601.5 | 2573.4 | 2542.9 | 2514.8 | 2484.4 | 2472.6 | 2460.9 | 2446.9 | 2435.1 | 2493.7 |
| 57.5° | 2749.2 | 2643.7 | 2601.5 | 2557.0 | 2514.8 | 2470.3 | 2430.4 | 2388.3 | 2348.4 | 2306.2 | 2296.9 |
| 60°   | 2786.7 | 2664.8 | 2599.2 | 2531.2 | 2465.6 | 2397.6 | 2299.2 | 2200.8 | 2102.3 | 2003.9 | 1952.3 |
| 62.5° | 2772.6 | 2617.9 | 2517.2 | 2414.0 | 2313.3 | 2210.1 | 2057.8 | 1905.5 | 1750.8 | 1598.4 | 1525.8 |
| 65°   | 2730.4 | 2526.5 | 2381.2 | 2233.6 | 2088.3 | 1940.6 | 1757.8 | 1575.0 | 1392.2 | 1209.4 | 1141.4 |
| 67.5° | 2641.4 | 2374.2 | 2170.3 | 1968.7 | 1764.8 | 1560.9 | 1375.8 | 1190.6 | 1005.5 | 820.3  | 771.1  |
| 70°   | 2446.9 | 2111.7 | 1872.6 | 1631.2 | 1392.2 | 1150.8 | 993.7  | 834.4  | 677.3  | 518.0  | 494.5  |
| 72.5° | 2107.0 | 1729.7 | 1485.9 | 1244.5 | 1000.8 | 757.0  | 649.2  | 541.4  | 433.6  | 325.8  | 318.7  |
| 75°   | 1563.3 | 1218.7 | 1031.2 | 841.4  | 653.9  | 464.1  | 400.8  | 339.8  | 276.6  | 213.3  | 215.6  |
| 77.5° | 848.4  | 635.2  | 546.1  | 457.0  | 365.6  | 276.6  | 246.1  | 215.6  | 185.2  | 154.7  | 159.4  |
| 80°   | 281.2  | 192.2  | 178.1  | 164.1  | 150.0  | 135.9  | 124.2  | 112.5  | 100.8  | 89.1   | 93.7   |
| 82.5° | 77.3   | 58.6   | 63.3   | 70.3   | 75.0   | 79.7   | 79.7   | 79.7   | 77.3   | 77.3   | 77.3   |
| 85°   | 32.8   | 30.5   | 28.1   | 28.1   | 25.8   | 23.4   | 28.1   | 32.8   | 37.5   | 42.2   | 44.5   |
| 87.5° | 9.4    | 9.4    | 9.4    | 7.0    | 7.0    | 4.7    | 4.7    | 4.7    | 4.7    | 4.7    | 7.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  | 768.7  |
| 2.5°  | 956.2  | 951.6  | 946.9  | 939.8  | 935.1  | 928.1  | 921.1  | 914.1  | 907.0  | 897.6  | 890.6  |
| 5°    | 937.5  | 942.2  | 946.9  | 949.2  | 953.9  | 956.2  | 958.6  | 960.9  | 963.3  | 963.3  | 965.6  |
| 7.5°  | 1028.9 | 1031.2 | 1031.2 | 1017.2 | 1005.5 | 991.4  | 977.3  | 975.0  | 975.0  | 972.6  | 970.3  |
| 10°   | 1005.5 | 1057.0 | 1108.6 | 1108.6 | 1106.2 | 1106.2 | 1103.9 | 1103.9 | 1106.2 | 1106.2 | 1106.2 |
| 12.5° | 1108.6 | 1132.0 | 1155.5 | 1146.1 | 1139.1 | 1129.7 | 1120.3 | 1080.5 | 1038.3 | 998.4  | 956.2  |
| 15°   | 951.6  | 975.0  | 1000.8 | 1035.9 | 1071.1 | 1106.2 | 1141.4 | 1139.1 | 1139.1 | 1136.7 | 1134.4 |
| 17.5° | 1043.0 | 1066.4 | 1087.5 | 1071.1 | 1054.7 | 1035.9 | 1019.5 | 989.1  | 958.6  | 928.1  | 897.6  |
| 20°   | 890.6  | 871.9  | 853.1  | 928.1  | 1003.1 | 1078.1 | 1153.1 | 1150.8 | 1150.8 | 1148.4 | 1146.1 |
| 22.5° | 1019.5 | 1054.7 | 1092.2 | 1064.1 | 1035.9 | 1007.8 | 979.7  | 975.0  | 968.0  | 963.3  | 956.2  |
| 25°   | 1057.0 | 1017.2 | 979.7  | 1050.0 | 1122.6 | 1193.0 | 1263.3 | 1275.0 | 1286.7 | 1296.1 | 1307.8 |
| 27.5° | 1134.4 | 1188.3 | 1242.2 | 1228.1 | 1214.1 | 1197.6 | 1183.6 | 1193.0 | 1202.3 | 1211.7 | 1221.1 |
| 30°   | 1277.3 | 1284.4 | 1291.4 | 1394.5 | 1500.0 | 1603.1 | 1706.2 | 1720.3 | 1732.0 | 1746.1 | 1757.8 |
| 32.5° | 1523.4 | 1600.8 | 1680.5 | 1743.7 | 1809.4 | 1872.6 | 1935.9 | 2020.3 | 2107.0 | 2191.4 | 2275.8 |
| 35°   | 1797.6 | 1900.8 | 2003.9 | 2125.8 | 2250.0 | 2371.9 | 2493.7 | 2524.2 | 2557.0 | 2587.5 | 2617.9 |
| 37.5° | 2008.6 | 2125.8 | 2243.0 | 2369.5 | 2493.7 | 2620.3 | 2744.5 | 2767.9 | 2791.4 | 2814.8 | 2838.3 |
| 40°   | 2203.1 | 2310.9 | 2418.7 | 2552.3 | 2685.9 | 2819.5 | 2953.1 | 2971.9 | 2990.6 | 3009.4 | 3028.1 |
| 42.5° | 2362.5 | 2467.9 | 2575.8 | 2709.4 | 2842.9 | 2976.5 | 3110.1 | 3126.5 | 3140.6 | 3157.0 | 3171.1 |
| 45°   | 2514.8 | 2639.0 | 2763.3 | 2880.4 | 2997.6 | 3112.5 | 3229.7 | 3241.4 | 3250.8 | 3262.5 | 3271.8 |
| 47.5° | 2603.9 | 2728.1 | 2852.3 | 2962.5 | 3072.6 | 3180.4 | 3290.6 | 3290.6 | 3290.6 | 3290.6 | 3290.6 |
| 50°   | 2711.7 | 2854.7 | 3000.0 | 3056.2 | 3110.1 | 3166.4 | 3220.3 | 3208.6 | 3196.8 | 3182.8 | 3171.1 |
| 52.5° | 2683.6 | 2796.1 | 2906.2 | 2927.3 | 2948.4 | 2969.5 | 2990.6 | 2960.1 | 2932.0 | 2901.5 | 2871.1 |
| 55°   | 2552.3 | 2608.6 | 2667.2 | 2632.0 | 2594.5 | 2559.4 | 2521.9 | 2435.1 | 2348.4 | 2261.7 | 2175.0 |
| 57.5° | 2287.5 | 2278.1 | 2268.7 | 2175.0 | 2083.6 | 1989.8 | 1896.1 | 1839.8 | 1785.9 | 1729.7 | 1673.4 |
| 60°   | 1903.1 | 1851.5 | 1800.0 | 1715.6 | 1631.2 | 1546.9 | 1462.5 | 1432.0 | 1399.2 | 1368.7 | 1335.9 |
| 62.5° | 1453.1 | 1380.5 | 1307.8 | 1265.6 | 1223.4 | 1181.2 | 1139.1 | 1108.6 | 1075.8 | 1045.3 | 1012.5 |
| 65°   | 1075.8 | 1007.8 | 939.8  | 904.7  | 869.5  | 832.0  | 796.9  | 775.8  | 754.7  | 731.2  | 710.2  |
| 67.5° | 724.2  | 675.0  | 625.8  | 604.7  | 581.2  | 560.2  | 536.7  | 527.3  | 515.6  | 506.2  | 494.5  |
| 70°   | 468.7  | 445.3  | 419.5  | 410.2  | 403.1  | 393.7  | 384.4  | 375.0  | 365.6  | 356.2  | 346.9  |
| 72.5° | 311.7  | 304.7  | 297.7  | 293.0  | 288.3  | 283.6  | 278.9  | 274.2  | 267.2  | 262.5  | 255.5  |
| 75°   | 215.6  | 218.0  | 218.0  | 215.6  | 215.6  | 213.3  | 210.9  | 192.2  | 173.4  | 154.7  | 135.9  |
| 77.5° | 161.7  | 166.4  | 168.7  | 157.0  | 145.3  | 131.2  | 119.5  | 117.2  | 114.8  | 112.5  | 110.2  |
| 80°   | 100.8  | 105.5  | 110.2  | 105.5  | 103.1  | 98.4   | 93.7   | 89.1   | 84.4   | 79.7   | 75.0   |
| 82.5° | 77.3   | 77.3   | 77.3   | 72.7   | 68.0   | 60.9   | 56.2   | 53.9   | 51.6   | 49.2   | 46.9   |
| 85°   | 46.9   | 49.2   | 51.6   | 46.9   | 39.8   | 35.2   | 28.1   | 23.4   | 18.7   | 14.1   | 9.4    |
| 87.5° | 7.0    | 9.4    | 9.4    | 9.4    | 7.0    | 7.0    | 4.7    | 4.7    | 4.7    | 2.3    | 2.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560602

CATALOG NUMBER: SDL-PA1-50-760-U-T2R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 357.5° | 360°   |
|-------|--------|--------|
| 0°    | 768.7  | 768.7  |
| 2.5°  | 871.9  | 853.1  |
| 5°    | 968.0  | 970.3  |
| 7.5°  | 911.7  | 850.8  |
| 10°   | 1106.2 | 1106.2 |
| 12.5° | 944.5  | 930.5  |
| 15°   | 1129.7 | 1125.0 |
| 17.5° | 895.3  | 890.6  |
| 20°   | 1143.7 | 1141.4 |
| 22.5° | 956.2  | 953.9  |
| 25°   | 1310.1 | 1310.1 |
| 27.5° | 1221.1 | 1218.7 |
| 30°   | 1757.8 | 1757.8 |
| 32.5° | 2320.3 | 2362.5 |
| 35°   | 2625.0 | 2632.0 |
| 37.5° | 2850.0 | 2859.4 |
| 40°   | 3035.1 | 3042.2 |
| 42.5° | 3173.4 | 3173.4 |
| 45°   | 3271.8 | 3271.8 |
| 47.5° | 3288.3 | 3285.9 |
| 50°   | 3164.0 | 3157.0 |
| 52.5° | 2842.9 | 2812.5 |
| 55°   | 2158.6 | 2139.8 |
| 57.5° | 1668.7 | 1661.7 |
| 60°   | 1335.9 | 1335.9 |
| 62.5° | 1003.1 | 993.7  |
| 65°   | 700.8  | 689.1  |
| 67.5° | 489.8  | 485.2  |
| 70°   | 346.9  | 344.5  |
| 72.5° | 253.1  | 250.8  |
| 75°   | 133.6  | 128.9  |
| 77.5° | 110.2  | 107.8  |
| 80°   | 77.3   | 77.3   |
| 82.5° | 46.9   | 44.5   |
| 85°   | 7.0    | 4.7    |
| 87.5° | 2.3    | 2.3    |
| 90°   | 0.0    | 0.0    |



Report Generated By 670245982











--- HS --- SS

u





























(END OF REPORT)