

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560614

Luminaire Tested: **SDL-PA1-50-760-U-T4W-HSS**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560614  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-50-760-U-T4W-HSS  
Description: Springdale  
(1) 70 CRI, 5700K, 670mA LIGHT ENGINE WITH 24 LEDS AND TYPE IV WIDE OPTICS AND HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4660.1 lumens  
Efficiency: N/A  
Efficacy: 88.9 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type IV - Medium  
BUG Rating: B1 - U0 - G2

Input Watts (W): 52.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P560614

CATALOG NUMBER: SDL-PA1-50-760-U-T4W-HSS

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 5.9 fc  
 Type IV - Medium - N/A

REPORT NUMBER: P560614

CATALOG NUMBER: SDL-PA1-50-760-U-T4W-HSS

## Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P560614

CATALOG NUMBER: SDL-PA1-50-760-U-T4W-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 391.2    | 0.0    | 391.2  |
|                    | % Fixture | 8.4      | 0.0    | 8.4    |
| <b>Street Side</b> | Lumens    | 4268.9   | 0.0    | 4268.9 |
|                    | % Fixture | 91.6     | 0.0    | 91.6   |
| <b>Total</b>       | Lumens    | 4660.1   | 0.0    | 4660.1 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 44.4   | 1.0       |
| 10°-20°   | 97.5   | 2.1       |
| 20°-30°   | 164.9  | 3.5       |
| 30°-40°   | 303.7  | 6.5       |
| 40°-50°   | 498.5  | 10.7      |
| 50°-60°   | 887.2  | 19.0      |
| 60°-70°   | 1327.5 | 28.5      |
| 70°-80°   | 1181.9 | 25.4      |
| 80°-90°   | 154.4  | 3.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4660.1 | 100.0     |
| 0°-180°   | 4660.1 | 100.0     |



REPORT NUMBER: P560614


CATALOG NUMBER: SDL-PA1-50-760-U-T4W-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 225.3  | 4.8       |                         |      |         |
| FM   | (30°-60°)   | 1498.0 | 32.1      |                         |      |         |
| FH   | (60°-80°)   | 2393.6 | 51.4      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 152.0  | 3.3       |                         |      | G2/225  |
| BL   | (0°-30°)    | 81.6   | 1.8       | B0/110                  |      |         |
| BM   | (30°-60°)   | 191.4  | 4.1       | B0/220                  |      |         |
| BH   | (60°-80°)   | 115.8  | 2.5       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 2.4    | 0.1       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type IV Medium





REPORT NUMBER: P560614

CATALOG NUMBER: SDL-PA1-50-760-U-T4W-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    | 50°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  |
| 2.5°  | 531.6  | 571.4  | 576.1  | 578.4  | 583.1  | 585.4  | 585.4  | 585.4  | 585.4  | 583.1  | 583.1  |
| 5°    | 562.0  | 559.7  | 557.3  | 555.0  | 552.7  | 548.0  | 543.3  | 536.3  | 531.6  | 526.9  | 522.2  |
| 7.5°  | 550.3  | 552.7  | 559.7  | 564.4  | 562.0  | 559.7  | 564.4  | 566.7  | 559.7  | 550.3  | 541.0  |
| 10°   | 641.7  | 637.0  | 632.3  | 627.6  | 620.6  | 613.5  | 557.3  | 501.1  | 496.5  | 489.4  | 484.8  |
| 12.5° | 562.0  | 632.3  | 632.3  | 632.3  | 632.3  | 632.3  | 594.8  | 557.3  | 498.8  | 440.3  | 372.3  |
| 15°   | 702.5  | 700.2  | 690.8  | 681.5  | 618.2  | 552.7  | 517.5  | 482.4  | 482.4  | 480.1  | 452.0  |
| 17.5° | 583.1  | 583.1  | 629.9  | 674.4  | 648.7  | 622.9  | 573.7  | 524.6  | 454.3  | 381.7  | 409.8  |
| 20°   | 737.7  | 737.7  | 728.3  | 718.9  | 611.2  | 503.5  | 508.2  | 512.9  | 517.5  | 522.2  | 433.2  |
| 22.5° | 606.5  | 601.8  | 597.2  | 592.5  | 604.2  | 615.9  | 519.9  | 421.5  | 477.7  | 531.6  | 414.5  |
| 25°   | 740.0  | 747.0  | 742.3  | 735.3  | 639.3  | 543.3  | 564.4  | 583.1  | 510.5  | 437.9  | 508.2  |
| 27.5° | 634.6  | 627.6  | 618.2  | 606.5  | 613.5  | 620.6  | 576.1  | 529.2  | 555.0  | 580.8  | 466.0  |
| 30°   | 777.5  | 779.8  | 775.1  | 770.4  | 679.1  | 587.8  | 585.4  | 580.8  | 559.7  | 536.3  | 524.6  |
| 32.5° | 962.5  | 943.7  | 878.2  | 812.6  | 756.4  | 700.2  | 655.7  | 611.2  | 629.9  | 646.3  | 583.1  |
| 35°   | 1051.5 | 1016.3 | 988.2  | 957.8  | 864.1  | 768.1  | 714.2  | 658.0  | 660.4  | 662.7  | 637.0  |
| 37.5° | 1138.1 | 1086.6 | 1051.5 | 1016.3 | 903.9  | 791.5  | 733.0  | 674.4  | 693.2  | 709.6  | 681.5  |
| 40°   | 1168.6 | 1140.5 | 1119.4 | 1098.3 | 978.9  | 857.1  | 789.2  | 718.9  | 728.3  | 735.3  | 726.0  |
| 42.5° | 1245.8 | 1241.1 | 1229.4 | 1215.4 | 1072.5 | 927.3  | 845.4  | 763.4  | 772.8  | 779.8  | 775.1  |
| 45°   | 1430.8 | 1423.8 | 1423.8 | 1421.5 | 1236.5 | 1049.1 | 941.4  | 833.7  | 843.0  | 852.4  | 847.7  |
| 47.5° | 1669.7 | 1658.0 | 1643.9 | 1627.5 | 1430.8 | 1231.8 | 1077.2 | 920.3  | 920.3  | 920.3  | 927.3  |
| 50°   | 1920.3 | 1903.9 | 1873.4 | 1840.6 | 1641.6 | 1442.5 | 1245.8 | 1049.1 | 1028.0 | 1004.6 | 1030.4 |
| 52.5° | 2180.2 | 2152.1 | 2100.6 | 2046.7 | 1871.1 | 1695.5 | 1473.0 | 1248.2 | 1184.9 | 1119.4 | 1152.2 |
| 55°   | 2320.7 | 2290.3 | 2255.1 | 2217.7 | 2074.8 | 1929.6 | 1702.5 | 1475.3 | 1377.0 | 1276.3 | 1311.4 |
| 57.5° | 2435.5 | 2428.4 | 2412.0 | 2395.6 | 2285.6 | 2175.5 | 1948.4 | 1718.9 | 1585.4 | 1451.9 | 1482.4 |
| 60°   | 2592.4 | 2583.0 | 2590.0 | 2597.0 | 2512.7 | 2428.4 | 2213.0 | 1995.2 | 1824.3 | 1651.0 | 1641.6 |
| 62.5° | 2709.4 | 2707.1 | 2742.2 | 2777.4 | 2732.9 | 2686.0 | 2444.8 | 2201.3 | 2035.0 | 1866.4 | 1819.6 |
| 65°   | 2601.7 | 2632.2 | 2763.3 | 2894.5 | 2887.4 | 2878.1 | 2653.2 | 2426.1 | 2262.2 | 2095.9 | 2035.0 |
| 67.5° | 2374.6 | 2388.6 | 2583.0 | 2775.0 | 2859.3 | 2941.3 | 2782.0 | 2620.5 | 2491.7 | 2360.5 | 2248.1 |
| 70°   | 2161.5 | 2191.9 | 2362.9 | 2533.8 | 2751.6 | 2969.4 | 2842.9 | 2716.5 | 2690.7 | 2662.6 | 2517.4 |
| 72.5° | 1955.4 | 2009.3 | 2168.5 | 2327.7 | 2618.1 | 2906.2 | 2831.2 | 2756.3 | 2857.0 | 2957.7 | 2784.4 |
| 75°   | 1250.5 | 1262.2 | 1564.3 | 1864.1 | 2231.7 | 2597.0 | 2693.1 | 2789.1 | 3011.5 | 3234.0 | 3035.0 |
| 77.5° | 365.3  | 405.1  | 632.3  | 859.4  | 1281.0 | 1700.1 | 2028.0 | 2355.8 | 2789.1 | 3222.3 | 2978.8 |
| 80°   | 124.1  | 133.5  | 166.3  | 196.7  | 421.5  | 646.3  | 1025.7 | 1402.7 | 1906.2 | 2409.7 | 2238.7 |
| 82.5° | 60.9   | 63.2   | 79.6   | 93.7   | 142.8  | 192.0  | 386.4  | 578.4  | 934.4  | 1288.0 | 1318.4 |
| 85°   | 18.7   | 18.7   | 28.1   | 37.5   | 60.9   | 84.3   | 145.2  | 203.7  | 323.2  | 440.3  | 372.3  |
| 87.5° | 4.7    | 4.7    | 7.0    | 9.4    | 14.1   | 18.7   | 18.7   | 18.7   | 14.1   | 9.4    | 11.7   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P560614

CATALOG NUMBER: SDL-PA1-50-760-U-T4W-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°  | 105°  |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|-------|
| 0°    | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4  | 571.4 | 571.4 |
| 2.5°  | 585.4  | 585.4  | 585.4  | 583.1  | 578.4  | 576.1  | 571.4  | 566.7  | 562.0  | 559.7 | 555.0 |
| 5°    | 515.2  | 545.6  | 573.7  | 576.1  | 576.1  | 569.1  | 562.0  | 555.0  | 548.0  | 541.0 | 533.9 |
| 7.5°  | 529.2  | 512.9  | 496.5  | 498.8  | 501.1  | 498.8  | 494.1  | 482.4  | 473.0  | 454.3 | 433.2 |
| 10°   | 423.9  | 412.2  | 398.1  | 402.8  | 407.5  | 419.2  | 430.9  | 421.5  | 407.5  | 372.3 | 334.9 |
| 12.5° | 416.8  | 414.5  | 409.8  | 374.7  | 337.2  | 356.0  | 372.3  | 363.0  | 348.9  | 313.8 | 276.3 |
| 15°   | 356.0  | 358.3  | 358.3  | 393.4  | 428.5  | 442.6  | 454.3  | 442.6  | 426.2  | 379.4 | 330.2 |
| 17.5° | 459.0  | 435.6  | 412.2  | 398.1  | 381.7  | 386.4  | 391.1  | 339.6  | 356.0  | 325.5 | 292.7 |
| 20°   | 475.4  | 398.1  | 320.8  | 384.1  | 447.3  | 468.4  | 489.4  | 477.7  | 456.6  | 381.7 | 304.4 |
| 22.5° | 433.2  | 461.3  | 489.4  | 449.6  | 409.8  | 384.1  | 356.0  | 344.2  | 330.2  | 297.4 | 264.6 |
| 25°   | 536.3  | 459.0  | 379.4  | 454.3  | 526.9  | 531.6  | 536.3  | 515.2  | 491.8  | 398.1 | 304.4 |
| 27.5° | 480.1  | 505.8  | 529.2  | 545.6  | 562.0  | 583.1  | 604.2  | 580.8  | 524.6  | 414.5 | 302.1 |
| 30°   | 571.4  | 606.5  | 641.7  | 695.5  | 749.4  | 765.8  | 779.8  | 754.1  | 709.6  | 524.6 | 337.2 |
| 32.5° | 597.2  | 667.4  | 737.7  | 758.7  | 777.5  | 798.5  | 819.6  | 798.5  | 744.7  | 519.9 | 292.7 |
| 35°   | 667.4  | 716.6  | 763.4  | 796.2  | 829.0  | 847.7  | 866.5  | 852.4  | 779.8  | 512.9 | 245.9 |
| 37.5° | 688.5  | 754.1  | 817.3  | 854.8  | 889.9  | 906.3  | 920.3  | 920.3  | 817.3  | 508.2 | 196.7 |
| 40°   | 721.3  | 803.2  | 885.2  | 920.3  | 953.1  | 978.9  | 1002.3 | 1011.7 | 859.4  | 505.8 | 149.9 |
| 42.5° | 786.8  | 859.4  | 932.0  | 988.2  | 1042.1 | 1079.6 | 1117.0 | 1124.1 | 908.6  | 512.9 | 114.7 |
| 45°   | 857.1  | 934.4  | 1011.7 | 1086.6 | 1161.5 | 1215.4 | 1266.9 | 1262.2 | 967.2  | 531.6 | 93.7  |
| 47.5° | 957.8  | 1030.4 | 1103.0 | 1229.4 | 1353.6 | 1405.1 | 1454.3 | 1421.5 | 1028.0 | 555.0 | 82.0  |
| 50°   | 1060.8 | 1149.8 | 1238.8 | 1400.4 | 1559.6 | 1606.5 | 1651.0 | 1583.0 | 1086.6 | 583.1 | 77.3  |
| 52.5° | 1194.3 | 1299.7 | 1405.1 | 1590.1 | 1775.1 | 1817.2 | 1859.4 | 1721.2 | 1131.1 | 601.8 | 72.6  |
| 55°   | 1351.2 | 1487.0 | 1622.9 | 1798.5 | 1971.8 | 2021.0 | 2070.1 | 1857.0 | 1152.2 | 611.2 | 70.3  |
| 57.5° | 1540.9 | 1697.8 | 1852.4 | 2013.9 | 2173.2 | 2241.1 | 2306.7 | 1990.5 | 1161.5 | 613.5 | 65.6  |
| 60°   | 1725.9 | 1899.2 | 2072.5 | 2210.6 | 2348.8 | 2454.2 | 2557.2 | 2121.7 | 1156.8 | 608.9 | 58.5  |
| 62.5° | 1896.8 | 2088.9 | 2278.6 | 2407.4 | 2536.2 | 2662.6 | 2789.1 | 2227.0 | 1126.4 | 587.8 | 46.8  |
| 65°   | 2074.8 | 2278.6 | 2480.0 | 2592.4 | 2704.8 | 2868.7 | 3030.3 | 2318.4 | 1084.2 | 559.7 | 32.8  |
| 67.5° | 2236.4 | 2430.8 | 2625.1 | 2751.6 | 2878.1 | 3039.6 | 3198.9 | 2341.8 | 1023.4 | 524.6 | 23.4  |
| 70°   | 2372.2 | 2583.0 | 2791.4 | 2920.2 | 3049.0 | 3131.0 | 3210.6 | 2238.7 | 901.6  | 459.0 | 16.4  |
| 72.5° | 2559.6 | 2749.3 | 2936.6 | 3002.2 | 3065.4 | 2922.6 | 2777.4 | 1866.4 | 676.8  | 346.6 | 14.1  |
| 75°   | 2728.2 | 2819.5 | 2908.5 | 2768.0 | 2627.5 | 2243.4 | 1859.4 | 1175.6 | 330.2  | 173.3 | 14.1  |
| 77.5° | 2557.2 | 2508.1 | 2458.9 | 2028.0 | 1594.8 | 1184.9 | 772.8  | 461.3  | 103.0  | 56.2  | 9.4   |
| 80°   | 1852.4 | 1627.5 | 1400.4 | 969.5  | 536.3  | 358.3  | 178.0  | 103.0  | 25.8   | 16.4  | 7.0   |
| 82.5° | 997.6  | 770.4  | 541.0  | 348.9  | 156.9  | 105.4  | 51.5   | 35.1   | 11.7   | 9.4   | 4.7   |
| 85°   | 360.6  | 285.7  | 208.4  | 161.6  | 114.7  | 67.9   | 18.7   | 11.7   | 7.0    | 7.0   | 4.7   |
| 87.5° | 32.8   | 37.5   | 42.2   | 32.8   | 21.1   | 14.1   | 4.7    | 4.7    | 4.7    | 4.7   | 2.3   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |





REPORT NUMBER: P560614

CATALOG NUMBER: SDL-PA1-50-760-U-T4W-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 110°  | 115°  | 120°  | 125°  | 130°  | 135°  | 140°  | 145°  | 150°  | 155°  | 160°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 571.4 | 571.4 | 571.4 | 571.4 | 571.4 | 571.4 | 571.4 | 571.4 | 571.4 | 571.4 | 571.4 |
| 2.5°  | 552.7 | 550.3 | 548.0 | 543.3 | 541.0 | 538.6 | 522.2 | 505.8 | 487.1 | 468.4 | 468.4 |
| 5°    | 503.5 | 473.0 | 456.6 | 440.3 | 428.5 | 416.8 | 414.5 | 409.8 | 405.1 | 400.4 | 398.1 |
| 7.5°  | 421.5 | 409.8 | 400.4 | 391.1 | 379.4 | 367.7 | 356.0 | 344.2 | 334.9 | 325.5 | 304.4 |
| 10°   | 316.1 | 297.4 | 283.4 | 269.3 | 262.3 | 252.9 | 238.9 | 222.5 | 222.5 | 222.5 | 220.1 |
| 12.5° | 274.0 | 271.6 | 236.5 | 199.1 | 187.3 | 175.6 | 173.3 | 171.0 | 166.3 | 159.2 | 149.9 |
| 15°   | 271.6 | 210.8 | 180.3 | 147.5 | 140.5 | 131.1 | 117.1 | 100.7 | 98.4  | 93.7  | 105.4 |
| 17.5° | 245.9 | 199.1 | 163.9 | 128.8 | 103.0 | 77.3  | 82.0  | 84.3  | 96.0  | 105.4 | 112.4 |
| 20°   | 222.5 | 140.5 | 117.1 | 91.3  | 84.3  | 74.9  | 79.6  | 84.3  | 82.0  | 77.3  | 89.0  |
| 22.5° | 208.4 | 149.9 | 110.1 | 70.3  | 74.9  | 79.6  | 74.9  | 67.9  | 79.6  | 91.3  | 98.4  |
| 25°   | 201.4 | 96.0  | 86.6  | 74.9  | 70.3  | 65.6  | 74.9  | 82.0  | 77.3  | 72.6  | 86.6  |
| 27.5° | 199.1 | 96.0  | 82.0  | 65.6  | 70.3  | 74.9  | 72.6  | 67.9  | 77.3  | 84.3  | 82.0  |
| 30°   | 213.1 | 86.6  | 77.3  | 67.9  | 65.6  | 63.2  | 67.9  | 72.6  | 72.6  | 70.3  | 82.0  |
| 32.5° | 189.7 | 86.6  | 77.3  | 65.6  | 65.6  | 63.2  | 63.2  | 63.2  | 70.3  | 77.3  | 82.0  |
| 35°   | 163.9 | 79.6  | 72.6  | 63.2  | 60.9  | 58.5  | 60.9  | 60.9  | 67.9  | 72.6  | 82.0  |
| 37.5° | 135.8 | 74.9  | 67.9  | 58.5  | 56.2  | 53.9  | 53.9  | 51.5  | 58.5  | 65.6  | 72.6  |
| 40°   | 110.1 | 70.3  | 63.2  | 53.9  | 51.5  | 49.2  | 49.2  | 49.2  | 53.9  | 56.2  | 60.9  |
| 42.5° | 91.3  | 65.6  | 58.5  | 49.2  | 46.8  | 44.5  | 44.5  | 42.2  | 44.5  | 46.8  | 49.2  |
| 45°   | 79.6  | 63.2  | 56.2  | 46.8  | 44.5  | 39.8  | 37.5  | 35.1  | 35.1  | 35.1  | 35.1  |
| 47.5° | 70.3  | 58.5  | 53.9  | 46.8  | 42.2  | 35.1  | 32.8  | 28.1  | 25.8  | 23.4  | 21.1  |
| 50°   | 65.6  | 53.9  | 49.2  | 42.2  | 37.5  | 30.4  | 25.8  | 21.1  | 18.7  | 14.1  | 14.1  |
| 52.5° | 60.9  | 49.2  | 44.5  | 37.5  | 30.4  | 23.4  | 18.7  | 11.7  | 11.7  | 9.4   | 9.4   |
| 55°   | 58.5  | 46.8  | 39.8  | 32.8  | 25.8  | 16.4  | 11.7  | 7.0   | 7.0   | 4.7   | 4.7   |
| 57.5° | 56.2  | 44.5  | 37.5  | 28.1  | 18.7  | 9.4   | 7.0   | 4.7   | 4.7   | 4.7   | 4.7   |
| 60°   | 49.2  | 39.8  | 30.4  | 18.7  | 11.7  | 4.7   | 4.7   | 2.3   | 4.7   | 4.7   | 4.7   |
| 62.5° | 39.8  | 30.4  | 21.1  | 11.7  | 7.0   | 2.3   | 2.3   | 2.3   | 4.7   | 4.7   | 4.7   |
| 65°   | 28.1  | 21.1  | 14.1  | 7.0   | 4.7   | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   |
| 67.5° | 21.1  | 16.4  | 11.7  | 4.7   | 4.7   | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   |
| 70°   | 14.1  | 11.7  | 9.4   | 4.7   | 4.7   | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   |
| 72.5° | 11.7  | 9.4   | 7.0   | 2.3   | 2.3   | 0.0   | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   |
| 75°   | 11.7  | 9.4   | 7.0   | 2.3   | 2.3   | 0.0   | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   |
| 77.5° | 9.4   | 7.0   | 4.7   | 2.3   | 2.3   | 0.0   | 2.3   | 4.7   | 4.7   | 4.7   | 4.7   |
| 80°   | 7.0   | 4.7   | 4.7   | 2.3   | 2.3   | 0.0   | 2.3   | 4.7   | 4.7   | 4.7   | 4.7   |
| 82.5° | 4.7   | 4.7   | 4.7   | 2.3   | 2.3   | 0.0   | 4.7   | 7.0   | 7.0   | 4.7   | 4.7   |
| 85°   | 4.7   | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   | 4.7   | 7.0   | 7.0   | 7.0   | 4.7   |
| 87.5° | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   | 2.3   | 4.7   | 7.0   | 7.0   | 7.0   | 4.7   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

REPORT NUMBER: P560614

CATALOG NUMBER: SDL-PA1-50-760-U-T4W-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 165°  | 170°  | 175°  | 180°  |
|-------|-------|-------|-------|-------|
| 0°    | 571.4 | 571.4 | 571.4 | 571.4 |
| 2.5°  | 466.0 | 466.0 | 463.7 | 463.7 |
| 5°    | 393.4 | 393.4 | 391.1 | 391.1 |
| 7.5°  | 283.4 | 278.7 | 271.6 | 274.0 |
| 10°   | 217.8 | 213.1 | 208.4 | 213.1 |
| 12.5° | 140.5 | 142.8 | 142.8 | 135.8 |
| 15°   | 114.7 | 124.1 | 131.1 | 131.1 |
| 17.5° | 119.4 | 119.4 | 117.1 | 117.1 |
| 20°   | 100.7 | 110.1 | 119.4 | 119.4 |
| 22.5° | 103.0 | 98.4  | 93.7  | 93.7  |
| 25°   | 98.4  | 105.4 | 110.1 | 110.1 |
| 27.5° | 79.6  | 82.0  | 84.3  | 84.3  |
| 30°   | 91.3  | 96.0  | 98.4  | 98.4  |
| 32.5° | 86.6  | 91.3  | 93.7  | 96.0  |
| 35°   | 89.0  | 93.7  | 96.0  | 96.0  |
| 37.5° | 79.6  | 82.0  | 84.3  | 84.3  |
| 40°   | 63.2  | 65.6  | 67.9  | 67.9  |
| 42.5° | 49.2  | 49.2  | 46.8  | 49.2  |
| 45°   | 32.8  | 32.8  | 30.4  | 32.8  |
| 47.5° | 18.7  | 18.7  | 18.7  | 18.7  |
| 50°   | 11.7  | 11.7  | 11.7  | 11.7  |
| 52.5° | 7.0   | 7.0   | 7.0   | 7.0   |
| 55°   | 4.7   | 4.7   | 4.7   | 4.7   |
| 57.5° | 4.7   | 4.7   | 2.3   | 2.3   |
| 60°   | 2.3   | 2.3   | 2.3   | 2.3   |
| 62.5° | 2.3   | 2.3   | 0.0   | 0.0   |
| 65°   | 0.0   | 0.0   | 0.0   | 0.0   |
| 67.5° | 0.0   | 0.0   | 0.0   | 0.0   |
| 70°   | 0.0   | 0.0   | 0.0   | 0.0   |
| 72.5° | 0.0   | 0.0   | 0.0   | 0.0   |
| 75°   | 2.3   | 2.3   | 0.0   | 0.0   |
| 77.5° | 2.3   | 2.3   | 0.0   | 0.0   |
| 80°   | 2.3   | 2.3   | 0.0   | 0.0   |
| 82.5° | 2.3   | 2.3   | 0.0   | 0.0   |
| 85°   | 2.3   | 2.3   | 2.3   | 0.0   |
| 87.5° | 2.3   | 2.3   | 2.3   | 0.0   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   |



Report Generated By 670245982









--- HS --- SS



u











(END OF REPORT)