

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P561303

Luminaire Tested: **SDL-PA1-90-760-U-SL3**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P561303  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-90-760-U-SL3  
Description: Springdale  
(1) 70 CRI, 5700K, 1180mA LIGHT ENGINE WITH 24 LEDS AND TYPE III SPILL  
LIGHT ELIMINATOR OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10170.7 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type III - Medium  
BUG Rating: B2 - U0 - G3

Input Watts (W): 92.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P561303

CATALOG NUMBER: SDL-PA1-90-760-U-SL3

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 7.3 fc

Type III - Medium - N/A

REPORT NUMBER: P561303

CATALOG NUMBER: SDL-PA1-90-760-U-SL3

## Luminous Intensity Polar Plot



— Vertical Plane Through 60-Deg Lateral      - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P561303

CATALOG NUMBER: SDL-PA1-90-760-U-SL3


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 1634.8   | 0.0    | 1634.8  |
|                    | % Fixture | 16.1     | 0.0    | 16.1    |
| <b>Street Side</b> | Lumens    | 8535.9   | 0.0    | 8535.9  |
|                    | % Fixture | 83.9     | 0.0    | 83.9    |
| <b>Total</b>       | Lumens    | 10170.7  | 0.0    | 10170.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 211.6   | 2.1       |
| 10°-20°   | 381.8   | 3.8       |
| 20°-30°   | 500.2   | 4.9       |
| 30°-40°   | 825.4   | 8.1       |
| 40°-50°   | 1288.9  | 12.7      |
| 50°-60°   | 1962.3  | 19.3      |
| 60°-70°   | 2431.4  | 23.9      |
| 70°-80°   | 2148.0  | 21.1      |
| 80°-90°   | 421.1   | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 10170.7 | 100.0     |
| 0°-180°   | 10170.7 | 100.0     |



REPORT NUMBER: P561303


CATALOG NUMBER: SDL-PA1-90-760-U-SL3

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 667.7  | 6.6       |                         |      |         |
| FM   | (30°-60°)   | 3490.9 | 34.3      |                         |      |         |
| FH   | (60°-80°)   | 3996.4 | 39.3      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 380.9  | 3.7       |                         |      | G3/500  |
| BL   | (0°-30°)    | 425.9  | 4.2       | B1/500                  |      |         |
| BM   | (30°-60°)   | 585.7  | 5.8       | B1/1000                 |      |         |
| BH   | (60°-80°)   | 583.0  | 5.7       | B2/1000                 |      | G2/1000 |
| BVH  | (80°-90°)   | 40.1   | 0.4       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G3**

Type III Medium





REPORT NUMBER: P561303

CATALOG NUMBER: SDL-PA1-90-760-U-SL3

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    | 50°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 |
| 2.5°  | 2409.5 | 2681.4 | 2618.1 | 2554.7 | 2651.6 | 2744.7 | 2774.5 | 2800.5 | 2815.4 | 2830.3 | 2845.2 |
| 5°    | 2238.2 | 2241.9 | 2245.6 | 2249.4 | 2260.5 | 2268.0 | 2282.9 | 2297.8 | 2312.7 | 2323.8 | 2338.7 |
| 7.5°  | 1728.0 | 1787.6 | 1884.4 | 1981.2 | 2040.8 | 2096.7 | 2130.2 | 2160.0 | 2182.3 | 2204.7 | 2227.0 |
| 10°   | 1921.6 | 1932.8 | 1936.5 | 1936.5 | 1955.2 | 1973.8 | 1832.3 | 1687.0 | 1757.8 | 1828.5 | 1750.3 |
| 12.5° | 1508.3 | 1549.2 | 1672.1 | 1791.3 | 1828.5 | 1862.1 | 1795.0 | 1728.0 | 1623.7 | 1515.7 | 1508.3 |
| 15°   | 1731.7 | 1742.9 | 1746.6 | 1746.6 | 1631.2 | 1515.7 | 1437.5 | 1355.6 | 1418.9 | 1478.5 | 1340.7 |
| 17.5° | 1340.7 | 1351.9 | 1448.7 | 1545.5 | 1564.1 | 1582.7 | 1500.8 | 1418.9 | 1236.4 | 1050.2 | 1225.2 |
| 20°   | 1593.9 | 1601.4 | 1601.4 | 1601.4 | 1407.7 | 1214.1 | 1229.0 | 1240.1 | 1299.7 | 1359.3 | 1310.9 |
| 22.5° | 1284.8 | 1284.8 | 1284.8 | 1284.8 | 1344.4 | 1400.3 | 1281.1 | 1161.9 | 1229.0 | 1296.0 | 1236.4 |
| 25°   | 1616.3 | 1627.4 | 1601.4 | 1571.6 | 1392.8 | 1214.1 | 1269.9 | 1325.8 | 1225.2 | 1124.7 | 1214.1 |
| 27.5° | 1474.7 | 1463.6 | 1411.4 | 1355.6 | 1381.6 | 1407.7 | 1284.8 | 1161.9 | 1240.1 | 1318.3 | 1281.1 |
| 30°   | 1958.9 | 1925.4 | 1869.5 | 1813.6 | 1601.4 | 1389.1 | 1355.6 | 1322.1 | 1255.0 | 1184.3 | 1262.5 |
| 32.5° | 2603.2 | 2517.5 | 2256.8 | 1996.1 | 1865.8 | 1735.4 | 1567.9 | 1400.3 | 1385.4 | 1366.7 | 1389.1 |
| 35°   | 2774.5 | 2718.6 | 2610.6 | 2498.9 | 2275.4 | 2048.3 | 1836.0 | 1620.0 | 1549.2 | 1474.7 | 1489.6 |
| 37.5° | 2808.0 | 2789.4 | 2767.0 | 2740.9 | 2513.8 | 2286.6 | 2055.7 | 1824.8 | 1750.3 | 1672.1 | 1616.3 |
| 40°   | 2834.0 | 2848.9 | 2889.9 | 2927.2 | 2700.0 | 2469.1 | 2260.5 | 2048.3 | 1970.1 | 1888.1 | 1791.3 |
| 42.5° | 2953.2 | 2994.2 | 3046.3 | 3094.7 | 2886.2 | 2677.6 | 2495.2 | 2312.7 | 2212.1 | 2111.6 | 2022.2 |
| 45°   | 3228.8 | 3251.2 | 3307.0 | 3359.1 | 3161.8 | 2960.7 | 2752.1 | 2539.8 | 2454.2 | 2368.5 | 2279.2 |
| 47.5° | 3631.0 | 3668.3 | 3664.5 | 3660.8 | 3441.1 | 3217.6 | 2983.0 | 2744.7 | 2688.8 | 2629.2 | 2543.6 |
| 50°   | 4137.5 | 4111.4 | 4040.7 | 3969.9 | 3731.6 | 3489.5 | 3213.9 | 2934.6 | 2908.5 | 2878.7 | 2808.0 |
| 52.5° | 4390.7 | 4372.1 | 4275.3 | 4174.7 | 3932.7 | 3690.6 | 3392.7 | 3091.0 | 3124.5 | 3158.0 | 3091.0 |
| 55°   | 4405.6 | 4394.5 | 4323.7 | 4252.9 | 4018.3 | 3783.7 | 3519.3 | 3254.9 | 3336.8 | 3418.7 | 3392.7 |
| 57.5° | 4297.6 | 4301.3 | 4279.0 | 4252.9 | 4044.4 | 3835.8 | 3616.1 | 3396.4 | 3537.9 | 3675.7 | 3701.8 |
| 60°   | 4022.0 | 4077.9 | 4115.1 | 4152.4 | 4022.0 | 3891.7 | 3701.8 | 3511.8 | 3727.8 | 3943.8 | 4014.6 |
| 62.5° | 3511.8 | 3560.3 | 3694.3 | 3824.7 | 3850.7 | 3873.1 | 3746.5 | 3616.1 | 3906.6 | 4193.4 | 4308.8 |
| 65°   | 2722.3 | 2789.4 | 2990.5 | 3191.6 | 3400.1 | 3608.7 | 3638.5 | 3668.3 | 4159.8 | 4651.4 | 4748.2 |
| 67.5° | 1698.2 | 1735.4 | 1947.7 | 2156.3 | 2577.1 | 2994.2 | 3232.5 | 3470.9 | 4320.0 | 5165.3 | 5318.0 |
| 70°   | 897.5  | 953.4  | 1057.6 | 1158.2 | 1519.4 | 1880.7 | 2364.8 | 2848.9 | 4077.9 | 5306.9 | 5932.5 |
| 72.5° | 681.5  | 703.9  | 759.7  | 815.6  | 942.2  | 1068.8 | 1374.2 | 1679.6 | 3191.6 | 4699.8 | 6141.1 |
| 75°   | 491.6  | 510.2  | 569.8  | 625.7  | 752.3  | 875.2  | 1001.8 | 1124.7 | 1970.1 | 2815.4 | 5090.9 |
| 77.5° | 286.8  | 294.2  | 324.0  | 350.1  | 547.4  | 744.8  | 882.6  | 1016.7 | 1221.5 | 1422.6 | 3634.7 |
| 80°   | 197.4  | 201.1  | 212.3  | 223.4  | 309.1  | 394.8  | 659.2  | 923.6  | 1016.7 | 1106.1 | 2409.5 |
| 82.5° | 130.3  | 149.0  | 156.4  | 163.9  | 193.7  | 223.4  | 387.3  | 547.4  | 804.4  | 1057.6 | 1646.1 |
| 85°   | 67.0   | 74.5   | 89.4   | 100.6  | 115.4  | 126.6  | 175.0  | 219.7  | 666.6  | 1109.8 | 1184.3 |
| 87.5° | 7.4    | 11.2   | 14.9   | 14.9   | 18.6   | 22.3   | 33.5   | 44.7   | 201.1  | 357.5  | 305.4  |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P561303

CATALOG NUMBER: SDL-PA1-90-760-U-SL3

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   | 105°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 |
| 2.5°  | 2860.1 | 2867.6 | 2863.8 | 2871.3 | 2875.0 | 2878.7 | 2882.5 | 2882.5 | 2878.7 | 2871.3 | 2863.8 |
| 5°    | 2353.6 | 2502.6 | 2755.8 | 2781.9 | 2808.0 | 2815.4 | 2822.9 | 2826.6 | 2819.2 | 2808.0 | 2796.8 |
| 7.5°  | 2245.6 | 2268.0 | 2040.8 | 2223.3 | 2402.1 | 2416.9 | 2428.1 | 2420.7 | 2424.4 | 2323.8 | 2219.6 |
| 10°   | 1672.1 | 1690.7 | 1698.2 | 1754.1 | 1806.2 | 1929.1 | 2052.0 | 2033.4 | 2018.5 | 1839.7 | 1657.2 |
| 12.5° | 1500.8 | 1597.6 | 1620.0 | 1526.9 | 1433.8 | 1560.4 | 1687.0 | 1672.1 | 1646.1 | 1482.2 | 1318.3 |
| 15°   | 1202.9 | 1102.3 | 1318.3 | 1519.4 | 1716.8 | 1836.0 | 1951.4 | 1917.9 | 1888.1 | 1679.6 | 1467.3 |
| 17.5° | 1396.5 | 1456.1 | 1385.4 | 1415.2 | 1445.0 | 1534.3 | 1620.0 | 1567.9 | 1549.2 | 1404.0 | 1255.0 |
| 20°   | 1262.5 | 1258.7 | 1210.3 | 1385.4 | 1560.4 | 1735.4 | 1906.7 | 1854.6 | 1765.2 | 1482.2 | 1195.4 |
| 22.5° | 1176.8 | 1418.9 | 1523.2 | 1500.8 | 1474.7 | 1407.7 | 1337.0 | 1292.3 | 1225.2 | 1161.9 | 1094.9 |
| 25°   | 1299.7 | 1199.2 | 1281.1 | 1549.2 | 1813.6 | 1862.1 | 1910.5 | 1798.7 | 1653.5 | 1366.7 | 1080.0 |
| 27.5° | 1243.9 | 1400.3 | 1504.5 | 1683.3 | 1858.3 | 2025.9 | 2193.5 | 2044.5 | 1854.6 | 1497.1 | 1135.9 |
| 30°   | 1340.7 | 1426.3 | 1716.8 | 2052.0 | 2387.2 | 2446.7 | 2502.6 | 2297.8 | 2044.5 | 1683.3 | 1322.1 |
| 32.5° | 1411.4 | 1638.6 | 1895.6 | 2156.3 | 2413.2 | 2457.9 | 2502.6 | 2271.7 | 1981.2 | 1582.7 | 1184.3 |
| 35°   | 1500.8 | 1668.4 | 1903.0 | 2208.4 | 2513.8 | 2524.9 | 2532.4 | 2264.3 | 1936.5 | 1485.9 | 1031.6 |
| 37.5° | 1560.4 | 1750.3 | 2003.6 | 2327.6 | 2651.6 | 2629.2 | 2603.2 | 2297.8 | 1921.6 | 1418.9 | 916.1  |
| 40°   | 1694.5 | 1858.3 | 2130.2 | 2461.6 | 2793.1 | 2755.8 | 2718.6 | 2368.5 | 1925.4 | 1351.9 | 774.6  |
| 42.5° | 1929.1 | 1992.4 | 2286.6 | 2640.4 | 2994.2 | 2953.2 | 2908.5 | 2491.4 | 1970.1 | 1314.6 | 655.4  |
| 45°   | 2186.1 | 2215.8 | 2469.1 | 2871.3 | 3273.5 | 3221.4 | 3169.2 | 2681.4 | 2052.0 | 1296.0 | 540.0  |
| 47.5° | 2454.2 | 2446.7 | 2681.4 | 3169.2 | 3653.4 | 3541.6 | 3429.9 | 2904.8 | 2204.7 | 1333.2 | 461.8  |
| 50°   | 2733.5 | 2722.3 | 2949.5 | 3474.6 | 3999.7 | 3880.5 | 3761.4 | 3172.9 | 2379.7 | 1400.3 | 417.1  |
| 52.5° | 3020.3 | 3046.3 | 3213.9 | 3761.4 | 4305.1 | 4197.1 | 4085.4 | 3463.4 | 2551.0 | 1474.7 | 398.5  |
| 55°   | 3362.9 | 3444.8 | 3511.8 | 4059.3 | 4606.7 | 4498.7 | 4387.0 | 3761.4 | 2789.4 | 1590.2 | 391.0  |
| 57.5° | 3724.1 | 3832.1 | 3861.9 | 4360.9 | 4860.0 | 4789.2 | 4714.7 | 4044.4 | 3031.4 | 1724.3 | 413.4  |
| 60°   | 4085.4 | 4226.9 | 4334.9 | 4737.1 | 5135.6 | 5053.6 | 4971.7 | 4331.1 | 3258.6 | 1873.2 | 487.9  |
| 62.5° | 4420.5 | 4617.9 | 4792.9 | 5087.1 | 5377.6 | 5280.8 | 5184.0 | 4580.7 | 3515.6 | 2078.1 | 636.8  |
| 65°   | 4841.3 | 5016.4 | 5206.3 | 5400.0 | 5589.9 | 5496.8 | 5403.7 | 4893.5 | 3858.2 | 2335.0 | 808.1  |
| 67.5° | 5470.7 | 5522.9 | 5619.7 | 5738.9 | 5854.3 | 5798.4 | 5738.9 | 5277.1 | 4156.1 | 2484.0 | 808.1  |
| 70°   | 6554.4 | 6439.0 | 6293.7 | 6290.0 | 6282.6 | 6193.2 | 6100.1 | 5493.1 | 4174.7 | 2424.4 | 674.1  |
| 72.5° | 7578.6 | 7973.3 | 7511.5 | 7176.4 | 6841.2 | 6446.4 | 6048.0 | 5202.6 | 3686.9 | 2111.6 | 536.3  |
| 75°   | 7362.6 | 8896.9 | 8673.5 | 7764.8 | 6856.1 | 6141.1 | 5426.0 | 4532.2 | 3035.2 | 1746.6 | 458.1  |
| 77.5° | 5843.1 | 7850.4 | 8062.7 | 7228.5 | 6390.6 | 5422.3 | 4450.3 | 3504.4 | 2104.1 | 1243.9 | 383.6  |
| 80°   | 3709.2 | 5869.2 | 5906.4 | 5131.8 | 4353.5 | 3314.5 | 2275.4 | 1526.9 | 1013.0 | 659.2  | 305.4  |
| 82.5° | 2234.5 | 3474.6 | 3024.0 | 2167.4 | 1310.9 | 908.7  | 502.8  | 484.1  | 372.4  | 275.6  | 178.8  |
| 85°   | 1258.7 | 1701.9 | 1221.5 | 800.7  | 379.9  | 271.9  | 160.1  | 171.3  | 163.9  | 134.1  | 100.6  |
| 87.5° | 249.5  | 294.2  | 201.1  | 115.4  | 29.8   | 29.8   | 26.1   | 26.1   | 18.6   | 18.6   | 14.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P561303

CATALOG NUMBER: SDL-PA1-90-760-U-SL3

**CANDELA DISTRIBUTION (continued):**

|       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   | 160°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 | 2901.1 |
| 2.5°  | 2863.8 | 2863.8 | 2856.4 | 2848.9 | 2845.2 | 2841.5 | 2729.8 | 2618.1 | 2543.6 | 2465.4 | 2446.7 |
| 5°    | 2659.0 | 2521.2 | 2416.9 | 2312.7 | 2290.3 | 2268.0 | 2264.3 | 2260.5 | 2249.4 | 2234.5 | 2230.7 |
| 7.5°  | 2100.4 | 1977.5 | 2063.2 | 2145.1 | 2130.2 | 2111.6 | 2100.4 | 2085.5 | 2059.4 | 2033.4 | 1903.0 |
| 10°   | 1616.3 | 1575.3 | 1575.3 | 1571.6 | 1541.8 | 1512.0 | 1579.0 | 1646.1 | 1720.5 | 1795.0 | 1787.6 |
| 12.5° | 1377.9 | 1433.8 | 1288.5 | 1139.6 | 1221.5 | 1299.7 | 1374.2 | 1445.0 | 1482.2 | 1519.4 | 1404.0 |
| 15°   | 1299.7 | 1128.4 | 1080.0 | 1031.6 | 1068.8 | 1106.1 | 998.1  | 886.3  | 972.0  | 1057.6 | 1076.3 |
| 17.5° | 1165.6 | 1076.3 | 1027.9 | 975.7  | 834.2  | 689.0  | 737.4  | 785.8  | 782.1  | 778.3  | 759.7  |
| 20°   | 1087.4 | 975.7  | 890.1  | 800.7  | 733.7  | 666.6  | 595.9  | 521.4  | 487.9  | 450.6  | 540.0  |
| 22.5° | 1035.3 | 975.7  | 797.0  | 618.2  | 566.1  | 513.9  | 458.1  | 398.5  | 420.8  | 439.4  | 454.3  |
| 25°   | 905.0  | 726.2  | 625.7  | 525.1  | 443.2  | 357.5  | 361.2  | 365.0  | 346.3  | 327.7  | 413.4  |
| 27.5° | 916.1  | 692.7  | 536.3  | 379.9  | 350.1  | 316.5  | 297.9  | 275.6  | 305.4  | 331.4  | 338.9  |
| 30°   | 960.8  | 599.6  | 454.3  | 309.1  | 275.6  | 242.1  | 253.2  | 260.7  | 260.7  | 260.7  | 297.9  |
| 32.5° | 852.8  | 521.4  | 387.3  | 249.5  | 230.9  | 208.6  | 212.3  | 212.3  | 230.9  | 249.5  | 268.1  |
| 35°   | 722.5  | 409.7  | 316.5  | 219.7  | 201.1  | 182.5  | 189.9  | 197.4  | 216.0  | 234.6  | 260.7  |
| 37.5° | 621.9  | 324.0  | 260.7  | 197.4  | 186.2  | 175.0  | 178.8  | 182.5  | 201.1  | 216.0  | 238.3  |
| 40°   | 525.1  | 271.9  | 230.9  | 189.9  | 178.8  | 167.6  | 171.3  | 171.3  | 186.2  | 201.1  | 216.0  |
| 42.5° | 454.3  | 249.5  | 219.7  | 186.2  | 175.0  | 160.1  | 163.9  | 163.9  | 175.0  | 186.2  | 197.4  |
| 45°   | 391.0  | 238.3  | 212.3  | 182.5  | 171.3  | 156.4  | 156.4  | 152.7  | 163.9  | 171.3  | 178.8  |
| 47.5° | 350.1  | 234.6  | 208.6  | 182.5  | 167.6  | 149.0  | 145.2  | 141.5  | 152.7  | 160.1  | 171.3  |
| 50°   | 327.7  | 234.6  | 208.6  | 178.8  | 160.1  | 141.5  | 137.8  | 134.1  | 149.0  | 160.1  | 178.8  |
| 52.5° | 320.3  | 238.3  | 208.6  | 178.8  | 156.4  | 134.1  | 134.1  | 134.1  | 160.1  | 186.2  | 193.7  |
| 55°   | 320.3  | 245.8  | 212.3  | 175.0  | 152.7  | 130.3  | 137.8  | 145.2  | 152.7  | 160.1  | 160.1  |
| 57.5° | 327.7  | 242.1  | 204.8  | 167.6  | 152.7  | 134.1  | 130.3  | 126.6  | 130.3  | 134.1  | 134.1  |
| 60°   | 361.2  | 234.6  | 197.4  | 160.1  | 141.5  | 122.9  | 119.2  | 115.4  | 122.9  | 126.6  | 126.6  |
| 62.5° | 435.7  | 230.9  | 197.4  | 160.1  | 137.8  | 115.4  | 115.4  | 111.7  | 115.4  | 119.2  | 122.9  |
| 65°   | 532.5  | 257.0  | 208.6  | 160.1  | 137.8  | 115.4  | 108.0  | 100.6  | 108.0  | 111.7  | 111.7  |
| 67.5° | 554.9  | 301.7  | 242.1  | 178.8  | 145.2  | 111.7  | 104.3  | 96.8   | 104.3  | 108.0  | 108.0  |
| 70°   | 502.8  | 331.4  | 260.7  | 189.9  | 152.7  | 111.7  | 104.3  | 93.1   | 96.8   | 100.6  | 96.8   |
| 72.5° | 432.0  | 324.0  | 257.0  | 186.2  | 149.0  | 108.0  | 100.6  | 89.4   | 93.1   | 93.1   | 89.4   |
| 75°   | 368.7  | 279.3  | 219.7  | 156.4  | 126.6  | 93.1   | 85.7   | 78.2   | 81.9   | 81.9   | 81.9   |
| 77.5° | 309.1  | 230.9  | 178.8  | 122.9  | 100.6  | 74.5   | 70.8   | 67.0   | 70.8   | 74.5   | 70.8   |
| 80°   | 242.1  | 175.0  | 134.1  | 89.4   | 74.5   | 55.9   | 59.6   | 59.6   | 63.3   | 63.3   | 63.3   |
| 82.5° | 141.5  | 104.3  | 85.7   | 63.3   | 52.1   | 41.0   | 44.7   | 48.4   | 52.1   | 52.1   | 52.1   |
| 85°   | 85.7   | 67.0   | 55.9   | 44.7   | 37.2   | 26.1   | 33.5   | 37.2   | 37.2   | 37.2   | 33.5   |
| 87.5° | 14.9   | 14.9   | 14.9   | 14.9   | 11.2   | 7.4    | 14.9   | 18.6   | 18.6   | 18.6   | 14.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P561303

CATALOG NUMBER: SDL-PA1-90-760-U-SL3

**CANDELA DISTRIBUTION (continued):**

|       | 165°   | 170°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|
| 0°    | 2901.1 | 2901.1 | 2901.1 | 2901.1 |
| 2.5°  | 2424.4 | 2424.4 | 2420.7 | 2420.7 |
| 5°    | 2227.0 | 2219.6 | 2212.1 | 2219.6 |
| 7.5°  | 1772.7 | 1720.5 | 1668.4 | 1683.3 |
| 10°   | 1776.4 | 1772.7 | 1769.0 | 1765.2 |
| 12.5° | 1284.8 | 1243.9 | 1202.9 | 1176.8 |
| 15°   | 1091.2 | 1080.0 | 1065.1 | 1065.1 |
| 17.5° | 737.4  | 703.9  | 670.3  | 648.0  |
| 20°   | 629.4  | 648.0  | 662.9  | 670.3  |
| 22.5° | 469.2  | 484.1  | 499.0  | 506.5  |
| 25°   | 495.3  | 532.5  | 566.1  | 569.8  |
| 27.5° | 342.6  | 361.2  | 376.1  | 368.7  |
| 30°   | 335.2  | 346.3  | 357.5  | 357.5  |
| 32.5° | 286.8  | 316.5  | 346.3  | 350.1  |
| 35°   | 286.8  | 301.7  | 316.5  | 320.3  |
| 37.5° | 257.0  | 268.1  | 275.6  | 279.3  |
| 40°   | 230.9  | 238.3  | 242.1  | 242.1  |
| 42.5° | 204.8  | 223.4  | 238.3  | 238.3  |
| 45°   | 182.5  | 230.9  | 279.3  | 294.2  |
| 47.5° | 178.8  | 249.5  | 320.3  | 335.2  |
| 50°   | 193.7  | 260.7  | 324.0  | 331.4  |
| 52.5° | 197.4  | 234.6  | 268.1  | 268.1  |
| 55°   | 156.4  | 175.0  | 189.9  | 186.2  |
| 57.5° | 134.1  | 149.0  | 160.1  | 160.1  |
| 60°   | 126.6  | 145.2  | 160.1  | 163.9  |
| 62.5° | 122.9  | 130.3  | 137.8  | 145.2  |
| 65°   | 111.7  | 111.7  | 111.7  | 111.7  |
| 67.5° | 104.3  | 104.3  | 100.6  | 100.6  |
| 70°   | 93.1   | 93.1   | 93.1   | 93.1   |
| 72.5° | 85.7   | 85.7   | 85.7   | 81.9   |
| 75°   | 78.2   | 78.2   | 74.5   | 74.5   |
| 77.5° | 67.0   | 67.0   | 67.0   | 67.0   |
| 80°   | 59.6   | 59.6   | 55.9   | 55.9   |
| 82.5° | 48.4   | 48.4   | 44.7   | 41.0   |
| 85°   | 29.8   | 29.8   | 26.1   | 22.3   |
| 87.5° | 11.2   | 11.2   | 7.4    | 3.7    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    |



Report Generated By 670245982









--- HS --- SS



u











(END OF REPORT)