

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P623516

Luminaire Tested: **IFLD-L-SA7E-827-U-44**

Issue Date: 11/2/2022

Test Information

Test Method: LM-79-2019
Report Number: P623516
Test Lab: INNOVATION CENTER(G2)
Issue Date: 11/2/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: IFLD-L-SA7E-827-U-44
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ Nema 4 distribution lens
Light Source: (112) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	43088.2 lumens	Max Intensity:	139327.8 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	80.9 lumens/watt		
Luminous Opening:	Rectangular (W 2' x L: 1' x H: 0')		

Beam Angle (50%):	28.6°H x 28.6°V	Field Angle (10%):	52.7°H x 52.7°V
Beam Lumens:	15547 lumens	Field Lumens:	26253.3 lumens
Beam Efficiency:	36.1%	Field Efficiency:	60.9%


Input Watts (W): 532.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P623516

CATALOG NUMBER: IFLD-L-SA7E-827-U-44

Iso-Candela Plot




REPORT NUMBER: P623516
CATALOG NUMBER: IFLD-L-SA7E-827-U-44

Lumen Table

Vertical Angle (degrees)																
	1.0	7.3		18.5		29.6		34.2		29.6		18.5		7.3		1.0
90																
80																
70																
60	3.3	3.5	7.2	11.8	16.6	20.8	24.0	25.8	25.8	24.0	20.8	16.6	11.8	7.2	3.5	3.3
50		5.3	10.9	17.5	24.2	30.0	34.5	36.9	36.9	34.5	30.0	24.2	17.5	10.9	5.3	
40	5.7	7.1	14.2	22.5	30.8	39.2	46.7	51.5	51.5	46.7	39.2	30.8	22.5	14.2	7.1	5.7
30		8.7	17.0	26.7	38.3	54.5	79.5	105.9	105.9	79.5	54.5	38.3	26.7	17.0	8.7	
20	7.5	9.8	19.1	30.6	49.4	103.4	283.5	513.4	513.4	283.5	103.4	49.4	30.6	19.1	9.8	7.5
10		10.7	20.6	34.4	67.9	267.6	920.3	1775.2	1775.2	920.3	267.6	67.9	34.4	20.6	10.7	
0	8.2	11.1	21.4	36.8	88.0	471.4	1727.1	3404.9	3404.9	1727.1	471.4	88.0	36.8	21.4	11.1	8.2
-10		11.1	21.4	36.8	88.0	471.4	1727.1	3404.9	3404.9	1727.1	471.4	88.0	36.8	21.4	11.1	
-20	7.5	10.7	20.6	34.4	67.9	267.6	920.3	1775.2	1775.2	920.3	267.6	67.9	34.4	20.6	10.7	7.5
-30		9.8	19.1	30.6	49.4	103.4	283.5	513.4	513.4	283.5	103.4	49.4	30.6	19.1	9.8	
-40	5.7	8.7	17.0	26.7	38.3	54.5	79.5	105.9	105.9	79.5	54.5	38.3	26.7	17.0	8.7	5.7
-50		7.1	14.2	22.5	30.8	39.2	46.7	51.5	51.5	46.7	39.2	30.8	22.5	14.2	7.1	
-60	3.3	5.3	10.9	17.5	24.2	30.0	34.5	36.9	36.9	34.5	30.0	24.2	17.5	10.9	5.3	3.3
-70		3.5	7.2	11.8	16.6	20.8	24.0	25.8	25.8	24.0	20.8	16.6	11.8	7.2	3.5	
-80	1.0	7.3		18.5		29.6		34.2		29.6		18.5		7.3		1.0
-90																
Horizontal Angle (degrees)																

REPORT NUMBER: P623516
CATALOG NUMBER: IFLD-L-SA7E-827-U-44

Luminous Intensity Polar Plot




— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: P623516

CATALOG NUMBER: IFLD-L-SA7E-827-U-44

Luminous Intensity Plot



Beam:

H Angle: 28.6°
V Angle: 28.6°
Lumens: 15547
Efficiency: 36.1%

Field:

H Angle: 52.7°
V Angle: 52.7°
Lumens: 26253.3
Efficiency: 60.9%

Spill:

Lumens: 16834.9
Efficiency: 39.1%

— Vertical Distribution through 0-Deg
- - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P623516

CATALOG NUMBER: IFLD-L-SA7E-827-U-44

FIELD
BEAM

CANDELA DISTRIBUTION:

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	49.4	49.4	49.4	49.4	49.4	49.4	49.4	44.9	44.9	44.9	44.9
85°	112.3	112.3	112.3	112.3	112.3	107.8	107.8	107.8	103.3	103.3	98.8
82.5°	179.7	179.7	179.7	179.7	175.2	175.2	170.7	170.7	166.2	166.2	161.7
80°	256.1	256.1	256.1	256.1	251.6	247.1	247.1	242.6	238.1	233.6	229.1
77.5°	345.9	345.9	345.9	341.4	336.9	336.9	332.4	323.5	319.0	310.0	305.5
75°	444.7	444.7	444.7	440.3	435.8	431.3	422.3	417.8	408.8	399.8	386.3
72.5°	552.6	552.6	552.6	548.1	539.1	534.6	525.6	516.6	507.6	494.2	480.7
70°	655.9	655.9	655.9	646.9	642.4	633.4	624.4	615.5	602.0	588.5	575.0
67.5°	759.2	759.2	759.2	750.2	745.7	736.8	727.8	714.3	700.8	682.8	669.4
65°	853.6	853.6	849.1	844.6	840.1	831.1	817.6	808.6	795.2	777.2	759.2
62.5°	952.4	952.4	947.9	943.4	934.4	925.4	912.0	898.5	880.5	862.5	844.6
60°	1051.2	1051.2	1046.7	1042.2	1033.3	1019.8	1006.3	992.8	974.9	952.4	929.9
57.5°	1132.1	1132.1	1127.6	1123.1	1114.1	1105.1	1091.7	1078.2	1060.2	1042.2	1015.3
55°	1217.4	1217.4	1213.0	1204.0	1195.0	1186.0	1172.5	1154.6	1136.6	1114.1	1096.1
52.5°	1316.3	1316.3	1311.8	1302.8	1289.3	1275.8	1257.9	1235.4	1213.0	1190.5	1163.5
50°	1415.1	1415.1	1406.1	1397.1	1388.2	1370.2	1352.2	1329.8	1302.8	1275.8	1244.4
47.5°	1536.4	1536.4	1527.4	1513.9	1496.0	1478.0	1451.1	1419.6	1392.6	1361.2	1325.3
45°	1684.7	1684.7	1671.2	1657.7	1635.2	1603.8	1572.3	1536.4	1496.0	1455.5	1410.6
42.5°	1877.8	1877.8	1859.9	1837.4	1806.0	1765.5	1716.1	1666.7	1617.3	1563.4	1509.5
40°	2138.4	2138.4	2111.4	2080.0	2030.6	1972.2	1900.3	1832.9	1765.5	1689.1	1621.8
37.5°	2547.2	2547.2	2502.3	2443.9	2363.0	2264.2	2142.9	2053.0	1949.7	1850.9	1761.0
35°	3216.6	3216.6	3135.7	3032.4	2888.6	2708.9	2515.8	2363.0	2192.3	2053.0	1922.8
32.5°	4407.1	4407.1	4245.3	4043.2	3769.1	3418.7	3095.3	2825.7	2547.2	2331.6	2124.9
30°	6711.7	6711.7	6365.8	5939.0	5350.5	4613.7	4061.1	3544.5	3072.8	2717.9	2416.9
27.5°	11037.9	10858.2	10319.1	9434.1	8221.1	6711.7	5750.3	4658.6	3912.9	3234.5	2816.7
25°	17426.1	17129.6	16240.1	14789.0	12812.4	10570.7	8607.5	6536.5	5229.2	4101.6	3324.4
22.5°	25189.0	24780.2	23571.7	21599.5	18926.5	15943.6	12767.4	9789.0	7138.4	5422.3	4101.6
20°	34380.5	33832.4	32210.6	29578.1	26038.0	22242.0	18001.1	14011.8	10188.8	7138.4	5229.2
17.5°	46514.5	45678.9	43221.5	39268.2	34380.5	29263.6	23962.5	18814.2	14011.8	9789.0	6536.5
15°	63958.5	62547.9	58423.9	51873.9	44263.8	37129.8	30368.7	23962.5	18001.1	12767.4	8607.5
12.5°	84125.0	82161.8	76478.9	67615.4	57273.8	45993.4	37129.8	29263.6	22242.0	15943.6	10570.7
10°	101115.3	99044.3	93172.7	84282.2	71168.9	57273.8	44263.8	34380.5	26038.0	18926.5	12812.4
7.5°	115468.6	113150.5	106820.7	97094.6	84282.2	67615.4	51873.9	39268.2	29578.1	21599.5	14789.0
5°	127935.0	124997.0	117629.4	106820.7	93172.7	76478.9	58423.9	43221.5	32210.6	23571.7	16240.1
2.5°	136264.0	132813.8	124997.0	113150.5	99044.3	82161.8	62547.9	45678.9	33832.4	24780.2	17129.6
0°	139327.8	136264.0	127935.0	115468.6	101115.3	84125.0	63958.5	46514.5	34380.5	25189.0	17426.1

REPORT NUMBER: P623516

CATALOG NUMBER: IFLD-L-SA7E-827-U-44

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	44.9	44.9	40.4	40.4	40.4	35.9	35.9	35.9	31.4	31.4	31.4
85°	98.8	94.3	94.3	89.8	85.4	80.9	80.9	76.4	71.9	67.4	62.9
82.5°	157.2	152.7	148.2	143.8	139.3	130.3	125.8	121.3	112.3	107.8	103.3
80°	220.1	215.6	206.7	202.2	193.2	184.2	175.2	166.2	157.2	148.2	139.3
77.5°	296.5	283.0	274.0	265.1	251.6	242.6	229.1	220.1	206.7	193.2	179.7
75°	377.4	363.9	350.4	336.9	323.5	305.5	292.0	274.0	260.6	242.6	229.1
72.5°	467.2	449.2	431.3	413.3	395.3	377.4	359.4	336.9	319.0	296.5	274.0
70°	557.1	539.1	521.1	498.7	476.2	453.7	431.3	404.3	381.9	354.9	327.9
67.5°	651.4	628.9	606.5	584.0	561.6	534.6	503.2	476.2	444.7	413.3	386.3
65°	741.2	718.8	691.8	664.9	637.9	611.0	579.5	548.1	512.1	476.2	444.7
62.5°	822.1	799.7	777.2	745.7	718.8	687.3	655.9	615.5	579.5	543.6	503.2
60°	907.5	880.5	853.6	822.1	790.7	759.2	723.3	682.8	646.9	602.0	561.6
57.5°	988.3	961.4	929.9	898.5	862.5	826.6	790.7	750.2	709.8	664.9	620.0
55°	1069.2	1042.2	1010.8	974.9	934.4	894.0	853.6	813.1	772.7	723.3	673.9
52.5°	1136.6	1109.6	1078.2	1051.2	1006.3	965.9	920.9	871.5	826.6	777.2	727.8
50°	1208.5	1177.0	1141.1	1109.6	1073.7	1033.3	983.8	934.4	880.5	831.1	777.2
47.5°	1289.3	1248.9	1208.5	1168.0	1132.1	1087.2	1046.7	992.8	938.9	880.5	826.6
45°	1370.2	1325.3	1280.3	1230.9	1186.0	1141.1	1096.1	1051.2	992.8	934.4	871.5
42.5°	1455.5	1401.6	1352.2	1302.8	1248.9	1195.0	1145.6	1096.1	1046.7	983.8	920.9
40°	1554.4	1491.5	1428.6	1370.2	1316.3	1253.4	1195.0	1141.1	1087.2	1033.3	965.9
37.5°	1666.7	1590.3	1513.9	1442.1	1374.7	1316.3	1248.9	1186.0	1132.1	1073.7	1006.3
35°	1810.4	1698.1	1608.3	1518.4	1442.1	1370.2	1302.8	1230.9	1168.0	1109.6	1051.2
32.5°	1972.2	1832.9	1711.6	1608.3	1513.9	1428.6	1352.2	1280.3	1208.5	1141.1	1078.2
30°	2169.8	1990.1	1832.9	1698.1	1590.3	1491.5	1401.6	1325.3	1248.9	1177.0	1109.6
27.5°	2448.4	2169.8	1972.2	1810.4	1666.7	1554.4	1455.5	1370.2	1289.3	1208.5	1136.6
25°	2816.7	2416.9	2124.9	1922.8	1761.0	1621.8	1509.5	1410.6	1325.3	1244.4	1163.5
22.5°	3234.5	2717.9	2331.6	2053.0	1850.9	1689.1	1563.4	1455.5	1361.2	1275.8	1190.5
20°	3912.9	3072.8	2547.2	2192.3	1949.7	1765.5	1617.3	1496.0	1392.6	1302.8	1213.0
17.5°	4658.6	3544.5	2825.7	2363.0	2053.0	1832.9	1666.7	1536.4	1419.6	1329.8	1235.4
15°	5750.3	4061.1	3095.3	2515.8	2142.9	1900.3	1716.1	1572.3	1451.1	1352.2	1257.9
12.5°	6711.7	4613.7	3418.7	2708.9	2264.2	1972.2	1765.5	1603.8	1478.0	1370.2	1275.8
10°	8221.1	5350.5	3769.1	2888.6	2363.0	2030.6	1806.0	1635.2	1496.0	1388.2	1289.3
7.5°	9434.1	5939.0	4043.2	3032.4	2443.9	2080.0	1837.4	1657.7	1513.9	1397.1	1302.8
5°	10319.1	6365.8	4245.3	3135.7	2502.3	2111.4	1859.9	1671.2	1527.4	1406.1	1311.8
2.5°	10858.2	6711.7	4407.1	3216.6	2547.2	2138.4	1877.8	1684.7	1536.4	1415.1	1316.3
0°	11037.9	6711.7	4407.1	3216.6	2547.2	2138.4	1877.8	1684.7	1536.4	1415.1	1316.3

REPORT NUMBER: P623516

CATALOG NUMBER: IFLD-L-SA7E-827-U-44

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	27.0	27.0	22.5	22.5	22.5	18.0	18.0	13.5	13.5	9.0	9.0
85°	58.4	53.9	49.4	44.9	40.4	35.9	35.9	31.4	27.0	22.5	18.0
82.5°	94.3	89.8	80.9	71.9	67.4	58.4	49.4	44.9	40.4	31.4	27.0
80°	130.3	121.3	112.3	103.3	94.3	80.9	71.9	62.9	49.4	40.4	35.9
77.5°	170.7	157.2	143.8	130.3	116.8	107.8	94.3	80.9	67.4	53.9	40.4
75°	211.1	193.2	179.7	161.7	148.2	130.3	112.3	98.8	85.4	67.4	49.4
72.5°	256.1	233.6	215.6	193.2	175.2	157.2	134.8	116.8	98.8	80.9	62.9
70°	305.5	278.5	251.6	229.1	206.7	179.7	157.2	134.8	112.3	94.3	71.9
67.5°	354.9	323.5	292.0	260.6	233.6	206.7	179.7	157.2	130.3	107.8	80.9
65°	404.3	368.4	336.9	301.0	265.1	233.6	206.7	175.2	148.2	116.8	94.3
62.5°	458.2	417.8	377.4	336.9	301.0	260.6	229.1	193.2	161.7	130.3	103.3
60°	516.6	471.7	422.3	377.4	336.9	292.0	251.6	215.6	179.7	143.8	112.3
57.5°	570.5	521.1	471.7	417.8	368.4	323.5	278.5	233.6	193.2	157.2	121.3
55°	624.4	570.5	516.6	458.2	404.3	354.9	305.5	256.1	211.1	170.7	130.3
52.5°	673.9	620.0	561.6	503.2	444.7	386.3	327.9	274.0	229.1	179.7	139.3
50°	723.3	664.9	602.0	543.6	476.2	413.3	354.9	296.5	242.6	193.2	148.2
47.5°	772.7	709.8	646.9	579.5	512.1	444.7	381.9	319.0	260.6	206.7	157.2
45°	813.1	750.2	682.8	615.5	548.1	476.2	404.3	336.9	274.0	220.1	166.2
42.5°	853.6	790.7	723.3	655.9	579.5	503.2	431.3	359.4	292.0	229.1	175.2
40°	894.0	826.6	759.2	687.3	611.0	534.6	453.7	377.4	305.5	242.6	184.2
37.5°	934.4	862.5	790.7	718.8	637.9	561.6	476.2	395.3	323.5	251.6	193.2
35°	974.9	898.5	822.1	745.7	664.9	584.0	498.7	413.3	336.9	265.1	202.2
32.5°	1010.8	929.9	853.6	777.2	691.8	606.5	521.1	431.3	350.4	274.0	206.7
30°	1042.2	961.4	880.5	799.7	718.8	628.9	539.1	449.2	363.9	283.0	215.6
27.5°	1069.2	988.3	907.5	822.1	741.2	651.4	557.1	467.2	377.4	296.5	220.1
25°	1096.1	1015.3	929.9	844.6	759.2	669.4	575.0	480.7	386.3	305.5	229.1
22.5°	1114.1	1042.2	952.4	862.5	777.2	682.8	588.5	494.2	399.8	310.0	233.6
20°	1136.6	1060.2	974.9	880.5	795.2	700.8	602.0	507.6	408.8	319.0	238.1
17.5°	1154.6	1078.2	992.8	898.5	808.6	714.3	615.5	516.6	417.8	323.5	242.6
15°	1172.5	1091.7	1006.3	912.0	817.6	727.8	624.4	525.6	422.3	332.4	247.1
12.5°	1186.0	1105.1	1019.8	925.4	831.1	736.8	633.4	534.6	431.3	336.9	247.1
10°	1195.0	1114.1	1033.3	934.4	840.1	745.7	642.4	539.1	435.8	336.9	251.6
7.5°	1204.0	1123.1	1042.2	943.4	844.6	750.2	646.9	548.1	440.3	341.4	256.1
5°	1213.0	1127.6	1046.7	947.9	849.1	759.2	655.9	552.6	444.7	345.9	256.1
2.5°	1217.4	1132.1	1051.2	952.4	853.6	759.2	655.9	552.6	444.7	345.9	256.1
0°	1217.4	1132.1	1051.2	952.4	853.6	759.2	655.9	552.6	444.7	345.9	256.1

REPORT NUMBER: P623516

CATALOG NUMBER: IFLD-L-SA7E-827-U-44

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°
90°	0.0	0.0	0.0	0.0
87.5°	4.5	4.5	0.0	0.0
85°	13.5	9.0	4.5	0.0
82.5°	18.0	13.5	4.5	0.0
80°	27.0	18.0	9.0	0.0
77.5°	31.4	22.5	9.0	0.0
75°	40.4	27.0	13.5	0.0
72.5°	44.9	31.4	13.5	0.0
70°	49.4	35.9	18.0	0.0
67.5°	58.4	35.9	18.0	0.0
65°	67.4	40.4	22.5	0.0
62.5°	71.9	44.9	22.5	0.0
60°	80.9	49.4	22.5	0.0
57.5°	89.8	53.9	27.0	0.0
55°	94.3	58.4	27.0	0.0
52.5°	103.3	62.9	31.4	0.0
50°	107.8	67.4	31.4	0.0
47.5°	112.3	71.9	31.4	0.0
45°	121.3	76.4	35.9	0.0
42.5°	125.8	80.9	35.9	0.0
40°	130.3	80.9	35.9	0.0
37.5°	139.3	85.4	40.4	0.0
35°	143.8	89.8	40.4	0.0
32.5°	148.2	94.3	40.4	0.0
30°	152.7	94.3	44.9	0.0
27.5°	157.2	98.8	44.9	0.0
25°	161.7	98.8	44.9	0.0
22.5°	166.2	103.3	44.9	0.0
20°	166.2	103.3	44.9	0.0
17.5°	170.7	107.8	44.9	0.0
15°	170.7	107.8	49.4	0.0
12.5°	175.2	107.8	49.4	0.0
10°	175.2	112.3	49.4	0.0
7.5°	179.7	112.3	49.4	0.0
5°	179.7	112.3	49.4	0.0
2.5°	179.7	112.3	49.4	0.0
0°	179.7	112.3	49.4	0.0

(END OF REPORT)