

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P623804

Luminaire Tested: **IFLD-L-SA7C-830-U-55**

Issue Date: 11/2/2022

Test Information

Test Method: LM-79-2019
Report Number: P623804
Test Lab: INNOVATION CENTER(G2)
Issue Date: 11/2/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: IFLD-L-SA7C-830-U-55
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ Nema 5 distribution lens
Light Source: (112) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp:	N/A	NEMA Type:	5H x 5V
Luminaire Lumens:	36728.6 lumens	Max Intensity:	44883.9 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 10°V
Efficacy:	99.5 lumens/watt		
Luminous Opening:	Rectangular (W 2' x L: 1' x H: 0')		
Beam Angle (50%):	49.5°H x 53.1°V	Field Angle (10%):	73.6°H x 75.3°V
Beam Lumens:	18255 lumens	Field Lumens:	23741.2 lumens
Beam Efficiency:	49.7%	Field Efficiency:	64.6%

Input Watts (W): 369
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P623804
CATALOG NUMBER: IFLD-L-SA7C-830-U-55

Iso-Candela Plot




REPORT NUMBER: P623804
CATALOG NUMBER: IFLD-L-SA7C-830-U-55

Lumen Table

90																			
80	1.1		8.1		21.0		33.9		39.3		33.9		21.0		8.1		1.1		
70	3.7		4.0	8.3	13.7	19.3	24.1	27.6	29.4	29.4	27.6	24.1	19.3	13.7	8.3	4.0	3.7		
60			6.2	12.7	20.2	27.1	32.9	37.3	39.8	39.8	37.3	32.9	27.1	20.2	12.7	6.2			
50	6.5		8.3	16.4	24.8	33.2	43.0	54.5	63.3	63.3	54.5	43.0	33.2	24.8	16.4	8.3	6.5		
40			10.1	19.0	28.7	43.6	77.6	151.6	228.7	228.7	151.6	77.6	43.6	28.7	19.0	10.1			
30	8.7		11.4	20.9	33.7	70.4	224.4	520.0	738.0	738.0	520.0	224.4	70.4	33.7	20.9	11.4	8.7		
20			12.2	22.3	40.2	130.0	489.8	958.3	1221.6	1221.6	958.3	489.8	130.0	40.2	22.3	12.2			
10	9.5		12.6	23.0	45.4	190.8	674.7	1185.5	1344.4	1344.4	1185.5	674.7	190.8	45.4	23.0	12.6	9.5		
0			12.6	23.0	45.4	190.8	674.7	1185.5	1344.4	1344.4	1185.5	674.7	190.8	45.4	23.0	12.6			
-10	8.7		12.2	22.3	40.2	130.0	489.8	958.3	1221.6	1221.6	958.3	489.8	130.0	40.2	22.3	12.2	8.7		
-20			11.4	20.9	33.7	70.4	224.4	520.0	738.0	738.0	520.0	224.4	70.4	33.7	20.9	11.4			
-30	6.5		10.1	19.0	28.7	43.6	77.6	151.6	228.7	228.7	151.6	77.6	43.6	28.7	19.0	10.1	6.5		
-40			8.3	16.4	24.8	33.2	43.0	54.5	63.3	63.3	54.5	43.0	33.2	24.8	16.4	8.3			
-50	3.7		6.2	12.7	20.2	27.1	32.9	37.3	39.8	39.8	37.3	32.9	27.1	20.2	12.7	6.2	3.7		
-60			4.0	8.3	13.7	19.3	24.1	27.6	29.4	29.4	27.6	24.1	19.3	13.7	8.3	4.0			
-70	1.1																1.1		
-80			8.1		21.0		33.9		39.3		33.9		21.0		8.1				
-90	1.1		8.1		21.0		33.9		39.3		33.9		21.0		8.1		1.1		
	-90	-80	-70	-60	-50	-40	-30	-20	-10	0	10	20	30	40	50	60	70	80	90
	Horizontal Angle (degrees)																		

REPORT NUMBER: P623804
CATALOG NUMBER: IFLD-L-SA7C-830-U-55

Luminous Intensity Polar Plot




— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 10-Deg

REPORT NUMBER: P623804

CATALOG NUMBER: IFLD-L-SA7C-830-U-55

Luminous Intensity Plot



Beam:

H Angle: 49.5°
V Angle: 53.1°
Lumens: 18255
Efficiency: 49.7%

Field:

H Angle: 73.6°
V Angle: 75.3°
Lumens: 23741.2
Efficiency: 64.6%

Spill:

Lumens: 12987.4
Efficiency: 35.4%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 10-Deg

REPORT NUMBER: P623804

CATALOG NUMBER: IFLD-L-SA7C-830-U-55

FIELD
BEAM

CANDELA DISTRIBUTION:

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	49.6	49.6	49.6	49.6	49.6	49.6	49.6	45.8	45.8	45.8	45.8
85°	122.1	122.1	122.1	122.1	122.1	118.3	118.3	114.5	114.5	110.6	106.8
82.5°	198.4	198.4	198.4	198.4	194.6	194.6	190.8	187.0	183.1	179.3	175.5
80°	290.0	290.0	290.0	290.0	286.2	282.3	278.5	274.7	267.1	263.3	255.6
77.5°	396.8	396.8	396.8	393.0	389.2	385.4	377.7	370.1	362.5	354.8	347.2
75°	518.9	518.9	518.9	511.3	507.4	499.8	492.2	484.6	473.1	461.7	450.2
72.5°	644.8	644.8	644.8	637.2	629.5	621.9	614.3	602.8	591.4	576.1	560.9
70°	763.1	763.1	763.1	755.4	747.8	740.2	728.7	717.3	702.0	686.8	671.5
67.5°	885.2	885.2	885.2	873.7	866.1	858.5	847.0	831.7	816.5	797.4	778.3
65°	984.4	984.4	980.5	976.7	969.1	957.7	950.0	934.8	919.5	904.2	885.2
62.5°	1075.9	1075.9	1072.1	1068.3	1060.7	1049.2	1037.8	1026.3	1011.1	992.0	972.9
60°	1152.2	1152.2	1148.4	1144.6	1137.0	1129.3	1117.9	1106.5	1091.2	1075.9	1056.9
57.5°	1228.5	1228.5	1224.7	1220.9	1213.3	1201.8	1190.4	1178.9	1163.7	1144.6	1125.5
55°	1308.7	1308.7	1304.9	1297.2	1289.6	1278.1	1266.7	1251.4	1232.4	1213.3	1194.2
52.5°	1404.1	1404.1	1396.4	1388.8	1377.3	1365.9	1346.8	1327.7	1304.9	1282.0	1259.1
50°	1530.0	1530.0	1522.3	1510.9	1491.8	1472.7	1449.8	1419.3	1392.6	1362.1	1331.6
47.5°	1716.9	1716.9	1701.6	1682.6	1655.9	1625.3	1583.4	1537.6	1499.4	1461.3	1415.5
45°	1991.6	1991.6	1968.7	1938.2	1896.2	1842.8	1781.8	1716.9	1652.0	1587.2	1522.3
42.5°	2438.0	2438.0	2396.0	2342.6	2270.1	2178.6	2064.1	1957.3	1865.7	1762.7	1674.9
40°	3208.7	3208.7	3128.6	3029.4	2892.0	2716.5	2506.7	2338.8	2178.6	1999.2	1877.2
37.5°	4578.4	4578.4	4422.0	4231.2	3964.2	3628.4	3224.0	2953.1	2655.5	2373.2	2167.1
35°	6997.4	6997.4	6696.0	6325.9	5810.8	5162.2	4471.6	3960.3	3391.9	2956.9	2571.6
32.5°	10965.3	10965.3	10423.6	9755.9	8836.4	7672.7	6566.2	5593.3	4578.4	3857.3	3162.9
30°	15681.1	15681.1	14971.5	14097.7	12899.7	11388.8	9813.1	8084.7	6482.3	5196.5	4147.3
27.5°	20557.1	20354.9	19744.5	18748.7	17382.8	15681.1	13716.2	11484.2	9317.1	7050.8	5551.3
25°	25601.0	25364.5	24666.3	23521.7	21957.4	20030.6	17817.7	15322.5	12647.9	9946.6	7352.2
22.5°	30698.4	30431.3	29637.7	28344.3	26589.2	24429.7	21923.0	19149.3	16161.9	13040.9	9946.6
20°	35410.3	35128.0	34296.2	32949.4	31133.3	28764.0	25978.8	22903.6	19599.5	16161.9	12647.9
17.5°	39355.4	39084.5	38283.3	36997.5	35410.3	32789.2	29893.3	26512.9	22903.6	19149.3	15322.5
15°	42236.0	42003.3	41320.3	40240.6	38622.9	36303.1	33353.8	29893.3	25978.8	21923.0	17817.7
12.5°	44147.5	43960.5	43422.6	42583.2	41133.4	39187.5	36303.1	32789.2	28764.0	24429.7	20030.6
10°	44883.9	44792.3	44540.5	44155.1	42918.9	41133.4	38622.9	35410.3	31133.3	26589.2	21957.4
7.5°	44689.3	44719.8	44807.5	44708.3	44155.1	42583.2	40240.6	36997.5	32949.4	28344.3	23521.7
5°	43994.9	44158.9	44567.2	44807.5	44540.5	43422.6	41320.3	38283.3	34296.2	29637.7	24666.3
2.5°	43376.8	43632.4	44158.9	44719.8	44792.3	43960.5	42003.3	39084.5	35128.0	30431.3	25364.5
0°	43071.6	43376.8	43994.9	44689.3	44883.9	44147.5	42236.0	39355.4	35410.3	30698.4	25601.0

REPORT NUMBER: P623804

CATALOG NUMBER: IFLD-L-SA7C-830-U-55

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	45.8	42.0	42.0	42.0	38.2	38.2	38.2	34.3	34.3	30.5	30.5
85°	106.8	103.0	99.2	95.4	91.6	87.8	83.9	80.1	76.3	68.7	64.9
82.5°	171.7	167.9	164.1	156.4	152.6	145.0	137.4	129.7	122.1	118.3	110.6
80°	248.0	240.4	232.7	225.1	213.7	202.2	194.6	183.1	175.5	164.1	156.4
77.5°	335.8	324.3	312.9	297.6	286.2	274.7	259.4	248.0	232.7	217.5	202.2
75°	435.0	419.7	400.6	385.4	370.1	351.0	331.9	312.9	293.8	274.7	255.6
72.5°	541.8	522.7	503.6	484.6	461.7	435.0	412.1	385.4	362.5	339.6	312.9
70°	652.4	629.5	606.6	583.7	557.0	526.5	499.8	469.3	438.8	408.2	377.7
67.5°	755.4	732.5	705.8	682.9	652.4	621.9	587.6	553.2	518.9	480.7	442.6
65°	862.3	835.6	805.0	774.5	744.0	709.7	675.3	641.0	599.0	557.0	518.9
62.5°	950.0	927.1	900.4	869.9	835.6	797.4	763.1	717.3	675.3	633.3	583.7
60°	1034.0	1007.3	984.4	950.0	919.5	885.2	843.2	797.4	751.6	702.0	656.2
57.5°	1106.5	1083.6	1056.9	1026.3	992.0	957.7	919.5	877.5	824.1	774.5	721.1
55°	1171.3	1144.6	1117.9	1091.2	1060.7	1022.5	984.4	942.4	896.6	843.2	786.0
52.5°	1236.2	1209.5	1178.9	1152.2	1117.9	1083.6	1045.4	1003.4	957.7	908.1	847.0
50°	1301.0	1270.5	1240.0	1205.7	1171.3	1137.0	1098.8	1060.7	1011.1	961.5	908.1
47.5°	1377.3	1339.2	1301.0	1262.9	1228.5	1186.6	1148.4	1106.5	1064.5	1011.1	957.7
45°	1472.7	1415.5	1369.7	1323.9	1282.0	1240.0	1194.2	1152.2	1106.5	1060.7	1003.4
42.5°	1591.0	1514.7	1453.7	1392.6	1339.2	1289.6	1243.8	1194.2	1148.4	1098.8	1045.4
40°	1751.2	1648.2	1549.0	1472.7	1404.1	1343.0	1289.6	1240.0	1186.6	1137.0	1083.6
37.5°	1961.1	1816.1	1678.8	1568.1	1480.4	1404.1	1339.2	1282.0	1228.5	1171.3	1117.9
35°	2277.8	2026.0	1850.4	1690.2	1568.1	1472.7	1392.6	1323.9	1262.9	1205.7	1152.2
32.5°	2724.2	2335.0	2052.7	1850.4	1678.8	1549.0	1453.7	1369.7	1301.0	1240.0	1178.9
30°	3311.7	2773.8	2335.0	2026.0	1816.1	1648.2	1514.7	1415.5	1339.2	1270.5	1209.5
27.5°	4242.7	3311.7	2724.2	2277.8	1961.1	1751.2	1591.0	1472.7	1377.3	1301.0	1236.2
25°	5551.3	4147.3	3162.9	2571.6	2167.1	1877.2	1674.9	1522.3	1415.5	1331.6	1259.1
22.5°	7050.8	5196.5	3857.3	2956.9	2373.2	1999.2	1762.7	1587.2	1461.3	1362.1	1282.0
20°	9317.1	6482.3	4578.4	3391.9	2655.5	2178.6	1865.7	1652.0	1499.4	1392.6	1304.9
17.5°	11484.2	8084.7	5593.3	3960.3	2953.1	2338.8	1957.3	1716.9	1537.6	1419.3	1327.7
15°	13716.2	9813.1	6566.2	4471.6	3224.0	2506.7	2064.1	1781.8	1583.4	1449.8	1346.8
12.5°	15681.1	11388.8	7672.7	5162.2	3628.4	2716.5	2178.6	1842.8	1625.3	1472.7	1365.9
10°	17382.8	12899.7	8836.4	5810.8	3964.2	2892.0	2270.1	1896.2	1655.9	1491.8	1377.3
7.5°	18748.7	14097.7	9755.9	6325.9	4231.2	3029.4	2342.6	1938.2	1682.6	1510.9	1388.8
5°	19744.5	14971.5	10423.6	6696.0	4422.0	3128.6	2396.0	1968.7	1701.6	1522.3	1396.4
2.5°	20354.9	15681.1	10965.3	6997.4	4578.4	3208.7	2438.0	1991.6	1716.9	1530.0	1404.1
0°	20557.1	15681.1	10965.3	6997.4	4578.4	3208.7	2438.0	1991.6	1716.9	1530.0	1404.1

REPORT NUMBER: P623804

CATALOG NUMBER: IFLD-L-SA7C-830-U-55

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	26.7	26.7	22.9	22.9	19.1	19.1	15.3	15.3	11.4	11.4	7.6
85°	61.0	53.4	49.6	45.8	42.0	38.2	34.3	30.5	26.7	22.9	19.1
82.5°	103.0	95.4	83.9	76.3	68.7	61.0	49.6	45.8	38.2	30.5	26.7
80°	145.0	133.5	122.1	110.6	99.2	87.8	76.3	64.9	53.4	42.0	34.3
77.5°	187.0	171.7	160.2	145.0	129.7	114.5	99.2	83.9	68.7	53.4	42.0
75°	236.6	217.5	198.4	179.3	160.2	141.2	125.9	106.8	87.8	68.7	53.4
72.5°	290.0	263.3	240.4	217.5	190.8	171.7	148.8	129.7	106.8	83.9	64.9
70°	347.2	316.7	286.2	255.6	228.9	198.4	175.5	148.8	125.9	99.2	76.3
67.5°	404.4	370.1	335.8	297.6	263.3	232.7	198.4	171.7	141.2	114.5	87.8
65°	473.1	427.3	385.4	343.4	301.4	263.3	228.9	190.8	160.2	129.7	99.2
62.5°	538.0	488.4	438.8	389.2	343.4	297.6	255.6	217.5	179.3	145.0	110.6
60°	602.8	549.4	492.2	438.8	385.4	335.8	286.2	240.4	198.4	160.2	122.1
57.5°	667.7	606.6	549.4	488.4	427.3	370.1	316.7	263.3	217.5	171.7	133.5
55°	724.9	667.7	602.8	538.0	473.1	404.4	347.2	290.0	236.6	187.0	145.0
52.5°	786.0	721.1	656.2	583.7	518.9	442.6	377.7	312.9	255.6	202.2	156.4
50°	843.2	774.5	702.0	633.3	557.0	480.7	408.2	339.6	274.7	217.5	164.1
47.5°	896.6	824.1	751.6	675.3	599.0	518.9	438.8	362.5	293.8	232.7	175.5
45°	942.4	877.5	797.4	717.3	641.0	553.2	469.3	385.4	312.9	248.0	183.1
42.5°	984.4	919.5	843.2	763.1	675.3	587.6	499.8	412.1	331.9	259.4	194.6
40°	1022.5	957.7	885.2	797.4	709.7	621.9	526.5	435.0	351.0	274.7	202.2
37.5°	1060.7	992.0	919.5	835.6	744.0	652.4	557.0	461.7	370.1	286.2	213.7
35°	1091.2	1026.3	950.0	869.9	774.5	682.9	583.7	484.6	385.4	297.6	225.1
32.5°	1117.9	1056.9	984.4	900.4	805.0	705.8	606.6	503.6	400.6	312.9	232.7
30°	1144.6	1083.6	1007.3	927.1	835.6	732.5	629.5	522.7	419.7	324.3	240.4
27.5°	1171.3	1106.5	1034.0	950.0	862.3	755.4	652.4	541.8	435.0	335.8	248.0
25°	1194.2	1125.5	1056.9	972.9	885.2	778.3	671.5	560.9	450.2	347.2	255.6
22.5°	1213.3	1144.6	1075.9	992.0	904.2	797.4	686.8	576.1	461.7	354.8	263.3
20°	1232.4	1163.7	1091.2	1011.1	919.5	816.5	702.0	591.4	473.1	362.5	267.1
17.5°	1251.4	1178.9	1106.5	1026.3	934.8	831.7	717.3	602.8	484.6	370.1	274.7
15°	1266.7	1190.4	1117.9	1037.8	950.0	847.0	728.7	614.3	492.2	377.7	278.5
12.5°	1278.1	1201.8	1129.3	1049.2	957.7	858.5	740.2	621.9	499.8	385.4	282.3
10°	1289.6	1213.3	1137.0	1060.7	969.1	866.1	747.8	629.5	507.4	389.2	286.2
7.5°	1297.2	1220.9	1144.6	1068.3	976.7	873.7	755.4	637.2	511.3	393.0	290.0
5°	1304.9	1224.7	1148.4	1072.1	980.5	885.2	763.1	644.8	518.9	396.8	290.0
2.5°	1308.7	1228.5	1152.2	1075.9	984.4	885.2	763.1	644.8	518.9	396.8	290.0
0°	1308.7	1228.5	1152.2	1075.9	984.4	885.2	763.1	644.8	518.9	396.8	290.0

REPORT NUMBER: P623804

CATALOG NUMBER: IFLD-L-SA7C-830-U-55

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°
90°	0.0	0.0	0.0	0.0
87.5°	7.6	3.8	3.8	0.0
85°	11.4	7.6	3.8	0.0
82.5°	19.1	11.4	7.6	0.0
80°	26.7	19.1	7.6	0.0
77.5°	30.5	22.9	11.4	0.0
75°	38.2	26.7	11.4	0.0
72.5°	45.8	30.5	15.3	0.0
70°	49.6	34.3	15.3	0.0
67.5°	61.0	38.2	19.1	0.0
65°	68.7	42.0	19.1	0.0
62.5°	76.3	45.8	22.9	0.0
60°	83.9	49.6	22.9	0.0
57.5°	95.4	53.4	26.7	0.0
55°	103.0	61.0	26.7	0.0
52.5°	110.6	64.9	30.5	0.0
50°	118.3	68.7	30.5	0.0
47.5°	122.1	76.3	34.3	0.0
45°	129.7	80.1	34.3	0.0
42.5°	137.4	83.9	38.2	0.0
40°	145.0	87.8	38.2	0.0
37.5°	152.6	91.6	38.2	0.0
35°	156.4	95.4	42.0	0.0
32.5°	164.1	99.2	42.0	0.0
30°	167.9	103.0	42.0	0.0
27.5°	171.7	106.8	45.8	0.0
25°	175.5	106.8	45.8	0.0
22.5°	179.3	110.6	45.8	0.0
20°	183.1	114.5	45.8	0.0
17.5°	187.0	114.5	45.8	0.0
15°	190.8	118.3	49.6	0.0
12.5°	194.6	118.3	49.6	0.0
10°	194.6	122.1	49.6	0.0
7.5°	198.4	122.1	49.6	0.0
5°	198.4	122.1	49.6	0.0
2.5°	198.4	122.1	49.6	0.0
0°	198.4	122.1	49.6	0.0

(END OF REPORT)