

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P722540

Luminaire Tested: **IFLD-S-SA2B-760-U-76-VI**

Issue Date: 10/26/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P722540  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 10/26/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: IFLD-S-SA2B-760-U-76-VI  
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ Nema  
7x6 Flood distribution lens with Visor  
Light Source: (32) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


|                                   |                                      |                      |                   |
|-----------------------------------|--------------------------------------|----------------------|-------------------|
| Lumens per Lamp:                  | N/A                                  | NEMA Type:           | 6H x 6V           |
| Luminaire Lumens:                 | 11942.3 lumens                       | Max Intensity:       | 8337.1 candela    |
| Efficiency:                       | N/A                                  | Max Intensity Angle: | 0°H x 30°V        |
| Efficacy:                         | 144.9 lumens/watt                    |                      |                   |
| Luminous Opening:                 | Rectangular (W 1' x L: 0.5' x H: 0') |                      |                   |
| Beam Angle (50%):                 | 68.6°H x 68.4°V                      | Field Angle (10%):   | 111.9°H x 109.7°V |
| Beam Lumens:                      | 7618.7 lumens                        | Field Lumens:        | 11259 lumens      |
| Beam Efficiency:                  | 63.8%                                | Field Efficiency:    | 94.3%             |
| Input Watts (W):                  | 82.4                                 |                      |                   |
| Input Voltage (V):                | 120                                  |                      |                   |
| Input Current (Ain):              | NR                                   |                      |                   |
| Voltage Rise (V):                 | NR                                   |                      |                   |
| Power Factor:                     | NR                                   |                      |                   |
| Total Harmonic Distortion (THDi): | NR                                   |                      |                   |
| Frequency (hertz):                | 60                                   |                      |                   |
| Stabilization Time:               | NR                                   |                      |                   |
| Operation Time:                   | NR                                   |                      |                   |
| Ambient Temperature (°C):         | NR                                   |                      |                   |
| Test Distance:                    | 28.75 FT                             |                      |                   |



REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI


## Iso-Candela Plot



REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI


## Lumen Table



REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI

## Luminous Intensity Polar Plot




— Vertical Distribution Through 0-Deg      - - - Horizontal Distribution Through 30-Deg

REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI

## Luminous Intensity Plot



**Beam:**

H Angle: 68.6°

V Angle: 68.4°

Lumens: 7618.7

Efficiency: 63.8%

**Field:**

H Angle: 111.9°

V Angle: 109.7°

Lumens: 11259

Efficiency: 94.3%

**Spill:**

Lumens: 683.4

Efficiency: 5.7%

— Vertical Distribution through 0-Deg

- - Horizontal Distribution through 30-Deg

REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI

FIELD  
BEAM

**CANDELA DISTRIBUTION:**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 1.9    | 1.9    | 1.9    | 1.9    | 1.9    | 1.9    | 1.9    |
| 85°    | 0.0    | 1.9    | 1.9    | 1.9    | 3.8    | 3.8    | 3.8    | 3.8    | 3.8    | 3.8    | 5.7    |
| 82.5°  | 0.0    | 1.9    | 1.9    | 1.9    | 3.8    | 3.8    | 3.8    | 3.8    | 5.7    | 5.7    | 7.6    |
| 80°    | 1.9    | 1.9    | 1.9    | 1.9    | 3.8    | 3.8    | 3.8    | 5.7    | 5.7    | 7.6    | 7.6    |
| 77.5°  | 1.9    | 1.9    | 1.9    | 3.8    | 3.8    | 3.8    | 5.7    | 5.7    | 7.6    | 7.6    | 9.5    |
| 75°    | 1.9    | 1.9    | 1.9    | 3.8    | 3.8    | 5.7    | 5.7    | 5.7    | 7.6    | 7.6    | 9.5    |
| 72.5°  | 0.0    | 1.9    | 1.9    | 3.8    | 3.8    | 5.7    | 5.7    | 5.7    | 7.6    | 7.6    | 7.6    |
| 70°    | 1.9    | 1.9    | 1.9    | 3.8    | 3.8    | 5.7    | 5.7    | 5.7    | 7.6    | 7.6    | 7.6    |
| 67.5°  | 1.9    | 1.9    | 1.9    | 3.8    | 3.8    | 5.7    | 5.7    | 7.6    | 7.6    | 7.6    | 9.5    |
| 65°    | 1.9    | 1.9    | 1.9    | 3.8    | 5.7    | 5.7    | 7.6    | 9.5    | 9.5    | 11.4   | 13.3   |
| 62.5°  | 1.9    | 3.8    | 3.8    | 5.7    | 7.6    | 9.5    | 20.9   | 32.3   | 32.3   | 22.8   | 19.0   |
| 60°    | 226.3  | 245.3  | 243.4  | 220.5  | 192.0  | 161.6  | 155.9  | 150.2  | 138.8  | 121.7  | 127.4  |
| 57.5°  | 429.7  | 452.5  | 462.0  | 456.3  | 441.1  | 414.5  | 399.3  | 382.2  | 359.3  | 332.7  | 302.3  |
| 55°    | 813.7  | 823.3  | 802.3  | 762.4  | 718.7  | 675.0  | 659.7  | 636.9  | 602.7  | 568.5  | 522.9  |
| 52.5°  | 1203.5 | 1235.8 | 1226.3 | 1186.4 | 1127.5 | 1049.5 | 963.9  | 897.4  | 857.5  | 819.4  | 773.8  |
| 50°    | 1469.7 | 1483.0 | 1509.6 | 1557.1 | 1574.3 | 1521.0 | 1382.2 | 1203.5 | 1076.1 | 1140.8 | 1091.3 |
| 47.5°  | 2319.6 | 2386.1 | 2372.8 | 2338.6 | 2281.5 | 2137.0 | 1943.1 | 1783.4 | 1650.3 | 1606.6 | 1614.2 |
| 45°    | 2850.0 | 2876.6 | 2867.1 | 2851.9 | 2825.3 | 2690.3 | 2475.5 | 2230.2 | 2106.6 | 2057.2 | 2005.8 |
| 42.5°  | 3285.4 | 3313.9 | 3319.6 | 3321.5 | 3293.0 | 3169.4 | 2975.5 | 2730.2 | 2606.6 | 2464.1 | 2351.9 |
| 40°    | 4116.3 | 4158.1 | 4110.6 | 4047.8 | 3952.8 | 3812.1 | 3621.9 | 3395.7 | 3177.0 | 3002.1 | 2869.0 |
| 37.5°  | 4646.7 | 4698.1 | 4717.1 | 4713.3 | 4692.3 | 4631.5 | 4397.7 | 4182.8 | 3848.2 | 3456.5 | 3526.9 |
| 35°    | 5905.4 | 5958.6 | 5943.4 | 5886.4 | 5855.9 | 5791.3 | 5563.1 | 5308.4 | 4888.2 | 4462.3 | 4348.2 |
| 32.5°  | 7781.9 | 7897.9 | 7681.2 | 7443.5 | 7297.1 | 7348.4 | 7116.5 | 6492.9 | 6298.9 | 5530.8 | 5175.3 |
| 30°    | 8337.1 | 8335.2 | 8224.9 | 8128.0 | 8008.2 | 7983.5 | 7546.2 | 7048.0 | 6572.7 | 6034.7 | 5585.9 |
| 27.5°  | 8167.9 | 8133.7 | 8040.5 | 7970.1 | 7858.0 | 7799.0 | 7371.2 | 6975.8 | 6426.3 | 5945.3 | 5511.8 |
| 25°    | 7515.7 | 7542.4 | 7447.3 | 7434.0 | 7390.3 | 7276.2 | 7063.2 | 6618.3 | 6127.8 | 5595.5 | 5283.6 |
| 22.5°  | 7179.2 | 7169.7 | 7055.6 | 6989.1 | 7042.3 | 6920.6 | 6835.1 | 6386.4 | 5874.9 | 5426.2 | 5051.7 |
| 20°    | 6631.7 | 6633.6 | 6605.0 | 6599.3 | 6567.0 | 6511.9 | 6443.4 | 6125.9 | 5764.7 | 5380.6 | 4930.0 |
| 17.5°  | 6937.8 | 7015.7 | 7049.9 | 6766.6 | 6846.5 | 6783.8 | 6711.5 | 6268.5 | 5996.6 | 5656.3 | 5068.8 |
| 15°    | 7386.5 | 7357.9 | 7323.7 | 7308.5 | 7264.8 | 7205.8 | 7074.6 | 6721.0 | 6253.3 | 5901.6 | 5443.4 |
| 12.5°  | 7409.3 | 7354.1 | 7340.8 | 7338.9 | 7293.3 | 7211.5 | 7084.2 | 6791.4 | 6376.9 | 5949.1 | 5576.4 |
| 10°    | 7458.7 | 7401.7 | 7394.1 | 7403.6 | 7333.2 | 7281.9 | 7154.5 | 6882.6 | 6414.9 | 6030.8 | 5679.1 |
| 7.5°   | 7538.6 | 7443.5 | 7487.2 | 7458.7 | 7426.4 | 7344.6 | 7207.7 | 6941.6 | 6553.7 | 6139.2 | 5770.4 |
| 5°     | 7559.5 | 7454.9 | 7502.4 | 7475.8 | 7428.3 | 7348.4 | 7200.1 | 6979.6 | 6639.3 | 6182.9 | 5806.5 |
| 2.5°   | 7508.1 | 7477.7 | 7456.8 | 7407.4 | 7386.5 | 7299.0 | 7158.3 | 6922.5 | 6599.3 | 6163.9 | 5798.9 |
| 0°     | 7454.9 | 7481.5 | 7434.0 | 7384.6 | 7375.0 | 7304.7 | 7184.9 | 6972.0 | 6692.5 | 6217.2 | 5863.5 |
| -2.5°  | 7466.3 | 7445.4 | 7413.1 | 7361.7 | 7312.3 | 7211.5 | 7103.2 | 6903.5 | 6603.1 | 6101.2 | 5772.3 |
| -5°    | 7466.3 | 7369.3 | 7373.1 | 7375.0 | 7325.6 | 7221.0 | 7089.9 | 6920.6 | 6549.9 | 6099.3 | 5745.7 |
| -7.5°  | 7321.8 | 7238.2 | 7224.8 | 7213.4 | 7200.1 | 7103.2 | 7000.5 | 6789.5 | 6460.5 | 6049.9 | 5671.5 |
| -10°   | 7108.9 | 7027.1 | 7034.7 | 7017.6 | 6975.8 | 6911.1 | 6833.2 | 6643.1 | 6373.1 | 5894.0 | 5521.3 |
| -12.5° | 6842.7 | 6806.6 | 6785.7 | 6757.1 | 6715.3 | 6658.3 | 6578.4 | 6399.7 | 6110.7 | 5701.9 | 5348.3 |
| -15°   | 6527.1 | 6500.5 | 6481.5 | 6464.3 | 6403.5 | 6344.6 | 6240.0 | 6074.6 | 5894.0 | 5454.8 | 5093.5 |
| -17.5° | 6211.5 | 6144.9 | 6118.3 | 6095.5 | 6055.6 | 5960.5 | 5865.4 | 5741.9 | 5489.0 | 5141.1 | 4831.1 |
| -20°   | 5806.5 | 5766.6 | 5734.2 | 5703.8 | 5646.8 | 5572.6 | 5494.7 | 5352.1 | 5133.4 | 4852.1 | 4530.7 |

REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| -22.5° | 5382.5 | 5359.7 | 5333.1 | 5295.1 | 5257.0 | 5186.7 | 5078.3 | 4941.4 | 4770.3 | 4466.1 | 4165.7 |
| -25°   | 4945.2 | 4901.5 | 4869.2 | 4833.0 | 4802.6 | 4738.0 | 4633.4 | 4502.2 | 4287.4 | 4025.0 | 3774.0 |
| -27.5° | 4430.0 | 4388.1 | 4371.0 | 4329.2 | 4302.6 | 4243.6 | 4139.1 | 4017.4 | 3823.5 | 3602.9 | 3348.1 |
| -30°   | 3848.2 | 3855.8 | 3836.8 | 3796.8 | 3764.5 | 3688.5 | 3608.6 | 3506.0 | 3353.9 | 3142.8 | 2914.7 |
| -32.5° | 3310.1 | 3319.6 | 3296.8 | 3255.0 | 3213.2 | 3158.0 | 3083.9 | 2990.7 | 2876.6 | 2675.1 | 2477.4 |
| -35°   | 2772.1 | 2768.3 | 2749.2 | 2724.5 | 2696.0 | 2650.4 | 2566.7 | 2496.4 | 2365.2 | 2224.5 | 2087.6 |
| -37.5° | 2289.1 | 2298.6 | 2292.9 | 2279.6 | 2247.3 | 2209.3 | 2140.8 | 2076.2 | 1979.2 | 1855.6 | 1749.2 |
| -40°   | 1907.0 | 1918.4 | 1910.8 | 1897.5 | 1869.0 | 1846.1 | 1800.5 | 1743.5 | 1665.5 | 1559.0 | 1469.7 |
| -42.5° | 1614.2 | 1621.8 | 1612.3 | 1600.9 | 1576.2 | 1559.0 | 1522.9 | 1475.4 | 1410.7 | 1329.0 | 1249.1 |
| -45°   | 1382.2 | 1384.1 | 1374.6 | 1367.0 | 1348.0 | 1327.1 | 1296.7 | 1258.6 | 1207.3 | 1150.3 | 1085.6 |
| -47.5° | 1199.7 | 1197.8 | 1188.3 | 1180.7 | 1165.5 | 1146.5 | 1121.8 | 1087.5 | 1047.6 | 1003.9 | 952.5  |
| -50°   | 1040.0 | 1049.5 | 1045.7 | 1038.1 | 1026.7 | 1013.4 | 988.7  | 952.5  | 912.6  | 880.3  | 844.2  |
| -52.5° | 929.7  | 931.6  | 929.7  | 929.7  | 927.8  | 918.3  | 889.8  | 853.7  | 809.9  | 781.4  | 751.0  |
| -55°   | 827.1  | 836.6  | 840.4  | 844.2  | 846.1  | 846.1  | 811.8  | 773.8  | 732.0  | 703.5  | 680.7  |
| -57.5° | 743.4  | 749.1  | 752.9  | 762.4  | 770.0  | 775.7  | 745.3  | 711.1  | 678.8  | 652.1  | 631.2  |
| -60°   | 671.2  | 678.8  | 684.5  | 694.0  | 699.7  | 703.5  | 684.5  | 661.6  | 642.6  | 625.5  | 595.1  |
| -62.5° | 606.5  | 612.2  | 617.9  | 623.6  | 629.3  | 633.1  | 625.5  | 614.1  | 604.6  | 597.0  | 559.0  |
| -65°   | 541.9  | 547.6  | 553.3  | 560.9  | 566.6  | 570.4  | 568.5  | 560.9  | 553.3  | 545.7  | 511.4  |
| -67.5° | 482.9  | 488.6  | 496.2  | 498.1  | 501.9  | 503.8  | 500.0  | 494.3  | 484.8  | 475.3  | 448.7  |
| -70°   | 420.2  | 424.0  | 427.8  | 427.8  | 427.8  | 425.9  | 422.1  | 414.5  | 405.0  | 391.7  | 370.7  |
| -72.5° | 363.1  | 366.9  | 370.7  | 365.0  | 361.2  | 355.5  | 349.8  | 340.3  | 330.8  | 321.3  | 309.9  |
| -75°   | 309.9  | 311.8  | 311.8  | 304.2  | 298.5  | 292.8  | 285.2  | 279.5  | 270.0  | 262.4  | 252.9  |
| -77.5° | 247.2  | 247.2  | 247.2  | 241.5  | 237.7  | 233.9  | 228.2  | 222.4  | 214.8  | 209.1  | 201.5  |
| -80°   | 192.0  | 192.0  | 192.0  | 190.1  | 184.4  | 180.6  | 176.8  | 173.0  | 167.3  | 163.5  | 159.7  |
| -82.5° | 146.4  | 146.4  | 146.4  | 144.5  | 140.7  | 138.8  | 135.0  | 131.2  | 129.3  | 125.5  | 123.6  |
| -85°   | 106.5  | 108.4  | 108.4  | 106.5  | 104.6  | 100.8  | 98.9   | 97.0   | 95.1   | 93.2   | 89.4   |
| -87.5° | 72.2   | 72.2   | 72.2   | 70.3   | 68.4   | 68.4   | 66.5   | 62.7   | 58.9   | 57.0   | 55.1   |
| -90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI

**CANDELA DISTRIBUTION (continued):**

|        | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5°  | 1.9    | 1.9    | 1.9    | 1.9    | 1.9    | 1.9    | 1.9    | 1.9    | 1.9    | 1.9    | 1.9    |
| 85°    | 5.7    | 5.7    | 5.7    | 7.6    | 7.6    | 7.6    | 7.6    | 7.6    | 7.6    | 7.6    | 5.7    |
| 82.5°  | 9.5    | 9.5    | 11.4   | 11.4   | 13.3   | 13.3   | 13.3   | 13.3   | 13.3   | 13.3   | 13.3   |
| 80°    | 9.5    | 11.4   | 13.3   | 15.2   | 17.1   | 19.0   | 19.0   | 19.0   | 19.0   | 17.1   | 17.1   |
| 77.5°  | 11.4   | 11.4   | 13.3   | 15.2   | 17.1   | 19.0   | 20.9   | 22.8   | 20.9   | 20.9   | 20.9   |
| 75°    | 11.4   | 13.3   | 13.3   | 15.2   | 17.1   | 19.0   | 20.9   | 22.8   | 22.8   | 22.8   | 22.8   |
| 72.5°  | 9.5    | 11.4   | 13.3   | 15.2   | 15.2   | 17.1   | 19.0   | 19.0   | 20.9   | 20.9   | 22.8   |
| 70°    | 9.5    | 11.4   | 13.3   | 13.3   | 15.2   | 15.2   | 17.1   | 19.0   | 19.0   | 20.9   | 20.9   |
| 67.5°  | 11.4   | 13.3   | 13.3   | 15.2   | 17.1   | 17.1   | 17.1   | 19.0   | 19.0   | 20.9   | 20.9   |
| 65°    | 13.3   | 15.2   | 15.2   | 17.1   | 19.0   | 19.0   | 20.9   | 20.9   | 20.9   | 22.8   | 22.8   |
| 62.5°  | 22.8   | 22.8   | 22.8   | 20.9   | 22.8   | 22.8   | 22.8   | 24.7   | 24.7   | 22.8   | 24.7   |
| 60°    | 117.9  | 85.6   | 58.9   | 74.1   | 66.5   | 30.4   | 30.4   | 30.4   | 28.5   | 28.5   | 26.6   |
| 57.5°  | 277.6  | 258.6  | 222.4  | 188.2  | 169.2  | 150.2  | 93.2   | 38.0   | 38.0   | 34.2   | 30.4   |
| 55°    | 463.9  | 401.2  | 374.6  | 328.9  | 279.5  | 256.7  | 212.9  | 144.5  | 68.4   | 45.6   | 39.9   |
| 52.5°  | 718.7  | 659.7  | 591.3  | 498.1  | 431.6  | 378.4  | 342.2  | 271.9  | 182.5  | 97.0   | 60.8   |
| 50°    | 962.0  | 935.4  | 893.6  | 802.3  | 663.5  | 574.2  | 515.2  | 435.4  | 327.0  | 199.6  | 114.1  |
| 47.5°  | 1549.5 | 1327.1 | 1192.1 | 1121.8 | 1005.8 | 836.6  | 722.5  | 633.1  | 501.9  | 336.5  | 201.5  |
| 45°    | 1950.7 | 1810.0 | 1595.2 | 1446.9 | 1275.8 | 1097.0 | 948.7  | 846.1  | 690.2  | 503.8  | 315.6  |
| 42.5°  | 2294.8 | 2173.2 | 1979.2 | 1762.5 | 1581.9 | 1348.0 | 1157.9 | 1022.9 | 891.7  | 688.3  | 471.5  |
| 40°    | 2737.8 | 2593.3 | 2407.0 | 2196.0 | 1984.9 | 1686.4 | 1378.4 | 1214.9 | 1070.4 | 889.8  | 636.9  |
| 37.5°  | 3467.9 | 3213.2 | 2909.0 | 2675.1 | 2399.4 | 2146.5 | 1724.5 | 1435.5 | 1264.3 | 1076.1 | 830.9  |
| 35°    | 4346.3 | 4066.8 | 3559.2 | 3249.3 | 2880.4 | 2504.0 | 2123.7 | 1695.9 | 1452.6 | 1252.9 | 1009.6 |
| 32.5°  | 5163.9 | 4755.1 | 4104.9 | 3741.7 | 3496.4 | 2802.5 | 2408.9 | 2038.2 | 1646.5 | 1401.2 | 1112.2 |
| 30°    | 5390.1 | 4939.5 | 4473.7 | 4049.7 | 3631.4 | 3070.6 | 2604.7 | 2315.8 | 1889.9 | 1490.6 | 1209.2 |
| 27.5°  | 5162.0 | 4852.1 | 4490.8 | 4097.2 | 3644.7 | 3163.7 | 2724.5 | 2448.8 | 2068.6 | 1551.4 | 1285.3 |
| 25°    | 4930.0 | 4606.8 | 4353.9 | 4025.0 | 3606.7 | 3158.0 | 2728.3 | 2532.5 | 2207.4 | 1669.3 | 1327.1 |
| 22.5°  | 4684.7 | 4483.2 | 4274.1 | 3907.1 | 3511.7 | 3175.1 | 2851.9 | 2604.7 | 2279.6 | 1802.4 | 1344.2 |
| 20°    | 4698.1 | 4566.9 | 4336.8 | 3846.3 | 3494.5 | 3275.9 | 3000.2 | 2696.0 | 2357.6 | 1918.4 | 1357.5 |
| 17.5°  | 4911.0 | 4739.9 | 4450.9 | 4025.0 | 3648.5 | 3378.6 | 3123.8 | 2821.5 | 2437.4 | 2021.1 | 1519.1 |
| 15°    | 5173.4 | 4912.9 | 4610.6 | 4236.0 | 3810.2 | 3490.7 | 3218.9 | 2909.0 | 2528.7 | 2116.1 | 1663.6 |
| 12.5°  | 5363.5 | 4992.8 | 4709.5 | 4371.0 | 3985.1 | 3612.4 | 3281.6 | 2975.5 | 2614.3 | 2194.1 | 1772.0 |
| 10°    | 5428.1 | 5091.6 | 4757.0 | 4454.7 | 4074.4 | 3677.1 | 3329.1 | 3017.3 | 2688.4 | 2254.9 | 1851.8 |
| 7.5°   | 5462.4 | 5177.2 | 4789.3 | 4492.7 | 4127.7 | 3717.0 | 3367.2 | 3040.1 | 2747.3 | 2296.7 | 1903.2 |
| 5°     | 5458.6 | 5222.8 | 4814.0 | 4504.1 | 4156.2 | 3734.1 | 3393.8 | 3045.8 | 2789.2 | 2332.9 | 1933.6 |
| 2.5°   | 5441.5 | 5253.2 | 4854.0 | 4523.1 | 4213.2 | 3766.4 | 3445.1 | 3057.3 | 2804.4 | 2372.8 | 1954.5 |
| 0°     | 5504.2 | 5255.1 | 4895.8 | 4528.8 | 4251.3 | 3777.8 | 3467.9 | 3047.7 | 2783.5 | 2384.2 | 1952.6 |
| -2.5°  | 5369.2 | 5143.0 | 4886.3 | 4479.4 | 4199.9 | 3751.2 | 3426.1 | 3017.3 | 2737.8 | 2370.9 | 1945.0 |
| -5°    | 5346.4 | 5061.2 | 4806.4 | 4433.8 | 4114.4 | 3696.1 | 3348.1 | 2960.3 | 2665.6 | 2327.2 | 1914.6 |
| -7.5°  | 5285.5 | 4983.2 | 4728.5 | 4397.7 | 4034.5 | 3639.0 | 3274.0 | 2901.3 | 2587.6 | 2258.7 | 1870.9 |
| -10°   | 5152.5 | 4863.5 | 4644.8 | 4319.7 | 3937.5 | 3557.3 | 3184.6 | 2823.4 | 2496.4 | 2165.6 | 1802.4 |
| -12.5° | 4962.3 | 4673.3 | 4456.6 | 4154.3 | 3815.9 | 3447.0 | 3078.2 | 2722.6 | 2391.8 | 2066.7 | 1720.7 |
| -15°   | 4747.5 | 4454.7 | 4237.9 | 3962.3 | 3635.2 | 3275.9 | 2943.2 | 2595.2 | 2272.0 | 1962.1 | 1623.7 |
| -17.5° | 4504.1 | 4226.5 | 4017.4 | 3749.3 | 3424.2 | 3082.0 | 2751.1 | 2435.5 | 2133.2 | 1853.7 | 1511.5 |
| -20°   | 4222.7 | 3952.8 | 3760.7 | 3492.6 | 3194.1 | 2861.4 | 2540.1 | 2241.6 | 1969.7 | 1707.3 | 1387.9 |

REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI

**CANDELA DISTRIBUTION (continued):**

|        | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| -22.5° | 3874.8 | 3637.1 | 3418.5 | 3178.9 | 2918.5 | 2614.3 | 2315.8 | 2051.5 | 1791.0 | 1534.3 | 1260.5 |
| -25°   | 3519.3 | 3289.2 | 3076.3 | 2857.6 | 2608.6 | 2346.2 | 2091.4 | 1851.8 | 1597.1 | 1365.1 | 1137.0 |
| -27.5° | 3123.8 | 2918.5 | 2728.3 | 2526.8 | 2298.6 | 2072.4 | 1863.3 | 1629.4 | 1408.8 | 1211.1 | 1015.3 |
| -30°   | 2701.7 | 2534.4 | 2369.0 | 2190.3 | 2005.8 | 1815.7 | 1629.4 | 1408.8 | 1235.8 | 1078.0 | 912.6  |
| -32.5° | 2296.7 | 2146.5 | 2013.5 | 1880.4 | 1720.7 | 1564.8 | 1399.3 | 1235.8 | 1091.3 | 952.5  | 813.7  |
| -35°   | 1941.2 | 1781.5 | 1707.3 | 1600.9 | 1473.5 | 1332.8 | 1197.8 | 1083.7 | 967.7  | 842.3  | 718.7  |
| -37.5° | 1633.2 | 1530.5 | 1443.1 | 1363.2 | 1262.4 | 1140.8 | 1043.8 | 950.6  | 853.7  | 739.6  | 633.1  |
| -40°   | 1391.7 | 1317.6 | 1230.1 | 1171.2 | 1089.4 | 1002.0 | 905.0  | 827.1  | 745.3  | 652.1  | 564.7  |
| -42.5° | 1197.8 | 1137.0 | 1079.9 | 1017.2 | 956.3  | 882.2  | 798.5  | 724.4  | 650.2  | 581.8  | 509.5  |
| -45°   | 1038.1 | 994.4  | 948.7  | 897.4  | 844.2  | 779.5  | 711.1  | 635.0  | 581.8  | 520.9  | 460.1  |
| -47.5° | 906.9  | 874.6  | 836.6  | 796.6  | 751.0  | 694.0  | 631.2  | 576.1  | 520.9  | 469.6  | 410.7  |
| -50°   | 802.3  | 771.9  | 741.5  | 707.3  | 667.3  | 617.9  | 570.4  | 519.0  | 467.7  | 418.3  | 363.1  |
| -52.5° | 714.9  | 688.3  | 663.5  | 635.0  | 597.0  | 555.2  | 511.4  | 465.8  | 418.3  | 368.8  | 325.1  |
| -55°   | 654.0  | 623.6  | 598.9  | 570.4  | 536.2  | 496.2  | 456.3  | 414.5  | 368.8  | 330.8  | 294.7  |
| -57.5° | 604.6  | 570.4  | 541.9  | 511.4  | 477.2  | 443.0  | 406.9  | 368.8  | 334.6  | 298.5  | 264.3  |
| -60°   | 562.8  | 522.9  | 490.5  | 460.1  | 427.8  | 395.5  | 365.0  | 332.7  | 300.4  | 268.1  | 233.9  |
| -62.5° | 519.0  | 477.2  | 437.3  | 408.8  | 384.1  | 355.5  | 328.9  | 298.5  | 270.0  | 237.7  | 212.9  |
| -65°   | 469.6  | 429.7  | 391.7  | 366.9  | 344.1  | 319.4  | 294.7  | 268.1  | 243.4  | 218.6  | 195.8  |
| -67.5° | 414.5  | 380.3  | 353.6  | 330.8  | 308.0  | 287.1  | 264.3  | 241.5  | 220.5  | 195.8  | 173.0  |
| -70°   | 347.9  | 328.9  | 313.7  | 296.6  | 275.7  | 256.7  | 235.8  | 214.8  | 192.0  | 171.1  | 150.2  |
| -72.5° | 296.6  | 285.2  | 273.8  | 256.7  | 237.7  | 220.5  | 203.4  | 184.4  | 165.4  | 146.4  | 129.3  |
| -75°   | 243.4  | 233.9  | 224.4  | 212.9  | 197.7  | 184.4  | 169.2  | 152.1  | 136.9  | 123.6  | 110.3  |
| -77.5° | 195.8  | 188.2  | 182.5  | 173.0  | 161.6  | 150.2  | 140.7  | 129.3  | 117.9  | 104.6  | 91.3   |
| -80°   | 155.9  | 152.1  | 150.2  | 146.4  | 136.9  | 127.4  | 119.8  | 110.3  | 98.9   | 89.4   | 79.9   |
| -82.5° | 121.7  | 121.7  | 119.8  | 117.9  | 110.3  | 102.7  | 97.0   | 89.4   | 81.8   | 74.1   | 64.6   |
| -85°   | 89.4   | 87.5   | 87.5   | 85.6   | 79.9   | 76.1   | 70.3   | 66.5   | 60.8   | 53.2   | 49.4   |
| -87.5° | 53.2   | 51.3   | 49.4   | 47.5   | 43.7   | 41.8   | 38.0   | 36.1   | 32.3   | 28.5   | 26.6   |
| -90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI

**CANDELA DISTRIBUTION (continued):**

|        | 55°    | 57.5°  | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°  | 77.5° | 80°  |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|------|-------|------|
| 90°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  |
| 87.5°  | 1.9    | 1.9    | 1.9   | 1.9   | 1.9   | 1.9   | 1.9   | 1.9   | 1.9  | 0.0   | 0.0  |
| 85°    | 5.7    | 3.8    | 3.8   | 3.8   | 3.8   | 3.8   | 1.9   | 1.9   | 1.9  | 1.9   | 1.9  |
| 82.5°  | 11.4   | 11.4   | 9.5   | 9.5   | 7.6   | 5.7   | 3.8   | 3.8   | 3.8  | 1.9   | 1.9  |
| 80°    | 17.1   | 17.1   | 17.1  | 15.2  | 13.3  | 9.5   | 7.6   | 5.7   | 3.8  | 1.9   | 1.9  |
| 77.5°  | 20.9   | 19.0   | 19.0  | 17.1  | 17.1  | 15.2  | 11.4  | 9.5   | 5.7  | 3.8   | 1.9  |
| 75°    | 20.9   | 20.9   | 20.9  | 19.0  | 19.0  | 17.1  | 15.2  | 11.4  | 9.5  | 5.7   | 3.8  |
| 72.5°  | 22.8   | 20.9   | 20.9  | 20.9  | 19.0  | 17.1  | 15.2  | 13.3  | 11.4 | 7.6   | 3.8  |
| 70°    | 20.9   | 20.9   | 20.9  | 20.9  | 19.0  | 19.0  | 15.2  | 13.3  | 13.3 | 7.6   | 5.7  |
| 67.5°  | 20.9   | 20.9   | 20.9  | 19.0  | 19.0  | 17.1  | 15.2  | 13.3  | 13.3 | 9.5   | 5.7  |
| 65°    | 22.8   | 20.9   | 20.9  | 20.9  | 19.0  | 17.1  | 15.2  | 13.3  | 13.3 | 11.4  | 7.6  |
| 62.5°  | 24.7   | 22.8   | 22.8  | 20.9  | 19.0  | 17.1  | 15.2  | 13.3  | 13.3 | 11.4  | 7.6  |
| 60°    | 26.6   | 24.7   | 22.8  | 22.8  | 20.9  | 19.0  | 15.2  | 15.2  | 13.3 | 11.4  | 7.6  |
| 57.5°  | 28.5   | 26.6   | 26.6  | 24.7  | 22.8  | 20.9  | 17.1  | 15.2  | 13.3 | 11.4  | 9.5  |
| 55°    | 34.2   | 30.4   | 28.5  | 28.5  | 26.6  | 22.8  | 19.0  | 15.2  | 13.3 | 11.4  | 9.5  |
| 52.5°  | 45.6   | 36.1   | 32.3  | 32.3  | 30.4  | 26.6  | 20.9  | 17.1  | 13.3 | 11.4  | 9.5  |
| 50°    | 72.2   | 45.6   | 38.0  | 34.2  | 34.2  | 30.4  | 24.7  | 19.0  | 13.3 | 11.4  | 9.5  |
| 47.5°  | 114.1  | 76.1   | 45.6  | 39.9  | 38.0  | 36.1  | 28.5  | 19.0  | 15.2 | 11.4  | 9.5  |
| 45°    | 188.2  | 112.2  | 74.1  | 47.5  | 39.9  | 38.0  | 32.3  | 20.9  | 15.2 | 13.3  | 9.5  |
| 42.5°  | 258.6  | 174.9  | 114.1 | 57.0  | 47.5  | 41.8  | 34.2  | 22.8  | 17.1 | 13.3  | 9.5  |
| 40°    | 406.9  | 239.6  | 159.7 | 93.2  | 55.1  | 43.7  | 38.0  | 26.6  | 17.1 | 13.3  | 9.5  |
| 37.5°  | 551.4  | 317.5  | 214.8 | 136.9 | 62.7  | 49.4  | 39.9  | 28.5  | 19.0 | 13.3  | 11.4 |
| 35°    | 695.9  | 444.9  | 266.2 | 182.5 | 83.7  | 58.9  | 41.8  | 30.4  | 19.0 | 13.3  | 11.4 |
| 32.5°  | 825.2  | 564.7  | 319.4 | 228.2 | 125.5 | 70.3  | 45.6  | 32.3  | 20.9 | 15.2  | 11.4 |
| 30°    | 931.6  | 675.0  | 414.5 | 268.1 | 163.5 | 85.6  | 49.4  | 32.3  | 22.8 | 15.2  | 11.4 |
| 27.5°  | 1011.5 | 760.5  | 511.4 | 309.9 | 195.8 | 100.8 | 57.0  | 36.1  | 22.8 | 15.2  | 11.4 |
| 25°    | 1076.1 | 827.1  | 597.0 | 353.6 | 224.4 | 125.5 | 68.4  | 38.0  | 24.7 | 17.1  | 11.4 |
| 22.5°  | 1127.5 | 882.2  | 667.3 | 412.6 | 258.6 | 150.2 | 83.7  | 41.8  | 24.7 | 17.1  | 11.4 |
| 20°    | 1197.8 | 937.3  | 714.9 | 475.3 | 294.7 | 173.0 | 97.0  | 45.6  | 24.7 | 17.1  | 13.3 |
| 17.5°  | 1258.6 | 992.5  | 752.9 | 528.6 | 330.8 | 190.1 | 112.2 | 49.4  | 26.6 | 17.1  | 13.3 |
| 15°    | 1329.0 | 1045.7 | 787.1 | 570.4 | 365.0 | 205.3 | 125.5 | 53.2  | 26.6 | 19.0  | 13.3 |
| 12.5°  | 1405.0 | 1095.1 | 811.8 | 604.6 | 401.2 | 218.6 | 136.9 | 60.8  | 28.5 | 19.0  | 13.3 |
| 10°    | 1483.0 | 1137.0 | 832.8 | 629.3 | 427.8 | 232.0 | 144.5 | 68.4  | 30.4 | 19.0  | 13.3 |
| 7.5°   | 1560.9 | 1175.0 | 859.4 | 640.7 | 439.2 | 247.2 | 148.3 | 76.1  | 30.4 | 20.9  | 13.3 |
| 5°     | 1614.2 | 1199.7 | 897.4 | 648.3 | 444.9 | 264.3 | 154.0 | 85.6  | 32.3 | 20.9  | 13.3 |
| 2.5°   | 1659.8 | 1214.9 | 937.3 | 654.0 | 446.8 | 273.8 | 152.1 | 91.3  | 34.2 | 20.9  | 13.3 |
| 0°     | 1680.7 | 1214.9 | 963.9 | 650.2 | 441.1 | 283.3 | 152.1 | 97.0  | 34.2 | 20.9  | 13.3 |
| -2.5°  | 1648.4 | 1249.1 | 956.3 | 652.1 | 443.0 | 283.3 | 159.7 | 98.9  | 38.0 | 22.8  | 13.3 |
| -5°    | 1597.1 | 1262.4 | 933.5 | 642.6 | 439.2 | 283.3 | 169.2 | 100.8 | 39.9 | 22.8  | 15.2 |
| -7.5°  | 1547.6 | 1268.2 | 906.9 | 633.1 | 433.5 | 275.7 | 171.1 | 98.9  | 43.7 | 24.7  | 15.2 |
| -10°   | 1483.0 | 1205.4 | 872.7 | 616.0 | 422.1 | 270.0 | 174.9 | 98.9  | 45.6 | 24.7  | 15.2 |
| -12.5° | 1408.8 | 1129.4 | 830.9 | 591.3 | 408.8 | 264.3 | 176.8 | 98.9  | 47.5 | 26.6  | 15.2 |
| -15°   | 1323.3 | 1051.4 | 783.3 | 564.7 | 389.8 | 256.7 | 173.0 | 97.0  | 49.4 | 26.6  | 17.1 |
| -17.5° | 1226.3 | 975.4  | 733.9 | 532.4 | 368.8 | 247.2 | 165.4 | 95.1  | 49.4 | 26.6  | 17.1 |
| -20°   | 1116.0 | 899.3  | 678.8 | 500.0 | 344.1 | 235.8 | 157.8 | 91.3  | 49.4 | 26.6  | 17.1 |

REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI

**CANDELA DISTRIBUTION (continued):**

|        | 55°    | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°  | 77.5° | 80°  |
|--------|--------|-------|-------|-------|-------|-------|-------|-------|------|-------|------|
| -22.5° | 1017.2 | 829.0 | 621.7 | 463.9 | 317.5 | 222.4 | 148.3 | 87.5  | 49.4 | 28.5  | 17.1 |
| -25°   | 935.4  | 760.5 | 578.0 | 427.8 | 289.0 | 207.2 | 138.8 | 83.7  | 49.4 | 28.5  | 17.1 |
| -27.5° | 849.9  | 686.4 | 532.4 | 393.6 | 270.0 | 193.9 | 129.3 | 79.9  | 47.5 | 28.5  | 17.1 |
| -30°   | 762.4  | 614.1 | 484.8 | 355.5 | 251.0 | 180.6 | 121.7 | 74.1  | 47.5 | 28.5  | 17.1 |
| -32.5° | 682.6  | 555.2 | 441.1 | 317.5 | 230.1 | 167.3 | 114.1 | 72.2  | 45.6 | 28.5  | 17.1 |
| -35°   | 604.6  | 501.9 | 395.5 | 287.1 | 207.2 | 154.0 | 106.5 | 70.3  | 45.6 | 28.5  | 17.1 |
| -37.5° | 540.0  | 452.5 | 353.6 | 266.2 | 193.9 | 142.6 | 98.9  | 66.5  | 43.7 | 28.5  | 17.1 |
| -40°   | 486.7  | 406.9 | 313.7 | 243.4 | 182.5 | 131.2 | 91.3  | 64.6  | 43.7 | 28.5  | 17.1 |
| -42.5° | 437.3  | 363.1 | 289.0 | 224.4 | 171.1 | 123.6 | 85.6  | 62.7  | 41.8 | 28.5  | 17.1 |
| -45°   | 393.6  | 325.1 | 264.3 | 207.2 | 157.8 | 114.1 | 81.8  | 58.9  | 39.9 | 28.5  | 19.0 |
| -47.5° | 349.8  | 298.5 | 241.5 | 192.0 | 144.5 | 102.7 | 78.0  | 57.0  | 38.0 | 26.6  | 19.0 |
| -50°   | 315.6  | 270.0 | 222.4 | 174.9 | 131.2 | 98.9  | 74.1  | 53.2  | 38.0 | 26.6  | 19.0 |
| -52.5° | 285.2  | 243.4 | 201.5 | 157.8 | 119.8 | 93.2  | 70.3  | 49.4  | 36.1 | 26.6  | 19.0 |
| -55°   | 256.7  | 218.6 | 180.6 | 140.7 | 112.2 | 87.5  | 64.6  | 45.6  | 36.1 | 26.6  | 19.0 |
| -57.5° | 228.2  | 195.8 | 159.7 | 127.4 | 102.7 | 81.8  | 60.8  | 45.6  | 36.1 | 26.6  | 19.0 |
| -60°   | 205.3  | 174.9 | 144.5 | 117.9 | 95.1  | 74.1  | 55.1  | 43.7  | 34.2 | 26.6  | 19.0 |
| -62.5° | 186.3  | 157.8 | 131.2 | 106.5 | 87.5  | 66.5  | 53.2  | 43.7  | 34.2 | 26.6  | 17.1 |
| -65°   | 167.3  | 142.6 | 117.9 | 97.0  | 78.0  | 62.7  | 51.3  | 41.8  | 34.2 | 26.6  | 17.1 |
| -67.5° | 148.3  | 125.5 | 106.5 | 85.6  | 72.2  | 60.8  | 49.4  | 41.8  | 32.3 | 24.7  | 17.1 |
| -70°   | 129.3  | 110.3 | 93.2  | 79.9  | 68.4  | 57.0  | 47.5  | 39.9  | 32.3 | 22.8  | 15.2 |
| -72.5° | 114.1  | 97.0  | 83.7  | 74.1  | 64.6  | 55.1  | 45.6  | 38.0  | 30.4 | 20.9  | 13.3 |
| -75°   | 97.0   | 85.6  | 76.1  | 66.5  | 58.9  | 51.3  | 43.7  | 34.2  | 26.6 | 19.0  | 13.3 |
| -77.5° | 81.8   | 74.1  | 66.5  | 60.8  | 53.2  | 45.6  | 38.0  | 30.4  | 24.7 | 17.1  | 11.4 |
| -80°   | 70.3   | 64.6  | 58.9  | 53.2  | 47.5  | 39.9  | 34.2  | 26.6  | 20.9 | 15.2  | 9.5  |
| -82.5° | 57.0   | 53.2  | 47.5  | 43.7  | 39.9  | 34.2  | 28.5  | 22.8  | 15.2 | 11.4  | 7.6  |
| -85°   | 43.7   | 39.9  | 38.0  | 34.2  | 30.4  | 24.7  | 19.0  | 15.2  | 11.4 | 7.6   | 3.8  |
| -87.5° | 22.8   | 20.9  | 19.0  | 17.1  | 15.2  | 11.4  | 9.5   | 7.6   | 5.7  | 3.8   | 1.9  |
| -90°   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  |

REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° |
|--------|-------|-----|-------|-----|
| 90°    | 0.0   | 0.0 | 0.0   | 0.0 |
| 87.5°  | 0.0   | 0.0 | 0.0   | 0.0 |
| 85°    | 0.0   | 0.0 | 0.0   | 0.0 |
| 82.5°  | 0.0   | 0.0 | 0.0   | 0.0 |
| 80°    | 1.9   | 0.0 | 0.0   | 0.0 |
| 77.5°  | 1.9   | 0.0 | 0.0   | 0.0 |
| 75°    | 1.9   | 1.9 | 0.0   | 0.0 |
| 72.5°  | 1.9   | 1.9 | 0.0   | 0.0 |
| 70°    | 1.9   | 1.9 | 0.0   | 0.0 |
| 67.5°  | 3.8   | 1.9 | 0.0   | 0.0 |
| 65°    | 3.8   | 1.9 | 0.0   | 0.0 |
| 62.5°  | 3.8   | 1.9 | 0.0   | 0.0 |
| 60°    | 3.8   | 1.9 | 0.0   | 0.0 |
| 57.5°  | 5.7   | 1.9 | 1.9   | 0.0 |
| 55°    | 5.7   | 1.9 | 1.9   | 0.0 |
| 52.5°  | 5.7   | 1.9 | 1.9   | 0.0 |
| 50°    | 5.7   | 3.8 | 1.9   | 0.0 |
| 47.5°  | 5.7   | 3.8 | 1.9   | 0.0 |
| 45°    | 5.7   | 3.8 | 1.9   | 0.0 |
| 42.5°  | 5.7   | 3.8 | 1.9   | 0.0 |
| 40°    | 7.6   | 3.8 | 1.9   | 0.0 |
| 37.5°  | 7.6   | 3.8 | 1.9   | 0.0 |
| 35°    | 7.6   | 3.8 | 1.9   | 0.0 |
| 32.5°  | 7.6   | 3.8 | 1.9   | 0.0 |
| 30°    | 7.6   | 3.8 | 1.9   | 0.0 |
| 27.5°  | 7.6   | 5.7 | 1.9   | 0.0 |
| 25°    | 7.6   | 5.7 | 1.9   | 0.0 |
| 22.5°  | 9.5   | 5.7 | 1.9   | 0.0 |
| 20°    | 9.5   | 5.7 | 1.9   | 0.0 |
| 17.5°  | 9.5   | 5.7 | 1.9   | 0.0 |
| 15°    | 9.5   | 5.7 | 1.9   | 0.0 |
| 12.5°  | 9.5   | 5.7 | 1.9   | 0.0 |
| 10°    | 9.5   | 5.7 | 1.9   | 0.0 |
| 7.5°   | 9.5   | 5.7 | 1.9   | 0.0 |
| 5°     | 9.5   | 5.7 | 1.9   | 0.0 |
| 2.5°   | 9.5   | 5.7 | 1.9   | 0.0 |
| 0°     | 9.5   | 5.7 | 1.9   | 0.0 |
| -2.5°  | 9.5   | 5.7 | 1.9   | 0.0 |
| -5°    | 9.5   | 5.7 | 1.9   | 0.0 |
| -7.5°  | 9.5   | 5.7 | 1.9   | 0.0 |
| -10°   | 9.5   | 5.7 | 1.9   | 0.0 |
| -12.5° | 11.4  | 5.7 | 1.9   | 0.0 |
| -15°   | 11.4  | 5.7 | 1.9   | 0.0 |
| -17.5° | 11.4  | 5.7 | 1.9   | 0.0 |
| -20°   | 11.4  | 5.7 | 1.9   | 0.0 |

REPORT NUMBER: P722540

CATALOG NUMBER: IFLD-S-SA2B-760-U-76-VI

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° |
|--------|-------|-----|-------|-----|
| -22.5° | 11.4  | 5.7 | 1.9   | 0.0 |
| -25°   | 11.4  | 5.7 | 1.9   | 0.0 |
| -27.5° | 11.4  | 5.7 | 1.9   | 0.0 |
| -30°   | 11.4  | 5.7 | 1.9   | 0.0 |
| -32.5° | 11.4  | 5.7 | 1.9   | 0.0 |
| -35°   | 11.4  | 5.7 | 1.9   | 0.0 |
| -37.5° | 11.4  | 5.7 | 1.9   | 0.0 |
| -40°   | 11.4  | 5.7 | 1.9   | 0.0 |
| -42.5° | 9.5   | 5.7 | 1.9   | 0.0 |
| -45°   | 11.4  | 5.7 | 1.9   | 0.0 |
| -47.5° | 11.4  | 5.7 | 1.9   | 0.0 |
| -50°   | 11.4  | 5.7 | 1.9   | 0.0 |
| -52.5° | 11.4  | 5.7 | 1.9   | 0.0 |
| -55°   | 11.4  | 5.7 | 1.9   | 0.0 |
| -57.5° | 11.4  | 5.7 | 1.9   | 0.0 |
| -60°   | 11.4  | 5.7 | 1.9   | 0.0 |
| -62.5° | 9.5   | 5.7 | 1.9   | 0.0 |
| -65°   | 9.5   | 3.8 | 1.9   | 0.0 |
| -67.5° | 9.5   | 3.8 | 1.9   | 0.0 |
| -70°   | 9.5   | 3.8 | 1.9   | 0.0 |
| -72.5° | 7.6   | 3.8 | 1.9   | 0.0 |
| -75°   | 7.6   | 3.8 | 1.9   | 0.0 |
| -77.5° | 5.7   | 1.9 | 0.0   | 0.0 |
| -80°   | 5.7   | 1.9 | 0.0   | 0.0 |
| -82.5° | 3.8   | 1.9 | 0.0   | 0.0 |
| -85°   | 1.9   | 1.9 | 0.0   | 0.0 |
| -87.5° | 1.9   | 0.0 | 0.0   | 0.0 |
| -90°   | 0.0   | 0.0 | 0.0   | 0.0 |

(END OF REPORT)