

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P980834

Luminaire Tested: **UFLD-S-CA1-50-750-U-66**

Issue Date: 04/10/2025

Test Information

Test Method: LM-79-08
Report Number: P980834
Test Lab: INNOVATION CENTER(G2)
Issue Date: 04/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: UFLD-S-CA1-50-750-U-66
Description: UTILITY FLOOD SMALL SIZE 50W 70CRI 5000K LED FIXTURE NEMA 6
Light Source: (1) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6828.8 lumens
Efficiency: N/A
Efficacy: 133.4 lumens/watt
Luminous Opening: Rectangular (W 0.42' x L: 0.31' x H: 0')
IES Classification: Type I - Short
BUG Rating: B3 - U0 - G1

Input Watts (W): 51.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 8.18%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P980834

CATALOG NUMBER: UFLD-S-CA1-50-750-U-66

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 12.7 fc

Type I - Short - N/A

REPORT NUMBER: P980834

CATALOG NUMBER: UFLD-S-CA1-50-750-U-66

Luminous Intensity Polar Plot



REPORT NUMBER: P980834

CATALOG NUMBER: UFLD-S-CA1-50-750-U-66

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3020.3	0.0	3020.3
	% Fixture	44.2	0.0	44.2
Street Side	Lumens	3808.5	0.0	3808.5
	% Fixture	55.8	0.0	55.8
Total	Lumens	6828.8	0.0	6828.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.7	4.0
10°-20°	789.9	11.6
20°-30°	1258.7	18.4
30°-40°	1573.6	23.0
40°-50°	1544.2	22.6
50°-60°	1104.0	16.2
60°-70°	244.3	3.6
70°-80°	37.5	0.5
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6828.8	100.0
0°-180°	6828.8	100.0

Coefficient of Utilization



REPORT NUMBER: P980834


CATALOG NUMBER: UFLD-S-CA1-50-750-U-66

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1270.1	18.6			
FM	(30°-60°)	2406.5	35.2			
FH	(60°-80°)	129.9	1.9			G0/660
FVH	(80°-90°)	2.0	0.0			G0/10
BL	(0°-30°)	1051.1	15.4	B3/2500		
BM	(30°-60°)	1815.4	26.6	B2/2500		
BH	(60°-80°)	151.9	2.2	B1/500		G1/500
BVH	(80°-90°)	2.0	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G1

Type I Short





REPORT NUMBER: P980834

CATALOG NUMBER: UFLD-S-CA1-50-750-U-66

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3
2.5°	2756.1	2760.6	2765.0	2771.7	2780.6	2785.1	2780.6	2776.2	2773.9	2778.4	2780.6
5°	2794.0	2800.7	2802.9	2807.4	2811.8	2807.4	2805.1	2800.7	2798.4	2800.7	2807.4
7.5°	2849.7	2854.1	2851.9	2849.7	2847.5	2831.9	2816.3	2809.6	2809.6	2816.3	2834.1
10°	2898.7	2907.6	2896.5	2887.6	2872.0	2847.5	2820.7	2805.1	2809.6	2823.0	2845.2
12.5°	2961.1	2961.1	2949.9	2941.0	2905.4	2876.4	2840.8	2816.3	2816.3	2840.8	2865.3
15°	3036.8	3030.2	3025.7	3001.2	2958.9	2912.1	2867.5	2831.9	2825.2	2863.1	2878.7
17.5°	3132.7	3108.1	3097.0	3054.7	2996.7	2936.6	2876.4	2847.5	2827.4	2867.5	2849.7
20°	3264.1	3246.3	3210.6	3143.8	3025.7	2947.7	2876.4	2838.5	2823.0	2845.2	2827.4
22.5°	3433.4	3422.3	3342.1	3257.4	3101.5	2956.6	2865.3	2814.0	2809.6	2798.4	2760.6
25°	3640.6	3611.7	3529.2	3408.9	3215.1	3043.5	2863.1	2769.5	2753.9	2724.9	2658.1
27.5°	3816.7	3785.5	3685.2	3578.3	3371.1	3172.8	2880.9	2716.0	2698.2	2678.1	2595.7
30°	3825.6	3838.9	3812.2	3732.0	3515.9	3226.2	2912.1	2700.4	2660.3	2589.0	2491.0
32.5°	3645.1	3676.3	3740.9	3769.9	3625.1	3290.8	2938.8	2707.1	2633.6	2462.0	2381.8
35°	3027.9	3090.3	3355.5	3605.0	3656.2	3384.4	2961.1	2707.1	2624.7	2370.7	2308.3
37.5°	2326.1	2377.3	2602.4	3054.7	3518.1	3442.4	3010.1	2691.5	2613.5	2377.3	2292.7
40°	1900.5	1929.5	2027.5	2335.0	3032.4	3346.5	3059.1	2709.3	2580.1	2381.8	2301.6
42.5°	1784.7	1782.4	1762.4	1876.0	2312.7	3065.8	3092.5	2753.9	2524.4	2352.8	2286.0
45°	1706.7	1702.2	1684.4	1706.7	1829.2	2508.8	3068.0	2834.1	2455.3	2250.3	2205.8
47.5°	1622.0	1624.3	1617.6	1626.5	1604.2	1905.0	2929.9	2867.5	2337.2	2078.8	2063.2
50°	1419.3	1452.7	1541.8	1550.7	1492.8	1537.4	2508.8	2851.9	2252.6	2029.8	2016.4
52.5°	882.3	935.8	1198.7	1421.5	1388.1	1388.1	1913.9	2874.2	2101.1	2011.9	2020.8
55°	311.9	352.0	641.7	978.1	1243.3	1267.8	1512.9	2557.8	2083.2	2043.1	2052.0
57.5°	78.0	95.8	196.1	423.3	837.8	1149.7	1352.4	2112.2	1581.9	1526.2	1548.5
60°	91.4	89.1	122.5	135.9	325.3	909.0	1218.7	1426.0	1020.5	955.8	967.0
62.5°	98.0	91.4	95.8	120.3	53.5	445.6	971.4	848.9	421.1	311.9	329.8
65°	86.9	82.4	75.8	111.4	37.9	82.4	572.6	249.5	60.2	95.8	86.9
67.5°	57.9	60.2	62.4	89.1	35.6	35.6	75.8	62.4	42.3	86.9	75.8
70°	33.4	35.6	42.3	53.5	35.6	29.0	33.4	51.2	35.6	86.9	75.8
72.5°	20.1	20.1	20.1	22.3	35.6	24.5	22.3	42.3	31.2	80.2	75.8
75°	15.6	15.6	15.6	13.4	31.2	15.6	15.6	33.4	26.7	57.9	57.9
77.5°	13.4	13.4	13.4	11.1	17.8	13.4	13.4	24.5	24.5	29.0	33.4
80°	8.9	8.9	8.9	8.9	11.1	11.1	8.9	13.4	11.1	13.4	15.6
82.5°	4.5	6.7	6.7	4.5	6.7	6.7	6.7	8.9	6.7	8.9	8.9
85°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	4.5	2.2	2.2	4.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P980834

CATALOG NUMBER: UFLD-S-CA1-50-750-U-66

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3	2787.3
2.5°	2785.1	2796.2	2811.8	2836.3	2845.2	2860.8	2874.2	2885.3	2885.3	2880.9
5°	2820.7	2851.9	2894.2	2932.1	2945.5	2961.1	2967.8	2978.9	2976.7	2974.5
7.5°	2851.9	2900.9	2945.5	2972.2	2967.8	2947.7	2934.4	2916.5	2909.8	2914.3
10°	2876.4	2921.0	2941.0	2923.2	2869.7	2823.0	2762.8	2722.7	2702.6	2709.3
12.5°	2885.3	2900.9	2883.1	2785.1	2718.2	2673.7	2624.7	2597.9	2586.8	2589.0
15°	2887.6	2851.9	2753.9	2680.4	2631.3	2575.6	2535.5	2511.0	2511.0	2513.3
17.5°	2840.8	2753.9	2669.2	2613.5	2544.4	2486.5	2464.2	2455.3	2399.6	2408.5
20°	2798.4	2673.7	2626.9	2540.0	2457.5	2419.7	2290.4	2277.1	2279.3	2281.5
22.5°	2709.3	2615.7	2573.4	2459.8	2366.2	2261.5	2243.7	2230.3	2232.5	2232.5
25°	2586.8	2533.3	2475.4	2357.3	2243.7	2223.6	2210.2	2192.4	2183.5	2185.7
27.5°	2517.7	2450.9	2343.9	2243.7	2170.1	2179.0	2163.4	2136.7	2136.7	2138.9
30°	2430.8	2366.2	2223.6	2105.5	2112.2	2125.6	2087.7	2074.3	2067.6	2067.6
32.5°	2323.9	2234.7	2110.0	1998.6	2038.7	2034.2	1987.4	1991.9	1996.3	1991.9
35°	2243.7	2127.8	2023.1	1962.9	1947.3	1929.5	1905.0	1920.6	1927.3	1922.8
37.5°	2223.6	2085.5	1976.3	1934.0	1873.8	1840.4	1847.1	1862.7	1871.6	1869.3
40°	2216.9	2043.1	1936.2	1891.6	1811.4	1782.4	1791.4	1822.6	1833.7	1831.5
42.5°	2208.0	2014.2	1911.7	1858.2	1746.8	1726.7	1769.1	1798.0	1800.3	1798.0
45°	2161.2	1983.0	1896.1	1789.1	1648.8	1673.3	1726.7	1742.3	1715.6	1704.5
47.5°	2052.0	1925.0	1849.3	1704.5	1568.6	1615.3	1622.0	1452.7	1354.7	1332.4
50°	2020.8	1927.3	1795.8	1604.2	1519.5	1566.3	1274.4	973.7	851.1	826.6
52.5°	2011.9	1905.0	1815.9	1499.5	1501.7	1321.2	804.3	476.8	383.2	365.4
55°	2034.2	2003.0	1849.3	1437.1	1397.0	860.0	374.3	225.0	231.7	225.0
57.5°	1535.1	1675.5	1889.4	1339.1	1020.5	414.4	236.2	218.3	202.8	198.3
60°	958.1	1091.7	1383.6	1151.9	523.6	247.3	240.6	202.8	196.1	193.8
62.5°	316.4	485.7	793.2	757.5	144.8	245.1	242.9	180.5	180.5	180.5
65°	80.2	82.4	218.3	260.7	106.9	218.3	231.7	169.3	164.9	171.6
67.5°	69.1	62.4	115.9	102.5	89.1	151.5	202.8	162.6	153.7	153.7
70°	69.1	73.5	113.6	95.8	55.7	82.4	147.1	100.3	89.1	82.4
72.5°	64.6	71.3	100.3	86.9	37.9	40.1	64.6	33.4	31.2	26.7
75°	55.7	57.9	78.0	78.0	40.1	20.1	26.7	22.3	22.3	20.1
77.5°	37.9	29.0	44.6	55.7	29.0	13.4	11.1	11.1	11.1	8.9
80°	20.1	11.1	11.1	8.9	11.1	11.1	6.7	8.9	8.9	6.7
82.5°	11.1	6.7	6.7	4.5	4.5	6.7	4.5	4.5	4.5	4.5
85°	4.5	4.5	2.2	2.2	2.2	4.5	2.2	2.2	2.2	2.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.2	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Lumark

Report Number: SP1-2501-319-11

Test Date: 02/05/2025

Luminaire Tested: NFFLD-C55-7050-66

Data in this report applies to families of products including NFFLD-C55-7050-66


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2501-319-11
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 02/06/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Lumark
 Catalog Number: **NFFLD-C55-7050-66**
 Description: LUMARK NIGHT FALCON 16900LM NEMA 6

Spectral Parameters

CCT (K): 5108
 CIE u' : 0.2083
 CIE v' : 0.4860
 Duv: 0.0028
 CIE x: 0.3426
 CIE y: 0.3552
 CIE z: 0.3022
 Peak Wavelength (nm): 449
 Dominant Wavelength (nm): 568
 Purity: 9.36717
 R_f: 77.8
 R_g: 93.2

CRI (Ra): 75.3
 R1: 71.3
 R2: 82.0
 R3: 90.0
 R4: 74.3
 R5: 73.5
 R6: 75.6
 R7: 81.5
 R8: 54.1
 R9: -33.6
 R10: 58.1
 R11: 71.9
 R12: 56.4
 R13: 73.5
 R14: 94.6
 R15: 63.4



Test Conditions


Stabilization Time: 48M
 Operation Time: 1H 48M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2501-319-11


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-319-11

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2501-319-11

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	274	NR	620	466	NR	750	11	NR	880	0	NR
365	0	NR	495	319	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	366	NR	630	380	NR	760	8	NR	890	0	NR
375	0	NR	505	409	NR	635	338	NR	765	7	NR	895	0	NR
380	0	NR	510	445	NR	640	300	NR	770	6	NR	900	0	NR
385	2	NR	515	475	NR	645	264	NR	775	5	NR	905	0	NR
390	4	NR	520	499	NR	650	230	NR	780	5	NR	910	0	NR
395	6	NR	525	520	NR	655	201	NR	785	4	NR	915	0	NR
400	10	NR	530	542	NR	660	174	NR	790	3	NR	920	0	NR
405	18	NR	535	562	NR	665	151	NR	795	3	NR	925	0	NR
410	33	NR	540	584	NR	670	131	NR	800	3	NR	930	0	NR
415	59	NR	545	607	NR	675	112	NR	805	2	NR	935	0	NR
420	103	NR	550	629	NR	680	97	NR	810	2	NR	940	0	NR
425	173	NR	555	650	NR	685	83	NR	815	2	NR	945	0	NR
430	274	NR	560	673	NR	690	71	NR	820	2	NR	950	0	NR
435	412	NR	565	690	NR	695	61	NR	825	1	NR	955	0	NR
440	595	NR	570	705	NR	700	52	NR	830	1	NR	960	0	NR
445	849	NR	575	712	NR	705	44	NR	835	1	NR	965	0	NR
450	999	NR	580	713	NR	710	38	NR	840	1	NR	970	0	NR
455	805	NR	585	703	NR	715	33	NR	845	1	NR	975	0	NR
460	555	NR	590	686	NR	720	28	NR	850	1	NR	980	0	NR
465	428	NR	595	661	NR	725	24	NR	855	1	NR	985	0	NR
470	319	NR	600	630	NR	730	20	NR	860	1	NR	990	0	NR
475	251	NR	605	593	NR	735	18	NR	865	1	NR	995	0	NR
480	236	NR	610	552	NR	740	15	NR	870	0	NR	1000	0	NR
485	247	NR	615	510	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2501-319-11

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.89

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	274	NR	620	466	NR	750	11	NR	880	0	NR
365	0	NR	495	319	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	366	NR	630	380	NR	760	8	NR	890	0	NR
375	0	NR	505	409	NR	635	338	NR	765	7	NR	895	0	NR
380	0	NR	510	445	NR	640	300	NR	770	6	NR	900	0	NR
385	2	NR	515	475	NR	645	264	NR	775	5	NR	905	0	NR
390	4	NR	520	499	NR	650	230	NR	780	5	NR	910	0	NR
395	6	NR	525	520	NR	655	201	NR	785	4	NR	915	0	NR
400	10	NR	530	542	NR	660	174	NR	790	3	NR	920	0	NR
405	18	NR	535	562	NR	665	151	NR	795	3	NR	925	0	NR
410	33	NR	540	584	NR	670	131	NR	800	3	NR	930	0	NR
415	59	NR	545	607	NR	675	112	NR	805	2	NR	935	0	NR
420	103	NR	550	629	NR	680	97	NR	810	2	NR	940	0	NR
425	173	NR	555	650	NR	685	83	NR	815	2	NR	945	0	NR
430	274	NR	560	673	NR	690	71	NR	820	2	NR	950	0	NR
435	412	NR	565	690	NR	695	61	NR	825	1	NR	955	0	NR
440	595	NR	570	705	NR	700	52	NR	830	1	NR	960	0	NR
445	849	NR	575	712	NR	705	44	NR	835	1	NR	965	0	NR
450	999	NR	580	713	NR	710	38	NR	840	1	NR	970	0	NR
455	805	NR	585	703	NR	715	33	NR	845	1	NR	975	0	NR
460	555	NR	590	686	NR	720	28	NR	850	1	NR	980	0	NR
465	428	NR	595	661	NR	725	24	NR	855	1	NR	985	0	NR
470	319	NR	600	630	NR	730	20	NR	860	1	NR	990	0	NR
475	251	NR	605	593	NR	735	18	NR	865	1	NR	995	0	NR
480	236	NR	610	552	NR	740	15	NR	870	0	NR	1000	0	NR
485	247	NR	615	510	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2501-319-11

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.96


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	274	NR	620	466	NR	750	11	NR	880	0	NR
365	0	NR	495	319	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	366	NR	630	380	NR	760	8	NR	890	0	NR
375	0	NR	505	409	NR	635	338	NR	765	7	NR	895	0	NR
380	0	NR	510	445	NR	640	300	NR	770	6	NR	900	0	NR
385	2	NR	515	475	NR	645	264	NR	775	5	NR	905	0	NR
390	4	NR	520	499	NR	650	230	NR	780	5	NR	910	0	NR
395	6	NR	525	520	NR	655	201	NR	785	4	NR	915	0	NR
400	10	NR	530	542	NR	660	174	NR	790	3	NR	920	0	NR
405	18	NR	535	562	NR	665	151	NR	795	3	NR	925	0	NR
410	33	NR	540	584	NR	670	131	NR	800	3	NR	930	0	NR
415	59	NR	545	607	NR	675	112	NR	805	2	NR	935	0	NR
420	103	NR	550	629	NR	680	97	NR	810	2	NR	940	0	NR
425	173	NR	555	650	NR	685	83	NR	815	2	NR	945	0	NR
430	274	NR	560	673	NR	690	71	NR	820	2	NR	950	0	NR
435	412	NR	565	690	NR	695	61	NR	825	1	NR	955	0	NR
440	595	NR	570	705	NR	700	52	NR	830	1	NR	960	0	NR
445	849	NR	575	712	NR	705	44	NR	835	1	NR	965	0	NR
450	999	NR	580	713	NR	710	38	NR	840	1	NR	970	0	NR
455	805	NR	585	703	NR	715	33	NR	845	1	NR	975	0	NR
460	555	NR	590	686	NR	720	28	NR	850	1	NR	980	0	NR
465	428	NR	595	661	NR	725	24	NR	855	1	NR	985	0	NR
470	319	NR	600	630	NR	730	20	NR	860	1	NR	990	0	NR
475	251	NR	605	593	NR	735	18	NR	865	1	NR	995	0	NR
480	236	NR	610	552	NR	740	15	NR	870	0	NR	1000	0	NR
485	247	NR	615	510	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2501-319-11





TM-30-18

Summary

$R_f = 77.8$
 $R_g = 93.2$
 $CIE R_a = 75.3$
 $R_g = -33.6$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 69	CES51 = 92	CES76 = 62
CES02 = 60	CES27 = 91	CES52 = 91	CES77 = 75
CES03 = 30	CES28 = 86	CES53 = 83	CES78 = 63
CES04 = 69	CES29 = 73	CES54 = 86	CES79 = 85
CES05 = 46	CES30 = 87	CES55 = 85	CES80 = 83
CES06 = 50	CES31 = 76	CES56 = 78	CES81 = 80
CES07 = 39	CES32 = 69	CES57 = 78	CES82 = 93
CES08 = 38	CES33 = 83	CES58 = 78	CES83 = 92
CES09 = 29	CES34 = 77	CES59 = 87	CES84 = 88
CES10 = 73	CES35 = 87	CES60 = 91	CES85 = 81
CES11 = 56	CES36 = 92	CES61 = 85	CES86 = 74
CES12 = 61	CES37 = 84	CES62 = 88	CES87 = 79
CES13 = 41	CES38 = 95	CES63 = 81	CES88 = 81
CES14 = 74	CES39 = 97	CES64 = 72	CES89 = 74
CES15 = 70	CES40 = 92	CES65 = 68	CES90 = 81
CES16 = 46	CES41 = 96	CES66 = 68	CES91 = 78
CES17 = 49	CES42 = 87	CES67 = 65	CES92 = 59
CES18 = 55	CES43 = 84	CES68 = 71	CES93 = 76
CES19 = 71	CES44 = 99	CES69 = 78	CES94 = 54
CES20 = 64	CES45 = 89	CES70 = 65	CES95 = 67
CES21 = 85	CES46 = 87	CES71 = 61	CES96 = 78
CES22 = 77	CES47 = 91	CES72 = 86	CES97 = 88
CES23 = 91	CES48 = 80	CES73 = 57	CES98 = 78
CES24 = 90	CES49 = 86	CES74 = 94	CES99 = 63
CES25 = 71	CES50 = 91	CES75 = 62	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)