

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P800643

Luminaire Tested: **ARCH-M-PA2-60-722-24VDC-5WQ**

Issue Date: 5/19/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P800643  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1910-568-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/19/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: ARCH-M-PA2-60-722-24VDC-5WQ  
Description: ARCHEON-M ROADWAY AND AREA LUMINAIRE  
(2) 70 CRI, 2200K, 405mA LIGHT ENGINES WITH 16 LEDS AND TYPE V WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7822 lumens  
Efficiency: N/A  
Efficacy: 128.2 lumens/watt  
Luminous Opening: Rectangular (W 0.75' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G2


Input Watts (W): 61  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P800643

CATALOG NUMBER: ARCH-M-PA2-60-722-24VDC-5WQ

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 2.9 fc  
 Type V - Short - N/A

REPORT NUMBER: P800643  
CATALOG NUMBER: ARCH-M-PA2-60-722-24VDC-5WQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P800643

CATALOG NUMBER: ARCH-M-PA2-60-722-24VDC-5WQ

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 3911.0   | 0.0    | 3911.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 3911.0   | 0.0    | 3911.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 7822.0   | 0.0    | 7822.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 59.4   | 0.8       |
| 10°-20°   | 172.3  | 2.2       |
| 20°-30°   | 292.7  | 3.7       |
| 30°-40°   | 446.5  | 5.7       |
| 40°-50°   | 735.2  | 9.4       |
| 50°-60°   | 1283.9 | 16.4      |
| 60°-70°   | 2152.6 | 27.5      |
| 70°-80°   | 2303.7 | 29.5      |
| 80°-90°   | 375.7  | 4.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 7822.0 | 100.0     |
| 0°-180°   | 7822.0 | 100.0     |



REPORT NUMBER: P800643


CATALOG NUMBER: ARCH-M-PA2-60-722-24VDC-5WQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 262.2  | 3.4       |                         |      |         |
| FM   | (30°-60°)   | 1232.8 | 15.8      |                         |      |         |
| FH   | (60°-80°)   | 2228.1 | 28.5      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 187.9  | 2.4       |                         |      | G2/225  |
| BL   | (0°-30°)    | 262.2  | 3.4       | B1/500                  |      |         |
| BM   | (30°-60°)   | 1232.8 | 15.8      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 2228.1 | 28.5      | B3/2500                 |      | G2/5000 |
| BVH  | (80°-90°)   | 187.9  | 2.4       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G2**

Type V Short





REPORT NUMBER: P800643

CATALOG NUMBER: ARCH-M-PA2-60-722-24VDC-5WQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 647.3  | 647.3  | 647.3  | 647.3  | 647.3  | 647.3  | 647.3  | 647.3  | 647.3  | 647.3  | 647.3  |
| 2.5°  | 643.3  | 643.3  | 643.3  | 642.3  | 640.3  | 639.3  | 637.3  | 638.3  | 638.3  | 638.3  | 638.3  |
| 5°    | 635.3  | 635.3  | 634.3  | 633.3  | 631.3  | 630.3  | 628.3  | 630.3  | 630.3  | 630.3  | 630.3  |
| 7.5°  | 620.3  | 621.3  | 621.3  | 620.3  | 617.3  | 616.3  | 613.3  | 614.3  | 614.3  | 615.3  | 614.3  |
| 10°   | 612.3  | 612.3  | 611.3  | 606.3  | 601.3  | 599.3  | 598.3  | 601.3  | 604.3  | 607.3  | 607.3  |
| 12.5° | 612.3  | 612.3  | 610.3  | 602.3  | 595.3  | 595.3  | 595.3  | 599.3  | 605.3  | 611.3  | 612.3  |
| 15°   | 615.3  | 615.3  | 611.3  | 602.3  | 598.3  | 599.3  | 599.3  | 603.3  | 610.3  | 618.3  | 619.3  |
| 17.5° | 617.3  | 617.3  | 612.3  | 603.3  | 603.3  | 606.3  | 604.3  | 607.3  | 614.3  | 623.3  | 624.3  |
| 20°   | 620.3  | 620.3  | 613.3  | 606.3  | 606.3  | 609.3  | 609.3  | 612.3  | 618.3  | 627.3  | 628.3  |
| 22.5° | 626.3  | 625.3  | 618.3  | 612.3  | 612.3  | 614.3  | 616.3  | 620.3  | 625.3  | 633.3  | 635.3  |
| 25°   | 633.3  | 633.3  | 627.3  | 626.3  | 628.3  | 633.3  | 632.3  | 631.3  | 633.3  | 640.3  | 643.3  |
| 27.5° | 637.3  | 637.3  | 633.3  | 636.3  | 644.3  | 648.3  | 643.3  | 639.3  | 639.3  | 646.3  | 647.3  |
| 30°   | 650.3  | 649.3  | 645.3  | 647.3  | 654.3  | 656.3  | 653.3  | 648.3  | 651.3  | 659.3  | 660.3  |
| 32.5° | 672.3  | 672.3  | 666.3  | 666.3  | 671.3  | 679.2  | 669.3  | 666.3  | 670.3  | 679.2  | 680.2  |
| 35°   | 706.2  | 706.2  | 698.2  | 694.2  | 698.2  | 709.2  | 694.2  | 693.2  | 700.2  | 710.2  | 711.2  |
| 37.5° | 749.2  | 749.2  | 744.2  | 734.2  | 735.2  | 742.2  | 729.2  | 728.2  | 741.2  | 752.2  | 752.2  |
| 40°   | 803.1  | 806.1  | 801.1  | 789.1  | 785.1  | 786.1  | 776.1  | 777.1  | 792.1  | 805.1  | 805.1  |
| 42.5° | 870.0  | 872.0  | 864.0  | 855.0  | 850.1  | 847.1  | 837.1  | 839.1  | 857.0  | 874.0  | 874.0  |
| 45°   | 950.9  | 951.9  | 943.9  | 933.0  | 927.0  | 925.0  | 915.0  | 920.0  | 940.0  | 957.9  | 956.9  |
| 47.5° | 1041.8 | 1042.8 | 1034.8 | 1023.9 | 1019.9 | 1022.9 | 1012.9 | 1012.9 | 1030.9 | 1045.8 | 1043.8 |
| 50°   | 1144.7 | 1146.7 | 1137.7 | 1132.7 | 1129.7 | 1137.7 | 1125.7 | 1114.8 | 1126.7 | 1141.7 | 1139.7 |
| 52.5° | 1258.6 | 1263.6 | 1257.6 | 1259.6 | 1270.6 | 1280.6 | 1260.6 | 1236.6 | 1242.6 | 1252.6 | 1249.6 |
| 55°   | 1396.4 | 1402.4 | 1404.4 | 1411.4 | 1440.4 | 1457.4 | 1424.4 | 1384.5 | 1381.5 | 1382.5 | 1377.5 |
| 57.5° | 1551.3 | 1555.3 | 1568.3 | 1584.2 | 1644.2 | 1671.1 | 1619.2 | 1550.3 | 1528.3 | 1515.3 | 1512.3 |
| 60°   | 1707.1 | 1714.1 | 1746.1 | 1779.0 | 1870.9 | 1919.9 | 1840.0 | 1724.1 | 1677.1 | 1653.2 | 1648.2 |
| 62.5° | 1863.9 | 1877.9 | 1929.9 | 1985.8 | 2119.6 | 2192.6 | 2069.7 | 1901.9 | 1834.0 | 1804.0 | 1796.0 |
| 65°   | 2045.7 | 2062.7 | 2125.6 | 2196.6 | 2345.4 | 2448.3 | 2299.4 | 2085.7 | 2012.8 | 1972.8 | 1962.8 |
| 67.5° | 2258.5 | 2276.5 | 2327.4 | 2406.3 | 2547.2 | 2648.1 | 2516.2 | 2273.5 | 2178.6 | 2127.6 | 2119.6 |
| 70°   | 2433.3 | 2449.3 | 2504.2 | 2584.1 | 2689.0 | 2803.9 | 2678.0 | 2423.3 | 2337.4 | 2301.4 | 2296.4 |
| 72.5° | 2406.3 | 2427.3 | 2508.2 | 2628.1 | 2777.9 | 2907.8 | 2748.9 | 2452.3 | 2328.4 | 2278.5 | 2262.5 |
| 75°   | 2101.7 | 2124.6 | 2220.5 | 2437.3 | 2711.0 | 2904.8 | 2646.1 | 2259.5 | 2113.6 | 2071.7 | 2063.7 |
| 77.5° | 1391.5 | 1413.4 | 1575.2 | 1916.9 | 2367.4 | 2647.1 | 2335.4 | 1892.9 | 1658.2 | 1557.3 | 1551.3 |
| 80°   | 562.4  | 590.3  | 745.2  | 1107.8 | 1678.1 | 2057.7 | 1732.1 | 1211.7 | 817.1  | 659.3  | 627.3  |
| 82.5° | 130.9  | 155.8  | 226.7  | 408.5  | 859.0  | 1281.6 | 934.0  | 452.5  | 262.7  | 186.8  | 167.8  |
| 85°   | 54.9   | 55.9   | 96.9   | 132.9  | 268.7  | 517.4  | 305.7  | 164.8  | 133.9  | 97.9   | 95.9   |
| 87.5° | 21.0   | 22.0   | 46.9   | 55.9   | 85.9   | 97.9   | 103.9  | 84.9   | 78.9   | 48.9   | 46.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2101-121-4

Luminaire Tested: IFLD-S-SA2B-722-U-T3R

Test Date: 03/03/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2101-121-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 03/03/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2B-722-U-T3R**  
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 800mA.

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 2218    | CRI (Ra): | 72.2 |      |       |
| CIE u':                   | 0.2889  | R1:       | 69.1 | R9:  | -16.8 |
| CIE v':                   | 0.5350  | R2:       | 83.2 | R10: | 61.9  |
| Duv:                      | -0.0005 | R3:       | 95.4 | R11: | 60.1  |
| CIE x:                    | 0.5026  | R4:       | 66.4 | R12: | 51.2  |
| CIE y:                    | 0.4136  | R5:       | 66.2 | R13: | 71.3  |
| CIE z:                    | 0.0839  | R6:       | 76.7 | R14: | 97.1  |
| Peak Wavelength (nm):     | 606     | R7:       | 76.7 |      |       |
| Dominant Wavelength (nm): | 587     | R8:       | 43.9 |      |       |
| Purity:                   | 75.3    |           |      |      |       |
| Rf:                       | 70      |           |      |      |       |
| Rg:                       | 99.3    |           |      |      |       |



### Test Conditions

Stabilization Time: 95M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3/31%  
 Sphere Temperature (°C): 24.8

REPORT NUMBER: SP1-2101-121-4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-4

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-4

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2623             | 0.0              | 490       | 7941             | 1.1              | 620       | 205150           | 53.4             | 750       | 13431            | 0.0              | 880       | 3867             | 0.0              |
| 365       | 2260             | 0.0              | 495       | 11299            | 2.0              | 625       | 198277           | 43.7             | 755       | 12426            | 0.0              | 885       | 3345             | 0.0              |
| 370       | 2306             | 0.0              | 500       | 16633            | 3.7              | 630       | 187878           | 34.0             | 760       | 11385            | 0.0              | 890       | 2956             | 0.0              |
| 375       | 2437             | 0.0              | 505       | 23672            | 6.6              | 635       | 176836           | 26.6             | 765       | 9797             | 0.0              | 895       | 2272             | 0.0              |
| 380       | 2473             | 0.0              | 510       | 32025            | 11.0             | 640       | 164455           | 19.7             | 770       | 8562             | 0.0              | 900       | 3003             | 0.0              |
| 385       | 2203             | 0.0              | 515       | 41295            | 17.1             | 645       | 154086           | 14.8             | 775       | 7810             | 0.0              | 905       | 2480             | 0.0              |
| 390       | 2262             | 0.0              | 520       | 50628            | 24.6             | 650       | 141592           | 10.3             | 780       | 7052             | 0.0              | 910       | 2068             | 0.0              |
| 395       | 2028             | 0.0              | 525       | 58836            | 31.6             | 655       | 128604           | 7.4              | 785       | 6345             | 0.0              | 915       | 2064             | 0.0              |
| 400       | 1806             | 0.0              | 530       | 67109            | 39.5             | 660       | 116713           | 4.9              | 790       | 5524             | 0.0              | 920       | 2581             | 0.0              |
| 405       | 1945             | 0.0              | 535       | 74404            | 46.1             | 665       | 104993           | 3.3              | 795       | 5788             | 0.0              | 925       | 3137             | 0.0              |
| 410       | 3199             | 0.0              | 540       | 81280            | 53.0             | 670       | 93149            | 2.0              | 800       | 5282             | 0.0              | 930       | 2747             | 0.0              |
| 415       | 5572             | 0.0              | 545       | 88806            | 59.1             | 675       | 82543            | 1.4              | 805       | 4258             | 0.0              | 935       | 2471             | 0.0              |
| 420       | 10322            | 0.0              | 550       | 97367            | 66.2             | 680       | 73089            | 0.8              | 810       | 5156             | 0.0              | 940       | 2339             | 0.0              |
| 425       | 18494            | 0.1              | 555       | 106598           | 72.8             | 685       | 64438            | 0.6              | 815       | 4391             | 0.0              | 945       | 2917             | 0.0              |
| 430       | 28541            | 0.2              | 560       | 117615           | 79.9             | 690       | 56546            | 0.3              | 820       | 4383             | 0.0              | 950       | 1966             | 0.0              |
| 435       | 37453            | 0.4              | 565       | 129103           | 85.8             | 695       | 49328            | 0.2              | 825       | 4881             | 0.0              | 955       | 1580             | 0.0              |
| 440       | 44455            | 0.7              | 570       | 141415           | 92.0             | 700       | 43493            | 0.1              | 830       | 3588             | 0.0              | 960       | 1318             | 0.0              |
| 445       | 45934            | 1.0              | 575       | 155854           | 97.0             | 705       | 38035            | 0.1              | 835       | 3835             | 0.0              | 965       | 1419             | 0.0              |
| 450       | 37926            | 1.0              | 580       | 168613           | 100.2            | 710       | 33716            | 0.0              | 840       | 3014             | 0.0              | 970       | 1917             | 0.0              |
| 455       | 24793            | 0.8              | 585       | 182390           | 101.3            | 715       | 30449            | 0.0              | 845       | 3765             | 0.0              | 975       | 1210             | 0.0              |
| 460       | 15340            | 0.6              | 590       | 194054           | 100.3            | 720       | 27240            | 0.0              | 850       | 2906             | 0.0              | 980       | 3915             | 0.0              |
| 465       | 10883            | 0.6              | 595       | 203639           | 96.5             | 725       | 24231            | 0.0              | 855       | 2947             | 0.0              | 985       | 3180             | 0.0              |
| 470       | 8138             | 0.5              | 600       | 211043           | 91.0             | 730       | 21490            | 0.0              | 860       | 3864             | 0.0              | 990       | 5676             | 0.0              |
| 475       | 6653             | 0.5              | 605       | 214591           | 83.1             | 735       | 18548            | 0.0              | 865       | 3546             | 0.0              | 995       | 4736             | 0.0              |
| 480       | 6220             | 0.6              | 610       | 214337           | 73.6             | 740       | 16963            | 0.0              | 870       | 3253             | 0.0              | 1000      | 5113             | 0.0              |
| 485       | 6613             | 0.8              | 615       | 211915           | 64.0             | 745       | 14922            | 0.0              | 875       | 2450             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-4

### Scotopic Flux vs. Wavelength



Scotopic Lumens: 7290.1

S/P: 0.84

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2623             | 0.0              | 490       | 7941             | 12.2             | 620       | 205150           | 2.6              | 750       | 13431            | 0.0              | 880       | 3867             | 0.0              |
| 365       | 2260             | 0.0              | 495       | 11299            | 18.3             | 625       | 198277           | 1.7              | 755       | 12426            | 0.0              | 885       | 3345             | 0.0              |
| 370       | 2306             | 0.0              | 500       | 16633            | 27.8             | 630       | 187878           | 1.1              | 760       | 11385            | 0.0              | 890       | 2956             | 0.0              |
| 375       | 2437             | 0.0              | 505       | 23672            | 40.2             | 635       | 176836           | 0.7              | 765       | 9797             | 0.0              | 895       | 2272             | 0.0              |
| 380       | 2473             | 0.0              | 510       | 32025            | 54.3             | 640       | 164455           | 0.4              | 770       | 8562             | 0.0              | 900       | 3003             | 0.0              |
| 385       | 2203             | 0.0              | 515       | 41295            | 68.4             | 645       | 154086           | 0.3              | 775       | 7810             | 0.0              | 905       | 2480             | 0.0              |
| 390       | 2262             | 0.0              | 520       | 50628            | 80.5             | 650       | 141592           | 0.2              | 780       | 7052             | 0.0              | 910       | 2068             | 0.0              |
| 395       | 2028             | 0.0              | 525       | 58836            | 88.0             | 655       | 128604           | 0.1              | 785       | 6345             | 0.0              | 915       | 2064             | 0.0              |
| 400       | 1806             | 0.0              | 530       | 67109            | 92.5             | 660       | 116713           | 0.1              | 790       | 5524             | 0.0              | 920       | 2581             | 0.0              |
| 405       | 1945             | 0.1              | 535       | 74404            | 92.7             | 665       | 104993           | 0.0              | 795       | 5788             | 0.0              | 925       | 3137             | 0.0              |
| 410       | 3199             | 0.2              | 540       | 81280            | 89.8             | 670       | 93149            | 0.0              | 800       | 5282             | 0.0              | 930       | 2747             | 0.0              |
| 415       | 5572             | 0.6              | 545       | 88806            | 85.1             | 675       | 82543            | 0.0              | 805       | 4258             | 0.0              | 935       | 2471             | 0.0              |
| 420       | 10322            | 1.7              | 550       | 97367            | 79.6             | 680       | 73089            | 0.0              | 810       | 5156             | 0.0              | 940       | 2339             | 0.0              |
| 425       | 18494            | 4.5              | 555       | 106598           | 72.8             | 685       | 64438            | 0.0              | 815       | 4391             | 0.0              | 945       | 2917             | 0.0              |
| 430       | 28541            | 9.7              | 560       | 117615           | 65.7             | 690       | 56546            | 0.0              | 820       | 4383             | 0.0              | 950       | 1966             | 0.0              |
| 435       | 37453            | 16.7             | 565       | 129103           | 57.9             | 695       | 49328            | 0.0              | 825       | 4881             | 0.0              | 955       | 1580             | 0.0              |
| 440       | 44455            | 24.8             | 570       | 141415           | 49.9             | 700       | 43493            | 0.0              | 830       | 3588             | 0.0              | 960       | 1318             | 0.0              |
| 445       | 45934            | 30.8             | 575       | 155854           | 42.4             | 705       | 38035            | 0.0              | 835       | 3835             | 0.0              | 965       | 1419             | 0.0              |
| 450       | 37926            | 29.4             | 580       | 168613           | 34.7             | 710       | 33716            | 0.0              | 840       | 3014             | 0.0              | 970       | 1917             | 0.0              |
| 455       | 24793            | 21.7             | 585       | 182390           | 27.9             | 715       | 30449            | 0.0              | 845       | 3765             | 0.0              | 975       | 1210             | 0.0              |
| 460       | 15340            | 14.8             | 590       | 194054           | 21.6             | 720       | 27240            | 0.0              | 850       | 2906             | 0.0              | 980       | 3915             | 0.0              |
| 465       | 10883            | 11.5             | 595       | 203639           | 16.2             | 725       | 24231            | 0.0              | 855       | 2947             | 0.0              | 985       | 3180             | 0.0              |
| 470       | 8138             | 9.4              | 600       | 211043           | 11.9             | 730       | 21490            | 0.0              | 860       | 3864             | 0.0              | 990       | 5676             | 0.0              |
| 475       | 6653             | 8.3              | 605       | 214591           | 8.4              | 735       | 18548            | 0.0              | 865       | 3546             | 0.0              | 995       | 4736             | 0.0              |
| 480       | 6220             | 8.4              | 610       | 214337           | 5.8              | 740       | 16963            | 0.0              | 870       | 3253             | 0.0              | 1000      | 5113             | 0.0              |
| 485       | 6613             | 9.6              | 615       | 211915           | 3.9              | 745       | 14922            | 0.0              | 875       | 2450             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-4

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 2276.7**

**M/P: 0.26**


| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2623             | 0.0              | 490       | 7941             | 6.6              | 620       | 205150           | 0.2              | 750       | 13431            | 0.0              | 880       | 3867             | 0.0              |
| 365       | 2260             | 0.0              | 495       | 11299            | 9.3              | 625       | 198277           | 0.1              | 755       | 12426            | 0.0              | 885       | 3345             | 0.0              |
| 370       | 2306             | 0.0              | 500       | 16633            | 13.4             | 630       | 187878           | 0.1              | 760       | 11385            | 0.0              | 890       | 2956             | 0.0              |
| 375       | 2437             | 0.0              | 505       | 23672            | 18.2             | 635       | 176836           | 0.0              | 765       | 9797             | 0.0              | 895       | 2272             | 0.0              |
| 380       | 2473             | 0.0              | 510       | 32025            | 23.0             | 640       | 164455           | 0.0              | 770       | 8562             | 0.0              | 900       | 3003             | 0.0              |
| 385       | 2203             | 0.0              | 515       | 41295            | 27.0             | 645       | 154086           | 0.0              | 775       | 7810             | 0.0              | 905       | 2480             | 0.0              |
| 390       | 2262             | 0.0              | 520       | 50628            | 29.5             | 650       | 141592           | 0.0              | 780       | 7052             | 0.0              | 910       | 2068             | 0.0              |
| 395       | 2028             | 0.0              | 525       | 58836            | 29.8             | 655       | 128604           | 0.0              | 785       | 6345             | 0.0              | 915       | 2064             | 0.0              |
| 400       | 1806             | 0.0              | 530       | 67109            | 29.0             | 660       | 116713           | 0.0              | 790       | 5524             | 0.0              | 920       | 2581             | 0.0              |
| 405       | 1945             | 0.0              | 535       | 74404            | 26.8             | 665       | 104993           | 0.0              | 795       | 5788             | 0.0              | 925       | 3137             | 0.0              |
| 410       | 3199             | 0.1              | 540       | 81280            | 23.8             | 670       | 93149            | 0.0              | 800       | 5282             | 0.0              | 930       | 2747             | 0.0              |
| 415       | 5572             | 0.4              | 545       | 88806            | 20.6             | 675       | 82543            | 0.0              | 805       | 4258             | 0.0              | 935       | 2471             | 0.0              |
| 420       | 10322            | 1.2              | 550       | 97367            | 17.5             | 680       | 73089            | 0.0              | 810       | 5156             | 0.0              | 940       | 2339             | 0.0              |
| 425       | 18494            | 2.9              | 555       | 106598           | 14.4             | 685       | 64438            | 0.0              | 815       | 4391             | 0.0              | 945       | 2917             | 0.0              |
| 430       | 28541            | 6.0              | 560       | 117615           | 11.6             | 690       | 56546            | 0.0              | 820       | 4383             | 0.0              | 950       | 1966             | 0.0              |
| 435       | 37453            | 10.0             | 565       | 129103           | 9.1              | 695       | 49328            | 0.0              | 825       | 4881             | 0.0              | 955       | 1580             | 0.0              |
| 440       | 44455            | 14.9             | 570       | 141415           | 6.9              | 700       | 43493            | 0.0              | 830       | 3588             | 0.0              | 960       | 1318             | 0.0              |
| 445       | 45934            | 18.1             | 575       | 155854           | 5.2              | 705       | 38035            | 0.0              | 835       | 3835             | 0.0              | 965       | 1419             | 0.0              |
| 450       | 37926            | 17.5             | 580       | 168613           | 3.8              | 710       | 33716            | 0.0              | 840       | 3014             | 0.0              | 970       | 1917             | 0.0              |
| 455       | 24793            | 13.0             | 585       | 182390           | 2.7              | 715       | 30449            | 0.0              | 845       | 3765             | 0.0              | 975       | 1210             | 0.0              |
| 460       | 15340            | 9.0              | 590       | 194054           | 1.9              | 720       | 27240            | 0.0              | 850       | 2906             | 0.0              | 980       | 3915             | 0.0              |
| 465       | 10883            | 7.1              | 595       | 203639           | 1.3              | 725       | 24231            | 0.0              | 855       | 2947             | 0.0              | 985       | 3180             | 0.0              |
| 470       | 8138             | 5.8              | 600       | 211043           | 0.9              | 730       | 21490            | 0.0              | 860       | 3864             | 0.0              | 990       | 5676             | 0.0              |
| 475       | 6653             | 5.1              | 605       | 214591           | 0.6              | 735       | 18548            | 0.0              | 865       | 3546             | 0.0              | 995       | 4736             | 0.0              |
| 480       | 6220             | 5.0              | 610       | 214337           | 0.4              | 740       | 16963            | 0.0              | 870       | 3253             | 0.0              | 1000      | 5113             | 0.0              |
| 485       | 6613             | 5.5              | 615       | 211915           | 0.3              | 745       | 14922            | 0.0              | 875       | 2450             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-4


TM-30-18

### Summary

$R_f = 70$   
 $R_g = 99.3$   
 CIE  $R_a = 72.2$   
 $R_g = -16.8$




### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 57 | CES51 = 74 | CES76 = 57 |
| CES02 = 65 | CES27 = 76 | CES52 = 76 | CES77 = 81 |
| CES03 = 32 | CES28 = 84 | CES53 = 65 | CES78 = 64 |
| CES04 = 72 | CES29 = 46 | CES54 = 78 | CES79 = 85 |
| CES05 = 52 | CES30 = 48 | CES55 = 75 | CES80 = 84 |
| CES06 = 52 | CES31 = 52 | CES56 = 65 | CES81 = 63 |
| CES07 = 44 | CES32 = 51 | CES57 = 62 | CES82 = 92 |
| CES08 = 43 | CES33 = 54 | CES58 = 66 | CES83 = 83 |
| CES09 = 29 | CES34 = 71 | CES59 = 84 | CES84 = 92 |
| CES10 = 79 | CES35 = 86 | CES60 = 90 | CES85 = 81 |
| CES11 = 62 | CES36 = 78 | CES61 = 84 | CES86 = 56 |
| CES12 = 68 | CES37 = 80 | CES62 = 71 | CES87 = 78 |
| CES13 = 45 | CES38 = 54 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 85 | CES65 = 67 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 90 |
| CES17 = 51 | CES42 = 79 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 64 | CES68 = 70 | CES93 = 78 |
| CES19 = 74 | CES44 = 98 | CES69 = 80 | CES94 = 52 |
| CES20 = 68 | CES45 = 73 | CES70 = 64 | CES95 = 76 |
| CES21 = 89 | CES46 = 67 | CES71 = 64 | CES96 = 78 |
| CES22 = 81 | CES47 = 61 | CES72 = 87 | CES97 = 77 |
| CES23 = 92 | CES48 = 48 | CES73 = 57 | CES98 = 72 |
| CES24 = 92 | CES49 = 64 | CES74 = 87 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 |            |



### Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)