

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P579490

Luminaire Tested: **CST-CA10-760-740-U-T5-HSS-HM-EX120**

Issue Date: 11/18/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P579490  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2110-429-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 11/18/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: CST-CA10-760-740-U-T5-HSS-HM-EX120  
Description: CELESTEON HIGH MAST LUMINAIRE WITH FIELD INSTALLED SHIELD  
Light Source: (10) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 78317 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B5 - U3 - G5

Input Watts (W): 761.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P579490

CATALOG NUMBER: CST-CA10-760-740-U-T5-HSS-HM-EX120

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 8.7 fc  
 Type IV - Short - N/A

REPORT NUMBER: P579490  
CATALOG NUMBER: CST-CA10-760-740-U-T5-HSS-HM-EX120

## Luminous Intensity Polar Plot



REPORT NUMBER: P579490

CATALOG NUMBER: CST-CA10-760-740-U-T5-HSS-HM-EX120

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 23378.1  | 7.9    | 23385.9 |
|                    | % Fixture | 29.9     | 0.0    | 29.9    |
| <b>Street Side</b> | Lumens    | 54842.9  | 88.2   | 54931.1 |
|                    | % Fixture | 70.0     | 0.1    | 70.1    |
| <b>Total</b>       | Lumens    | 78221.0  | 96.0   | 78317.0 |
|                    | % Fixture | 99.9     | 0.1    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 748.2   | 1.0       |
| 10°-20°   | 2316.2  | 3.0       |
| 20°-30°   | 3887.0  | 5.0       |
| 30°-40°   | 6302.9  | 8.0       |
| 40°-50°   | 10299.6 | 13.2      |
| 50°-60°   | 16141.4 | 20.6      |
| 60°-70°   | 21618.3 | 27.6      |
| 70°-80°   | 15756.8 | 20.1      |
| 80°-90°   | 1150.7  | 1.5       |
| 90°-100°  | 73.6    | 0.1       |
| 100°-110° | 20.9    | 0.0       |
| 110°-120° | 1.5     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 78221.0 | 99.9      |
| 0°-180°   | 78317.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P579490


CATALOG NUMBER: CST-CA10-760-740-U-T5-HSS-HM-EX120

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |        |        |
|------|-------------|---------|-----------|-------------------------|--------|--------|
|      |             |         |           | B                       | U      | G      |
| FL   | (0°-30°)    | 3863.0  | 4.9       |                         |        |        |
| FM   | (30°-60°)   | 21413.3 | 27.3      |                         |        |        |
| FH   | (60°-80°)   | 28656.7 | 36.6      |                         |        | G5     |
| FVH  | (80°-90°)   | 909.9   | 1.2       |                         |        | G5     |
| BL   | (0°-30°)    | 3088.3  | 3.9       | B4/5000                 |        |        |
| BM   | (30°-60°)   | 11330.7 | 14.5      | B5                      |        |        |
| BH   | (60°-80°)   | 8718.4  | 11.1      | B5                      |        | G5     |
| BVH  | (80°-90°)   | 240.7   | 0.3       |                         |        | G3/500 |
| UL   | (90°-100°)  | 73.6    | 0.1       |                         | U3/500 |        |
| UH   | (100°-180°) | 22.4    | 0.0       |                         | U2/50  |        |

**BUG Rating: B5-U3-G5**

Type IV Short



REPORT NUMBER: P579490

CATALOG NUMBER: CST-CA10-760-740-U-T5-HSS-HM-EX120

**CANDELA DISTRIBUTION (FULL):**

|        | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 85°     | 90°     |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3  |
| 2.5°   | 7908.5  | 7862.4  | 7865.7  | 7908.5  | 7780.1  | 7822.9  | 7766.9  | 7809.7  | 7780.1  | 7790.0  | 7809.7  |
| 5°     | 7957.9  | 7908.5  | 7911.8  | 7964.5  | 7849.2  | 7885.4  | 7809.7  | 7832.8  | 7806.4  | 7819.6  | 7819.6  |
| 7.5°   | 8056.6  | 8000.7  | 7997.4  | 8030.3  | 7911.8  | 7924.9  | 7855.8  | 7859.1  | 7819.6  | 7845.9  | 7832.8  |
| 10°    | 8204.8  | 8158.7  | 8125.8  | 8145.5  | 8040.2  | 8033.6  | 7944.7  | 7948.0  | 7898.6  | 7928.2  | 7905.2  |
| 12.5°  | 8385.9  | 8323.3  | 8316.7  | 8323.3  | 8208.1  | 8181.8  | 8089.6  | 8096.2  | 8007.3  | 8053.3  | 8027.0  |
| 15°    | 8616.4  | 8517.6  | 8517.6  | 8553.8  | 8405.6  | 8385.9  | 8273.9  | 8280.5  | 8188.3  | 8224.6  | 8198.2  |
| 17.5°  | 8899.5  | 8804.0  | 8787.6  | 8813.9  | 8685.5  | 8659.2  | 8543.9  | 8537.3  | 8435.3  | 8445.2  | 8422.1  |
| 20°    | 9265.0  | 9169.5  | 9130.0  | 9195.8  | 9034.5  | 9014.7  | 8876.5  | 8863.3  | 8754.6  | 8725.0  | 8711.8  |
| 22.5°  | 9604.1  | 9528.4  | 9508.6  | 9581.0  | 9413.1  | 9396.7  | 9265.0  | 9248.5  | 9146.4  | 9103.6  | 8843.5  |
| 25°    | 9986.0  | 9969.6  | 9963.0  | 9986.0  | 9828.0  | 9795.1  | 9693.0  | 9669.9  | 9584.3  | 9531.7  | 9215.6  |
| 27.5°  | 10479.9 | 10473.3 | 10453.6 | 10456.8 | 10312.0 | 10282.3 | 10186.9 | 10170.4 | 10081.5 | 10022.2 | 9617.3  |
| 30°    | 10996.8 | 10996.8 | 10954.0 | 10977.1 | 10904.6 | 10858.5 | 10782.8 | 10723.5 | 10667.6 | 10605.0 | 10094.7 |
| 32.5°  | 11592.7 | 11589.4 | 11549.9 | 11619.1 | 11566.4 | 11566.4 | 11520.3 | 11457.7 | 11359.0 | 11329.3 | 10710.4 |
| 35°    | 12359.9 | 12310.5 | 12294.0 | 12406.0 | 12389.5 | 12419.1 | 12402.7 | 12336.8 | 12254.5 | 12185.4 | 11434.7 |
| 37.5°  | 13209.3 | 13196.2 | 13245.6 | 13314.7 | 13350.9 | 13429.9 | 13380.5 | 13377.3 | 13364.1 | 13189.6 | 11240.4 |
| 40°    | 14256.3 | 14200.4 | 14269.5 | 14305.7 | 14279.4 | 14407.8 | 14365.0 | 14401.2 | 14500.0 | 13097.4 | 11227.3 |
| 42.5°  | 15300.0 | 15250.7 | 15300.0 | 15477.8 | 15438.3 | 15593.1 | 15573.3 | 15714.9 | 15770.9 | 13291.6 | 12139.3 |
| 45°    | 16584.1 | 16528.1 | 16567.6 | 16778.4 | 16798.1 | 16985.8 | 17087.9 | 17222.8 | 17249.2 | 14549.4 | 13239.0 |
| 47.5°  | 18059.1 | 17966.9 | 18042.7 | 18141.4 | 18441.1 | 18618.8 | 18717.6 | 18882.2 | 19050.2 | 16063.9 | 14490.1 |
| 50°    | 19685.6 | 19679.0 | 19761.3 | 19932.5 | 20274.9 | 20452.7 | 20623.9 | 20795.2 | 21071.7 | 17752.9 | 15892.7 |
| 52.5°  | 21753.3 | 21710.5 | 21852.0 | 22013.4 | 22316.3 | 22589.5 | 22793.7 | 22971.5 | 23267.8 | 19461.7 | 17410.5 |
| 55°    | 24117.2 | 23969.1 | 24239.1 | 24512.3 | 24640.7 | 24963.4 | 25105.0 | 25253.1 | 25536.3 | 21259.4 | 18296.2 |
| 57.5°  | 26668.9 | 26632.7 | 26820.4 | 26919.1 | 27195.7 | 27396.5 | 27472.3 | 27633.6 | 27630.3 | 23129.5 | 19804.1 |
| 60°    | 29181.0 | 29141.5 | 29362.1 | 29421.4 | 29642.0 | 29823.1 | 29796.7 | 29941.6 | 29994.3 | 24884.4 | 21282.4 |
| 62.5°  | 31824.9 | 31759.0 | 31963.2 | 31976.3 | 31844.6 | 32137.7 | 32108.0 | 32229.9 | 32183.8 | 26599.8 | 22737.7 |
| 65°    | 34715.7 | 34765.1 | 34830.9 | 34560.9 | 34244.8 | 34498.4 | 34491.8 | 34722.2 | 34886.9 | 28996.7 | 24686.8 |
| 67.5°  | 38498.7 | 38436.1 | 38097.0 | 37445.1 | 36678.0 | 36421.2 | 36147.9 | 36315.8 | 36361.9 | 30188.5 | 25684.5 |
| 70°    | 36865.6 | 36727.4 | 36575.9 | 35910.8 | 34985.6 | 34333.7 | 33909.0 | 34086.8 | 34274.5 | 28529.1 | 24123.8 |
| 72.5°  | 32885.1 | 32542.6 | 31838.1 | 31252.0 | 30718.6 | 30083.2 | 29566.3 | 29875.8 | 30287.3 | 25305.8 | 21361.5 |
| 75°    | 25944.6 | 25625.2 | 25111.6 | 24713.2 | 24426.7 | 24420.2 | 24397.1 | 24637.5 | 24578.2 | 20548.2 | 17367.7 |
| 77.5°  | 16067.2 | 16735.6 | 17209.7 | 16870.5 | 16989.1 | 16745.4 | 17282.1 | 17598.2 | 17884.6 | 14730.5 | 12373.1 |
| 80°    | 7417.9  | 7589.1  | 8428.7  | 8211.4  | 8036.9  | 7987.5  | 8020.4  | 8570.3  | 8731.6  | 6611.3  | 5537.9  |
| 82.5°  | 1692.3  | 1623.2  | 1682.4  | 1560.6  | 1554.0  | 1481.6  | 1491.5  | 1491.5  | 1438.8  | 1218.2  | 1020.7  |
| 85°    | 856.0   | 875.8   | 882.4   | 846.2   | 747.4   | 671.7   | 622.3   | 526.8   | 454.4   | 388.5   | 329.2   |
| 87.5°  | 572.9   | 589.3   | 599.2   | 549.8   | 493.9   | 431.3   | 391.8   | 319.4   | 253.5   | 158.0   | 121.8   |
| 90°    | 391.8   | 388.5   | 378.6   | 352.3   | 316.1   | 270.0   | 217.3   | 151.5   | 88.9    | 32.9    | 23.0    |
| 92.5°  | 279.9   | 273.3   | 270.0   | 246.9   | 220.6   | 184.4   | 141.6   | 95.5    | 49.4    | 23.0    | 13.2    |
| 95°    | 184.4   | 181.1   | 181.1   | 167.9   | 148.2   | 121.8   | 95.5    | 62.6    | 36.2    | 19.8    | 13.2    |
| 97.5°  | 128.4   | 125.1   | 125.1   | 118.5   | 105.4   | 88.9    | 65.8    | 42.8    | 29.6    | 19.8    | 13.2    |
| 100°   | 88.9    | 88.9    | 88.9    | 82.3    | 75.7    | 62.6    | 49.4    | 32.9    | 26.3    | 19.8    | 13.2    |
| 102.5° | 59.3    | 59.3    | 62.6    | 59.3    | 52.7    | 42.8    | 32.9    | 26.3    | 23.0    | 16.5    | 13.2    |
| 105°   | 39.5    | 39.5    | 39.5    | 39.5    | 36.2    | 29.6    | 26.3    | 23.0    | 19.8    | 16.5    | 13.2    |
| 107.5° | 26.3    | 26.3    | 26.3    | 26.3    | 23.0    | 19.8    | 19.8    | 19.8    | 16.5    | 16.5    | 13.2    |
| 110°   | 16.5    | 16.5    | 16.5    | 19.8    | 16.5    | 16.5    | 16.5    | 16.5    | 16.5    | 13.2    | 13.2    |



REPORT NUMBER: P579490

CATALOG NUMBER: CST-CA10-760-740-U-T5-HSS-HM-EX120

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 5°  | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P579490

CATALOG NUMBER: CST-CA10-760-740-U-T5-HSS-HM-EX120

**CANDELA DISTRIBUTION (continued):**

|        | 95°     | 105°    | 115°    | 125°    | 135°    | 145°    | 155°    | 165°   | 175°    | 180°    |
|--------|---------|---------|---------|---------|---------|---------|---------|--------|---------|---------|
| 0°     | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3  | 7760.3 | 7760.3  | 7760.3  |
| 2.5°   | 7793.2  | 7747.2  | 7770.2  | 7724.1  | 7704.3  | 7661.5  | 7743.9  | 7750.4 | 7743.9  | 7757.0  |
| 5°     | 7803.1  | 7750.4  | 7776.8  | 7724.1  | 7714.2  | 7664.8  | 7747.2  | 7747.2 | 7727.4  | 7737.3  |
| 7.5°   | 7826.2  | 7770.2  | 7790.0  | 7727.4  | 7727.4  | 7668.1  | 7766.9  | 7760.3 | 7743.9  | 7766.9  |
| 10°    | 7905.2  | 7839.3  | 7839.3  | 7780.1  | 7786.7  | 7724.1  | 7845.9  | 7845.9 | 7832.8  | 7872.3  |
| 12.5°  | 8027.0  | 7944.7  | 7948.0  | 7865.7  | 7878.8  | 7829.5  | 7977.6  | 7984.2 | 7984.2  | 8050.1  |
| 15°    | 8185.0  | 8059.9  | 8073.1  | 7984.2  | 8010.5  | 7951.3  | 8083.0  | 8076.4 | 8092.9  | 8188.3  |
| 17.5°  | 8379.3  | 8241.0  | 8125.8  | 7836.0  | 7664.8  | 7671.4  | 8063.2  | 8244.3 | 8033.6  | 8096.2  |
| 20°    | 8461.6  | 7790.0  | 7424.5  | 7319.1  | 7296.1  | 6930.6  | 6183.2  | 6298.5 | 7003.1  | 7309.3  |
| 22.5°  | 7908.5  | 7694.5  | 7658.3  | 7523.3  | 6525.6  | 6249.1  | 6295.2  | 6229.3 | 5537.9  | 5146.1  |
| 25°    | 8178.5  | 8036.9  | 7954.6  | 6766.0  | 6542.1  | 6492.7  | 6459.8  | 5834.2 | 5083.6  | 5119.8  |
| 27.5°  | 8560.4  | 8376.0  | 7388.3  | 6795.6  | 6838.4  | 6762.7  | 6571.7  | 5248.2 | 5225.1  | 5284.4  |
| 30°    | 9011.5  | 8547.2  | 7200.6  | 7144.6  | 7194.0  | 7095.2  | 5524.7  | 5472.1 | 5472.1  | 5531.3  |
| 32.5°  | 9564.6  | 7753.7  | 7641.8  | 7648.4  | 7615.5  | 6496.0  | 5814.5  | 5801.3 | 5840.8  | 5890.2  |
| 35°    | 9409.8  | 8270.7  | 8280.5  | 8336.5  | 8260.8  | 6354.4  | 6268.8  | 6219.5 | 6252.4  | 6272.1  |
| 37.5°  | 9106.9  | 9047.7  | 9047.7  | 8985.1  | 7052.4  | 6851.6  | 6759.4  | 6752.8 | 6749.5  | 6749.5  |
| 40°    | 9870.8  | 9814.8  | 9745.7  | 9637.0  | 7378.4  | 7431.1  | 7292.8  | 7276.3 | 7286.2  | 7322.4  |
| 42.5°  | 10740.0 | 10716.9 | 10710.4 | 8270.7  | 8056.6  | 8096.2  | 7948.0  | 7905.2 | 7905.2  | 7987.5  |
| 45°    | 11763.9 | 11734.3 | 11006.7 | 8840.2  | 8804.0  | 8850.1  | 8685.5  | 8583.4 | 8639.4  | 8698.7  |
| 47.5°  | 12939.4 | 12939.4 | 9745.7  | 9693.0  | 9693.0  | 9719.3  | 9554.7  | 9416.4 | 9472.4  | 9492.2  |
| 50°    | 14226.7 | 12215.0 | 10723.5 | 10674.1 | 10720.2 | 10707.1 | 10535.9 | 9251.8 | 10440.4 | 10450.3 |
| 52.5°  | 14585.6 | 11879.2 | 11796.9 | 11740.9 | 11796.9 | 11787.0 | 11609.2 | 7717.5 | 11293.1 | 11454.5 |
| 55°    | 12929.5 | 12939.4 | 12922.9 | 12840.6 | 12899.8 | 12876.8 | 12702.3 | 8425.4 | 8326.6  | 7421.2  |
| 57.5°  | 13979.8 | 13992.9 | 13986.4 | 13973.2 | 14025.9 | 10190.2 | 13156.7 | 7612.2 | 4648.9  | 4652.2  |
| 60°    | 15122.3 | 15056.4 | 15036.7 | 15007.0 | 12718.8 | 7223.7  | 5481.9  | 530.1  | 1817.4  | 1791.1  |
| 62.5°  | 16159.4 | 16136.3 | 16067.2 | 16050.7 | 10792.7 | 5689.4  | 5557.7  | 121.8  | 95.5    | 92.2    |
| 65°    | 17601.5 | 17397.3 | 17341.4 | 17166.9 | 11503.8 | 6058.1  | 5933.0  | 36.2   | 3.3     | 0.0     |
| 67.5°  | 18138.1 | 17723.3 | 17522.5 | 17430.3 | 11704.7 | 6249.1  | 6008.7  | 36.2   | 3.3     | 0.0     |
| 70°    | 17124.1 | 16610.4 | 16356.9 | 16254.9 | 10937.5 | 5840.8  | 5603.8  | 36.2   | 3.3     | 0.0     |
| 72.5°  | 15184.8 | 14806.2 | 14704.1 | 14378.2 | 9643.6  | 5126.4  | 4918.9  | 36.2   | 0.0     | 0.0     |
| 75°    | 12455.4 | 12317.1 | 12192.0 | 11846.3 | 7839.3  | 4072.8  | 3888.4  | 32.9   | 0.0     | 0.0     |
| 77.5°  | 9064.1  | 8860.0  | 8629.5  | 8254.2  | 5291.0  | 2660.3  | 2564.8  | 29.6   | 0.0     | 0.0     |
| 80°    | 4085.9  | 3918.0  | 3862.1  | 3276.0  | 1876.7  | 865.9   | 763.8   | 26.3   | 0.0     | 0.0     |
| 82.5°  | 793.5   | 714.5   | 678.2   | 651.9   | 421.4   | 233.8   | 204.1   | 19.8   | 0.0     | 0.0     |
| 85°    | 270.0   | 299.6   | 349.0   | 385.2   | 237.1   | 141.6   | 118.5   | 13.2   | 0.0     | 0.0     |
| 87.5°  | 105.4   | 141.6   | 171.2   | 177.8   | 88.9    | 59.3    | 32.9    | 6.6    | 0.0     | 0.0     |
| 90°    | 19.8    | 26.3    | 23.0    | 16.5    | 9.9     | 3.3     | 0.0     | 0.0    | 0.0     | 0.0     |
| 92.5°  | 9.9     | 13.2    | 9.9     | 9.9     | 6.6     | 3.3     | 0.0     | 0.0    | 0.0     | 0.0     |
| 95°    | 13.2    | 13.2    | 13.2    | 9.9     | 6.6     | 3.3     | 0.0     | 0.0    | 0.0     | 0.0     |
| 97.5°  | 13.2    | 13.2    | 13.2    | 9.9     | 6.6     | 3.3     | 0.0     | 0.0    | 0.0     | 0.0     |
| 100°   | 13.2    | 13.2    | 13.2    | 9.9     | 6.6     | 3.3     | 0.0     | 0.0    | 0.0     | 0.0     |
| 102.5° | 13.2    | 13.2    | 13.2    | 9.9     | 6.6     | 3.3     | 0.0     | 0.0    | 0.0     | 0.0     |
| 105°   | 13.2    | 16.5    | 13.2    | 9.9     | 6.6     | 3.3     | 0.0     | 0.0    | 0.0     | 0.0     |
| 107.5° | 13.2    | 16.5    | 13.2    | 9.9     | 6.6     | 3.3     | 0.0     | 0.0    | 0.0     | 0.0     |
| 110°   | 13.2    | 16.5    | 13.2    | 9.9     | 6.6     | 3.3     | 0.0     | 0.0    | 0.0     | 0.0     |



REPORT NUMBER: P579490

CATALOG NUMBER: CST-CA10-760-740-U-T5-HSS-HM-EX120

**CANDELA DISTRIBUTION (continued):**

|        | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|--------|-----|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2104-215-1

Luminaire Tested: CST-CA6-230-740-U-T4

Test Date: 04/20/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2104-215-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/20/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **CST-CA6-230-740-U-T4**  
 Description: STREETWORKS HIGH MAST LUMINAIRE

230W

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3783    | CRI (Ra): | 75.1 |      |       |
| CIE u':                   | 0.2297  | R1:       | 72.8 | R9:  | -19.0 |
| CIE v':                   | 0.5046  | R2:       | 81.9 | R10: | 57.0  |
| Duv:                      | -0.0008 | R3:       | 89.0 | R11: | 70.7  |
| CIE x:                    | 0.3897  | R4:       | 74.1 | R12: | 48.2  |
| CIE y:                    | 0.3804  | R5:       | 72.3 | R13: | 74.4  |
| CIE z:                    | 0.2299  | R6:       | 74.5 | R14: | 93.7  |
| Peak Wavelength (nm):     | 450     | R7:       | 81.7 |      |       |
| Dominant Wavelength (nm): | 580     | R8:       | 54.6 |      |       |
| Purity:                   | 31.3    |           |      |      |       |
| Rf:                       | 76.5    |           |      |      |       |
| Rg:                       | 95.6    |           |      |      |       |



### Test Conditions

Stabilization Time: 47M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.5/39%  
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2104-215-1

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2104-215-1

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP1-2104-215-1

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 13329            | 0.0              | 490       | 105235           | 15.0             | 620       | 524343           | 136.4            | 750       | 24224            | 0.0              | 880       | 16135            | 0.0              |
| 365       | 11697            | 0.0              | 495       | 137678           | 25.0             | 625       | 488932           | 107.9            | 755       | 22376            | 0.0              | 885       | 16876            | 0.0              |
| 370       | 10917            | 0.0              | 500       | 186689           | 41.2             | 630       | 445400           | 80.6             | 760       | 20109            | 0.0              | 890       | 13554            | 0.0              |
| 375       | 12548            | 0.0              | 505       | 244611           | 68.4             | 635       | 403534           | 60.6             | 765       | 18097            | 0.0              | 895       | 11525            | 0.0              |
| 380       | 13932            | 0.0              | 510       | 298987           | 102.7            | 640       | 366414           | 43.8             | 770       | 17366            | 0.0              | 900       | 14656            | 0.0              |
| 385       | 13265            | 0.0              | 515       | 348170           | 144.2            | 645       | 331272           | 31.9             | 775       | 16226            | 0.0              | 905       | 11999            | 0.0              |
| 390       | 11808            | 0.0              | 520       | 390427           | 189.3            | 650       | 297360           | 21.7             | 780       | 14803            | 0.0              | 910       | 12965            | 0.0              |
| 395       | 10395            | 0.0              | 525       | 421211           | 226.1            | 655       | 263291           | 15.1             | 785       | 15199            | 0.0              | 915       | 15939            | 0.0              |
| 400       | 9348             | 0.0              | 530       | 446063           | 262.6            | 660       | 232931           | 9.7              | 790       | 12989            | 0.0              | 920       | 16238            | 0.0              |
| 405       | 9479             | 0.0              | 535       | 465110           | 288.4            | 665       | 204719           | 6.5              | 795       | 12106            | 0.0              | 925       | 14419            | 0.0              |
| 410       | 12414            | 0.0              | 540       | 479189           | 312.2            | 670       | 177096           | 3.9              | 800       | 12942            | 0.0              | 930       | 14788            | 0.0              |
| 415       | 21574            | 0.0              | 545       | 495864           | 330.0            | 675       | 153254           | 2.6              | 805       | 13253            | 0.0              | 935       | 18619            | 0.0              |
| 420       | 41448            | 0.1              | 550       | 516625           | 351.1            | 680       | 132874           | 1.5              | 810       | 12808            | 0.0              | 940       | 13995            | 0.0              |
| 425       | 79385            | 0.4              | 555       | 538555           | 367.8            | 685       | 115378           | 1.0              | 815       | 12903            | 0.0              | 945       | 18047            | 0.0              |
| 430       | 141845           | 1.1              | 560       | 562412           | 382.2            | 690       | 100157           | 0.6              | 820       | 12621            | 0.0              | 950       | 21418            | 0.0              |
| 435       | 231290           | 2.7              | 565       | 585835           | 389.5            | 695       | 85561            | 0.4              | 825       | 13903            | 0.0              | 955       | 23138            | 0.0              |
| 440       | 374482           | 5.9              | 570       | 608681           | 395.8            | 700       | 75396            | 0.2              | 830       | 11870            | 0.0              | 960       | 13665            | 0.0              |
| 445       | 596715           | 12.4             | 575       | 629563           | 391.7            | 705       | 65658            | 0.1              | 835       | 11069            | 0.0              | 965       | 14793            | 0.0              |
| 450       | 719656           | 18.7             | 580       | 646820           | 384.3            | 710       | 58172            | 0.1              | 840       | 15291            | 0.0              | 970       | 14396            | 0.0              |
| 455       | 530438           | 17.8             | 585       | 659231           | 366.3            | 715       | 52563            | 0.1              | 845       | 15125            | 0.0              | 975       | 11155            | 0.0              |
| 460       | 330446           | 13.5             | 590       | 665630           | 344.2            | 720       | 47085            | 0.0              | 850       | 15336            | 0.0              | 980       | 17987            | 0.0              |
| 465       | 241999           | 12.5             | 595       | 656228           | 311.1            | 725       | 41741            | 0.0              | 855       | 15791            | 0.0              | 985       | 16185            | 0.0              |
| 470       | 167096           | 10.4             | 600       | 646946           | 278.8            | 730       | 37415            | 0.0              | 860       | 14660            | 0.0              | 990       | 22120            | 0.0              |
| 475       | 113791           | 8.9              | 605       | 628643           | 243.4            | 735       | 32125            | 0.0              | 865       | 12528            | 0.0              | 995       | 11943            | 0.0              |
| 480       | 96126            | 9.1              | 610       | 599057           | 205.8            | 740       | 29322            | 0.0              | 870       | 14089            | 0.0              | 1000      | 16020            | 0.0              |
| 485       | 94467            | 11.2             | 615       | 565669           | 170.8            | 745       | 26862            | 0.0              | 875       | 11732            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-1

### Scotopic Flux vs. Wavelength



Scotopic Lumens: 54268.8

S/P: 1.5

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 13329                         | 0.0                            | 490               | 105235                        | 162.0                          | 620               | 524343                        | 6.6                            | 750               | 24224                         | 0.0                            | 880               | 16135                         | 0.0                            |
| 365               | 11697                         | 0.0                            | 495               | 137678                        | 222.6                          | 625               | 488932                        | 4.1                            | 755               | 22376                         | 0.0                            | 885               | 16876                         | 0.0                            |
| 370               | 10917                         | 0.0                            | 500               | 186689                        | 312.3                          | 630               | 445400                        | 2.5                            | 760               | 20109                         | 0.0                            | 890               | 13554                         | 0.0                            |
| 375               | 12548                         | 0.0                            | 505               | 244611                        | 415.8                          | 635               | 403534                        | 1.5                            | 765               | 18097                         | 0.0                            | 895               | 11525                         | 0.0                            |
| 380               | 13932                         | 0.0                            | 510               | 298987                        | 506.8                          | 640               | 366414                        | 0.9                            | 770               | 17366                         | 0.0                            | 900               | 14656                         | 0.0                            |
| 385               | 13265                         | 0.0                            | 515               | 348170                        | 577.1                          | 645               | 331272                        | 0.6                            | 775               | 16226                         | 0.0                            | 905               | 11999                         | 0.0                            |
| 390               | 11808                         | 0.0                            | 520               | 390427                        | 620.6                          | 650               | 297360                        | 0.3                            | 780               | 14803                         | 0.0                            | 910               | 12965                         | 0.0                            |
| 395               | 10395                         | 0.1                            | 525               | 421211                        | 630.1                          | 655               | 263291                        | 0.2                            | 785               | 15199                         | 0.0                            | 915               | 15939                         | 0.0                            |
| 400               | 9348                          | 0.1                            | 530               | 446063                        | 615.0                          | 660               | 232931                        | 0.1                            | 790               | 12989                         | 0.0                            | 920               | 16238                         | 0.0                            |
| 405               | 9479                          | 0.3                            | 535               | 465110                        | 579.6                          | 665               | 204719                        | 0.1                            | 795               | 12106                         | 0.0                            | 925               | 14419                         | 0.0                            |
| 410               | 12414                         | 0.7                            | 540               | 479189                        | 529.5                          | 670               | 177096                        | 0.0                            | 800               | 12942                         | 0.0                            | 930               | 14788                         | 0.0                            |
| 415               | 21574                         | 2.2                            | 545               | 495864                        | 475.4                          | 675               | 153254                        | 0.0                            | 805               | 13253                         | 0.0                            | 935               | 18619                         | 0.0                            |
| 420               | 41448                         | 6.8                            | 550               | 516625                        | 422.4                          | 680               | 132874                        | 0.0                            | 810               | 12808                         | 0.0                            | 940               | 13995                         | 0.0                            |
| 425               | 79385                         | 19.4                           | 555               | 538555                        | 368.0                          | 685               | 115378                        | 0.0                            | 815               | 12903                         | 0.0                            | 945               | 18047                         | 0.0                            |
| 430               | 141845                        | 48.3                           | 560               | 562412                        | 314.4                          | 690               | 100157                        | 0.0                            | 820               | 12621                         | 0.0                            | 950               | 21418                         | 0.0                            |
| 435               | 231290                        | 103.4                          | 565               | 585835                        | 262.8                          | 695               | 85561                         | 0.0                            | 825               | 13903                         | 0.0                            | 955               | 23138                         | 0.0                            |
| 440               | 374482                        | 209.3                          | 570               | 608681                        | 214.8                          | 700               | 75396                         | 0.0                            | 830               | 11870                         | 0.0                            | 960               | 13665                         | 0.0                            |
| 445               | 596715                        | 399.6                          | 575               | 629563                        | 171.5                          | 705               | 65658                         | 0.0                            | 835               | 11069                         | 0.0                            | 965               | 14793                         | 0.0                            |
| 450               | 719656                        | 557.8                          | 580               | 646820                        | 133.3                          | 710               | 58172                         | 0.0                            | 840               | 15291                         | 0.0                            | 970               | 14396                         | 0.0                            |
| 455               | 530438                        | 463.5                          | 585               | 659231                        | 100.8                          | 715               | 52563                         | 0.0                            | 845               | 15125                         | 0.0                            | 975               | 11155                         | 0.0                            |
| 460               | 330446                        | 319.2                          | 590               | 665630                        | 74.1                           | 720               | 47085                         | 0.0                            | 850               | 15336                         | 0.0                            | 980               | 17987                         | 0.0                            |
| 465               | 241999                        | 255.6                          | 595               | 656228                        | 52.3                           | 725               | 41741                         | 0.0                            | 855               | 15791                         | 0.0                            | 985               | 16185                         | 0.0                            |
| 470               | 167096                        | 192.4                          | 600               | 646946                        | 36.5                           | 730               | 37415                         | 0.0                            | 860               | 14660                         | 0.0                            | 990               | 22120                         | 0.0                            |
| 475               | 113791                        | 142.3                          | 605               | 628643                        | 24.7                           | 735               | 32125                         | 0.0                            | 865               | 12528                         | 0.0                            | 995               | 11943                         | 0.0                            |
| 480               | 96126                         | 129.8                          | 610               | 599057                        | 16.2                           | 740               | 29322                         | 0.0                            | 870               | 14089                         | 0.0                            | 1000              | 16020                         | 0.0                            |
| 485               | 94467                         | 136.9                          | 615               | 565669                        | 10.5                           | 745               | 26862                         | 0.0                            | 875               | 11732                         | 0.0                            |                   |                               |                                |



REPORT NUMBER: SP1-2104-215-1

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: 20938.3      M/P: 0.58**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 13329            | 0.0              | 490       | 105235           | 87.6             | 620       | 524343           | 0.4              | 750       | 24224            | 0.0              | 880       | 16135            | 0.0              |
| 365       | 11697            | 0.0              | 495       | 137678           | 113.7            | 625       | 488932           | 0.3              | 755       | 22376            | 0.0              | 885       | 16876            | 0.0              |
| 370       | 10917            | 0.0              | 500       | 186689           | 150.1            | 630       | 445400           | 0.2              | 760       | 20109            | 0.0              | 890       | 13554            | 0.0              |
| 375       | 12548            | 0.0              | 505       | 244611           | 187.7            | 635       | 403534           | 0.1              | 765       | 18097            | 0.0              | 895       | 11525            | 0.0              |
| 380       | 13932            | 0.0              | 510       | 298987           | 214.7            | 640       | 366414           | 0.1              | 770       | 17366            | 0.0              | 900       | 14656            | 0.0              |
| 385       | 13265            | 0.0              | 515       | 348170           | 227.5            | 645       | 331272           | 0.0              | 775       | 16226            | 0.0              | 905       | 11999            | 0.0              |
| 390       | 11808            | 0.0              | 520       | 390427           | 227.3            | 650       | 297360           | 0.0              | 780       | 14803            | 0.0              | 910       | 12965            | 0.0              |
| 395       | 10395            | 0.1              | 525       | 421211           | 213.6            | 655       | 263291           | 0.0              | 785       | 15199            | 0.0              | 915       | 15939            | 0.0              |
| 400       | 9348             | 0.1              | 530       | 446063           | 192.8            | 660       | 232931           | 0.0              | 790       | 12989            | 0.0              | 920       | 16238            | 0.0              |
| 405       | 9479             | 0.2              | 535       | 465110           | 167.4            | 665       | 204719           | 0.0              | 795       | 12106            | 0.0              | 925       | 14419            | 0.0              |
| 410       | 12414            | 0.5              | 540       | 479189           | 140.2            | 670       | 177096           | 0.0              | 800       | 12942            | 0.0              | 930       | 14788            | 0.0              |
| 415       | 21574            | 1.4              | 545       | 495864           | 115.2            | 675       | 153254           | 0.0              | 805       | 13253            | 0.0              | 935       | 18619            | 0.0              |
| 420       | 41448            | 4.7              | 550       | 516625           | 92.7             | 680       | 132874           | 0.0              | 810       | 12808            | 0.0              | 940       | 13995            | 0.0              |
| 425       | 79385            | 12.4             | 555       | 538555           | 72.6             | 685       | 115378           | 0.0              | 815       | 12903            | 0.0              | 945       | 18047            | 0.0              |
| 430       | 141845           | 30.0             | 560       | 562412           | 55.5             | 690       | 100157           | 0.0              | 820       | 12621            | 0.0              | 950       | 21418            | 0.0              |
| 435       | 231290           | 61.7             | 565       | 585835           | 41.1             | 695       | 85561            | 0.0              | 825       | 13903            | 0.0              | 955       | 23138            | 0.0              |
| 440       | 374482           | 125.1            | 570       | 608681           | 29.7             | 700       | 75396            | 0.0              | 830       | 11870            | 0.0              | 960       | 13665            | 0.0              |
| 445       | 596715           | 235.4            | 575       | 629563           | 21.0             | 705       | 65658            | 0.0              | 835       | 11069            | 0.0              | 965       | 14793            | 0.0              |
| 450       | 719656           | 331.6            | 580       | 646820           | 14.5             | 710       | 58172            | 0.0              | 840       | 15291            | 0.0              | 970       | 14396            | 0.0              |
| 455       | 530438           | 277.9            | 585       | 659231           | 9.8              | 715       | 52563            | 0.0              | 845       | 15125            | 0.0              | 975       | 11155            | 0.0              |
| 460       | 330446           | 194.7            | 590       | 665630           | 6.5              | 720       | 47085            | 0.0              | 850       | 15336            | 0.0              | 980       | 17987            | 0.0              |
| 465       | 241999           | 158.1            | 595       | 656228           | 4.2              | 725       | 41741            | 0.0              | 855       | 15791            | 0.0              | 985       | 16185            | 0.0              |
| 470       | 167096           | 119.6            | 600       | 646946           | 2.7              | 730       | 37415            | 0.0              | 860       | 14660            | 0.0              | 990       | 22120            | 0.0              |
| 475       | 113791           | 86.9             | 605       | 628643           | 1.7              | 735       | 32125            | 0.0              | 865       | 12528            | 0.0              | 995       | 11943            | 0.0              |
| 480       | 96126            | 77.2             | 610       | 599057           | 1.1              | 740       | 29322            | 0.0              | 870       | 14089            | 0.0              | 1000      | 16020            | 0.0              |
| 485       | 94467            | 77.9             | 615       | 565669           | 0.7              | 745       | 26862            | 0.0              | 875       | 11732            | 0.0              |           |                  |                  |

### Summary

$R_f = 76.5$   
 $R_g = 95.6$   
 CIE  $R_a = 75.1$   
 $R_g = -19.0$




### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 66 | CES51 = 90 | CES76 = 56 |
| CES02 = 61 | CES27 = 89 | CES52 = 89 | CES77 = 73 |
| CES03 = 31 | CES28 = 83 | CES53 = 81 | CES78 = 58 |
| CES04 = 70 | CES29 = 69 | CES54 = 87 | CES79 = 84 |
| CES05 = 48 | CES30 = 84 | CES55 = 86 | CES80 = 81 |
| CES06 = 51 | CES31 = 72 | CES56 = 77 | CES81 = 79 |
| CES07 = 40 | CES32 = 64 | CES57 = 77 | CES82 = 92 |
| CES08 = 39 | CES33 = 79 | CES58 = 77 | CES83 = 90 |
| CES09 = 29 | CES34 = 73 | CES59 = 87 | CES84 = 87 |
| CES10 = 74 | CES35 = 85 | CES60 = 90 | CES85 = 78 |
| CES11 = 57 | CES36 = 91 | CES61 = 84 | CES86 = 73 |
| CES12 = 63 | CES37 = 81 | CES62 = 87 | CES87 = 79 |
| CES13 = 42 | CES38 = 94 | CES63 = 75 | CES88 = 83 |
| CES14 = 74 | CES39 = 96 | CES64 = 69 | CES89 = 73 |
| CES15 = 71 | CES40 = 91 | CES65 = 66 | CES90 = 83 |
| CES16 = 47 | CES41 = 94 | CES66 = 63 | CES91 = 76 |
| CES17 = 49 | CES42 = 82 | CES67 = 60 | CES92 = 62 |
| CES18 = 56 | CES43 = 78 | CES68 = 68 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 76 | CES94 = 57 |
| CES20 = 65 | CES45 = 86 | CES70 = 60 | CES95 = 69 |
| CES21 = 86 | CES46 = 84 | CES71 = 54 | CES96 = 79 |
| CES22 = 78 | CES47 = 87 | CES72 = 85 | CES97 = 86 |
| CES23 = 92 | CES48 = 80 | CES73 = 52 | CES98 = 79 |
| CES24 = 91 | CES49 = 82 | CES74 = 94 | CES99 = 69 |
| CES25 = 72 | CES50 = 90 | CES75 = 56 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)