

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P510644

Luminaire Tested: **CST-CA6-230-722-U-T5R**

Issue Date: 4/6/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P510644  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/6/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: CST-CA6-230-722-U-T5R  
Description: CELESTEON HIGH MAST LUMINAIRE  
Light Source: (6) 2200K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 30052 lumens  
Efficiency: N/A  
Efficacy: 131.9 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G4


Input Watts (W): 227.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P510644  
 CATALOG NUMBER: CST-CA6-230-722-U-T5R

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 2.5 fc  
 Type V - Short - N/A

REPORT NUMBER: P510644  
CATALOG NUMBER: CST-CA6-230-722-U-T5R

## Luminous Intensity Polar Plot



REPORT NUMBER: P510644

CATALOG NUMBER: CST-CA6-230-722-U-T5R


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 15026.0  | 0.0    | 15026.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 15026.0  | 0.0    | 15026.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 30052.0  | 0.0    | 30052.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 210.6   | 0.7       |
| 10°-20°   | 652.6   | 2.2       |
| 20°-30°   | 1238.4  | 4.1       |
| 30°-40°   | 2150.9  | 7.2       |
| 40°-50°   | 3743.9  | 12.5      |
| 50°-60°   | 6396.0  | 21.3      |
| 60°-70°   | 9419.4  | 31.3      |
| 70°-80°   | 5987.7  | 19.9      |
| 80°-90°   | 252.6   | 0.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 30052.0 | 100.0     |
| 0°-180°   | 30052.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P510644


CATALOG NUMBER: CST-CA6-230-722-U-T5R

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|--------|-----------|-------------------------|------|----------|
|      |             |        |           | B                       | U    | G        |
| FL   | (0°-30°)    | 1050.8 | 3.5       |                         |      |          |
| FM   | (30°-60°)   | 6145.4 | 20.4      |                         |      |          |
| FH   | (60°-80°)   | 7703.5 | 25.6      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 126.3  | 0.4       |                         |      | G2/225   |
| BL   | (0°-30°)    | 1050.8 | 3.5       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 6145.4 | 20.4      | B4/8500                 |      |          |
| BH   | (60°-80°)   | 7703.5 | 25.6      | B5                      |      | G4/12000 |
| BVH  | (80°-90°)   | 126.3  | 0.4       |                         |      | G2/225   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |          |

**BUG Rating: B5-U0-G4**

Type V Short



FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

REPORT NUMBER: P510644  
CATALOG NUMBER: CST-CA6-230-722-U-T5R

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 2210.5  |
| 2.5°  | 2211.1  |
| 5°    | 2206.7  |
| 7.5°  | 2203.0  |
| 10°   | 2206.7  |
| 12.5° | 2230.5  |
| 15°   | 2276.2  |
| 17.5° | 2340.2  |
| 20°   | 2427.0  |
| 22.5° | 2529.6  |
| 25°   | 2650.5  |
| 27.5° | 2781.4  |
| 30°   | 2935.5  |
| 32.5° | 3124.7  |
| 35°   | 3373.3  |
| 37.5° | 3659.4  |
| 40°   | 3977.4  |
| 42.5° | 4334.7  |
| 45°   | 4758.8  |
| 47.5° | 5247.9  |
| 50°   | 5814.3  |
| 52.5° | 6426.1  |
| 55°   | 7097.4  |
| 57.5° | 7767.7  |
| 60°   | 8434.3  |
| 62.5° | 9102.8  |
| 65°   | 9898.8  |
| 67.5° | 10067.8 |
| 70°   | 9275.4  |
| 72.5° | 7889.2  |
| 75°   | 5989.7  |
| 77.5° | 3661.9  |
| 80°   | 1162.3  |
| 82.5° | 197.3   |
| 85°   | 111.5   |
| 87.5° | 40.4    |
| 90°   | 0.0     |

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2104-215-4

Luminaire Tested: CST-CA10-630-722-U-T3


Test Date: 04/20/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2104-215-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/20/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **CST-CA10-630-722-U-T3**  
 Description: STREETWORKS HIGH MAST LUMINAIRE

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 2174    | CRI (Ra): | 72.8 |      |       |
| CIE u':                   | 0.2919  | R1:       | 70.2 | R9:  | -23.3 |
| CIE v':                   | 0.5354  | R2:       | 86.8 | R10: | 71.8  |
| Duv:                      | -0.0007 | R3:       | 92.8 | R11: | 63.6  |
| CIE x:                    | 0.5067  | R4:       | 66.8 | R12: | 66.0  |
| CIE y:                    | 0.4131  | R5:       | 69.1 | R13: | 73.5  |
| CIE z:                    | 0.0802  | R6:       | 84.7 | R14: | 96.9  |
| Peak Wavelength (nm):     | 608     | R7:       | 73.2 |      |       |
| Dominant Wavelength (nm): | 587     | R8:       | 39.0 |      |       |
| Purity:                   | 76.7    |           |      |      |       |
| Rf:                       | 75.7    |           |      |      |       |
| Rg:                       | 96.7    |           |      |      |       |



### Test Conditions


Stabilization Time: 79M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.7/32%  
 Sphere Temperature (°C): 24.8

REPORT NUMBER: SP1-2104-215-4


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2104-215-4

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2104-215-4

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 23398            | 0.0              | 490       | 137099           | 19.5             | 620       | 2038916          | 530.6            | 750       | 99721            | 0.0              | 880       | 32326            | 0.0              |
| 365       | 18626            | 0.0              | 495       | 174286           | 31.6             | 625       | 1946743          | 429.5            | 755       | 91432            | 0.0              | 885       | 29783            | 0.0              |
| 370       | 21702            | 0.0              | 500       | 232711           | 51.3             | 630       | 1814508          | 328.4            | 760       | 83300            | 0.0              | 890       | 12135            | 0.0              |
| 375       | 22606            | 0.0              | 505       | 303528           | 84.9             | 635       | 1681061          | 252.6            | 765       | 72172            | 0.0              | 895       | 22953            | 0.0              |
| 380       | 25296            | 0.0              | 510       | 374456           | 128.6            | 640       | 1557170          | 186.1            | 770       | 65008            | 0.0              | 900       | 27214            | 0.0              |
| 385       | 27032            | 0.0              | 515       | 445274           | 184.5            | 645       | 1430182          | 137.7            | 775       | 56809            | 0.0              | 905       | 17038            | 0.0              |
| 390       | 22156            | 0.0              | 520       | 510296           | 247.5            | 650       | 1300435          | 95.0             | 780       | 49368            | 0.0              | 910       | 6896             | 0.0              |
| 395       | 20190            | 0.0              | 525       | 566771           | 304.3            | 655       | 1165554          | 66.9             | 785       | 51733            | 0.0              | 915       | 17142            | 0.0              |
| 400       | 18423            | 0.0              | 530       | 617892           | 363.8            | 660       | 1044122          | 43.5             | 790       | 41796            | 0.0              | 920       | 7675             | 0.0              |
| 405       | 16139            | 0.0              | 535       | 664903           | 412.3            | 665       | 932131           | 29.6             | 795       | 42601            | 0.0              | 925       | 21587            | 0.0              |
| 410       | 19812            | 0.0              | 540       | 711603           | 463.7            | 670       | 808971           | 17.7             | 800       | 36382            | 0.0              | 930       | 32992            | 0.0              |
| 415       | 29121            | 0.1              | 545       | 768835           | 511.7            | 675       | 701208           | 11.7             | 805       | 41419            | 0.0              | 935       | 35464            | 0.0              |
| 420       | 46007            | 0.1              | 550       | 841179           | 571.6            | 680       | 610741           | 7.1              | 810       | 35865            | 0.0              | 940       | 34460            | 0.0              |
| 425       | 76329            | 0.4              | 555       | 932641           | 637.0            | 685       | 533825           | 4.6              | 815       | 39722            | 0.0              | 945       | 46305            | 0.0              |
| 430       | 117696           | 0.9              | 560       | 1040487          | 707.1            | 690       | 459427           | 2.6              | 820       | 37236            | 0.0              | 950       | 38353            | 0.0              |
| 435       | 166890           | 2.0              | 565       | 1164360          | 774.2            | 695       | 399973           | 1.7              | 825       | 31566            | 0.0              | 955       | 30772            | 0.0              |
| 440       | 227762           | 3.6              | 570       | 1307677          | 850.3            | 700       | 347460           | 1.0              | 830       | 42647            | 0.0              | 960       | 32413            | 0.0              |
| 445       | 315427           | 6.6              | 575       | 1470810          | 915.2            | 705       | 302187           | 0.6              | 835       | 41433            | 0.0              | 965       | 35310            | 0.0              |
| 450       | 409560           | 10.6             | 580       | 1637734          | 973.2            | 710       | 262909           | 0.4              | 840       | 24213            | 0.0              | 970       | 28048            | 0.0              |
| 455       | 381103           | 12.8             | 585       | 1807622          | 1004.4           | 715       | 236689           | 0.3              | 845       | 31358            | 0.0              | 975       | 26258            | 0.0              |
| 460       | 269221           | 11.0             | 590       | 1958195          | 1012.4           | 720       | 209675           | 0.1              | 850       | 30957            | 0.0              | 980       | 31067            | 0.0              |
| 465       | 203513           | 10.5             | 595       | 2055425          | 974.3            | 725       | 184999           | 0.1              | 855       | 38865            | 0.0              | 985       | 40288            | 0.0              |
| 470       | 163989           | 10.2             | 600       | 2141598          | 923.0            | 730       | 160261           | 0.1              | 860       | 23238            | 0.0              | 990       | 29366            | 0.0              |
| 475       | 129159           | 10.1             | 605       | 2185430          | 846.3            | 735       | 140736           | 0.0              | 865       | 32686            | 0.0              | 995       | 54854            | 0.0              |
| 480       | 115440           | 11.0             | 610       | 2170089          | 745.5            | 740       | 125207           | 0.0              | 870       | 41855            | 0.0              | 1000      | 50994            | 0.0              |
| 485       | 120959           | 14.3             | 615       | 2123505          | 641.1            | 745       | 110736           | 0.0              | 875       | 35838            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-4

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 72942.9

S/P: 0.88

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 23398            | 0.0              | 490       | 137099           | 211.1            | 620       | 2038916          | 25.5             | 750       | 99721            | 0.0              | 880       | 32326            | 0.0              |
| 365       | 18626            | 0.0              | 495       | 174286           | 281.7            | 625       | 1946743          | 16.4             | 755       | 91432            | 0.0              | 885       | 29783            | 0.0              |
| 370       | 21702            | 0.0              | 500       | 232711           | 389.3            | 630       | 1814508          | 10.3             | 760       | 83300            | 0.0              | 890       | 12135            | 0.0              |
| 375       | 22606            | 0.0              | 505       | 303528           | 516.0            | 635       | 1681061          | 6.4              | 765       | 72172            | 0.0              | 895       | 22953            | 0.0              |
| 380       | 25296            | 0.0              | 510       | 374456           | 634.7            | 640       | 1557170          | 4.0              | 770       | 65008            | 0.0              | 900       | 27214            | 0.0              |
| 385       | 27032            | 0.1              | 515       | 445274           | 738.0            | 645       | 1430182          | 2.4              | 775       | 56809            | 0.0              | 905       | 17038            | 0.0              |
| 390       | 22156            | 0.1              | 520       | 510296           | 811.1            | 650       | 1300435          | 1.5              | 780       | 49368            | 0.0              | 910       | 6896             | 0.0              |
| 395       | 20190            | 0.2              | 525       | 566771           | 847.9            | 655       | 1165554          | 0.9              | 785       | 51733            | 0.0              | 915       | 17142            | 0.0              |
| 400       | 18423            | 0.3              | 530       | 617892           | 851.9            | 660       | 1044122          | 0.6              | 790       | 41796            | 0.0              | 920       | 7675             | 0.0              |
| 405       | 16139            | 0.5              | 535       | 664903           | 828.5            | 665       | 932131           | 0.3              | 795       | 42601            | 0.0              | 925       | 21587            | 0.0              |
| 410       | 19812            | 1.2              | 540       | 711603           | 786.3            | 670       | 808971           | 0.2              | 800       | 36382            | 0.0              | 930       | 32992            | 0.0              |
| 415       | 29121            | 3.0              | 545       | 768835           | 737.2            | 675       | 701208           | 0.1              | 805       | 41419            | 0.0              | 935       | 35464            | 0.0              |
| 420       | 46007            | 7.6              | 550       | 841179           | 687.8            | 680       | 610741           | 0.1              | 810       | 35865            | 0.0              | 940       | 34460            | 0.0              |
| 425       | 76329            | 18.7             | 555       | 932641           | 637.4            | 685       | 533825           | 0.0              | 815       | 39722            | 0.0              | 945       | 46305            | 0.0              |
| 430       | 117696           | 40.1             | 560       | 1040487          | 581.6            | 690       | 459427           | 0.0              | 820       | 37236            | 0.0              | 950       | 38353            | 0.0              |
| 435       | 166890           | 74.6             | 565       | 1164360          | 522.4            | 695       | 399973           | 0.0              | 825       | 31566            | 0.0              | 955       | 30772            | 0.0              |
| 440       | 227762           | 127.3            | 570       | 1307677          | 461.5            | 700       | 347460           | 0.0              | 830       | 42647            | 0.0              | 960       | 32413            | 0.0              |
| 445       | 315427           | 211.2            | 575       | 1470810          | 400.6            | 705       | 302187           | 0.0              | 835       | 41433            | 0.0              | 965       | 35310            | 0.0              |
| 450       | 409560           | 317.4            | 580       | 1637734          | 337.4            | 710       | 262909           | 0.0              | 840       | 24213            | 0.0              | 970       | 28048            | 0.0              |
| 455       | 381103           | 333.0            | 585       | 1807622          | 276.3            | 715       | 236689           | 0.0              | 845       | 31358            | 0.0              | 975       | 26258            | 0.0              |
| 460       | 269221           | 260.0            | 590       | 1958195          | 218.0            | 720       | 209675           | 0.0              | 850       | 30957            | 0.0              | 980       | 31067            | 0.0              |
| 465       | 203513           | 214.9            | 595       | 2055425          | 163.9            | 725       | 184999           | 0.0              | 855       | 38865            | 0.0              | 985       | 40288            | 0.0              |
| 470       | 163989           | 188.8            | 600       | 2141598          | 120.7            | 730       | 160261           | 0.0              | 860       | 23238            | 0.0              | 990       | 29366            | 0.0              |
| 475       | 129159           | 161.5            | 605       | 2185430          | 85.9             | 735       | 140736           | 0.0              | 865       | 32686            | 0.0              | 995       | 54854            | 0.0              |
| 480       | 115440           | 155.9            | 610       | 2170089          | 58.8             | 740       | 125207           | 0.0              | 870       | 41855            | 0.0              | 1000      | 50994            | 0.0              |
| 485       | 120959           | 175.3            | 615       | 2123505          | 39.3             | 745       | 110736           | 0.0              | 875       | 35838            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-4

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 23955.7**      **M/P: 0.29**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 23398            | 0.0              | 490       | 137099           | 114.1            | 620       | 2038916          | 1.6              | 750       | 99721            | 0.0              | 880       | 32326            | 0.0              |
| 365       | 18626            | 0.0              | 495       | 174286           | 143.9            | 625       | 1946743          | 1.0              | 755       | 91432            | 0.0              | 885       | 29783            | 0.0              |
| 370       | 21702            | 0.0              | 500       | 232711           | 187.1            | 630       | 1814508          | 0.6              | 760       | 83300            | 0.0              | 890       | 12135            | 0.0              |
| 375       | 22606            | 0.0              | 505       | 303528           | 232.9            | 635       | 1681061          | 0.4              | 765       | 72172            | 0.0              | 895       | 22953            | 0.0              |
| 380       | 25296            | 0.0              | 510       | 374456           | 268.9            | 640       | 1557170          | 0.2              | 770       | 65008            | 0.0              | 900       | 27214            | 0.0              |
| 385       | 27032            | 0.0              | 515       | 445274           | 290.9            | 645       | 1430182          | 0.2              | 775       | 56809            | 0.0              | 905       | 17038            | 0.0              |
| 390       | 22156            | 0.1              | 520       | 510296           | 297.1            | 650       | 1300435          | 0.1              | 780       | 49368            | 0.0              | 910       | 6896             | 0.0              |
| 395       | 20190            | 0.1              | 525       | 566771           | 287.4            | 655       | 1165554          | 0.1              | 785       | 51733            | 0.0              | 915       | 17142            | 0.0              |
| 400       | 18423            | 0.2              | 530       | 617892           | 267.0            | 660       | 1044122          | 0.0              | 790       | 41796            | 0.0              | 920       | 7675             | 0.0              |
| 405       | 16139            | 0.3              | 535       | 664903           | 239.3            | 665       | 932131           | 0.0              | 795       | 42601            | 0.0              | 925       | 21587            | 0.0              |
| 410       | 19812            | 0.8              | 540       | 711603           | 208.3            | 670       | 808971           | 0.0              | 800       | 36382            | 0.0              | 930       | 32992            | 0.0              |
| 415       | 29121            | 1.9              | 545       | 768835           | 178.6            | 675       | 701208           | 0.0              | 805       | 41419            | 0.0              | 935       | 35464            | 0.0              |
| 420       | 46007            | 5.3              | 550       | 841179           | 151.0            | 680       | 610741           | 0.0              | 810       | 35865            | 0.0              | 940       | 34460            | 0.0              |
| 425       | 76329            | 11.9             | 555       | 932641           | 125.8            | 685       | 533825           | 0.0              | 815       | 39722            | 0.0              | 945       | 46305            | 0.0              |
| 430       | 117696           | 24.9             | 560       | 1040487          | 102.6            | 690       | 459427           | 0.0              | 820       | 37236            | 0.0              | 950       | 38353            | 0.0              |
| 435       | 166890           | 44.5             | 565       | 1164360          | 81.7             | 695       | 399973           | 0.0              | 825       | 31566            | 0.0              | 955       | 30772            | 0.0              |
| 440       | 227762           | 76.1             | 570       | 1307677          | 63.9             | 700       | 347460           | 0.0              | 830       | 42647            | 0.0              | 960       | 32413            | 0.0              |
| 445       | 315427           | 124.4            | 575       | 1470810          | 49.0             | 705       | 302187           | 0.0              | 835       | 41433            | 0.0              | 965       | 35310            | 0.0              |
| 450       | 409560           | 188.7            | 580       | 1637734          | 36.6             | 710       | 262909           | 0.0              | 840       | 24213            | 0.0              | 970       | 28048            | 0.0              |
| 455       | 381103           | 199.7            | 585       | 1807622          | 26.9             | 715       | 236689           | 0.0              | 845       | 31358            | 0.0              | 975       | 26258            | 0.0              |
| 460       | 269221           | 158.6            | 590       | 1958195          | 19.2             | 720       | 209675           | 0.0              | 850       | 30957            | 0.0              | 980       | 31067            | 0.0              |
| 465       | 203513           | 133.0            | 595       | 2055425          | 13.2             | 725       | 184999           | 0.0              | 855       | 38865            | 0.0              | 985       | 40288            | 0.0              |
| 470       | 163989           | 117.4            | 600       | 2141598          | 9.0              | 730       | 160261           | 0.0              | 860       | 23238            | 0.0              | 990       | 29366            | 0.0              |
| 475       | 129159           | 98.6             | 605       | 2185430          | 6.0              | 735       | 140736           | 0.0              | 865       | 32686            | 0.0              | 995       | 54854            | 0.0              |
| 480       | 115440           | 92.8             | 610       | 2170089          | 3.9              | 740       | 125207           | 0.0              | 870       | 41855            | 0.0              | 1000      | 50994            | 0.0              |
| 485       | 120959           | 99.7             | 615       | 2123505          | 2.5              | 745       | 110736           | 0.0              | 875       | 35838            | 0.0              |           |                  |                  |


REPORT NUMBER: SP1-2104-215-4

TM-30-18





### Summary

$R_f = 75.7$   
 $R_g = 96.7$   
 CIE  $R_a = 72.8$   
 $R_g = -23.3$

### Spectral Power Distribution Comparison







### Color Vector Graphics





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 68 | CES51 = 84 | CES76 = 70 |
| CES02 = 65 | CES27 = 88 | CES52 = 83 | CES77 = 79 |
| CES03 = 32 | CES28 = 89 | CES53 = 77 | CES78 = 73 |
| CES04 = 72 | CES29 = 66 | CES54 = 87 | CES79 = 85 |
| CES05 = 52 | CES30 = 75 | CES55 = 85 | CES80 = 84 |
| CES06 = 53 | CES31 = 69 | CES56 = 76 | CES81 = 57 |
| CES07 = 44 | CES32 = 65 | CES57 = 75 | CES82 = 93 |
| CES08 = 43 | CES33 = 73 | CES58 = 78 | CES83 = 87 |
| CES09 = 29 | CES34 = 81 | CES59 = 86 | CES84 = 92 |
| CES10 = 79 | CES35 = 91 | CES60 = 94 | CES85 = 72 |
| CES11 = 62 | CES36 = 96 | CES61 = 85 | CES86 = 52 |
| CES12 = 68 | CES37 = 90 | CES62 = 92 | CES87 = 78 |
| CES13 = 45 | CES38 = 81 | CES63 = 78 | CES88 = 77 |
| CES14 = 75 | CES39 = 94 | CES64 = 73 | CES89 = 62 |
| CES15 = 72 | CES40 = 90 | CES65 = 71 | CES90 = 77 |
| CES16 = 49 | CES41 = 86 | CES66 = 71 | CES91 = 91 |
| CES17 = 51 | CES42 = 87 | CES67 = 69 | CES92 = 60 |
| CES18 = 57 | CES43 = 74 | CES68 = 74 | CES93 = 74 |
| CES19 = 74 | CES44 = 99 | CES69 = 85 | CES94 = 49 |
| CES20 = 69 | CES45 = 81 | CES70 = 70 | CES95 = 71 |
| CES21 = 89 | CES46 = 76 | CES71 = 72 | CES96 = 77 |
| CES22 = 81 | CES47 = 77 | CES72 = 89 | CES97 = 79 |
| CES23 = 92 | CES48 = 66 | CES73 = 64 | CES98 = 75 |
| CES24 = 92 | CES49 = 75 | CES74 = 87 | CES99 = 67 |
| CES25 = 74 | CES50 = 84 | CES75 = 75 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)