

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P721885

Luminaire Tested: **CST-CA8-400-760-U-T5N**

Issue Date: 10/25/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P721885  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-13)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/25/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: CST-CA8-400-760-U-T5N  
Description: CELESTEON HIGH MAST LUMINAIRE  
Light Source: (8) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 64523 lumens  
Efficiency: N/A  
Efficacy: 161.0 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G4

Input Watts (W): 400.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P721885

CATALOG NUMBER: CST-CA8-400-760-U-T5N

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd


--- 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 7.1 fc  
 Type V - Short - N/A

REPORT NUMBER: P721885  
CATALOG NUMBER: CST-CA8-400-760-U-T5N

## Luminous Intensity Polar Plot



REPORT NUMBER: P721885

CATALOG NUMBER: CST-CA8-400-760-U-T5N


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 32261.5  | 0.0    | 32261.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 32261.5  | 0.0    | 32261.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 64523.0  | 0.0    | 64523.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 453.4   | 0.7       |
| 10°-20°   | 1478.1  | 2.3       |
| 20°-30°   | 3139.4  | 4.9       |
| 30°-40°   | 6656.5  | 10.3      |
| 40°-50°   | 12658.9 | 19.6      |
| 50°-60°   | 20082.6 | 31.1      |
| 60°-70°   | 16975.1 | 26.3      |
| 70°-80°   | 2792.7  | 4.3       |
| 80°-90°   | 286.4   | 0.4       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 64523.0 | 100.0     |
| 0°-180°   | 64523.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P721885


CATALOG NUMBER: CST-CA8-400-760-U-T5N

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 2535.4  | 3.9       |                         |      |          |
| FM   | (30°-60°)   | 19699.0 | 30.5      |                         |      |          |
| FH   | (60°-80°)   | 9883.9  | 15.3      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 143.2   | 0.2       |                         |      | G2/225   |
| BL   | (0°-30°)    | 2535.4  | 3.9       | B4/5000                 |      |          |
| BM   | (30°-60°)   | 19699.0 | 30.5      | B5                      |      |          |
| BH   | (60°-80°)   | 9883.9  | 15.3      | B5                      |      | G4/12000 |
| BVH  | (80°-90°)   | 143.2   | 0.2       |                         |      | G2/225   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B5-U0-G4**

Type V Short



REPORT NUMBER: P721885

CATALOG NUMBER: CST-CA8-400-760-U-T5N

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 85°     | 90°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 4632.5  | 4632.5  | 4632.5  | 4632.5  | 4632.5  | 4632.5  | 4632.5  | 4632.5  | 4632.5  | 4632.5  | 4632.5  |
| 2.5°  | 4666.0  | 4654.4  | 4650.8  | 4645.9  | 4648.3  | 4649.5  | 4656.2  | 4656.8  | 4656.8  | 4662.9  | 4673.3  |
| 5°    | 4718.3  | 4703.1  | 4697.6  | 4691.5  | 4694.5  | 4697.6  | 4703.7  | 4707.3  | 4706.7  | 4710.4  | 4719.5  |
| 7.5°  | 4774.8  | 4769.3  | 4762.7  | 4759.0  | 4759.0  | 4767.5  | 4763.3  | 4770.0  | 4769.3  | 4773.6  | 4779.1  |
| 10°   | 4858.7  | 4846.6  | 4846.0  | 4839.3  | 4842.3  | 4849.6  | 4850.8  | 4849.6  | 4850.8  | 4853.3  | 4866.0  |
| 12.5° | 4965.2  | 4962.1  | 4963.9  | 4958.5  | 4956.6  | 4964.5  | 4966.4  | 4974.3  | 4976.7  | 4984.0  | 4991.9  |
| 15°   | 5136.6  | 5117.2  | 5114.7  | 5114.1  | 5117.8  | 5130.0  | 5133.6  | 5148.2  | 5154.9  | 5165.2  | 5182.9  |
| 17.5° | 5330.6  | 5337.3  | 5325.2  | 5323.9  | 5323.3  | 5333.1  | 5342.8  | 5375.0  | 5385.4  | 5409.1  | 5424.3  |
| 20°   | 5640.1  | 5628.0  | 5620.7  | 5591.5  | 5584.2  | 5601.2  | 5636.5  | 5679.1  | 5699.1  | 5736.8  | 5765.4  |
| 22.5° | 6053.7  | 6033.0  | 5983.1  | 5948.5  | 5933.9  | 5963.1  | 6001.4  | 6069.5  | 6150.3  | 6197.2  | 6209.9  |
| 25°   | 6651.4  | 6569.9  | 6507.9  | 6446.5  | 6424.6  | 6467.8  | 6529.8  | 6638.0  | 6739.6  | 6833.2  | 6876.4  |
| 27.5° | 7379.3  | 7327.6  | 7204.2  | 7107.5  | 7069.2  | 7105.7  | 7234.6  | 7387.2  | 7573.3  | 7670.6  | 7685.2  |
| 30°   | 8303.6  | 8276.9  | 8119.4  | 7938.2  | 7870.1  | 7933.3  | 8085.3  | 8293.3  | 8552.3  | 8752.4  | 8787.7  |
| 32.5° | 9448.1  | 9312.5  | 9093.6  | 8886.2  | 8813.2  | 8890.5  | 9043.1  | 9341.7  | 9690.7  | 9912.1  | 9987.5  |
| 35°   | 10760.4 | 10607.1 | 10278.1 | 9959.5  | 9865.2  | 9875.0  | 10119.4 | 10540.2 | 11017.6 | 11326.5 | 11411.0 |
| 37.5° | 12207.7 | 12051.4 | 11663.4 | 11169.0 | 10950.7 | 10967.1 | 11287.0 | 11834.3 | 12488.6 | 12825.5 | 12937.4 |
| 40°   | 13752.2 | 13590.5 | 13190.3 | 12633.3 | 12274.5 | 12201.6 | 12629.1 | 13295.5 | 13960.2 | 14366.4 | 14409.6 |
| 42.5° | 15262.1 | 15070.6 | 14748.9 | 14191.9 | 13864.7 | 13668.9 | 14185.2 | 14789.0 | 15459.2 | 15825.3 | 15853.8 |
| 45°   | 16610.9 | 16573.8 | 16315.4 | 15911.6 | 15642.2 | 15468.9 | 15837.4 | 16437.0 | 16905.2 | 17136.9 | 17221.5 |
| 47.5° | 17914.7 | 17891.6 | 17808.9 | 17667.8 | 17734.7 | 17446.5 | 17623.4 | 17895.2 | 18152.5 | 18322.7 | 18388.4 |
| 50°   | 19057.3 | 19081.6 | 19244.0 | 19484.2 | 19968.3 | 19676.4 | 19621.0 | 19328.5 | 19335.8 | 19349.2 | 19417.3 |
| 52.5° | 20001.1 | 20130.0 | 20538.7 | 21263.5 | 22308.8 | 22302.1 | 21464.8 | 20692.5 | 20343.5 | 20188.4 | 20202.4 |
| 55°   | 20823.9 | 21044.6 | 21719.6 | 23216.1 | 24712.1 | 24786.9 | 23647.9 | 21937.3 | 21283.0 | 20952.2 | 20995.3 |
| 57.5° | 21278.1 | 21614.4 | 22757.0 | 25028.9 | 27160.9 | 27250.9 | 25982.4 | 23315.9 | 21817.5 | 20980.1 | 21016.0 |
| 60°   | 19718.9 | 20285.1 | 22391.5 | 26198.3 | 29033.8 | 29075.2 | 27409.6 | 23424.1 | 20164.7 | 18682.7 | 18465.6 |
| 62.5° | 16136.6 | 16921.1 | 19892.8 | 25292.2 | 28166.1 | 28037.8 | 26516.3 | 21396.1 | 16564.7 | 14767.2 | 14584.7 |
| 65°   | 12121.3 | 12858.9 | 15970.6 | 21656.3 | 24713.9 | 24544.8 | 22995.4 | 16910.1 | 12144.4 | 10236.2 | 10011.8 |
| 67.5° | 6560.2  | 7674.2  | 10585.8 | 16542.8 | 19701.3 | 20274.7 | 18128.1 | 11786.2 | 7067.4  | 5123.9  | 4926.8  |
| 70°   | 2265.8  | 2928.0  | 5397.5  | 10384.6 | 14210.1 | 14785.4 | 12362.1 | 6321.2  | 3092.8  | 1933.8  | 1736.1  |
| 72.5° | 804.5   | 927.4   | 2029.2  | 5015.0  | 8090.2  | 8964.0  | 6670.3  | 2542.5  | 985.7   | 718.2   | 703.6   |
| 75°   | 568.0   | 586.2   | 721.2   | 1635.2  | 3502.7  | 4290.2  | 2630.0  | 844.0   | 614.8   | 574.7   | 571.0   |
| 77.5° | 507.2   | 517.5   | 584.4   | 665.9   | 1070.3  | 1370.1  | 809.4   | 612.4   | 533.9   | 511.4   | 503.5   |
| 80°   | 482.2   | 490.1   | 509.6   | 546.1   | 606.9   | 631.2   | 546.1   | 523.6   | 485.9   | 476.1   | 473.1   |
| 82.5° | 421.4   | 419.6   | 425.1   | 440.3   | 467.6   | 473.7   | 438.4   | 410.5   | 411.1   | 399.5   | 394.1   |
| 85°   | 285.2   | 302.2   | 289.5   | 273.6   | 339.3   | 341.1   | 318.0   | 238.4   | 270.6   | 265.1   | 242.6   |
| 87.5° | 86.4    | 97.3    | 77.2    | 53.5    | 73.6    | 57.2    | 51.7    | 53.5    | 51.1    | 44.4    | 40.1    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2104-215-3

Luminaire Tested: CST-CA6-230-757-U-T4

Test Date: 04/21/2021




### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2104-215-3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/21/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **CST-CA6-230-757-U-T4**  
 Description: STREETWORKS HIGH MAST LUMINAIRE

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 5385   | CRI (Ra): | 74.4 |      |       |
| CIE u':                   | 0.2065 | R1:       | 71.8 | R9:  | -25.2 |
| CIE v':                   | 0.4808 | R2:       | 79.4 | R10: | 50.6  |
| Duv:                      | 0.0018 | R3:       | 84.2 | R11: | 72.0  |
| CIE x:                    | 0.3351 | R4:       | 74.7 | R12: | 46.0  |
| CIE y:                    | 0.3467 | R5:       | 72.8 | R13: | 73.1  |
| CIE z:                    | 0.3182 | R6:       | 71.2 | R14: | 91.2  |
| Peak Wavelength (nm):     | 450    | R7:       | 82.2 |      |       |
| Dominant Wavelength (nm): | 560    | R8:       | 58.6 |      |       |
| Purity:                   | 4.7    |           |      |      |       |
| Rf:                       | 75.3   |           |      |      |       |
| Rg:                       | 94.2   |           |      |      |       |



### Test Conditions


Stabilization Time: 66M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.7/32%  
 Sphere Temperature (°C): 24.8

REPORT NUMBER: SP1-2104-215-3


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2104-215-3

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5700K 7-step quadrangle

REPORT NUMBER: SP1-2104-215-3

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 16696            | 0.0              | 490       | 164243           | 23.3             | 620       | 415797           | 108.2            | 750       | 22190            | 0.0              | 880       | 22866            | 0.0              |
| 365       | 13447            | 0.0              | 495       | 207773           | 37.7             | 625       | 382869           | 84.5             | 755       | 18942            | 0.0              | 885       | 21901            | 0.0              |
| 370       | 14521            | 0.0              | 500       | 267487           | 59.0             | 630       | 344785           | 62.4             | 760       | 18760            | 0.0              | 890       | 20912            | 0.0              |
| 375       | 15598            | 0.0              | 505       | 333279           | 93.2             | 635       | 309549           | 46.5             | 765       | 19375            | 0.0              | 895       | 19858            | 0.0              |
| 380       | 16553            | 0.0              | 510       | 393084           | 135.0            | 640       | 280226           | 33.5             | 770       | 16788            | 0.0              | 900       | 21828            | 0.0              |
| 385       | 15196            | 0.0              | 515       | 446481           | 185.0            | 645       | 249624           | 24.0             | 775       | 17302            | 0.0              | 905       | 17086            | 0.0              |
| 390       | 13481            | 0.0              | 520       | 488198           | 236.7            | 650       | 224464           | 16.4             | 780       | 15672            | 0.0              | 910       | 17542            | 0.0              |
| 395       | 11977            | 0.0              | 525       | 518433           | 278.3            | 655       | 199646           | 11.5             | 785       | 14771            | 0.0              | 915       | 16185            | 0.0              |
| 400       | 11331            | 0.0              | 530       | 543281           | 319.9            | 660       | 175926           | 7.3              | 790       | 13984            | 0.0              | 920       | 17995            | 0.0              |
| 405       | 11814            | 0.0              | 535       | 561190           | 348.0            | 665       | 155139           | 4.9              | 795       | 14040            | 0.0              | 925       | 15557            | 0.0              |
| 410       | 16208            | 0.0              | 540       | 572451           | 373.0            | 670       | 134630           | 2.9              | 800       | 13342            | 0.0              | 930       | 26095            | 0.0              |
| 415       | 26808            | 0.0              | 545       | 585457           | 389.7            | 675       | 117218           | 2.0              | 805       | 14668            | 0.0              | 935       | 19199            | 0.0              |
| 420       | 50871            | 0.1              | 550       | 599090           | 407.1            | 680       | 102027           | 1.2              | 810       | 14789            | 0.0              | 940       | 23080            | 0.0              |
| 425       | 101020           | 0.5              | 555       | 616995           | 421.4            | 685       | 89213            | 0.8              | 815       | 17650            | 0.0              | 945       | 26343            | 0.0              |
| 430       | 192411           | 1.5              | 560       | 629425           | 427.7            | 690       | 78917            | 0.4              | 820       | 14937            | 0.0              | 950       | 29934            | 0.0              |
| 435       | 336902           | 4.0              | 565       | 636833           | 423.4            | 695       | 68780            | 0.3              | 825       | 16011            | 0.0              | 955       | 22346            | 0.0              |
| 440       | 581105           | 9.1              | 570       | 639836           | 416.0            | 700       | 60229            | 0.2              | 830       | 16981            | 0.0              | 960       | 16017            | 0.0              |
| 445       | 974221           | 20.3             | 575       | 636704           | 396.2            | 705       | 53321            | 0.1              | 835       | 15554            | 0.0              | 965       | 18299            | 0.0              |
| 450       | 1195987          | 31.0             | 580       | 633339           | 376.3            | 710       | 47871            | 0.1              | 840       | 16030            | 0.0              | 970       | 16401            | 0.0              |
| 455       | 889289           | 29.8             | 585       | 623206           | 346.3            | 715       | 44671            | 0.0              | 845       | 19004            | 0.0              | 975       | 23481            | 0.0              |
| 460       | 566512           | 23.2             | 590       | 607134           | 313.9            | 720       | 40236            | 0.0              | 850       | 18632            | 0.0              | 980       | 26457            | 0.0              |
| 465       | 410582           | 21.2             | 595       | 578226           | 274.1            | 725       | 35616            | 0.0              | 855       | 21549            | 0.0              | 985       | 32065            | 0.0              |
| 470       | 276356           | 17.2             | 600       | 554348           | 238.9            | 730       | 31102            | 0.0              | 860       | 21257            | 0.0              | 990       | 31414            | 0.0              |
| 475       | 187504           | 14.7             | 605       | 526616           | 203.9            | 735       | 28341            | 0.0              | 865       | 20272            | 0.0              | 995       | 30650            | 0.0              |
| 480       | 156769           | 14.9             | 610       | 490933           | 168.7            | 740       | 25553            | 0.0              | 870       | 20808            | 0.0              | 1000      | 26490            | 0.0              |
| 485       | 151040           | 17.9             | 615       | 453646           | 136.9            | 745       | 23976            | 0.0              | 875       | 22729            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-3


### Scotopic Flux vs. Wavelength


**Scotopic Lumens: 72376.6**
**S/P: 1.89**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 16696            | 0.0              | 490       | 164243           | 252.9            | 620       | 415797           | 5.2              | 750       | 22190            | 0.0              | 880       | 22866            | 0.0              |
| 365       | 13447            | 0.0              | 495       | 207773           | 335.9            | 625       | 382869           | 3.2              | 755       | 18942            | 0.0              | 885       | 21901            | 0.0              |
| 370       | 14521            | 0.0              | 500       | 267487           | 447.4            | 630       | 344785           | 2.0              | 760       | 18760            | 0.0              | 890       | 20912            | 0.0              |
| 375       | 15598            | 0.0              | 505       | 333279           | 566.6            | 635       | 309549           | 1.2              | 765       | 19375            | 0.0              | 895       | 19858            | 0.0              |
| 380       | 16553            | 0.0              | 510       | 393084           | 666.2            | 640       | 280226           | 0.7              | 770       | 16788            | 0.0              | 900       | 21828            | 0.0              |
| 385       | 15196            | 0.0              | 515       | 446481           | 740.0            | 645       | 249624           | 0.4              | 775       | 17302            | 0.0              | 905       | 17086            | 0.0              |
| 390       | 13481            | 0.1              | 520       | 488198           | 776.0            | 650       | 224464           | 0.3              | 780       | 15672            | 0.0              | 910       | 17542            | 0.0              |
| 395       | 11977            | 0.1              | 525       | 518433           | 775.6            | 655       | 199646           | 0.2              | 785       | 14771            | 0.0              | 915       | 16185            | 0.0              |
| 400       | 11331            | 0.2              | 530       | 543281           | 749.0            | 660       | 175926           | 0.1              | 790       | 13984            | 0.0              | 920       | 17995            | 0.0              |
| 405       | 11814            | 0.4              | 535       | 561190           | 699.3            | 665       | 155139           | 0.1              | 795       | 14040            | 0.0              | 925       | 15557            | 0.0              |
| 410       | 16208            | 1.0              | 540       | 572451           | 632.6            | 670       | 134630           | 0.0              | 800       | 13342            | 0.0              | 930       | 26095            | 0.0              |
| 415       | 26808            | 2.8              | 545       | 585457           | 561.3            | 675       | 117218           | 0.0              | 805       | 14668            | 0.0              | 935       | 19199            | 0.0              |
| 420       | 50871            | 8.4              | 550       | 599090           | 489.9            | 680       | 102027           | 0.0              | 810       | 14789            | 0.0              | 940       | 23080            | 0.0              |
| 425       | 101020           | 24.7             | 555       | 616995           | 421.7            | 685       | 89213            | 0.0              | 815       | 17650            | 0.0              | 945       | 26343            | 0.0              |
| 430       | 192411           | 65.5             | 560       | 629425           | 351.8            | 690       | 78917            | 0.0              | 820       | 14937            | 0.0              | 950       | 29934            | 0.0              |
| 435       | 336902           | 150.6            | 565       | 636833           | 285.7            | 695       | 68780            | 0.0              | 825       | 16011            | 0.0              | 955       | 22346            | 0.0              |
| 440       | 581105           | 324.8            | 570       | 639836           | 225.8            | 700       | 60229            | 0.0              | 830       | 16981            | 0.0              | 960       | 16017            | 0.0              |
| 445       | 974221           | 652.3            | 575       | 636704           | 173.4            | 705       | 53321            | 0.0              | 835       | 15554            | 0.0              | 965       | 18299            | 0.0              |
| 450       | 1195987          | 927.0            | 580       | 633339           | 130.5            | 710       | 47871            | 0.0              | 840       | 16030            | 0.0              | 970       | 16401            | 0.0              |
| 455       | 889289           | 777.1            | 585       | 623206           | 95.2             | 715       | 44671            | 0.0              | 845       | 19004            | 0.0              | 975       | 23481            | 0.0              |
| 460       | 566512           | 547.2            | 590       | 607134           | 67.6             | 720       | 40236            | 0.0              | 850       | 18632            | 0.0              | 980       | 26457            | 0.0              |
| 465       | 410582           | 433.6            | 595       | 578226           | 46.1             | 725       | 35616            | 0.0              | 855       | 21549            | 0.0              | 985       | 32065            | 0.0              |
| 470       | 276356           | 318.2            | 600       | 554348           | 31.2             | 730       | 31102            | 0.0              | 860       | 21257            | 0.0              | 990       | 31414            | 0.0              |
| 475       | 187504           | 234.4            | 605       | 526616           | 20.7             | 735       | 28341            | 0.0              | 865       | 20272            | 0.0              | 995       | 30650            | 0.0              |
| 480       | 156769           | 211.8            | 610       | 490933           | 13.3             | 740       | 25553            | 0.0              | 870       | 20808            | 0.0              | 1000      | 26490            | 0.0              |
| 485       | 151040           | 218.9            | 615       | 453646           | 8.4              | 745       | 23976            | 0.0              | 875       | 22729            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-3

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 29860.2**      **M/P: 0.78**


| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 16696            | 0.0              | 490       | 164243           | 136.7            | 620       | 415797           | 0.3              | 750       | 22190            | 0.0              | 880       | 22866            | 0.0              |
| 365       | 13447            | 0.0              | 495       | 207773           | 171.5            | 625       | 382869           | 0.2              | 755       | 18942            | 0.0              | 885       | 21901            | 0.0              |
| 370       | 14521            | 0.0              | 500       | 267487           | 215.0            | 630       | 344785           | 0.1              | 760       | 18760            | 0.0              | 890       | 20912            | 0.0              |
| 375       | 15598            | 0.0              | 505       | 333279           | 255.8            | 635       | 309549           | 0.1              | 765       | 19375            | 0.0              | 895       | 19858            | 0.0              |
| 380       | 16553            | 0.0              | 510       | 393084           | 282.2            | 640       | 280226           | 0.0              | 770       | 16788            | 0.0              | 900       | 21828            | 0.0              |
| 385       | 15196            | 0.0              | 515       | 446481           | 291.7            | 645       | 249624           | 0.0              | 775       | 17302            | 0.0              | 905       | 17086            | 0.0              |
| 390       | 13481            | 0.0              | 520       | 488198           | 284.2            | 650       | 224464           | 0.0              | 780       | 15672            | 0.0              | 910       | 17542            | 0.0              |
| 395       | 11977            | 0.1              | 525       | 518433           | 262.9            | 655       | 199646           | 0.0              | 785       | 14771            | 0.0              | 915       | 16185            | 0.0              |
| 400       | 11331            | 0.1              | 530       | 543281           | 234.8            | 660       | 175926           | 0.0              | 790       | 13984            | 0.0              | 920       | 17995            | 0.0              |
| 405       | 11814            | 0.2              | 535       | 561190           | 202.0            | 665       | 155139           | 0.0              | 795       | 14040            | 0.0              | 925       | 15557            | 0.0              |
| 410       | 16208            | 0.6              | 540       | 572451           | 167.5            | 670       | 134630           | 0.0              | 800       | 13342            | 0.0              | 930       | 26095            | 0.0              |
| 415       | 26808            | 1.8              | 545       | 585457           | 136.0            | 675       | 117218           | 0.0              | 805       | 14668            | 0.0              | 935       | 19199            | 0.0              |
| 420       | 50871            | 5.8              | 550       | 599090           | 107.5            | 680       | 102027           | 0.0              | 810       | 14789            | 0.0              | 940       | 23080            | 0.0              |
| 425       | 101020           | 15.7             | 555       | 616995           | 83.2             | 685       | 89213            | 0.0              | 815       | 17650            | 0.0              | 945       | 26343            | 0.0              |
| 430       | 192411           | 40.6             | 560       | 629425           | 62.1             | 690       | 78917            | 0.0              | 820       | 14937            | 0.0              | 950       | 29934            | 0.0              |
| 435       | 336902           | 89.9             | 565       | 636833           | 44.7             | 695       | 68780            | 0.0              | 825       | 16011            | 0.0              | 955       | 22346            | 0.0              |
| 440       | 581105           | 194.2            | 570       | 639836           | 31.3             | 700       | 60229            | 0.0              | 830       | 16981            | 0.0              | 960       | 16017            | 0.0              |
| 445       | 974221           | 384.3            | 575       | 636704           | 21.2             | 705       | 53321            | 0.0              | 835       | 15554            | 0.0              | 965       | 18299            | 0.0              |
| 450       | 1195987          | 551.1            | 580       | 633339           | 14.2             | 710       | 47871            | 0.0              | 840       | 16030            | 0.0              | 970       | 16401            | 0.0              |
| 455       | 889289           | 465.9            | 585       | 623206           | 9.3              | 715       | 44671            | 0.0              | 845       | 19004            | 0.0              | 975       | 23481            | 0.0              |
| 460       | 566512           | 333.8            | 590       | 607134           | 6.0              | 720       | 40236            | 0.0              | 850       | 18632            | 0.0              | 980       | 26457            | 0.0              |
| 465       | 410582           | 268.3            | 595       | 578226           | 3.7              | 725       | 35616            | 0.0              | 855       | 21549            | 0.0              | 985       | 32065            | 0.0              |
| 470       | 276356           | 197.8            | 600       | 554348           | 2.3              | 730       | 31102            | 0.0              | 860       | 21257            | 0.0              | 990       | 31414            | 0.0              |
| 475       | 187504           | 143.2            | 605       | 526616           | 1.5              | 735       | 28341            | 0.0              | 865       | 20272            | 0.0              | 995       | 30650            | 0.0              |
| 480       | 156769           | 126.0            | 610       | 490933           | 0.9              | 740       | 25553            | 0.0              | 870       | 20808            | 0.0              | 1000      | 26490            | 0.0              |
| 485       | 151040           | 124.5            | 615       | 453646           | 0.5              | 745       | 23976            | 0.0              | 875       | 22729            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-3





TM-30-18

### Summary

$R_f = 75.3$   
 $R_g = 94.2$   
 CIE  $R_a = 74.4$   
 $R_g = -25.2$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 64 | CES51 = 91 | CES76 = 51 |
| CES02 = 59 | CES27 = 89 | CES52 = 91 | CES77 = 67 |
| CES03 = 30 | CES28 = 81 | CES53 = 81 | CES78 = 53 |
| CES04 = 69 | CES29 = 69 | CES54 = 86 | CES79 = 80 |
| CES05 = 46 | CES30 = 87 | CES55 = 84 | CES80 = 76 |
| CES06 = 50 | CES31 = 72 | CES56 = 76 | CES81 = 79 |
| CES07 = 38 | CES32 = 63 | CES57 = 76 | CES82 = 90 |
| CES08 = 38 | CES33 = 81 | CES58 = 76 | CES83 = 89 |
| CES09 = 29 | CES34 = 70 | CES59 = 87 | CES84 = 85 |
| CES10 = 72 | CES35 = 83 | CES60 = 89 | CES85 = 78 |
| CES11 = 55 | CES36 = 88 | CES61 = 83 | CES86 = 78 |
| CES12 = 61 | CES37 = 78 | CES62 = 83 | CES87 = 77 |
| CES13 = 41 | CES38 = 97 | CES63 = 76 | CES88 = 82 |
| CES14 = 74 | CES39 = 96 | CES64 = 67 | CES89 = 75 |
| CES15 = 70 | CES40 = 91 | CES65 = 64 | CES90 = 82 |
| CES16 = 46 | CES41 = 96 | CES66 = 60 | CES91 = 72 |
| CES17 = 48 | CES42 = 79 | CES67 = 57 | CES92 = 62 |
| CES18 = 55 | CES43 = 78 | CES68 = 65 | CES93 = 77 |
| CES19 = 71 | CES44 = 99 | CES69 = 73 | CES94 = 57 |
| CES20 = 64 | CES45 = 87 | CES70 = 57 | CES95 = 66 |
| CES21 = 85 | CES46 = 86 | CES71 = 49 | CES96 = 78 |
| CES22 = 77 | CES47 = 89 | CES72 = 83 | CES97 = 87 |
| CES23 = 91 | CES48 = 82 | CES73 = 47 | CES98 = 78 |
| CES24 = 90 | CES49 = 84 | CES74 = 90 | CES99 = 65 |
| CES25 = 71 | CES50 = 91 | CES75 = 51 |            |







Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)