

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1066475

Luminaire Tested: **NVN-SA6C-722-U-RBC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1066475  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: NVN-SA6C-722-U-RBC  
Description: Navion AREA AND ROADWAY LUMINAIRE 1050mA 6xLight Square PACKAGE  
70CRI 2200K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (84) 2200K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 21036.1 lumens  
Efficiency: N/A  
Efficacy: 75.4 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G4

Input Watts (W): 279.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 4.2 fc  
 Type III - Short - N/A

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 125.1    | 0.0    | 125.1   |
|                    | % Fixture | 0.6      | 0.0    | 0.6     |
| <b>Street Side</b> | Lumens    | 20910.9  | 0.0    | 20910.9 |
|                    | % Fixture | 99.4     | 0.0    | 99.4    |
| <b>Total</b>       | Lumens    | 21036.1  | 0.0    | 21036.1 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 6.2     | 0.0       |
| 10°-20°   | 30.9    | 0.1       |
| 20°-30°   | 392.6   | 1.9       |
| 30°-40°   | 1323.2  | 6.3       |
| 40°-50°   | 3996.2  | 19.0      |
| 50°-60°   | 7050.6  | 33.5      |
| 60°-70°   | 6211.5  | 29.5      |
| 70°-80°   | 1977.3  | 9.4       |
| 80°-90°   | 47.6    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 21036.1 | 100.0     |
| 0°-180°   | 21036.1 | 100.0     |



REPORT NUMBER: P1066475


CATALOG NUMBER: NVN-SA6C-722-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 410.9   | 2.0       |                         |      |          |
| FM   | (30°-60°)   | 12321.5 | 58.6      |                         |      |          |
| FH   | (60°-80°)   | 8139.8  | 38.7      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 38.7    | 0.2       |                         |      | G1/100   |
| BL   | (0°-30°)    | 18.8    | 0.1       | B0/110                  |      |          |
| BM   | (30°-60°)   | 48.5    | 0.2       | B0/220                  |      |          |
| BH   | (60°-80°)   | 49.0    | 0.2       | B0/110                  |      | G0/110   |
| BVH  | (80°-90°)   | 8.9     | 0.0       |                         |      | G0/10    |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B0-U0-G4**

Type III Short



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°    | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° | 25°   |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 59.4   | 59.4   | 59.4  | 59.4  | 59.4  | 59.4  | 59.4  | 59.4  | 59.4  | 59.4  | 59.4  |
| 2.5°   | 52.8   | 52.8   | 52.8  | 52.8  | 52.8  | 52.8  | 52.8  | 52.8  | 52.8  | 52.8  | 46.2  |
| 5°     | 66.0   | 66.0   | 66.0  | 59.4  | 59.4  | 59.4  | 52.8  | 52.8  | 52.8  | 52.8  | 52.8  |
| 7.5°   | 79.2   | 72.6   | 72.6  | 66.0  | 66.0  | 66.0  | 59.4  | 59.4  | 59.4  | 59.4  | 52.8  |
| 10°    | 92.4   | 85.8   | 85.8  | 79.2  | 79.2  | 72.6  | 72.6  | 66.0  | 66.0  | 59.4  | 59.4  |
| 12.5°  | 105.6  | 99.0   | 92.4  | 85.8  | 85.8  | 79.2  | 79.2  | 72.6  | 72.6  | 66.0  | 66.0  |
| 15°    | 118.7  | 112.1  | 105.6 | 99.0  | 92.4  | 92.4  | 85.8  | 79.2  | 72.6  | 72.6  | 66.0  |
| 17.5°  | 138.5  | 125.3  | 118.7 | 105.6 | 99.0  | 92.4  | 85.8  | 79.2  | 79.2  | 72.6  | 72.6  |
| 20°    | 145.1  | 131.9  | 125.3 | 112.1 | 105.6 | 99.0  | 92.4  | 85.8  | 79.2  | 79.2  | 72.6  |
| 22.5°  | 171.5  | 145.1  | 138.5 | 125.3 | 118.7 | 112.1 | 99.0  | 92.4  | 85.8  | 79.2  | 72.6  |
| 25°    | 211.1  | 171.5  | 151.7 | 131.9 | 125.3 | 112.1 | 105.6 | 92.4  | 85.8  | 79.2  | 72.6  |
| 27.5°  | 257.3  | 191.3  | 171.5 | 145.1 | 131.9 | 118.7 | 105.6 | 92.4  | 85.8  | 79.2  | 72.6  |
| 30°    | 316.7  | 224.3  | 191.3 | 158.3 | 145.1 | 131.9 | 112.1 | 99.0  | 92.4  | 85.8  | 72.6  |
| 32.5°  | 442.0  | 277.1  | 224.3 | 171.5 | 151.7 | 138.5 | 118.7 | 99.0  | 92.4  | 85.8  | 72.6  |
| 35°    | 534.3  | 336.4  | 270.5 | 197.9 | 171.5 | 151.7 | 125.3 | 99.0  | 92.4  | 85.8  | 72.6  |
| 37.5°  | 620.1  | 343.0  | 277.1 | 211.1 | 184.7 | 158.3 | 125.3 | 99.0  | 92.4  | 85.8  | 72.6  |
| 40°    | 758.6  | 356.2  | 277.1 | 197.9 | 178.1 | 151.7 | 131.9 | 105.6 | 99.0  | 85.8  | 79.2  |
| 42.5°  | 1022.5 | 409.0  | 296.9 | 184.7 | 164.9 | 151.7 | 131.9 | 112.1 | 99.0  | 92.4  | 79.2  |
| 45°    | 1702.0 | 606.9  | 402.4 | 191.3 | 171.5 | 151.7 | 131.9 | 112.1 | 105.6 | 92.4  | 85.8  |
| 47.5°  | 2896.0 | 1055.5 | 626.7 | 197.9 | 178.1 | 151.7 | 131.9 | 105.6 | 99.0  | 92.4  | 79.2  |
| 50°    | 3707.5 | 1352.4 | 791.6 | 230.9 | 197.9 | 171.5 | 138.5 | 105.6 | 99.0  | 92.4  | 85.8  |
| 52.5°  | 3938.3 | 1438.1 | 857.6 | 270.5 | 230.9 | 191.3 | 145.1 | 105.6 | 99.0  | 99.0  | 92.4  |
| 55°    | 3608.5 | 1398.5 | 857.6 | 316.7 | 263.9 | 217.7 | 164.9 | 112.1 | 105.6 | 105.6 | 99.0  |
| 57.5°  | 3067.6 | 1293.0 | 818.0 | 343.0 | 290.3 | 230.9 | 178.1 | 118.7 | 112.1 | 112.1 | 105.6 |
| 60°    | 2526.6 | 1088.5 | 738.9 | 382.6 | 323.2 | 263.9 | 204.5 | 145.1 | 138.5 | 131.9 | 118.7 |
| 62.5°  | 2005.5 | 877.4  | 646.5 | 409.0 | 349.6 | 283.7 | 224.3 | 158.3 | 151.7 | 145.1 | 138.5 |
| 65°    | 1510.7 | 765.2  | 600.3 | 428.8 | 362.8 | 296.9 | 230.9 | 164.9 | 158.3 | 158.3 | 151.7 |
| 67.5°  | 1161.1 | 699.3  | 573.9 | 442.0 | 376.0 | 310.1 | 244.1 | 178.1 | 171.5 | 164.9 | 158.3 |
| 70°    | 917.0  | 646.5  | 540.9 | 435.4 | 376.0 | 316.7 | 250.7 | 191.3 | 178.1 | 171.5 | 158.3 |
| 72.5°  | 765.2  | 587.1  | 501.4 | 415.6 | 369.4 | 323.2 | 277.1 | 230.9 | 204.5 | 184.7 | 158.3 |
| 75°    | 639.9  | 527.8  | 455.2 | 376.0 | 343.0 | 316.7 | 283.7 | 250.7 | 217.7 | 184.7 | 151.7 |
| 77.5°  | 422.2  | 382.6  | 349.6 | 316.7 | 296.9 | 277.1 | 250.7 | 230.9 | 197.9 | 171.5 | 138.5 |
| 80°    | 178.1  | 164.9  | 171.5 | 171.5 | 171.5 | 171.5 | 164.9 | 164.9 | 145.1 | 125.3 | 99.0  |
| 82.5°  | 39.6   | 33.0   | 39.6  | 39.6  | 39.6  | 39.6  | 33.0  | 33.0  | 33.0  | 26.4  | 26.4  |
| 85°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30°   | 32.5° | 35°  | 37.5° | 40°  | 42.5° | 45°  | 47.5° | 50°  | 52.5° |
|--------|-------|-------|-------|------|-------|------|-------|------|-------|------|-------|
| 0°     | 59.4  | 59.4  | 59.4  | 59.4 | 59.4  | 59.4 | 59.4  | 59.4 | 59.4  | 59.4 | 59.4  |
| 2.5°   | 46.2  | 46.2  | 46.2  | 46.2 | 46.2  | 46.2 | 46.2  | 46.2 | 46.2  | 46.2 | 46.2  |
| 5°     | 52.8  | 52.8  | 52.8  | 46.2 | 46.2  | 46.2 | 46.2  | 46.2 | 46.2  | 46.2 | 46.2  |
| 7.5°   | 52.8  | 52.8  | 52.8  | 46.2 | 46.2  | 46.2 | 46.2  | 39.6 | 39.6  | 39.6 | 39.6  |
| 10°    | 52.8  | 52.8  | 52.8  | 46.2 | 46.2  | 46.2 | 46.2  | 39.6 | 39.6  | 39.6 | 39.6  |
| 12.5°  | 59.4  | 59.4  | 52.8  | 52.8 | 46.2  | 46.2 | 46.2  | 39.6 | 39.6  | 39.6 | 39.6  |
| 15°    | 59.4  | 59.4  | 52.8  | 52.8 | 46.2  | 46.2 | 46.2  | 39.6 | 39.6  | 39.6 | 39.6  |
| 17.5°  | 66.0  | 59.4  | 59.4  | 52.8 | 46.2  | 46.2 | 46.2  | 39.6 | 39.6  | 39.6 | 39.6  |
| 20°    | 66.0  | 59.4  | 59.4  | 52.8 | 46.2  | 46.2 | 46.2  | 39.6 | 39.6  | 39.6 | 39.6  |
| 22.5°  | 66.0  | 59.4  | 59.4  | 52.8 | 46.2  | 46.2 | 39.6  | 39.6 | 33.0  | 33.0 | 26.4  |
| 25°    | 66.0  | 59.4  | 59.4  | 52.8 | 46.2  | 46.2 | 39.6  | 39.6 | 33.0  | 26.4 | 26.4  |
| 27.5°  | 66.0  | 59.4  | 59.4  | 52.8 | 46.2  | 39.6 | 39.6  | 33.0 | 26.4  | 19.8 | 19.8  |
| 30°    | 66.0  | 59.4  | 59.4  | 52.8 | 46.2  | 39.6 | 33.0  | 26.4 | 19.8  | 19.8 | 13.2  |
| 32.5°  | 66.0  | 59.4  | 52.8  | 46.2 | 39.6  | 33.0 | 33.0  | 26.4 | 19.8  | 13.2 | 13.2  |
| 35°    | 66.0  | 59.4  | 52.8  | 46.2 | 39.6  | 33.0 | 33.0  | 26.4 | 19.8  | 13.2 | 13.2  |
| 37.5°  | 66.0  | 59.4  | 52.8  | 46.2 | 39.6  | 33.0 | 26.4  | 19.8 | 13.2  | 13.2 | 6.6   |
| 40°    | 66.0  | 59.4  | 52.8  | 46.2 | 39.6  | 33.0 | 26.4  | 19.8 | 13.2  | 13.2 | 6.6   |
| 42.5°  | 66.0  | 59.4  | 52.8  | 46.2 | 39.6  | 33.0 | 26.4  | 19.8 | 13.2  | 13.2 | 6.6   |
| 45°    | 72.6  | 66.0  | 59.4  | 46.2 | 39.6  | 33.0 | 33.0  | 26.4 | 19.8  | 13.2 | 13.2  |
| 47.5°  | 72.6  | 66.0  | 59.4  | 46.2 | 39.6  | 33.0 | 33.0  | 26.4 | 19.8  | 13.2 | 13.2  |
| 50°    | 79.2  | 72.6  | 66.0  | 52.8 | 46.2  | 39.6 | 33.0  | 19.8 | 13.2  | 13.2 | 6.6   |
| 52.5°  | 85.8  | 79.2  | 72.6  | 66.0 | 59.4  | 46.2 | 33.0  | 19.8 | 6.6   | 6.6  | 6.6   |
| 55°    | 92.4  | 85.8  | 85.8  | 79.2 | 72.6  | 52.8 | 39.6  | 19.8 | 0.0   | 0.0  | 0.0   |
| 57.5°  | 99.0  | 92.4  | 92.4  | 85.8 | 79.2  | 59.4 | 39.6  | 19.8 | 0.0   | 0.0  | 0.0   |
| 60°    | 112.1 | 105.6 | 99.0  | 85.8 | 79.2  | 59.4 | 39.6  | 19.8 | 0.0   | 0.0  | 0.0   |
| 62.5°  | 131.9 | 118.7 | 99.0  | 85.8 | 66.0  | 52.8 | 33.0  | 19.8 | 0.0   | 0.0  | 0.0   |
| 65°    | 145.1 | 125.3 | 105.6 | 79.2 | 59.4  | 46.2 | 33.0  | 13.2 | 0.0   | 0.0  | 0.0   |
| 67.5°  | 151.7 | 125.3 | 105.6 | 79.2 | 52.8  | 39.6 | 26.4  | 13.2 | 0.0   | 0.0  | 0.0   |
| 70°    | 145.1 | 118.7 | 99.0  | 72.6 | 46.2  | 33.0 | 26.4  | 13.2 | 0.0   | 0.0  | 0.0   |
| 72.5°  | 131.9 | 112.1 | 85.8  | 66.0 | 39.6  | 33.0 | 19.8  | 13.2 | 0.0   | 0.0  | 0.0   |
| 75°    | 118.7 | 99.0  | 72.6  | 52.8 | 26.4  | 19.8 | 13.2  | 6.6  | 0.0   | 0.0  | 0.0   |
| 77.5°  | 105.6 | 85.8  | 59.4  | 39.6 | 13.2  | 13.2 | 6.6   | 6.6  | 0.0   | 0.0  | 0.0   |
| 80°    | 79.2  | 59.4  | 39.6  | 19.8 | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 82.5°  | 19.8  | 13.2  | 13.2  | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 85°    | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 87.5°  | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 55°  | 57.5° | 60°  | 62.5° | 65°  | 67.5° | 70°  | 72.5° | 75°  | 77.5° | 80°  |
|--------|------|-------|------|-------|------|-------|------|-------|------|-------|------|
| 0°     | 59.4 | 59.4  | 59.4 | 59.4  | 59.4 | 59.4  | 59.4 | 59.4  | 59.4 | 59.4  | 59.4 |
| 2.5°   | 39.6 | 39.6  | 39.6 | 39.6  | 39.6 | 39.6  | 39.6 | 39.6  | 39.6 | 39.6  | 39.6 |
| 5°     | 39.6 | 39.6  | 39.6 | 39.6  | 33.0 | 33.0  | 33.0 | 33.0  | 33.0 | 33.0  | 33.0 |
| 7.5°   | 39.6 | 39.6  | 39.6 | 39.6  | 33.0 | 33.0  | 33.0 | 33.0  | 26.4 | 26.4  | 26.4 |
| 10°    | 33.0 | 33.0  | 33.0 | 33.0  | 33.0 | 33.0  | 33.0 | 33.0  | 26.4 | 26.4  | 26.4 |
| 12.5°  | 33.0 | 33.0  | 33.0 | 33.0  | 33.0 | 33.0  | 33.0 | 33.0  | 26.4 | 26.4  | 26.4 |
| 15°    | 33.0 | 33.0  | 33.0 | 33.0  | 33.0 | 33.0  | 33.0 | 26.4  | 26.4 | 19.8  | 19.8 |
| 17.5°  | 33.0 | 33.0  | 33.0 | 33.0  | 26.4 | 26.4  | 26.4 | 19.8  | 19.8 | 13.2  | 13.2 |
| 20°    | 33.0 | 33.0  | 33.0 | 26.4  | 26.4 | 19.8  | 19.8 | 13.2  | 13.2 | 6.6   | 6.6  |
| 22.5°  | 26.4 | 19.8  | 19.8 | 13.2  | 13.2 | 6.6   | 6.6  | 6.6   | 0.0  | 0.0   | 0.0  |
| 25°    | 19.8 | 13.2  | 13.2 | 6.6   | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 27.5°  | 13.2 | 6.6   | 6.6  | 6.6   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 30°    | 13.2 | 6.6   | 6.6  | 6.6   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 32.5°  | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 35°    | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 37.5°  | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 40°    | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 42.5°  | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 45°    | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 47.5°  | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 50°    | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 52.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 55°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 57.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 60°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 62.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 65°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 67.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 70°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 72.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 75°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 77.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 80°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 82.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 85°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 87.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 92.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 95°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 97.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 100°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 102.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 105°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 107.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 110°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85°  | 87.5° | 90°  | 92.5° | 95°  | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|------|-------|------|-------|------|-------|------|--------|------|--------|
| 0°     | 59.4  | 59.4 | 59.4  | 59.4 | 59.4  | 59.4 | 59.4  | 59.4 | 59.4   | 59.4 | 59.4   |
| 2.5°   | 39.6  | 33.0 | 33.0  | 33.0 | 33.0  | 33.0 | 33.0  | 33.0 | 33.0   | 33.0 | 33.0   |
| 5°     | 33.0  | 33.0 | 33.0  | 33.0 | 26.4  | 26.4 | 26.4  | 26.4 | 26.4   | 26.4 | 26.4   |
| 7.5°   | 26.4  | 26.4 | 26.4  | 26.4 | 26.4  | 26.4 | 19.8  | 19.8 | 19.8   | 19.8 | 19.8   |
| 10°    | 26.4  | 19.8 | 19.8  | 19.8 | 19.8  | 19.8 | 19.8  | 19.8 | 19.8   | 13.2 | 13.2   |
| 12.5°  | 26.4  | 19.8 | 19.8  | 19.8 | 13.2  | 13.2 | 13.2  | 13.2 | 13.2   | 6.6  | 6.6    |
| 15°    | 19.8  | 13.2 | 13.2  | 13.2 | 6.6   | 6.6  | 6.6   | 6.6  | 6.6    | 0.0  | 0.0    |
| 17.5°  | 13.2  | 6.6  | 6.6   | 6.6  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 20°    | 6.6   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 22.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 25°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 30°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 35°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 37.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 40°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 42.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 45°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 50°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 55°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 60°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 65°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 67.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 70°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 72.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 75°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 77.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 80°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0°     | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 |
| 2.5°   | 33.0 | 33.0   | 33.0 | 33.0   | 33.0 | 33.0   | 33.0 | 33.0   | 33.0 | 39.6   | 39.6 |
| 5°     | 26.4 | 26.4   | 26.4 | 26.4   | 26.4 | 26.4   | 26.4 | 26.4   | 26.4 | 26.4   | 26.4 |
| 7.5°   | 19.8 | 19.8   | 19.8 | 19.8   | 19.8 | 19.8   | 19.8 | 19.8   | 19.8 | 19.8   | 19.8 |
| 10°    | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  |
| 12.5°  | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  | 6.6    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 15°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 17.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 20°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 22.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 25°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0°     | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   |
| 2.5°   | 39.6   | 39.6 | 39.6   | 39.6 | 39.6   | 46.2 | 46.2   | 52.8 | 52.8   | 59.4 | 59.4   |
| 5°     | 26.4   | 26.4 | 33.0   | 33.0 | 33.0   | 33.0 | 39.6   | 39.6 | 39.6   | 46.2 | 46.2   |
| 7.5°   | 19.8   | 19.8 | 19.8   | 19.8 | 19.8   | 26.4 | 26.4   | 33.0 | 33.0   | 39.6 | 39.6   |
| 10°    | 6.6    | 6.6  | 13.2   | 13.2 | 13.2   | 13.2 | 19.8   | 19.8 | 19.8   | 26.4 | 33.0   |
| 12.5°  | 0.0    | 0.0  | 6.6    | 6.6  | 6.6    | 6.6  | 13.2   | 13.2 | 13.2   | 19.8 | 26.4   |
| 15°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 6.6    | 6.6  | 6.6    | 13.2 | 19.8   |
| 17.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 13.2   |
| 20°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    |
| 22.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 6.6    |
| 25°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 87.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0°     | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 |
| 2.5°   | 66.0 | 66.0   | 72.6 | 72.6   | 79.2 | 79.2   | 85.8 | 85.8   | 85.8 | 85.8   | 85.8 |
| 5°     | 52.8 | 52.8   | 59.4 | 66.0   | 66.0 | 72.6   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 |
| 7.5°   | 46.2 | 46.2   | 52.8 | 59.4   | 59.4 | 66.0   | 72.6 | 72.6   | 79.2 | 79.2   | 79.2 |
| 10°    | 33.0 | 39.6   | 46.2 | 52.8   | 52.8 | 59.4   | 66.0 | 66.0   | 72.6 | 72.6   | 72.6 |
| 12.5°  | 26.4 | 33.0   | 39.6 | 46.2   | 46.2 | 52.8   | 59.4 | 59.4   | 66.0 | 66.0   | 72.6 |
| 15°    | 19.8 | 26.4   | 33.0 | 39.6   | 39.6 | 46.2   | 52.8 | 52.8   | 59.4 | 66.0   | 72.6 |
| 17.5°  | 13.2 | 19.8   | 26.4 | 33.0   | 33.0 | 39.6   | 46.2 | 52.8   | 59.4 | 59.4   | 66.0 |
| 20°    | 13.2 | 13.2   | 19.8 | 26.4   | 26.4 | 33.0   | 39.6 | 46.2   | 52.8 | 52.8   | 59.4 |
| 22.5°  | 6.6  | 6.6    | 13.2 | 19.8   | 19.8 | 26.4   | 33.0 | 39.6   | 46.2 | 46.2   | 52.8 |
| 25°    | 0.0  | 0.0    | 6.6  | 13.2   | 13.2 | 19.8   | 26.4 | 26.4   | 33.0 | 33.0   | 39.6 |
| 27.5°  | 0.0  | 0.0    | 6.6  | 6.6    | 13.2 | 13.2   | 19.8 | 19.8   | 26.4 | 26.4   | 33.0 |
| 30°    | 0.0  | 0.0    | 6.6  | 6.6    | 13.2 | 13.2   | 19.8 | 19.8   | 26.4 | 26.4   | 26.4 |
| 32.5°  | 0.0  | 0.0    | 0.0  | 6.6    | 6.6  | 6.6    | 13.2 | 13.2   | 19.8 | 19.8   | 26.4 |
| 35°    | 0.0  | 0.0    | 0.0  | 6.6    | 6.6  | 6.6    | 13.2 | 13.2   | 19.8 | 19.8   | 19.8 |
| 37.5°  | 0.0  | 0.0    | 0.0  | 6.6    | 6.6  | 6.6    | 13.2 | 13.2   | 13.2 | 13.2   | 19.8 |
| 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 13.2 | 13.2   | 13.2 |
| 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 13.2 | 13.2   | 13.2 |
| 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 13.2 | 13.2   | 13.2 |
| 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 13.2 | 13.2   | 13.2 |
| 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 13.2 | 13.2   | 13.2 |
| 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  |
| 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  |
| 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  |
| 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  |
| 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  |
| 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  |
| 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  |
| 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  |
| 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  |
| 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  |
| 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 13.2 | 13.2   | 13.2 |
| 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 13.2 | 13.2   | 13.2 |
| 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  | 6.6    | 13.2 |
| 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  |
| 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  |
| 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0°     | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   |
| 2.5°   | 92.4   | 92.4 | 92.4   | 92.4 | 92.4   | 92.4 | 92.4   | 92.4 | 92.4   | 85.8 | 85.8   |
| 5°     | 85.8   | 85.8 | 85.8   | 85.8 | 85.8   | 85.8 | 85.8   | 85.8 | 85.8   | 79.2 | 79.2   |
| 7.5°   | 85.8   | 85.8 | 85.8   | 85.8 | 85.8   | 85.8 | 85.8   | 85.8 | 85.8   | 79.2 | 79.2   |
| 10°    | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   |
| 12.5°  | 72.6   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   |
| 15°    | 72.6   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   |
| 17.5°  | 66.0   | 72.6 | 72.6   | 72.6 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   |
| 20°    | 59.4   | 66.0 | 66.0   | 66.0 | 72.6   | 72.6 | 72.6   | 72.6 | 79.2   | 79.2 | 79.2   |
| 22.5°  | 52.8   | 59.4 | 59.4   | 59.4 | 66.0   | 66.0 | 66.0   | 66.0 | 72.6   | 72.6 | 72.6   |
| 25°    | 46.2   | 46.2 | 52.8   | 52.8 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   |
| 27.5°  | 33.0   | 39.6 | 39.6   | 39.6 | 46.2   | 46.2 | 46.2   | 46.2 | 52.8   | 52.8 | 52.8   |
| 30°    | 33.0   | 33.0 | 33.0   | 33.0 | 39.6   | 39.6 | 39.6   | 39.6 | 46.2   | 46.2 | 46.2   |
| 32.5°  | 26.4   | 33.0 | 33.0   | 33.0 | 39.6   | 39.6 | 39.6   | 39.6 | 46.2   | 46.2 | 46.2   |
| 35°    | 26.4   | 26.4 | 26.4   | 26.4 | 33.0   | 33.0 | 33.0   | 33.0 | 39.6   | 39.6 | 39.6   |
| 37.5°  | 19.8   | 26.4 | 26.4   | 26.4 | 33.0   | 33.0 | 33.0   | 33.0 | 39.6   | 39.6 | 39.6   |
| 40°    | 19.8   | 19.8 | 19.8   | 19.8 | 26.4   | 26.4 | 26.4   | 26.4 | 33.0   | 33.0 | 33.0   |
| 42.5°  | 19.8   | 19.8 | 19.8   | 19.8 | 26.4   | 26.4 | 26.4   | 26.4 | 33.0   | 33.0 | 33.0   |
| 45°    | 19.8   | 19.8 | 19.8   | 19.8 | 26.4   | 26.4 | 26.4   | 26.4 | 33.0   | 33.0 | 33.0   |
| 47.5°  | 19.8   | 19.8 | 19.8   | 19.8 | 26.4   | 26.4 | 26.4   | 26.4 | 33.0   | 33.0 | 33.0   |
| 50°    | 19.8   | 19.8 | 19.8   | 19.8 | 26.4   | 26.4 | 26.4   | 26.4 | 33.0   | 33.0 | 33.0   |
| 52.5°  | 13.2   | 13.2 | 13.2   | 13.2 | 19.8   | 19.8 | 19.8   | 19.8 | 26.4   | 26.4 | 26.4   |
| 55°    | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 19.8   | 19.8 | 19.8   |
| 57.5°  | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 19.8   | 19.8 | 19.8   |
| 60°    | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   |
| 62.5°  | 6.6    | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  | 6.6    |
| 65°    | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 6.6  | 6.6    |
| 67.5°  | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   |
| 70°    | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   |
| 72.5°  | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   |
| 75°    | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   |
| 77.5°  | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   |
| 80°    | 19.8   | 19.8 | 19.8   | 19.8 | 19.8   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   |
| 82.5°  | 13.2   | 19.8 | 19.8   | 19.8 | 19.8   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   |
| 85°    | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   |
| 87.5°  | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   | 13.2 | 13.2   |
| 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240°  | 242.5° | 245°  |
|--------|------|--------|------|--------|------|--------|------|--------|-------|--------|-------|
| 0°     | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4 | 59.4   | 59.4  | 59.4   | 59.4  |
| 2.5°   | 85.8 | 85.8   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2  | 85.8   | 85.8  |
| 5°     | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2  | 85.8   | 85.8  |
| 7.5°   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2 | 79.2   | 79.2  | 85.8   | 85.8  |
| 10°    | 79.2 | 79.2   | 79.2 | 79.2   | 72.6 | 72.6   | 79.2 | 79.2   | 79.2  | 85.8   | 85.8  |
| 12.5°  | 79.2 | 79.2   | 79.2 | 79.2   | 72.6 | 72.6   | 79.2 | 79.2   | 85.8  | 85.8   | 92.4  |
| 15°    | 79.2 | 79.2   | 72.6 | 72.6   | 72.6 | 72.6   | 79.2 | 79.2   | 85.8  | 85.8   | 92.4  |
| 17.5°  | 79.2 | 79.2   | 72.6 | 72.6   | 72.6 | 72.6   | 79.2 | 79.2   | 85.8  | 85.8   | 92.4  |
| 20°    | 79.2 | 79.2   | 72.6 | 72.6   | 72.6 | 72.6   | 72.6 | 72.6   | 79.2  | 85.8   | 85.8  |
| 22.5°  | 72.6 | 72.6   | 72.6 | 72.6   | 66.0 | 66.0   | 72.6 | 72.6   | 79.2  | 85.8   | 85.8  |
| 25°    | 59.4 | 66.0   | 66.0 | 66.0   | 66.0 | 66.0   | 72.6 | 72.6   | 79.2  | 85.8   | 85.8  |
| 27.5°  | 52.8 | 59.4   | 59.4 | 59.4   | 59.4 | 66.0   | 66.0 | 72.6   | 79.2  | 85.8   | 85.8  |
| 30°    | 46.2 | 52.8   | 52.8 | 52.8   | 59.4 | 66.0   | 66.0 | 72.6   | 79.2  | 85.8   | 85.8  |
| 32.5°  | 46.2 | 52.8   | 52.8 | 52.8   | 59.4 | 59.4   | 66.0 | 66.0   | 72.6  | 79.2   | 85.8  |
| 35°    | 46.2 | 46.2   | 52.8 | 52.8   | 52.8 | 59.4   | 59.4 | 66.0   | 72.6  | 79.2   | 85.8  |
| 37.5°  | 46.2 | 46.2   | 52.8 | 52.8   | 52.8 | 59.4   | 59.4 | 66.0   | 72.6  | 79.2   | 85.8  |
| 40°    | 39.6 | 46.2   | 46.2 | 52.8   | 52.8 | 59.4   | 59.4 | 66.0   | 72.6  | 85.8   | 92.4  |
| 42.5°  | 39.6 | 39.6   | 46.2 | 46.2   | 52.8 | 59.4   | 59.4 | 66.0   | 72.6  | 85.8   | 92.4  |
| 45°    | 39.6 | 46.2   | 46.2 | 52.8   | 59.4 | 66.0   | 66.0 | 72.6   | 79.2  | 85.8   | 92.4  |
| 47.5°  | 39.6 | 46.2   | 46.2 | 52.8   | 66.0 | 66.0   | 72.6 | 72.6   | 79.2  | 85.8   | 92.4  |
| 50°    | 39.6 | 46.2   | 46.2 | 52.8   | 72.6 | 72.6   | 72.6 | 72.6   | 79.2  | 85.8   | 92.4  |
| 52.5°  | 33.0 | 39.6   | 39.6 | 46.2   | 59.4 | 66.0   | 72.6 | 79.2   | 85.8  | 92.4   | 99.0  |
| 55°    | 26.4 | 33.0   | 33.0 | 39.6   | 52.8 | 59.4   | 72.6 | 85.8   | 92.4  | 99.0   | 105.6 |
| 57.5°  | 26.4 | 26.4   | 33.0 | 33.0   | 46.2 | 59.4   | 79.2 | 92.4   | 99.0  | 105.6  | 112.1 |
| 60°    | 19.8 | 19.8   | 26.4 | 26.4   | 39.6 | 52.8   | 72.6 | 92.4   | 99.0  | 112.1  | 118.7 |
| 62.5°  | 13.2 | 19.8   | 19.8 | 26.4   | 33.0 | 52.8   | 72.6 | 92.4   | 105.6 | 118.7  | 125.3 |
| 65°    | 13.2 | 13.2   | 19.8 | 19.8   | 33.0 | 46.2   | 66.0 | 79.2   | 99.0  | 118.7  | 138.5 |
| 67.5°  | 19.8 | 19.8   | 26.4 | 26.4   | 33.0 | 46.2   | 66.0 | 79.2   | 99.0  | 125.3  | 145.1 |
| 70°    | 19.8 | 19.8   | 26.4 | 26.4   | 39.6 | 52.8   | 66.0 | 79.2   | 99.0  | 125.3  | 145.1 |
| 72.5°  | 19.8 | 19.8   | 26.4 | 26.4   | 39.6 | 46.2   | 59.4 | 72.6   | 92.4  | 112.1  | 131.9 |
| 75°    | 13.2 | 19.8   | 19.8 | 19.8   | 33.0 | 39.6   | 52.8 | 66.0   | 85.8  | 105.6  | 125.3 |
| 77.5°  | 13.2 | 13.2   | 13.2 | 13.2   | 26.4 | 33.0   | 46.2 | 52.8   | 72.6  | 92.4   | 112.1 |
| 80°    | 13.2 | 13.2   | 13.2 | 13.2   | 19.8 | 26.4   | 39.6 | 46.2   | 66.0  | 85.8   | 105.6 |
| 82.5°  | 13.2 | 13.2   | 6.6  | 6.6    | 13.2 | 19.8   | 26.4 | 33.0   | 52.8  | 66.0   | 85.8  |
| 85°    | 13.2 | 13.2   | 6.6  | 6.6    | 6.6  | 13.2   | 13.2 | 19.8   | 26.4  | 33.0   | 39.6  |
| 87.5°  | 13.2 | 13.2   | 6.6  | 6.6    | 6.6  | 6.6    | 6.6  | 6.6    | 6.6   | 6.6    | 6.6   |
| 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   | 272.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|--------|
| 0°     | 59.4   | 59.4  | 59.4   | 59.4  | 59.4   | 59.4  | 59.4   | 59.4  | 59.4   | 59.4   | 59.4   |
| 2.5°   | 85.8   | 85.8  | 92.4   | 92.4  | 92.4   | 92.4  | 92.4   | 92.4  | 92.4   | 92.4   | 92.4   |
| 5°     | 85.8   | 92.4  | 92.4   | 99.0  | 99.0   | 99.0  | 105.6  | 105.6 | 105.6  | 105.6  | 105.6  |
| 7.5°   | 85.8   | 92.4  | 92.4   | 99.0  | 99.0   | 99.0  | 105.6  | 105.6 | 105.6  | 112.1  | 112.1  |
| 10°    | 85.8   | 92.4  | 92.4   | 99.0  | 99.0   | 105.6 | 112.1  | 112.1 | 118.7  | 118.7  | 118.7  |
| 12.5°  | 92.4   | 99.0  | 99.0   | 105.6 | 105.6  | 112.1 | 118.7  | 118.7 | 125.3  | 131.9  | 131.9  |
| 15°    | 92.4   | 99.0  | 105.6  | 105.6 | 112.1  | 118.7 | 125.3  | 125.3 | 131.9  | 138.5  | 145.1  |
| 17.5°  | 92.4   | 99.0  | 105.6  | 105.6 | 112.1  | 118.7 | 131.9  | 138.5 | 145.1  | 158.3  | 164.9  |
| 20°    | 92.4   | 99.0  | 105.6  | 105.6 | 112.1  | 125.3 | 131.9  | 145.1 | 151.7  | 164.9  | 178.1  |
| 22.5°  | 92.4   | 99.0  | 105.6  | 112.1 | 118.7  | 131.9 | 145.1  | 151.7 | 164.9  | 184.7  | 197.9  |
| 25°    | 92.4   | 99.0  | 105.6  | 112.1 | 118.7  | 131.9 | 145.1  | 158.3 | 171.5  | 197.9  | 224.3  |
| 27.5°  | 92.4   | 99.0  | 112.1  | 118.7 | 125.3  | 138.5 | 158.3  | 171.5 | 184.7  | 230.9  | 277.1  |
| 30°    | 92.4   | 99.0  | 112.1  | 118.7 | 125.3  | 145.1 | 164.9  | 178.1 | 197.9  | 277.1  | 349.6  |
| 32.5°  | 92.4   | 105.6 | 112.1  | 125.3 | 131.9  | 151.7 | 178.1  | 197.9 | 217.7  | 329.8  | 435.4  |
| 35°    | 92.4   | 105.6 | 112.1  | 125.3 | 131.9  | 158.3 | 184.7  | 211.1 | 237.5  | 402.4  | 567.3  |
| 37.5°  | 92.4   | 105.6 | 112.1  | 125.3 | 131.9  | 171.5 | 211.1  | 250.7 | 290.3  | 461.8  | 633.3  |
| 40°    | 99.0   | 112.1 | 118.7  | 131.9 | 138.5  | 178.1 | 217.7  | 257.3 | 296.9  | 468.4  | 639.9  |
| 42.5°  | 99.0   | 112.1 | 118.7  | 131.9 | 138.5  | 171.5 | 211.1  | 244.1 | 277.1  | 468.4  | 659.7  |
| 45°    | 99.0   | 112.1 | 125.3  | 131.9 | 145.1  | 178.1 | 211.1  | 237.5 | 270.5  | 514.6  | 752.0  |
| 47.5°  | 99.0   | 112.1 | 125.3  | 131.9 | 145.1  | 178.1 | 211.1  | 244.1 | 277.1  | 679.5  | 1075.3 |
| 50°    | 99.0   | 112.1 | 125.3  | 131.9 | 145.1  | 184.7 | 224.3  | 263.9 | 303.5  | 1015.9 | 1728.4 |
| 52.5°  | 105.6  | 112.1 | 125.3  | 131.9 | 138.5  | 184.7 | 230.9  | 277.1 | 323.2  | 1319.4 | 2308.9 |
| 55°    | 112.1  | 118.7 | 125.3  | 131.9 | 138.5  | 197.9 | 257.3  | 316.7 | 376.0  | 1418.3 | 2454.0 |
| 57.5°  | 118.7  | 125.3 | 131.9  | 131.9 | 138.5  | 211.1 | 290.3  | 362.8 | 435.4  | 1411.7 | 2381.5 |
| 60°    | 125.3  | 131.9 | 138.5  | 145.1 | 151.7  | 224.3 | 303.5  | 376.0 | 448.6  | 1279.8 | 2111.0 |
| 62.5°  | 138.5  | 151.7 | 164.9  | 171.5 | 184.7  | 257.3 | 323.2  | 395.8 | 461.8  | 1048.9 | 1629.4 |
| 65°    | 158.3  | 171.5 | 178.1  | 191.3 | 197.9  | 263.9 | 336.4  | 402.4 | 468.4  | 870.8  | 1266.6 |
| 67.5°  | 164.9  | 178.1 | 184.7  | 197.9 | 204.5  | 270.5 | 336.4  | 402.4 | 468.4  | 738.9  | 1002.7 |
| 70°    | 164.9  | 178.1 | 191.3  | 197.9 | 211.1  | 277.1 | 336.4  | 402.4 | 461.8  | 639.9  | 818.0  |
| 72.5°  | 151.7  | 171.5 | 184.7  | 204.5 | 217.7  | 277.1 | 329.8  | 389.2 | 442.0  | 567.3  | 692.7  |
| 75°    | 145.1  | 171.5 | 191.3  | 217.7 | 237.5  | 277.1 | 323.2  | 362.8 | 402.4  | 494.8  | 587.1  |
| 77.5°  | 131.9  | 164.9 | 197.9  | 230.9 | 263.9  | 290.3 | 310.1  | 336.4 | 356.2  | 415.6  | 475.0  |
| 80°    | 125.3  | 158.3 | 191.3  | 224.3 | 257.3  | 270.5 | 277.1  | 290.3 | 296.9  | 303.5  | 310.1  |
| 82.5°  | 99.0   | 125.3 | 151.7  | 171.5 | 197.9  | 184.7 | 178.1  | 164.9 | 151.7  | 145.1  | 138.5  |
| 85°    | 46.2   | 52.8  | 52.8   | 59.4  | 59.4   | 59.4  | 52.8   | 52.8  | 46.2   | 39.6   | 33.0   |
| 87.5°  | 6.6    | 6.6   | 6.6    | 6.6   | 6.6    | 6.6   | 6.6    | 6.6   | 6.6    | 6.6    | 6.6    |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  | 300°    |
|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 59.4   | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    |
| 2.5°   | 92.4   | 92.4    | 92.4    | 92.4    | 85.8    | 85.8    | 85.8    | 85.8    | 79.2    | 79.2    | 79.2    |
| 5°     | 105.6  | 105.6   | 105.6   | 105.6   | 99.0    | 99.0    | 99.0    | 99.0    | 92.4    | 92.4    | 92.4    |
| 7.5°   | 112.1  | 112.1   | 112.1   | 112.1   | 112.1   | 112.1   | 112.1   | 112.1   | 112.1   | 112.1   | 112.1   |
| 10°    | 125.3  | 125.3   | 125.3   | 131.9   | 131.9   | 131.9   | 131.9   | 131.9   | 131.9   | 131.9   | 131.9   |
| 12.5°  | 138.5  | 138.5   | 145.1   | 145.1   | 151.7   | 151.7   | 158.3   | 158.3   | 164.9   | 164.9   | 164.9   |
| 15°    | 151.7  | 158.3   | 164.9   | 171.5   | 171.5   | 178.1   | 184.7   | 191.3   | 197.9   | 204.5   | 211.1   |
| 17.5°  | 178.1  | 184.7   | 197.9   | 211.1   | 224.3   | 237.5   | 257.3   | 283.7   | 303.5   | 323.2   | 349.6   |
| 20°    | 197.9  | 217.7   | 257.3   | 303.5   | 343.0   | 382.6   | 481.6   | 580.5   | 679.5   | 778.4   | 877.4   |
| 22.5°  | 237.5  | 277.1   | 409.0   | 547.5   | 679.5   | 811.4   | 1121.5  | 1431.5  | 1735.0  | 2045.0  | 2322.1  |
| 25°    | 316.7  | 402.4   | 705.9   | 1009.3  | 1306.2  | 1609.6  | 2163.8  | 2724.5  | 3278.7  | 3832.8  | 4347.4  |
| 27.5°  | 435.4  | 593.7   | 1088.5  | 1589.9  | 2084.6  | 2579.4  | 3384.2  | 4195.6  | 5000.5  | 5811.9  | 6530.9  |
| 30°    | 606.9  | 864.2   | 1603.0  | 2348.5  | 3087.3  | 3826.2  | 4842.1  | 5864.6  | 6880.6  | 7896.5  | 8556.2  |
| 32.5°  | 824.6  | 1207.2  | 2144.0  | 3080.8  | 4017.5  | 4954.3  | 6075.7  | 7197.2  | 8312.1  | 9433.6  | 10132.8 |
| 35°    | 1055.5 | 1543.7  | 2671.7  | 3806.4  | 4934.5  | 6069.1  | 7250.0  | 8430.8  | 9611.7  | 10792.5 | 11650.1 |
| 37.5°  | 1187.4 | 1741.6  | 3080.8  | 4419.9  | 5752.5  | 7091.7  | 8384.7  | 9684.2  | 10977.2 | 12270.2 | 13312.5 |
| 40°    | 1312.8 | 1979.1  | 3522.7  | 5066.4  | 6610.1  | 8153.8  | 9664.5  | 11175.1 | 12685.8 | 14196.5 | 15535.7 |
| 42.5°  | 1497.5 | 2335.3  | 4136.3  | 5937.2  | 7731.6  | 9532.5  | 11518.2 | 13510.5 | 15496.1 | 17481.8 | 19540.0 |
| 45°    | 1880.1 | 3008.2  | 5343.5  | 7678.8  | 10007.5 | 12342.8 | 15159.7 | 17983.2 | 20800.0 | 23623.5 | 26262.3 |
| 47.5°  | 2803.7 | 4525.5  | 7711.8  | 10898.1 | 14084.4 | 17270.7 | 20516.4 | 23762.0 | 27007.7 | 30253.4 | 33393.5 |
| 50°    | 4340.8 | 6946.5  | 10931.1 | 14915.6 | 18893.5 | 22878.1 | 26117.1 | 29356.2 | 32588.7 | 35827.8 | 38948.1 |
| 52.5°  | 5785.5 | 9262.0  | 13543.4 | 17831.4 | 22112.8 | 26400.8 | 29270.4 | 32140.1 | 35009.8 | 37879.4 | 40900.8 |
| 55°    | 6280.2 | 10099.9 | 14434.0 | 18774.8 | 23108.9 | 27449.7 | 30213.8 | 32984.5 | 35748.6 | 38512.7 | 41646.2 |
| 57.5°  | 5844.9 | 9308.2  | 13675.4 | 18042.5 | 22403.1 | 26770.2 | 29857.6 | 32951.5 | 36038.9 | 39132.8 | 42490.6 |
| 60°    | 4894.9 | 7672.2  | 12257.0 | 16848.5 | 21433.3 | 26018.2 | 29501.3 | 32984.5 | 36467.7 | 39950.8 | 43302.1 |
| 62.5°  | 3879.0 | 6121.9  | 10977.2 | 15832.6 | 20687.9 | 25543.2 | 29085.7 | 32634.9 | 36177.4 | 39719.9 | 42292.7 |
| 65°    | 2975.2 | 4683.8  | 9460.0  | 14242.7 | 19018.9 | 23801.6 | 26704.3 | 29613.5 | 32516.1 | 35425.4 | 37206.5 |
| 67.5°  | 2210.0 | 3417.2  | 7593.0  | 11775.5 | 15951.3 | 20127.1 | 22264.5 | 24408.5 | 26545.9 | 28689.9 | 30075.3 |
| 70°    | 1629.4 | 2434.3  | 5277.5  | 8120.8  | 10957.5 | 13800.7 | 15760.0 | 17719.3 | 19672.0 | 21631.2 | 23069.4 |
| 72.5°  | 1128.1 | 1556.9  | 3258.9  | 4967.5  | 6669.5  | 8371.5  | 10357.1 | 12342.8 | 14321.9 | 16307.5 | 17943.6 |
| 75°    | 771.8  | 956.6   | 1754.8  | 2553.0  | 3351.2  | 4149.5  | 5653.5  | 7157.6  | 8661.7  | 10165.8 | 11030.0 |
| 77.5°  | 573.9  | 672.9   | 910.4   | 1154.5  | 1391.9  | 1629.4  | 1919.7  | 2210.0  | 2500.2  | 2790.5  | 3166.5  |
| 80°    | 316.7  | 316.7   | 349.6   | 376.0   | 409.0   | 435.4   | 514.6   | 600.3   | 679.5   | 765.2   | 870.8   |
| 82.5°  | 145.1  | 151.7   | 164.9   | 178.1   | 184.7   | 197.9   | 211.1   | 224.3   | 237.5   | 250.7   | 250.7   |
| 85°    | 39.6   | 46.2    | 46.2    | 39.6    | 39.6    | 33.0    | 33.0    | 39.6    | 39.6    | 39.6    | 39.6    |
| 87.5°  | 6.6    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 90°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  | 325°    | 327.5°  |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    |
| 2.5°   | 79.2    | 72.6    | 72.6    | 72.6    | 66.0    | 66.0    | 66.0    | 66.0    | 66.0    | 66.0    | 66.0    |
| 5°     | 92.4    | 92.4    | 92.4    | 92.4    | 85.8    | 85.8    | 85.8    | 85.8    | 85.8    | 79.2    | 79.2    |
| 7.5°   | 112.1   | 105.6   | 105.6   | 105.6   | 105.6   | 105.6   | 105.6   | 105.6   | 105.6   | 99.0    | 99.0    |
| 10°    | 131.9   | 131.9   | 131.9   | 131.9   | 131.9   | 131.9   | 131.9   | 131.9   | 131.9   | 125.3   | 125.3   |
| 12.5°  | 164.9   | 164.9   | 164.9   | 164.9   | 171.5   | 171.5   | 164.9   | 164.9   | 164.9   | 158.3   | 158.3   |
| 15°    | 217.7   | 224.3   | 230.9   | 230.9   | 237.5   | 237.5   | 237.5   | 230.9   | 230.9   | 224.3   | 217.7   |
| 17.5°  | 369.4   | 389.2   | 415.6   | 442.0   | 468.4   | 488.2   | 488.2   | 475.0   | 461.8   | 448.6   | 435.4   |
| 20°    | 982.9   | 1081.9  | 1187.4  | 1293.0  | 1405.1  | 1484.3  | 1431.5  | 1391.9  | 1352.4  | 1306.2  | 1266.6  |
| 22.5°  | 2605.8  | 2882.8  | 3166.5  | 3364.4  | 3562.3  | 3700.9  | 3588.7  | 3371.0  | 3153.3  | 2942.2  | 2724.5  |
| 25°    | 4861.9  | 5369.9  | 5884.4  | 6095.5  | 6313.2  | 6471.6  | 6399.0  | 6069.1  | 5739.3  | 5416.1  | 5086.2  |
| 27.5°  | 7250.0  | 7962.5  | 8681.5  | 8866.2  | 9050.9  | 9189.5  | 9163.1  | 8734.3  | 8305.5  | 7876.7  | 7447.9  |
| 30°    | 9215.9  | 9875.6  | 10535.2 | 10720.0 | 10904.7 | 11030.0 | 10891.5 | 10462.7 | 10033.9 | 9605.1  | 9176.3  |
| 32.5°  | 10838.7 | 11538.0 | 12243.8 | 12487.9 | 12732.0 | 12896.9 | 12732.0 | 12217.5 | 11702.9 | 11194.9 | 10680.4 |
| 35°    | 12507.7 | 13358.7 | 14216.3 | 14526.4 | 14836.4 | 15034.3 | 14757.3 | 14124.0 | 13490.7 | 12864.0 | 12230.7 |
| 37.5°  | 14354.9 | 15390.6 | 16432.9 | 16855.1 | 17283.9 | 17580.7 | 17369.6 | 16578.0 | 15779.8 | 14988.2 | 14189.9 |
| 40°    | 16881.5 | 18220.6 | 19566.4 | 20325.1 | 21077.1 | 21611.4 | 21235.4 | 20318.5 | 19394.9 | 18477.9 | 17554.4 |
| 42.5°  | 21604.8 | 23663.1 | 25721.3 | 26809.8 | 27891.7 | 28676.7 | 28254.5 | 27126.5 | 25998.4 | 24870.3 | 23742.2 |
| 45°    | 28901.0 | 31533.2 | 34171.9 | 35761.8 | 37358.2 | 38532.5 | 38044.3 | 36626.0 | 35201.1 | 33782.7 | 32364.4 |
| 47.5°  | 36533.6 | 39673.8 | 42813.9 | 44080.5 | 45353.7 | 46343.2 | 46224.5 | 44456.5 | 42688.5 | 40927.2 | 39159.2 |
| 50°    | 42075.0 | 45195.4 | 48315.7 | 49404.2 | 50499.3 | 51310.7 | 51007.2 | 48757.7 | 46501.6 | 44252.0 | 41995.9 |
| 52.5°  | 43922.2 | 46936.9 | 49958.3 | 51257.9 | 52557.5 | 53527.3 | 53157.8 | 50624.6 | 48091.4 | 45564.8 | 43031.6 |
| 55°    | 44779.8 | 47913.3 | 51046.8 | 52630.1 | 54219.9 | 55381.0 | 54846.6 | 52069.3 | 49285.4 | 46508.1 | 43724.3 |
| 57.5°  | 45848.5 | 49206.3 | 52564.1 | 54299.1 | 56034.1 | 57287.5 | 56575.0 | 53698.8 | 50822.5 | 47952.9 | 45076.6 |
| 60°    | 46653.3 | 49997.9 | 53349.1 | 54741.1 | 56139.6 | 57116.0 | 56429.9 | 53632.8 | 50829.1 | 48032.0 | 45234.9 |
| 62.5°  | 44872.1 | 47444.9 | 50017.7 | 51053.4 | 52089.1 | 52841.2 | 52452.0 | 49800.0 | 47148.0 | 44496.1 | 41844.1 |
| 65°    | 38994.3 | 40775.4 | 42563.2 | 43262.5 | 43955.1 | 44489.5 | 44370.8 | 42134.4 | 39898.1 | 37668.3 | 35432.0 |
| 67.5°  | 31467.2 | 32852.6 | 34244.5 | 35234.0 | 36230.2 | 37002.0 | 36916.3 | 34877.8 | 32839.4 | 30800.9 | 28762.5 |
| 70°    | 24514.1 | 25952.2 | 27390.3 | 28637.1 | 29890.6 | 30860.3 | 30735.0 | 28841.6 | 26941.7 | 25048.4 | 23148.5 |
| 72.5°  | 19586.2 | 21222.2 | 22858.3 | 23570.7 | 24283.2 | 24784.6 | 24415.1 | 22983.6 | 21545.5 | 20113.9 | 18675.8 |
| 75°    | 11894.2 | 12751.8 | 13616.0 | 13609.4 | 13609.4 | 13530.2 | 13160.8 | 12342.8 | 11524.8 | 10706.8 | 9888.8  |
| 77.5°  | 3542.5  | 3918.6  | 4294.6  | 4657.4  | 5026.8  | 5303.9  | 5231.3  | 4802.5  | 4367.1  | 3938.3  | 3503.0  |
| 80°    | 976.3   | 1075.3  | 1180.8  | 1227.0  | 1273.2  | 1332.6  | 1484.3  | 1378.8  | 1273.2  | 1174.2  | 1068.7  |
| 82.5°  | 250.7   | 250.7   | 250.7   | 244.1   | 237.5   | 224.3   | 204.5   | 191.3   | 178.1   | 164.9   | 151.7   |
| 85°    | 39.6    | 33.0    | 33.0    | 33.0    | 26.4    | 26.4    | 26.4    | 26.4    | 19.8    | 19.8    | 13.2    |
| 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    | 352.5°  | 355°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    |
| 2.5°   | 66.0    | 66.0    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 59.4    | 52.8    |
| 5°     | 79.2    | 79.2    | 72.6    | 72.6    | 72.6    | 72.6    | 72.6    | 72.6    | 72.6    | 72.6    | 66.0    |
| 7.5°   | 99.0    | 99.0    | 92.4    | 92.4    | 92.4    | 92.4    | 85.8    | 85.8    | 85.8    | 85.8    | 79.2    |
| 10°    | 125.3   | 118.7   | 118.7   | 112.1   | 112.1   | 112.1   | 105.6   | 105.6   | 105.6   | 99.0    | 99.0    |
| 12.5°  | 158.3   | 151.7   | 151.7   | 145.1   | 138.5   | 138.5   | 131.9   | 125.3   | 118.7   | 118.7   | 112.1   |
| 15°    | 211.1   | 204.5   | 197.9   | 191.3   | 184.7   | 171.5   | 164.9   | 151.7   | 145.1   | 138.5   | 131.9   |
| 17.5°  | 402.4   | 369.4   | 336.4   | 303.5   | 277.1   | 250.7   | 224.3   | 197.9   | 184.7   | 171.5   | 158.3   |
| 20°    | 1121.5  | 969.7   | 824.6   | 679.5   | 587.1   | 494.8   | 402.4   | 310.1   | 270.5   | 237.5   | 197.9   |
| 22.5°  | 2427.7  | 2124.2  | 1827.3  | 1523.9  | 1279.8  | 1042.3  | 798.2   | 554.1   | 461.8   | 376.0   | 283.7   |
| 25°    | 4512.3  | 3931.8  | 3357.8  | 2777.3  | 2315.5  | 1853.7  | 1391.9  | 930.2   | 758.6   | 587.1   | 415.6   |
| 27.5°  | 6695.9  | 5943.8  | 5191.8  | 4439.7  | 3707.5  | 2968.6  | 2229.8  | 1497.5  | 1200.6  | 910.4   | 613.5   |
| 30°    | 8378.1  | 7579.8  | 6788.2  | 5990.0  | 5066.4  | 4142.9  | 3212.7  | 2289.1  | 1820.7  | 1352.4  | 877.4   |
| 32.5°  | 9822.8  | 8958.6  | 8101.0  | 7236.8  | 6168.1  | 5099.4  | 4030.7  | 2962.0  | 2374.9  | 1787.8  | 1194.0  |
| 35°    | 11254.3 | 10271.4 | 9295.0  | 8312.1  | 7164.2  | 6016.4  | 4868.5  | 3720.7  | 2975.2  | 2229.8  | 1477.7  |
| 37.5°  | 12995.9 | 11795.3 | 10601.2 | 9407.2  | 8226.3  | 7052.1  | 5871.2  | 4690.4  | 3740.4  | 2797.1  | 1847.1  |
| 40°    | 16030.5 | 14500.0 | 12976.1 | 11445.6 | 10066.9 | 8694.7  | 7316.0  | 5937.2  | 4743.2  | 3549.1  | 2348.5  |
| 42.5°  | 21822.5 | 19902.8 | 17989.7 | 16070.0 | 14163.5 | 12257.0 | 10343.9 | 8437.4  | 6735.4  | 5040.0  | 3338.0  |
| 45°    | 29903.7 | 27443.1 | 24989.1 | 22528.4 | 20179.9 | 17838.0 | 15489.5 | 13141.0 | 10555.0 | 7969.1  | 5376.5  |
| 47.5°  | 36467.7 | 33769.5 | 31078.0 | 28379.9 | 25774.1 | 23174.9 | 20569.1 | 17963.4 | 14651.7 | 11346.7 | 8035.0  |
| 50°    | 39429.7 | 36856.9 | 34290.7 | 31717.9 | 29105.5 | 26486.6 | 23867.6 | 21255.2 | 17455.4 | 13662.2 | 9862.4  |
| 52.5°  | 40425.8 | 37813.4 | 35207.7 | 32595.3 | 30002.7 | 27410.1 | 24817.5 | 22225.0 | 18273.4 | 14328.5 | 10376.9 |
| 55°    | 40973.3 | 38215.8 | 35464.9 | 32707.4 | 29916.9 | 27119.9 | 24322.8 | 21532.3 | 17600.5 | 13675.4 | 9743.6  |
| 57.5°  | 42081.6 | 39080.0 | 36085.0 | 33083.5 | 29903.7 | 26724.0 | 23537.7 | 20358.0 | 16479.1 | 12600.1 | 8721.1  |
| 60°    | 42286.1 | 39330.7 | 36381.9 | 33433.1 | 29916.9 | 26400.8 | 22878.1 | 19361.9 | 15509.3 | 11663.3 | 7810.7  |
| 62.5°  | 39376.9 | 36909.7 | 34449.0 | 31981.8 | 28459.0 | 24936.3 | 21406.9 | 17884.2 | 14196.5 | 10508.9 | 6814.6  |
| 65°    | 33301.2 | 31170.4 | 29046.2 | 26915.4 | 24039.1 | 21169.5 | 18293.2 | 15417.0 | 12125.1 | 8839.8  | 5548.0  |
| 67.5°  | 26677.9 | 24593.2 | 22515.2 | 20430.6 | 18266.8 | 16109.6 | 13945.8 | 11782.1 | 9242.3  | 6702.5  | 4162.6  |
| 70°    | 21149.7 | 19144.2 | 17145.3 | 15139.9 | 13226.8 | 11307.1 | 9387.4  | 7474.3  | 5897.6  | 4327.6  | 2750.9  |
| 72.5°  | 16762.7 | 14843.0 | 12929.9 | 11010.2 | 9275.2  | 7540.3  | 5805.3  | 4070.3  | 3285.3  | 2506.8  | 1721.8  |
| 75°    | 8892.6  | 7896.5  | 6907.0  | 5910.8  | 4934.5  | 3951.5  | 2968.6  | 1992.3  | 1682.2  | 1372.2  | 1055.5  |
| 77.5°  | 3067.6  | 2632.2  | 2203.4  | 1768.0  | 1471.1  | 1174.2  | 877.4   | 580.5   | 547.5   | 521.2   | 488.2   |
| 80°    | 930.2   | 791.6   | 653.1   | 514.6   | 455.2   | 395.8   | 336.4   | 277.1   | 257.3   | 237.5   | 211.1   |
| 82.5°  | 145.1   | 131.9   | 125.3   | 112.1   | 105.6   | 105.6   | 99.0    | 92.4    | 79.2    | 72.6    | 59.4    |
| 85°    | 13.2    | 6.6     | 6.6     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 59.4   | 59.4   |
| 2.5°   | 52.8   | 52.8   |
| 5°     | 66.0   | 66.0   |
| 7.5°   | 79.2   | 79.2   |
| 10°    | 92.4   | 92.4   |
| 12.5°  | 105.6  | 105.6  |
| 15°    | 125.3  | 118.7  |
| 17.5°  | 145.1  | 138.5  |
| 20°    | 158.3  | 145.1  |
| 22.5°  | 191.3  | 164.9  |
| 25°    | 244.1  | 204.5  |
| 27.5°  | 316.7  | 250.7  |
| 30°    | 409.0  | 316.7  |
| 32.5°  | 606.9  | 442.0  |
| 35°    | 732.3  | 534.3  |
| 37.5°  | 897.2  | 620.1  |
| 40°    | 1154.5 | 752.0  |
| 42.5°  | 1636.0 | 1022.5 |
| 45°    | 2790.5 | 1695.4 |
| 47.5°  | 4730.0 | 2889.4 |
| 50°    | 6062.6 | 3707.5 |
| 52.5°  | 6432.0 | 3931.8 |
| 55°    | 5818.5 | 3608.5 |
| 57.5°  | 4842.1 | 3067.6 |
| 60°    | 3964.7 | 2526.6 |
| 62.5°  | 3126.9 | 1998.9 |
| 65°    | 2256.1 | 1510.7 |
| 67.5°  | 1622.8 | 1161.1 |
| 70°    | 1180.8 | 910.4  |
| 72.5°  | 936.8  | 758.6  |
| 75°    | 745.4  | 633.3  |
| 77.5°  | 461.8  | 422.2  |
| 80°    | 191.3  | 178.1  |
| 82.5°  | 46.2   | 39.6   |
| 85°    | 0.0    | 0.0    |
| 87.5°  | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |

REPORT NUMBER: P1066475

CATALOG NUMBER: NVN-SA6C-722-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-722-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 2200K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 2160     | CRI (Ra): | 71.9 |      |       |
| CIE u':                   | 0.2927   | R1:       | 68.7 | R9:  | -17.8 |
| CIE v':                   | 0.5388   | R2:       | 82.6 | R10: | 60.5  |
| Duv:                      | 0.0015   | R3:       | 95.5 | R11: | 60.2  |
| CIE x:                    | 0.5130   | R4:       | 66.4 | R12: | 48.2  |
| CIE y:                    | 0.4197   | R5:       | 65.4 | R13: | 70.7  |
| CIE z:                    | 0.0674   | R6:       | 75.9 | R14: | 96.8  |
| Peak Wavelength (nm):     | 609      | R7:       | 77.2 | R15: | 61.8  |
| Dominant Wavelength (nm): | 587      | R8:       | 43.5 |      |       |
| Purity:                   | 79.96089 |           |      |      |       |
| Rf:                       | 70.6     |           |      |      |       |
| Rg:                       | 97.6     |           |      |      |       |



### Test Conditions

Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2


REPORT NUMBER: SP1-2407-184-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |



REPORT NUMBER: SP1-2407-184-2

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 27                                   | NR                             | 620               | 966                                  | NR                             | 750               | 46                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 42                                   | NR                             | 625               | 930                                  | NR                             | 755               | 39                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 67                                   | NR                             | 630               | 888                                  | NR                             | 760               | 34                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 101                                  | NR                             | 635               | 835                                  | NR                             | 765               | 30                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 139                                  | NR                             | 640               | 778                                  | NR                             | 770               | 26                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 183                                  | NR                             | 645               | 717                                  | NR                             | 775               | 22                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 224                                  | NR                             | 650               | 656                                  | NR                             | 780               | 19                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 262                                  | NR                             | 655               | 595                                  | NR                             | 785               | 17                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 299                                  | NR                             | 660               | 536                                  | NR                             | 790               | 15                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 3                                    | NR                             | 535               | 332                                  | NR                             | 665               | 480                                  | NR                             | 795               | 13                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 365                                  | NR                             | 670               | 425                                  | NR                             | 800               | 11                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 17                                   | NR                             | 545               | 400                                  | NR                             | 675               | 376                                  | NR                             | 805               | 10                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 36                                   | NR                             | 550               | 437                                  | NR                             | 680               | 332                                  | NR                             | 810               | 8                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 67                                   | NR                             | 555               | 479                                  | NR                             | 685               | 291                                  | NR                             | 815               | 8                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 105                                  | NR                             | 560               | 525                                  | NR                             | 690               | 255                                  | NR                             | 820               | 7                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 141                                  | NR                             | 565               | 579                                  | NR                             | 695               | 221                                  | NR                             | 825               | 6                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 169                                  | NR                             | 570               | 639                                  | NR                             | 700               | 192                                  | NR                             | 830               | 5                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 173                                  | NR                             | 575               | 703                                  | NR                             | 705               | 167                                  | NR                             | 835               | 4                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 136                                  | NR                             | 580               | 769                                  | NR                             | 710               | 144                                  | NR                             | 840               | 4                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 80                                   | NR                             | 585               | 832                                  | NR                             | 715               | 125                                  | NR                             | 845               | 3                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 45                                   | NR                             | 590               | 890                                  | NR                             | 720               | 109                                  | NR                             | 850               | 3                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 32                                   | NR                             | 595               | 937                                  | NR                             | 725               | 94                                   | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 23                                   | NR                             | 600               | 972                                  | NR                             | 730               | 81                                   | NR                             | 860               | 2                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 18                                   | NR                             | 605               | 992                                  | NR                             | 735               | 70                                   | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 18                                   | NR                             | 610               | 998                                  | NR                             | 740               | 61                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 20                                   | NR                             | 615               | 990                                  | NR                             | 745               | 53                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-2

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 0.8

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 27                                   | NR                             | 620               | 966                                  | NR                             | 750               | 46                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 42                                   | NR                             | 625               | 930                                  | NR                             | 755               | 39                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 67                                   | NR                             | 630               | 888                                  | NR                             | 760               | 34                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 101                                  | NR                             | 635               | 835                                  | NR                             | 765               | 30                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 139                                  | NR                             | 640               | 778                                  | NR                             | 770               | 26                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 183                                  | NR                             | 645               | 717                                  | NR                             | 775               | 22                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 224                                  | NR                             | 650               | 656                                  | NR                             | 780               | 19                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 262                                  | NR                             | 655               | 595                                  | NR                             | 785               | 17                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 299                                  | NR                             | 660               | 536                                  | NR                             | 790               | 15                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 3                                    | NR                             | 535               | 332                                  | NR                             | 665               | 480                                  | NR                             | 795               | 13                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 365                                  | NR                             | 670               | 425                                  | NR                             | 800               | 11                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 17                                   | NR                             | 545               | 400                                  | NR                             | 675               | 376                                  | NR                             | 805               | 10                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 36                                   | NR                             | 550               | 437                                  | NR                             | 680               | 332                                  | NR                             | 810               | 8                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 67                                   | NR                             | 555               | 479                                  | NR                             | 685               | 291                                  | NR                             | 815               | 8                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 105                                  | NR                             | 560               | 525                                  | NR                             | 690               | 255                                  | NR                             | 820               | 7                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 141                                  | NR                             | 565               | 579                                  | NR                             | 695               | 221                                  | NR                             | 825               | 6                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 169                                  | NR                             | 570               | 639                                  | NR                             | 700               | 192                                  | NR                             | 830               | 5                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 173                                  | NR                             | 575               | 703                                  | NR                             | 705               | 167                                  | NR                             | 835               | 4                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 136                                  | NR                             | 580               | 769                                  | NR                             | 710               | 144                                  | NR                             | 840               | 4                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 80                                   | NR                             | 585               | 832                                  | NR                             | 715               | 125                                  | NR                             | 845               | 3                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 45                                   | NR                             | 590               | 890                                  | NR                             | 720               | 109                                  | NR                             | 850               | 3                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 32                                   | NR                             | 595               | 937                                  | NR                             | 725               | 94                                   | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 23                                   | NR                             | 600               | 972                                  | NR                             | 730               | 81                                   | NR                             | 860               | 2                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 18                                   | NR                             | 605               | 992                                  | NR                             | 735               | 70                                   | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 18                                   | NR                             | 610               | 998                                  | NR                             | 740               | 61                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 20                                   | NR                             | 615               | 990                                  | NR                             | 745               | 53                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-2

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 1.21**

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 27                                   | NR                             | 620               | 966                                  | NR                             | 750               | 46                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 42                                   | NR                             | 625               | 930                                  | NR                             | 755               | 39                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 67                                   | NR                             | 630               | 888                                  | NR                             | 760               | 34                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 101                                  | NR                             | 635               | 835                                  | NR                             | 765               | 30                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 139                                  | NR                             | 640               | 778                                  | NR                             | 770               | 26                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 183                                  | NR                             | 645               | 717                                  | NR                             | 775               | 22                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 224                                  | NR                             | 650               | 656                                  | NR                             | 780               | 19                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 262                                  | NR                             | 655               | 595                                  | NR                             | 785               | 17                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 299                                  | NR                             | 660               | 536                                  | NR                             | 790               | 15                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 3                                    | NR                             | 535               | 332                                  | NR                             | 665               | 480                                  | NR                             | 795               | 13                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 365                                  | NR                             | 670               | 425                                  | NR                             | 800               | 11                                   | NR                             | 930               | 1                                    | NR                             |
| 415               | 17                                   | NR                             | 545               | 400                                  | NR                             | 675               | 376                                  | NR                             | 805               | 10                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 36                                   | NR                             | 550               | 437                                  | NR                             | 680               | 332                                  | NR                             | 810               | 8                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 67                                   | NR                             | 555               | 479                                  | NR                             | 685               | 291                                  | NR                             | 815               | 8                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 105                                  | NR                             | 560               | 525                                  | NR                             | 690               | 255                                  | NR                             | 820               | 7                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 141                                  | NR                             | 565               | 579                                  | NR                             | 695               | 221                                  | NR                             | 825               | 6                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 169                                  | NR                             | 570               | 639                                  | NR                             | 700               | 192                                  | NR                             | 830               | 5                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 173                                  | NR                             | 575               | 703                                  | NR                             | 705               | 167                                  | NR                             | 835               | 4                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 136                                  | NR                             | 580               | 769                                  | NR                             | 710               | 144                                  | NR                             | 840               | 4                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 80                                   | NR                             | 585               | 832                                  | NR                             | 715               | 125                                  | NR                             | 845               | 3                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 45                                   | NR                             | 590               | 890                                  | NR                             | 720               | 109                                  | NR                             | 850               | 3                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 32                                   | NR                             | 595               | 937                                  | NR                             | 725               | 94                                   | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 23                                   | NR                             | 600               | 972                                  | NR                             | 730               | 81                                   | NR                             | 860               | 2                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 18                                   | NR                             | 605               | 992                                  | NR                             | 735               | 70                                   | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 18                                   | NR                             | 610               | 998                                  | NR                             | 740               | 61                                   | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 20                                   | NR                             | 615               | 990                                  | NR                             | 745               | 53                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-2

TM-30-18

### Summary

$R_f = 70.6$   
 $R_g = 97.6$   
 $CIE R_a = 71.9$   
 $R_g = -17.8$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 60 | CES51 = 74 | CES76 = 58 |
| CES02 = 65 | CES27 = 77 | CES52 = 77 | CES77 = 82 |
| CES03 = 32 | CES28 = 85 | CES53 = 65 | CES78 = 65 |
| CES04 = 72 | CES29 = 50 | CES54 = 77 | CES79 = 86 |
| CES05 = 52 | CES30 = 49 | CES55 = 74 | CES80 = 85 |
| CES06 = 53 | CES31 = 55 | CES56 = 64 | CES81 = 61 |
| CES07 = 44 | CES32 = 55 | CES57 = 60 | CES82 = 93 |
| CES08 = 43 | CES33 = 55 | CES58 = 64 | CES83 = 83 |
| CES09 = 29 | CES34 = 75 | CES59 = 84 | CES84 = 93 |
| CES10 = 79 | CES35 = 88 | CES60 = 89 | CES85 = 81 |
| CES11 = 62 | CES36 = 78 | CES61 = 84 | CES86 = 55 |
| CES12 = 68 | CES37 = 82 | CES62 = 68 | CES87 = 79 |
| CES13 = 45 | CES38 = 54 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 86 | CES65 = 66 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 89 |
| CES17 = 51 | CES42 = 83 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 68 | CES68 = 71 | CES93 = 78 |
| CES19 = 74 | CES44 = 98 | CES69 = 81 | CES94 = 52 |
| CES20 = 68 | CES45 = 76 | CES70 = 65 | CES95 = 76 |
| CES21 = 89 | CES46 = 68 | CES71 = 64 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 88 | CES97 = 76 |
| CES23 = 92 | CES48 = 47 | CES73 = 59 | CES98 = 71 |
| CES24 = 92 | CES49 = 65 | CES74 = 85 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)